




Metal Halide Lamp Ballast


Catalog Number 71A65F1T
For 1000W M141 (Pulse Start)
60 Hz CWA
Status: Active

DIMENSIONS AND DATA

4 1/4 X 4 3/4 CORE - 2 COIL UNIT




Capacitor: MD2409-100



Capacitance: 24
Dia/Oval Dim: 1.75
Height: 3.9
Temp Rating: 90°C

Ignitor:


LI572-H5



Ballast to Lamp Distance
(BTL) = 5 feet
Temp Rating: 105°C

INPUT VOLTS	347	480			
CIRCUIT TYPE	CWA				
POWER FACTOR (min)	90%				
REGULATION					
Line Volts	±10%				
Lamp Watts	±10%				
LINE CURRENT (Amps)					
Operating.....	3.10	2.25			
Open Circuit.....	1.50	1.10			
Starting.....	2.50	1.80			
UL TEMPERATURE RATINGS					
Insulation Class	N(200°C)				
Coil Temperature Code	1029				
MIN. AMBIENT STARTING TEMP.	-20°F or -30°C				
NOM. OPEN CIRCUIT VOLTAGE	415				
INPUT VOLTAGE AT LAMP DROPOUT.....	174	240			
INPUT WATTS	1070				
RECOMMENDED FUSE (Amps).....	8	6			
CORE and COIL					
Dimension (A)	3.32				
Dimension (B)	5.25				
Weight (lbs.)	19				
Lead Lengths	12"				
CAPACITOR REQUIREMENT					
Microfarads	24.0				
Volts (min.)	480				
Fault Current Withstand (amps)					
60 Hz TEST PROCEDURES (Refer to Advance Test Procedure for HID Ballasts - Form 1270)					
High Potential Test (Volts)					
1 minute	1500				
2 seconds	2500				
Open Circuit Voltage Test (Volts)	370-460				
Short-Circuit Current Test (Amps)					
Secondary Current	4.90-6.10				
Input Current.....	1.95-2.95	1.40-2.10	-	-	-

Wiring Diagram:



Ordering Information

Order Suffix

Description

Data is based upon tests performed by Advance Transformer in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

ADVANCE TRANSFORMER CO.

O'HARE INTERNATIONAL CENTER · 10275 WEST HIGGINS ROAD · ROSEMONT, IL 60018
Customer Support/Technical Service: Phone: 800-372-3331 · Fax: 847-768-7768
Corporate Offices: Phone: 800-322-2086

01/06/11