




Metal Halide Lamp Ballast


Catalog Number 71A6742A
For 1500W M48
60 Hz CWA
Status: Active

DIMENSIONS AND DATA




INPUT VOLTS	480				
CIRCUIT TYPE	CWA				
POWER FACTOR (min)	90%				
REGULATION					
Line Volts	±10%				
Lamp Watts	±12%				
LINE CURRENT (Amps)					
Operating.....	3.43				
Open Circuit.....	1.56				
Starting.....	2.94				
UL TEMPERATURE RATINGS					
Insulation Class	H(180°C)				
Coil Temperature Code	1029				
MIN. AMBIENT STARTING TEMP.	-20°F or -30°C				
NOM. OPEN CIRCUIT VOLTAGE	460				
INPUT VOLTAGE AT LAMP DROPOUT.....	320				
INPUT WATTS	1610				
RECOMMENDED FUSE (Amps).....	10				
CORE and COIL					
Dimension (A)	4.70				
Dimension (B)	6.70				
Weight (lbs.)	30				
Lead Lengths	12"				
CAPACITOR REQUIREMENT					
Microfarads	32.0				
Volts (min.)	525				
Fault Current Withstand (amps)					
60 Hz TEST PROCEDURES (Refer to Advance Test Procedure for HID Ballasts - Form 1270)					
High Potential Test (Volts)					
1 minute	2000				
2 seconds	2500				
Open Circuit Voltage Test (Volts)	414-506				
Short-Circuit Current Test (Amps)					
Secondary Current	7.13-8.72				
Input Current.....	2.41-3.62	-	-	-	-

Capacitor: MD3202-100



Capacitance: 32
Dia/Oval Dim: 2.00
Height: 3.75
Temp Rating: 90°C



Ordering Information

Order Suffix	Description
001	STANDARD IC PACK - OIL CAP - FLAG TERMINALS
500A	STANDARD -500 BALLAST WITH ALUMINUM SECONDARY COIL

Ignitor: NA

This ballast does not
require the use of an ignitor.

Data is based upon tests performed by Advance Transformer in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

ADVANCE TRANSFORMER CO.

O'HARE INTERNATIONAL CENTER · 10275 WEST HIGGINS ROAD · ROSEMONT, IL 60018
Customer Support/Technical Service: Phone: 800-372-3331 · Fax: 847-768-7768
Corporate Offices: Phone: 800-322-2086

03/26/10