

Philips LED Lamps

3.5W Candle (direct white)



Applicable Philips Part Numbers

9290002417(427799), 9290002419(427815), 9290002418(427781), 9290002420(427807), 9290002417(427765), 9290002419(427773)

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613			X
Leviton	SureSlide	6615P			X
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674		1-10 ¹	>10
Leviton	Trimatron	6681			X
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06			X
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU			X
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA ²		2-42 ¹	1
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA		1-8 ¹	>8
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA			X
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W			X
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²		1-42 ¹	

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P			X
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	10-21	1-10	
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2 ²		1-42 ¹	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-42 ¹	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²		1-42 ¹	
Lutron	Nova	NLV1000 ²		1-47* ¹	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²			X
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²		1-42	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P			X
Lutron	Skylark	SCL153P v2 ²		4-42 ¹	1-4
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors

Lutron	Skylark	MSCL-OP153MH	1-24
Lutron	Maestro	MS-OPS2H	1-24
Leviton	Decora	IPS02	
Leviton	Decora	IPS15	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.

All rights reserved. Updated 6/28/2013

PHILIPS

Philips LED Lamps

6W PAR16



Applicable Philips Part Numbers
423509(9000224204), 423418(9290002242), 429316(9290002443)

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Cooper	REACT	RI061-VW-K2				
Leviton	Decora	6161				
Leviton	SureSlide	6613		1-16 ¹	>16	
Leviton	SureSlide	6615P				X
Leviton	SureSlide	6631				
Leviton	SureSlide	6633P				
Leviton	SureSlide	6674		1-8 ¹	>8	
Leviton	Trimatron	6681		1-8 ¹	>8	
Leviton	Trimatron	6683				
Leviton	Trimatron	6684				
Leviton	IllumaTech	IPE04-1LZ				
Leviton	IllumaTech	IPI06		1-8	>8	
Leviton	Monet	MNE04-ILW				
Leviton	Monet	MNI06-1				
Lightolier	Vega	V600VAU		1-16 ¹	>16	
Lightolier	Vega	V1000VAU				
Lightolier	Sunrise	ZP600VA ²		1-25 ¹		
Lightolier	Sunrise	ZP600				
Lightolier	Vega	V600				
Lightolier	Onset	OS600				
Lightolier	Onset	OS600VA		1-8 ¹	>8	
Lightolier	Onset	OS1000VA				
Lightolier	Astral Slider	A600				
Lightolier	Astral Slider	AP600				
Lightolier	MultiSet	MHP600VA		1-8 ¹	>8	
Lightolier	Momentum	MP2000VAI				
WattStopper	Micro Decorator	DCD267-W		1-16 ¹	>16	
WattStopper	Architectural	ADMLV-703-W				
WattStopper	Architectural	AD-1103-W				
WattStopper	Paddle	PDMLV-703-W				
WattStopper	Paddle	PD-703-W				
WattStopper	Slide	SDMLV-603-W				
WattStopper	Slide	SD-603-W				
Lutron	Skylark	CTCL-153P				
Lutron	Diva	DVCL-153PD				
Lutron	Diva	DVCL-153P v2 ²				X

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Lutron	Diva	DVPDC-203				
Lutron	Diva	DV-600P		1-16 ¹	>16	
Lutron	Diva	DV-603PG				
Lutron	DIVA	DVELV-300P		1-12		
Lutron	Diva	DVWCL-153PDH				
Lutron	Glyder	GL-600P				
Lutron	Maestro	MAEL-153M v2 ²		1-8 ¹	>8	
Lutron	Maestro	MAELV-600				
Lutron	Maestro	MALV-600				
Lutron	Maestro	MRF2-600M				
Lutron	Maestro	MRF2-6ND-120		1-25 ¹		
Lutron	Grafik Eye	NGRX-PB				
Lutron	Nova	NLV600 ²		1-25 ¹		
Lutron	Nova	NLV1000 ²		1-29* ¹		
Lutron	Nova	NT-600-W				
Lutron	Nova	NT-1500-WH				
Lutron	Nova	NT-2000-WH				
Lutron	Fluo	NTF-10				
Lutron	Nova	NTELV-300				
Lutron	Grafik Eye	QSGR-3P ²		1-29* ¹		
Lutron	Qoto	Q-600P				
Lutron	RADIO RA	RRD-6NA ²		1-25		
Lutron	Skylark	S-600P				
Lutron	Skylark	SELV-300P				
Lutron	Skylark	SLV-600P		1-8 ¹	>8	
Lutron	Skylark	SCL153P v2 ²				X
Lutron	Toggler	TG-600P				
Lutron	Credenza	TT-300				
Lutron	Credenza	TTCL-100DH				
Lutron	Power Module	PHPM-WBX				
Lutron	Verti	VT600-B-AL				
Lutron	Verti	VTELV-600M-B				
Lutron	Verti	VTELV-600M-I				

Sensors			
Lutron	Skylark	MSCL-OP153MH	1-25
Lutron	Maestro	MS-OPS2H	1-25
Leviton	Decora	IPS02	
Leviton	Decora	IPS15	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.

All rights reserved. Updated 6/28/2013



Philips LED Lamps 8W PAR20/AirFlux



Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Cooper	REACT	RI061-VW-K2				
Leviton	Decora	6161				
Leviton	SureSlide	6613		1-3 ¹		
Leviton	SureSlide	6615P	1-6			
Leviton	SureSlide	6631				
Leviton	SureSlide	6633P				
Leviton	SureSlide	6674		1-3 ¹	>3	
Leviton	Trimatron	6681		1-6 ¹	>6	
Leviton	Trimatron	6683				
Leviton	Trimatron	6684				
Leviton	IllumaTech	IPE04-1LZ				
Leviton	IllumaTech	IPI06		1-10 ¹	>10	
Leviton	Monet	MNE04-ILW				
Leviton	Monet	MNI06-1				
Lightolier	Vega	V600VAU		1-13 ¹		
Lightolier	Vega	V1000VAU				
Lightolier	Sunrise	ZP600VA ²		1-10 ¹	>10	
Lightolier	Sunrise	ZP600				
Lightolier	Vega	V600				
Lightolier	Onset	OS600				
Lightolier	Onset	OS600VA		1-13 ¹		
Lightolier	Onset	OS1000VA				
Lightolier	Astral Slider	A600				
Lightolier	Astral Slider	AP600				
Lightolier	MultiSet	MHP600VA		1-13 ¹		
Lightolier	Momentum	MP2000VAI				
WattStopper	Micro Decorator	DCD267-W		1-13 ¹		
WattStopper	Architectural	ADMLV-703-W				
WattStopper	Architectural	AD-1103-W				
WattStopper	Paddle	PDMLV-703-W				
WattStopper	Paddle	PD-703-W				
WattStopper	Slide	SDMLV-603-W				
WattStopper	Slide	SD-603-W				
Lutron	Skylark	CTCL-153P				
Lutron	Diva	DVCL-153PD				
Lutron	Diva	DVCL-153P v2 ²		1-13 ¹		

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Applicable Philips Part Numbers

426171(9290002335), 426148(9290002332), 426122(9290002330), 426130(9290002331), 426155(9290002333), 426163(9290002334), 426114(9290002329), 428698(9290002329)

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Lutron	Diva	DVPDC-203				
Lutron	Diva	DV-600P		1-10 ¹	>10	
Lutron	Diva	DV-603PG				
Lutron	DIVA	DVELV-300P	1-6			
Lutron	Diva	DVWCL-153PDH				
Lutron	Glyder	GL-600P				
Lutron	Maestro	MACL-153M v2 ²		1-13 ¹		
Lutron	Maestro	MAELV-600				
Lutron	Maestro	MALV-600				
Lutron	Maestro	MRF2-600M				
Lutron	Maestro	MRF2-6ND-120		1-13 ¹		
Lutron	Grafik Eye	NGRX-PB				
Lutron	Nova	NLV600 ²		1-13 ¹		
Lutron	Nova	NLV1000 ²		1-23 ¹		
Lutron	Nova	NT-600-W				
Lutron	Nova	NT-1500-WH				
Lutron	Nova	NT-2000-WH				
Lutron	Fluo	NTF-10				
Lutron	Nova	NTELV-300				
Lutron	Grafik Eye	QSGR-3P ²		1-18 ¹		
Lutron	Qoto	Q-600P				
Lutron	RADIO RA	RRD-6NA ²	1-13			
Lutron	Skylark	S-600P				
Lutron	Skylark	SELV-300P				
Lutron	Skylark	SLV-600P		1-13 ¹		
Lutron	Skylark	SCL153P v2 ²		1-13 ¹		
Lutron	Toggler	TG-600P				
Lutron	Credenza	TT-300				
Lutron	Credenza	TTCL-100DH				
Lutron	Power Module	PHPM-WBX				
Lutron	Verti	VT600-B-AL				
Lutron	Verti	VTELV-600M-B				
Lutron	Verti	VTELV-600M-I				

Sensors

Lutron	Skylark	MSCL-OP153MH	
Lutron	Maestro	MS-OPS2H	
Leviton	Decora	IPS02	
Leviton	Decora	IPS15	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.

All rights reserved. Updated 6/28/2013

Philips LED Lamps

8W R20



Applicable Philips Part Numbers
420331(9290002192), 423400(9290002192), 428813(9290002192)

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-18		
Leviton	SureSlide	6615P	1-9		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-14		>14
Leviton	Trimatron	6681	1-8	9-10	>10
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-18	
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-18		
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA ²	1-18		
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA	1-8		>8
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA	1-10		>10
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-18		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²	1-18		

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-8	9-10	>10
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P			X
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2 ²		1-18 ¹	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-18		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²	1-18		
Lutron	Nova	NLV1000 ²	1-18		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²			X
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-18		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-8	9-18	
Lutron	Skylark	SCL153P v2 ²		1-18	
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors			
Lutron	Skylark	MSCL-OP153MH	1-18
Lutron	Maestro	MS-OPS2H	1-18
Leviton	Decora	IPS02	
Leviton	Decora	IPS15	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 6/28/2013



Philips LED Lamps
8W A19 Bulb (White)
40W Equivalent



Applicable Philips Part Numbers
 423483(9290002267), 424374(9290002267), 425256(9290002295),
 429266(9290002267)

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Cooper	REACT	RI061-VW-K2				
Leviton	Decora	6161				
Leviton	SureSlide	6613			1-12	>12
Leviton	SureSlide	6615P		1-9		
Leviton	SureSlide	6631				
Leviton	SureSlide	6633P				
Leviton	SureSlide	6674				X
Leviton	Trimatron	6681				X
Leviton	Trimatron	6683				
Leviton	Trimatron	6684				
Leviton	IllumaTech	IPE04-1LZ				
Leviton	IllumaTech	IPI06		1-9		>9
Leviton	Monet	MNE04-ILW				
Leviton	Monet	MNI06-1				
Lightolier	Vega	V600VAU		1-13		
Lightolier	Vega	V1000VAU				
Lightolier	Sunrise	ZP600VA ²				X
Lightolier	Sunrise	ZP600				
Lightolier	Vega	V600				
Lightolier	Onset	OS600				
Lightolier	Onset	OS600VA		1-13		
Lightolier	Onset	OS1000VA				
Lightolier	Astral Slider	A600				
Lightolier	Astral Slider	AP600				
Lightolier	MultiSet	MHP600VA				X
Lightolier	Momentum	MP2000VAI				
WattStopper	Micro Decorator	DCD267-W		2-13 ¹		1
WattStopper	Architectural	ADMLV-703-W				
WattStopper	Architectural	AD-1103-W				
WattStopper	Paddle	PDMLV-703-W				
WattStopper	Paddle	PD-703-W				
WattStopper	Slide	SDMLV-603-W				
WattStopper	Slide	SD-603-W				
Lutron	Skylark	CTCL-153P				
Lutron	Diva	DVCL-153PD				
Lutron	Diva	DVCL-153P v2 ²		1-18		

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Lutron	Diva	DVPDC-203				
Lutron	Diva	DV-600P		1-6		>6
Lutron	Diva	DV-603PG				
Lutron	DIVA	DVELV-300P			1-9	
Lutron	Diva	DVWCL-153PDH				
Lutron	Glyder	GL-600P				
Lutron	Maestro	MACL-153M v2 ²		1-12		>12
Lutron	Maestro	MAELV-600				
Lutron	Maestro	MALV-600				
Lutron	Maestro	MRF2-600M				
Lutron	Maestro	MRF2-6ND-120		1-12		>12
Lutron	Grafik Eye	NGRX-PB				
Lutron	Nova	NLV600 ²		1-8	8-11	>11
Lutron	Nova	NLV1000 ²		1-8	8-11	>11
Lutron	Nova	NT-600-W				
Lutron	Nova	NT-1500-WH				
Lutron	Nova	NT-2000-WH				
Lutron	Fluo	NTF-10				
Lutron	Nova	NTELV-300				
Lutron	Grafik Eye	QSGR-3P ²		1-17		
Lutron	Qoto	Q-600P				
Lutron	RADIO RA	RRD-6NA ²		1-13		
Lutron	Skylark	S-600P				
Lutron	Skylark	SELV-300P				
Lutron	Skylark	SLV-600P			1-12	>12
Lutron	Skylark	SCL153P v2 ²		1-18		
Lutron	Toggler	TG-600P				
Lutron	Credenza	TT-300				
Lutron	Credenza	TTCL-100DH				
Lutron	Power Module	PHPM-WBX				
Lutron	Verti	VT600-B-AL				
Lutron	Verti	VTELV-600M-B				
Lutron	Verti	VTELV-600M-I				

Sensors			
Lutron	Skylark	MSCL-OP153MH	1-18
Lutron	Maestro	MS-OPS2H	1-18
Leviton	Decora	IPS02	
Leviton	Decora	IPS15	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 6/28/2013



Philips LED Lamps
11W A19 Bulb (White)
60W Equivalent



Applicable Philips Part Numbers	
423491(9290002268), 424382(9290002268), 425264(9290002296), 429258(9290002268)	

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2		1-2 ¹	>3
Leviton	Decora	6161			
Leviton	SureSlide	6613		1-13 ¹	
Leviton	SureSlide	6615P		1-4 ¹	>4
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674		1-4 ¹	>4
Leviton	Trimatron	6681			X
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06			X
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU		1-13 ¹	
Lightolier	Vega	V1000VAU		1-11* ¹	
Lightolier	Sunrise	ZP600VA ²		1-2 ¹	>2
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA		1-13 ¹	
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA		1-2 ¹	>2
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W		1-13 ¹	
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W		1-12 ¹	
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W		1-8 ¹	>8
WattStopper	Slide	SD-603-W		1-8 ¹	>8
Lutron	Skylark	CTCL-153P		1-5 ¹	>5
Lutron	Diva	DVCL-153PD		1-13 ¹	
Lutron	Diva	DVCL-153P v2 ²		1-13 ¹	

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P		1-4 ¹	>4
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P		1-6 ¹	
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2		1-13 ¹	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-13 ¹	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600		1-13 ¹	
Lutron	Nova	NLV1000		1-13* ¹	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P per zone		1-13* ¹	
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA		1-13* ¹	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-13 ¹	
Lutron	Skylark	SCL153P v2		1-13* ¹	
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors		
Lutron	Skylark	MSCL-OP153MH
Lutron	Maestro	MS-OPS2H
Leviton	Decora	IPS02
Leviton	Decora	IPS15

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 6/28/2013



Philips LED Lamps 13W BR30 AirFlux



Applicable Philips Part Numbers

420554(9290002197), 420281(9290002198), 423798(9290002197), 429282(9290002197)

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-11		
Leviton	SureSlide	6615P	1-5		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-11		
Leviton	Trimatron	6681		1-8	>8
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-11		
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-11		
Lightolier	Vega	V1000VAU	1-16*		
Lightolier	Sunrise	ZP600VA ²	1-11		
Lightolier	Sunrise	ZP600		1-5	>5
Lightolier	Vega	V600			
Lightolier	Onset	OS600			X
Lightolier	Onset	OS600VA	1-11		
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600		1-7	>7
Lightolier	MultiSet	MHP600VA	1-11		
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-11		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P	1-11		
Lutron	Diva	DVCL-153PD		1-11	
Lutron	Diva	DVCL-153P v2 ²	1-11		

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P		1-11	
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P		1-5	
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2 ²		1-11	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600		1-11	
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-11	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²		1-11	
Lutron	Nova	NLV1000 ²		1-16*	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²		1-11*	
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²		1-11	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-11	
Lutron	Skylark	SCL153P v2 ²		1-11 ¹	
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors

Lutron	Skylark	MSCL-OP153MH			
Lutron	Maestro	MS-OPS2H			
Leviton	Decora	IPS02			
Leviton	Decora	IPS15			

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 6/28/2013

PHILIPS

Philips LED Lamps

13W BR30 AirFlux DimTone



Applicable Philips Part Numbers

426445(9290002344)

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2		1-11 ¹	
Leviton	Decora	6161			
Leviton	SureSlide	6613		1-11 ¹	
Leviton	SureSlide	6615P		1-5 ¹	
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674		1-4 ¹	>4
Leviton	Trimatron	6681		1-4 ¹	>4
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ		1-8 ¹	
Leviton	IllumaTech	IPI06		1-7 ¹	>7
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU		1-11 ¹	
Lightolier	Vega	V1000VAU		1-16* ¹	
Lightolier	Sunrise	ZP600VA ²		1-5 ¹	>5
Lightolier	Sunrise	ZP600			X
Lightolier	Vega	V600			
Lightolier	Onset	OS600			X
Lightolier	Onset	OS600VA		1-11 ¹	
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600		1-11 ¹	
Lightolier	MultiSet	MHP600VA		1-6 ¹	>6
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W		1-11 ¹	
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD		1-11 ¹	
Lutron	Diva	DVCL-153P v2 ²		1-11 ¹	

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Diva	DVPDC-203		1-11 ¹	
Lutron	Diva	DV-600P		1-5 ¹	>5
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P		1-5 ¹	
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2 ²		1-11 ¹	
Lutron	Maestro	MAELV-600		1-11 ¹	
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-11 ¹	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²		1-11 ¹	
Lutron	Nova	NLV1000 ²		1-16* ¹	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300		1-5 ¹	
Lutron	Grafik Eye	QSGR-3P ²		1-13* ¹	
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²		1-11 ¹	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-11 ¹	
Lutron	Skylark	SCL153P v2 ²		1-11 ¹	
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors

Lutron	Skylark	MSCL-OP153MH			
Lutron	Maestro	MS-OPS2H			
Leviton	Decora	IPS02			
Leviton	Decora	IPS15			

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 6/28/2013

Philips LED Lamps

13W PAR30S and PAR30L AirFlux



Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			X
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-11		
Leviton	SureSlide	6615P	1-5		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-11		
Leviton	Trimatron	6681			X
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-2	>2
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-11		
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA ²	1-11		
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA	1-8		>8
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA	1-11		
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-11		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD		1-11	
Lutron	Diva	DVCL-153P v2 ²	1-11		

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Applicable Philips Part Numbers

9290002304(425371), 9290002306(425397), 9290002302(425355), 9290002303(425363), 9290002305(425389), 9290002284(423442), 9290002286(423459), 9290002285(423467), 9290002287(423475), 9290002301(425348), 9290002300(425330), 9290002233(420471), 9290002234(420497), 9290002235(420505), 9290002244(420802), 9290002201(420315), 9290002323(425298)

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-11		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-5		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2 ²	1-11		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M	1-11		
Lutron	Maestro	MRF2-6ND-120	1-11		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²	1-11		
Lutron	Nova	NLV1000 ²	1-16*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²	1-11*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-11		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-11		
Lutron	Skylark	SCL153P v2 ²	1-11		
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors

Lutron	Skylark	MSCL-OP153MH			
Lutron	Maestro	MS-OPS2H			
Leviton	Decora	IPS02			
Leviton	Decora	IPS15			

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 6/28/2013

Philips LED Lamps

14W BR40 AirFlux



Applicable Philips Part Numbers
9290002199(420562), 9290002199(423756)

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2		1-10	
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-10		
Leviton	SureSlide	6615P			X
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-10		
Leviton	Trimatron	6681	1-10		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-10	
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-10		
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA ²	1-10		
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA	1-10		
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA	1-10		
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-10		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²	1-10		

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-10		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-5		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MAEL-153M v2 ²	1-10		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-10		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²	1-10		
Lutron	Nova	NLV1000 ²	1-10*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²	1-10*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-10		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-10		
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors		
Lutron	Skylark	MSCL-OP153MH
Lutron	Maestro	MS-OPS2H
Leviton	Decora	IPS02
Leviton	Decora	IPS15

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 6/28/2013



Philips LED Lamps
17W A21 Bulb (Remote Phosphor)
75W Equivalent



Applicable Philips Part Numbers	
17E26A21D(418590), 9290002018(422220)	

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613		1-8 ¹	
Leviton	SureSlide	6615P		1-4 ¹	
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674		1-8 ¹	
Leviton	Trimatron	6681		1-6 ¹	>6
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IP106		1-8 ¹	
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU		1-5 ¹	
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA ²		1-8 ¹	
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA		1-8 ¹	
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA		1-8 ¹	
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W		1-8 ¹	
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P		1-8 ¹	
Lutron	Diva	DVCL-153PD		1-4 ¹	
Lutron	Diva	DVCL-153P v2 ²		1-8 ¹	

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Diva	DVPDC-203			X
Lutron	Diva	DV-600P		1-8 ¹	
Lutron	Diva	DV-603PG		1-8 ¹	
Lutron	DIVA	DVELV-300P		1-4 ¹	
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P		1-8 ¹	
Lutron	Maestro	MACL-153M v2 ²		1-8 ¹	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-8 ¹	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²		1-8 ¹	
Lutron	Nova	NLV1000 ²		1-14 ¹	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²		1-11* ¹	
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²		1-8 ¹	
Lutron	Skylark	S-600P		1-8 ¹	
Lutron	Skylark	SELV-300P		1-8 ¹	
Lutron	Skylark	SLV-600P		1-4 ¹	>4
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggle	TG-600P		1-4 ¹	>4
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors		
Lutron	Skylark	MSCL-OP153MH
Lutron	Maestro	MS-OPS2H
Leviton	Decora	IPS02
Leviton	Decora	IPS15

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 6/28/2013



Philips LED Lamps

18W PAR38 AirFlux



Applicable Philips Part Numbers
9290002309(425421), 9290002311(425447), 9290002307(425405), 9290002308(425413), 9290002310(425439), 9290002236(420513), 9290002237(420521), 9290002245(420885), 9290002246(420893)

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-8		
Leviton	SureSlide	6615P		1-4 ¹	
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-8		
Leviton	Trimatron	6681		1-8 ¹	
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-8		
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-8		
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA ²	1-8		
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA		1-8 ¹	
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA	1-8		
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W		1-8 ¹	
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²	1-8		

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-8		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-4		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2 ²		1-8 ¹	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-8		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²		1-13 ¹	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²		1-11 ¹	
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-8		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-8 ¹	
Lutron	Skylark	SCL153P v2 ²	1-8		
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors		
Lutron	Skylark	MSCL-OP153MH
Lutron	Maestro	MS-OPS2H
Leviton	Decora	IPS02
Leviton	Decora	IPS15

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 6/28/2013



Philips LED Lamps

19.5W PAR38 AirFlux



Applicable Philips Part Numbers
9290002316(425496), 9290002317(425504), 9290002291(423350), 9290002312(425454), 9290002314(425470), 9290002252(421214), 9290002253(421222), 9290002313(425462), 9290002315(425488), 9290002251(423426), 9290002321(425272), 9290002322(425280)

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2			X
Leviton	Decora	6161			
Leviton	SureSlide	6613		1-7 ¹	
Leviton	SureSlide	6615P		1-3 ¹	
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674		1-7 ¹	
Leviton	Trimatron	6681		1-7 ¹	
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-7 ¹	
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-7		
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA ²	1-7		
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA	1-7		
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA	1-7		
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W		1-7 ¹	
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W	1-7		
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W	1-7		
WattStopper	Slide	SD-603-W	1-7		
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD		1-7	
Lutron	Diva	DVCL-153P v2 ²		1-7 ¹	

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P		1-7 ¹	
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-3		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MAELV-153M v2 ²		1-7 ¹	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-7 ¹	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²	1-7		
Lutron	Nova	NLV1000 ²	1-12		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²	1-7*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²		1-7 ¹	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-7 ¹	
Lutron	Skylark	SCL153P v2 ²		1-7 ¹	
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors		
Lutron	Skylark	MSCL-OP153MH
Lutron	Maestro	MS-OPS2H
Leviton	Decora	IPS02
Leviton	Decora	IPS15

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 6/28/2013



Philips LED Lamps
22W A21 Bulb
100W Equivalent



Applicable Philips Part Numbers	
9290002290(423525), 9290002290(424432)	

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			X
Leviton	Decora	6161			
Leviton	SureSlide	6613			X
Leviton	SureSlide	6615P			X
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674			X
Leviton	Trimatron	6681			X
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-6 ¹	
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU			X
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA ²		1-6 ¹	
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA		1-6 ¹	
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA		1-6 ¹	
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W		1-6 ¹	
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			X
Lutron	Diva	DVCL-153P v2 ²			X

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P			X
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P			X
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2 ²		1-6 ¹	
Lutron	Maestro	MAELV-600		1-6 ¹	
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-6 ¹	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²		1-6 ¹	
Lutron	Nova	NLV1000 ²		1-10 ¹	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²		1-8 ¹	
Lutron	Qoto	Q-600P			X
Lutron	RADIO RA	RRD-6NA ²		1-6 ¹	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P		1-6	
Lutron	Skylark	SLV-600P		1-6 ¹	
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors		
Lutron	Skylark	MSCL-OP153MH
Lutron	Maestro	MS-OPS2H
Leviton	Decora	IPS02
Leviton	Decora	IPS15

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.

All rights reserved. Updated 6/28/2013



Philips LED Lamps
10.5W SlimStyle A19 Bulb
60W Equivalent



Applicable Philips Part Numbers
 9290002709(433235), 9290002709(433151), 9290002707(433227),
 9290002707(433144)

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-14		
Leviton	SureSlide	6615P		1-5	
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-14		
Leviton	Trimatron	6681		1-14	
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-14		
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU			
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA ²			
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA			
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA			
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-14		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²		1-14	

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P		1-14	
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P		1-5	
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2 ²		1-14	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-14	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²		1-14*	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²		1-14*	
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²		1-14	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-8	
Lutron	Skylark	SCL153P v2 ²		1-14	
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors			
Lutron	Skylark	MSCL-OP153MH	
Lutron	Maestro	MS-OPS2H	
Leviton	Decora	IPS02	
Leviton	Decora	IPS15	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 2/26/14



Philips LED Lamps
8W SlimStyle A19 Bulb
40W Equivalent



Applicable Philips Part Numbers	
9290002706(433219), 9290002706(433136), 9290002704(433201), 9290002704(433128)	

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-18		
Leviton	SureSlide	6615P	1-8		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-18		
Leviton	Trimatron	6681	1-18		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-18		
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU			
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA ²			
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA			
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA			
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-18		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²		1-18	

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-18		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-8		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2 ²	1-18		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-18		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²		1-18*	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²	1-18*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-18		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-11		
Lutron	Skylark	SCL153P v2 ²		1-18	
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors			
Lutron	Skylark	MSCL-OP153MH	
Lutron	Maestro	MS-OPS2H	
Leviton	Decora	IPS02	
Leviton	Decora	IPS15	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 2/26/14

