



PHILIPS

Landscape



Luminaire Smart Service Guide

U.S. Service Smart and Spec Smart
product portfolio for Landscape luminaires

Updated October 2014

Contents

Accent LED - Line Voltage	4
Accent LED - Low Voltage	5
Accent - Line Voltage	6
Accent - Line Voltage Accessories	7
Accent - Low Voltage	8-9
Beacon - Line Voltage	9
Beacon - Low Voltage	9
Bollard LED - Line Voltage	10
Bollard - Line Voltage	10
Deck Light LED - Low Voltage	11
Deck Light - Low Voltage	11
Down Light LED - Low Voltage	12
Down Light - Low Voltage	12
Inground/ Ingrade LED - Line Voltage	13
Inground/ Ingrade LED - Low Voltage	13
Inground/ Ingrade - Line Voltage	14
Inground/ Ingrade - Line Voltage Accessories	14
Inground/ Ingrade - Low Voltage	15
Inground/ Ingrade - Low Voltage Accessories	15
Landscape Accessories, General	16-17
Mini Flood/Wall Washer LED - Line Voltage	18
Mini Flood/Wall Washer LED - Low Voltage	18
Mini Flood/Wall Washer - Line Voltage	18
Mini Flood/Wall Washer - Low Voltage	19
Path Light LED - Low Voltage	19
Path Light - Line Voltage	20
Path Light - Low Voltage	20-21
Path Light Accessories	21
Step Light LED - Line Voltage	22
Step Light - Line Voltage	22
Step Light - Low Voltage	23
Step Light Accessories	23
Transformers/Power Supply	23
Underwater LED - Low Voltage	24
Underwater - Line Voltage	24
Underwater - Low Voltage	24
Lamp Holders	24



About this guide

This guide was created specifically for the landscape product portfolio and mainly includes A (Service Smart) and B (Spec Smart) products from the Hadco brand. You will also find a limited selection of Gardco products in this particular guide. The goal of our service program is to ensure we fully support your shelf-stocking requirements and provide you with reliable leadtimes to address the demanding timelines of new construction and retrofit lighting projects. This program allows you to select the product and corresponding lead time to meet the needs of your specific customer's project.

In this new Smart Service Guide, you will find all Service Smart and Spec Smart items, stock locations, as well as an indication of our recommended distributor shelf stock items. Please refer to the separate Luminaire Smart Service Guide for our Indoor and Outdoor (other than landscape) product portfolio that fits the aforementioned criteria.

To support this service program, we have developed the following categories:

- **Service Smart products** are in stock and will be shipped in 48hrs from our warehouses*.
- **Distributor Stock products** are a subset of the Service Smart items that should be maintained on distributor shelves at all times to manage everyday contractor demand.
- **Spec Smart products** will be assembled to order and ship within 2 weeks from our factories*.

* Service promise is calculated from the time the order is entered until it is shipped.

Philips

Luminaire Smart Service Guide

Our commitment to you

Our delivery promise is backed by a significant investment in finished goods and component inventory. If any unforeseen issues arise or if order volume exceeds maximum order quantity, we will do our best to meet your needs and confirm an acceptable ship date.

Standard lead time products will ship within 4 weeks, while lead times for special, made to order and custom configured products can be confirmed by contacting the order desk.

Lead time is from the time the order is entered and received by our warehouse. Our goal is to enter orders within 1 business day of receipt.

To enable fast order entry, orders must be received with complete and correct catalog numbers and reference to the source of pricing (i.e. quote number or pricing program). It is recommended that you reference “Smart Guide” on your orders for product in this guide to speed the order entry process.

In order to avoid delays, it is recommended that stock orders be “stand alone” so that they may be shipped within the promised time-frame.

To ensure we satisfy all our customers optimally and meet the committed lead times, maximum order quantities may apply. If the order exceeds the set threshold, Philips will contact you to work out a feasible schedule for your large order. It is always advised to work with your Philips representative to give advance notice of your large order.

Stock availability

Philips Lighting maintains stock levels of items in this landscape guide in the Carrollton, TX warehouse. Look for the code in the “Stocked In” column of this Smart Service Guide.



In case you have questions, please contact your sales representative or Customer Service.

Philips Contact Center: 1-855-486-2216

Terms and Conditions

Freight Terms: Individual order Minimum of \$1,000;
\$100 shipping and handling fee for orders less than \$1,000.
1% 10th Prox 2nd, Net 25th Prox 2nd for Stock Orders
1% 10th Prox, Net 25th Prox for Drop Ship/Project Business

Warehouse legend

C = Carrollton, Texas



Landscape



Accent LED - Line Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352016836	B1-ALED7NFWL	120V, LED, Warm, 7 Watts, Narrow Flood, Small Aluminum Bullet w/ Shroud, Black	✓		C
783352016775	B1-ALED7NFWS	120V, LED, Warm, 7 Watts, Narrow Flood, Small Aluminum Bullet w/ Shroud, Black	✓		C
783352016850	B1-HLED7NFWL	120V, LED, Warm, 7 Watts, Narrow Flood, Small Aluminum Bullet w/ Shroud, Bronze	✓		C
783352016812	B1-GLED7NFWS	120V, LED, Warm, 7 Watts, Narrow Flood, Small Aluminum Bullet w/ Shroud, Verde	✓		C
783352017999	B1-HLED7NFWS	120V, LED, Warm, 7 Watts, Narrow Flood, Small Aluminum Bullet w/ Shroud, Bronze	✓		C
783352017956	B3-ALED13NFW	120V, LED, Warm, 13 Watts, Narrow Flood, Medium Aluminum Bullet w/ Shroud, Black	✓		C
783352018007	B3-HLED13NFW	120V, LED, Warm, 13 Watts, Narrow Flood, Medium Aluminum Bullet w/ Shroud, Bronze	✓		C
783352016928	B4-ALED18NFWL	120V, LED, Warm, 18 Watts, Narrow Flood, Large Bullet / Long Shroud, Black	✓		C
783352016935	B4-HLED18NFWL •	120V, LED, Warm, 18 Watts, Narrow Flood, Large Bullet / Long Shroud, Bronze	✓		C
783352016904	B4-HLED18NFWS	120V, LED, Warm, 18 Watts, Narrow Flood, Large Bullet / Short Shroud, Bronze	✓		C
---	BN4-HL	120V, 150W, E17 HID, Large Aluminum Bullet w/Reflector & Long Shroud, Bronze		✓	
---	BN4-HS	120V, 150W, E17 HID, Large Aluminum Bullet w/Reflector & Short Shroud, Bronze		✓	
783352017468	BT1-ALED7FLCS	120V, LED, Cool, 7 Watts, Flood, Small Bullet W/ Short Shroud, Black	✓		C
783352017376	BT1-ALED7SPWL	120V, LED, Warm, 7 Watts, Spot, Small Bullet W/ Long Shroud, Black	✓		C
783352017567	BT1-HLED7FLCL	120V, LED, Cool, 7 Watts, Flood, Small Bullet W/Long Shroud, Bronze	✓		C
783352017581	BT1-HLED7FLCS	120V, LED, Cool, 7 Watts, Flood, Small Bullet W/Short Shroud, Bronze	✓		C
783352017765	BT5016-ALED4NFW •	120V, LED, Warm, 4 Watts, Narrow Flood, Micro Bullet, Black	✓		C
783352017703	BT5016-ALED7FLW	120V, LED, Warm, 7 Watts, Flood, Micro Bullet, Black	✓		C
783352017734	BT5016-HLED7FLC	120V, LED, Cool, 7 Watts, Flood, Micro Bullet, Bronze	✓		C
783352017727	BT5016-HLED7FLW •	120V, LED, Warm, 7 Watts, Flood, Micro Bullet, Bronze	✓		C
783352017673	BT5016-HLED7NFC	120V, LED, Cool, 7 Watts, Narrow Flood, Micro Bullet, Bronze	✓		C
783352017666	BT5016-HLED7NFW	120V, LED, Warm, 7 Watts, Narrow Flood, Micro Bullet, Bronze	✓		C
783352018106	BU3-ALED13NFW	120V, LED, Warm, 12 Watts, Narrow Flood, Medium Ultem Composite Bullet, Black	✓		C
783352018205	BU3-GLED13NFW	120V, LED, Warm, 12 Watts, Narrow Flood, Medium Ultem Composite Bullet, Verde	✓		C

C = Carrollton, Texas

A blue dot "•" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.



Accent LED - Low Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352017154	BL5016-AS7LED4NFW ●	12V, LED, Warm, 4 Watts, Narrow Flood, Micro Bullet W/Stake, Black	✓		C
783352017086	BL5016-AS7LED7FLC	12V, LED, Cool, 7 Watts, Flood, Micro Bullet W/Stake, Black	✓		C
783352017079	BL5016-AS7LED7FLW ●	12V, LED, Warm, 7 Watts, Flood, Micro Bullet W/Stake, Black	✓		C
783352017000	BL5016-AS7LED7NFC	12V, LED, Cool, 7 Watts, Narrow Flood, Micro Bullet W/Stake, Black	✓		C
783352016997	BL5016-AS7LED7NFW ●	12V, LED, Warm, 7 Watts, Narrow Flood, Micro Bullet W/Stake, Black	✓		C
783352016959	BL5016-AS7LED7SPW ●	12V, LED, Warm, 7 Watts, Spot, Micro Bullet W/Stake, Black	✓		C
783352017116	BL5016-GS7LED7FLW	12V, LED, Warm, 7 Watts, Flood, Micro Bullet W/Stake, Verde	✓		C
783352017031	BL5016-GS7LED7NFW	12V, LED, Warm, 7 Watts, Narrow Flood, Micro Bullet W/Stake, Verde	✓		C
783352016973	BL5016-GS7LED7SPW	12V, LED, Warm, 7 Watts, Spot, Micro Bullet W/Stake, Verde	✓		C
783388020487	BL5016-HS7LED4NFC	12V, LED, Cool, 4 Watts, Narrow Flood, Micro Bullet W/Stake, Bronze	✓		C
783352017161	BL5016-HS7LED4NFW ●	12V, LED, Warm, 4 Watts, Narrow Flood, Micro Bullet W/Stake, Bronze	✓		C
783352016966	BL5016-HS7LED7SPW ●	12V, LED, Warm, 7 Watts, Spot, Micro Bullet W/Stake, Bronze	✓		C
783352017109	BL5016-HS7LED7FLC ●	12V, LED, Cool, 7 Watts, Flood, Micro Bullet W/Stake, Bronze	✓		C
783352017093	BL5016-HS7LED7FLW ●	12V, LED, Warm, 7 Watts, Flood, Micro Bullet W/Stake, Bronze	✓		C
783352017024	BL5016-HS7LED7NFC ●	12V, LED, Cool, 7 Watts, Narrow Flood, Micro Bullet W/Stake, Bronze	✓		C
783352017017	BL5016-HS7LED7NFW ●	12V, LED, Warm, 7 Watts, Narrow Flood, Micro Bullet W/Stake, Bronze	✓		C
783352016966	BL5016-TS7LED4NFW	12V, LED, Warm, 4 Watts, Narrow Flood, Micro Bullet W/Stake, Speckled Stone	✓		C
783352017185	BL5016-TS7LED7FLW	12V, LED, Warm, 7 Watts, Flood, Micro Bullet W/Stake, Speckled Stone	✓		C
783352017130	BL5016-TS7LED7SPW ●	12V, LED, Warm, 7 Watts, Spot, Micro Bullet W/Stake, Speckled Stone	✓		C
783352016980	BL616-AS7LED4NFW	12V, LED, Warm, 4 Watts, Narrow Flood, Micro Bullet W/Stake, Black	✓		C
783352017345	BL616-AS7LED7FLC	12V, LED, Cool, 7 Watts, Flood, Micro Bullet W/Stake, Black	✓		C
783352017291	BL616-AS7LED7FLW	12V, LED, Warm, 7 Watts, Flood, Micro Bullet W/Stake, Black	✓		C
783352017284	BL616-GS7LED4NFW	12V, LED, Warm, 4 Watts, Flood, Micro Bullet W/Stake, Verde	✓		C
783352017369	BL616-HS7LED7FLC	12V, LED, Warm, 7 Watts, Flood, Micro Bullet W/Stake, Bronze	✓		C
783352017314	BL616-HS7LED7FLW	12V, LED, Cool, 7 Watts, Flood, Micro Bullet W/Stake, Bronze	✓		C
783352017307	BL616-HS7LED7SPW	12V, LED, Warm, 7 Watts, Spot, Micro Bullet W/Stake, Bronze	✓		C
783352017208	BL7D1FC-AS7	12V, LED, Cool, 1.6 Watts, Frosted Lens, Micro Bullet W/Stake, Black	✓		C
---	BL7D1FW-AS7	12V, LED, Warm, 1.6 Watts, Frosted Lens, Micro Bullet W/Stake, Black		✓	
---	BL7D1FW-HS7	12V, LED, Warm, 1.6 Watts, Frosted Lens, Micro Bullet W/Stake, Bronze		✓	
---	MA5SPDHW-HLS7	12V, LED, Warm, 6.2 Watts, Spot, Medium Machined Accent LED Long Shroud, Bronze		✓	
---	MA5SPDLW-HS7	12V, LED, Warm, 6.2 Watts, Spot, Medium Machined Accent LED, Bronze		✓	
---	MA5SPDLW-HLS7	12V, LED, Warm, 5.1 Watts, Spot, Medium Machined Accent LED Long Shroud, Bronze		✓	
---	MA5SPDLW-HS7	12V, LED, Warm, 5.1 Watts, Spot, Medium Machined Accent LED, Bronze		✓	
---	MA7DW-HLS7	12V, LED, Warm, Small Machined Accent LED Shroud, Bronze		✓	
---	MA7DW-HS7	12V, LED, Warm, Small Machined Accent LED Shroud, Bronze		✓	
---	MA7DC-ALS7	12V, LED, Cool, Small Machined Accent LED Shroud, Black		✓	
---	MA7DC-AS7	12V, LED, Cool, Small Machined Accent LED, Black		✓	
---	MA7DW-ALS7	12V, LED, Warm, Small Machined Accent LED Shroud, Black		✓	
---	MA7DW-AS7	12V, LED, Warm, Small Machined Accent LED, Black		✓	
783361020213	BL9DW-AS7	12V, LED, Warm, Small Architectural Accent LED, FlexScape, Black	✓		C
783362020229	BL9DW-HS7	12V, LED, Warm, Small Architectural Accent LED, FlexScape, Bronze	✓		C
783363020235	BL9DC-AS7	12V, LED, Cool, Small Architectural Accent LED, FlexScape, Black	✓		C
783364020241	BL9DC-HS7	12V, LED, Cool, Small Architectural Accent LED, FlexScape, Bronze	✓		C

C = Carrollton, Texas

A blue dot "●" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.



Accent - Line Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352002341	1020-H ●	120V, 150W, PAR 38, Large Classic, Bronze	✓		C
783352003485	B1-A ●	120V, 100W, PAR/R20, Small Aluminum Bullet, Black	✓		C
783352003508	B1-G ●	120V, 100W, PAR/R20, Small Aluminum Bullet, Verde	✓		C
783352003515	B1-H ●	120V, 100W, PAR/R20, Small Aluminum Bullet, Bronze	✓		C
783352003539	B1-NL ●	120V, 100W, PAR/R20, Small Brass Bullet w/ Shroud, Natural Bronze	✓		C
783352003546	B1-OBL	120V, 100W, PAR/R20, Small Brass Bullet w/ Shroud, Oiled Brass	✓		C
783352003577	B3-A ●	120V, 100W, PAR/R30, Medium Aluminum Bullet w/ Shroud, Black	✓		C
783352003584	B3-G	120V, 100W, PAR/R30, Medium Aluminum Bullet w/ Shroud, Verde	✓		C
783352003591	B3-H ●	120V, 100W, PAR/R30, Medium Aluminum Bullet w/ Shroud, Bronze	✓		C
783352003614	B4-A ●	120V, 300W, R40, Large Bullet, Black	✓		C
783352003638	B4-G	120V, 300W, R40, Large Bullet, Verde	✓		C
783352003645	B4-H ●	120V, 300W, R40, Large Bullet, Bronze	✓		C
---	BF432-AS	120V, 32W, CFL, Large Bullet / Short Shroud, Black		✓	
---	BN4-AS	120V, 150W, E17 HID, Large Aluminum Bullet w/Reflector & Short Shroud, Black		✓	
783352004994	BT5016-A ●	120V, 50W, MR16, Micro Bullet W/ Integral Transformer, Black	✓		C
783352005014	BT5016-H ●	120V, 50W, MR16, Micro Bullet W/ Integral Transformer, Black	✓		C
783352005052	BU1-A ●	120V, 50W, PAR/R20, Small Ultem Composite Bullet, Black	✓		C
783352005069	BU1-G ●	120V, 50W, PAR/R20, Small Ultem Composite Bullet, Verde	✓		C
783352005076	BU1-H ●	120V, 50W, PAR/R20, Small Ultem Composite Bullet, Black	✓		C
783352005083	BU3-A ●	120V, 75W PAR30, Medium Ultem Composite Bullet, Black	✓		C
783352005090	BU3-G ●	120V, 75W PAR30, Medium Ultem Composite Bullet, Verde	✓		C
783352005106	BU3-H ●	120V, 75W PAR30, Medium Ultem Composite Bullet, Bronze	✓		C
783352005113	BU4-A ●	Large Ultem Composite Bullet, Black	✓		C
783352005120	BU4-G ●	Large Ultem Composite Bullet, Verde	✓		C
783352005137	BU4-H ●	Large Ultem Composite Bullet, Bronze	✓		C
---	BUN4-HL	120V, 100W, E17 HID, Large Ultem Bullet - HID Narrow Spot, Bronze		✓	
---	BUW4-HL	120V, 100W, E17 HID, Large Ultem Bullet - HID Wide Flood, Bronze		✓	
---	BUW4-HS	120V, 100W, E17 HID, Large Ultem Bullet - HID Wide Flood, Bronze		✓	
---	BW4-AL	120V, 100W, E17 HID, Large Aluminum Bullet w/Reflector & Large Shrd, Black		✓	
---	BW4-AS	120V, 100W, E17 HID, Large Aluminum Bullet w/Reflector & Short Shrd, Black		✓	
---	BW4-HL	120V, 100W, E17 HID, Large Aluminum Bullet w/Reflector & Large Shrd, Bronze		✓	
---	BW4-HS	120V, 100W, E17 HID, Large Aluminum Bullet w/Reflector & Short Shrd, Bronze		✓	
783352020079	MA3PA-A	120V, 75W PAR 30, Large Machined Accent Incandescent, Black	✓		C
783352020055	MA3PA-AL	120V, 75W PAR 30, Large Machined Accent Incandescent Long Shroud, Black	✓		C
783352020086	MA3PA-H	120V, 75W PAR 30, Large Machined Accent Incandescent, Bronze	✓		C
783352020062	MA3PA-HL	120V, 75W PAR 30, Large Machined Accent Incandescent Long Shroud, Bronze	✓		C

C = Carrollton, Texas

A blue dot "●" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.

Accent - Line Voltage Accessories

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352002501	1HSC	Short Shroud w/Convex Lens (B1), Bronze	✓		C
783352002518	1HSO ●	Short Shroud (B1), Bronze	✓		C
783352007520	ML1	Cut-off Louver (B1)	✓		C
783352000491	ML3	Cut-off Louver (B3)	✓		C
783352007537	ML4	Cut-off Louver (B4),	✓		C
783352002778	4ALC	Long Shroud w/Convex Lens (B4), Black	✓		C
783352002785	4ALO	Long Shroud (B4), Black	✓		C
783352002808	4ASC	Short Shroud w/Convex Lens (B4), Black	✓		C
783352002815	4ASO	Short Shroud (B4), Black	✓		C
783352002846	4GLC	Long Shroud w/Convex Lens (B4), Verde	✓		C
783352002853	4GLO	Long Shroud (B4), Verde	✓		C
783352002884	4GSO	Short Shroud (B4), Verde	✓		C
783352002907	4HLC ●	Long Shroud w/Convex Lens (B4), Bronze	✓		C
783352002914	4HLO ●	Long Shroud (B4), Bronze	✓		C
783352002938	4HSC	Short Shroud w/Convex Lens (B4), Bronze	✓		C
783352002945	4HSO ●	Short Shroud (B4), Bronze	✓		C
783352002372	1ALC	Long Shroud w/Convex Lens (B1), Black	✓		C
783352002389	1ALO ●	Long Shroud (B1), Black	✓		C
783352002402	1ASC	Short Shroud w/Convex Lens (B1), Black	✓		C
783352001542	1ASO ●	Short Shroud (B1), Black	✓		C
---	1GLO	Long Shroud (B1), Verde		✓	
783352002464	1GSO	Short Shroud (B1), Verde	✓		C
783352002488	1HLC ●	Long Shroud w/Convex Lens (B1), Bronze	✓		C
783352001559	1HLO ●	Long Shroud (B1), Bronze	✓		C
783352002587	1UALC ●	Small Ultem Shroud, Black	✓		C
783352002594	1UALO ●	Small Ultem Shroud, Black	✓		C
783352002600	1UASC	Small Ultem Shroud, Black	✓		C
783352002617	1UASO ●	Small Ultem Shroud, Black	✓		C
783352002624	1UGLC ●	Small Ultem Shroud, Verde	✓		C
783352002631	1UGLO	Small Ultem Shroud, Verde	✓		C
783352002648	1UGSC	Small Ultem Shroud, Verde	✓		C
783352002655	1UGSO ●	Small Ultem Shroud, Verde	✓		C
783352002662	1UHLC ●	Small Ultem Shroud, Bronze	✓		C
783352002679	1UHLO ●	Small Ultem Shroud, Bronze	✓		C
783352002686	1UHSC	Small Ultem Shroud, Bronze	✓		C
783352002693	1UHSO ●	Small Ultem Shroud, Bronze	✓		C
783429020896	ML31	Cut-off Louver (BU3)	✓		C
783356020167	4UALC ●	Large Ultem Shroud, Black	✓		C
783352002952	4UALO	Large Ultem Shroud, Black	✓		C
783374020347	4UASC	Large Ultem Shroud, Black	✓		C
783352002969	4UASO ●	Large Ultem Shroud, Black	✓		C
783352002976	4UGLC ●	Large Ultem Shroud, Verde	✓		C
783352002983	4UGLO ●	Large Ultem Shroud, Verde	✓		C
783352002990	4UGSC	Large Ultem Shroud, Verde	✓		C
783352003003	4UGSO ●	Large Ultem Shroud, Verde	✓		C
783375020353	4UHLC	Large Ultem Shroud, Bronze	✓		C
783352003010	4UHLO	Large Ultem Shroud, Bronze	✓		C
783376020369	4UHSC	Large Ultem Shroud, Bronze	✓		C
783352003027	4UHSO ●	Large Ultem Shroud, Bronze	✓		C

C = Carrollton, Texas

A blue dot "●" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.



Accent - Low Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352019493	BL1-ALS7 ●	12V, 75W, MR16, Small Bullet w/ Long Shroud & Stake, Black	✓		C
783352019509	BL1-ASS7	12V, 75W, MR16, Small Bullet w/ Short Shroud & Stake, Black	✓		C
783352020116	BL1-HLS7 ●	12V, 75W, MR16, Small Bullet w/ Long Shroud & Stake, Bronze	✓		C
783353020139	BL1-HSS7 ●	12V, 75W, MR16, Small Bullet w/ Short Shroud & Stake, Bronze	✓		C
783352019516	BL1-NLS7	12V, 75W, MR16, Small Brass Bullet w/ Shroud & Stake, Natural Bronze	✓		C
783352019523	BL1-OBSL7	12V, 75W, MR16, Small Brass Bullet w/ Shroud & Stake, Oiled Brass	✓		C
783352004079	BL36S7-HL ●	12V, 20W, PAR36, Bullet, Lamp, Stake, Bronze	✓		C
783352004147	BL5016-ABULK25	12V, 50W, MR16, Micro Bullet w/Stake, Bulk Pack 25, Black	✓		C
783352004154	BL5016-AS7 ●	12V, 50W, MR16, Micro Bullet w/Stake, Black	✓		C
783352002068	BL5016-AS7BAB ●	12V, 20W, MR16, Micro Bullet w/Stake & Lamp, Black	✓		C
783352004208	BL5016-GS7	12V, 50W, MR16, Micro Bullet w/Stake, Verde	✓		C
783352004215	BL5016-GS725	12V, 50W, MR16, Micro Bullet w/Stake, Bulk Pack 25, Verde	✓		C
783352004222	BL5016-GS7BAB ●	12V, 20W, MR16, Micro Bullet W/Stake & Lamp, Verde	✓		C
783352004253	BL5016-HBULK25	12V, 50W, MR16, Micro Bullet Bulk Pack 25, Bronze	✓		C
783352004260	BL5016-HS7 ●	12V, 50W, MR16, Micro Bullet w/Stake, Bronze	✓		C
783352004277	BL5016-HS725	12V, 50W, MR16, Micro Bullet w/Stake, Bulk Pack 25, Bronze	✓		C
783352002150	BL5016-HS7BAB	12V, 20W, MR16, Micro Bullet w/Stake & Lamp, Bronze	✓		C
783352004307	BL5016-TS7BAB	12V, 20W, MR16, Micro Bullet w/Stake & Lamp, Speckled Stone	✓		C
783352004352	BL616-AS7	12V, 50W, MR16, Micro Bullet w/Stake, Black	✓		C
783352004376	BL616-AS7BAB	12V, 20W, MR16, Micro Bullet w/Stake & Lamp, Black	✓		C
783352019547	BL616-GS7	12V, 50W, MR16, Micro Bullet w/Stake, Verde	✓		C
783352004420	BL616-GS7BAB	12V, 20W, MR16, Micro Bullet w/Stake & Lamp, Verde	✓		C
783352004468	BL616-HS7	12V, 50W MR16, Micro Bullet W/Stake, Bronze	✓		C
783352004475	BL616-HS725	12V, 50W MR16, Micro Bullet W/Stake, Bulk Pack 25, Bronze	✓		C
783352004482	BL616-HS7BAB	12V, 20W, MR16, Micro Bullet W/Stake & Lamp, Bronze	✓		C
783354020145	BL711-AS7 ●	12V, 35W MR11, Micro Bullet W/Stake, Black	✓		C
783352004543	BL711-AS720T3	12V, 20W, T3, Micro Bullet w/ Stake, 20W, T3 Lamp, Black	✓		C
783355020151	BL711-HS7 ●	12V, 35W MR11, Micro Bullet W/Stake, Bronze	✓		C
783352004604	BL711-HS720T3	12V, 20W, T3, Micro Bullet w/ Stake, 20W, T3 Lamp, Bronze	✓		C
783352019554	BPL36-AS7	12V, 50W PAR36, Non-Metallic Bullet, Black	✓		C
783352019561	BPL36-GS7	12V, 50W PAR36, Non-Metallic Bullet, Verde	✓		C
783352019578	BPL36-HS7	12V, 50W PAR36, Non-Metallic Bullet, Bronze	✓		C
783389020493	BUL16-AS7	12V, 35W MR16, Micro Ultem Composite Bullet w/Stake, Black	✓		C
783352002136	BUL16-AS7BAB	12V, 20W, MR16, Micro Ultem Composite Bullet w/Lamp & Stake, Black	✓		C
783352018212	BUL16-AS7LED4NFW	12V, LED, Warm, 4 Watts, Narrow Flood, Black	✓		C
783390020505	BUL16-GS7	12V, 35W MR16, Micro Ultem Composite Bullet w/Stake, Verde	✓		C
783352019585	BUL16-GS7BAB	12V, 20W, MR16, Micro Ultem Composite Bullet w/Lamp & Stake, Verde	✓		C
783352018236	BUL16-GS7LED4NFW	12V, LED, Warm, 4 Watts, Narrow Flood, Verde	✓		C
783352020109	BUL16-HS7	12V, 35W MR16, Micro Ultem Composite Bullet w/Stake, Bronze	✓		C
783392020527	BUL16-HS7BAB	12V, 20W, MR16, Micro Ultem Composite Bullet w/Lamp & Stake, Bronze	✓		C
783352018229	BUL16-HS7LED4NFW	12V, LED, Warm, 4 Watts, Narrow Flood, Bronze	✓		C
783352019592	BUL1-ALS7	12V, 50W MR16, Small Ultem Composite Bullet, Black	✓		C
783352019608	BUL1-ASS7	12V, 50W MR16, Small Ultem Composite Bullet, Black	✓		C
783352019615	BUL1-GLS7	12V, 50W MR16, Small Ultem Composite Bullet, Verde	✓		C
783352019622	BUL1-GSS7	12V, 50W MR16, Small Ultem Composite Bullet, Verde	✓		C
783352019639	BUL1-HLS7	12V, 50W MR16, Small Ultem Composite Bullet, Bronze	✓		C
783352019646	BUL1-HSS7	12V, 50W MR16, Small Ultem Composite Bullet, Bronze	✓		C

C = Carrollton, Texas

A blue dot "●" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.

Accent - Low Voltage - continued

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352001917	CUL16S7	12V, 20W, MR16, MR16 Bullet w/ Stake, Copper	✓		C
783352018243	CUL16-S7LED4NFW	12V, LED, Warm, 4 Watts, Narrow Flood, Copper	✓		C
783352006271	EL1-NS7	12V, 10W T3, Egg Light, Micro Bullet, Natural Bronze	✓		C
783352019998	MA5-ALS7	12V, 35W MR16, Medium Machined Accent Long Shroud, Black	✓		C
783352020031	MA5-ALS7BAB	12V, 20W, MR16, Medium Machined Accent Long Shroud & BAB Lamp, Black	✓		C
783352019974	MA5-AS7	12V, 35W MR16, Medium Machined Accent, Black	✓		C
783352020017	MA5-AS7BAB	12V, 20W, MR16, Medium Machined Accent & BAB Lamp, Black	✓		C
783352020000	MA5-HLS7	12V, 35W MR16, Medium Machined Accent Long Shroud, Bronze	✓		C
783352020048	MA5-HLS7BAB	12V, 20W, MR16, Medium Machined Accent Long Shroud & BAB Lamp, Bronze	✓		C
783352019981	MA5-HS7	12V, 35W MR16, Medium Machined Accent, Bronze	✓		C
783352020024	MA5-HS7BAB	12V, 20W, MR16, Medium Machined Accent & BAB Lamp, Bronze	✓		C
783352019912	MA7-ALS7	12V, 20W, T3, Small Machined Accent Small Shroud, Black	✓		C
783352019950	MA7-ALS720T3	12V, 20W, T3, Small Machined Accent Small Shroud, Lamp Included, Black	✓		C
783352019899	MA7-AS7	12V, 20W, T3, Small Machined Accent, Black	✓		C
783352019936	MA7-AS720T3	12V, 20W, T3, Small Machined Accent Small Shroud, Lamp Included, Black	✓		C
783352019929	MA7-HLS7	12V, 20W, T3, Small Machined Accent Small Shroud, Bronze	✓		C
783352019967	MA7-HLS720T3	12V, 20W, T3, Small Machined Accent Small Shroud, Lamp Included, Bronze	✓		C
783352019905	MA7-HS7	12V, 20W, T3, Small Machined Accent, Bronze	✓		C
783352019943	MA7-HS720T3	12V, 20W, T3, Small Machined Accent Small Shroud, Lamp Included, Bronze	✓		C



Beacon - Line Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352002266	1010-H •	120V, 100W, A19, Beacons, Bronze	✓		C
783352002280	1012-H •	120V, 100W, A19, Composite Beacon, Bronze	✓		C
783352006219	DWC1-A	120V, 20W, T3, Composite Semi Recessed Beacon, Black	✓		C
783352006226	DWC2-A •	120V, 20W, T3, Composite Semi Recessed Beacon, Black	✓		C



Beacon - Low Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352006233	DWCL1-A •	12V, 20W, T3, Composite Mini-Beacon, Black	✓		C
783352006240	DWCL2-A •	12V, 20W, T3, Composite Semi Recessed Beacon, Black	✓		C
783352006257	DWL1-N	12v, 20W, T3, Mini-Beacon, Natural Bronze	✓		C

C = Carrollton, Texas

A blue dot "•" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.



Bollard LED - Line Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
---	DB14AA012LE	120V, LED, Warm, 11W, Clear Symmetric, Round Top Bollard, Black		✓	
---	DB14HA012LE	120V, LED, Warm, 11W, Clear Symmetric, Round Top Bollard, Bronze		✓	
---	DB21AA012LE	120V, LED, Warm, 11W, Clear Symmetric, Round Top Bollard, Black		✓	
---	DB21HA012LE	120V, LED, Warm, 11W, Clear Symmetric, Round Top Bollard, Bronze		✓	
---	DB30AA012LE	120V, LED, Warm, 11W, Clear Symmetric, Round Top Bollard, Black		✓	
---	DB30HA012LE	120V, LED, Warm, 11W, Clear Symmetric, Round Top Bollard, Bronze		✓	



Bollard - Line Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783402020622	DB14-A •	120V, 100W INC, Round Top Bollard, Black	✓		C
783352014825	DB14-H •	120V, 100W INC, Round Top Bollard, Bronze	✓		C
783403020638	DB21-A	120V, 100W INC, Round Top Bollard, Black	✓		C
---	DB21AA042FE	120V, 42W PLT, Round Top Bollard, Black		✓	
783404020644	DB21-H	120V, 100W INC, Round Top Bollard, Bronze	✓		C
---	DB21HA042FE	120V, 42W PLT, Round Top Bollard, Bronze		✓	
---	DB21HA050HE	120V, 50W MH, Round Top Bollard, Bronze		✓	
783358020189	DB30-A	120V, 100W INC, 100W INC Round Top Bollard, Black	✓		C
---	DB30AA0100HE	120V, 100W MH, Round Top Bollard, Black		✓	
---	DB30AA026FE	120V, 26W CFL, Round Top Bollard, Black		✓	
---	DB30AA050HE	120V, 50W MH, Round Top Bollard, Black		✓	
---	DB30AA070HE	120V, 70W MH, Round Top Bollard, Black		✓	
783352014832	DB30-H	120V, 100W INC, 100W INC Round Top Bollard, Bronze	✓		C
---	DB30HA0100HE	120V, 100W MH, Round Top Bollard, Bronze		✓	
---	DB30HA026FE	120V, 26W CFL, Round Top Bollard, Bronze		✓	
---	DB30HA042FE	120V, 42W PLT, Round Top Bollard, Bronze		✓	
---	DB30HA050HE	120V, 50W MH, Round Top Bollard, Bronze		✓	
---	DB30HA070HE	120V, 70W MH, Round Top Bollard, Bronze		✓	
---	DB30HA070SE	120V, 70W HPS, Round Top Bollard, Bronze		✓	

C = Carrollton, Texas

A blue dot "•" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.



Deck Light LED - Low Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
---	DAL1DC-H	12V, LED, Cool, Aluminum Deck Light, Bronze		✓	
---	DAL1DC-SS	12V, LED, Cool, Deck Light, Stainless Steel		✓	
---	DAL1DW-A	12V, LED, Warm, 1.7 Watts, Aluminum Deck Light, Black		✓	
---	DAL1DW-B	12V, LED, Warm, 1.7 Watts, Aluminum Deck Light, White		✓	
---	DAL1DW-H	12V, LED, Warm, 1.7 Watts, Aluminum Deck Light, Bronze		✓	
---	DAL1DW-SS	12V, LED, Warm, 1.7 Watts, Deck Light, Stainless Steel		✓	
---	DAL1DW-T	12V, LED, Warm, Aluminum Deck Light, Speckled Stone		✓	
---	DCL1DC-N	12V, LED, Cool, 1.7 Watts, Deck Light, Natural Brass		✓	
---	DCL1DW-N	12V, LED, Warm, 1.7 Watts, Deck Light, Natural Brass		✓	
---	DUL1DC-A	12V, LED, Cool, 1.7 Watts, Ultem Deck Light, Black		✓	
---	DUL1DW-A	12V, LED, Warm, 1.7 Watts, Ultem Deck Light, Black		✓	
---	DUL1DW-H	12V, LED, Warm, 1.7 Watts, Ultem Deck Light, Bronze		✓	



Deck Light -Low Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
---	CUL20	12V, 10W Xenon T3, Bell Shape Deck Light, Copper		✓	
783352002099	DAL1-A ●	12V, 10W T3 ,Round Step Light, Black	✓		C
783352005915	DAL1-B ●	12V, 10W T3, Round Step Light, White	✓		C
783352005922	DAL1-G	12V, 10W T3, Round Step Light, Verde	✓		C
783352001993	DAL1-H ●	12V, 10W T3, Round Step Light, Bronze	✓		C
783352002006	DAL1-SS ●	12V, 10W T3, Stainless Steel Round Step Light, Stainless Steel	✓		C
---	DAL1-T	12V, 10W T3, Round Step Light, Speckled Stone		✓	
783352006004	DCL1-N ●	12V, 10W T3, Brass Deck Light, Natural Brass	✓		C
783352006035	DL4-N	12V, 10W T3, 4x4 Deck Post Light, Natural Brass	✓		C
783352006172	DUL1-A ●	12V, 10W T3, Ultem Round Step Light, Black	✓		C
783352006189	DUL1-G	12V, 10W T3, Ultem Round Step Light, Verde	✓		C
783352006196	DUL1-H ●	12V, 10W T3, Ultem Round Step Light, Bronze	✓		C
783352006110	DSL1-A	12V, 18W 1141, Square Surface, Black	✓		C
783352006127	DSL1-B	12V, 18W 1141, Square Surface, White	✓		C
783352006387	GACL1-AC	12V, 10W Xenon T3, Deck Light 1/2 Cylinder Down Light, Copper	✓		C
783352006394	GACL2-AC ●	12V, 10W Xenon T3, Deck Light 1/2 Cylinder Up and Down Light, Copper	✓		C
783352002013	GADL1-AC ●	12V, 10W Xenon T3, Deck Light, Copper	✓		C
783352006400	GADL2-AC ●	12V, 10W Xenon T3, Garden Art Hammered Deck Light, Copper	✓		C
783352006417	GADL4-AC	12V, 10W T3, Garden Art 4x4 Post Top Deck Light, Copper	✓		C
783352007292	LLL12-AC	12V, 10W Xenon T3, Copper Line Light, 12", Copper	✓		C
783352007315	LLL24-AC	12V, 10W Xenon T3, Copper Line Light, 24", Copper	✓		C
783352007322	LLL6-AC ●	12V, 10W Xenon T3, Copper Line Light, 6", Copper	✓		C
783352007605	MPLLL ●	Mounting Plate for LLL	✓		C
783352001764	RFL1-A	12V, 12W 93, Recessed Step light, Black	✓		C
783352008930	RL13-A	12V, 100W T3, Composite Deck Light, Black	✓		C
783352009081	RLL1-A ●	12V, 12W 93, Rec Louver Step Light, Black	✓		C
783357020173	RLL2-PC ●	12V, 12W 93, Mini Recessed Louver Step Light, Copper	✓		C
783436020964	RLL2-SS	12V, 12W 93, Mini Recessed Louver Step Light, Stainless Steel	✓		C
783352012791	SRL3-A ●	12V, 18W 1141, Deck Light, Black	✓		C
783352012821	SRL3-H ●	12V, 18W 1141, Deck Light, Bronze	✓		C
783352000316	SRL4-A ●	12V, 10W Xenon T3, Deck Light, Black	✓		C
783352000323	SRL4-B ●	12V, 10W Xenon T3, Deck Light, White	✓		C
783352000330	SRL4-G ●	12V, 10W Xenon T3, Deck Light, Verde	✓		C
783352000347	SRL4-H ●	12V, 10W Xenon T3, Deck Light, Bronze	✓		C

C = Carrollton, Texas

A blue dot "●" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.



Down Light LED - Low Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
---	DL1DW3-A	12V, LED, Warm, LED Down Light, Black		✓	
---	DL1DW3-G	12V, LED, Warm, LED Down Light, Verde		✓	
783352018250	DRL1-ALED4NFW	12V, LED, Warm, 4 Watts, Narrow Flood, Black	✓		C
783352018311	DRL1-ALED7FLW	12V, LED, Warm, 7 Watts, Flood, Black	✓		C
783352018298	DRL1-ALED7SPW	12V, LED, Warm, 7 Watts, Spot, Black	✓		C
---	DRL1DW2-A	12V, LED, Warm, Down Light, Black		✓	
783352018366	DRL1-GLED7FLC	12V, LED, Cool, 7 Watts, Flood, Verde	✓		C
783352018328	DRL1-GLED7FLW	12V, LED, Warm, 7 Watts, Flood, Verde	✓		C
783352018373	DRL2-ALED4NFW	12V, LED, Warm, 4 Watts, Narrow Flood, Black	✓		C
783352018434	DRL2-ALED7FLW	12V, LED, Warm, 7 Watts, Flood, Black	✓		C
783352018397	DRL2-ALED7NFW	12V, LED, Warm, 7 Watts, Narrow Flood, Black	✓		C
783352018410	DRL2-ALED7SPW	12V, LED, Warm, 7 Watts, Spot, Black	✓		C
783352018380	DRL2-GLED4NFW	12V, LED, Warm, 4 Watts, Narrow Flood, Verde	✓		C
783352018274	DRL1-ALED7NFW	12V, LED, Warm, 7 Watts, Narrow Flood, Black	✓		C



Down Light - Low Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352006011	DL1-A	12V, 27W 1156, Down light, Black	✓		C
783352006028	DL1-G	12V, 27W 1156, Down light, Verde	✓		C
783352006080	DRL2-A •	12V, 35W MR16, Round Bracket, Black	✓		C
783352006103	DRL2-G	12V, 35W MR16, Round Bracket, Verde	✓		C
783352006141	DSL2-A	12V, 18W 1141, Square Bracket, Black	✓		C
783352006158	DSL2-B	12V, 18W 1141, Square Bracket, White	✓		C
783352006486	GAHL1-AC •	12V, 27W 1156, Sm Hanging Down Light, Copper	✓		C

C = Carrollton, Texas

A blue dot "•" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.



Inground/Ingrade LED - Line Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
---	I25NNFW	120V, LED, Warm, 17 Watts, Narrow Flood, Bronze, Natural Brass		✓	
---	I3GHLED7NFW	120V, LED, 8 Watt, Inground with Composite Rock Guard, Bronze		✓	
783352018687	IT216G-HLED4NFW •	120V / 12V, LED, Warm, 4 Watts, Narrow Flood, Bronze	✓		C
783352018786	IT216G-HLED7FLC	120V / 12V, LED, Cool, 7 Watts, Flood, Bronze	✓		C
783352018724	IT216G-HLED7FLW	120V / 12V, LED, Warm, 7 Watts, Flood, Bronze	✓		C
783352018700	IT216G-HLED7NFW	120V / 12V, LED, Warm, 7 Watts, Narrow Flood, Bronze	✓		C
783352018571	IT216-HLED7FLW	120V / 12V, LED, Warm, 7 Watts, Flood, Bronze	✓		C
783352018564	IT216-SSLED7FLW	120V / 12V, LED, Warm, 7 Watts, Flood, Stainless Steel	✓		C



Inground/Ingrade LED - Low Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352019097	IL116G-HLED4NFW	12V, LED, Warm, 4 Watts, Narrow Flood, Bronze	✓		C
783352019196	IL116G-HLED7FLC	12V, LED, Cool, 7 Watts, Flood, Bronze	✓		C
783352019134	IL116G-HLED7FLW	12V, LED, Warm, 7 Watts, Flood, Bronze	✓		C
783352019110	IL116G-HLED7NFW	12V, LED, Warm, 7 Watts, Narrow Flood, Bronze	✓		C
783352018922	IL116-HLED4NFW	12V, LED, Warm, 4 Watts, Narrow Flood, Bronze	✓		C
783352018984	IL116-HLED7FLW	12V, LED, Warm, 7 Watts, Flood, Bronze	✓		C
783352019042	IL116-HLED7NFC	12V, LED, Cool, 7 Watts, Narrow Flood, Bronze	✓		C
783352018953	IL116-HLED7NFW	12V, LED, Warm, 7 Watts, Narrow Flood, Bronze	✓		C
783352018960	IL116-NLED7FLW	12V, LED, Warm, 7 Watts, Flood, Natural Brass	✓		C
783352018939	IL116-NLED7NFW	12V, LED, Warm, 7 Watts, Narrow Flood, Natural Brass	✓		C
783352018977	IL116-SSLED7FLW	12V, LED, Warm, 7 Watts, Flood, Stainless Steel	✓		C
783352019202	IUL516-HLED4NFW	12V, LED, Warm, 4 Watts, Narrow Flood, Bronze	✓		C
783352019103	IL116G-NLED7NFW	12V, LED, Warm, 7 Watts, Narrow Flood, Natural Brass	✓		C
783352019011	IL116-HLED7SPW	12V, LED, Warm, 7 Watts, Narrow Spot, Bronze	✓		C
783365020257	IL9DW-A •	12V, LED, Warm, Zoomable Optics, FlexScape, Black	✓		C
783366020263	IL9DC-A •	12V, LED, Cool, Zoomable Optics, FlexScape, Black	✓		C

C = Carrollton, Texas

A blue dot "•" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.



Inground/Ingrade - Line Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
---	I25-N	120V, 100W Incandecent, Inground, Natural Brass		✓	
783352006714	I3G-H •	120V, 100W Par/R20, Inground with Composite Rock Guard, Bronze	✓		C
---	I3GH0100H120	120V, 100W MH, Inground with Composite Rock Guard, Bronze		✓	
---	I3GHSP100H120	120V, 100W MH, Inground with Composite Rock Guard, Bronze		✓	
---	I3G-N	120V, 100W Par/R20, Inground with Cast Bronze Rock Guard, Natural Brass		✓	
783352006721	I3-H •	120V, 100W Par/R20, Inground with Composite Ring, Bronze	✓		C
---	I3-N	120V, 100W Par/R20, Inground with Cast Bronze Ring, Natural Brass		✓	
783408020688	I3-SS	120V, 100W Par/R20, Inground with Stainless Steel Ring, Stainless Steel	✓		C
783409020694	I4G-H	120V, 150W PAR 38, Large Inground/Medium Base Socket/Stainless Steel Trim Ring, Bronze	✓		C
783410020706	I4G-N	120V, 150W PAR 38, Large Inground/Medium Base Socket/Bronze Rock Guard, Natural Brass	✓		C
---	I4-H	120V, 150W PAR 38, Large Inground/Medium Base Socket/Bronze Trim Ring, Bronze		✓	
---	I4-N	120V, 150W PAR 38, Large Inground/Medium Base Socket/Cast Bronze Trim Ring, Natural Brass		✓	
783411020712	I4-SS	120V, 150W PAR 38, Large Inground/Medium Base Socket/Cast Bronze Rock Guard, Stainless Steel	✓		C
783352007223	IT216G-H	120V / 12V, 75W MR16, Small Inground w/Composite Rock Guard, Bronze	✓		C
783422020824	IT216G-N	120V / 12V, 75W MR16, Small Inground w/Cast Bronze Rock Guard, Natural Brass	✓		C
783352018694	IT216G-NLED7NFW	120V / 12V, LED, Warm, 7 Watts, Narrow Flood, Natural Brass	✓		C
783352001740	IT216-H	120V / 12V, 75W MR16, Small Inground w/Composite Trim Ring, Bronze	✓		C
783423020830	IT216-N	120V / 12V, 75W MR16, Small Inground w/Cast Bronze Trim Ring, Natural Brass	✓		C
783352018557	IT216-NLED7FLW	120V / 12V, LED, Warm, 7 Watts, Flood, Natural Brass	✓		C
783424020846	IT216-SS	120V / 12V, 75W MR16, Small Inground w/Stainless Steel Trim Ring, Stainless Steel	✓		C
783352006691	I2G-H	120V, 100W R30, Small Inground w/Bronze Rock GuardGuard, Bronze	✓		C
783406020666	I2G-N	120V, 100W R30, Small Inground w/Cast Bronze Rock Guard, Natural Brass	✓		C
783352007230	IT236G-H	120V / 12V, 75W PAR 36, Small Inground w/Composite Rock Guard, Bronze	✓		C
783425020852	IT236G-N	120V / 12V, 75W PAR 36, Small Inground w/Cast Bronze Rock Guard, Natural Brass	✓		C
783352007247	IT236-H	120V / 12V, 75W PAR 36, Small Inground w/Composite Trim Ring, Bronze	✓		C
783426020868	IT236-N	120V / 12V, 75W PAR 36, Small Inground w/Cast Bronze Trim Ring, Natural Brass	✓		C
783427020874	IT236-SS	120V / 12V, 75W PAR 36, Small Inground w/Stainless Steel Trim Ring, Stainless Steel	✓		C
---	I25CRGN	External Cast Bronze Rock Guard (i2.5), Natural Brass		✓	
---	I35CRGN	Rock Guard (i3.5), Natural Brass		✓	

Inground/Ingrade - Line Voltage Accessories

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352005625	CP3	Concrete Pour Kit (I3)	✓		C
783395020555	CPS3	Stainless Steel Concrete Pour Kit (I3), Stainless Steel	✓		C
783352006745	I3-HHO	I3-H Housing Only, Bronze	✓		C
783421020818	IS3H	I3 External Glare Shield	✓		C
---	CPS35	Stainless Steel Concrete Pour Kit (i35)		✓	
---	MA5	Mounting Compound for I4		✓	
783352005632	CP4	Concrete Pour Kit (I4)	✓		C
783352000408	CP5	Concrete Pour Kit, IUL516 & IL9	✓		
783396020561	CPS4	Stainless Steel Concrete Pour Kit (I4)	✓		C
783352006776	I4-HHO	I4, Housing Only, Bronze	✓		C
783352007193	IS4H	Shield	✓		C
---	CPS25 •	Stainless Steel Concrete Pour Kit (i2.5), Stainless Steel		✓	
---	CPS15	Concrete Pour Kit (i1.5)		✓	

C = Carrollton, Texas

A blue dot "•" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.



Inground/Ingrade - Low Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352006707	I2-H •	120V, 100W R30, Small Inground with Bronze Trim Ring, Bronze	✓		C
783352015617	I2-N	120V, 100W R30, Small Inground with Cast Bronze Trim Ring, Natural Brass	✓		C
783407020672	I2-SS	120V, 100W R30, Small Inground with Stainless Steel Trim Ring, Stainless Steel	✓		C
783352000125	IL116G-H	12V, 75W MR16, Inground w/Guard, Bronze	✓		C
783352000132	IL116-H	12V, 75W MR16, Inground, Bronze	✓		C
783416020672	IL116-N	12V, 75W MR16, Composite Inground with Cast Bronze Trim Ring, Natural Brass	✓		C
783352007032	IL136G-H	12V, 75W PAR 36, Inground w/Guard, Bronze	✓		C
783352007049	IL136-H	12V, 75W PAR 36, Inground, Bronze	✓		C
783419020790	IL136-N	12V, 75W PAR 36, Composite Inground with Cast Bronze Trim Ring, Natural Brass	✓		C
783352000149	IL336-A •	12V, 50W PAR 36, Well Light, Black	✓		C
783352007070	IL336-ABULK25	12V, 50W PAR 36, Well Light, Bulk Pack 25, Black	✓		C
783352000156	IL336-AL •	12V, 20W PAR 36, Well Light w/Lamp, Black	✓		C
783352002143	IL336-ALBULK25	12V, 20W PAR 36, Well Light w/Lamp, Bulk Pack 25, Black	✓		C
783352007254	IUL516-H	12V, 35W MR16, Ultem Micro Inground, MR16, Bronze	✓		C
783352007261	IUL516-HBAB	12V, 20W MR16, Ultem Micro Inground, MR16, w/Lamp, Bronze	✓		C
783352002167	IUL516-HBULK25	12V, 35W MR16, Ultem Micro Inground, MR16, Bulk Pack 25, Bronze	✓		C

Inground/Ingrade - Low Voltage Accessories

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
---	IBLR	Internal Ice Blue Lens (for i15 / i25)		✓	
---	ICGR	Internal Honeycomb Louver (for i15 / i25)		✓	
---	ILSLR	Internal Linear Spread Lens (for i25 / i25)		✓	
---	IMSLR	Internal Multi-Directional Spread Lens (for i15 / i25)		✓	
---	LEDADP	LED Accessory Adaptor Ring		✓	
783352000392	CP2 •	Concrete Pour Kit (I2)	✓		C
783394020549	CPS2	Stainless Steel Concrete Pour Kit (I2), Stainless Steel	✓		C
783352000477	IS1H	Inground Shield (for Mini Inground)	✓		C
783352000446	IG30H	Rock Guard w/o Lens (for IL336 Wellyte)	✓		C
783352000453	IG3H •	Rock Guard w/Lens (for IL336 Wellyte)	✓		C
783352000460	IL3H •	Lens Guard (for IL336 Wellyte)	✓		C

C = Carrollton, Texas

A blue dot "•" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.



Landscape Accessories, General

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
---	BI1	Cast Iron Box (1/2" NPT)		✓	
783352003690	BI2	Cast Iron Box (3/4" NPT)	✓		C
783352001573	BI3 ●	Cast Iron Box w/four 1/2" NPT+ two 1/2" NPT	✓		C
783352003706	BI4 ●	Cast Iron Box w/two 1/2" NPT+ two 1/2" NPT	✓		C
783359020195	IAS16 ●	MR16 Linear Spread Lens Accessory	✓		C
783352000415	IBL1	Ice Blue Lens,	✓		C
783352000422	IBL16	Ice Blue Lens,	✓		C
783352000439	ICG16 ●	Cut-Off Grille for MR 16	✓		C
783413020734	ICG20	Internal Snap On Honeycomb Louver, PAR20 Lamp	✓		C
783414020740	ICG30	Snap on Cut-Off Grill for PAR 30	✓		C
783352006943	ICG36	Snap on Cut-Off Grill for PAR 36	✓		C
783352006950	ICG38	Internal Snap On Honeycomb Louver, PAR38 Lamp	✓		C
783352007209	ISL16 ●	Spread Lens	✓		C
783352002037	LVC3 ●	Connectors (Box of 12)	✓		C
---	M0040A	Low Voltage Mounting Canopy, Black		✓	
783352007377	MA1	Potting Compound (Box of 6)	✓		C
783352007407	MA22 ●	Silicone-Filled Wire Connectors	✓		C
783352007421	MA4	Corrosion Preventive Compound	✓		C
783352001757	MC1A ●	LV Mounting Canopy (Box of 6), Black	✓		C
783352007490	MC1H ●	LV Mounting Canopy (Box of 6), Bronze	✓		C
783428020880	MC1N	LV Mounting Canopy (Brass), Natural Bronze	✓		C
783352007506	MF1	Lag Screws for Tree Mounting (Box of 12)	✓		C
783352000507	MLB1	Ice Blue Lens	✓		C
783352000514	MLS1	Spread Lens	✓		C
783352008671	PC15	Plug-In Photo Cell, Remote Mount	✓		C
783352001818	PC3 ●	Plug-In Photo Cell, Direct Mount	✓		C
783352011978	S1 ●	Low Voltage Stake	✓		C
783352012128	S35B ●	Perma-Post 3.5" O.D. (Box of 9), White	✓		C
783352012203	S3A	Perma-Post 3" O.D. (Box of 12), Black	✓		C
---	S3B	Perma-Post 3" O.D. (Box of 12), White		✓	
783352012227	S3G ●	Perma-Post 3" O.D. (Box of 12), Verde	✓		C
783352012234	S3H ●	Perma-Post 3" O.D. (Box of 12), Bronze	✓		C
783352012241	S3N ●	Perma-Post 3" O.D. Natural Bronze	✓		C
783352012319	S6 ●	Low-Volt Telescoping PVC Stake (Box of 12)	✓		C
---	S6N	Low-Volt Telescoping PVC Stake (Box of 12), Natural Bronze		✓	
783352001825	S7 ●	Low Voltage Mounting Stake (Box of 12)	✓		C
783352012326	S7BULK200	Stake,12V, Arrow 200 Bulk Pack	✓		C
783352012333	S7N	Low Voltage Mounting Stake, Natural Bronze	✓		C
783352012340	S8 ●	15" Low Voltage Mounting Stake (Box of 12)	✓		C
783352012364	S8N	Low Voltage Mounting Stake, Natural Bronze	✓		C

C = Carrollton, Texas

A blue dot "●" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.

Landscape Accessories, General - continued

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352001665	T5 ●	Plug In Timer, Analog	✓		C
783352001672	T6 ●	Plug In Timer, Digital	✓		C
783352013644	TM1A	N/S,Tree Mount Adapter, Black	✓		C
783352013668	TM1H ●	Tree Mount Adapter, Bronze	✓		C
783445021051	TM2A	Tree Mount Junction Box, Black	✓		C
783352001726	TM2H ●	Tree Mount Junction Box, Bronze	✓		C
783352001733	TMC2H ●	Composite Tree Mount Junction Box, Bronze	✓		C
783352013729	TMS10 ●	Nylon Tree Strap, 10 Foot	✓		C
783360020207	TS375-12 ●	Perma Post w/ Integral Transformer	✓		C
---	A18	Wedge Base Adapter		✓	
783352007360	LVC4 ●	Low Voltage "T" Connector	✓		C
783352000484	MGM1	Cut-off Grill	✓		C
783430020908	MR1620MFL	MR16 Medium Flood (BAB)	✓		C
783431020914	MR1635FL	MR16-Flood (FMW) (Box of 6)	✓		C
---	MR1635SP	MR16-Spot (FRB) (Box of 6)		✓	
783352008633	PAR3620WFL	PAR36 Wide Flood, Halogen	✓		C
783352008657	PAR3636WFL	PAR36 Capsylite,12V, 36W, 12/BX	✓		C
783443021039	T410	Bi-Pin Halogen Lamp (Box of 6)	✓		C
783444021045	T420	Bi-Pin Halogen Lamp (Box of 6)	✓		C
---	T450	Bi-Pin Halogen Lamp (Box of 6)		✓	
783352002426	1GLC	Long Shroud w/Convex Lens (B1)	✓		C

C = Carrollton, Texas

A blue dot "●" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.



Mini Flood/Wall Washer LED - Line Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
---	WAM1DC-H	120V, LED, Cool, Mini Arch Flood, Bronze		✓	
---	WAM1DWF-H	120V, LED, Warm, Mini Arch Flood w/Frosted Shroud, Bronze		✓	
---	WBM1DC-H	120V, LED, Cool, Mini Arch Flood, Bronze		✓	



Mini Flood/Wall Washer LED - Low Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
---	AAL1DW3-HS7	12V, LED, Warm, 3.8 Watts, Wall Washer Light With Stake, Bronze		✓	
---	AUL1DW3-AS7	12V, LED, Warm, 3.8 Watts, Ultem Wall Washer With Stake, Black		✓	
---	WAML1DC3F-AS7	12V, LED, Cool, Mini Arch Flood w/ Frosted Shroud Black		✓	
---	WAML1DC3F-HS7	12V, LED, Cool, Mini Arch Flood w/Frosted Shroud, Bronze		✓	
---	WAML1DC3-HS7	12V, LED, Cool, Mini Arch Flood w/Shroud, Bronze		✓	
---	WAML1DW2F-AS7	12V, LED, Warm, Mini Arch Flood w/ Frosted Shroud (low), Black		✓	
---	WAML1DW2F-HS7	12V, LED, Warm, Mini Arch Flood w/ Frosted Shroud (low), Bronze		✓	
---	WAML1DW3F-AS7	12V, LED, Warm, Mini Arch Flood w/Frosted Shroud, Black		✓	
---	WAML1DW3F-HS7	12V, LED, Warm, Mini Arch Flood w/Frosted Shroud, Bronze		✓	
---	WAML1DW3-HS7	12V, LED, Warm, Mini Arch Flood w/Shroud, Bronze		✓	
---	WBML1DC3-AS7	12V, LED, Cool, Mini Arch Flood, Black		✓	
783451021113	WAML1DC3-GS7	12V, LED, Cool, Mini Arch Flood w/Shroud, Verde	✓		C



Mini Flood/Wall Washer - Line Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
---	WAMT14-A	12V, 50W T4, Micro Floodlight w/ Integral Transformer, w/ Shroud, Black		✓	
783452021129	WAMT14-H	12V, 50W T4, Micro Floodlight w/ Integral Transformer, w/ Shroud, Bronze	✓		C
783352014535	WAM1-A	120V, 75W T3, Mini Arch Flood w/Shroud, Black	✓		C
783352014566	WAM1-H	120V, 75W T3, Mini Arch Flood w/Shroud, Bronze	✓		C

C = Carrollton, Texas

A blue dot "•" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.



Mini Flood/Wall Washer - Low Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352003195	AAL1-AS7	12V, 27W 1156, Wall Washer Light With Stake, Black	✓		C
783352019462	AUL1-GS7	12V, 20W T3, Ultem Wall Washer With Stake, Verde	✓		C
783352014580	WAML14-AS7	12V, 50W T4, Mini Arch Flood w/Shroud, Black	✓		C
---	WAML14F-AS7	12V, 50W T4, Mini Arch Flood w/Shroud, Black		✓	
783449021095	WAML14F-AS720T3	12V, 20W T3, Mini Arch Flood w/Shroud, with Lamp, Black	✓		C
---	WAML14F-AS735T3	12V, 20W T3, Mini Arch Flood w/Shroud, with Lamp, Black		✓	
783450021107	WAML14F-HS7 •	12V, 50W T4, Mini Arch Flood w/Shroud, Bronze	✓		C
783361020213	WAML14F-HS720T3	12V, 20W T3, Mini Arch Flood w/Shroud, with Lamp, Bronze	✓		C
---	WAML14-HS7	12V, 50W T4, Mini Arch Flood w/Shroud, Bronze		✓	
---	WAML14-HS720T3	12V, 20W T3, Mini Arch Flood w/Shroud, with Lamp, Bronze		✓	
---	WBML14-HS7	12V, 35W T3, Mini Arch Flood w/Shroud, Bronze		✓	



Path Light LED - Low Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
---	CUL10DW-S7	12V, LED, Warm, 4.2 Watts, Path Light with Stake, Copper		✓	
---	CUL14DC-S7	12V, LED, Cool, 4.2 Watts, Path Light with Stake, Copper		✓	
---	CUL14DW-S7	12V, LED, Warm, 4.2 Watts, Path Light with Stake, Copper		✓	
---	CUL2DCS7	12V, LED, Cool, 4.2 Watts, Path Light with Stake, Copper		✓	
---	CUL2DWS7	12V, LED, Warm, 4.2 Watts, Path Light with Stake, Copper		✓	
---	CUL7DCS7	12V, LED, Cool, 4.2 Watts, Path Light with Stake, Copper		✓	
---	CUL7DWS7	12V, LED, Warm, 4.2 Watts, Path Light with Stake, Copper		✓	
---	CUL9DWS7	12V, LED, Warm, 4.2 Watts, Path Light with Stake, Copper		✓	
783352019752	ML4D3-AS7	12V, LED, Cool, 3.8 Watts, Mushroom, Black	✓		C
783352019769	ML4D3-GS7	12V, LED, Cool, 3.8 Watts, Mushroom, Verde	✓		C
783352001924	ML4D3-HS7	12V, LED, Cool, 3.8 Watts, Mushroom, Bronze	✓		C
783352019776	ML4DW3-AS7	12V, LED, Warm, 3.8 Watts, Mushroom (Warm), Black	✓		C
783352019783	ML4DW3-GS7	12V, LED, Warm, 3.8 Watts, Mushroom (Warm), Verde	✓		C
783352019790	ML4DW3-HS7	12V, LED, Warm, 3.8 Watts, Mushroom (Warm), Bronze	✓		C
783434020942	RL4D3-AS7	12V, LED, Cool, Horizon Path light, Black	✓		C
---	RL4DW3-AS7	12V, LED, Warm, Horizon Path light, Black		✓	
---	RL4DW3-HS7	12V, LED, Warm, Horizon Path light, Bronze		✓	
---	RL9D3-AS7	12V, LED, Cool, Horizon Path Light With Stake, Black		✓	
---	RL9D3-HS7	12V, LED, Cool, Horizon Path Light With Stake, Bronze		✓	
---	RL9DW3-AS7	12V, LED, Warm, Horizon Path Light With Stake, Black		✓	
---	RL9DW3-HS7	12V, LED, Warm, Horizon Path Light With Stake, Bronze		✓	
783435020958	RL4D3-HS7	12V, LED, Cool, Horizon Path light, Bronze	✓		C

C = Carrollton, Texas

A blue dot "•" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.



Path Light - Line Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352001603	MU5-G	120V, 100W A19, Med Mushroom, Verde	✓		C
783352007919	MU5-H	120V, 100W A19, Med Mushroom, Bronze	✓		C
783352007926	MU5-N	120V, 100W A19, Med Brass Mushroom, Natural Brass	✓		C
783352008558	P39-K	120V, 75W A19, 2 Tier Pagoda, Garden Green	✓		C
783352008589	P3-G	120V, 75W A19, Small Horizontal Path light, Verde	✓		C
783352008770	Q39-K	120V, 100W A19, 3 Tier Pagoda, Garden Green	✓		C
783352008800	QF59-K	120V, 13W PL13, 3 Tier Pagoda, Garden Green	✓		C
---	R39-K	120V, 100W A19, Large Top (3 Tier), Garden Green		✓	
783352008909	R3-G	120V, 100W A19, Large Indirect, Verde	✓		C
---	SK2-G	120V, 60W A19, Aluminum Path Light, Verde		✓	
783352012999	T39-G •	120V, 100W A19, Large Tudor Down light, Verde	✓		C
783352013743	TR5-G	120V, 100W A19, Large Tudor, Verde	✓		C
783352014092	TU3-G	120V, 100W A19, Large Tulip, Verde	✓		C



Path Light - Low Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783379020397	AL41-AS7	12V, 20W T3, Architectural Mushroom with Glass Finial, Black	✓		C
783352019417	AL41-GS7	12V, 20W T3, Architectural Mushroom with Glass Finial, Verde	✓		C
783352019448	AL43-GS7	12V, 20W T3, Architectural Stem Mount Path light, Verde	✓		C
783352019653	CPL12-AS7	12V, 20W T3, Contemporary Path light, Flat Roof w/Stake, Black	✓		C
783352019660	CPL12-HS7	12V, 20W T3, Contemporary Path light, Flat Roof w/Stake, Bronze	✓		C
783352019677	CPL21-AS7 •	12V, 20W T3, Contemporary Path light, Rounded Roof w/Stake, Black	✓		C
783352019684	CPL21-HS7 •	12V, 20W T3, Contemporary Path light, Rounded Roof w/Stake, Bronze	✓		C
783352005656	CUL10S7	12V, 20W T3, Large Adjustable Path light w/ Stake, Copper	✓		C
783352019370	CUL14S7 •	12V, 20W T3, Path Light With Stake, Copper	✓		C
783352005748	CUL2S7 •	12V, 20W T3, Small Path light w/Stake, Copper	✓		C
783352005809	CUL4S7	12V, 20W T3, Micro Adjustable Path light w/ Stake, Copper	✓		C
783352005830	CUL6S7 •	12V, 20W T3, Path light w/ Stake, Copper	✓		C
783352001955	CUL7S7 •	12V, 20W T3, Medium Path light w/ Straight Stem w/ Stake, Copper	✓		C
783397020577	CUL7S7BULK25	12V, 20W T3, Medium Path light w/ Straight Stem w/ Stake, Bulk Pack 25, Copper	✓		C
783352005892	CUL9S7 •	12V, 20W T3, Large Path light with Stake, Copper	✓		C
783352006363	FUL1-GS7	12V, 27W 1156, Small Floral w/ Stake, Verde	✓		C
783352019691	GAL3-ACS7 •	12V, 10W Xenon T3, Garden Art Line Light Contemporary Path light, Copper	✓		C
783352019707	GAML1-ACS7	12V, 10W T3, Small Mushroom, Copper	✓		C
783352019714	GAML2-ACS7	12V, 20W T3, Large Mushroom, Copper	✓		C
783352019721	GAML3-ACS7	12V, 10W T3, Garden Art 3-Mushroom Path light, Copper	✓		C
783352019738	GAML4-ACS7	12V, 10W T3, Garden Art Small Hammered Roof Path light, Copper	✓		C
783352019745	GAML5-ACS7	12V, 20W T3, Garden Art Large Hammered Roof Path light, Copper	✓		C
783352006578	GASL5-ACS7	12V, 20W T3, Garden Art Mission Mini Bollard, Copper	✓		C
783352014139	TUL1-GS7 •	12V, 20W T3, SM Tulip Path light, w/Lamp and Stake, Verde	✓		C
---	KCL1-GS7	12V, 18W T5, Aluminum Path Light / Lamp Included, Verde		✓	
---	MLL2-HS7	12V, 18W T5, Aluminum Path Light, Bronze		✓	

C = Carrollton, Texas

A blue dot "•" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.

Path Light - Low Voltage - continued

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352007674	MSL12-AS7 ●	12V, 27W 1156, Advent w/12" Stem, Black	✓		C
783352007698	MSL12-GS7	12V, 27W 1156, Advent w/12" Stem, Verde	✓		C
783352007711	MSL12-HS7	12V, 27W 1156, Advent w/12" Stem, Bronze	✓		C
783352007735	MSL18-AS7 ●	12V, 27W 1156, Advent w/18" Stem, Black	✓		C
783352007759	MSL18-GS7	12V, 27W 1156, Advent w/18" Stem, Verde	✓		C
783352007773	MSL18-HS7	12V, 27W 1156, Advent w/18" Stem, Bronze	✓		C
783352008046	MUL4-AS7 ●	12V, 20W T3, Sm Mushroom w/ lamp, Black	✓		C
783352008053	MUL4-AS725	12V, 20W T3, Sm Mushroom w/ lamp, Bulk Pack 25, Black	✓		C
783352008077	MUL4-GS7 ●	12V, 20W T3, Sm Mushroom w/ lamp, Verde	✓		C
783352002020	MUL4-HS7 ●	12V, 20W T3, Sm Mushroom w/ lamp, Bronze	✓		C
783352008114	MUL4-HS725	12V, 20W T3, Sm Mushroom w/ lamp, Bulk Pack 25, Bronze	✓		C
783352001931	MUL4-NS7	12V, 20W T3, Sm Mushroom w/ lamp, Natural Brass	✓		C
783352008190	MUL5-AS7	12V, 20W T3, Med Mushroom, Black	✓		C
783352008213	MUL5-GS7	12V, 20W T3, Med Mushroom, Verde	✓		C
783352008237	MUL5-HS7 ●	12V, 20W T3, Med Mushroom, Bronze	✓		C
783352019813	MUL5-NS7	12V, 20W T3, Med Brass Mushroom, Natural Brass	✓		C
783352019820	PL39-KS7	12V, 27W 1156, 2 Tier Pagoda, Garden Green	✓		C
783352019837	PL3-GS7	12V, 27W 1156, Small Indirect, Verde	✓		C
783352001948	RL4-AS7 ●	12V, 20W T3, Large Horizon, Black	✓		C
783352009029	RL4-GS7	12V, 20W T3, Large Horizon, Verde	✓		C
783352009043	RL4-HS7 ●	12V, 20W T3, Large Horizon, Bronze	✓		C
783352019288	RL9-AS7	12V, 20W T3, Horizon Path Light With Stake, Black	✓		C
783352019295	RL9-HS7 ●	12V, 20W T3, Horizon Path Light With Stake, Bronze	✓		C
783352012449	SPL18-AS7	12V, 27W 1156, Sm Pinnacle 18", Black	✓		C
783352012463	SPL18-GS7	12V, 27W 1156, Sm Pinnacle 18", Verde	✓		C
783352012500	SPL1-AS7	12V, 27W 1156, Sm Pinnacle 32", Black	✓		C
783352012555	SPL1-GS7	12V, 27W 1156, Sm Pinnacle 32", Verde	✓		C
783352019844	SPL5-NS7	12V, 20W T3, Brass Path light, Nautical, Natural Brass	✓		C
---	TL19-GS7	12V, 20W Xenon T3, Small Tudor Down light, Verde		✓	
783352019868	TRL4-GS7 ●	12V, 20W T3, Small Tudor w/ Stake, Verde	✓		C
783433020936	RL3-GS7	12V, 27W 1156, Large Indirect, Verde	✓		C

Path Light Accessories

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352011985	S12A	12" Stem, Black	✓		C
783352011992	S12G ●	12" Stem, Verde	✓		C
783441021017	S12GM	12" Stem, Verde	✓		C
783442021023	S12HM	12" Stem, Bronze	✓		C
---	S12K	12" Stem, Garden Green		✓	
783352012067	S24A	24" Stem, Black	✓		C
783352012074	S24G ●	24" Stem, Verde	✓		C
783352012081	S24H	24" Stake, Bronze	✓		C
---	S24K	24" Stem, Garden Green		✓	
783352012135	S36A	36" Stem, Black	✓		C
783352012142	S36G	36" Stem, Verde	✓		C
---	S36K	36" Stem, Garden Green		✓	

C = Carrollton, Texas

A blue dot "●" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.



Step Light LED - Line Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783438020986	RSC2AK5D3E	120V, LED, 3Watt, Louvered Brick light, Black	✓		C
783439020992	RSC2AK5D5E	120V, LED, 5Watt, Louvered Brick light, Black	✓		C
783440021001	RSC2HK5D3E	120V, LED, 3Watt, Louvered Brick light, Bronze	✓		C
---	RSC2HK5D5E	120V, LED, 5Watt, Louvered Brick light, Bronze		✓	
---	RSC2NK5D5WE	120V, LED, 5Watt, Louvered Brick light, Natural Brass		✓	
783352007438	MAKEC	Mounting Kit for Bricklyte in Existing Stud Wall,	✓		C
783352007445	MAKES	Mounting Kit for Existing Stud Wall,	✓		C
783352001979	MAKM •	Mounting Kit for in Masonry,	✓		C
783352007452	MAKNS	Mounting Kit for in New Stud Wall,	✓		C
783352010094	RS2-AHO •	HSG Only for RSB2/RSC2/RSF2, Black, Black	✓		C
783352010100	RS2-BHO	HSG for RSB2/RSC2/RSF2, White, White	✓		C
783352010117	RS2-HHO •	HSG Only for RSB2/RSC2/RSF2, Bronze, Bronze	✓		C
783437020970	RS2-NHO	HSG Only for RSC2/RSV2, Natural Bronze, Natural Brass	✓		C



Step Light - Line Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783363020235	781369145488	941C-HSG/HWK ASSY	✓		C
783366020263	781369262710	941U-HSG/HWK ASSY (FLUOR)	✓		C
783369020291	781369454955	940U HSG/HWK ASSY	✓		C
783370020303	781369454962	940C HSG/HWK ASSY	✓		C
783362020229	781369087726	946C-HSG/HWK ASSY	✓		C
783364020241	781369238609	944C-HSG/HWK ASSY	✓		C
783365020257	781369240121	945C-HSG/HWK ASSY	✓		C
783367020279	781369411569	942C-HSG/HWK ASSY	✓		C
783368020285	781369416076	943C-HSG/HWK ASSY	✓		C
---	CB100AK5F13E	120V, 13W PLC13, Composite Brick light, Black		✓	
---	CB100AK5IE	120V, 40W T10, Composite Brick light, Black		✓	
---	CB100HK5F13E	120V, 13W PLC13, Composite Brick light, Bronze		✓	
---	CB100HK5IE	120V, 40W T10, Composite Brick light, Bronze		✓	
783398020583	D2953910-REPL	REPL FACEPLATE ASSY 942PG BRP	✓		C
783399020599	D3006100-REPL	REPL.FACEPLATE ASSY 942RDG WP	✓		C
783400020600	D4484001	COVER ASSY 963C SQUARE BLP/L	✓		C
783401020616	D4484003	COVER ASSY 963C SQUARE WP/L	✓		C
783352010148	RSB2AT5F13E	120V, 13W PLC13 (K5F13E), 13W PLC13 (K5F13E) Bubble Brick light, Black	✓		C
783352010186	RSB2AT5IE	120V, 40W T10 (K5IE) ,40W T10 (K5IE) Bubble Brick light, Black	✓		C
783352010223	RSB2HT5F13E	120V, 13W PLC13 (K5F13E), 13W PLC13 (K5F13E) Bubble Brick light, Bronze	✓		C
783352010278	RSB2HT5IE	120V, 40W T10 (K5IE) ,40W T10 (K5IE) Bubble Brick light, Bronze	✓		C
783352010728	RSC2AK5F13E •	120V, 13W PLC13 (K5F13E), 13W PLC13 (K5F13E) Louvered Brick light, Black	✓		C
783352010766	RSC2AK5IE •	120V, 40W T10 (K5IE) ,40W T10 (K5IE) Louvered Brick light, Black	✓		C
783352010810	RSC2BK5F13E	120V, 13W PLC13 (K5F13E), 13W PLC13 (K5F13E) Louvered Brick light, White	✓		C
---	RSC2BK5IE	120V, 40W T10 (K5IE) ,40W T10 (K5IE) Louvered Brick light, White		✓	
783352010940	RSC2HK5F13E •	120V, 13W PLC13 (K5F13E), 13W PLC13 (K5F13E) Louvered Brick light, Bronze	✓		C
---	RSC2HK5F18E	120V, 18W PLC18, Louvered Brick Light, Bronze		✓	
783352010995	RSC2HK5IE •	120V, 40W T10 (K5IE) ,40W T10 (K5IE) Louvered Brick light, Bronze	✓		C
783352011510	RSF2AL5F13E	120V, 13W T10, 13W T10 Opal Lens Brick light, Black	✓		C
---	RSF2AL5F18E	120V, 18W T10, 18W T10 Opal Lens Brick light, Black		✓	
783352011626	RSF2HL5F13E	120V, 13W T10, 13W T10 Opal Lens Brick light, Bronze	✓		C
783352011664	RSF2HL5IE	120V, 40W T10, 40W T10 Opal Lens Brick light, Bronze	✓		C
---	RSS2AK5F13E	120V, 13W T10, 13W T10 Opal Lens Brick light, Black		✓	

C = Carrollton, Texas

A blue dot "•" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.



Step Light - Low Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352005526	CB100AK5812	12V, (2) 18W 1141, Composite Brick light, Black	✓		C
783352005557	CB100HK5812	12V, (2) 18W 1141, Composite Brick light, Bronze	✓		C
783352011404	RSCL2AK5812	12V, (2) 18W 1141, Low Voltage Louver Brick light, Black	✓		C
783352011459	RSCL2HK5812 •	12V, (2) 18W 1141, Low Voltage Louver Brick light, Bronze	✓		C

Step Light Accessories

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352007438	MAKEC	Mounting Kit for Bricklyte in Existing Stud Wall,	✓		C
783352007445	MAKES	Mounting Kit for Existing Stud Wall,	✓		C
783352001979	MAKM •	Mounting Kit for in Masonry,	✓		C
783352007452	MAKNS	Mounting Kit for in New Stud Wall,	✓		C
783352010094	RS2-AHO •	HSG Only for RSB2/RSC2/RSF2, Black, Black	✓		C
783352010100	RS2-BHO	HSG for RSB2/RSC2/RSF2, White, White	✓		C
783352010117	RS2-HHO •	HSG Only for RSB2/RSC2/RSF2, Bronze, Bronze	✓		C
783437020970	RS2-NHO	HSG Only for RSC2/RSV2, Natural Bronze, Natural Brass	✓		C



Transformers/Power Supply

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352003256	ABH1001	Above Ground Ballast	✓		C
783352016751	ABH1501	Above Ground Ballast	✓		C
783352003294	ABH351	Above Ground Ballast	✓		C
783352003300	ABH501	Above Ground Ballast	✓		C
783352003324	ABH701	Above Ground Ballast	✓		C
783352006783	IBH1001	Inground Ballast Box	✓		C
783412020728	IBH1501	Inground Ballast Box	✓		C
783352006820	IBH351	Inground Ballast Box	✓		C
783352006844	IBH501	Inground Ballast Box	✓		C
783352006868	IBH701	Inground Ballast Box	✓		C
783352013057	TB100-12	100 VA Transformer	✓		C
783352013224	TBC303-15 •	Inground Transformer 300W quad tap w/ breakers	✓		C
783352013248	TBC603-15 •	Inground Transformer 600W quad tap w/ breakers	✓		C
783352015037	TC152-12 •	150VA/150W Transformer, Grey	✓		C
783352015044	TC152-12TP •	150VA/150W Transformer w/Timer & Photo Cell, Grey	✓		C
783352015051	TC354-15 •	300VA MULTITAP TFMR, SM Painted, Hinged Door, Grey	✓		C
783352015068	TC654-15 •	600VA MULTITAP TFMR, SM Painted, Hinged Door, Grey	✓		C
783352015075	TC954-15 •	900VA MULTITAP TFMR, SM Painted, Hinged Door, Grey	✓		C
783352015457	TSS1293-22	1200W, 12-22V, MULTI TAP, Stainless Steel	✓		C
783352015006	TSS354-15 •	300VA MULTITAP TFMR, SM Stainless, Hinged Door, Stainless Steel	✓		C
783352015013	TSS654-15 •	600VA MULTITAP TFMR, SM Stainless, Hinged Door, Stainless Steel	✓		C
783352016539	TSS693-22	600W, 12-22V, MULTI TAP, Stainless Steel	✓		C
783352015020	TSS954-15 •	900VA MULTITAP TFMR, SM Stainless, Hinged Door, Stainless Steel	✓		C
783352016546	TSS993-22	900W, 12-22V, MULTI TAP, Stainless Steel	✓		C

C = Carrollton, Texas

A blue dot "•" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.



Underwater LED - Low Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352019271	UWUL516-HLED4NFW •	12V, LED, 4 Watts, Narrow Flood, Warm CCT, Bronze	✓		C



Underwater - Line Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
---	UW1250-N	120V, 250W, T4, Freestanding Underwater, Natural Brass		✓	



Underwater - Low Voltage

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783352014252	UWL1-A	12V, 10W, T3, Underwater Spread, Black	✓		C
783352014337	UWUL516-H •	12V, 50W, MR16, Micro Underwater, Bronze	✓		C



Lamp Holders

UPC Code	Catalog Number	Description	Service Smart	Spec Smart	Stocked In
783371020319	30KL	150W, Max Lamp Holder	✓		C
783372020325	3300BULK	Lampholder, Smooth Zinc Finish	✓		C
783373020331	3300WHT	Lampholder, White Finish	✓		C
783377020375	6400E	500W Power Beam, Aluminum Finish Enclosed	✓		C
783446021067	V4400	75 W - 300W Natural Aluminum Open Flood	✓		C
783447021073	V4400E	74W - 300W Natural Aluminum Enclosed Flood	✓		C
786034100908	CLD1500	250W / PAR38 / QPAR38 Lamp holder	✓		C

C = Carrollton, Texas

A blue dot "•" beside a blue catalog number indicates item is a recommended distributor shelf stock item.

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this guide.

Product information may change without notice. Contact your local Philips sales representative for additional product information.



©2014 Koninklijke Philips N.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

PLT-1407BR 10/14 philips.com/luminaires

Philips Lighting
North America Corporation
200 Franklin Square Drive
Somerset, NJ 08873
Tel. 855-486-2216

Imported by: Philips Lighting,
A division of Philips Electronics Ltd.
281 Hillmount Rd,
Markham, ON, Canada L6C 2S3
Tel. 800-668-9008