

UPC	6NC	Pkg Part No.	Product Description	Product Tech
46677408923	408922	822590	EL-A PAR38 23W 2pc	CFLi
46677408565	408567	821209 / 821210	BC-EL-mdTQS 18W T2	CFLi
46677417406	417402	821514	BC-EL-mCan T2 9W	CFLi
46677419950	419951	821682	EL-A PAR38 23W	CFLi
46677418076	418079	821964	BC- EL-mdTQS 13W T2 6.5K	CFLi
46677211073	211078	822748	EL-A G40 23W	CFLi
46677417086	417089	821237	BC-EL-mdTQS 18W T4	CFLi
46677414023	414029	821301	EL-mdT2 13W 3.5K	CFLi
46677413996	413996	822175	EL-mdTQS 13W T2	CFLi
46677414016	414011	822176	EL-mdTQS 23W T2	CFLi
46677414047	414045	822178	EL-mdT2 13W 5K	CFLi
46677414054	414052	822181	EL-mdT2 23W 3.5K	CFLi
46677227913	227918	822589	EL-A PAR38 23W 2pc	CFLi
46677200800	200808	819247	EL-A SWP 20W	CFLi
46677408558	408559	21206 / 82120	BC-EL-mdTQS 13W T2	CFLi
46677408572	408575	21211 / 82121	BC-EL-mdTQS 23W T2	CFLi
46677139476	139477	821218	BC-EL-dT 42W LL	CFLi
46677405854	405852	821228	EL-mdTQ D2D 14W	CFLi
46677417079	417071	821236	BC-EL-mdTQS 13W T4	CFLi
46677417093	417097	821238	BC-EL-mdTQS 23W T4	CFLi
46677420055	420059	821244	BC-EL-mdT 20W 1% DIM	CFLi
46677408541	408542	21246 / 82124	BC-EL-mdTQS 9W T2	CFLi
46677417062	417063	821248	BC-EL-mdTQS 9W T3	CFLi
46677417376	417378	821390	EL-A SWP 14W	CFLi
46677156398	156398	821393	EL-mdT 32W	CFLi
46677411381	411389	821407	EL-mdT 13W GU24 4.1K	CFLi
46677411770	411777	821408	EL-mdT 18W GU24 4.1K	CFLi
46677418083	418087	821424	BC-EL-mdTQS 18W T3	CFLi
46677419790	419796	21503 / 82150	BC-EL-A SWP 9W	CFLi
46677419776	419770	21506 / 82150	BC-EL-A FAN 9W	CFLi
46677418632	418632	821509	BC-EL-A 15W R30	CFLi
46677416782	416784	821511	BC-EL-A PAR38 23W	CFLi
46677417437	417436	821515	BC-EL-Can T2 9W	CFLi
46677419783	419788	21525 / 82152	BC-EL-A FAN 9W	CFLi
46677411398	411397	821547	EL-mdT 23W GU24 4.1K	CFLi
46677130770	130773	821605	SLS Universal 20W	CFLi
46677135744	135749	821608	SLS Universal 25W	CFLi
46677146917	146910	821616	SLS Universal 14W	CFLi
46677407155	407155	821624	EL-dT DIM 32W	CFLi
46677139483	139485	821634	EL-dT42W	CFLi
46677211936	211938	821635	EL-3W 11-23-34W	CFLi
46677417413	417410	821668	EL-mCan T2 9W	CFLi
46677417444	417444	821669	EL-Can T2 9W	CFLi
46677418625	418624	821679	EL-A R30 15W 4.1K	CFLi
46677419806	419804	21961 / 82196	BC-EL-A SWP 14W	CFLi
46677419813	419812	21979 / 82198	BC-EL-A SWP 14W	CFLi

46677418090	418095	821985	BC-EL-mdTQS 23W T3	CFLi
46677418069	418061	821986	BC-EL-mdTQS 13W T3	CFLi
46677417420	417428	21997 / 82199	BC-EL-Can T2 9W	CFLi
46677417390	417394	21999 / 82150	BC-EL-mCan T2 9W	CFLi
46677406202	406207	822032	EL-A 15W R30	CFLi
46677157036	157032	822033	EL-A 15W R30	CFLi
46677406219	406215	822034	EL-A 15W R31	CFLi
46677419974	419977	822058	EL-A R30 EDIM 16W	CFLi
46677419998	419993	822059	EL-A R40 EDIM 20W	CFLi
46677420017	420018	822060	EL-A PAR38 EDIM 20W	CFLi
46677414030	414037	822180	EL-mdT2 13W 4.1K	CFLi
46677414061	414060	822182	EL-mdT2 23W 4.1K	CFLi
46677414078	414078	822183	EL-mdT2 23W 5K	CFLi
46677414085	414086	822184	EL-mdT2 26W 4.1K	CFLi
46677414092	414094	822185	EL-mdT2 26W 5K	CFLi
46677414009	414003	822187	EL-mdTQS 18W T2	CFLi
46677157029	157024	822578	EL-A R40 23W	CFLi
46677157166	157164	822588	EL-A PAR38 23W 2pc	CFLi
46677427535	427534	822670	EL-A R20 13W 3K	CFLi
46677426828	426825	822720	EL-A R20 13W	CFLi
46677211066	211060	822749	EL-A G30 16W	CFLi
46677417239	417238	822765	EL-mdT 13W GU24	CFLi
46677417246	417246	822766	EL-mdT 18W GU24	CFLi
46677417253	417253	822767	EL-mdT 23W GU24	CFLi
46677420024	420026	822807	EL-mdT 15W 1% DIM	CFLi
46677420031	420034	822808	EL-mdT 20W 1% DIM	CFLi
46677417352	417352	822820	EL-A G25 T3 9W	CFLi
46677413989	413988	822832	EL-mdTQS 9W T2	CFLi
46677422295	422295	822867	EL-Can T2 5W	CFLi
46677422301	422303	822868	EL-mCan T2 5W	CFLi
46677147921	147926	822872	EL-mdT 5W	CFLi
46677417338	417337	23025 / 82302	BC-EL-A G25 T3 9W	CFLi
46677417345	417345	23027 / 82302	BC-EL-A G25 T3 9W	CFLi
46677422318	422311	823030	BC-EL-mCan T2 5W	CFLi
46677420093	420091	823031	BC- EL-mdTQS 13W T2 6.5K	CFLi
46677426835	426833	823041	BC-EL-A R20 13W	CFLi
46677417451	417451	23225 / 82322	BC-EL-A FAN 5W	CFLi
46677421205	421206	823227	BC-EL-A R40 23W	CFLi
46677417475	417477	823699	EL-A FAN 5W	CFLi
46677427870	427872	824150	EL-A G25 14W 6-1	CFLi
46677417369	417360	824151	EL-A SWP 9W	CFLi
46677407780	407783	824177	EL-O 14W Prisma	CFLi
46677414108	414102	824178	EL-mdT2 26W	CFLi
46677419981	419985	824384	BC-EL-A R30 EDIM 16W	CFLi
46677428730	428730	824480	BC-EL-mdT 20W 1% DIM	CFLi
46677428723	428722	824481	BC-EL-mdT 15W 1% DIM	CFLi
46677420000	420000	824490	BC-EL-A R40 EDIM 20W	CFLi

46677431242	431247	824605	EL-mdT3 9W 4.1K	CFLi
46677431761	431767	824649	EL-dT 65W	CFLi
46677432348	432344	824716	EL-dT 65W 4.1K	CFLi
46677408671	408674	824962	BC-EL-O 14W Prisma SC	CFLi
46677415044	415042	824963	EL-A T2 SC 9W 6-2	CFLi
46677415037	415034	824964	EL-A T2 SC 14W 6-2	CFLi
46677433604	433607	824965	EL-A T2 SC 14W 6.5K 2PK	CFLi
46677433550	433557	824966	BC-EL-mdTQS 23W T2 6.5K	CFLi
46677433611	433615	24968 / 82497	BC-EL-A R30 EDIM 16W 6.5K 2PK	CFLi
46677428747	428748	25303 / 82497	BC-EL-A R30 EDIM 16W	CFLi
46677225193	248765	819732	65BR30-FL55 120V 12-1	GLS
46677167820	167411	819735	65BR-FL60-LL 120V 8-1 TP	GLS
46677225360	389130	819738	65BR-FL60 120V 24-1	GLS
46677104511	270819	819747	40A 120V 12-4	GLS
46677293802	293803	820402	65BR30-FL55 120-130V SP 12-1	GLS
46677167691	167692	820453	65BR30-SP20-LL 120V 12-1 TP	GLS
46677223038	223032	820457	45BR30-FL55-LL TP 120V 4-3	GLS
46677167684	167684	820497	65BR30-FL-55-LL 120V 12-1	GLS
46677167516	167510	820511	45BR30-FL55-LL 120V 12-1 TP	GLS
46677104559	374819	820543	40A-W-TP 120V 12-4	GLS
46677137854	137851	820544	65BR30-FL-NTL 120V 12-1 TP	GLS
46677104566	374835	820552	60A-W-TP 120V 12-4	GLS
46677135584	135582	820556	40A-NTL-TP 120V 12-4 TP	GLS
46677167974	167972	820567	40A-CL-LL 120V 12-2 WP TP	GLS
46677168698	168690	820572	DURAMAX 40W MED 120V A19 SW 40W	GLS
46677169534	169532	820623	50-150A-WL 120V 4-3	GLS
46677270032	270033	820626	150A 120V 48PK	GLS
46677374181	374181	820641	150A-CL 120-130V 60PK	GLS
46677104528	270827	820690	60A 120V 12-4	GLS
46677168223	168229	820798	BC60BA9-1-2-CL-LL 6-2 TP	GLS
46677168421	168427	820799	BC60F15-CL-LL 6-2 TP	GLS
46677140083	140087	821759	65BR40-FL 130V 12-1 PRO	GLS
46677168742	234278	821760	DIS60A-WL 120V 72-4	GLS
46677222482	222489	821766	60A19-35 130V 48PK PLC	GLS
46677169480	169482	821784	50-150A-WL 120V 12-1	GLS
46677169497	169490	821786	50-250A-WL 120V 12-1	GLS
46677101183	366625	821789	30-100A-SW 120V 12-1	GLS
46677169473	169474	821800	30-100A-WL 120V 12-1	GLS
46677104559	374827	821803	40A-W-TP 120V 24-4	GLS
46677106188	234146	821805	60A 120V 24-2LP-SL W-P	GLS
46677109110	323592	821807	50-150A-DL 120V 12-1	GLS
46677168742	168740	821809	DURAMAX 60W MED 120V A19 SW 40W	GLS
46677143558	143552	822075	50ER30 120-130V 24-1	GLS
46677385682	385682	822097	150BR38-5FL 12-1 PK	GLS
46677225827	248872	822345	65BR30-FLVALUE PACK 1-12	GLS
46677387792	387795	822346	65BR-FL-VP 1-12 PACK	GLS
46677226916	429472	822587	65BR30-FL55 8-3 TP	GLS

46677138103	138107	822761	60T10-64 120V 24-1	GLS
46677138110	138115	822762	60T10-64-IF 120V 24-1	GLS
46677167943	167940	823477	60A-CL-LL 120V 12-2 PS TP	GLS
46677135591	135590	823485	60A-NTL-TP 120V 12-4 TP	GLS
46677149994	149996	823492	60A-52A-99-EW 120-130V 48-1	GLS
46677373993	373993	823493	40A-CL 120V-130V 48PK	GLS
46677222468	222463	823494	60A-99 130V 48PK PLC	GLS
46677140076	140079	823495	65BR30-FL 130V 12-1 PRO	GLS
46677374693	374694	824115	60A 120V 48-1	GLS
46677374716	374710	824116	60A 130V 48-1	GLS
46677104566	374843	824118	60A-W-TP 120V 24-4	GLS
46677375225	375220	824120	60A-CL 130V 48PK	GLS
46677135645	135640	824124	50-150A-NTL 120V 12-1 TP	GLS
46677432317	432310	824143	40A-W-TP 120V 6-6	GLS
46677408862	408864	824648	65BR30-B3G1 120V	GLS
46677374662	374660	825281	40A 130V 48PK	GLS
46677374655	374652	825284	40A 120V 48PK	GLS
46677213596	213595	820395	40BR30/HEA/FL 120V 12/1	HAL
46677222383	222380	820401	40BR40/HEA/FL 120V 12/1	HAL
46677144975	144971	820521	40PAR30S/IRC/FL25 120V 15PK	HAL
46677238568	238568	820538	55PAR30S/IRC+/FL25 120V 15/1	HAL
46677238575	238576	820539	55PAR30S/IRC+/WFL40 120V 15/1	HAL
46677238551	238550	820541	55PAR30S/IRC+/SP10 120V 15/1	HAL
46677282066	385518	820786	BC60F15/HAL/POSTTOP 4PK TP	HAL
46677238476	238477	821263	55PAR38/IRC+/SP10 120V 12/1	HAL
46677238506	238501	821265	83PAR38/IRC+/SP10 120V 12/1	HAL
46677238520	238527	821269	83PAR38/IRC+/WFL40 120V 12/1	HAL
46677420857	420851	822042	40G25/EV/W 120V 12/1 TP	HAL
46677420840	420844	822043	40G25/EV/CL 120V 12/1 TP	HAL
46677144999	144997	822653	50PAR30S/IRC+/SP10 120V 15PK	HAL
46677238001	238006	822654	50PAR30L/IRC+/WFL40 120V 15/1	HAL
46677234294	234294	822655	50PAR30L/IRC+/FL25 120V 15/1	HAL
46677237998	237990	822656	50PAR30L/IRC+/SP10 120V 15/1	HAL
46677145019	145011	822662	50PAR30S/IRC+/WFL40 120V 15/1	HAL
46677145002	145003	822664	50PAR30S/IRC+/FL25 120V 15PK	HAL
46677423858	423855	823043	BC72F15/EV/CL 120V 4/1	HAL
46677237301	237305	823652	50PAR30S/IRCE/SP10 120V 15/1	HAL
46677237295	237297	823653	40PAR30S/IRCE/FL25 120V 15/1	HAL
46677237318	237313	823654	50PAR30S/IRCE/FL25 120V 15/1	HAL
46677237394	237396	823657	60PAR38/IRCE/SP10 120V 12/1	HAL
46677237288	237511	823659	40PAR30S/IRCE/SP10 120V 15/1	HAL
46677134129	134122	824020	BC45PAR16/HAL/FL/LL 6/1 TP	HAL
46677134136	134130	824021	BC60PAR16/HAL/FL/LL 120V 6/1	HAL
46677428952	428952	824076	53PAR30L/EVP/WFL40 120V 15/1	HAL
46677428907	428904	824078	53PAR30S/EVP/FL25 120V 15/1	HAL
46677428884	428888	824080	53PAR30S/EVP/SP10 120V 15/1	HAL
46677428983	428986	824081	53PAR30S/EVP/WFL40 120V 15/1	HAL

46677428853	428854	824085	53PAR38/EVP/FL25 120V 12/1	HAL
46677428891	428896	824087	53PAR38/EVP/SP10 120V	HAL
46677426736	426734	824168	40PAR38/IRCE/UT4/SP10 120V 12/1	HAL
46677426743	426742	824169	40PAR38/IRCE/UT4/FL25 120V 12/1	HAL
46677429454	429456	824170	50PAR38/IRCE/UT4/FL25 120V 12/1	HAL
46677429461	429464	824171	50PAR38/IRCE/UT4/SP10 120V 12/1	HAL
46677429447	429449	824172	70PAR38/IRCE/UT4/SP10 120V 12/1	HAL
46677429997	429992	824173	40PAR38/IRCE/UT4/WFL40 120V 12/1	HAL
46677430184	430181	824174	50PAR38/IRCE/UT4/WFL40 120V 12/1	HAL
46677430191	430199	824175	70PAR38/IRCE/UT4/WFL40 120V 12/1	HAL
46677430207	430207	824176	70PAR38/IRCE/UT4/FL25 120V 12/1	HAL
46677419561	419564	824180	53PAR30L/EV/SP10 120V 6/1 TP	HAL
46677420208	420208	824181	50PAR30L/EV/FL25/LL 120V 6/1 TP	HAL
46677421434	421438	824182	53PAR30S/EV/FL25 120V 6/1 TP	HAL
46677226954	226951	824188	43A19/EV/NTL 120V 12/2	HAL
46677226961	226969	824189	53A19/EV/NTL 120V 12/2	HAL
46677424268	424267	824491	BC40BA11/E26/EV/CL 120V 6/2 TP	HAL
46677424275	424275	824492	BC25B11/E26/EV/CL 120V 6/2 TP	HAL
46677424282	424283	824493	BC40B11/E26/EV/CL 120V 6/2 TP	HAL
46677421199	421198	824514	70BR40/EV/FL 120V 4/1	HAL
46677421168	421164	824515	40BR40/EV/FL 120V 4/1	HAL
46677421182	421180	824516	50BR30/EV/FL 120V 5/1	HAL
46677421069	421065	824518	40BR30/EV/FL 120V 5/1	HAL
46677421175	421172	824518	40R20/EV/FL 120V 6/1	HAL
46677419547	419549	824537	53PAR30L/EV/FL25 120V 6/1 TP	HAL
46677421120	421123	824538	53PAR30S/EV/SP10 120V 6/1 TP	HAL
46677419554	429365	824539	53PAR30L/EV/FL25 120V 16/2 TP	HAL
46677226992	226993	824590	72A19/EV/NTL 120V 12/2	HAL
46677229979	229971	824597	70BR40/HEA/FL 120V 12/1	HAL
46677428921	428920	824602	53PAR30L/EVP/FL25 120V 15/1	HAL
46677147273	408831	824614	45R20/HAL/FL 120V 6/1	HAL
46677238445	238444	824634	39PAR38/IRC+/SP10 120V 12/1	HAL
46677238452	238451	824635	39PAR38/IRC+/FL25 120V 12/1	HAL
46677421335	430421	824855	70PAR38/EV/FL25/LL 120V 6/2 TP	HAL
46677421267	421263	824857	70PAR38/EV/SP10/LL 120V 6/1 TP	HAL
46677419455	419457	824860	53PAR38/EV/SP10 120V 6/1 TP	HAL
46677424985	424985	824863	83PAR38/EV/FL25/LL 120V 6/1 TP	HAL
46677421304	421305	824864	70PAR38/EV/FL25/LL 120V 6/1 TP	HAL
46677421281	421289	824865	39PAR38/EV/FL25/LL 120V 6/1 TP	HAL
46677419448	419440	824866	53PAR38/EV/FL25 120V 6/1 TP	HAL
46677138615	138610	824868	70PAR38/IRC+/SP10 120V	HAL
46677138622	138628	824869	70PAR38/IRC+/FL25 120V	HAL
46677138639	138636	824870	70PAR38/IRC+/WFL40 120V	HAL
46677138769	138768	824871	100PAR38/IRC+/SP10 120V 12PK	HAL
46677138776	138776	824872	100PAR38/IRC/FL25 120V	HAL
46677138783	138784	824873	100PAR38/IRC+/WFL40 120V 12PK	HAL
46677145033	145037	824874	40PAR38/IRC/FL25 120V 12PK	HAL

46677145057	145052	824875	50PAR38/IRC+/SP10 120V 12PK	HAL
46677145064	145060	824876	50PAR38/IRC+/FL25 120V 12PK	HAL
46677145071	145078	824877	50PAR38/IRC/WFL40 120V 12PK	HAL
46677216733	216739	824878	50PAR38/IRC+/FL25/LTD 120V	HAL
46677238650	238659	824881	55PAR38/IRC+/FL25 120V 12/1	HAL
46677238490	238493	824882	55PAR38/IRC+/WFL40 120V 12/1	HAL
46677238513	238519	824883	83PAR38/IRC+/FL25 120V 12/1	HAL
46677424251	424259	824974	BC25B11/E26/EV/CL 120V 6/2 TP	HAL
46677433727	433722	824975	BC43F15/EV/CL 120V 4/1 TP	HAL
46677433567	433565	824978	BC40G16.5/EV/CL 120V 6/2 TP	HAL
46677433574	433573	824979	BC40G16.5/EV/W 120V 6/2 TP	HAL
46677434748	434746	824986	BC45PAR16/EV/FL 120V 6/1TP	HAL
46677434724	434720	824987	BC60PAR16/EV/FL 120V 6/1TP	HAL
46677433680	433680	825165	40G25/EV/CL 120V 4/3 TP	HAL
46677433697	433698	825166	40G25/EV/W 120V 4/3 TP	HAL
46677409845	409847	825176	43A19/EV 120V 12/2	HAL
46677409838	409839	825177	29A19/EV 120V 12/2	HAL
46677410506	410506	825178	29A19/EV/CL 120V 12/2	HAL
46677410490	410498	825181	43A19/EV/CL 120V 12/2	HAL
46677428914	428912	825184	39PAR30S/EVP/SP10 120V 15/1	HAL
46677419417	429373	825185	72PAR38/EV/FL25 120V 6/2 TP	HAL
46677419769	419762	825186	39PAR20/EV/FL25 120V 6/4	HAL
46677419868	419861	825187	39PAR20/EV/FL25 120V 6/1 TP	HAL
46677419400	419408	825191	72PAR38/EV/FL25 120V 6/1 TP	HAL
46677419462	428805	825192	72PAR38/EV/FL25 120V 1/4	HAL
46677428846	428847	825194	39PAR38/EVP/FL25 120V 12/1	HAL
46677428969	428960	825195	39PAR30S/EVP/FL25 120V 15/1	HAL
46677425203	425207	825196	39PAR20/EVP/FL25 120V 15/1	HAL
46677428877	428870	825197	39PAR30L/EVP/FL25 120V 15/1	HAL
46677428945	428946	825198	72PAR38/EVP/SP10 120V 12/1	HAL
46677428938	428938	825199	72PAR38/EVP/FL25 120V 12/1	HAL
46677428860	428862	825200	39PAR38/EVP/SP10 120V 12/1	HAL
46677419387	419382	825201	72PAR38/EV/SP10 120V 6/1 TP	HAL
46677425128	425124	825202	39PAR20/EVP/SP10 120V 15/1	HAL
46677431495	431494	825257	72A19/EV/LL 120V 6/4	HAL
46677431501	431502	825258	43A19/EV/LL 120V 6/4	HAL
46677431518	431510	825259	29A19/EV/LL 120V 6/4	HAL
46677433529	433524	825270	53A19/EV/LL 120V 6/4	HAL
46677426033	426031	825278	43A19/EV 120V 6/4	HAL
46677426002	426007	825279	29A19/EV 120V 6/4	HAL
46677409821	409821	825353	72A19/EV 120V 12/2	HAL
46677410483	429241	825354	72A19/EV/CL 120V 12/2	HAL
46677433895	433896	825357	72A19/EV/LL 120V 12/2	HAL
46677433901	433904	825358	43A19/EV/LL 120V 12/2	HAL
46677433918	433912	825359	29A19/EV/LL 120V 12/2	HAL
46677433888	433888	825360	53A19/EV/LL 120V 12/2	HAL
46677419424	419424	825375	39PAR38/EV/FL25 120V 6/1 TP	HAL

46677419738	419739	825376	39PAR20/EV/SP10 120V 6/1 TP	HAL
46677419431	419432	825377	39PAR38/EV/SP10 120V 6/1 TP	HAL
46677419745	419747	825378	39PAR30L/EV/FL25 120V 6/1 TP	HAL
46677426040	426049	825456	72A19/EV 120V 6/4	HAL
46677420802	420802	822674	13PAR30L-END-F25 3000 DIM AF 6-1	LED
46677423353	423350	822696	19.5PAR38-END-F25 4000 DIM AF 6-1	LED
46677420529	420521	822713	18PAR38-END-F25 3000-950 DIM AF 6-1	LED
46677420888	420885	822714	18PAR38-END-F36 2700-900 DIM AF 6-1	LED
46677420895	420893	822715	18PAR38-END-F36 3000-950 DIM AF 6-1	LED
46677421212	421214	822716	19.5PAR38-END-F25 2700 DIM AF 6-1	LED
46677421229	421222	822717	19.5PAR38-END-F25 3000 DIM AF 6-1	LED
46677420307	420307	822777	BC10PAR30L-VIS-3000 25D DIM 120V	LED
46677420321	420323	822795	BC18PAR38-VIS-3000 25D DIM 120V	LED
46677420499	420497	824060	13PAR30L-END-F36 2700 DIM AF 6-1	LED
46677420505	420505	824061	13PAR30L-END-F36 3000 DIM AF 6-1	LED
46677420475	420471	824062	13PAR30L-END-F25 2700 DIM AF 6-1	LED
46677423513	423517	824072	15DL6-END-F90 2700 DIM 6-1	LED
46677423445	423442	824153	13PAR30S-END-F25 2700 DIM AF 6-1	LED
46677423452	423459	824154	13PAR30S-END-F25 3000 DIM AF 6-1	LED
46677423469	423467	824155	13PAR30S-END-F36 2700 DIM AF 6-1	LED
46677423476	423475	824156	13PAR30S-END-F36 3000 DIM AF 6-1	LED
46677426118	426114	824167	BC8PAR20-AMB-3000 DIM 120V	LED
46677423421	423426	824192	BC19.5PAR38-AMB-F25 3000 DIM 120V	LED
46677420314	420315	824194	BC13PAR30L-AMB-F25 3000 120V	LED
046677425289	425280	824197	BC19.5PAR38-AMB-F25 5000 DIM 120V	LED
046677425296	425298	824198	BC13PAR30L-AMB-5000 DIM 120V	LED
46677428815	428813	824269	8R20-F90 2700 DIM 6-1	LED
46677425333	425330	824273	13PAR30L-END-F25 4000 DIM AF 6-1	LED
46677425340	425348	824274	13PAR30L-END-F36 4000 DIM AF 6-1	LED
46677425432	425439	824275	18PAR38-END-F25 4000 DIM AF 6-1	LED
46677425388	425389	824276	13PAR30S-END-F25 4000 DIM AF 6-1	LED
46677425395	425397	824277	13PAR30S-END-F36 4000 DIM AF 6-1	LED
46677425449	425447	824278	18PAR38-END-F36 4000 DIM AF 6-1	LED
46677425463	425462	824279	19.5PAR38-END-F36 2700 DIM AF 6-1	LED
46677425487	425488	824280	19.5PAR38-END-F36 3000 DIM AF 6-1	LED
46677425500	425504	824281	19.5PAR38-END-F36 4000 DIM AF 6-1	LED
46677425364	425363	824282	13PAR30S-END-S15 3000 DIM AF 6-1	LED
46677425401	425405	824283	18PAR38-END-S15 2700 DIM AF 6-1	LED
46677425418	425413	824284	18PAR38-END-S15 3000 DIM AF 6-1	LED
46677425425	425421	824285	18PAR38-END-S15 4000 DIM AF 6-1	LED
46677425357	425355	824286	13PAR30S-END-S15 2700 DIM AF 6-1	LED
46677425371	425371	824287	13PAR30S-END-S15 4000 DIM AF 6-1	LED
46677430214	430215	824513	BC6PAR16-AMB-3000 25D DIM 120V	LED
46677429416	429415	824519	9.5BR30-VIS-2700 120V	LED
46677429409	429407	824520	13PAR38-VIS-F25 3000 AF 120V	LED
46677425272	425272	824546	BC19.5PAR38-AMB-F25 2700 DIM 120V	LED
46677425470	425470	824548	19.5PAR38-END-S15 3000 DIM AF 6-1	LED

46677425456	425454	824550	19.5PAR38-END-S15 2700 DIM AF 6-1	LED
46677425494	425496	824551	19.5PAR38-END-S15 4000 DIM AF 6-1	LED
46677426323	426320	824556	13PAR38-COREPRO-F25 2700 AF 6-1	LED
46677426330	426338	824557	13PAR38-COREPRO-F25 3000 AF 6-1	LED
46677426347	426346	824558	13PAR38-COREPRO-F25 4000 AF 6-1	LED
46677420291	423756	824561	BC14.5BR40-AMB-F60 2700 DIM 120V	LED
46677423407	423400	824562	BC8R20-AMB-2700 DIM 120V	LED
46677427771	427773	824566	BC3B12-AMB-2700- E26 DIM 120V	LED
46677429034	429035	824576	17PAR38-F25 3000 DIM AF 6-1	LED
46677429065	429068	824579	17PAR38-F36 3000 DIM AF 6-1	LED
46677426965	426964	824591	12PAR30S-F36 3000 AF SO 6-1	LED
46677426941	426940	824593	12PAR30S-F25 4000 AF SO 6-1	LED
46677426934	426932	824594	12PAR30S-F25 3000 AF SO 6-1	LED
46677426972	426972	824595	12PAR30S-F36 4000 AF SO 6-1	LED
46677431372	431379	824598	12PAR30S-F25 3500 AF SO 6-1	LED
46677431389	431387	824601	12PAR30S-F36 3500 AF sO 6-1	LED
46677427801	427807	824612	3.5F15-END-2700-E26 DIM 8-1	LED
46677427818	427815	824613	3.5B12-END-2700-E26 DIM 8-1	LED
46677426125	426122	824616	8PAR20-END-F25 2700 DIM AF 6-1	LED
46677426163	426163	824617	8PAR20-END-F36 3000 DIM AF 6-1	LED
46677426132	426130	824618	8PAR20-END-F25 3000 DIM AF 6-1	LED
46677426446	426445	824619	13BR30-END-F90 22K-27K DIM 6-1	LED
46677426156	426155	824620	8PAR20-END-F36 2700 DIM AF 6-1	LED
46677426170	426171	824622	8PAR20-END-F36 4000 DIM AF 6-1	LED
46677426149	426148	824623	8PAR20-END-F25 4000 DIM AF 6-1	LED
46677429386	429381	824624	10.5A19-VIS-3000 120V	LED
46677432188	432187	824637	15A21-2700-WHT DIM 6-1	LED
46677430108	430108	824639	13PAR38-F36 3000 DIM AF SO 6-1	LED
46677430061	430066	824643	13PAR38-F25 2700 DIM AF SO 6-1	LED
46677429096	429092	824646	19PAR38-F25 3000 DIM AF SO 6-1	LED
46677429492	429498	824651	9.5BR30-COREPRO-F90 2700 AF 6-1	LED
46677426927	426924	824652	12PAR30S-F25 2700 AF SO 6-1	LED
46677430047	430041	824704	13PAR38-S15 3000 DIM AF SO 6-1	LED
46677430023	430025	824707	19PAR38-S15 4000 DIM AF SO 6-1	LED
46677430016	430017	824708	19PAR38-S15 3000 DIM AF SO 6-1	LED
46677429133	429134	824709	19PAR38-F36 4000 DIM AF SO 6-1	LED
46677430009	430009	824710	19PAR38-S15 2700 DIM AF SO 6-1	LED
46677430085	430082	824711	13PAR38-F25 4000 DIM AF SO 6-1	LED
46677430030	430033	824713	13PAR38-S15 2700 DIM AF SO 6-1	LED
46677425258	425256	824714	BC8A19-AMB-5000 DIM 120V	LED
46677425265	425264	824715	BC11A19-AMB-5000 DIM 120V	LED
46677430511	430512	824858	10.5A19-COREPRO-3000 6-1	LED
46677431945	431940	824886	12BR40-END-S90 2700-800 DIM AF 6-1	LED
46677424381	424382	824888	BC11A19-AMB-2700 DIM 120V	LED
46677424374	424374	824902	BC7A19-AMB-2700 DIM 120V	LED
46677423483	423483	824905	7A19-2700 DIM 6-1	LED
46677423490	423491	824906	11A19-END-2700 DIM 6-1	LED



46677432966	432962	824907	12PAR30S-F25 2700 AF RO-B 6-1	LED
46677432973	432970	824908	12PAR30S-F25 3000 AF RO-B 6-1	LED
46677432935	432930	824920	BC11PAR30L-AMB-F25 3000 AF 120V	LED
46677432959	432954	824921	BC17PAR38-AMB-F25 3000 DIM 120V	LED
46677429348	429340	824932	BC4.5F15-AMB-2700-E26 DIM 120V	LED
46677429355	429357	824936	4.5F15-END-2700-E26 DIM 8-1	LED
46677432362	432369	824937	12PAR30S-S15 2700 AF RO 6-1	LED
46677432379	432377	824938	12PAR30S-S15 3000 AF RO 6-1	LED
46677432386	432385	824939	12PAR30S-S15 4000 AF RO 6-1	LED
46677433123	433128	824981	BC8A19-SLIM-2700 DIM 120V	LED
46677433130	433136	824982	BC7A19-SLIM-5000 DIM 120V	LED
46677433147	433144	824983	BC10.5A19-SLIM-2700 DIM 120V	LED
46677433154	433151	824984	BC10.5A19-SLIM-5000 DIM 120V	LED
46677433208	433201	825153	8A19-SLIM-2700 DIM 120V	LED
46677433215	433219	825154	7A19-SLIM-5000 DIM 120V	LED
46677433222	433227	825155	10.5A19-SLIM-2700 DIM 120V	LED
46677433239	433235	825156	10.5A19-SLIM-5000 DIM 120V	LED
46677430122	430124	825157	12PAR30L-F25 2700 DIM AF RO 6-1	LED
46677430146	430140	825159	12PAR30L-F25 4000 DIM AF RO 6-1	LED
46677430153	430157	825160	12PAR30L-F36 2700 DIM AF RO 6-1	LED
46677430177	430173	825162	12PAR30L-F36 4000 DIM AF RO 6-1	LED
46677293871	293878	825173	10.5BR30-F90 2700 DIM AF 6-1	LED
46677421946	423798	825174	BC10.5BR30-AMB-2700 DIM 120V	LED
46677425302	425306	825175	BC8.5BR30-AMB-5000 DIM 120V	LED
46677432218	432211	825362	19A21-2700-WHT DIM 6-1	LED
46677430948	430942	825369	11PAR30L-F25 2700 DIM AF 6-1	LED
46677430986	430982	825372	11PAR30L-F36 3000 DIM AF 6-1	LED
46677430979	430974	825373	11PAR30L-F36 2700 DIM AF 6-1	LED
46677430955	430958	825374	11PAR30L-F25 3000 DIM AF 6-1	LED
46677432164	432161	825380	BC15A21-AMB-2700 DIM WHT 120V	LED
46677422196	422196	825385	BC17PAR38-AMB-F25 3000 OD DIM 4-1	LED
46677418557	418558	825386	17PAR38-END-F25 3000-1050 OD 6-1	LED
46677431938	431932	825393	BC12BR40-AMB-F90 2700 DIM 120V	LED
46677420512	420513	82368002	18PAR38-END-F25 2700-900 DIM AF 6-1	LED
46677429027	429027	82457501	17PAR38-F25 2700 DIM AF 6-1	LED
46677429058	429050	82457801	17PAR38-F36 2700 DIM AF 6-1	LED
46677426958	426956	82459601	12PAR30S-F36 2700 AF SO 6-1	LED
46677430092	430090	82464001	13PAR38-F36 2700 DIM AF SO 6-1	LED
46677429126	429126	82464103	19PAR38-F36 3000 DIM AF SO 6-1	LED
46677430078	430074	82464202	13PAR38-F25 3000 DIM AF SO 6-1	LED
46677429119	429118	82464403	19PAR38-F36 2700 DIM AF SO 6-1	LED
46677429089	429084	82464503	19PAR38-F25 2700 DIM AF SO 6-1	LED
46677430054	430058	82470505	13PAR38-S15 4000 DIM AF SO 6-1	LED
46677430115	430116	82470601	13PAR38-F36 4000 DIM AF SO 6-1	LED
46677429102	429100	82471201	19PAR38-F25 4000 DIM AF SO 6-1	LED
46677430139	430132	82515801	12PAR30L-F25 3000 DIM AF RO 6-1	LED
46677430160	430165	82516101	12PAR30L-F36 3000 DIM AF RO 6-1	LED

46677424435	432195	825371 Dev	BC19A21-AMB-2700K DIM WHT 120V	LED
-------------	--------	------------	--------------------------------	-----

Channel	File name
Consumer	46677408923_408922_822590_EL-A PAR38 23W 2pc
Consumer	46677408565_408567_821209 / 821210_BC-EL-mdTQS 18W T2
Consumer	46677417406_417402_821514_BC-EL-mCan T2 9W
Professional	46677419950_419951_821682_EL-A PAR38 23W
Consumer	46677418076_418079_821964_BC-EL-mdTQS 13W T2 6.5K
Professional	46677211073_211078_822748_EL-A G40 23W
Consumer	46677417086_417089_821237_BC-EL-mdTQS 18W T4
Professional	46677414023_414029_821301_EL-mdT2 13W 3.5K
Professional	46677413996_413996_822175_EL-mdTQS 13W T2
Professional	46677414016_414011_822176_EL-mdTQS 23W T2
Professional	46677414047_414045_822178_EL-mdT2 13W 5K
Professional	46677414054_414052_822181_EL-mdT2 23W 3.5K
Consumer	46677227913_227918_822589_EL-A PAR38 23W 2pc
Professional	46677200800_200808_819247_EL-A SWP 20W
Consumer	46677408558_408559_821206 / 821208_BC-EL-mdTQS 13W T2
Consumer	46677408572_408575_821211 / 821212_BC-EL-mdTQS 23W T2
Consumer	46677139476_139477_821218_BC-EL-dT 42W LL
Consumer	46677405854_405852_821228_EL-mdTQ D2D 14W
Consumer	46677417079_417071_821236_BC-EL-mdTQS 13W T4
Consumer	46677417093_417097_821238_BC-EL-mdTQS 23W T4
Consumer	46677420055_420059_821244_BC-EL-mdT 20W 1% DIM
Consumer	46677408541_408542_821246 / 821247_BC-EL-mdTQS 9W T2
Consumer	46677417062_417063_821248_BC-EL-mdTQS 9W T3
Professional	46677417376_417378_821390_EL-A SWP 14W
Professional	46677156398_156398_821393_EL-mdT 32W
Professional	46677411381_411389_821407_EL-mdT 13W GU24 4.1K
Professional	46677411770_411777_821408_EL-mdT 18W GU24 4.1K
Consumer	46677418083_418087_821424_BC-EL-mdTQS 18W T3
Consumer	46677419790_419796_821503 / 821505_BC-EL-A SWP 9W
Consumer	46677419776_419770_821506 / 821507_BC-EL-A FAN 9W
Consumer	46677418632_418632_821509_BC-EL-A 15W R30
Consumer	46677416782_416784_821511_BC-EL-A PAR38 23W
Consumer	46677417437_417436_821515_BC-EL-Can T2 9W
Consumer	46677419783_419788_821525 / 821526_BC-EL-A FAN 9W
Professional	46677411398_411397_821547_EL-mdT 23W GU24 4.1K
Professional	46677130770_130773_821605_SLS Universal 20W
Professional	46677135744_135749_821608_SLS Universal 25W
Professional	46677146917_146910_821616_SLS Universal 14W
Professional	46677407155_407155_821624_EL-dT DIM 32W
Professional	46677139483_139485_821634_EL-dT42W
Professional	46677211936_211938_821635_EL-3W 11-23-34W
Professional	46677417413_417410_821668_EL-mCan T2 9W
Professional	46677417444_417444_821669_EL-Can T2 9W
Professional	46677418625_418624_821679_EL-A R30 15W 4.1K
Consumer	46677419806_419804_821961 / 821962_BC-EL-A SWP 14W
Consumer	46677419813_419812_821979 / 821980_BC-EL-A SWP 14W

Consumer	46677418090_418095_821985_BC-EL-mdTQS 23W T3
Consumer	46677418069_418061_821986_BC-EL-mdTQS 13W T3
Consumer	46677417420_417428_821997 / 821998_BC-EL-Can T2 9W
Consumer	46677417390_417394_821999 / 821500_BC-EL-mCan T2 9W
Consumer	46677406202_406207_822032_EL-A 15W R30
Professional	46677157036_157032_822033_EL-A 15W R30
Consumer	46677406219_406215_822034_EL-A 15W R31
Professional	46677419974_419977_822058_EL-A R30 EDIM 16W
Professional	46677419998_419993_822059_EL-A R40 EDIM 20W
Professional	46677420017_420018_822060_EL-A PAR38 EDIM 20W
Professional	46677414030_414037_822180_EL-mdT2 13W 4.1K
Professional	46677414061_414060_822182_EL-mdT2 23W 4.1K
Professional	46677414078_414078_822183_EL-mdT2 23W 5K
Professional	46677414085_414086_822184_EL-mdT2 26W 4.1K
Professional	46677414092_414094_822185_EL-mdT2 26W 5K
Professional	46677414009_414003_822187_EL-mdTQS 18W T2
Professional	46677157029_157024_822578_EL-A R40 23W
Professional	46677157166_157164_822588_EL-A PAR38 23W 2pc
Professional	46677427535_427534_822670_EL-A R20 13W 3K
Professional	46677426828_426825_822720_EL-A R20 13W
Professional	46677211066_211060_822749_EL-A G30 16W
Professional	46677417239_417238_822765_EL-mdT 13W GU24
Professional	46677417246_417246_822766_EL-mdT 18W GU24
Professional	46677417253_417253_822767_EL-mdT 23W GU24
Professional	46677420024_420026_822807_EL-mdT 15W 1% DIM
Professional	46677420031_420034_822808_EL-mdT 20W 1% DIM
Professional	46677417352_417352_822820_EL-A G25 T3 9W
Professional	46677413989_413988_822832_EL-mdTQS 9W T2
Professional	46677422295_422295_822867_EL-Can T2 5W
Professional	46677422301_422303_822868_EL-mCan T2 5W
Professional	46677147921_147926_822872_EL-mdT 5W
Consumer	46677417338_417337_823025 / 823026_BC-EL-A G25 T3 9W
Consumer	46677417345_417345_823027 / 823028_BC-EL-A G25 T3 9W
Consumer	46677422318_422311_823030_BC-EL-mCan T2 5W
Consumer	46677420093_420091_823031_BC-EL-mdTQS 13W T2 6.5K
Consumer	46677426835_426833_823041_BC-EL-A R20 13W
Consumer	46677417451_417451_823225 / 823226_BC-EL-A FAN 5W
Consumer	46677421205_421206_823227_BC-EL-A R40 23W
Professional	46677417475_417477_823699_EL-A FAN 5W
Professional	46677427870_427872_824150_EL-A G25 14W 6-1
Professional	46677417369_417360_824151_EL-A SWP 9W
Professional	46677407780_407783_824177_EL-O 14W Prisma
Professional	46677414108_414102_824178_EL-mdT2 26W
Consumer	46677419981_419985_824384_BC-EL-A R30 EDIM 16W
Consumer	46677428730_428730_824480_BC-EL-mdT 20W 1% DIM
Consumer	46677428723_428722_824481_BC-EL-mdT 15W 1% DIM
Consumer	46677420000_420000_824490_BC-EL-A R40 EDIM 20W

Professional	46677431242_431247_824605_EL-mdT3 9W 4.1K
Professional	46677431761_431767_824649_EL-dT 65W
Professional	46677432348_432344_824716_EL-dT 65W 4.1K
Consumer	46677408671_408674_824962_BC-EL-O 14W Prisma SC
Consumer	46677415044_415042_824963_EL-A T2 SC 9W 6-2
Consumer	46677415037_415034_824964_EL-A T2 SC 14W 6-2
Consumer	46677433604_433607_824965_EL-A T2 SC 14W 6.5K 2PK
Consumer	46677433550_433557_824966_BC-EL-mdTQS 23W T2 6.5K
Consumer	46677433611_433615_824968 / 824977_BC-EL-A R30 EDIM 16W 6.5K 2PK
Consumer	46677428747_428748_825303 / 824976_BC-EL-A R30 EDIM 16W
Professional	46677225193_248765_819732_65BR30-FL55 120V 12-1
Consumer	46677167820_167411_819735_65BR-FL60-LL 120V 8-1 TP
Professional	46677225360_389130_819738_65BR-FL60 120V 24-1
Consumer	46677104511_270819_819747_40A 120V 12-4
Consumer	46677293802_293803_820402_65BR30-FL55 120-130V SP 12-1
Consumer	46677167691_167692_820453_65BR30-SP20-LL 120V 12-1 TP
Consumer	46677223038_223032_820457_45BR30-FL55-LL TP 120V 4-3
Consumer	46677167684_167684_820497_65BR30-FL-55-LL 120V 12-1
Consumer	46677167516_167510_820511_45BR30-FL55-LL 120V 12-1 TP
Consumer	46677104559_374819_820543_40A-W-TP 120V 12-4
Consumer	46677137854_137851_820544_65BR30-FL-NTL 120V 12-1 TP
Consumer	46677104566_374835_820552_60A-W-TP 120V 12-4
Consumer	46677135584_135582_820556_40A-NTL-TP 120V 12-4 TP
Consumer	46677167974_167972_820567_40A-CL-LL 120V 12-2 WP TP
Consumer	46677168698_168690_820572_DURAMAX 40W MED 120V A19 SW 40W
Consumer	46677169534_169532_820623_50-150A-WL 120V 4-3
Professional	46677270032_270033_820626_150A 120V 48PK
Professional	46677374181_374181_820641_150A-CL 120-130V 60PK
Consumer	46677104528_270827_820690_60A 120V 12-4
Consumer	46677168223_168229_820798_BC60BA9-1-2-CL-LL 6-2 TP
Consumer	46677168421_168427_820799_BC60F15-CL-LL 6-2 TP
Professional	46677140083_140087_821759_65BR40-FL 130V 12-1 PRO
Consumer	46677168742_234278_821760_DIS60A-WL 120V 72-4
Professional	46677222482_222489_821766_60A19-35 130V 48PK PLC
Consumer	46677169480_169482_821784_50-150A-WL 120V 12-1
Consumer	46677169497_169490_821786_50-250A-WL 120V 12-1
Consumer	46677101183_366625_821789_30-100A-SW 120V 12-1
Consumer	46677169473_169474_821800_30-100A-WL 120V 12-1
Consumer	46677104559_374827_821803_40A-W-TP 120V 24-4
Consumer	46677106188_234146_821805_60A 120V 24-2LP-SL W-P
Consumer	46677109110_323592_821807_50-150A-DL 120V 12-1
Consumer	46677168742_168740_821809_DURAMAX 60W MED 120V A19 SW 40W
Professional	46677143558_143552_822075_50ER30 120-130V 24-1
Professional	46677385682_385682_822097_150BR38-5FL 12-1 PK
Consumer	46677225827_248872_822345_65BR30-FLVALUE PACK 1-12
Consumer	46677387792_387795_822346_65BR-FL-VP 1-12 PACK
Consumer	46677226916_429472_822587_65BR30-FL55 8-3 TP

Professional	46677138103_138107_822761_60T10-64 120V 24-1
Professional	46677138110_138115_822762_60T10-64-IF 120V 24-1
Consumer	46677167943_167940_823477_60A-CL-LL 120V 12-2 PS TP
Consumer	46677135591_135590_823485_60A-NTL-TP 120V 12-4 TP
Professional	46677149994_149996_823492_60A-52A-99-EW 120-130V 48-1
Professional	46677373993_373993_823493_40A-CL 120V-130V 48PK
Professional	46677222468_222463_823494_60A-99 130V 48PK PLC
Professional	46677140076_140079_823495_65BR30-FL 130V 12-1 PRO
Professional	46677374693_374694_824115_60A 120V 48-1
Professional	46677374716_374710_824116_60A 130V 48-1
Consumer	46677104566_374843_824118_60A-W-TP 120V 24-4
Professional	46677375225_375220_824120_60A-CL 130V 48PK
Consumer	46677135645_135640_824124_50-150A-NTL 120V 12-1 TP
Consumer	46677432317_432310_824143_40A-W-TP 120V 6-6
Consumer	46677408862_408864_824648_65BR30-B3G1 120V
Professional	46677374662_374660_825281_40A 130V 48PK
Professional	46677374655_374652_825284_40A 120V 48PK
Professional	46677213596_213595_820395_40BR30-HEA-FL 120V 12-1
Professional	46677222383_222380_820401_40BR40-HEA-FL 120V 12-1
Professional	46677144975_144971_820521_40PAR30S-IRC-FL25 120V 15PK
Professional	46677238568_238568_820538_55PAR30S-IRC+-FL25 120V 15-1
Professional	46677238575_238576_820539_55PAR30S-IRC+-WFL40 120V 15-1
Professional	46677238551_238550_820541_55PAR30S-IRC+-SP10 120V 15-1
Consumer	46677282066_385518_820786_BC60F15-HAL-POSTTOP 4PK TP
Professional	46677238476_238477_821263_55PAR38-IRC+-SP10 120V 12-1
Professional	46677238506_238501_821265_83PAR38-IRC+-SP10 120V 12-1
Professional	46677238520_238527_821269_83PAR38-IRC+-WFL40 120V 12-1
Both	46677420857_420851_822042_40G25-EV-W 120V 12-1 TP
Both	46677420840_420844_822043_40G25-EV-CL 120V 12-1 TP
Professional	46677144999_144997_822653_50PAR30S-IRC+-SP10 120V 15PK
Professional	46677238001_238006_822654_50PAR30L-IRC+-WFL40 120V 15-1
Professional	46677234294_234294_822655_50PAR30L-IRC+-FL25 120V 15-1
Professional	46677237998_237990_822656_50PAR30L-IRC+-SP10 120V 15-1
Professional	46677145019_145011_822662_50PAR30S-IRC+-WFL40 120V 15-1
Professional	46677145002_145003_822664_50PAR30S-IRC+-FL25 120V 15PK
Both	46677423858_423855_823043_BC72F15-EV-CL 120V 4-1
Professional	46677237301_237305_823652_50PAR30S-IRCE-SP10 120V 15-1
Professional	46677237295_237297_823653_40PAR30S-IRCE-FL25 120V 15-1
Professional	46677237318_237313_823654_50PAR30S-IRCE-FL25 120V 15-1
Professional	46677237394_237396_823657_60PAR38-IRCE-SP10 120V 12-1
Professional	46677237288_237511_823659_40PAR30S-IRCE-SP10 120V 15-1
Consumer	46677134129_134122_824020_BC45PAR16-HAL-FL-LL 6-1 TP
Consumer	46677134136_134130_824021_BC60PAR16-HAL-FL-LL 120V 6-1
Professional	46677428952_428952_824076_53PAR30L-EVP-WFL40 120V 15-1
Professional	46677428907_428904_824078_53PAR30S-EVP-FL25 120V 15-1
Professional	46677428884_428888_824080_53PAR30S-EVP-SP10 120V 15-1
Professional	46677428983_428986_824081_53PAR30S-EVP-WFL40 120V 15-1

Professional	46677428853_428854_824085_53PAR38-EVP-FL25 120V 12-1
Professional	46677428891_428896_824087_53PAR38-EVP-SP10 120V
Professional	46677426736_426734_824168_40PAR38-IRCE-UT4-SP10 120V 12-1
Professional	46677426743_426742_824169_40PAR38-IRCE-UT4-FL25 120V 12-1
Professional	46677429454_429456_824170_50PAR38-IRCE-UT4-FL25 120V 12-1
Professional	46677429461_429464_824171_50PAR38-IRCE-UT4-SP10 120V 12-1
Professional	46677429447_429449_824172_70PAR38-IRCE-UT4-SP10 120V 12-1
Professional	46677429997_429992_824173_40PAR38-IRCE-UT4-WFL40 120V 12-1
Professional	46677430184_430181_824174_50PAR38-IRCE-UT4-WFL40 120V 12-1
Professional	46677430191_430199_824175_70PAR38-IRCE-UT4-WFL40 120V 12-1
Professional	46677430207_430207_824176_70PAR38-IRCE-UT4-FL25 120V 12-1
Consumer	46677419561_419564_824180_53PAR30L-EV-SP10 120V 6-1 TP
Consumer	46677420208_420208_824181_50PAR30L-EV-FL25-LL 120V 6-1 TP
Consumer	46677421434_421438_824182_53PAR30S-EV-FL25 120V 6-1 TP
Both	46677226954_226951_824188_43A19-EV-NTL 120V 12-2
Both	46677226961_226969_824189_53A19-EV-NTL 120V 12-2
Both	46677424268_424267_824491_BC40BA11-E26-EV-CL 120V 6-2 TP
Both	46677424275_424275_824492_BC25B11-E26-EV-CL 120V 6-2 TP
Both	46677424282_424283_824493_BC40B11-E26-EV-CL 120V 6-2 TP
Consumer	46677421199_421198_824514_70BR40-EV-FL 120V 4-1
Consumer	46677421168_421164_824515_40BR40-EV-FL 120V 4-1
Consumer	46677421182_421180_824516_50BR30-EV-FL 120V 5-1
Consumer	46677421069_421065_824518_40BR30-EV-FL 120V 5-1
Consumer	46677421175_421172_824518_40R20-EV-FL 120V 6-1
Consumer	46677419547_419549_824537_53PAR30L-EV-FL25 120V 6-1 TP
Consumer	46677421120_421123_824538_53PAR30S-EV-SP10 120V 6-1 TP
Consumer	46677419554_429365_824539_53PAR30L-EV-FL25 120V 16-2 TP
Both	46677226992_226993_824590_72A19-EV-NTL 120V 12-2
Professional	46677229979_229971_824597_70BR40-HEA-FL 120V 12-1
Professional	46677428921_428920_824602_53PAR30L-EVP-FL25 120V 15-1
Consumer	46677147273_408831_824614_45R20-HAL-FL 120V 6-1
Professional	46677238445_238444_824634_39PAR38-IRC+-SP10 120V 12-1
Professional	46677238452_238451_824635_39PAR38-IRC+-FL25 120V 12-1
Consumer	46677421335_430421_824855_70PAR38-EV-FL25-LL 120V 6-2 TP
Consumer	46677421267_421263_824857_70PAR38-EV-SP10-LL 120V 6-1 TP
Consumer	46677419455_419457_824860_53PAR38-EV-SP10 120V 6-1 TP
Consumer	46677424985_424985_824863_83PAR38-EV-FL25-LL 120V 6-1 TP
Consumer	46677421304_421305_824864_70PAR38-EV-FL25-LL 120V 6-1 TP
Consumer	46677421281_421289_824865_39PAR38-EV-FL25-LL 120V 6-1 TP
Consumer	46677419448_419440_824866_53PAR38-EV-FL25 120V 6-1 TP
Professional	46677138615_138610_824868_70PAR38-IRC+-SP10 120V
Professional	46677138622_138628_824869_70PAR38-IRC+-FL25 120V
Professional	46677138639_138636_824870_70PAR38-IRC+-WFL40 120V
Professional	46677138769_138768_824871_100PAR38-IRC+-SP10 120V 12PK
Professional	46677138776_138776_824872_100PAR38-IRC-FL25 120V
Professional	46677138783_138784_824873_100PAR38-IRC+-WFL40 120V 12PK
Professional	46677145033_145037_824874_40PAR38-IRC-FL25 120V 12PK

Professional	46677145057_145052_824875_50PAR38-IRC+-SP10 120V 12PK
Professional	46677145064_145060_824876_50PAR38-IRC+-FL25 120V 12PK
Professional	46677145071_145078_824877_50PAR38-IRC-WFL40 120V 12PK
Professional	46677216733_216739_824878_50PAR38-IRC+-FL25-LTD 120V
Professional	46677238650_238659_824881_55PAR38-IRC+-FL25 120V 12-1
Professional	46677238490_238493_824882_55PAR38-IRC+-WFL40 120V 12-1
Professional	46677238513_238519_824883_83PAR38-IRC+-FL25 120V 12-1
Both	46677424251_424259_824974_BC25B11-E26-EV-CL 120V 6-2 TP
Both	46677433727_433722_824975_BC43F15-EV-CL 120V 4-1 TP
Consumer	46677433567_433565_824978_BC40G16.5-EV-CL 120V 6-2 TP
Consumer	46677433574_433573_824979_BC40G16.5-EV-W 120V 6-2 TP
Consumer	46677434748_434746_824986_BC45PAR16-EV-FL 120V 6-1TP
Consumer	46677434724_434720_824987_BC60PAR16-EV-FL 120V 6-1TP
Consumer	46677433680_433680_825165_40G25-EV-CL 120V 4-3 TP
Consumer	46677433697_433698_825166_40G25-EV-W 120V 4-3 TP
Both	46677409845_409847_825176_43A19-EV 120V 12-2
Both	46677409838_409839_825177_29A19-EV 120V 12-2
Both	46677410506_410506_825178_29A19-EV-CL 120V 12-2
Both	46677410490_410498_825181_43A19-EV-CL 120V 12-2
Professional	46677428914_428912_825184_39PAR30S-EVP-SP10 120V 15-1
Consumer	46677419417_429373_825185_72PAR38-EV-FL25 120V 6-2 TP
Consumer	46677419769_419762_825186_39PAR20-EV-FL25 120V 6-4
Consumer	46677419868_419861_825187_39PAR20-EV-FL25 120V 6-1 TP
Consumer	46677419400_419408_825191_72PAR38-EV-FL25 120V 6-1 TP
Consumer	46677419462_428805_825192_72PAR38-EV-FL25 120V 1-4
Professional	46677428846_428847_825194_39PAR38-EVP-FL25 120V 12-1
Professional	46677428969_428960_825195_39PAR30S-EVP-FL25 120V 15-1
Professional	46677425203_425207_825196_39PAR20-EVP-FL25 120V 15-1
Professional	46677428877_428870_825197_39PAR30L-EVP-FL25 120V 15-1
Professional	46677428945_428946_825198_72PAR38-EVP-SP10 120V 12-1
Professional	46677428938_428938_825199_72PAR38-EVP-FL25 120V 12-1
Professional	46677428860_428862_825200_39PAR38-EVP-SP10 120V 12-1
Consumer	46677419387_419382_825201_72PAR38-EV-SP10 120V 6-1 TP
Professional	46677425128_425124_825202_39PAR20-EVP-SP10 120V 15-1
Consumer	46677431495_431494_825257_72A19-EV-LL 120V 6-4
Consumer	46677431501_431502_825258_43A19-EV-LL 120V 6-4
Consumer	46677431518_431510_825259_29A19-EV-LL 120V 6-4
Consumer	46677433529_433524_825270_53A19-EV-LL 120V 6-4
Consumer	46677426033_426031_825278_43A19-EV 120V 6-4
Consumer	46677426002_426007_825279_29A19-EV 120V 6-4
Both	46677409821_409821_825353_72A19-EV 120V 12-2
both	46677410483_429241_825354_72A19-EV-CL 120V 12-2
Both	46677433895_433896_825357_72A19-EV-LL 120V 12-2
Both	46677433901_433904_825358_43A19-EV-LL 120V 12-2
Both	46677433918_433912_825359_29A19-EV-LL 120V 12-2
Both	46677433888_433888_825360_53A19-EV-LL 120V 12-2
Consumer	46677419424_419424_825375_39PAR38-EV-FL25 120V 6-1 TP



Consumer	46677419738_419739_825376_39PAR20-EV-SP10 120V 6-1 TP
Consumer	46677419431_419432_825377_39PAR38-EV-SP10 120V 6-1 TP
Consumer	46677419745_419747_825378_39PAR30L-EV-FL25 120V 6-1 TP
Consumer	46677426040_426049_825456_72A19-EV 120V 6-4
Professional	46677420802_420802_822674_13PAR30L-END-F25 3000 DIM AF 6-1
Professional	46677423353_423350_822696_19.5PAR38-END-F25 4000 DIM AF 6-1
Professional	46677420529_420521_822713_18PAR38-END-F25 3000-950 DIM AF 6-1
Professional	46677420888_420885_822714_18PAR38-END-F36 2700-900 DIM AF 6-1
Professional	46677420895_420893_822715_18PAR38-END-F36 3000-950 DIM AF 6-1
Professional	46677421212_421214_822716_19.5PAR38-END-F25 2700 DIM AF 6-1
Professional	46677421229_421222_822717_19.5PAR38-END-F25 3000 DIM AF 6-1
Consumer	46677420307_420307_822777_BC10PAR30L-VIS-3000 25D DIM 120V
Consumer	46677420321_420323_822795_BC18PAR38-VIS-3000 25D DIM 120V
Professional	46677420499_420497_824060_13PAR30L-END-F36 2700 DIM AF 6-1
Professional	46677420505_420505_824061_13PAR30L-END-F36 3000 DIM AF 6-1
Professional	46677420475_420471_824062_13PAR30L-END-F25 2700 DIM AF 6-1
Professional	46677423513_423517_824072_15DL6-END-F90 2700 DIM 6-1
Professional	46677423445_423442_824153_13PAR30S-END-F25 2700 DIM AF 6-1
Professional	46677423452_423459_824154_13PAR30S-END-F25 3000 DIM AF 6-1
Professional	46677423469_423467_824155_13PAR30S-END-F36 2700 DIM AF 6-1
Professional	46677423476_423475_824156_13PAR30S-END-F36 3000 DIM AF 6-1
Consumer	46677426118_426114_824167_BC8PAR20-AMB-3000 DIM 120V
Consumer	46677423421_423426_824192_BC19.5PAR38-AMB-F25 3000 DIM 120V
Consumer	46677420314_420315_824194_BC13PAR30L-AMB-F25 3000 120V
Consumer	46677425289_425280_824197_BC19.5PAR38-AMB-F25 5000 DIM 120V
Consumer	46677425296_425298_824198_BC13PAR30L-AMB-5000 DIM 120V
Professional	46677428815_428813_824269_8R20-F90 2700 DIM 6-1
Professional	46677425333_425330_824273_13PAR30L-END-F25 4000 DIM AF 6-1
Professional	46677425340_425348_824274_13PAR30L-END-F36 4000 DIM AF 6-1
Professional	46677425432_425439_824275_18PAR38-END-F25 4000 DIM AF 6-1
Professional	46677425388_425389_824276_13PAR30S-END-F25 4000 DIM AF 6-1
Professional	46677425395_425397_824277_13PAR30S-END-F36 4000 DIM AF 6-1
Professional	46677425449_425447_824278_18PAR38-END-F36 4000 DIM AF 6-1
Professional	46677425463_425462_824279_19.5PAR38-END-F36 2700 DIM AF 6-1
Professional	46677425487_425488_824280_19.5PAR38-END-F36 3000 DIM AF 6-1
Professional	46677425500_425504_824281_19.5PAR38-END-F36 4000 DIM AF 6-1
Professional	46677425364_425363_824282_13PAR30S-END-S15 3000 DIM AF 6-1
Professional	46677425401_425405_824283_18PAR38-END-S15 2700 DIM AF 6-1
Professional	46677425418_425413_824284_18PAR38-END-S15 3000 DIM AF 6-1
Professional	46677425425_425421_824285_18PAR38-END-S15 4000 DIM AF 6-1
Professional	46677425357_425355_824286_13PAR30S-END-S15 2700 DIM AF 6-1
Professional	46677425371_425371_824287_13PAR30S-END-S15 4000 DIM AF 6-1
Consumer	46677430214_430215_824513_BC6PAR16-AMB-3000 25D DIM 120V
Consumer	46677429416_429415_824519_9.5BR30-VIS-2700 120V
Consumer	46677429409_429407_824520_13PAR38-VIS-F25 3000 AF 120V
Consumer	46677425272_425272_824546_BC19.5PAR38-AMB-F25 2700 DIM 120V
Professional	46677425470_425470_824548_19.5PAR38-END-S15 3000 DIM AF 6-1

Professional	46677425456_425454_824550_19.5PAR38-END-S15 2700 DIM AF 6-1
Professional	46677425494_425496_824551_19.5PAR38-END-S15 4000 DIM AF 6-1
Professional	46677426323_426320_824556_13PAR38-COREPRO-F25 2700 AF 6-1
Professional	46677426330_426338_824557_13PAR38-COREPRO-F25 3000 AF 6-1
Professional	46677426347_426346_824558_13PAR38-COREPRO-F25 4000 AF 6-1
Consumer	46677420291_423756_824561_BC14.5BR40-AMB-F60 2700 DIM 120V
Consumer	46677423407_423400_824562_BC8R20-AMB-2700 DIM 120V
Consumer	46677427771_427773_824566_BC3B12-AMB-2700- E26 DIM 120V
Professional	46677429034_429035_824576_17PAR38-F25 3000 DIM AF 6-1
Professional	46677429065_429068_824579_17PAR38-F36 3000 DIM AF 6-1
Professional	46677426965_426964_824591_12PAR30S-F36 3000 AF SO 6-1
Professional	46677426941_426940_824593_12PAR30S-F25 4000 AF SO 6-1
Professional	46677426934_426932_824594_12PAR30S-F25 3000 AF SO 6-1
Professional	46677426972_426972_824595_12PAR30S-F36 4000 AF SO 6-1
Professional	46677431372_431379_824598_12PAR30S-F25 3500 AF SO 6-1
Professional	46677431389_431387_824601_12PAR30S-F36 3500 AF sO 6-1
Professional	46677427801_427807_824612_3.5F15-END-2700-E26 DIM 8-1
Professional	46677427818_427815_824613_3.5B12-END-2700-E26 DIM 8-1
Professional	46677426125_426122_824616_8PAR20-END-F25 2700 DIM AF 6-1
Professional	46677426163_426163_824617_8PAR20-END-F36 3000 DIM AF 6-1
Professional	46677426132_426130_824618_8PAR20-END-F25 3000 DIM AF 6-1
Professional	46677426446_426445_824619_13BR30-END-F90 22K-27K DIM 6-1
Professional	46677426156_426155_824620_8PAR20-END-F36 2700 DIM AF 6-1
Professional	46677426170_426171_824622_8PAR20-END-F36 4000 DIM AF 6-1
Professional	46677426149_426148_824623_8PAR20-END-F25 4000 DIM AF 6-1
Consumer	46677429386_429381_824624_10.5A19-VIS-3000 120V
Professional	46677432188_432187_825361_15A21-2700-WHT DIM 6-1
Professional	46677430108_430108_824639_13PAR38-F36 3000 DIM AF SO 6-1
Professional	46677430061_430066_824643_13PAR38-F25 2700 DIM AF SO 6-1
Professional	46677429096_429092_824646_19PAR38-F25 3000 DIM AF SO 6-1
Professional	46677429492_429498_824651_9.5BR30-COREPRO-F90 2700 AF 6-1
Professional	46677426927_426924_824652_12PAR30S-F25 2700 AF SO 6-1
Professional	46677430047_430041_824704_13PAR38-S15 3000 DIM AF SO 6-1
Professional	46677430023_430025_824707_19PAR38-S15 4000 DIM AF SO 6-1
Professional	46677430016_430017_824708_19PAR38-S15 3000 DIM AF SO 6-1
Professional	46677429133_429134_824709_19PAR38-F36 4000 DIM AF SO 6-1
Professional	46677430009_430009_824710_19PAR38-S15 2700 DIM AF SO 6-1
Professional	46677430085_430082_824711_13PAR38-F25 4000 DIM AF SO 6-1
Professional	46677430030_430033_824713_13PAR38-S15 2700 DIM AF SO 6-1
Consumer	46677425258_425256_824714_BC8A19-AMB-5000 DIM 120V
Consumer	46677425265_425264_824715_BC11A19-AMB-5000 DIM 120V
Professional	46677430511_430512_824858_10.5A19-COREPRO-3000 6-1
Professional	46677431945_431940_824886_12BR40-END-S90 2700-800 DIM AF 6-1
Consumer	46677424381_424382_824888_BC11A19-AMB-2700 DIM 120V
Consumer	46677424374_424374_824902_BC7A19-AMB-2700 DIM 120V
Professional	46677423483_423483_824905_7A19-2700 DIM 6-1
Professional	46677423490_423491_824906_11A19-END-2700 DIM 6-1

Professional	46677432966_432962_824907_12PAR30S-F25 2700 AF RO-B 6-1
Professional	46677432973_432970_824908_12PAR30S-F25 3000 AF RO-B 6-1
Consumer	46677432935_432930_824920_BC11PAR30L-AMB-F25 3000 AF 120V
Consumer	46677432959_432954_824921_BC17PAR38-AMB-F25 3000 DIM 120V
Consumer	46677429348_429340_824932_BC4.5F15-AMB-2700-E26 DIM 120V
Professional	46677429355_429357_824936_4.5F15-END-2700-E26 DIM 8-1
Professional	46677432362_432369_824937_12PAR30S-S15 2700 AF RO 6-1
Professional	46677432379_432377_824938_12PAR30S-S15 3000 AF RO 6-1
Professional	46677432386_432385_824939_12PAR30S-S15 4000 AF RO 6-1
Consumer	46677433123_433128_824981_BC8A19-SLIM-2700 DIM 120V
Consumer	46677433130_433136_824982_BC7A19-SLIM-5000 DIM 120V
Consumer	46677433147_433144_824983_BC10.5A19-SLIM-2700 DIM 120V
Consumer	46677433154_433151_824984_BC10.5A19-SLIM-5000 DIM 120V
Consumer	46677433208_433201_825153_8A19-SLIM-2700 DIM 120V
Consumer	46677433215_433219_825154_7A19-SLIM-5000 DIM 120V
Consumer	46677433222_433227_825155_10.5A19-SLIM-2700 DIM 120V
Consumer	46677433239_433235_825156_10.5A19-SLIM-5000 DIM 120V
Professional	46677430122_430124_825157_12PAR30L-F25 2700 DIM AF RO 6-1
Professional	46677430146_430140_825159_12PAR30L-F25 4000 DIM AF RO 6-1
Professional	46677430153_430157_825160_12PAR30L-F36 2700 DIM AF RO 6-1
Professional	46677430177_430173_825162_12PAR30L-F36 4000 DIM AF RO 6-1
Professional	46677293871_293878_825173_10.5BR30-F90 2700 DIM AF 6-1
Consumer	46677421946_423798_825174_BC10.5BR30-AMB-2700 DIM 120V
Consumer	46677425302_425306_825175_BC8.5BR30-AMB-5000 DIM 120V
Professional	46677432218_432211_825362_19A21-2700-WHT DIM 6-1
Professional	46677430948_430942_825369_11PAR30L-F25 2700 DIM AF 6-1
Professional	46677430986_430982_825372_11PAR30L-F36 3000 DIM AF 6-1
Professional	46677430979_430974_825373_11PAR30L-F36 2700 DIM AF 6-1
Professional	46677430955_430958_825374_11PAR30L-F25 3000 DIM AF 6-1
Consumer	46677432164_432161_825380_BC15A21-AMB-2700 DIM WHT 120V
Consumer	46677422196_422196_825385_BC17PAR38-AMB-F25 3000 OD DIM 4-1
Professional	46677418557_418558_825386_17PAR38-END-F25 3000-1050 OD 6-1
Consumer	46677431938_431932_825393_BC12BR40-AMB-F90 2700 DIM 120V
Professional	46677420512_420513_82368002_18PAR38-END-F25 2700-900 DIM AF 6-1
Professional	46677429027_429027_82457501_17PAR38-F25 2700 DIM AF 6-1
Professional	46677429058_429050_82457801_17PAR38-F36 2700 DIM AF 6-1
Professional	46677426958_426956_82459601_12PAR30S-F36 2700 AF SO 6-1
Professional	46677430092_430090_82464001_13PAR38-F36 2700 DIM AF SO 6-1
Professional	46677429126_429126_82464103_19PAR38-F36 3000 DIM AF SO 6-1
Professional	46677430078_430074_82464202_13PAR38-F25 3000 DIM AF SO 6-1
Professional	46677429119_429118_82464403_19PAR38-F36 2700 DIM AF SO 6-1
Professional	46677429089_429084_82464503_19PAR38-F25 2700 DIM AF SO 6-1
Professional	46677430054_430058_82470505_13PAR38-S15 4000 DIM AF SO 6-1
Professional	46677430115_430116_82470601_13PAR38-F36 4000 DIM AF SO 6-1
Professional	46677429102_429100_82471201_19PAR38-F25 4000 DIM AF SO 6-1
Professional	46677430139_430132_82515801_12PAR30L-F25 3000 DIM AF RO 6-1
Professional	46677430160_430165_82516101_12PAR30L-F36 3000 DIM AF RO 6-1

Consumer	46677432195_432195_825379_BC19A21-AMB-2700K DIM WHT 120V
----------	--