



PHILIPS

Retail Luminaires

Retail product guide **designed** **for you**

Philips Retail Product Guide

August 2015

Contents

Introduction	1
Indoor	5
Track	7
Accent/Track Lighting	8
Downlighting	13
Core Downlighting	14
Calculite Downlighting	19
Recessed	21
Industrial	24
Linear	27
Exit/Emergency	31
Outdoor	35
Garage & Canopy	37
Floodlights	39
Wall Mount	41
Site & Area	44

Philips

Retail Product Guide



About this guide

The guide was created to provide you with our top professional luminaire retail products in one easy-to-find location. The product selection allows you to choose the luminaire that best fits the needs of your specific customer's retail project. Indoor lighting products available through this guide are Philips Chloride, Philips Day-Brite and Philips Lightolier. The outdoor lighting products available are Philips Gardco and Philips Stonco.

In this guide, you will also find a selection of Service Smart and Spec Smart items from our Luminaire Smart Service Program. The program was created to provide a service program to ensure that we fully support your shelf-stocking requirements and provide you with reliable lead times to address the demanding timelines of construction and retrofit lighting projects. For more information, please see the descriptions to the right.

To support our luminaire service program, we have developed the following categories:

- **Service Smart products** are in stock and will be shipped in 48hrs from our warehouses*.
- **Spec Smart products** will be assembled to order and ship within 2 weeks from our factories*.

* Service time is calculated from the time the order is entered until it is shipped.

Philips

Retail Product Guide

Our commitment to you

Our Service Smart and Spec Smart items are backed by a significant investment in finished goods and component inventory. If any unforeseen issues arise or if order volume exceeds maximum order quantity, we will do our best to meet your needs and confirm an acceptable ship date.

Standard lead time products will ship within 4 to 8 weeks, while lead times for special, made to order and custom configured products for all Philips luminaire brands* can be confirmed by contacting the order desk.

Lead time is from the time the order is entered and received by our warehouse. Our goal is to enter orders within one business day of receipt.

To enable fast order entry, orders must be received with complete and correct catalog numbers and reference to the source of pricing (i.e. quote number or pricing program). It is recommended that you reference "Retail Guide" on your orders for product in this guide to speed the order entry process.

In order to avoid delays, it is recommended that stock orders be "stand alone" so that they may be shipped within the promised time-frame.

To ensure we satisfy all our customers optimally and meet the committed lead times, maximum order quantities may apply. If the order exceeds the set threshold, Philips will contact you to work out a feasible schedule for your large order. It is always advised to work with your Philips representative to give advance notice of your large order.

Contact Us

In case you have questions, please contact your Philips Sales Representative or Customer Service Representative.

Philips Contact Center: 1-855-486-2216



We understand that customer demand may change unexpectedly. Therefore, all items in our Retail Guide are now returnable, per our standard return policy terms and conditions.

- Visit www.philips.com/warranties for details on our standard terms and conditions

Terms and Conditions

Freight Terms: Individual order minimum of \$1,000;
\$100 shipping and handling fee for orders less than \$1,000.
1% 10th Prox 2nd, Net 25th Prox 2nd for Stock Orders
1% 10th Prox, Net 25th Prox for Drop Ship/Project Business

* This pertains also to brands and product categories not represented in this particular guide.



Indoor







Track

Accent/Track Lighting



CorePro LED Mini Cylinder

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	662057935348	912400531211	LT08RNF830WH	Flatback Cylinder LED Track 800LM 25DEG	✓	
Philips Lightolier	662057935324	912400531213	LT08RWF830WH	Flatback Cylinder LED Track 800LM 40DEG	✓	
Philips Lightolier	662057990101	912401050034	LT08RNF930WHCW	Flatback Cylinder LED Track Crisp White 800LM 25DEG		
Philips Lightolier	662057990132	912401050037	LT08RWF930WHCW	Flatback Cylinder LED Track Crisp White 800LM 40DEG		
Philips Lightolier	662057935331	912400531212	LT08RNF830BK	Flatback Cylinder LED Track 800LM 25DEG	✓	
Philips Lightolier	662057935355	912400531214	LT08RWF830BK	Flatback Cylinder LED Track 800LM 40DEG	✓	
Philips Lightolier	662057990118	912401050035	LT08RNF930BKCW	Flatback Cylinder LED 800lm NF BK CW		
Philips Lightolier	662057990149	912401050038	LT08RWF930BKCW	Flatback Cylinder LED 800lm WF BK CW		



Alcyon LED Vertical

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	662057542034	912400526405	LLAV1130WH	Alcyon LED Vertical 3000K 1000L White	✓	
Philips Lightolier	662057896298	912400520606	LLAV1230WH	Alcyon LED Vertical 3000K 2000L White	✓	
Philips Lightolier	662057896809	912400520464	LLAV11RF	Alcyon LED Vertical 600/1000 Cylinder Reflector Narrow Flood	✓	
Philips Lightolier	662057896816	912400520529	LLAV11RS	Alcyon LED Vertical 600/1000 Cylinder Reflector Spot	✓	
Philips Lightolier	662057896793	912400520530	LLAV11RF	Alcyon LED Vertical 600/1000 Cylinder Reflector Narrow Flood	✓	
Philips Lightolier	662057897110	912400520465	LLAV11RS	Alcyon LED Vertical 600/1000 Cylinder Reflector Flood	✓	
Philips Lightolier	662057896755	912400520467	LLAV12RS	Alcyon LED Vertical 2000 Cylinder Reflector Narrow Spot	✓	
Philips Lightolier	662057896786	912400520532	LLAV12RS	Alcyon LED Vertical 2000 Cylinder Reflector Spot	✓	
Philips Lightolier	662057896762	912400520531	LLAV12RF	Alcyon LED Vertical 2000 Cylinder Reflector Narrow Flood	✓	
Philips Lightolier	662057896779	912400520466	LLAV12RF	Alcyon LED Vertical 2000 Cylinder Reflector Flood	✓	
Philips Lightolier	662057542041	912400526404	LLAV1130BK	Alcyon LED Vertical CYL 3000K 1000L BK		✓
Philips Lightolier	662057896304	912400520605	LLAV1230BK	Alcyon LED Vertical CYL 2000LM 3000K BK		



Spot LED Track

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	662057576107	912400476414	LLAB030RSWH	Spot LED Spot 3000K White		✓
Philips Lightolier	662057577548	912400478763	LLAB030RNFWH	Spot LED Narrow Flood 3000K White	✓	
Philips Lightolier	662057577500	912400476411	LLAB030RFWH	Spot LED Flood 3000K White		✓
Philips Lightolier	662057609607	912400476426	LLAB130RSWH	Spot LED Large Spot 3000K White		✓
Philips Lightolier	662057609638	912400478776	LLAB130RNFWH	Spot LED Large Narrow Flood 3000K White	✓	
Philips Lightolier	662057576121	912400476413	LLAB030RSBK	Spot LED Spot 3000K Black		
Philips Lightolier	662057577555	912400478762	LLAB030RNFBK	Spot LED Narrow Flood 3000K Black	✓	
Philips Lightolier	662057577517	912400476410	LLAB030RFBK	Spot LED Flood 3000K Black		✓
Philips Lightolier	662057609614	912400476425	LLAB130RSBK	Spot LED Large Spot 3000K Black		
Philips Lightolier	662057609645	912400478775	LLAB130RNFBK	Spot LED Large Narrow Flood 3000K Black		
Philips Lightolier	662057610719	912400476422	LLAB130RFBK	Spot LED Large Flood 3000K Black		✓
Philips Lightolier	662057610702	912400476423	LLAB130RFWH	Spot LED Large Floor 3000K White	✓	
Philips Lightolier	662057651095	912400476447	LLABS30RFBK	Spot LED Small Flood 3000K Black		
Philips Lightolier	662057651057	912400476448	LLABS30RFWH	Spot LED Small Narrow Flood 3000K White		
Philips Lightolier	662057651033	912400478788	LLABS30RNFBK	Spot LED Small Narrow Flood 3000K Black		✓
Philips Lightolier	662057651019	912400476450	LLABS30RSBK	Spot LED Small Spot 3000K Black		
Philips Lightolier	662057650371	912400476451	LLABS30RSWH	Spot LED Small Spot 3000K White		



Mini Universal

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	784197902100	912400462730	9021WH	Mini Universal 250W Max Matte White	✓	
Philips Lightolier	784197902117	912400462729	9021BK	Mini Universal 250W Max Matte Black	✓	



Rings

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	662057905914	912400528335	9030NWH	Lytespan Gimbal Ring PAR30 WH	✓	
Philips Lightolier	662057905945	912400528337	9038NWH	Lytespan Gimbal Ring PAR38 WH	✓	
Philips Lightolier	662057905907	912400528334	9030NBK	Lytespan Gimbal Ring PAR30 BK	✓	
Philips Lightolier	662057905938	912400528336	9038NBK	Lytespan Gimbal Ring PAR38 BK	✓	



PowerWash

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	784197302498	912400462819	9276WH	2 X 24W T5 HO Flood 2' Matte White		✓



Basic Track & Accessories

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	784197594190	912400465047	6000NWH	2'IND Basic Track White	✓	
Philips Lightolier	784197594213	912400465050	6001NWH	4'IND Basic Track White	✓	
Philips Lightolier	784197594237	912400465053	6002NWH	8'IND Basic Track White	✓	
Philips Lightolier	784197594251	912400465056	6003NWH	8'Join Basic Track White	✓	
Philips Lightolier	784197594275	912400465059	6004NWH	4'IND Basic Track w/o Live End White	✓	
Philips Lightolier	662057572208	912400465062	6006NWH	6' Basic Plain Track w/o Live End White		
Philips Lightolier	784197594299	912400465065	6008NWH	8'IND Basic Track w/o Live End White	✓	
Philips Lightolier	784197594596	912400465074	6048NWH	Basic Live End White	✓	
Philips Lightolier	784197594572	912400465077	6049NWH	Basic Mini Coupler White	✓	
Philips Lightolier	784197594473	912400465080	6050NWH	Basic "L" Connector White	✓	
Philips Lightolier	784197594497	912400465083	6051NWH	Basic "T" Connector White	✓	
Philips Lightolier	784197594350	912400465092	6054NWH	Basic In-Line Connector White	✓	
Philips Lightolier	784197606008	912400462274	6060WH	End Feed Canopy White	✓	
Philips Lightolier	784197607401	912400462284	6074WH	LyteSpot Extension Wand 18"White		✓
Philips Lightolier	784197606015	912400462273	6060BK	End Feed Canopy Black	✓	
Philips Lightolier	784197594183	912400465046	6000NBK	2'IND Basic Track Black	✓	
Philips Lightolier	784197594206	912400465049	6001NBK	4'IND Basic Track Black	✓	
Philips Lightolier	784197594220	912400465052	6002NBK	8'IND Basic Track Black	✓	
Philips Lightolier	784197594244	912400465055	6003NBK	8'Join Basic Track MT Black		✓
Philips Lightolier	784197594268	912400465058	6004NBK	4'IND Basic Track w/o Live End Black	✓	
Philips Lightolier	784197594282	912400465064	6008NBK	8'IND Basic Track w/o Live End Black	✓	
Philips Lightolier	784197594589	912400465073	6048NBK	Basic Live End Black	✓	
Philips Lightolier	784197594565	912400465076	6049NBK	Basic Mini Coupler Black	✓	
Philips Lightolier	784197594466	912400465079	6050NBK	Basic "L" Connector Black		✓
Philips Lightolier	784197594480	912400465082	6051NBK	Basic "T" Connector Black	✓	
Philips Lightolier	784197594329	912400465091	6054NBK	Basic In-Line Connector Black		✓



Radius Track & Accessories

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	784197910129	912400462746	9102WH	Radius 2' Plain Track Matte White		✓
Philips Lightolier	784197910167	912400462749	9104WH	Radius 4' Plain Track Matte White		✓
Philips Lightolier	784197910204	912400462752	9106WH	Radius 6' Plain Track Matte White		✓
Philips Lightolier	784197910242	912400462755	9108WH	Radius 8' Plain Track Matte White	✓	
Philips Lightolier	784197910280	912400462761	9148WH	Radius Live End Feed Matte White	✓	
Philips Lightolier	784197910327	912400462763	9149WH	Radius Mini Coupler Matte White	✓	
Philips Lightolier	784197910365	912400462765	9150WH	Radius Flush Non-Feed Connector COMB L or NL	✓	
Philips Lightolier	784197170394	912400462767	9151WH	Radius Feed "T" Connector Matte White	✓	
Philips Lightolier	784197136857	912400462771	9155WH	Radius Feed Connector COMB L or In-Line Matte White		✓
Philips Lightolier	784197910488	912400462773	9160WH	Radius Live End Canopy Matte White		✓
Philips Lightolier	784197364069	912400462799	9188WH	Radius T-Bar Clip, Regressed (Set of 9)		
Philips Lightolier	784197369446	912400462801	9189WH	Radius T-Bar Clip, Flat, (Set of 9)		✓



PowerTrip

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	784197531584	912400492659	PLD600WH	PowerTrip New Design, Plug-In Breaker		✓
Philips Lightolier	784197531577	912400492658	PLD600BK	PowerTrip New Design, Plug-In Breaker		✓
Philips Lightolier	784197531638	912400492664	PLD900BK	PowerTrip New Design, Plug-In Breaker		✓
Philips Lightolier	784197531645	912400492665	PLD900WH	PowerTrip New Design, Plug-In Breaker		✓
Philips Lightolier	784197531324	912400472105	PLD1080BK	PowerTrip New Design, Plug-In Breaker		
Philips Lightolier	784197531331	912400472106	PLD1080WH	PowerTrip New Design, Plug-In Breaker		
Philips Lightolier	784197531386	912400472109	PLD1320BK	PowerTrip New Design, Plug-In Breaker		
Philips Lightolier	784197531393	912400472110	PLD1320WH	PowerTrip New Design, Plug-In Breaker		
Philips Lightolier	784197531409	912400472111	PLD1440BK	PowerTrip New Design, Plug-In Breaker		
Philips Lightolier	784197531416	912400472112	PLD1440WH	PowerTrip New Design, Plug-In Breaker		



Track Accessories

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	784197515546	912400462333	6170WH	Rectangular Monopoint, Matte White		✓
Philips Lightolier	784197515553	912400462332	6170BK	Rectangular Monopoint, Matte Black		
Philips Lightolier	784197619022	912400462345	6190WH	Monopoint White	✓	
Philips Lightolier	784197619015	912400462344	6190BK	Monopoint Black	✓	
Philips Lightolier	784197020064	912400460361	6087	Reg Panel Mtg Clips for Trk Ltg-9Clip/BX		✓
Philips Lightolier	784197608903	912400460363	6089	9/16 15/16 Grid Clnng Clip Kit(9Clip/Box)	✓	



Alcyon LED Recessed

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	662057913452	912400527072	LLAVRM11H212	Recessed Alcyon LED FIK 120V 2Head 600/1000Lm		✓
Philips Lightolier	662057913476	912400527073	LLAVRM11H227	Recessed Alcyon LED FIK 277V 2Head 600/1000Lm		✓
Philips Lightolier	662057913490	912400527074	LLAVRM11H312	Recessed Alcyon LED FIK 120V 3Head 600/1000Lm		✓
Philips Lightolier	662057913506	912400527075	LLAVRM11H327	Recessed Alcyon LED FIK 277V 3Head 600/1000Lm		✓
Philips Lightolier	662057913568	912400527080	LLAVRM12H212	Recessed Alcyon LED FIK 120V 2Head 2000Lm		✓
Philips Lightolier	662057913575	912400527081	LLAVRM12H227	Recessed Alcyon LED FIK 277V 2Head 2000Lm		
Philips Lightolier	662057913582	912400527082	LLAVRM12H312	Recessed Alcyon LED FIK 120V 3Head 2000Lm		✓
Philips Lightolier	662057913599	912400527083	LLAVRM12H327	Recessed Alcyon LED FIK 277V 3Head 2000Lm		
Philips Lightolier	662057912943	912400527025	LLAVRMWH1130H2	Recessed Alcyon LED White 3000K 2Head 1000Lm w/Trim		✓
Philips Lightolier	662057912967	912400527027	LLAVRMWH1130H3	Recessed Alcyon LED White 3000K 3Head 1000Lm w/Trim		✓



Alcyon LED Recessed

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	662057772028	912400474066	LLABR17WH	Recessed Spot LED Trim Section, 17" Length		✓
Philips Lightolier	662057772042	912400474070	LLABR24WH	Recessed Spot LED Trim Section, 24" Length		✓
Philips Lightolier	662057878126	912400519610	LLABR17WH030H2RNFV	Spot LED RM, LE&FIK, 2 head, 1000lm, White, 3000K, Narrow Flood, 120/277		
Philips Lightolier	662057878287	912400519472	LLABR24WH030H3RSV	Spot LED RM, LE&FIK, 3 head, 1000lm, White, 3000K, Spot, 120/277		
Philips Lightolier	662057878362	912400519618	LLABR24WH030H3RNFV	Spot LED RM, LE&FIK, 3 head, 1000lm, White, 3000K, Narrow Flood, 120/277		
Philips Lightolier	662057877679	912400519302	LLABR9WH130H1RSV	Spot LED RM, LE&FIK, 1 head, 2000lm, White, 3000K, Spot, 120/277		
Philips Lightolier	662057878140	912400519612	LLABR17WH130H2RNFV	Spot LED RM, LE&FIK, 2 head, 2000lm, White, 3000K, Narrow Flood, 120/277		✓
Philips Lightolier	662057878546	912400519467	LLABR24BK130H3RFV	Spot LED RM, LE&FIK, 3 head, 2000lm, Black, 3000K, Flood, 120/277		



Downlighting

Core Downlighting



SlimSurface LED Surface Mount Downlight, 4" and 6" Square and 5" and 7" Round

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	662057988788	912401050022	S4S827K7	Slim 4" Square 600 LM 27K 80CRI 120V WHT Triac Wet	✓	
Philips Lightolier	662057988801	912401050024	S4S830K7	Slim 4" Square 600 LM 30K 80CRI 120V WHT Triac Wet	✓	
Philips Lightolier	662057992419	912400531615	S4S830K7-D	Slim 4" Square 600 LM 30K 80CRI 120V WHT Triac Damp	✓	
Philips Lightolier	662057988825	912401050026	S4S927K7	Slim 4" Square 600 LM 27K 90CRI 120V WHT Triac Wet	✓	
Philips Lightolier	662057988672	912401050011	S5R827K7	Slim 5" Round 600 LM 27K 80CRI 120V WHT Triac Wet	✓	
Philips Lightolier	662057936055	912400530938	S5R830K7	Slim 5" Round 600 LM 30K 80CRI 120V WHT Triac Wet	✓	
Philips Lightolier	662057992433	912400531616	S5R830K7-D	Slim 5" Round 600 LM 30K 80CRI 120V WHT Triac Damp	✓	
Philips Lightolier	662057990927	912400531483	S5R830K7-ELV	Slim 5" Round 600 LM 30K 80CRI 120V WHT ELV Damp	✓	
Philips Lightolier	662057988702	912401050014	S5R927K7	Slim 5" Round 600 LM 27K 90CRI 120V WHT Triac Wet	✓	
Philips Lightolier	662057988849	912401050028	S6S827K10	Slim 6" Square 900 LM 27K 80CRI 120V WHT Triac Wet	✓	
Philips Lightolier	662057988863	912401050030	S6S830K10	Slim 6" Square 900 LM 30K 80CRI 120V WHT Triac Wet	✓	
Philips Lightolier	662057992426	912400531617	S6S830K10-D	Slim 6" Square 900 LM 30K 80CRI 120V WHT Triac Damp	✓	
Philips Lightolier	662057988887	912401050032	S6S927K10	Slim 6" Square 900 LM 27K 90CRI 120V WHT Triac Wet	✓	
Philips Lightolier	662057988726	912401050016	S7R827K10	Slim 7" Round 900 LM 27K 80CRI 120V WHT Triac Wet	✓	
Philips Lightolier	662057988740	912401050018	S7R830K10	Slim 7" Round 900 LM 30K 80CRI 120V WHT Triac Wet	✓	
Philips Lightolier	662057992440	912400531618	S7R830K10-D	Slim 7" Round 900 LM 30K 80CRI 120V WHT Triac Damp	✓	
Philips Lightolier	662057988764	912401050020	S7R927K10	Slim 7" Round 900 LM 27K 90CRI 120V WHT Triac Wet	✓	



6 3/4" Uniframe LED frames

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	662057383545	912400481969	1101LED09N35D1	6 3/4" Uniframe LED New Construction Non-IC Frame Dimming 900LM 3500K 120V		✓
Philips Lightolier	662057383644	912400481970	1101LED09N35D2	6 3/4" Uniframe LED New Construction Non-IC Frame Dimming 900LM 3500K 277V		
Philips Lightolier	662057544120	912400481973	1101LED15N35D1	6 3/4" Uniframe LED New Construction Non-IC Frame Dimming 1500LM 3500K 120V		✓
Philips Lightolier	662057544144	912400481974	1101LED15N35D2	6 3/4" Uniframe LED New Construction Non-IC Frame Dimming 1500LM 3500K 277V		✓



6 3/4" Lytensing Incandescent frames

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	784197110000	912400468331	1100AICM	6 3/4" INC Lytecaster IC Airseal Housing		
Philips Lightolier	784197110239	912400461862	1100IC	6 3/4" INC Lytecaster IC Frame	✓	
Philips Lightolier	784197110222	912400461868	1102P1	6 3/4" INC Lytecaster Non-IC Frame	✓	
Philips Lightolier	784197174583	912400491677	1103R	6 3/4" INC Lytecaster Remodeler Ring Non-IC	✓	



6 3/4" Lytensing Incandescent Trims

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	784197123154	912400460183	1105	6 3/4" Incandescent Trim Step Baffle Black		✓
Philips Lightolier	784197123352	912400460187	1113	6 3/4" Incandescent Trim Cone Specular Clear	✓	
Philips Lightolier	784197117108	912400460219	1171	6 3/4" Incandescent Trim Open Reflector White	✓	
Philips Lightolier	784197003500	912400460220	1176	6 3/4" Incandescent Trim Basic Baffle Black	✓	
Philips Lightolier	784197110703	912400461879	1105WH	6 3/4" Incandescent Trim Step Baffle White	✓	
Philips Lightolier	784197359713	912400461884	1113CD	6 3/4" Incandescent Trim Cone Clear Diffuse	✓	
Philips Lightolier	784197003517	912400461941	1176WH	6 3/4" Incandescent Trim Basic Baffle White	✓	
Philips Lightolier	784197194758	912400461942	1177LX	6 3/4" Incandescent Trim Flush Glass Shower Light White Plastic Flange	✓	
Philips Lightolier	784197117719	912400461944	1177SH	6 3/4" Incandescent Trim Flush Opalex Shower Light White Plastic Flange	✓	
Philips Lightolier	784197117818	912400461946	1178SH	6 3/4" Incandescent Trim Drop Opalex Shower Light White Plastic Flange	✓	



5" Lytecaster LED Round

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	662057993829	912401050059	L5R078WG	LCA LED 5" Module 80 CRI 27K 700LM WG	✓	
Philips Lightolier	662057993782	912401050060	L5R10827	LCA LED 5" Module 80 CRI 27K 1000LM		✓
Philips Lightolier	662057993799	912401050061	L5R10830	LCA LED 5" Module 80 CRI 30K 1000LM	✓	
Philips Lightolier	662057993805	912401050062	L5R10835	LCA LED 5" Module 80 CRI 35K 1000LM		✓
Philips Lightolier	662057993812	912401050063	L5R10927	LCA LED 5" Module 90 CRI 27K 1000LM		✓
Philips Lightolier	662057995663	912401050064	L5RA10827W	LCA LED 5" Round ADJ White 1000lm 827		✓
Philips Lightolier	662057995670	912401050065	L5RA10830W	LCA LED 5" Round ADJ White 1000lm 830		✓
Philips Lightolier	662057995687	912401050066	L5RA10835W	LCA LED 5" Round ADJ White 1000lm 835		✓
Philips Lightolier	662057995694	912401050067	L5RA10927W	LCA LED 5" Round ADJ White 1000lm 927		✓
Philips Lightolier	662057993904	912401050068	L5RAE1	LCA LED 5" 1000LM Round IC FIK Screw 120V	✓	
Philips Lightolier	662057993928	912401050069	L5RAEWG1	LCA LED 5" 700LM WG Round IC FIK Screw	✓	
Philips Lightolier	662057999685	912400533440	L5RAZ10U	LCA LED 5" 1000LM Round IC FIK Screw 0-10V U	✓	
Philips Lightolier	662057993836	912401050072	L5RBW	LCA LED 5" Round White Baffle	✓	
Philips Lightolier	662057993843	912401050073	L5RDD	LCA LED 5" Round Clear Diffuse Cone		✓
Philips Lightolier	662057993850	912401050074	L5RDW	LCA LED 5" Round White Cone And Flange		✓
Philips Lightolier	662057999845	912401050070	L5RANE1	Lytecaster LED 5" 1000LM Round IC FIK NAIL 120V	✓	



6" LyteCaster LED Round

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	662057993942	912401050075	L6R15827	LCA LED 6" Module 80 CRI 27K 1500LM		✓
Philips Lightolier	662057993959	912401050076	L6R15830	LCA LED 6" Module 80 CRI 30K 1500LM	✓	
Philips Lightolier	662057993966	912401050077	L6R15835	LCA LED 6" Module 80 CRI 35K 1500LM		✓
Philips Lightolier	662057993973	912401050078	L6R15927	LCA LED 6" Module 90 CRI 27K 1500LM		✓
Philips Lightolier	662057995700	912401050079	L6RA15827W	LCA LED 6" Round ADJ White 1500lm 827		✓
Philips Lightolier	662057995717	912401050080	L6RA15830W	LCA LED 6" Round ADJ White 1500lm 830		✓
Philips Lightolier	662057995724	912401050081	L6RA15835W	LCA LED 6" Round ADJ White 1500lm 835		✓
Philips Lightolier	662057995731	912401050082	L6RA15927W	LCA LED 6" Round ADJ White 1500lm 927		✓
Philips Lightolier	662057994062	912401050083	L6RAE1	LCA LED 6" 1500LM Round IC FIK Screw 120V	✓	
Philips Lightolier	662057999708	912400533442	L6RAZ10	LCA LED 6" 1500LM Round IC FIK Screw 0-10V U	✓	
Philips Lightolier	662057993980	912401050085	L6RBW	LCA LED 6" Round White Baffle	✓	
Philips Lightolier	662057993997	912401050086	L6RDD	LCA LED 6" Round Clear Diffuse Cone		✓
Philips Lightolier	662057994000	912401050087	L6RDW	LCA LED 6" Round White Cone		✓
Philips Lightolier	662057999708	912400533442	L6RAZ10U	Lytecaster LED 6" 1500LM Round IC FIK Screw 0-10V U	✓	
Philips Lightolier	662057999715	912400533443	L6RANZ10U	Lytecaster LED 6" 1500LM Round IC FIK NAIL 0-10V U	✓	



3" Lytecaster LED Accent

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	662057997575	912401052150	L3SD	3.75" 5 degree diffusion film		✓
Philips Lightolier	662057997582	912401052151	L3LS	3.75" linear spread film		✓
Philips Lightolier	662057997605	912401050202	L3RBW	3.75" Downlight White BaffleWhite Flange	✓	
Philips Lightolier	662057997629	912401052128	L3RDD	3.75" Downlight Diffused Cone White Flange	✓	
Philips Lightolier	662057997636	912401052127	L3RDW	3.75" Downlight White Cone White Flange	✓	
Philips Lightolier	662057997643	912401050201	L3RABW	3.75" Adjustable Accent White Baffle White Flange	✓	
Philips Lightolier	662057997667	912401050206	L3RAD	3.75" Adjustable Accent Diffused Cone White Flange	✓	
Philips Lightolier	662057997674	912401050205	L3RAW	3.75" Adjustable Accent White Cone White Flange	✓	
Philips Lightolier	662057997681	912401050196	L3RSW	3.75" Downlight Shower Light Flat Glass White	✓	
Philips Lightolier	662057997698	912401052119	L3RSA	3.75" Downlight Shower Light Flat Glass Aluminum	✓	
Philips Lightolier	662057997704	912401052118	L3RLWC	3.75" Wall Washer Chrome Cone White Flange	✓	
Philips Lightolier	662057997711	912401050211	L3RLWD	3.75" Wall Washer Diffused Cone White Flange	✓	
Philips Lightolier	662057997728	912401050210	L3RLWW	3.75" Wall Washer White Cone White Flange	✓	
Philips Lightolier	662057997735	912401050212	L3SDD	3.75" Square Downlight Diffuse Cone White Face Plate	✓	
Philips Lightolier	662057997742	912401050208	L3SDDA	3.75" Square Downlight Diffuse Cone Aluminum Face Plate	✓	
Philips Lightolier	662057997759	912401050197	L3SDW	3.75" Square Downlight White Cone White Face Plate	✓	
Philips Lightolier	662057997766	912401050198	L3SAD	3.75" Square Adjustable Diffuse Cone White Face Plate	✓	
Philips Lightolier	662057997773	912401050199	L3SADA	3.75" Square Adjustable Diffuse Cone Aluminum Face Plate	✓	
Philips Lightolier	662057997780	912401050207	L3SLWW	3.75" Square Wall Wash White Face Plate	✓	
Philips Lightolier	662057997797	912401050209	L3SLWA	3.75" Square Wall Wash Aluminum Face Plate	✓	
Philips Lightolier	662057997803	912401052120	L3SSW	3.75" Square Shower Light White Face Plate	✓	
Philips Lightolier	662057997810	912401052121	L3SSA	3.75" Square Shower Light Aluminum Face Plate	✓	
Philips Lightolier	662057997827	912401052122	L3RGW	3.75" Adjustable Gimbal White	✓	
Philips Lightolier	662057997834	912401052123	L3RGB	3.75" Adjustable Gimbal Black	✓	
Philips Lightolier	662057997841	912401052124	L3RGA	3.75" Adjustable Gimbal Aluminum	✓	
Philips Lightolier	662057997858	912401052125	L3RAPW	3.75" Adjustable Accent Pinhole Baffle White	✓	
Philips Lightolier	662057997865	912401052126	L3RAPA	3.75" Adjustable Accent Pinhole Baffle Aluminum	✓	
Philips Lightolier	662057997872	912401052148	L3AHW	3.75" Accessory Holder White		✓
Philips Lightolier	662057997889	912401052149	L3AHB	3.75" Accessory Holder Black		✓
Philips Lightolier	662057997988	912401052129	L308827NF	3.75" Light Engine 2700K 80CRI Narrow Flood	✓	
Philips Lightolier	662057997995	912401052131	L308827F	3.75" Light Engine 2700K 80CRI Flood		✓
Philips Lightolier	662057998015	912401052135	L308830NF	3.75" Light Engine 3000K 80CRI Narrow Flood	✓	
Philips Lightolier	662057998053	912401052136	L308830F	3.75" Light Engine 3000K 80CRI Flood		✓
Philips Lightolier	662057998121	912401052141	L308835NF	3.75" Light Engine 3500K 80CRI Narrow Flood	✓	
Philips Lightolier	662057998138	912401052142	L308835F	3.75" Light Engine 3500K 80CRI Flood	✓	
Philips Lightolier	662057998152	912401052132	L308927F	3.75" Light Engine 2700K 90CRI Flood		✓
Philips Lightolier	662057998183	912401052130	L308927NF	3.75" Light Engine 2700K 90CRI Narrow Flood	✓	
Philips Lightolier	662057998206	912401052152	L3RPS	Lytecaster 3.75" Replacement Optic Spot		✓
Philips Lightolier	662057998213	912401052153	L3RPNF	Lytecaster 3.75" Replacement Optic Narrow Flood		✓
Philips Lightolier	662057998220	912401052154	L3RPF	Lytecaster 3.75" Replacement Optic Spot Flood		✓
Philips Lightolier	662057999319	912401052147	L3CE1	3.75" Remodeler Non-IC 120V ELV Dim	✓	
Philips Lightolier	662057999326	912401052144	L3AE1	3.75" New Construction AirSeal IC 120V ELV Dim Screw	✓	
Philips Lightolier	662057999333	912401052145	L3ANE1	3.75" New Construction AirSeal IC 120V ELV Dim Nail	✓	
Philips Lightolier	662057999456	912401052146	L3NZ10U	3.75" New Construction Non-IC 120V/277 0-10V Dim Screw		✓



LyteProfile LED Downlights

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	662057981505	912401050150	P6RD10NZ103VB	6" LyteProfile FIK NC NON-IC 1000LM 347		
Philips Lightolier	662057981307	912401050141	P6RD10NZ10UVB	6" LyteProfile FIK NC NON-IC 1000LM Z10V		✓
Philips Lightolier	662057981406	912401050145	P6RD10NZ10UVBEM	6" LyteProfile FIK NC NON-IC 1000LM EM		✓
Philips Lightolier	662057981512	912401050151	P6RD15NZ103VB	6" LyteProfile FIK NC NON-IC 1500LM 347		
Philips Lightolier	662057981314	912401050142	P6RD15NZ10UVB	6" LyteProfile FIK NC NON-IC 1500LM Z10V	✓	
Philips Lightolier	662057981413	912401050146	P6RD15NZ10UVBEM	6" LyteProfile FIK NC NON-IC 1500LM EM		✓
Philips Lightolier	662057981321	912401050143	P6RD20NZ10UVB	6" LyteProfile FIK NC NON-IC 2000LM 120	✓	
Philips Lightolier	662057981420	912401050147	P6RD20NZ10UVBEM	6" LyteProfile FIK NC NON-IC 2000LM 120		✓
Philips Lightolier	662057981529	912401050152	P6RD20NZ103VB	6" LyteProfile FIK NC NON-IC 2000LM 277		
Philips Lightolier	662057981260	912401050137	P6RD827VB	6" LyteProfile LIGHT ENGINE 80 CRI 27K		
Philips Lightolier	662057981277	912401050138	P6RD830VB	6" LyteProfile LIGHT ENGINE 80 CRI 30K	✓	
Philips Lightolier	662057981284	912401050139	P6RD835VB	6" LyteProfile LIGHT ENGINE 80 CRI 35K	✓	
Philips Lightolier	662057981291	912401050140	P6RD840VB	6" LyteProfile LIGHT ENGINE 80 CRI 40K		
Philips Lightolier	662057994666	912400532720	P6RD10NZ10U	6" LyteProfile FIK NC NON-IC 1000LM Z10V		
Philips Lightolier	662057994673	912400532722	P6RD15NZ10U	6" LyteProfile FIK NC NON-IC 1500LM Z10V		
Philips Lightolier	662057994680	912400532724	P6RD20NZ101	6" LyteProfile FIK NC NON-IC 2000LM 120		
Philips Lightolier	662057994697	912400532725	P6RD20NZ102	6" LyteProfile FIK NC NON-IC 2000LM 277		
Philips Lightolier	662057994956	912400532728	P6RD10NZ10UE	6" LyteProfile FIK NC NON-IC 1000LM EM		
Philips Lightolier	662057994963	912400532729	P6RD15NZ10UE	6" LyteProfile FIK NC NON-IC 1500LM EM		
Philips Lightolier	662057995168	912400532730	P6RD20NZ101E	6" LyteProfile FIK NC NON-IC 2000LM 120		
Philips Lightolier	662057995175	912400532731	P6RD20NZ102E	6" LyteProfile FIK NC NON-IC 2000LM 277		
Philips Lightolier	662057994710	912400532739	P6RD830	6" LyteProfile LIGHT ENGINE 80 CRI 30K		
Philips Lightolier	662057994727	912400532740	P6RD835	6" LyteProfile LIGHT ENGINE 80 CRI 35K		
Philips Lightolier	662057994796	912400532706	P6RDCC	6" LyteProfile COMFORT Clear REFLECTOR		
Philips Lightolier	662057994864	912400532713	P6RLWC	6" LyteProfile COMFORT Clear LENS WW		
Philips Lightolier	662057981277	912401050138	P6RD830VB	6" LyteProfile LIGHT ENGINE 80CRI 30K VB	✓	
Philips Lightolier	662057981284	912401050139	P6RD835VB	6" LyteProfile LIGHT ENGINE 80CRI 35K VB	✓	
Philips Lightolier	662057981338	912401050091	P6RD25NZ101VB	6" LyteProfile FIK NonIC 2500 120 Z10 VB	✓	
Philips Lightolier	662057981345	912401050144	P6RD25NZ102VB	6" LyteProfile FIK NonIC 2500 277 Z10 VB	✓	
Philips Lightolier	662057981437	912401050148	P6RD25NZ101VBEM	6" LyteProfile FIK NonIC 2500 120 Z10 VB		✓
Philips Lightolier	662057981444	912401050149	P6RD25NZ102VBEM	6" LyteProfile FIK NonIC 2500 277 Z10 VB		✓

Calculite Downlighting



6" Calculite White LED Round

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	662057862347	912400514424	C6L15NUVBZ10	Calculite 6" 1500 Lumen LED New Construction 120-277V	✓	
Philips Lightolier	662057862385	912400514426	C6L20N1VBZ10	Calculite 6" 2000 Lumen LED New Construction 120V	✓	
Philips Lightolier	662057862361	912400513834	C6L15NUVBL	Calculite 6" 1500 Lumen LED New Construction 120-277V - Lutron Hi Lume		✓
Philips Lightolier	662057874142	912400518654	C6L15NUVBZ10VE	Calculite 6" 1500 Lumen LED New Construction 120-277V - Emergency		✓
Philips Lightolier	662057862354	912400514857	C6L15NUVBZ10VL	Calculite 6" 1500 Lumen LED New Construction 120-277V Chicago Plenum		✓
Philips Lightolier	662057862408	912400513835	C6L20N1VBL	Calculite 6" 2000 Lumen LED New Construction 120V Lutron Hi Lume		✓
Philips Lightolier	662057874159	912400518655	C6L20N1VBZ10VE	Calculite 6" 2000 Lumen LED New Construction 120V Emergency		✓
Philips Lightolier	662057862392	912400514858	C6L20N1VBZ10VL	Calculite 6" 2000 Lumen LED New Construction 120V Chicago Plenum		✓
Philips Lightolier	662057862422	912400514428	C6L20N2VBZ10	Calculite 6" 2000 Lumen LED New Construction 277V		✓
Philips Lightolier	662057874197	912400518656	C6L20N2VBZ10VE	Calculite 6" 2000 Lumen LED New Construction 277V Emergency		✓
Philips Lightolier	662057911090	912400526381	C6L10NUVBZ10	Calculite 6" 1000 Lumen LED New Construction 120-277V		✓
Philips Lightolier	662057862446	912400513836	C6L20N2VBL	Calculite 6" 2000 Lumen LED New Construction 277V		✓
Philips Lightolier	662057859491	912400516230	C6L1520DL30KMCCLWV	Calculite 6" 1500/2000lm Med Bm DL, 3000K, Comfort Clear White Flange		✓
Philips Lightolier	662057860541	912400516238	C6L1520DL30KWCCCLWV	Calculite 6" 1500/2000lm Wide Bm DL, 3000K, Comfort Clear White Flange		✓
Philips Lightolier	662057859637	912400516246	C6L1520DL35KMCCLWV	Calculite 6" 1500/2000lm Med Bm DL, 3500K, Comfort Clear White Flange		✓
Philips Lightolier	662057860701	912400516254	C6L1520DL35KWCCCLWV	Calculite 6" 1500/2000lm Wide Bm DL, 3500K, Comfort Clear White Flange		✓
Philips Lightolier	662057859774	912400515942	C6L1520WW30KCCLWV	Calculite 6" 1500/2000 Lumen 3000K LED Open WW - Comfort Clear White Flange		✓
Philips Lightolier	662057860121	912400515950	C6L1520WW35KCCLWV	Calculite 6" 1500/2000 Lumen 3500K LED Open WW - Comfort Clear White Flange		✓
Philips Lightolier	662057910536	912400526959	C6L10DL30KMCCLWV	Calculite 6" 1000 Lumen 3000K LED Downlight Trim, CCL Finish		✓
Philips Lightolier	662057910673	912400526973	C6L10DL35KMCCLWV	Calculite 6" 1000 Lumen 3500K LED Downlight Trim, CCL Finish		✓



7" Calculite White LED Round

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	662057862705	912400514439	C7L35N1VBZ10	Calculite 7" 3500 Lumen LED New Construction 120V		✓
Philips Lightolier	662057927657	912400530747	C7L50N1VBL	Calculite White LED 6000LM 7" NON-IC FRAME 120V LUTRON DIM		
Philips Lightolier	662057927626	912400530749	C7L50N1VBZ10	Calculite White LED 6000LM 7" NON-IC FRAME 120V 0-10V DIM		✓
Philips Lightolier	662057927664	912400530751	C7L50N2VBL	Calculite White LED 6000LM 7" NON-IC FRAME 277V LUTRON DIM		✓
Philips Lightolier	662057927640	912400530754	C7L50N2VBZ10	Calculite White LED 6000LM 7" NON-IC FRAME 277V 0-10V DIM		✓
Philips Lightolier	662057864259	912400516321	C7L1520DL30KMCCLWV	Calculite 7" 1500/2000 Lumen LED Medium Beam Downlight 3000K Comfort Clear White Flange		✓
Philips Lightolier	662057864877	912400516330	C7L1520DL30KWCCCLWV	Calculite 7" 1500/2000 Lumen LED Wide Beam Downlight 3000K Comfort Clear White Flange		
Philips Lightolier	662057864396	912400516338	C7L1520DL35KMCCLWV	Calculite 7" 1500/2000 Lumen LED Medium Beam Downlight 3500k Comfort Clear White Flange		✓
Philips Lightolier	662057865010	912400516346	C7L1520DL35KWCCCLWV	Calculite 7" 1500/2000 Lumen LED Wide Beam Downlight 3500k Comfort Clear White Flange		
Philips Lightolier	662057928555	912400530625	C7L50DL30KMCCLWV	Calculite White LED 7" 6000LM Trim, 3000K - Medium Beam, CCL Finish		✓
Philips Lightolier	662057927992	912400530639	C7L50DL30KNCCCLWV	Calculite White LED 7" 6000LM Trim - 3000K - Narrow Beam, CCL Finish		
Philips Lightolier	662057929125	912400530653	C7L50DL30KWCCCLWV	Calculite White LED 7" 6000LM Trim - 3000K - Wide Beam, CCL Finish		
Philips Lightolier	662057928708	912400530667	C7L50DL35KMCCLWV	Calculite White LED 7" 6000LM Trim - 3500K - Medium Beam, CCL Finish		
Philips Lightolier	662057929279	912400530695	C7L50DL35KWCCCLWV	Calculite White LED 7" 6000LM Trim - 3500K - Wide Beam, CCL Finish		✓
Philips Lightolier	662057928135	912400530681	C7L50DL35KNCCCLWV	Calculite White LED 7" 6000LM Trim - 3500K - Narrow Beam, CCL Finish		
Philips Lightolier	662057926995	912400529634	C7L35CW35KMCCLUV	Calculite White LED Cylinder7" 3500LM Cylinder ALUM. HSG 3500K, CCL Finish, Medium Beam		✓
Philips Lightolier	662057929835	912400530539	C7L50CW30KZ10VWCCLUV	Calculite White LED Cylinder7" Cylinder 6000LM White HSG - 3000K Wide Beam, CCL Finish		
Philips Lightolier	662057929866	912400530557	C7L50CW35KZ10VWCCLUV	Calculite White LED Cylinder7" Cylinder 6000LM White HSG - 3500K, Wide Beam, CCL Finish		



Recessed

Recessed



HP90 LED Recessed

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Day-Brite	734340199350	912400396103	HLS22GLR33L35ULA	2X2		
Philips Day-Brite	734340132854	912400396106	HLS24GLR41L35ULA	2X4		



DuaLED LED Recessed

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Day-Brite	782343882276	912400364135	2DLG38L835-2-D-UNV-DI	2x2, 3800lm, 3500K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		✓
Philips Day-Brite	782343873267	912400363564	2DLG44L835-2-D-UNV-DI	2x2, 4400lm, 3500K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		✓
Philips Day-Brite	782343815458	912400359283	2DLG42L835-4-D-UNV-DI	2x4, 4300lm, 3500K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		
Philips Day-Brite	782343841167	912400361222	2DLG49L835-4-D-UNV-DI	2x4, 4900lm, 3500K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver	✓	
Philips Day-Brite	782343947043	912400367873	2DLG58L835-4-D-UNV-DI	2x4, 5800lm, 3500K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		✓
Philips Day-Brite	782343820230	912400359615	2DLG73L835-4-D-UNV-DI	2x4, 7300lm, 3500K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		✓



EvoGrid LED

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Day-Brite	784197055837	912401274294	3EVG30L835-2-D-UNV	2x2, 3000lm, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver		
Philips Day-Brite	784197061593	912401272954	2EVG30L840-2-D-UNV-DIM	2x2, 3000lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver		✓
Philips Day-Brite	784197028770	912401272141	2EVG38L835-2-D-UNV-DIM	2x2, 3800lm, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver		✓
Philips Day-Brite	784197049133	912401272139	2EVG38L840-2-D-UNV-DIM	2x2, 3800lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver		✓
Philips Day-Brite	784197061302	912401272623	2EVG43L840-4-D-UNV-DIM	2x4, 4300lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver		
Philips Day-Brite	784197028954	912401273161	2EVG43L835-4-D-UNV-DIM	2x4, 4300lm, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver		
Philips Day-Brite	784197028787	912401272138	2EVG45L835-2-D-UNV-DIM	2x2, 4500lm, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver		✓
Philips Day-Brite	784197049140	912401272140	2EVG45L840-2-D-UNV-DIM	2x2, 4500lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver		✓
Philips Day-Brite	784197028961	912401272125	2EVG48L835-4-D-UNV-DIM	2x4, 4800lm, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver		✓
Philips Day-Brite	784197049102	912401272128	2EVG48L840-4-D-UNV-DIM	2x4, 4800lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver		✓
Philips Day-Brite	784197028978	912401272126	2EVG54L835-4-D-UNV-DIM	2x4, 5400lm, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver		✓
Philips Day-Brite	784197049119	912401272129	2EVG54L840-4-D-UNV-DIM	2x4, 5400lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver		✓
Philips Day-Brite	784197028985	912401272127	2EVG74L835-4-D-UNV-DIM	2x4, 7400lm, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver		✓
Philips Day-Brite	784197049126	912401272142	2EVG74L840-4-D-UNV-DIM	2x4, 7400lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver		✓



TG8 LED Recessed with Flat Steel Door Frame

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Day-Brite	78234333402	912401080019	2TG38L835-2-FS-02F-UN	2x2, 3800lm, 3500K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver		✓
Philips Day-Brite	782343332719	912401260245	2TG38L840-2-FS-02F-UN	2x2, 3800lm, 4000K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver	✓	
Philips Day-Brite	782343331156	912401080007	2TG32L835-4-FS-02F-UN	2x4, 3200lm, 3500K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver		✓
Philips Day-Brite	782343330142	912401080001	2TG32L840-4-FS-02F-UN	2x4, 3200lm, 4000K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver		
Philips Day-Brite	782343332030	912401080009	2TG43L835-4-FS-02F-UN	2x4, 4300lm, 3500K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver		✓
Philips Day-Brite	782343330425	912401080003	2TG43L840-4-FS-02F-UN	2x4, 4300lm, 4000K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver		
Philips Day-Brite	782343332221	912401080010	2TG48L835-4-FS-02F-UN	2x4, 4800lm, 3500K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver		✓
Philips Day-Brite	782343330432	912401080004	2TG48L840-4-FS-02F-UN	2x4, 4800lm, 4000K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver	✓	
Philips Day-Brite	782343332573	912401080011	2TG54L835-4-FS-02F-UN	2x4, 5400lm, 3500K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver		✓
Philips Day-Brite	782343330524	912401260999	2TG54L840-4-FS-02F-UN	2x4, 5400lm, 4000K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver	✓	



TG8 Recessed with Flat Steel Door Frame

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Day-Brite	734340607994	912400345503	1TG232-01-UNV-1/2-E	1x4, 2 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast		
Philips Day-Brite	781370989132	912400373181	2TG8217R-01-UNV-1/2-E	2x2, 2 Lamp, 17W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast		✓
Philips Day-Brite	781370943776	912400372909	2TG8231U6R-01-UNV-1/2-E	2x2, 2 Lamp, 31W U6 T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	✓	
Philips Day-Brite	781370989149	912400373182	2TG8317R-01-UNV-1/3-E	2x2, 3 Lamp, 17W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast		✓
Philips Day-Brite	734340981889	912400347273	2TG8232-01-UNV-1/2-EB	2x4, 2 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	✓	
Philips Day-Brite	734340976526	912400347245	2TG8332-01-UNV-1/21-EB	2x4, 3 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	✓	
Philips Day-Brite	734340976533	912400347246	2TG8332-01-UNV-1/3-EB	2x4, 3 Lamp, 32W T8, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	✓	
Philips Day-Brite	734340775488	912400346341	FMA1	1x4 Flange Mounting Frame Assembly For Recessed Fixtures	✓	
Philips Day-Brite	734340775471	912400346340	FMA2	2x2 Flange Mounting Frame Assembly For Recessed Fixtures	✓	
Philips Day-Brite	734340775464	912400346339	FMA2	2x4 Flange Mounting Frame Assembly For Recessed Fixtures	✓	
Philips Day-Brite	782343501603	912400350911	GC	Grid Clip For Recessed Fixtures (4 each)		



Industrial

Industrial



FBX LED High Bay

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Day-Brite	781370009946	912400389505	FBX16LL40-UN	Led High Bay, 16,000 LM, 4000K, Universal Electronic Driver	✓	
Philips Day-Brite	782343066874	912400389502	FBX24LL40-UN	Led High Bay, 24,000 LM, 4000K, Universal Electronic Driver	✓	
Philips Day-Brite	782343142394	912401261309	FBX CHAIN KI	54" Chain/Hnager Kit, Use with FBX High Bay	✓	



FBD LED High Bay

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Day-Brite	782343199558	912400348321	FBD454HO-UNV-1/4-EB-2LS	4 Lamp, 54W T5HO, Universal Electronic Ballast,Two Level Switching Option	✓	
Philips Day-Brite	782343393406	912401025118	FBD632-UNV-1/42-EB	6 Lamp, 32W T8, Universal Electronic Ballast,Two Level Switching Option	✓	
Philips Day-Brite	782343366097	912400349427	FBD632-UNV-1/42-EB	6 Lamp, 32W T8, Universal Electronic High Ballast Factor Ballast,Two Level Switching Option	✓	
Philips Day-Brite	782343264003	912400348812	FBD654HO-UNV-1/42-EB	6 Lamp, 54W T5HO, Universal Electronic Ballast,Two Level Switching Option	✓	
Philips Day-Brite	782343829615	912401025191	FBD-4E-1	Door Frame and Clear Lens Assembly, Use w/ 4 Lamp Fbd High Bay	✓	
Philips Day-Brite	782343829653	912401025192	FBD-6E-1	Door Frame and Clear Lens Assembly, Use w/ 6 Lamp FBD High Bay	✓	
Philips Day-Brite	782343829592	912401025189	WG-FBD	Wire Guard, Use w/ 4 Lamp FBD	✓	
Philips Day-Brite	782343829608	912401025190	WG-FBD	Wire Guard, Use w/ 6 Lamp FBD	✓	
Philips Day-Brite	781370531225	912400370644	FBF/FBE CHAIN KIT	54" Chain/Hanger Kit, Use w/ FBL, FBD, FBF High High Bays	✓	
Philips Day-Brite	781370899813	912400372688	FBF/FBE-GRIP	5' Gripple Hanger Kit, Use w/ FBL, FBD, FBF High Bays	✓	
Philips Day-Brite	781370988838	912400385687	FBF/FBE-GRIP1	10' Gripple Hanger Kit, Use w/ FBL, FBD, FBF High Bays		✓
Philips Day-Brite	781370809348	912400372247	FBF454HO-UNV-1/4-EB-2LS	4 Lamp, 54W T5HO, Universal Electronic Ballast,Two Level Switching Option, Uplight Option		
Philips Day-Brite	781370550103	912401025349	FBF654HO-UNV-1/42-EB	6 Lamp, 32W T8, Universal Electronic Ballast,Two Level Switching Option, Uplight Option		
Philips Day-Brite	781370476618	912400370430	FBF-4E-1	Door Frame and Clear Lens Assembly, Use w/ 4 Lamp FBF High Bay		
Philips Day-Brite	781370476632	912400370432	FBF-6E-1	Door Frame and Clear Lens Assembly, Use w/ 6 Lamp FBF High Bay	✓	
Philips Day-Brite	781370460723	912400370387	WG-FBF	Wire Guard, Use w/ 4 Lamp FBF High Bay or FBL High Bay		
Philips Day-Brite	781370460730	912400370388	WG-FBF	Wire Guard, Use w/ 6 Lamp FBF High Bay		



IA/IS All-Purpose Industrial

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Day-Brite	734340608229	912400345509	IA232-UNV-1/2-E	Uplight Reflector, 4', 2 Lamp, 32W T8, Universal Electronic Ballast	✓	
Philips Day-Brite	734340608243	912400345511	IS232-UNV-1/2-EB	Solid Top Reflector, 4', 2 Lamp, 32W T8, Universal Electronic Ballast	✓	
Philips Day-Brite	734340028409	912400342317	IS286HO-UNV-1/2-E	Solid Top Reflector, 8', 2 Lamp, 86W T8 380mA, Universal Electronic Ballast		
Philips Day-Brite	734340608236	912400345510	TIA232-UNV-1/4-E	Uplight Reflector, 8', 2 Lamp Tandem, 32W T8, Universal Electronic Ballast	✓	
Philips Day-Brite	734340608250	912400345512	TIS232-UNV-1/4-EB	Solid Top Reflector, 8', 2 Lamp Tandem, 32W T8, Universal Electronic Ballast	✓	
Philips Day-Brite	782343184103	912400348218	FKR-12	Chain Hanger Set, (2) 5" Chains & "V" Hooks, Use w/ IA Industrial, IS Industrial, T Strips	✓	
Philips Day-Brite	782343259009	912400348780	FKR-17	Wire Guard, Use w/ IA Industrial, IS Industrial	✓	
Philips Day-Brite	734340823424	912400346605	IS-4R-C	4' Solid Top Reflector For IS Industrial		✓




Vaporlume LED

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Day-Brite	782343494479	912400383547	DWAE27L840-2-UN	Wet Location Industrial, High Impact Acrylic Lens, Plastic Latches, 2', 2700lm, 4000K, Universal Electronic Driver	✓	
Philips Day-Brite	782343500699	912400383927	DWAE51L840-4-UN	Wet Location Industrial, High Impact Acrylic Lens, Plastic Latches, 4', 5100lm, 4000K, Universal Electronic Driver	✓	



Vaporlume

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Day-Brite	734340608267	912400345513	DWAE232-UNV-1/2-EB	Wet Location Industrial, High Impact Acrylic Lens, Plastic Latches, 4', 2 Lamp, 32W T8, Universal Electronic Ballast	✓	
Philips Day-Brite	734340608274	912400345514	TDWAE232-UNV-1/4-E	Wet Location Industrial, High Impact Acrylic Lens, Plastic Latches, 8', 2 Lamp Tandem, 32W T8, Universal Electronic Ballast	✓	
Philips Day-Brite	734340374599	912400344165	TB	Top Bracket Kit For V2/DW Industrial	✓	
Philips Day-Brite	734340374667	912400344170	V2/DW-4ARL-C	4' Replacement Acrylic Lens For DWAE Industrial	✓	
Philips Day-Brite	734340374704	912400344173	V2/DW-8AR	8' Replacement Acrylic Lens For DWAE Industrial	✓	
Philips Day-Brite	781370485887	912400370467	WB	Wall Bracket for V2/DW Vaporlume	✓	



Linear

Linear



OWL Wrap

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Day-Brite	781370176341	912400369691	OWN232-120-1/2-EB-R	4', 2 Lamp, 32W T8, Narrow Housing, 120V Ballast For Residential Use Only		
Philips Day-Brite	734340608281	912400345515	OWN232-UNV-1/2-EB	4', 2 Lamp, 32W T8, Narrow Housing, Universal Electronic Ballast	✓	
Philips Day-Brite	734340608298	912400345516	OWW432-UNV-1/4-EB	4', 4 Lamp, 32W T8, Wide Housing, Universal Electronic Ballast	✓	
Philips Day-Brite	734340608304	912400345517	OWW432-UNV-2/2-E	4', 4 Lamp, 32W T8, Wide Housing, Universal Electronic Ballast		
Philips Day-Brite	734340608311	912400345518	TOWN232-UNV-1/4-E	8', 2 Lamp Tandem, 32W T8, Narrow Housing, Universal Electronic Ballast	✓	



OWL LED Wrap

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Day-Brite	781370049003	912401261072	OWL440L840-UNV-DI	4', 4000lm, 4000K, Universal Electronic 0-10v Driver	✓	
Philips Day-Brite	781370049010	912401261075	OWL450L840-UNV-DI	4', 5000lm, 4000K, Universal Electronic 0-10v Driver		✓
Philips Day-Brite	781370049027	912401261077	OWL470L840-UNV-DI	4', 7000lm, 4000K, Universal Electronic 0-10v Driver		✓
Philips Day-Brite	781370169015	912401261079	OWL850L840-UNV-DI	8', 10000lm, 4000K, Universal Electronic 0-10v Driver		✓



FluxStream LED Strip

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Day-Brite	782343937198	912400367314	LF4104140ULA	4', 4100lm, 4000K, 10% Frosted Lens, Universal Electronic Driver		✓
Philips Day-Brite	782343942888	912400367707	LF4FR3140ULA	4', 3100lm, 4000K, 100% Frosted Lens, Universal Electronic Driver		✓
Philips Day-Brite	782343909959	912400365875	LF4FR3935ULA	4', 3900lm, 3500K, 100% Frosted Lens, Universal Electronic Driver	✓	
Philips Day-Brite	782343468463	912400350744	LF4FR3935USZ	4', 3900lm, 3500K, 100% Frosted Lens, Universal Electronic Step Dimming Driver	✓	
Philips Day-Brite	782343476901	912401025121	LF4FR3935UDZ	4', 3900lm, 3500K, 100% Frosted Lens, Universal Electronic 0-10V Dimming Driver	✓	
Philips Day-Brite	782343909973	912400365876	LF4FR3940ULA	4', 3900lm, 4000K, 100% Frosted Lens, Universal Electronic Driver	✓	
Philips Day-Brite	781370148560	912400394164	LF4FR3940USZ	4', 3900lm, 4000K, 100% Frosted Lens, Universal Electronic Step Dimming Driver	✓	
Philips Day-Brite	782343970560	912400368711	LF4FR3940UDZ	4', 3900lm, 4000K, 100% Frosted Lens, Universal Electronic 0-10V Dimming Driver	✓	
Philips Day-Brite	782343477960	912400382756	LF8104140ULA	8', 8200lm, 4000K, 10% Frosted Lens, Universal Electronic Driver		✓
Philips Day-Brite	781370074319	912400394660	LF8FR3935ULA	8', 7800lm, 3500K, 100% Frosted Lens, Universal Electronic Driver		✓
Philips Day-Brite	782343947012	912400367870	LFR4FLSLD3735ULA	4', 3700lm, 3500K, Solid Reflector, Frosted Lens, Universal Electronic Driver		
Philips Day-Brite	782343960844	912400368473	LFR4FLSLD3740ULA	4', 3700lm, 4000K, Solid Reflector, Frosted Lens, Universal Electronic Driver		✓
Philips Day-Brite	782343965399	912401042677	LF8FR3940ULA	8', 7800lm, 4000K, 100% Frost Lens, Universal Electronic Driver	✓	
Philips Day-Brite	782343458518	912400350588	LFCP	Continuous Row Coupler - Fluxstream/SV T5 Strip	✓	
Philips Day-Brite	782343978429	912400384961	EE9H	V-Hooks and 24" Chain (2) - Fluxstream/SV T5 Strip		
Philips Day-Brite	782343503836	912400397198	SV5-CP	Continuous Row Coupler - Fluxstream Reflector/SV5 T5 Strip Reflector		✓



FluxStream EZ LED Strip

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Day-Brite	782343978641	912400396119	LF4EZ3830ULAG	4', 4000lm, 3000K, 100% Frost Lens, Universal Electronic Driver, Non-dimming	✓	
Philips Day-Brite	782343978634	912400396118	LF4EZ3840ULAG	4', 4000lm, 4000K, 100% Frost Lens, Universal Electronic Driver, Non-dimming	✓	



T Standard Strip

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Day-Brite	734340776201	912400346349	T217-UNV-1/2-E	Standard Strip, 2', 2 Lamp, 17W T8, Universal Electronic Ballast	✓	
Philips Day-Brite	734340776218	912400346350	T225-UNV-1/2-E	Standard Strip, 3', 2 Lamp, 25W T8, Universal Electronic Ballast	✓	
Philips Day-Brite	734340826272	912400346616	T132-UNV-1/1-E	Standard Strip, 4', 1 Lamp, 32W T8, Universal Electronic Ballast	✓	
Philips Day-Brite	781370497842	912400370512	T232-120-1/2-EB-R	Standard Strip, 4', 2 Lamp, 32W T8, 120V Ballast For Residential Use Only		✓
Philips Day-Brite	734340608328	912400345519	T232-UNV-1/2-EB	Standard Strip, 4', 2 Lamp, 32W T8, Universal Electronic Ballast	✓	
Philips Day-Brite	782343100998	912400347814	T296-120-1/2-E	Standard Strip, 8', 2 Lamp, 75W T12 Slimline, 120V Electronic Ballast	✓	
Philips Day-Brite	734340608335	912400345520	TT132-UNV-1/2-E	Standard Strip, 8', 1 Lamp Tandem, 32W T8, Universal Electronic Ballast	✓	
Philips Day-Brite	734340608342	912400345521	TT232-UNV-1/4-EB	Standard Strip, 8', 2 Lamp Tandem, 32W T8, Universal Electronic Ballast	✓	

Strips and Accessories

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Day-Brite	782343300244	912400349033	CS-24	Straight Stem, 3/8" Trade Size, 24" Length	✓	
Philips Day-Brite	782343300367	912400349035	CS-36	Straight Stem, 3/8" Trade Size, 36" Length		
Philips Day-Brite	782343300480	912400349037	CS-48	Straight Stem, 3/8" Trade Size, 48" Length	✓	
Philips Day-Brite	782343297803	912400349015	CS-400	Rigid Canopy, Use w/ 3/8" Straight Stem	✓	
Philips Day-Brite	782343297902	912400349016	CS-500	42 Deg.Top Swivel Canopy, Use w/ 3/8" Straight Stem	✓	
Philips Day-Brite	782343296103	912400348995	CGS-4	Wire Guard, Use w/ 4' N Strip	✓	
Philips Day-Brite	782343296059	912400348992	CG-4	Wire Guard, Use w/ 4' T Strip, TH Strip	✓	
Philips Day-Brite	782343608647	912400351798	DSP-1R	Distributor Fluorescent Parts Service Pack		
Philips Day-Brite	782343296905	912400349007	FL-111	Sliding Hanger, Use w/ Strips or Industrials		
Philips Day-Brite	782343299708	912400349026	FL-123	5' Chain & "S" Hooks, Use w/ Strips or Industrials	✓	
Philips Day-Brite	782343403464	912400349781	TAR-4	4' Asymmetric Reflector For Standard T Strip		
Philips Day-Brite	782343810002	912400358892	TSR-4	4' Symmetric Reflector For Standard T Strip	✓	

EXIT



Exit/Emergency

Exit/Emergency



DEB Series - Emergency Ballast

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Chloride	734340643596	912400345722	DEB-1W	Fluorescent, 350-450 Lumens One Lamp, Damp Location	✓	
Philips Chloride	734340624021	912400345623	DEB-5W	Fluorescent, 1100-1400 Lumens One or Two Lamp, Damp Location	✓	
Philips Chloride	734340602395	912401025049	DEB-7L	Low-Profile Fluorescent, 390-700 Lumens One T5, T5HO, or T8 Lamp, Damp Location	✓	
Philips Chloride	782343823422	912400359847	DEB-7W	Fluorescent, 600-700 Lumens One or Two Lamp, Damp Location	✓	
Philips Chloride	734340929089	912400347041	DEB-8W	4-Pin CFL 700-1250 Lumens One Lamp, Damp Location, Low Mercury Lamps		
Philips Chloride	734340858402	912400346720	MCCAPS	Wire Bundle Kit for External Mounting		



New York City Approved

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Chloride	782343568231	912400351435	44RLU1RNY	NYC Universal Edge Lit LED Exit, Universal Mount, AC Only, Single Face, 8" Red Letters, Clear BackgRound, Satin Aluminum Housing		✓
Philips Chloride	782343568248	912400351436	44RLU2RNY	NYC Universal Edge Lit LED Exit, Universal Mount, AC Only, Double Face, Red Letters, Mirror BackgRound, Satin Aluminum Housing		✓
Philips Chloride	782343568262	912400351438	ER44RLDU2RNY	NYC Universal Edge Lit LED Exit, Universal Mount, Emergency Operation Nicad Battery, Double Face, 8" Red Letters, Mirror BackgRound, Satin Aluminum Housing	✓	



Ex Series Die-Formed Steel LED Exit Sign

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Chloride	734340673586	912400391396	EXEL3RW	Die Formed Steel LED Exit, Nicad Battery		



44R Line Edge-Lit

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Chloride	734340453713	912400344611	ER44RL1	Universal Edge-Lit LED Exit, Emergency LED, AC Only, Satin Aluminum Housing w/ Black End Caps, Single Face, Red or Green Letters, Surface Mounting	✓	
Philips Chloride	734340453720	912400344612	ER44RL2	Universal Edge-Lit LED Exit, Emergency LED, AC Only, Satin Aluminum Housing w/ Black End Caps, Single Face, Red or Green Letters with Mirror BackgRound, Surface Mounting		
Philips Chloride	734340234367	912400343447	ER44RLDU1	Universal Edge-Lit LED Exit, Emergency LED, Satin Aluminum Housing w/ Black End Caps, Single Face, Red or Green Letters, Self-Diagnostics, Universal Mounting	✓	
Philips Chloride	734340234374	912400343448	ER44RLDU2	Universal Edge-Lit LED Exit, Emergency LED, Satin Aluminum Housing w/ Black End Caps, Double Face, Red or Green Letters with Mirror BackgRound, Self-Diagnostics, Universal Mounting	✓	



Value+ Exit

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Chloride	782343263037	912400348807	VERWEM	Value+ Economy Grade Thermoplastic Exit, Red Letters, Emergency NiCad Battery, White Housing	✓	
Philips Chloride	782343263006	912400348805	VERW	Value+ Economy Grade Thermoplastic Exit, Red Letters, White Housing	✓	
Philips Chloride	782343263044	912400348808	VEGWEM	Value+ Economy Grade Thermoplastic Exit, Green Letters, Emergency NiCad Battery, White Housing	✓	
Philips Chloride	782343263020	912400348806	VEGW	Value+ Economy Grade Thermoplastic Exit, Green Letters, White Housing	✓	
Philips Chloride	781370104122	912401025277	VERBEM	Value+ Economy Grade Thermoplastic Exit, Green Letters, Emergency NiCad Battery, Black Housing	✓	



VALUE+ VU6 Unit

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Chloride	782343558386	912400351338	VU6-CS	Value +–VU6 Series (Contractor Grade) Thermoplastic Unit, Sealed Lead Calcium Battery, 6V–5.4W Tungsten Lamps, White Housing, 120/277V Selectable Input	✓	



VALUE+ VC Combo

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Lightolier	781370908478	912400372744	VCRWLRC	Value + Thermoplastic Combo, 6V 12W, Red Letters, No Remote, White Housing, 5.4W Tungsten Lamps	✓	
Philips Lightolier	734340325591	912400343919	VCGLWRC	Value+ Thermoplastic Combo, 6V 22W, Green Letters, White Housing, 12W Remote Capacity, 5.4W Tungsten Lamps	✓	



VALUE+ VCL Combo

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Chloride	782343767269	912400356039	VCLGW	Value+ Thermoplastic LED Combo, Emergency Lead Calcium Battery, 8W Remote, Green Letters, White Housing		



VALUE+ VU6F Unit

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Chloride	782343579749	912400390160	VU6F	Value+ Thermoplastic Emergency Unit, 6V 12W, No Remote, White Housing, 5.4W Tungsten Lamps	✓	



VALUE+ VU6L Unit

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Chloride	782343573716	912400351492	VU6L	Value + Thermoplastic Emergency Units, LED, White Housing, 2.2W Remote, 1.1W LED	✓	



VALUE+ II VA Unit


Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Chloride	782343753750	912400355216	VA6L40W20	Value+II High Capacity Thermoplastic Emergency Unit		
Philips Chloride	782343753651	912400355207	VA6	Value+ II-VA6 Series (Spec Grade) Semi-Recessed Lamp Head Thermoplastic Unit, Sealed Lead Calcium Battery, White Housing, 6V-6W MR16 Lamps, 120/277V Selectable Input		
Philips Chloride	782343753668	912400355208	VT6	Value+II-VT6 Series (Spec Grade) Thermoplastic Unit, Sealed Lead Calcium Battery, White Housing, 6V-5.4W Tungsten Lamps, 120/277V Selectable Input		



Outdoor







Garage & Canopy

Garage & Canopy



G3 Parking Garage and Canopy LED

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Gardco	N/A	912400816135	STK-G3-5-2-73VAR-NW-UNIV-NP	G3 Garage,T-5, 2-Board, 73W, NW, 6341 Lumens, 120/277V, Natural Paint	✓	
Philips Gardco	N/A	912400816380	STK-G3-5-2-73VAR-CW-UNIV-NP	G3 Garage,T-5, 2-Board, 73W, CW, 6341 Lumens, 120/277V, Natural Paint	✓	
Philips Gardco	N/A	912400817150	STK-G3-MR-5-2-73VAR-NW-UNIV-NP	G3 Garage, Motion Response,T-5, 2-Board, 73W, NW, 6341 Lm, 120/277V, Natural Paint		
Philips Gardco	N/A	912400815886	STK-G3-MR-5-2-73VAR-CW-UNIV-NP	G3 Garage, Motion Response,T-5, 2-Board, 73W, CW, 6341 Lm, 120/277V, Natural Paint	✓	
Philips Gardco	N/A	912400816152	STK-G3-5-1-55LA-NW-UNIV-NP	G3 Garage,T-5, 1-Board, 55W, NW, 4423 Lm, 120/277V, Natural Paint	✓	
Philips Gardco	N/A	912400816407	STK-G3-5-1-55LA-CW-UNIV-NP	G3 Garage,T-5, 1-Board, 55W, CW, 4423 Lm, 120/277V, Natural Paint	✓	
Philips Gardco	N/A	912400817391	STK-G3-MR-5-1-55LA-NW-UNIV-NP	G3 Garage, Motion Response,T-5, 1-Board, 55W, Neutral White, 4423 Lm, 120/277V, Natural Paint	✓	
Philips Gardco	N/A	912400816690	STK-G3-MR-5-1-55LA-CW-UNIV-NP	G3 Garage, Motion Response,T-5, 1-Board, 55W, CW, 4423 Lm, 120/277V, Natural Paint	✓	
Philips Gardco	N/A	912400817454	44356010843	Balanced J-Box for Pendant Mount, Natural Paint, 12" Minimum Pendant Required by Others	✓	



Designer Canopy LED

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Gardco	786034956437	912400478146	DCL20LED4K-8	Designer Canopy LED, 20 Hi-Lumen LEDs, 4700K Color Temp, Multi-Tap, Bronze	✓	



Floodlights

Floodlights



LytePro LED Floodlight

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Stonco	786034956925	912401050213	STKLPF1K-8	Stock LPF1, 4000K, Flood, Knuckle Mount, 120-277V,Textured Dark Bronze, (equal to LPF1-E-4K-FL-K-8-BZ)	✓	
Philips Stonco	786034956932	912401050214	STKLPF2K-8	Stock LPF2, 4000K, Flood, Knuckle Mount, 120-277V,Textured Dark Bronze, (equal to LPF2-E-4K-FL-K-8-BZ)	✓	
Philips Stonco	786034956949	912401050215	STKLPF3S-8	Stock LPF3, 4000K, Flood, Slip Fitter, 120-277V,Textured Dark Bronze, (equal to LPF3-C-4K-FL-S-8-BZ)	✓	
Philips Stonco	786034956956	912401050216	STKLPF4S-8	Stock LPF4, 4000K, Flood, Slip Fitter, 120-277V,Textured Dark Bronze, (equal to LPF4-C-4K-FL-S-8-BZ)	✓	
Philips Stonco	786034956963	912401050217	STKLPF4T-8	Stock LPF4, 4000K, Flood,Trunnion, 120-277V,Textured Dark Bronze, (equal to LPF4-C-4K-FL-T-8-BZ)	✓	
Philips Stonco	786034956987	912401050219	LPF1WG	LPF1 Wire Guard Accessory	✓	
Philips Stonco	786034956994	912401050220	LPF2WG	LPF2 Wire Guard Accessory	✓	
Philips Stonco	786034957007	912401050221	LPF3WG	LPF3 Wire Guard Accessory	✓	
Philips Stonco	786034957014	912401050222	LPF4WG	LPF4 Wire Guard Accessory	✓	
Philips Stonco	786034957373	912401050223	LPF1SG	LPF1 Stone Guard Accessory	✓	
Philips Stonco	786034957380	912401050224	LPF2SG	LPF2 Stone Guard Accessory	✓	
Philips Stonco	786034957397	912401050225	LPF3SG	LPF3 Stone Guard Accessory	✓	
Philips Stonco	786034957403	912401050226	LPF4SG	LPF4 Stone Guard Accessory	✓	
Philips Stonco	786034957366	912400528031	LPFW10BZ	LPF1 & LPF2 Wall/Surface Adaptor Accessory,Textured Dark Bronze		
Philips Stonco	786034957588	912401050227	LPFW10W	LPF1 & LPF2 Wall/Surface Adaptor Accessory,Textured White		
Philips Stonco	786034957595	912401050228	LPFW10DG	LPF1 & LPF2 Wall/Surface Adaptor Accessory,Textured Dark Gray		



Wall Mount

Wall Mount



LytePro 32 LED Wall Sconce (LP32)

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Stonco	-	912400531036	LPW32-78BZ	LPW32, 32 LED, 71W, 700mA, 4000K, 120-277V, Bronze textured paint	✓	
Philips Stonco	-	912400531037	LPW32-71BZPCB	LPW32, 32 LED, 71W, 700mA, 4000K, 120V, Bronze textured paint, w/button photocell	✓	
Philips Stonco	-	912400531038	LPW32-7DTBZMR	LPW32, 32 LED, 71W, 700mA, 4000K, 120/277V, Bronze textured paint, w/motion response	✓	
Philips Stonco	-	912400531034	LPW32-78DGY	LPW32, 32 LED, 71W, 700mA, 4000K, 120-277V, Dark gray textured paint	✓	
Philips Stonco	-	912400531043	LPWCVRPLT-BZ	LPW Universal wall cover mounting plate, Bronze textured paint	✓	
Philips Stonco	78603495679	912400461530	LP32T	LP32 Wall Sconce, 32 LED, 71W, 4000K, Typ 3, 120-277V, Titanium		
Philips Stonco	78603495680	912400461529	LP32P	LP32 Wall Sconce, 32 LED, 71W, 4000K, Typ 3, 120-277V, Bronze		
Philips Stonco	78603495681	912400461531	LP32W	LP32 Wall Sconce, 32 LED, 71W, 4000K, Typ 3, 120-277V, White	✓	



LytePro 16 LED Wall Sconce (LP16)

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Stonco	-	912400531024	LPW16-78BZ	LPW16, 16 LED, 40W, 700mA, 4000K, 120-277V, Bronze textured paint	✓	
Philips Stonco	-	912400531025	LPW16-71BZPCB	LPW16, 16 LED, 40W, 700mA, 4000K, 120V, Bronze textured paint, w/button photocell	✓	
Philips Stonco	-	912400531022	LPW16-78DGY	LPW16, 16 LED, 40W, 700mA, 4000K, 120-277V, Dark gray textured paint		
Philips Stonco	-	912400531032	LPW16-58BZ	LPW16, 16 LED, 30W, 530mA, 4000K, 120-277V, Bronze textured paint	✓	
Philips Stonco	-	912400531033	LPW16-51BZPCB	LPW16, 16 LED, 30W, 530mA, 4000K, 120V, Bronze textured paint, w/button photocell	✓	
Philips Stonco	-	912400531043	LPWCVRPLT-BZ	LPW Universal wall cover mounting plate, Bronze textured paint	✓	
Philips Stonco	78603495417	912400461521	LP16T	LP16 Wall Sconce, 16 LED, 40W, 4000K, Typ 3, 120-277V, Titanium	✓	
Philips Stonco	78603495418	912400461522	LP16W	LP16 Wall Sconce, 16 LED, 40W, 4000K, Typ 3, 120-277V, White	✓	



LytePro 7 LED Wall Sconce (LP7)

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Stonco	-	912400531020	LPW7-8BZ	LPW7, COB LED, 14W, 350mA, 4000K, 120-277V, Bronze textured paint	✓	
Philips Stonco	-	912400531021	LPW7-1BZPCB	LPW7, COB LED, 14W, 350mA, 4000K, 120V, Bronze textured paint, w/button photocell	✓	
Philips Stonco	-	912400531018	LPW7-8DGY	LPW7, COB LED, 14W, 350mA, 4000K, 120-277V, Dark gray textured paint	✓	
Philips Stonco	-	912400531043	LPWCVRPLT-BZ	LPW Universal wall cover mounting plate, Bronze textured paint	✓	
Philips Stonco	78603492862	912400491517	LP7T	LP7 Wall Sconce, 7 LED, 13W, 4000K, Typ 3, 120-240V, Titanium		
Philips Stonco	78603492863	912400491518	LP7W	LP7 Wall Sconce, 7 LED, 13W, 4000K, Typ 3, 120-240V, White	✓	




Twilighter Wall Pack LED

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Stonco	78603495644	912400486648	TLW10LED4KPCB-1	TLW LED Wall Pack, 14W, 120V, 4000K, Photocontrol, Bronze	✓	



LED Wall Light (LWL)

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Stonco	786034957359	912401050010	LWLLED1C5K120PCBBZ	LED Wall Light, 5000K, 12W, 120V, Photocell, Bronze	✓	



Site & Area

Site & Area



EcoForm LED (ECF)

Brand	UPC Code	12NC	Part Number	Description	Service Smart	Spec Smart
Philips Gardco	N/A	912400200636	RS-ECF-3-215LA-641A-NW-UNV-BR	ECF Area Light, Typ 3, 215W, 64 LED, 4000K, 120-277V, Bronze		✓
Philips Gardco	N/A	912400200637	RS-ECF-4-215LA-641A-NW-UNV-BR	ECF Area Light, Typ 4, 215W, 64 LED, 4000K, 120-277V, Bronze		✓
Philips Gardco	N/A	912400200638	RS-ECF-5-215LA-641A-NW-UNV-BR	ECF Area Light, Typ 5, 215W, 64 LED, 4000K, 120-277V, Bronze		✓
Philips Gardco	N/A	912400200645	RS-ECF-3-215LA-641A-NW-HVU-BR	ECF Area Light, Typ 3, 215W, 64 LED, 4000K, 347-480V, Bronze		
Philips Gardco	N/A	912400200646	RS-ECF-4-215LA-641A-NW-HVU-BR	ECF Area Light, Typ 4, 215W, 64 LED, 4000K, 347-480V, Bronze		
Philips Gardco	N/A	912400200647	RS-ECF-5-215LA-641A-NW-HVU-BR	ECF Area Light, Typ 5, 215W, 64 LED, 4000K, 347-480V, Bronze		
Philips Gardco	N/A	912400200633	RS-ECF-3-160LA-481A-NW-UNV-BR	ECF Area Light, Typ 3, 160W, 48 LED, 4000K, 120-277V, Bronze		✓
Philips Gardco	N/A	912400200634	RS-ECF-4-160LA-481A-NW-UNV-BR	ECF Area Light, Typ 4, 160W, 48 LED, 4000K, 120-277V, Bronze		✓
Philips Gardco	N/A	912400200635	RS-ECF-5-160LA-481A-NW-UNV-BR	ECF Area Light, Typ 5, 160W, 48 LED, 4000K, 120-277V, Bronze		✓
Philips Gardco	N/A	912400200642	RS-ECF-3-160LA-481A-NW-HVU-BR	ECF Area Light, Typ 3, 160W, 48 LED, 4000K, 347-480V, Bronze		
Philips Gardco	N/A	912400200643	RS-ECF-4-160LA-481A-NW-HVU-BR	ECF Area Light, Typ 4, 160W, 48 LED, 4000K, 347-480V, Bronze		
Philips Gardco	N/A	912400200644	RS-ECF-5-160LA-481A-NW-HVU-BR	ECF Area Light, Typ 5, 160W, 48 LED, 4000K, 347-480V, Bronze		
Philips Gardco	N/A	912400200639	RS-ECF-3-105LA-4870-NW-HVU-BR	ECF Area Light, Typ 3, 105W, 48 LED, 4000K, 347-480V, Bronze		
Philips Gardco	N/A	912400200640	RS-ECF-4-105LA-4870-NW-HVU-BR	ECF Area Light, Typ 4, 105W, 48 LED, 4000K, 347-480V, Bronze		
Philips Gardco	N/A	912400200641	RS-ECF-5-105LA-4870-NW-HVU-BR	ECF Area Light, Typ 5, 105W, 48 LED, 4000K, 347-480V, Bronze		
Philips Gardco	N/A	912400200630	RS-ECF-3-105LA-321A-NW-UNV-BR	ECF Area Light, Typ 3, 105W, 32 LED, 4000K, 120-277V, Bronze		✓
Philips Gardco	N/A	912400200631	RS-ECF-4-105LA-321A-NW-UNV-BR	ECF Area Light, Typ 4, 105W, 32 LED, 4000K, 120-277V, Bronze		✓
Philips Gardco	N/A	912400200632	RS-ECF-5-105LA-321A-NW-UNV-BR	ECF Area Light, Typ 5, 105W, 32 LED, 4000K, 120-277V, Bronze		✓
Philips Gardco	N/A	912400213901	RS-ECF-RAM-BR	ECF Retrofit Arm Kit, Bronze, Round/Square Pole 4"		✓



© 2015 Koninklijke Philips N.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

PLt-15105BR 08/15 philips.com

Philips Lighting
North America Corporation
200 Franklin Square Drive
Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
281 Hillmount Rd.
Markham, ON, Canada L6C 2S3
Tel. 800-668-9008