

# Ballast Autumn Advantage Promotion claim form

Promotion period: September 1 through October 31, 2015

For Official Rules, please

visit [www.philips.com/autumnadvantage](http://www.philips.com/autumnadvantage)

Allow 6-8 weeks after the end of the promo for delivery of rewards.

Gift cards available while supplies last.

Submit this ballast Autumn Advantage promotion claim form through one of the following ways:

- Enter this form information online at [www.philips.com/autumnadvantage](http://www.philips.com/autumnadvantage)
- Submit this form by email to [PhilipsLightingUS1@philips.com](mailto:PhilipsLightingUS1@philips.com)
- Submit this form by fax to 1-855-638-1522

## Choose your reward

- Level A** - \$250 in AMEX® Gift Cards  
Requires purchase of 100 or more qualifying ballast kits assorted over at least 6 SKUs
- Level B** - \$150 in AMEX® Gift Cards  
Requires purchase of at least 60 qualifying ballast kits assorted over at least 4 SKUs
- Level C** - \$50 in AMEX® Gift Cards  
Requires purchase of at least 25 qualifying ballast kits assorted over at least 2 SKUs

## Please indicate how you placed your order

- Customer Service     EDI     Inside Advance

## Reward ship to:

Account No. \_\_\_\_\_  
 Company \_\_\_\_\_  
 Street Address \_\_\_\_\_  
 City, State, Zip \_\_\_\_\_  
 Telephone \_\_\_\_\_  
 Purchaser \_\_\_\_\_  
 E-Mail \_\_\_\_\_  
 P.O. Number \_\_\_\_\_  
 Date \_\_\_\_\_  
 Reward Recipient \_\_\_\_\_

## HID Ballast Replacement Kits

Lamp Type	Watts	Input Voltage	Core & Coil Type	Catalog Number	Unit Qty.
Low Wattage MH	50	120/277	High Reactance	71A5181-001D	
	70	QuadriVolt		71A5191-001D	
	100			71A5292-001D	
	150			71A5390-001D	
			CWA	71A5492-001D	
				71A5493-500D	
Probe Start MH	175	QuadriVolt	CWA	71A5570-001D	
	250	QuadriVolt		71A5770-001D	
		5-TAP		71A5750-001D	
	400	480/120T		71A6041-001D	
		QuadriVolt		71A6071-001D	
	1000	5-TAP		71A6051-001D	
		QuadriVolt		71A6572-001	
	1500	5-TAP		71A6552-001	
480		71A6742-001			
				71A6772-001	
Pulse Start MH	175	QuadriVolt	CWA	71A5593-001D	
	250	5-TAP		71A5752-001D	
		QuadriVolt		71A5792-001D	
	350	QuadriVolt		71A5892-001D	
		5-TAP		71A5993-001D	
	400	480/120T		71A6042-001D	
		5-TAP		71A6052-001D	
	750	QuadriVolt		71A6092-001D	
5-TAP		71A6452-001D			
1000	5-TAP	71A6553-001			
High Pressure Sodium	70	120	Reactor	71A7907-001DB	
		QuadriVolt	CWA	71A7971-001D	
	100	120	Reactor	71A8007-001DB	
		QuadriVolt	CWA	71A8071-001D	
	150	120	Reactor	71A8107-001DB	
		480/120T	CWA	71A8142-001D	
	QuadriVolt	71A8172-001D			
	250	QuadriVolt	71A8271-001D		
		5-TAP	71A8251-001D		
	400	480/120T	71A8443-001D		
		QuadriVolt	71A8473-001D		
	1000	5-TAP	71A8453-001D		
QuadriVolt		71A8773-001			
				71A8753-001	

Total unit quantity

## VAL-U-PAK Plus HID lamp and ballast replacement kits

Lamp Type	Watts	Input Voltage	Kit Type	Catalog Number	Unit Qty.
Low Wattage MH	100	QuadVolt	High Reactance Core & Coil Kit w/ Lamp	77L5390-001D <sup>3</sup>	
Probe Start MH	175	QuadVolt	CWA Core & Coil Kit w/ Lamp	77L5570-001D	
	250	5-TAP		77L5750-001D	
	400	5-TAP		77L6051-001D	
	1000	5-TAP		77L6552-001	
High Pressure Sodium	150	QuadVolt	CWA Core & Coil Kit w/ Lamp	77L8172-001D-MOG	
	250	5-TAP		77L8251-001D	
	400	5-TAP		77L8453-001D	

Total unit quantity

Quad = 120/208/240/277V  
 5-TAP = 120/208/240/277/480V

Val-U-Pak PLUS = Individual carton and system-matched lamp

3. Contains clear mogul base ceramic pulse start metal halide ED23.5 lamp designed as a white light replacement for low wattage HPS

NOTE: All ballasts must be ordered in full carton quantities to qualify for reward

### Official Use Only

Order Release # \_\_\_\_\_