

PHILIPS
LEDALITE

Linear


FloatPlane LED



SPECIAL PREVIEW

Coast-to-coast style that your budget will love

You want your interior spaces to resonate, evoke emotion and satisfy a purpose. And now, it's easier than ever to integrate sleek and sporty linear LED style into your layout, within your budget.



With FloatPlane LED suspended and wall mount luminaires from Philips Ledalite, there's no need to worry about value engineering your design to the bottom line.

Fresh and playful with two profile options - Curve and Edge, FloatPlane's sleek minimalism (only 1.2" h x 8" w) blends seamlessly into your unique layout. Distribution options of 70% up, 75% down and 100% down give you further flexibility.

FloatPlane's performance rivals that of high-end LED luminaires in the industry with outputs **up to 129 LPW**. Now you can have the distinct energy savings of LED, with the affordability of fluorescent luminaires. FloatPlane frees you to achieve exciting new heights in design.

Contact your local Philips Sales Representative for more information.

Product launch date - October 23, 2015

Product Version			Light Source			Housing	
Family	Version	Mounting	Source	CRI & Color Temp	Lumen Package*	Optics**	Run Length
24 FloatPlane	G Edge R Curve	5 Suspended (Symmetric)	L LED	A CRI >80 4000K B CRI >80 3500K C CRI >80 3000K	B 6000 lm/4ft C 4500 lm/4ft E 3200 lm/4ft	AA Acrylic diffusers up/down, 70% up AG Acrylic diffusers up/down, 75% down kit AJ Acrylic diffusers up/down, 100% down kit	04 4ft 06 6ft 08 8ft XX Total Run Length in 2ft Increments
		8 Wall Mount (Asymmetric)			C 4200 lm/4ft E 3100 lm/4ft G 2200 lm/4ft		
					*Nominal output	**Nominal distribution, some up-light in 100% down version	
Electrical				Finish††	Options		
Wiring***		Voltage	Driver†			Controls	
1 1 cct 3 1 cct w/Emergency 5 1 cct w/Battery Pack 7 1 cct w/Dimming B 2 cct Switching A/B N 1 cct Dimming w/Battery Pack		1 120V 2 277V 3 347V	E Philips Advance	W White T Titanium B Black C Custom	DS Response Daylight Sensor DO Actilume Occupancy with Field-enabled Daylight		
*** Additional wiring types available, please ask.			† Alternative driver types available, please ask.	†† Please check lead time & pricing on custom colors.			



© 2015 Koninklijke Philips N.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting, North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
A division of Philips Electronics Ltd.
281 Hillmount Rd, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008