



ICN-4P16-TLED-N				
Brand Name	CENTIUM			
Driver Type	T8 LED Electronic			
Lamp Connection	Parallel			
Input Voltage	120-277V			
Input Frequency	50/60 Hz			
Status	Active			

Electrical Specifications

Compatible Lamp Information						Driver Specifications @120V/@277V						
T8 LED Lamp Brand	T8 LED Lamp Description	T8 LED Lamp Product No.	T8 LED Lamp Model No.	T8 LED Lamp Ordering Code	Bare Lamp Watts (W)	Nom. Initial Lumens	Min. Start Temp (°F/°C)	Num. of Lamps	Input Current (A)	Input Power (W)	Max THD%	Power Factor
Philips	LED InstantFit T8 - 4'	453589 453597	9290011239 9290011240	12T8/48-3000 IF 10/1 12T8/48-3500 IF 10/1	12	1500 1500	1500 1600 -13/-25	4	0.41/0/18	49	10	0.99/0.96
		453605 453613	9290011241 9290011242	12T8/48-4000 IF 10/1 12T8/48-5000 IF 10/1		1600 1650		3	0.34/0.15	41	15	0.99/0.95
Philips	LED InstantFit T8 - 4' High Output	456897 456905	9290011585 9290011586	15T8/48-3000 IF 10/1 15T8/48-3500 IF 10/1	15	2000 2000	-13/-25	4	0.51/0.22	61	10	0.99/0.97
		456913 456921	9290011587 9290011588	15T8/48-4000 IF 10/1 15T8/48-5000 IF 10/1		2100 2100		3	0.54/0.23	65	15	0.99/0.97
Philips	LED InstantFit T8 - 4' High Output	434860 434878	9290002880 9290002881	16.5T8/48-3000 IF 10/1 16.5T8/48-3500 IF 10/1	16.5	2000 2000	-13/-25	4	0.60/0.26	71	10	0.99/0.97
		434886 434894	9290002882 9290002883	16.5T8/48-4000 IF 10/1 16.5T8/48-5000 IF 10/1		2100 2150		З	0.50/0.22	60	15	0.99/0.97
Philips	LED InstantFit T8 - 3'	452052 452060	9290011183 9290011184	10.5T8/36-3000 IF 10/1 10.5T8/36-3500 IF 10/1	10.5	1100 1160	-13/-25	4	0.38/0.17	45	10	0.99/0.95
		452078 452086	9290011185 9290011186	10.5T8/36-4000 IF 10/1 10.5T8/36-5000 IF 10/1		1200 1270	-13/-23	3	0.31/0.14	38	15	0.99/0.94
Philips	LED InstantFit T8 - 2'	452011 452029	9290011179 9290011180	8.5T8/24-3000 IF 10/1 8.5T8/24-3500 IF 10/1	8.5	950 1040	040 050 -13/-25	4	0.33/0.15	39	10	0.99/0.94
		452037 452045	9290011181 9290011182	8.5T8/24-4000 IF 10/1 8.5T8/24-5000 IF 10/1		1050 1100		3	0.27/0.13	33	15	0.99/0.93













Revised: 07/28/15

Data is based on tests performed by Philips Lighting NA in a controlled environment and is representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice. All specifications are nominal unless otherwise noted.



ICN-4P16-TLED-N					
Brand Name	CENTIUM				
Driver Type	T8 LED Electronic				
Lamp Connection	Parallel				
Input Voltage	120-277V				
Input Frequency	50/60 Hz				
Status	Active				

Electrical Specifications

Notes:

Section I - Physical Characteristics

- 1.1 Driver shall be physically interchangeable with standard electromagnetic or standard electronic ballasts, where applicable.
- 1.2 Driver shall be provided with integral leads color coded per ANSI C82.11.

Section II - Performance Requirements

- 2.1 Driver shall energize compatible LED lamps within 1 second after mains power is applied.
- 2.2 Driver shall provide Independent Lamp Operation (ILO) allowing remaining lamp(s) to maintain full light output when one or more lamps fail.
- 2.3 Driver shall contain auto restart circuitry in order to restart lamps without resetting power.
- 2.4 Driver shall operate from a 50Hz or 60 Hz AC input source of 120V through 277V with sustained variations of +/- 10% (voltage and frequency).
- 2.5 Driver shall be high frequency electronic type and operate lamps at frequencies above 42 kHz to avoid interference with infrared devices and eliminate visible flicker
- 2.6 Driver shall have a Power Factor of 0.94 or above when operating the maximum rated number of compatible lamps, and 0.88 or above when operating the minimum rated number of compatible lamps.
- 2.7 Driver input current shall Total Harmonic Distortion (THD) of 10% or less when operating the maximum rated number of compatible lamps and 15% or less when operating the minimum rated number of compatible lamps.
- 2.8 Driver shall have a Class A sound rating.
- 2.9 Driver shall have a minimum starting temperature of -13°F / -25°C.
- 2.10 Driver shall tolerate sustained open circuit and short circuit output conditions.
- 2.11 Driver shall be capable of operating lamps remotely and in tandem for wire lengths up to 20 ft.
- 2.12 Driver shall be suitable of operation in up to a 45°C ambient temperature.

Section III - Regulatory Requirements

- 3.1 Driver shall not contain any Polychlorinated Biphenyl (PCB).
- 3.2 Driver shall be Underwriters Laboratories (UL) Recognized, Class P, and suitable for Damp and Dry conditions; and CSA Certified where applicable.
- 3.3 Driver shall comply with ANSI C62.41 Category A Transient protection.
- 3.4 Driver shall comply with the requirements of the Federal Communication Commission (FCC) rules and regulations, Title 47, CFR part 15, Non-Consumer (Class A) for EMI/RFI (conducted and radiated).
- 3.5 Driver shall comply with NEMA 410 for in-rush current limits.

Section IV - Other

- 4.1 Driver shall be manufactured in a factory certified to ISO 9001 Quality System Standards.
- 4.2 Driver shall carry a five year warranty from date of manufacture against defects in material and workmanship when operating in a 45°C ambient (