Philips T8 U-Bent Lamps

featuring ALTO[®] Lamp Technology

Environmentally Responsible Lamps



Ideal for commercial applications with 2' x 2' fixtures

Full Line of 6" Leg Spacing FB32T8 Lamps Range of color temperatures (3000K to 5000K)

Outstanding Lumen Performance

HI-VISION[®] Phosphor delivers:

- -95% lumen maintenance
- -85 CRI for TL830, 835, and 841 lamps
- -84 CRI for TL850 lamps
- -75 CRI for TL730, 735, 741, and 750 lamps


Sustainable Lighting Solution

Reduces the impact on the environment -Low mercury -Energy efficient

Philips T8 U-Bent Warranty Period: 24 Months



Philips Energy Advantage T8 U-Bent Lamps Rated Average Life



 Average life under specified test conditions with lamps turned off and restarted no more frequently than once every 3 operating hours. Lamp life is appreciably longer if lamps are started less frequently.

2) Average life under engineering data with lamps turned off and restarted once every 12 operating hours.



Philips Lighting 281 Hillmount Road Markham, Ontario Canada L6C 2S3 1-800-555-0050 www.philips.ca A Division of Philips Electronics Ltd.

Philips T8 U-Bent Lamps featuring ALTO® Lamp Technology

Electrical, Technical and Ordering Data (Subject to change without notice)

			Standard	Color	Nominal	Rated Average Life ¹		Approx.		Color
Product	_	Nominal	Package	Temp.	Length	12 Hour	12 Hour	Initial	Design	Rendering
Number	Description	Watts	Quantity	(Kelvin)	(in)	Instant Start	Programmed Start	Lumens ²	Lumens ³	CRI
37897-6	FB32T8/TL830/6/ALTO	32	20	3000K	22 7/16	24,000	30,000	2800	2535	85
37900-8	FB32T8/TL835/6/ALTO	32	20	3500K	22 7/6	24,000	30,000	2800	2535	85
37902-4	FB32T8/TL841/6/ALTO	32	20	4100K	22 7/16	24,000	30,000	2800	2535	85
37880-2	FB32T8/TL850/6/ALTO	32	20	5000K	22 7/6	24,000	30,000	2750	2500	84
37892-7	FB32T8/TL730/6/ALTO	32	20	3000K	22 7/6	24,000	30,000	2650	2370	75
37893-5	FB32T8/TL735/6/ALTO	32	20	3500K	22 7/16	24,000	30,000	2650	2370	75
37894-3	FB32T8/TL741/6/ALTO	32	20	4100K	22 7/6	24,000	30,000	2650	2370	75
37882-8	FB32T8/TL750/6/ALTO	32	20	5000K	22 7/16	24,000	30,000	2600	2325	75

1) Average life under specified test conditions with lamps turned off and restarted no more frequently than once every 12 operating hours. Lamp life is appreciably longer if lamps are started less frequently. 2) Approximate initial lumens. The lamp lumen output is based upon lamp performance after 100 hours of operating life, when the output is measured during operation on a reference ballast under standard laboratory conditions.

3) Design lumens are the approximate lamp lumen output at 40% of the lamp's rated average life. This output is based upon measurements obtained during lamp operation on a reference ballast under standard laboratory conditions.



† This lamp is better for the environment because of its reduced mercury content. All Philips ALTO® lamps give you end-of-life options which can simplify and reduce your lamp disposal costs depending on your state and local regulations.



© 2015 Koninklijke Philips N.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication. Philips Lighting Company 200 Franklin Square Drive Somerset, NJ 08873 Phone: 855-486-2216 Philips Lighting Company 281 Hillmount Road Markham ON, Canada L6C 2S3 Phone: 800-668-9008

P-5820-A philips.com/luminaires