

Philips LED Lamps

3.5W Candle (direct white)



Applicable Philips Part Numbers

9290002417(427799), 9290002419(427815), 9290002418(427781), 9290002420(427807), 9290002417(427765), 9290002419(427773)

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613			X
Leviton	SureSlide	6615P			X
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674		1-10 ¹	>10
Leviton	Trimatron	6681			X
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06			X
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU			X
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA ²		2-42 ¹	1
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA		1-8 ¹	>8
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA			X
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W			X
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²		1-42 ¹	

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P			X
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	10-21	1-10	
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2 ²		1-42 ¹	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-42 ¹	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²		1-42 ¹	
Lutron	Nova	NLV1000 ²		1-47* ¹	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²			X
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-42		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P			X
Lutron	Skylark	SCL153P v2 ²		4-42 ¹	1-4
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors

Lutron	Skylark	MSCL-OP153MH	1-24
Lutron	Maestro	MS-OPS2H	1-24
Leviton	Decora	IPS02	
Leviton	Decora	IPS15	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.

All rights reserved. Updated 6/28/2013

PHILIPS

Philips LED Lamps

2.5 W (25 W Equivalent) Candle

DiamondSpark



Applicable Philips Part Numbers	
435149(9290002799), 451831 (9290011151)	

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Cooper	REACT	RI061-VW-K2				
Leviton	Decora	6161				
Leviton	SureSlide	6613		1-7 ^{*1}		
Leviton	SureSlide	6615P				X
Leviton	SureSlide	6631				
Leviton	SureSlide	6633			1-7 ^{*1}	
Leviton	SureSlide	6672		1-7 ^{*1}		
Leviton	SureSlide	6674		1-7 ^{*1}		
Leviton	Trimatron	6602				X
Leviton	Trimatron	6681				X
Leviton	Trimatron	6683				
Leviton	Trimatron	6684				
Leviton	IllumaTech	IPE04-1LZ				
Leviton	IllumaTech	IPI06				X
Leviton	IllumaTech	IPM10		1-7 ^{*1}		
Leviton	Monet	MNE04-ILW				
Leviton	Monet	MNI06-1				
Philips	Sunrise	SR400RPC120				
Philips	Sunrise	SR1000VA120		1-7 ^{*1}		
Philips	Sunrise	SR150LED120		1-7 ^{*1}		
WattStopper	Micro Decorator	DCD267-W		1-7 ^{*1}		
WattStopper	Architectural	ADMLV-703-W				
WattStopper	Architectural	AD-1103-W				
WattStopper	Paddle	PDMLV-703-W				
WattStopper	Paddle	PD-703-W				
WattStopper	Slide	SDMLV-603-W				
WattStopper	Slide	SD-603-W				
Lutron	Skylark	CTCL-153P				
Lutron	Diva	DVCL-153PD				
Lutron	Diva	DVCL-153P v2 ²			1-7 ^{*1}	
Lutron	Diva	DVPDC-203				
Lutron	Diva	DV-600P			1-7 ^{*1}	
Lutron	Diva	DV-603PG				
Lutron	DIVA	DVELV-300P		1-7 ^{*1}		
Lutron	Diva	DVWCL-153PDH				
Lutron	Glyder	GL-600P				

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Lutron	Maestro	MAELV-600			1-7 ^{*1}	
Lutron	Maestro	MAELV-600				
Lutron	Maestro	MALV-600				
Lutron	Maestro	MRF2-600M				
Lutron	Maestro	MRF2-6ND-120			1-7 ^{*1}	
Lutron	Grafik Eye	NGRX-PB				
Lutron	Nova	NLV600 ²				
Lutron	Nova	NLV1000 ²			1-7 ^{*1}	
Lutron	Nova	NT-600-W				
Lutron	Nova	NT-1500-WH				
Lutron	Nova	NT-2000-WH				
Lutron	Fluo	NTF-10				
Lutron	Nova	NTELV-300				
Lutron	Grafik Eye	QSGR-3P ²			1-7 ^{*1}	
Lutron	Qoto	Q-600P				
Lutron	RADIO RA	RRD-6NA ²			1-7 ^{*1}	
Lutron	Skylark	S-600P				
Lutron	Skylark	SELV-300P				
Lutron	Skylark	SLV-600P			1-7 ^{*1}	
Lutron	Skylark	SCL153P v2 ²				
Lutron	Toggler	TG-600P				
Lutron	Credenza	TT-300				
Lutron	Credenza	TTCL-100DH				
Lutron	Power Module	PHPM-WBX				
Lutron	Verti	VT600-B-AL				
Lutron	Verti	VTELV-600M-B				
Lutron	Verti	VTELV-600M-I				
Lutron	Caseta	PD-6WCL (SD11)			1-7 ^{*1}	

Sensors			
Lutron	Maestro	MSCL-OP153MH	
Lutron	Maestro	MS-OPS2H	
Leviton	Decora	IPS02	
Leviton	Decora	IPS15	

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	TBD
Lutron	Panel Module	HW/LP-RPM-4U-120	TBD

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 7/24/14

Philips LED Lamps

4.5 W (40 W Equivalent) Candle

DiamondSpark



Applicable Philips Part Numbers	
435172(9290002797), 435156 (9290002889), 435164 (9290002798)	

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Cooper	REACT	RI061-VW-K2				
Leviton	Decora	6161				
Leviton	SureSlide	6613				X
Leviton	SureSlide	6615P				X
Leviton	SureSlide	6631				
Leviton	SureSlide	6633			1-10 ¹	
Leviton	SureSlide	6672			1-10 ¹	
Leviton	SureSlide	6674			1-10*	
Leviton	Trimatron	6602				X
Leviton	Trimatron	6681				X
Leviton	Trimatron	6683				
Leviton	Trimatron	6684				
Leviton	IllumaTech	IPE04-1LZ				
Leviton	IllumaTech	IPI06				X
Leviton	IllumaTech	IPM10			1-10 ¹	
Leviton	Monet	MNE04-ILW				
Leviton	Monet	MNI06-1				
Philips	Sunrise	SR400RPC120				
Philips	Sunrise	SR1000VA120			1-10*	
Philips	Sunrise	SR150LED120			1-10*	
WattStopper	Micro Decorator	DCD267-W		1-10*		
WattStopper	Architectural	ADMLV-703-W				
WattStopper	Architectural	AD-1103-W				
WattStopper	Paddle	PDMLV-703-W				
WattStopper	Paddle	PD-703-W				
WattStopper	Slide	SDMLV-603-W				
WattStopper	Slide	SD-603-W				
Lutron	Skylark	CTCL-153P				
Lutron	Diva	DVCL-153PD				
Lutron	Diva	DVCL-153P v2 ²				X
Lutron	Diva	DVPDC-203				
Lutron	Diva	DV-600P				X
Lutron	Diva	DV-603PG				
Lutron	DIVA	DVELV-300P				X
Lutron	Diva	DVWCL-153PDH				
Lutron	Glyder	GL-600P				

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Lutron	Maestro	MAELV-600			1-10*	
Lutron	Maestro	MAELV-600				
Lutron	Maestro	MALV-600				
Lutron	Maestro	MRF2-600M				
Lutron	Maestro	MRF2-6ND-120			1-10*	
Lutron	Grafik Eye	NGRX-PB				
Lutron	Nova	NLV600 ²				
Lutron	Nova	NLV1000 ²			1-10 ¹	
Lutron	Nova	NT-600-W				
Lutron	Nova	NT-1500-WH				
Lutron	Nova	NT-2000-WH				
Lutron	Fluo	NTF-10				
Lutron	Nova	NTELV-300				
Lutron	Grafik Eye	QSGR-3P ²			1-10*	
Lutron	Qoto	Q-600P				
Lutron	RADIO RA	RRD-6NA ²			1-10*	
Lutron	Skylark	S-600P				
Lutron	Skylark	SELV-300P				
Lutron	Skylark	SLV-600P			1-10*	
Lutron	Skylark	SCL153P v2 ²				
Lutron	Toggler	TG-600P				
Lutron	Credenza	TT-300				
Lutron	Credenza	TTCL-100DH				
Lutron	Power Module	PHPM-WBX				
Lutron	Verti	VT600-B-AL				
Lutron	Verti	VTELV-600M-B				
Lutron	Verti	VTELV-600M-I				
Lutron	Caseta	PD-6WCL (SD11)			1-10*	

Sensors			
Lutron	Maestro	MSCL-OP153MH	
Lutron	Maestro	MS-OPS2H	
Leviton	Decora	IPS02	
Leviton	Decora	IPS15	

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	TBD
Lutron	Panel Module	HW/LP-RPM-4U-120	TBD

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 6/23/14



Philips LED Lamps

6.5 W (60 W Equivalent) Candle

DiamondSpark



Applicable Philips Part Numbers	
435180 (9290002886), 452813 (9290011121)	

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-10*		
Leviton	SureSlide	6615P			X
Leviton	SureSlide	6631			
Leviton	SureSlide	6633		1-10*	
Leviton	SureSlide	6672	1-10*		
Leviton	SureSlide	6674		1-10*	
Leviton	Trimatron	6602			X
Leviton	Trimatron	6681			X
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06			X
Leviton	IllumaTech	IPM10	1-10*		
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120	1-10*		
Philips	Sunrise	SR150LED120		1-10*	
WattStopper	Micro Decorator	DCD267-W	1-10*		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²			X
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-10*		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P			X
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²		1-10*	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-10* ¹	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²		1-10* ¹	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²		1-10*	
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²		1-10*	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-10*	
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)		1-10*	

Sensors			
Lutron	Maestro	MSCL-OP153MH	
Lutron	Maestro	MS-OPS2H	
Leviton	Decora	IPS02	
Leviton	Decora	IPS15	

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	1-10*
Lutron	Panel Module	HW/LP-RPM-4U-120	1-10*

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 6/23/14

Philips LED Lamps

3.5W (25W Equivalent) Candle

DiamondSpark with warm glow effect



Applicable Philips Part Numbers	
9290011668(457242), 9290011668(457234), 9290011668(457226)	

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-35		
Leviton	SureSlide	6615P	1-17		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633	1-25		
Leviton	SureSlide	6672	1-35		
Leviton	SureSlide	6674	1-20		
Leviton	Trimatron	6602	1-15*		
Leviton	Trimatron	6681	1-25		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-35		
Leviton	IllumaTech	IPM10	2-25		1
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120	2-25*		1
Philips	Sunrise	SR150LED120	1-20		
WattStopper	Micro Decorator	DCD267-W	1-25		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²			X
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-15*		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-17		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²		1-35	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-35		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-47		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²	1-50		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-35		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-15	16-26	
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)	1-35		

Sensors				
Lutron	Maestro	MSCL-OP153MH	2-45	1
Lutron	Maestro	MS-OPS2H	1-45	
Leviton	Decora	IPS02	1-45	
Leviton	Decora	IPS15	1-35	

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	1-50*
Lutron	Panel Module	HW/LP-RPM-4U-120	1-50*

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 6/11/2015



Philips LED Lamps

4.5W (40W Equivalent) Candle

DiamondSpark with warm glow effect



Applicable Philips Part Numbers	
9290011673(457200), 9290011673(457192), 9290011673(457184), 9290011674(457150), 9290011674(457143), 9290011672(457176), 9290011672(457168), 9290011671(457218), 9290011670(457135), 9290011670(457127), 9290011670(457119)	

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-26		
Leviton	SureSlide	6615P	1-13		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633	1-26		
Leviton	SureSlide	6672	1-26		
Leviton	SureSlide	6674	1-10*		
Leviton	Trimatron	6602	1-26		
Leviton	Trimatron	6681	1-26		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-26		
Leviton	IllumaTech	IPM10	2-32		1
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120	2-32		1
Philips	Sunrise	SR150LED120	1-10*		
WattStopper	Micro Decorator	DCD267-W		1-26	
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²			X
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-26		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-13		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²		1-26	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-26	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-35		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²		1-50	
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²			X
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-19*		
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)			X

Sensors			
Lutron	Maestro	MSCL-OP153MH	1-33
Lutron	Maestro	MS-OPS2H	1-33
Leviton	Decora	IPS02	1-33
Leviton	Decora	IPS15	1-26

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	1-40*
Lutron	Panel Module	HW/LP-RPM-4U-120	1-45*

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 6/11/2015



Philips LED Lamps
7W (60W Equivalent) Candle
DiamondSpark with warm glow effect



Applicable Philips Part Numbers	
9290011820(458695), 9290011821(458661), 9290011822(458638), 9290011820(458687), 9290011821(458653), 9290011822(458620), 9290011820(459321), 9290011820(458703), 9290011821(458679)	

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-21		
Leviton	SureSlide	6615P		1-11	
Leviton	SureSlide	6631			
Leviton	SureSlide	6633		1-21	
Leviton	SureSlide	6672	1-21		
Leviton	SureSlide	6674		1-21	
Leviton	Trimatron	6602		1-21	
Leviton	Trimatron	6681	1-21		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-21	
Leviton	IllumaTech	IPM10		1-25	
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120		1-25	
Philips	Sunrise	SR150LED120		1-21	
WattStopper	Micro Decorator	DCD267-W		1-21	
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153P v2 ²			X
Lutron	Diva	DVCL-153P v2.1 ²	1-10	11-21	
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P		1-21	
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P		1-11	
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²		1-21	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-21	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-23*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²		1-25*	
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²		1-25	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-16	
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)			X

Sensors			
Lutron	Maestro	MSCL-OP153MH	X
Lutron	Maestro	MS-OPS2H	1-21
Leviton	Decora	IPS02	1-21
Leviton	Decora	IPS15	1-21

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	1-25*
Lutron	Panel Module	HW/LP-RPM-4U-120	1-25*

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 10/13/2015



Philips LED Lamps

6W PAR16



Applicable Philips Part Numbers
423509(9000224204), 423418(9290002242), 429316(9290002443)

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Cooper	REACT	RI061-VW-K2				
Leviton	Decora	6161				
Leviton	SureSlide	6613		1-16 ¹	>16	
Leviton	SureSlide	6615P				X
Leviton	SureSlide	6631				
Leviton	SureSlide	6633P				
Leviton	SureSlide	6674		1-8 ¹	>8	
Leviton	Trimatron	6681		1-8 ¹	>8	
Leviton	Trimatron	6683				
Leviton	Trimatron	6684				
Leviton	IllumaTech	IPE04-1LZ				
Leviton	IllumaTech	IPI06		1-8	>8	
Leviton	Monet	MNE04-ILW				
Leviton	Monet	MNI06-1				
Lightolier	Vega	V600VAU		1-16 ¹	>16	
Lightolier	Vega	V1000VAU				
Lightolier	Sunrise	ZP600VA ²		1-25 ¹		
Lightolier	Sunrise	ZP600				
Lightolier	Vega	V600				
Lightolier	Onset	OS600				
Lightolier	Onset	OS600VA		1-8 ¹	>8	
Lightolier	Onset	OS1000VA				
Lightolier	Astral Slider	A600				
Lightolier	Astral Slider	AP600				
Lightolier	MultiSet	MHP600VA		1-8 ¹	>8	
Lightolier	Momentum	MP2000VAI				
WattStopper	Micro Decorator	DCD267-W		1-16 ¹	>16	
WattStopper	Architectural	ADMLV-703-W				
WattStopper	Architectural	AD-1103-W				
WattStopper	Paddle	PDMLV-703-W				
WattStopper	Paddle	PD-703-W				
WattStopper	Slide	SDMLV-603-W				
WattStopper	Slide	SD-603-W				
Lutron	Skylark	CTCL-153P				
Lutron	Diva	DVCL-153PD				
Lutron	Diva	DVCL-153P v2 ²				X

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Lutron	Diva	DVPDC-203				
Lutron	Diva	DV-600P		1-16 ¹	>16	
Lutron	Diva	DV-603PG				
Lutron	DIVA	DVELV-300P		1-12		
Lutron	Diva	DVWCL-153PDH				
Lutron	Glyder	GL-600P				
Lutron	Maestro	MAEL-153M v2 ²		1-8 ¹	>8	
Lutron	Maestro	MAELV-600				
Lutron	Maestro	MALV-600				
Lutron	Maestro	MRF2-600M				
Lutron	Maestro	MRF2-6ND-120		1-25 ¹		
Lutron	Grafik Eye	NGRX-PB				
Lutron	Nova	NLV600 ²		1-25 ¹		
Lutron	Nova	NLV1000 ²		1-29* ¹		
Lutron	Nova	NT-600-W				
Lutron	Nova	NT-1500-WH				
Lutron	Nova	NT-2000-WH				
Lutron	Fluo	NTF-10				
Lutron	Nova	NTELV-300				
Lutron	Grafik Eye	QSGR-3P ²		1-29* ¹		
Lutron	Qoto	Q-600P				
Lutron	RADIO RA	RRD-6NA ²		1-25		
Lutron	Skylark	S-600P				
Lutron	Skylark	SELV-300P				
Lutron	Skylark	SLV-600P		1-8 ¹	>8	
Lutron	Skylark	SCL153P v2 ²				X
Lutron	Toggler	TG-600P				
Lutron	Credenza	TT-300				
Lutron	Credenza	TTCL-100DH				
Lutron	Power Module	PHPM-WBX				
Lutron	Verti	VT600-B-AL				
Lutron	Verti	VTELV-600M-B				
Lutron	Verti	VTELV-600M-I				

Sensors			
Lutron	Skylark	MSCL-OP153MH	1-25
Lutron	Maestro	MS-OPS2H	1-25
Leviton	Decora	IPS02	
Leviton	Decora	IPS15	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.

All rights reserved. Updated 6/28/2013



Philips LED Lamps 8W PAR20/AirFlux



Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613		1-3 ¹	
Leviton	SureSlide	6615P	1-6		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674		1-3 ¹	>3
Leviton	Trimatron	6681		1-6 ¹	>6
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-10 ¹	>10
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU		1-13 ¹	
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA ²		1-10 ¹	>10
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA		1-13 ¹	
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA		1-13 ¹	
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W		1-13 ¹	
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²		1-13 ¹	

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Applicable Philips Part Numbers

426171(9290002335), 426148(9290002332), 426122(9290002330), 426130(9290002331), 426155(9290002333), 426163(9290002334), 426114(9290002329), 428698(9290002329)

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P		1-10 ¹	>10
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-6		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2 ²		1-13 ¹	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-13 ¹	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²		1-13 ¹	
Lutron	Nova	NLV1000 ²		1-23 ¹	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²		1-18 ¹	
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-13		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-13 ¹	
Lutron	Skylark	SCL153P v2 ²		1-13 ¹	
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors

Lutron	Skylark	MSCL-OP153MH	
Lutron	Maestro	MS-OPS2H	
Leviton	Decora	IPS02	
Leviton	Decora	IPS15	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.

All rights reserved. Updated 6/28/2013

Philips LED Lamps

8W R20



Applicable Philips Part Numbers
420331(9290002192), 423400(9290002192), 428813(9290002192)

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-18		
Leviton	SureSlide	6615P	1-9		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-14		>14
Leviton	Trimatron	6681	1-8	9-10	>10
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-18	
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-18		
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA ²	1-18		
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA	1-8		>8
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA	1-10		>10
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-18		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²	1-18		

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-8	9-10	>10
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P			X
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2 ²		1-18 ¹	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-18		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²	1-18		
Lutron	Nova	NLV1000 ²	1-18		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²			X
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-18		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-8	9-18	
Lutron	Skylark	SCL153P v2 ²		1-18	
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors			
Lutron	Skylark	MSCL-OP153MH	1-18
Lutron	Maestro	MS-OPS2H	1-18
Leviton	Decora	IPS02	
Leviton	Decora	IPS15	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 6/28/2013



Philips LED Lamps
8W A19 Bulb (White)
40W Equivalent



Applicable Philips Part Numbers
 423483(9290002267), 424374(9290002267), 425256(9290002295),
 429266(9290002267)

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Cooper	REACT	RI061-VW-K2				
Leviton	Decora	6161				
Leviton	SureSlide	6613			1-12	>12
Leviton	SureSlide	6615P		1-9		
Leviton	SureSlide	6631				
Leviton	SureSlide	6633P				
Leviton	SureSlide	6674				X
Leviton	Trimatron	6681				X
Leviton	Trimatron	6683				
Leviton	Trimatron	6684				
Leviton	IllumaTech	IPE04-1LZ				
Leviton	IllumaTech	IPI06		1-9		>9
Leviton	Monet	MNE04-ILW				
Leviton	Monet	MNI06-1				
Lightolier	Vega	V600VAU		1-13		
Lightolier	Vega	V1000VAU				
Lightolier	Sunrise	ZP600VA ²				X
Lightolier	Sunrise	ZP600				
Lightolier	Vega	V600				
Lightolier	Onset	OS600				
Lightolier	Onset	OS600VA		1-13		
Lightolier	Onset	OS1000VA				
Lightolier	Astral Slider	A600				
Lightolier	Astral Slider	AP600				
Lightolier	MultiSet	MHP600VA				X
Lightolier	Momentum	MP2000VAI				
WattStopper	Micro Decorator	DCD267-W		2-13 ¹		1
WattStopper	Architectural	ADMLV-703-W				
WattStopper	Architectural	AD-1103-W				
WattStopper	Paddle	PDMLV-703-W				
WattStopper	Paddle	PD-703-W				
WattStopper	Slide	SDMLV-603-W				
WattStopper	Slide	SD-603-W				
Lutron	Skylark	CTCL-153P				
Lutron	Diva	DVCL-153PD				
Lutron	Diva	DVCL-153P v2 ²		1-18		

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Lutron	Diva	DVPDC-203				
Lutron	Diva	DV-600P		1-6		>6
Lutron	Diva	DV-603PG				
Lutron	DIVA	DVELV-300P			1-9	
Lutron	Diva	DVWCL-153PDH				
Lutron	Glyder	GL-600P				
Lutron	Maestro	MACL-153M v2 ²		1-12		>12
Lutron	Maestro	MAELV-600				
Lutron	Maestro	MALV-600				
Lutron	Maestro	MRF2-600M				
Lutron	Maestro	MRF2-6ND-120		1-12		>12
Lutron	Grafik Eye	NGRX-PB				
Lutron	Nova	NLV600 ²		1-8	8-11	>11
Lutron	Nova	NLV1000 ²		1-8	8-11	>11
Lutron	Nova	NT-600-W				
Lutron	Nova	NT-1500-WH				
Lutron	Nova	NT-2000-WH				
Lutron	Fluo	NTF-10				
Lutron	Nova	NTELV-300				
Lutron	Grafik Eye	QSGR-3P ²		1-17		
Lutron	Qoto	Q-600P				
Lutron	RADIO RA	RRD-6NA ²		1-13		
Lutron	Skylark	S-600P				
Lutron	Skylark	SELV-300P				
Lutron	Skylark	SLV-600P			1-12	>12
Lutron	Skylark	SCL153P v2 ²		1-18		
Lutron	Toggler	TG-600P				
Lutron	Credenza	TT-300				
Lutron	Credenza	TTCL-100DH				
Lutron	Power Module	PHPM-WBX				
Lutron	Verti	VT600-B-AL				
Lutron	Verti	VTELV-600M-B				
Lutron	Verti	VTELV-600M-I				

Sensors			
Lutron	Skylark	MSCL-OP153MH	1-18
Lutron	Maestro	MS-OPS2H	1-18
Leviton	Decora	IPS02	
Leviton	Decora	IPS15	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 6/28/2013



Philips LED Lamps
11W A19 Bulb (White)
60W Equivalent



Applicable Philips Part Numbers	
423491(9290002268), 424382(9290002268), 425264(9290002296), 429258(9290002268)	

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2		1-2 ¹	>3
Leviton	Decora	6161			
Leviton	SureSlide	6613		1-13 ¹	
Leviton	SureSlide	6615P		1-4 ¹	>4
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674		1-4 ¹	>4
Leviton	Trimatron	6681			X
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06			X
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU		1-13 ¹	
Lightolier	Vega	V1000VAU		1-11* ¹	
Lightolier	Sunrise	ZP600VA ²		1-2 ¹	>2
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA		1-13 ¹	
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA		1-2 ¹	>2
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W		1-13 ¹	
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W		1-12 ¹	
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W		1-8 ¹	>8
WattStopper	Slide	SD-603-W		1-8 ¹	>8
Lutron	Skylark	CTCL-153P		1-5 ¹	>5
Lutron	Diva	DVCL-153PD		1-13 ¹	
Lutron	Diva	DVCL-153P v2 ²		1-13 ¹	

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P		1-4 ¹	>4
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P		1-6 ¹	
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MAEL-153M v2		1-13 ¹	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-13 ¹	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600		1-13 ¹	
Lutron	Nova	NLV1000		1-13* ¹	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P per zone		1-13* ¹	
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA		1-13* ¹	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-13 ¹	
Lutron	Skylark	SCL153P v2		1-13* ¹	
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors		
Lutron	Skylark	MSCL-OP153MH
Lutron	Maestro	MS-OPS2H
Leviton	Decora	IPS02
Leviton	Decora	IPS15

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 6/28/2013



Philips LED Lamps 13W BR30 AirFlux



Applicable Philips Part Numbers

420554(9290002197), 420281(9290002198), 423798(9290002197), 429282(9290002197)

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-11		
Leviton	SureSlide	6615P	1-5		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-11		
Leviton	Trimatron	6681		1-8	>8
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-11		
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-11		
Lightolier	Vega	V1000VAU	1-16*		
Lightolier	Sunrise	ZP600VA ²	1-11		
Lightolier	Sunrise	ZP600		1-5	>5
Lightolier	Vega	V600			
Lightolier	Onset	OS600			X
Lightolier	Onset	OS600VA	1-11		
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600		1-7	>7
Lightolier	MultiSet	MHP600VA	1-11		
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-11		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P	1-11		
Lutron	Diva	DVCL-153PD		1-11	
Lutron	Diva	DVCL-153P v2 ²	1-11		

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P		1-11	
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P		1-5	
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2 ²		1-11	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600		1-11	
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-11	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²		1-11	
Lutron	Nova	NLV1000 ²		1-16*	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²		1-11*	
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²		1-11	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-11	
Lutron	Skylark	SCL153P v2 ²		1-11 ¹	
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors

Lutron	Skylark	MSCL-OP153MH			
Lutron	Maestro	MS-OPS2H			
Leviton	Decora	IPS02			
Leviton	Decora	IPS15			

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.

All rights reserved. Updated 6/28/2013

PHILIPS

Philips LED Lamps 13W BR30 AirFlux DimTone



Applicable Philips Part Numbers

426445(9290002344)

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2		1-11 ¹	
Leviton	Decora	6161			
Leviton	SureSlide	6613		1-11 ¹	
Leviton	SureSlide	6615P		1-5 ¹	
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674		1-4 ¹	>4
Leviton	Trimatron	6681		1-4 ¹	>4
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ		1-8 ¹	
Leviton	IllumaTech	IPI06		1-7 ¹	>7
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU		1-11 ¹	
Lightolier	Vega	V1000VAU		1-16* ¹	
Lightolier	Sunrise	ZP600VA ²		1-5 ¹	>5
Lightolier	Sunrise	ZP600			X
Lightolier	Vega	V600			
Lightolier	Onset	OS600			X
Lightolier	Onset	OS600VA		1-11 ¹	
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600		1-11 ¹	
Lightolier	MultiSet	MHP600VA		1-6 ¹	>6
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W		1-11 ¹	
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD		1-11 ¹	
Lutron	Diva	DVCL-153P v2 ²		1-11 ¹	

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Diva	DVPDC-203		1-11 ¹	
Lutron	Diva	DV-600P		1-5 ¹	>5
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P		1-5 ¹	
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MAEL-153M v2 ²		1-11 ¹	
Lutron	Maestro	MAELV-600		1-11 ¹	
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-11 ¹	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²		1-11 ¹	
Lutron	Nova	NLV1000 ²		1-16* ¹	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300		1-5 ¹	
Lutron	Grafik Eye	QSGR-3P ²		1-13* ¹	
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²		1-11 ¹	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-11 ¹	
Lutron	Skylark	SCL153P v2 ²		1-11 ¹	
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors

Lutron	Skylark	MSCL-OP153MH			
Lutron	Maestro	MS-OPS2H			
Leviton	Decora	IPS02			
Leviton	Decora	IPS15			

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 6/28/2013

Philips LED Lamps

13W PAR30S and PAR30L AirFlux



Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			X
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-11		
Leviton	SureSlide	6615P	1-5		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-11		
Leviton	Trimatron	6681			X
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-2	>2
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-11		
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA ²	1-11		
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA	1-8		>8
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA	1-11		
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-11		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD		1-11	
Lutron	Diva	DVCL-153P v2 ²	1-11		

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Applicable Philips Part Numbers

9290002304(425371), 9290002306(425397), 9290002302(425355), 9290002303(425363), 9290002305(425389), 9290002284(423442), 9290002286(423459), 9290002285(423467), 9290002287(423475), 9290002301(425348), 9290002300(425330), 9290002233(420471), 9290002234(420497), 9290002235(420505), 9290002244(420802), 9290002201(420315), 9290002323(425298)

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-11		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-5		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2 ²	1-11		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M	1-11		
Lutron	Maestro	MRF2-6ND-120	1-11		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²	1-11		
Lutron	Nova	NLV1000 ²	1-16*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²	1-11*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-11		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-11		
Lutron	Skylark	SCL153P v2 ²	1-11		
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors

Lutron	Skylark	MSCL-OP153MH			
Lutron	Maestro	MS-OPS2H			
Leviton	Decora	IPS02			
Leviton	Decora	IPS15			

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 6/28/2013

Philips LED Lamps 14W BR40 AirFlux



Applicable Philips Part Numbers
9290002199(420562), 9290002199(423756)

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2		1-10	
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-10		
Leviton	SureSlide	6615P			X
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-10		
Leviton	Trimatron	6681	1-10		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-10	
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-10		
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA ²	1-10		
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA	1-10		
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA	1-10		
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-10		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²	1-10		

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-10		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-5		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MAEL-153M v2 ²	1-10		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-10		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²	1-10		
Lutron	Nova	NLV1000 ²	1-10*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²	1-10*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-10		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-10		
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors		
Lutron	Skylark	MSCL-OP153MH
Lutron	Maestro	MS-OPS2H
Leviton	Decora	IPS02
Leviton	Decora	IPS15

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.

All rights reserved. Updated 6/28/2013

PHILIPS

Philips LED Lamps
17W A21 Bulb (Remote Phosphor)
75W Equivalent



Applicable Philips Part Numbers	
17E26A21D(418590), 9290002018(422220)	

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Cooper	REACT	RI061-VW-K2				
Leviton	Decora	6161				
Leviton	SureSlide	6613		1-8 ¹		
Leviton	SureSlide	6615P		1-4 ¹		
Leviton	SureSlide	6631				
Leviton	SureSlide	6633P				
Leviton	SureSlide	6674		1-8 ¹		
Leviton	Trimatron	6681		1-6 ¹	>6	
Leviton	Trimatron	6683				
Leviton	Trimatron	6684				
Leviton	IllumaTech	IPE04-1LZ				
Leviton	IllumaTech	IP106		1-8 ¹		
Leviton	Monet	MNE04-ILW				
Leviton	Monet	MNI06-1				
Lightolier	Vega	V600VAU		1-5 ¹		
Lightolier	Vega	V1000VAU				
Lightolier	Sunrise	ZP600VA ²		1-8 ¹		
Lightolier	Sunrise	ZP600				
Lightolier	Vega	V600				
Lightolier	Onset	OS600				
Lightolier	Onset	OS600VA		1-8 ¹		
Lightolier	Onset	OS1000VA				
Lightolier	Astral Slider	A600				
Lightolier	Astral Slider	AP600				
Lightolier	MultiSet	MHP600VA		1-8 ¹		
Lightolier	Momentum	MP2000VAI				
WattStopper	Micro Decorator	DCD267-W		1-8 ¹		
WattStopper	Architectural	ADMLV-703-W				
WattStopper	Architectural	AD-1103-W				
WattStopper	Paddle	PDMLV-703-W				
WattStopper	Paddle	PD-703-W				
WattStopper	Slide	SDMLV-603-W				
WattStopper	Slide	SD-603-W				
Lutron	Skylark	CTCL-153P		1-8 ¹		
Lutron	Diva	DVCL-153PD		1-4 ¹		
Lutron	Diva	DVCL-153P v2 ²		1-8 ¹		

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Lutron	Diva	DVPDC-203				X
Lutron	Diva	DV-600P		1-8 ¹		
Lutron	Diva	DV-603PG		1-8 ¹		
Lutron	DIVA	DVELV-300P		1-4 ¹		
Lutron	Diva	DVWCL-153PDH				
Lutron	Glyder	GL-600P		1-8 ¹		
Lutron	Maestro	MACL-153M v2 ²		1-8 ¹		
Lutron	Maestro	MAELV-600				
Lutron	Maestro	MALV-600				
Lutron	Maestro	MRF2-600M				
Lutron	Maestro	MRF2-6ND-120		1-8 ¹		
Lutron	Grafik Eye	NGRX-PB				
Lutron	Nova	NLV600 ²		1-8 ¹		
Lutron	Nova	NLV1000 ²		1-14 ¹		
Lutron	Nova	NT-600-W				
Lutron	Nova	NT-1500-WH				
Lutron	Nova	NT-2000-WH				
Lutron	Fluo	NTF-10				
Lutron	Nova	NTELV-300				
Lutron	Grafik Eye	QSGR-3P ²		1-11* ¹		
Lutron	Qoto	Q-600P				
Lutron	RADIO RA	RRD-6NA ²		1-8 ¹		
Lutron	Skylark	S-600P		1-8 ¹		
Lutron	Skylark	SELV-300P		1-8 ¹		
Lutron	Skylark	SLV-600P		1-4 ¹	>4	
Lutron	Skylark	SCL153P v2 ²				
Lutron	Toggle	TG-600P		1-4 ¹	>4	
Lutron	Credenza	TT-300				
Lutron	Credenza	TTCL-100DH				
Lutron	Power Module	PHPM-WBX				
Lutron	Verti	VT600-B-AL				
Lutron	Verti	VTELV-600M-B				
Lutron	Verti	VTELV-600M-I				

Sensors		
Lutron	Skylark	MSCL-OP153MH
Lutron	Maestro	MS-OPS2H
Leviton	Decora	IPS02
Leviton	Decora	IPS15

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 6/28/2013



Philips LED Lamps

18W PAR38 AirFlux



Applicable Philips Part Numbers
9290002309(425421), 9290002311(425447), 9290002307(425405), 9290002308(425413), 9290002310(425439), 9290002236(420513), 9290002237(420521), 9290002245(420885), 9290002246(420893)

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Cooper	REACT	RI061-VW-K2				
Leviton	Decora	6161				
Leviton	SureSlide	6613	1-8			
Leviton	SureSlide	6615P		1-4 ¹		
Leviton	SureSlide	6631				
Leviton	SureSlide	6633P				
Leviton	SureSlide	6674	1-8			
Leviton	Trimatron	6681		1-8 ¹		
Leviton	Trimatron	6683				
Leviton	Trimatron	6684				
Leviton	IllumaTech	IPE04-1LZ				
Leviton	IllumaTech	IPI06	1-8			
Leviton	Monet	MNE04-ILW				
Leviton	Monet	MNI06-1				
Lightolier	Vega	V600VAU	1-8			
Lightolier	Vega	V1000VAU				
Lightolier	Sunrise	ZP600VA ²	1-8			
Lightolier	Sunrise	ZP600				
Lightolier	Vega	V600				
Lightolier	Onset	OS600				
Lightolier	Onset	OS600VA		1-8 ¹		
Lightolier	Onset	OS1000VA				
Lightolier	Astral Slider	A600				
Lightolier	Astral Slider	AP600				
Lightolier	MultiSet	MHP600VA	1-8			
Lightolier	Momentum	MP2000VAI				
WattStopper	Micro Decorator	DCD267-W		1-8 ¹		
WattStopper	Architectural	ADMLV-703-W				
WattStopper	Architectural	AD-1103-W				
WattStopper	Paddle	PDMLV-703-W				
WattStopper	Paddle	PD-703-W				
WattStopper	Slide	SDMLV-603-W				
WattStopper	Slide	SD-603-W				
Lutron	Skylark	CTCL-153P				
Lutron	Diva	DVCL-153PD				
Lutron	Diva	DVCL-153P v2 ²	1-8			

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Lutron	Diva	DVPDC-203				
Lutron	Diva	DV-600P		1-8		
Lutron	Diva	DV-603PG				
Lutron	DIVA	DVELV-300P		1-4		
Lutron	Diva	DVWCL-153PDH				
Lutron	Glyder	GL-600P				
Lutron	Maestro	MACL-153M v2 ²			1-8 ¹	
Lutron	Maestro	MAELV-600				
Lutron	Maestro	MALV-600				
Lutron	Maestro	MRF2-600M				
Lutron	Maestro	MRF2-6ND-120		1-8		
Lutron	Grafik Eye	NGRX-PB				
Lutron	Nova	NLV600 ²				
Lutron	Nova	NLV1000 ²			1-13 ¹	
Lutron	Nova	NT-600-W				
Lutron	Nova	NT-1500-WH				
Lutron	Nova	NT-2000-WH				
Lutron	Fluo	NTF-10				
Lutron	Nova	NTELV-300				
Lutron	Grafik Eye	QSGR-3P ²			1-11 ¹	
Lutron	Qoto	Q-600P				
Lutron	RADIO RA	RRD-6NA ²		1-8		
Lutron	Skylark	S-600P				
Lutron	Skylark	SELV-300P				
Lutron	Skylark	SLV-600P			1-8 ¹	
Lutron	Skylark	SCL153P v2 ²		1-8		
Lutron	Toggler	TG-600P				
Lutron	Credenza	TT-300				
Lutron	Credenza	TTCL-100DH				
Lutron	Power Module	PHPM-WBX				
Lutron	Verti	VT600-B-AL				
Lutron	Verti	VTELV-600M-B				
Lutron	Verti	VTELV-600M-I				

Sensors		
Lutron	Skylark	MSCL-OP153MH
Lutron	Maestro	MS-OPS2H
Leviton	Decora	IPS02
Leviton	Decora	IPS15

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 6/28/2013



Philips LED Lamps

19.5W PAR38 AirFlux



Applicable Philips Part Numbers
9290002316(425496), 9290002317(425504), 9290002291(423350), 9290002312(425454), 9290002314(425470), 9290002252(421214), 9290002253(421222), 9290002313(425462), 9290002315(425488), 9290002251(423426), 9290002321(425272), 9290002322(425280)

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2			X
Leviton	Decora	6161			
Leviton	SureSlide	6613		1-7 ¹	
Leviton	SureSlide	6615P		1-3 ¹	
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674		1-7 ¹	
Leviton	Trimatron	6681		1-7 ¹	
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-7 ¹	
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU	1-7		
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA ²	1-7		
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA	1-7		
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA	1-7		
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W		1-7 ¹	
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W	1-7		
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W	1-7		
WattStopper	Slide	SD-603-W	1-7		
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD		1-7	
Lutron	Diva	DVCL-153P v2 ²		1-7 ¹	

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P		1-7 ¹	
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-3		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MAEL-153M v2 ²		1-7 ¹	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-7 ¹	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²	1-7		
Lutron	Nova	NLV1000 ²	1-12		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²	1-7*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²		1-7 ¹	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-7 ¹	
Lutron	Skylark	SCL153P v2 ²		1-7 ¹	
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors		
Lutron	Skylark	MSCL-OP153MH
Lutron	Maestro	MS-OPS2H
Leviton	Decora	IPS02
Leviton	Decora	IPS15

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 6/28/2013



Philips LED Lamps
22W A21 Bulb
100W Equivalent



Applicable Philips Part Numbers	
9290002290(423525), 9290002290(424432)	

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			X
Leviton	Decora	6161			
Leviton	SureSlide	6613			X
Leviton	SureSlide	6615P			X
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674			X
Leviton	Trimatron	6681			X
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-6 ¹	
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU			X
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA ²		1-6 ¹	
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA		1-6 ¹	
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA		1-6 ¹	
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W		1-6 ¹	
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			X
Lutron	Diva	DVCL-153P v2 ²			X

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker, good dimming range. Possible minor pop-on.
OK	A minor, low % flicker which is hard to find, some limit of dim-range, relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P			X
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P			X
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2 ²		1-6 ¹	
Lutron	Maestro	MAELV-600		1-6 ¹	
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-6 ¹	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²		1-6 ¹	
Lutron	Nova	NLV1000 ²		1-10 ¹	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²		1-8* ¹	
Lutron	Qoto	Q-600P			X
Lutron	RADIO RA	RRD-6NA ²		1-6 ¹	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P		1-6	
Lutron	Skylark	SLV-600P		1-6 ¹	
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors		
Lutron	Skylark	MSCL-OP153MH
Lutron	Maestro	MS-OPS2H
Leviton	Decora	IPS02
Leviton	Decora	IPS15

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2013 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 6/28/2013



Philips LED Lamps
10.5W SlimStyle A19 Bulb
60W Equivalent



Applicable Philips Part Numbers
 9290002709(433235), 9290002709(433151), 9290002707(433227),
 9290002707(433144)

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-14		
Leviton	SureSlide	6615P		1-5	
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-14		
Leviton	Trimatron	6681		1-14	
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-14		
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU			
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA ²			
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA			
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA			
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-14		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²		1-14	

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P		1-14	
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P		1-5	
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2 ²		1-14	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-14	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²		1-14*	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²		1-14*	
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²		1-14	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-8	
Lutron	Skylark	SCL153P v2 ²		1-14	
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors			
Lutron	Skylark	MSCL-OP153MH	
Lutron	Maestro	MS-OPS2H	
Leviton	Decora	IPS02	
Leviton	Decora	IPS15	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 2/26/14



Philips LED Lamps
8W SlimStyle A19 Bulb
40W Equivalent



Applicable Philips Part Numbers	
9290002706(433219), 9290002706(433136), 9290002704(433201), 9290002704(433128)	

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-18		
Leviton	SureSlide	6615P	1-8		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633P			
Leviton	SureSlide	6674	1-18		
Leviton	Trimatron	6681	1-18		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-18		
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Lightolier	Vega	V600VAU			
Lightolier	Vega	V1000VAU			
Lightolier	Sunrise	ZP600VA ²			
Lightolier	Sunrise	ZP600			
Lightolier	Vega	V600			
Lightolier	Onset	OS600			
Lightolier	Onset	OS600VA			
Lightolier	Onset	OS1000VA			
Lightolier	Astral Slider	A600			
Lightolier	Astral Slider	AP600			
Lightolier	MultiSet	MHP600VA			
Lightolier	Momentum	MP2000VAI			
WattStopper	Micro Decorator	DCD267-W	1-18		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²		1-18	

² This dimmer has low end trim adjustment that may be used for optimal performance.

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-18		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-8		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			
Lutron	Maestro	MACL-153M v2 ²	1-18		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-18		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²		1-18*	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²	1-18*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-18		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-11		
Lutron	Skylark	SCL153P v2 ²		1-18	
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			

Sensors		
Lutron	Skylark	MSCL-OP153MH
Lutron	Maestro	MS-OPS2H
Leviton	Decora	IPS02
Leviton	Decora	IPS15

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless higher value approved by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 2/26/14



Philips LED Lamps
9.5W Warm Glow BR30
65W Equivalent



Applicable Philips Part Numbers

9290011117(452243), 9290011117(452235), 9290011117(452268), 9290011117(452284)

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-12*		
Leviton	SureSlide	6615P	1-7		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633			
Leviton	SureSlide	6672			
Leviton	SureSlide	6674	1-12*		
Leviton	Trimatron	6602			
Leviton	Trimatron	6681	1-12*		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-6		
Leviton	IllumaTech	IPM10			
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120			
Philips	Sunrise	SR150LED120	1-12*		
WattStopper	Micro Decorator	DCD267-W	1-12*		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²		1-15	
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-12*		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-7		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²	1-12*		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-12*		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-12*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²	1-12*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²		1-12*	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-7		
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)			1-15

Sensors

Lutron	Maestro	MSCL-OP153MH	1-12*		
Lutron	Maestro	MS-OPS2H	1-12*		
Leviton	Decora	IPS02	1-12*		
Leviton	Decora	IPS15	1-12*		

Panel Modules

Lutron	Panel Module	GP (Harrier) Card	1-27		
Lutron	Panel Module	HW/LP-RPM-4U-120	1 - 38		

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.

All rights reserved. Updated 11/5/14



Philips LED Lamps
9.5W SlimStyle BR30
65W Equivalent



Applicable Philips Part Numbers	
9290011118(452359), 9290011118(452383), 9290011118(452391), 9290011118(452417), 9290011119(452441), 9290011119(452466), 9290011119(452482)	

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-8*		
Leviton	SureSlide	6615P	1-5		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633			
Leviton	SureSlide	6672	1-8*		
Leviton	SureSlide	6674	1-8*		
Leviton	Trimatron	6602			
Leviton	Trimatron	6681		1-8*	
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-8*		
Leviton	IllumaTech	IPM10			
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120			
Philips	Sunrise	SR150LED120	1-8*		
WattStopper	Micro Decorator	DCD267-W	1-8*		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²			X
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P		1-8*	
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-5		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²	1-8*		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-8*		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-8*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²			X
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-15		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-7		
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)		1-15	

Sensors			
Lutron	Maestro	MSCL-OP153MH	1-8*
Lutron	Maestro	MS-OPS2H	1-8*
Leviton	Decora	IPS02	1-8*
Leviton	Decora	IPS15	1-8*

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	1-26
Lutron	Panel Module	HW/LP-RPM-4U-120	1 - 38

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 11/5/14



Philips LED Lamps

12W PAR30S AF SO



Applicable Philips Part Numbers

92900112304 (435271), 92900112204 (435263), 92900112904 (435339),
92900112804 (435321), 92900112604 (435305), 92900112504 (435297),

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-8*		
Leviton	SureSlide	6615P		1-4	
Leviton	SureSlide	6631			
Leviton	SureSlide	6633	1-8*		
Leviton	SureSlide	6672		1-8*	
Leviton	SureSlide	6674	1-8*		
Leviton	Trimatron	6602		1-12	
Leviton	Trimatron	6681	1-12		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-8*	
Leviton	IllumaTech	IPM10			
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120	1-8*		
Philips	Sunrise	SR150LED120	1-8*		
WattStopper	Micro Decorator	DCD267-W	1-2	3-12	
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²			X
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-12		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-4		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²		1-12	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-8*		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-8*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²			X
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-8*		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-8*		
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)		1-12	

Sensors

Lutron	Maestro	MSCL-OP153MH	1-8*		
Lutron	Maestro	MS-OPS2H	1-8*		
Leviton	Decora	IPS02	1-8*		
Leviton	Decora	IPS15	1-8*		

Panel Modules

Lutron	Panel Module	GP (Harrier) Card			
Lutron	Panel Module	HW/LP-RPM-4U-120			

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.

All rights reserved. Updated 11/21/14

Philips LED Lamps

17W PAR38 AF SO



Applicable Philips Part Numbers

929001113104 (435354), 929001113204 (435362), 929001113404 (435388), 929001113504 (435396), 929001113704 (435412), 929001113804 (435420),

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-8*		
Leviton	SureSlide	6615P	1-4		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633	1-8*		
Leviton	SureSlide	6672	1-8*		
Leviton	SureSlide	6674			
Leviton	Trimatron	6602	1-8*		
Leviton	Trimatron	6681	1-8*		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-8*	
Leviton	IllumaTech	IPM10			
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120	1-8*		
Philips	Sunrise	SR150LED120	1-8*		
WattStopper	Micro Decorator	DCD267-W	1-8*		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²			X
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-8*		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P		1-4	
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²		1-8*	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-8*		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-8*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²	1-8*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²			
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-5*		
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)		1-8*	

Sensors

Lutron	Maestro	MSCL-OP153MH	1-8*
Lutron	Maestro	MS-OPS2H	1-8*
Leviton	Decora	IPS02	1-8*
Leviton	Decora	IPS15	1-8*

Panel Modules

Lutron	Panel Module	GP (Harrier) Card	1-8*
Lutron	Panel Module	HW/LP-RPM-4U-120	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.

All rights reserved. Updated 11/21/14

Philips LED Lamps

15W PAR38 ULW DIM



Applicable Philips Part Numbers	
929001111104 (453431)	

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-8*		
Leviton	SureSlide	6615P	1-4*		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633	1-8*		
Leviton	SureSlide	6672	1-8*		
Leviton	SureSlide	6674	1-8*		
Leviton	Trimatron	6602	1-8*		
Leviton	Trimatron	6681	1-8*		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-8*		
Leviton	IllumaTech	IPM10	1-8*		
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120			
Philips	Sunrise	SR150LED120	1-8*		
WattStopper	Micro Decorator	DCD267-W	1-8*		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²	1-10		
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-8*		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-4*		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²	1-8*		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-8*		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-8*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²	1-8*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-10		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-8*		
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)	1-10		

Sensors			
Lutron	Maestro	MSCL-OP153MH	1-10
Lutron	Maestro	MS-OPS2H	1-10*
Leviton	Decora	IPS02	1-10*
Leviton	Decora	IPS15	1-10*

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	1-21
Lutron	Panel Module	HW/LP-RPM-4U-120	1-30

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 11/21/14



Philips LED Lamps
6W A19 5000K
40W Equivalent



Applicable Philips Part Numbers	
9290011348(455808), 9290011348(455782), 9290011178(453209), 9290011178(453274), 9290011178(454058), 9290011348(455790)	

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-12*		
Leviton	SureSlide	6615P	1-12*		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633	1-12*		
Leviton	SureSlide	6672	1-12*		
Leviton	SureSlide	6674	1-12*		
Leviton	Trimatron	6602	1-12*		
Leviton	Trimatron	6681	1-12*		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-12*		
Leviton	IllumaTech	IPM10		1-12*	
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120	1-12*		
Philips	Sunrise	SR150LED120	1-12*		
WattStopper	Micro Decorator	DCD267-W	1-12*		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²		1-12*	
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-12*		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-12*		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²		1-12*	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-12*		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-12*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²	1-12*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-12*		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-12*		
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)		1-12*	

Sensors			
Lutron	Maestro	MSCL-OP153MH	1-12*
Lutron	Maestro	MS-OPS2H	1-12*
Leviton	Decora	IPS02	1-12*
Leviton	Decora	IPS15	1-12*

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	
Lutron	Panel Module	HW/LP-RPM-4U-120	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2015 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 1/30/15



Philips LED Lamps
6.5W Warm Glow A19
40W Equivalent



Applicable Philips Part Numbers
 9290011347(455774), 9290011347(455766), 9290011347(455741),
 9290011176(453316), 9290011176(453183)

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-23		
Leviton	SureSlide	6615P		1-7*	
Leviton	SureSlide	6631			
Leviton	SureSlide	6633	1-23		
Leviton	SureSlide	6672	1-23		
Leviton	SureSlide	6674	1-23		
Leviton	Trimatron	6602	1-23		
Leviton	Trimatron	6681	1-23		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-23		
Leviton	IllumaTech	IPM10	2-23		1
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120	2-23		1
Philips	Sunrise	SR150LED120	1-23		
WattStopper	Micro Decorator	DCD267-W		1-23	
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²			X
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-23		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-7*		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²		1-23	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-23		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-23*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²	1-23*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-23		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-10*		
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)	1-23		

Sensors			
Lutron	Maestro	MSCL-OP153MH	1-23
Lutron	Maestro	MS-OPS2H	1-23
Leviton	Decora	IPS02	1-23
Leviton	Decora	IPS15	1-23

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	
Lutron	Panel Module	HW/LP-RPM-4U-120	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2015 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 1/30/15



Philips LED Lamps

9.5W Warm Glow A19

60W Equivalent



Applicable Philips Part Numbers	
9290011175(453258), 9290011175(453324), 9290011345(455865), 9290011345(455857), 9290011345(455840), 9290011345(455831), 9290011345(455832), 9290011345(455816), 9290011175(453225), 9290011345(455824)	

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-15		
Leviton	SureSlide	6615P	1-8		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633		1-15	
Leviton	SureSlide	6672	1-15		
Leviton	SureSlide	6674	1-15		
Leviton	Trimatron	6602		1-15	
Leviton	Trimatron	6681	1-15		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-15		
Leviton	IllumaTech	IPM10	1-15		
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120	1-15		
Philips	Sunrise	SR150LED120	1-15		
WattStopper	Micro Decorator	DCD267-W	1-15		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²		1-15	
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-15		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-8		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²		1-15	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-15	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²		1-15*	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²		1-15*	
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²		1-15	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-15	
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)		1-15	

Sensors			
Lutron	Maestro	MSCL-OP153MH	1-15
Lutron	Maestro	MS-OPS2H	1-15
Leviton	Decora	IPS02	1-15
Leviton	Decora	IPS15	1-15

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	1-19
Lutron	Panel Module	HW/LP-RPM-4U-120	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2015 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 1/30/15



Philips LED Lamps
9W A19 5000K
60W Equivalent



Applicable Philips Part Numbers
 9290011346(455881), 9290011346(455907), 9290011346(455899),
 9290011346(455873), 9290011177(453282), 9290011177(453241),
 9290011177(454041)

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-15		
Leviton	SureSlide	6615P	1-8		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633	1-15		
Leviton	SureSlide	6672	1-15		
Leviton	SureSlide	6674	1-15		
Leviton	Trimatron	6602	1-15		
Leviton	Trimatron	6681	1-15		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-15		
Leviton	IllumaTech	IPM10	1-15		
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120	1-15		
Philips	Sunrise	SR150LED120	1-15		
WattStopper	Micro Decorator	DCD267-W	1-15		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²		1-15	
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-15		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P		1-8	
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²		1-15	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-15		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-15*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²		1-15*	
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-15		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-15		
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)		1-15	

Sensors			
Lutron	Maestro	MSCL-OP153MH	1-15
Lutron	Maestro	MS-OPS2H	1-15
Leviton	Decora	IPS02	1-15
Leviton	Decora	IPS15	1-15

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	
Lutron	Panel Module	HW/LP-RPM-4U-120	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2015 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 1/30/15



Philips LED Lamps

12W BR40 AirFlux



Applicable Philips Part Numbers	
929000258083(451914)	

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-10*		
Leviton	SureSlide	6615P	1-5*		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633			
Leviton	SureSlide	6672			
Leviton	SureSlide	6674	1-10*		
Leviton	Trimatron	6602			
Leviton	Trimatron	6681	1-5*		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-10*		
Leviton	IllumaTech	IPM10			
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120			
Philips	Sunrise	SR150LED120	1-10*		
WattStopper	Micro Decorator	DCD267-W	1-10*		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²	1-12		
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-10*		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-5*		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²	1-12		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-10*		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-13*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²	1-18*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-10*		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-8*		
Lutron	Skylark	SCL153P v2 ²	1-12		
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)	1-12		

Sensors			
Lutron	Maestro	MSCL-OP153MH	1-12
Lutron	Maestro	MS-OPS2H	1-12*
Leviton	Decora	IPS02	1-12*
Leviton	Decora	IPS15	1-12*

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	1-18
Lutron	Panel Module	HW/LP-RPM-4U-120	1-25

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2015 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 1/30/15



Philips LED Lamps
15W A21 Bulb
75W Equivalent



Applicable Philips Part Numbers	
9290002595A(453159), 9290002595A(451898)	

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-8*		
Leviton	SureSlide	6615P	1-4*		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633			
Leviton	SureSlide	6672			
Leviton	SureSlide	6674			X
Leviton	Trimatron	6602			
Leviton	Trimatron	6681	1-8*		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-8*	
Leviton	IllumaTech	IPM10			
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120			
Philips	Sunrise	SR150LED120			X
WattStopper	Micro Decorator	DCD267-W	1-8*		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²			X
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-8*		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-4*		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²		1-8*	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-8*		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-8*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²			X
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-8*		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-6*		
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)			

Sensors		
Lutron	Maestro	MSCL-OP153MH
Lutron	Maestro	MS-OPS2H
Leviton	Decora	IPS02
Leviton	Decora	IPS15

Panel Modules		
Lutron	Panel Module	GP (Harrier) Card
Lutron	Panel Module	HW/LP-RPM-4U-120

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2015 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 1/30/15



Philips LED Lamps
19W A21 Bulb
100W Equivalent



Applicable Philips Part Numbers
9290002596A(451906)

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-6*		
Leviton	SureSlide	6615P		1-3	
Leviton	SureSlide	6631			
Leviton	SureSlide	6633			
Leviton	SureSlide	6672			
Leviton	SureSlide	6674			X
Leviton	Trimatron	6602			
Leviton	Trimatron	6681	1-6*		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06			X
Leviton	IllumaTech	IPM10			
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120			
Philips	Sunrise	SR150LED120			X
WattStopper	Micro Decorator	DCD267-W	1-6*		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²		1-7	
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-6*		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-3*		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²		1-6*	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-6*	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²		1-6*	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²			X
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²		1-7	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-4*	
Lutron	Skylark	SCL153P v2 ²		1-7	
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)			

Sensors			
Lutron	Maestro	MSCL-OP153MH	1-7
Lutron	Maestro	MS-OPS2H	
Leviton	Decora	IPS02	
Leviton	Decora	IPS15	

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	1-12
Lutron	Panel Module	HW/LP-RPM-4U-120	1-17

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2015 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 1/30/15



Philips LED Lamps
13W SlimStyle A21 Bulb
75W Equivalent



Applicable Philips Part Numbers
 9290011120(452771), 9290011120(452805), 9290011120(452789),
 9290011120(452755), 9290011120(452748), 9290011120(452730)

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-13		
Leviton	SureSlide	6615P		1-8	
Leviton	SureSlide	6631			
Leviton	SureSlide	6633			
Leviton	SureSlide	6672			
Leviton	SureSlide	6674	1-13		
Leviton	Trimatron	6602			
Leviton	Trimatron	6681	1-13		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-13		
Leviton	IllumaTech	IPM10			
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120			
Philips	Sunrise	SR150LED120	1-13		
WattStopper	Micro Decorator	DCD267-W	1-13		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²			X
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-13		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-7		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²	1-13		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-13		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-13*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²			X
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-13		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-10		
Lutron	Skylark	SCL153P v2 ²			X
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)			

Sensors			
Lutron	Maestro	MSCL-OP153MH	1-13
Lutron	Maestro	MS-OPS2H	1-13*
Leviton	Decora	IPS02	1-13*
Leviton	Decora	IPS15	1-13*

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	
Lutron	Panel Module	HW/LP-RPM-4U-120	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2015 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 1/30/15



Philips LED Lamps

13W PAR38 SO GEN2



Applicable Philips Part Numbers
 9290011322(454751), 9290011321(454744), 9290011320(454736),
 9290011319(454728)

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Cooper	REACT	RI061-VW-K2				
Leviton	Decora	6161				
Leviton	SureSlide	6613		1-8*		
Leviton	SureSlide	6615P			1-5*	
Leviton	SureSlide	6631				
Leviton	SureSlide	6633		1-8*		
Leviton	SureSlide	6672		1-8*		
Leviton	SureSlide	6674		1-8*		
Leviton	Trimatron	6602		1-8*		
Leviton	Trimatron	6681		1-8*		
Leviton	Trimatron	6683				
Leviton	Trimatron	6684				
Leviton	IllumaTech	IPE04-1LZ				
Leviton	IllumaTech	IPI06		1-8*		
Leviton	IllumaTech	IPM10			1-8*	
Leviton	Monet	MNE04-ILW				
Leviton	Monet	MNI06-1				
Philips	Sunrise	SR400RPC120				
Philips	Sunrise	SR1000VA120			1-8*	
Philips	Sunrise	SR150LED120		1-8*		
WattStopper	Micro Decorator	DCD267-W		1-8*		
WattStopper	Architectural	ADMLV-703-W				
WattStopper	Architectural	AD-1103-W				
WattStopper	Paddle	PDMLV-703-W				
WattStopper	Paddle	PD-703-W				
WattStopper	Slide	SDMLV-603-W				
WattStopper	Slide	SD-603-W				
Lutron	Skylark	CTCL-153P				
Lutron	Diva	DVCL-153PD				
Lutron	Diva	DVCL-153P v2 ²			1-8*	
Lutron	Diva	DVPDC-203				
Lutron	Diva	DV-600P		1-8*		
Lutron	Diva	DV-603PG				
Lutron	DIVA	DVELV-300P		1-5*		
Lutron	Diva	DVWCL-153PDH				
Lutron	Glyder	GL-600P				

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Lutron	Maestro	MAELV-600			1-8*	
Lutron	Maestro	MAELV-600				
Lutron	Maestro	MALV-600				
Lutron	Maestro	MRF2-600M				
Lutron	Maestro	MRF2-6ND-120		1-8*		
Lutron	Grafik Eye	NGRX-PB				
Lutron	Nova	NLV600 ²				
Lutron	Nova	NLV1000 ²		1-8*		
Lutron	Nova	NT-600-W				
Lutron	Nova	NT-1500-WH				
Lutron	Nova	NT-2000-WH				
Lutron	Fluo	NTF-10				
Lutron	Nova	NTELV-300				
Lutron	Grafik Eye	QSGR-3P ²				X
Lutron	Qoto	Q-600P				
Lutron	RADIO RA	RRD-6NA ²		1-8*		
Lutron	Skylark	S-600P				
Lutron	Skylark	SELV-300P				
Lutron	Skylark	SLV-600P				X
Lutron	Skylark	SCL153P v2 ²				
Lutron	Toggle	TG-600P				
Lutron	Credenza	TT-300				
Lutron	Credenza	TTCL-100DH				
Lutron	Power Module	PHPM-WBX				
Lutron	Verti	VT600-B-AL				
Lutron	Verti	VTELV-600M-B				
Lutron	Verti	VTELV-600M-I				
Lutron	Caseta	PD-6WCL (SD11)			1-8*	

Sensors			
Lutron	Maestro	MSCL-OP153MH	1-8*
Lutron	Maestro	MS-OPS2H	1-8*
Leviton	Decora	IPS02	1-8*
Leviton	Decora	IPS15	1-8*

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	
Lutron	Panel Module	HW/LP-RPM-4U-120	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 6/11/2015



Philips LED Lamps

10.5W PAR30L AF



Applicable Philips Part Numbers
 9290011114(452656), 9290011114(452623), 9290011114(434992),
 9290011114(452615), 9290011113(434984)

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	2-7*		1
Leviton	SureSlide	6615P		1-6*	
Leviton	SureSlide	6631			
Leviton	SureSlide	6633			
Leviton	SureSlide	6672			
Leviton	SureSlide	6674	1-7*		
Leviton	Trimatron	6602			
Leviton	Trimatron	6681	1-7*		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-7*	
Leviton	IllumaTech	IPM10			
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120			
Philips	Sunrise	SR150LED120	1-7*		
WattStopper	Micro Decorator	DCD267-W	1-7*		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²			X
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-7*		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-6*		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²	1-7*		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-7*		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-7*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²	1-7*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-7*		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-7*		
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)			

Sensors		
Lutron	Maestro	MSCL-OP153MH
Lutron	Maestro	MS-OPS2H
Leviton	Decora	IPS02
Leviton	Decora	IPS15

Panel Modules		
Lutron	Panel Module	GP (Harrier) Card
Lutron	Panel Module	HW/LP-RPM-4U-120

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 6/1/2015



Philips LED Lamps

11W PAR30L AF



Applicable Philips Part Numbers
9290002551(432930)

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Cooper	REACT	RI061-VW-K2				
Leviton	Decora	6161	1-8*			
Leviton	SureSlide	6613	1-9*			
Leviton	SureSlide	6615P	1-5*			
Leviton	SureSlide	6631	1-4*			
Leviton	SureSlide	6633				X
Leviton	SureSlide	6672				
Leviton	SureSlide	6674	1-9*			
Leviton	Trimatron	6602				
Leviton	Trimatron	6681	1-7*			
Leviton	Trimatron	6683				
Leviton	Trimatron	6684	1-3*			
Leviton	IllumaTech	IPE04-1LZ				
Leviton	IllumaTech	IPI06	1-9*			
Leviton	IllumaTech	IPM10				
Leviton	Monet	MNE04-ILW				
Leviton	Monet	MNI06-1				
Philips	Sunrise	SR400RPC120				
Philips	Sunrise	SR1000VA120				
Philips	Sunrise	SR150LED120	1-9*			
WattStopper	Micro Decorator	DCD267-W	1-9*			
WattStopper	Architectural	ADMLV-703-W				
WattStopper	Architectural	AD-1103-W				
WattStopper	Paddle	PDMLV-703-W				
WattStopper	Paddle	PD-703-W				
WattStopper	Slide	SDMLV-603-W				
WattStopper	Slide	SD-603-W				
Lutron	Skylark	CTCL-153P				
Lutron	Diva	DVCL-153PD				
Lutron	Diva	DVCL-153P v2 ²	1-8*			
Lutron	Diva	DVPDC-203				
Lutron	Diva	DV-600P	1-9*			
Lutron	Diva	DV-603PG				
Lutron	DIVA	DVELV-300P	1-5*			
Lutron	Diva	DVWCL-153PDH				
Lutron	Glyder	GL-600P	1-8*			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²	1-9*			
Lutron	Maestro	MAELV-600	1-9*			
Lutron	Maestro	MALV-600				
Lutron	Maestro	MRF2-600M				
Lutron	Maestro	MRF2-6ND-120	1-9*			
Lutron	Grafik Eye	NGRX-PB				
Lutron	Nova	NLV600 ²				
Lutron	Nova	NLV1000 ²	1-11*			
Lutron	Nova	NT-600-W				
Lutron	Nova	NT-1500-WH				
Lutron	Nova	NT-2000-WH				
Lutron	Fluo	NTF-10				
Lutron	Nova	NTELV-300				
Lutron	Grafik Eye	QSGR-3P ²	1-15*			
Lutron	Qoto	Q-600P	1-9*			
Lutron	RADIO RA	RRD-6NA ²	1-9*			
Lutron	Skylark	S-600P	1-9*			
Lutron	Skylark	SELV-300P				
Lutron	Skylark	SLV-600P				
Lutron	Skylark	SCL153P v2 ²	1-7*			
Lutron	Toggle	TG-600P	1-9*			
Lutron	Credenza	TT-300	1-5*			
Lutron	Credenza	TTCL-100DH	1-4*			
Lutron	Power Module	PHPM-WBX				
Lutron	Verti	VT600-B-AL				
Lutron	Verti	VTELV-600M-B				
Lutron	Verti	VTELV-600M-I				
Lutron	Caseta	PD-6WCL (SD11)				

Sensors			
Lutron	Maestro	MSCL-OP153MH	
Lutron	Maestro	MS-OPS2H	
Leviton	Decora	IPS02	
Leviton	Decora	IPS15	

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	
Lutron	Panel Module	HW/LP-RPM-4U-120	

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 6/11/2015



Philips LED Lamps

5W PAR20 AF



Applicable Philips Part Numbers	
9290011105(454256), 9290011105(434976)	

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-12*		
Leviton	SureSlide	6615P		1-12*	
Leviton	SureSlide	6631			
Leviton	SureSlide	6633			
Leviton	SureSlide	6672			
Leviton	SureSlide	6674		1-12*	
Leviton	Trimatron	6602			
Leviton	Trimatron	6681	1-12*		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06			X
Leviton	IllumaTech	IPM10			
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120			
Philips	Sunrise	SR150LED120		1-12*	
WattStopper	Micro Decorator	DCD267-W	1-12*		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²			X
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P		1-12*	
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-12*		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²		1-12*	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-12*	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²		1-12*	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²			X
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²		1-12*	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-12*	
Lutron	Skylark	SCL153P v2 ²			X
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)			

Sensors		
Lutron	Maestro	MSCL-OP153MH
Lutron	Maestro	MS-OPS2H
Leviton	Decora	IPS02
Leviton	Decora	IPS15

Panel Modules		
Lutron	Panel Module	GP (Harrier) Card
Lutron	Panel Module	HW/LP-RPM-4U-120

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
All rights reserved. Updated 6/11/2015



Philips LED Lamps

6W PAR20 AF



Applicable Philips Part Numbers

9290011448(458919), 9290011452(456111), 9290011451(456103), 9290011450(456095), 9290011449(456087), 9290011448(456079), 9290011447(456061), 9290011446(456053), 9290011445(456046), 9290011487(456269)

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-20		
Leviton	SureSlide	6615P	1-10		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633	1-20		
Leviton	SureSlide	6672	1-20		
Leviton	SureSlide	6674	1-20		
Leviton	Trimatron	6602	1-20		
Leviton	Trimatron	6681	1-20		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-20		
Leviton	IllumaTech	IPM10			X
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120			X
Philips	Sunrise	SR150LED120	1-20		
WattStopper	Micro Decorator	DCD267-W	1-20		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²			X
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-20		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-10		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²		1-20	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120			X
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-20*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²	1-20*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-20		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-20		
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)			X

Sensors

Lutron	Maestro	MSCL-OP153MH	1-20
Lutron	Maestro	MS-OPS2H	1-20*
Leviton	Decora	IPS02	1-20*
Leviton	Decora	IPS15	1-20*

Panel Modules

Lutron	Panel Module	GP (Harrier) Card	1-20*
Lutron	Panel Module	HW/LP-RPM-4U-120	1-20*

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.

All rights reserved. Updated 10/8/2015

Philips LED Lamps

12.5W PAR30L SO AF



Applicable Philips Part Numbers

9290011328(454710), 9290011327(454702), 9290011326(454694),
9290011325(454686), 9290011324(454678), 9290011323(454660)

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-8*		
Leviton	SureSlide	6615P	1-5*		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633		1-8*	
Leviton	SureSlide	6672	1-8*		
Leviton	SureSlide	6674	1-8*		
Leviton	Trimatron	6602	1-8*		
Leviton	Trimatron	6681	1-8*		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-8*		
Leviton	IllumaTech	IPM10	1-8*		
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120	1-8*		
Philips	Sunrise	SR150LED120	1-8*		
WattStopper	Micro Decorator	DCD267-W	1-8*		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153PD			
Lutron	Diva	DVCL-153P v2 ²	1-8*		
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-8*		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-5*		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²	1-8*		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-8*		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-8*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²		1-8*	
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-8*		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-8*		
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)	1-8*		

Sensors

Lutron	Maestro	MSCL-OP153MH	1-8*		
Lutron	Maestro	MS-OPS2H	1-8*		
Leviton	Decora	IPS02	1-8*		
Leviton	Decora	IPS15	1-8*		

Panel Modules

Lutron	Panel Module	GP (Harrier) Card			
Lutron	Panel Module	HW/LP-RPM-4U-120			

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.

All rights reserved. Updated 10/8/2015

Philips LED Lamps
4.5W GU10
with warm glow effect



Applicable Philips Part Numbers	
9290011565(457267), 9290011565(457648), 9290011565(457655)	

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Cooper	REACT	RI061-VW-K2				
Leviton	Decora	6161				
Leviton	SureSlide	6613	1-20*			
Leviton	SureSlide	6615P	1-20*			
Leviton	SureSlide	6631				
Leviton	SureSlide	6633	1-20*			
Leviton	SureSlide	6672	1-20*			
Leviton	SureSlide	6674	1-20*			
Leviton	Trimatron	6602	1-20*			
Leviton	Trimatron	6681	1-20*			
Leviton	Trimatron	6683				
Leviton	Trimatron	6684				
Leviton	IllumaTech	IPE04-1LZ				
Leviton	IllumaTech	IPI06	1-20*			
Leviton	IllumaTech	IPM10				
Leviton	Monet	MNE04-ILW				
Leviton	Monet	MNI06-1				
Philips	Sunrise	SR400RPC120				
Philips	Sunrise	SR1000VA120		1-20*		
Philips	Sunrise	SR150LED120	1-20*			
WattStopper	Micro Decorator	DCD267-W	1-20*			
WattStopper	Architectural	ADMLV-703-W				
WattStopper	Architectural	AD-1103-W				
WattStopper	Paddle	PDMLV-703-W				
WattStopper	Paddle	PD-703-W				
WattStopper	Slide	SDMLV-603-W				
WattStopper	Slide	SD-603-W				
Lutron	Skylark	CTCL-153P				
Lutron	Diva	DVCL-153PD				
Lutron	Diva	DVCL-153P v2 ²				X
Lutron	Diva	DVPDC-203				
Lutron	Diva	DV-600P	1-20*			
Lutron	Diva	DV-603PG				
Lutron	DIVA	DVELV-300P	1-20*			
Lutron	Diva	DVWCL-153PDH				
Lutron	Glyder	GL-600P				

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²				X
Lutron	Maestro	MAELV-600				
Lutron	Maestro	MALV-600				
Lutron	Maestro	MRF2-600M				
Lutron	Maestro	MRF2-6ND-120				X
Lutron	Grafik Eye	NGRX-PB				
Lutron	Nova	NLV600 ²				
Lutron	Nova	NLV1000 ²	1-20*			
Lutron	Nova	NT-600-W				
Lutron	Nova	NT-1500-WH				
Lutron	Nova	NT-2000-WH				
Lutron	Fluo	NTF-10				
Lutron	Nova	NTELV-300				
Lutron	Grafik Eye	QSGR-3P ²	1-20*			
Lutron	Qoto	Q-600P				
Lutron	RADIO RA	RRD-6NA ²	1-20*			
Lutron	Skylark	S-600P				
Lutron	Skylark	SELV-300P				
Lutron	Skylark	SLV-600P	1-20*			
Lutron	Skylark	SCL153P v2 ²				
Lutron	Toggle	TG-600P				
Lutron	Credenza	TT-300				
Lutron	Credenza	TTCL-100DH				
Lutron	Power Module	PHPM-WBX				
Lutron	Verti	VT600-B-AL				
Lutron	Verti	VTELV-600M-B				
Lutron	Verti	VTELV-600M-I				
Lutron	Caseta	PD-6WCL (SD11)			1-20*	

Sensors			
Lutron	Maestro	MSCL-OP153MH	1-20*
Lutron	Maestro	MS-OPS2H	1-20*
Leviton	Decora	IPS02	1-20*
Leviton	Decora	IPS15	1-20*

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	1-20*
Lutron	Panel Module	HW/LP-RPM-4U-120	1-20*

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 10/8/2015



Philips LED Lamps
6W R20 (50W Equivalent)
with warm glow effect



Applicable Philips Part Numbers
 9290011557(456979), 9290011557(456995), 9290011557(456987)

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613		1-25	
Leviton	SureSlide	6615P	1-12		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633		1-25	
Leviton	SureSlide	6672	1-25		
Leviton	SureSlide	6674		1-25	
Leviton	Trimatron	6602	1-25		
Leviton	Trimatron	6681	1-25		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-25		
Leviton	IllumaTech	IPM10		2-25	1
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120		2-25	1
Philips	Sunrise	SR150LED120		1-25	
WattStopper	Micro Decorator	DCD267-W		2-25	1
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153P v2 ²			X
Lutron	Diva	DVCL-153P v2.1 ²		1-25	
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P		1-25	
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-12		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer			Use With Up to # of Bulbs		
Brand	Model	Part #	Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²		1-25	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-25	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-25*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²		1-15	16-25
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²		1-25	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-15	
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)		1-15	16-25

Sensors					
Lutron	Maestro	MSCL-OP153MH		1-15	16-25
Lutron	Maestro	MS-OPS2H		1-25	
Leviton	Decora	IPS02		1-25	
Leviton	Decora	IPS15		1-25	

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	1-25*
Lutron	Panel Module	HW/LP-RPM-4U-120	1-25*

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 10/13/2015



Philips LED Lamps
9W BR30 (65W Equivalent)
with warm glow effect



Applicable Philips Part Numbers	
9290011555(457044), 9290011555(457051), 9290011555(457036), 9290011555(457077), 9290011555(457069)	

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Cooper	REACT	RI061-VW-K2				
Leviton	Decora	6161				
Leviton	SureSlide	6613			1-16	
Leviton	SureSlide	6615P		1-8		
Leviton	SureSlide	6631				
Leviton	SureSlide	6633			1-16	
Leviton	SureSlide	6672		1-16		
Leviton	SureSlide	6674			1-16	
Leviton	Trimatron	6602		1-16		
Leviton	Trimatron	6681		1-16		
Leviton	Trimatron	6683				
Leviton	Trimatron	6684				
Leviton	IllumaTech	IPE04-1LZ				
Leviton	IllumaTech	IPI06		1-16		
Leviton	IllumaTech	IPM10			1-16	
Leviton	Monet	MNE04-ILW				
Leviton	Monet	MNI06-1				
Philips	Sunrise	SR400RPC120				
Philips	Sunrise	SR1000VA120			1-16	
Philips	Sunrise	SR150LED120			1-16	
WattStopper	Micro Decorator	DCD267-W			1-16	
WattStopper	Architectural	ADMLV-703-W				
WattStopper	Architectural	AD-1103-W				
WattStopper	Paddle	PDMLV-703-W				
WattStopper	Paddle	PD-703-W				
WattStopper	Slide	SDMLV-603-W				
WattStopper	Slide	SD-603-W				
Lutron	Skylark	CTCL-153P				
Lutron	Diva	DVCL-153P v2 ²				X
Lutron	Diva	DVCL-153P v2.1 ²		1-16		
Lutron	Diva	DVPDC-203				
Lutron	Diva	DV-600P		1-16		
Lutron	Diva	DV-603PG				
Lutron	DIVA	DVELV-300P		1-8		
Lutron	Diva	DVWCL-153PDH				
Lutron	Glyder	GL-600P				

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²			1-16	
Lutron	Maestro	MAELV-600				
Lutron	Maestro	MALV-600				
Lutron	Maestro	MRF2-600M				
Lutron	Maestro	MRF2-6ND-120			1-16	
Lutron	Grafik Eye	NGRX-PB				
Lutron	Nova	NLV600 ²				
Lutron	Nova	NLV1000 ²		1-16*		
Lutron	Nova	NT-600-W				
Lutron	Nova	NT-1500-WH				
Lutron	Nova	NT-2000-WH				
Lutron	Fluo	NTF-10				
Lutron	Nova	NTELV-300				
Lutron	Grafik Eye	QSGR-3P ²			1-16*	
Lutron	Qoto	Q-600P				
Lutron	RADIO RA	RRD-6NA ²			1-16	
Lutron	Skylark	S-600P				
Lutron	Skylark	SELV-300P				
Lutron	Skylark	SLV-600P			1-12	
Lutron	Skylark	SCL153P v2 ²				
Lutron	Toggler	TG-600P				
Lutron	Credenza	TT-300				
Lutron	Credenza	TTCL-100DH				
Lutron	Power Module	PHPM-WBX				
Lutron	Verti	VT600-B-AL				
Lutron	Verti	VTELV-600M-B				
Lutron	Verti	VTELV-600M-I				
Lutron	Caseta	PD-6WCL (SD11)			1-16	

Sensors			
Lutron	Maestro	MSCL-OP153MH	1-16
Lutron	Maestro	MS-OPS2H	1-16
Leviton	Decora	IPS02	1-16
Leviton	Decora	IPS15	1-16

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	1-16*
Lutron	Panel Module	HW/LP-RPM-4U-120	1-16*

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 10/13/2015



Philips LED Lamps
9W BR40 (65W Equivalent)
with warm glow effect



Applicable Philips Part Numbers	
9290011558(457010), 9290011558(457002), 9290011558(457028)	

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Cooper	REACT	RI061-VW-K2				
Leviton	Decora	6161				
Leviton	SureSlide	6613			1-16	
Leviton	SureSlide	6615P		1-8		
Leviton	SureSlide	6631				
Leviton	SureSlide	6633			1-16	
Leviton	SureSlide	6672		1-16		
Leviton	SureSlide	6674			1-16	
Leviton	Trimatron	6602		1-16		
Leviton	Trimatron	6681		1-16		
Leviton	Trimatron	6683				
Leviton	Trimatron	6684				
Leviton	IllumaTech	IPE04-1LZ				
Leviton	IllumaTech	IPI06		1-16		
Leviton	IllumaTech	IPM10			1-16	
Leviton	Monet	MNE04-ILW				
Leviton	Monet	MNI06-1				
Philips	Sunrise	SR400RPC120				
Philips	Sunrise	SR1000VA120			1-16	
Philips	Sunrise	SR150LED120			1-16	
WattStopper	Micro Decorator	DCD267-W			1-16	
WattStopper	Architectural	ADMLV-703-W				
WattStopper	Architectural	AD-1103-W				
WattStopper	Paddle	PDMLV-703-W				
WattStopper	Paddle	PD-703-W				
WattStopper	Slide	SDMLV-603-W				
WattStopper	Slide	SD-603-W				
Lutron	Skylark	CTCL-153P				
Lutron	Diva	DVCL-153P v2 ²				X
Lutron	Diva	DVCL-153P v2.1 ²		1-16		
Lutron	Diva	DVPDC-203				
Lutron	Diva	DV-600P		1-16		
Lutron	Diva	DV-603PG				
Lutron	DIVA	DVELV-300P		1-8		
Lutron	Diva	DVWCL-153PDH				
Lutron	Glyder	GL-600P				

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²			1-16	
Lutron	Maestro	MAELV-600				
Lutron	Maestro	MALV-600				
Lutron	Maestro	MRF2-600M				
Lutron	Maestro	MRF2-6ND-120			1-16	
Lutron	Grafik Eye	NGRX-PB				
Lutron	Nova	NLV600 ²				
Lutron	Nova	NLV1000 ²		1-16*		
Lutron	Nova	NT-600-W				
Lutron	Nova	NT-1500-WH				
Lutron	Nova	NT-2000-WH				
Lutron	Fluo	NTF-10				
Lutron	Nova	NTELV-300				
Lutron	Grafik Eye	QSGR-3P ²			1-16*	
Lutron	Qoto	Q-600P				
Lutron	RADIO RA	RRD-6NA ²			1-16	
Lutron	Skylark	S-600P				
Lutron	Skylark	SELV-300P				
Lutron	Skylark	SLV-600P			1-12	
Lutron	Skylark	SCL153P v2 ²				
Lutron	Toggler	TG-600P				
Lutron	Credenza	TT-300				
Lutron	Credenza	TTCL-100DH				
Lutron	Power Module	PHPM-WBX				
Lutron	Verti	VT600-B-AL				
Lutron	Verti	VTELV-600M-B				
Lutron	Verti	VTELV-600M-I				
Lutron	Caseta	PD-6WCL (SD11)			1-16	

Sensors			
Lutron	Maestro	MSCL-OP153MH	1-16
Lutron	Maestro	MS-OPS2H	1-16
Leviton	Decora	IPS02	1-16
Leviton	Decora	IPS15	1-16

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	1-16*
Lutron	Panel Module	HW/LP-RPM-4U-120	1-16*

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 10/13/2015



Philips LED Lamps
7W Clear Classic Bulb (40W Equivalent)
with warm glow effect



Applicable Philips Part Numbers	
9290011817(458802), 9290011817(458794), 9290011818(458760), 9290011815(458737), 9290011817(458810), 9290011818(458786), 9290011815(458752), 9290011818(458778), 9290011815(458745)	

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613		1-21	
Leviton	SureSlide	6615P	1-11		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633		1-21	
Leviton	SureSlide	6672	1-21		
Leviton	SureSlide	6674	1-21		
Leviton	Trimatron	6602	1-21		
Leviton	Trimatron	6681		1-21	
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06	1-21		
Leviton	IllumaTech	IPM10	2-21		1
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120	2-21		1
Philips	Sunrise	SR150LED120	1-21		
WattStopper	Micro Decorator	DCD267-W	2-21		1
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153P v2 ²			X
Lutron	Diva	DVCL-153P v2.1 ²	1-15	16-21	
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-21		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-11		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²	1-21		
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-15	16-21	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-21*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²	1-21*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²			X
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P	1-16		
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggler	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)	1-21		

Sensors			
Lutron	Maestro	MSCL-OP153MH	1-21
Lutron	Maestro	MS-OPS2H	1-21
Leviton	Decora	IPS02	1-21
Leviton	Decora	IPS15	1-21

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	1-21*
Lutron	Panel Module	HW/LP-RPM-4U-120	1-21*

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 10/13/2015



Philips LED Lamps
10W Clear Classic Bulb (60W Equivalent)
with warm glow effect



Applicable Philips Part Numbers	
9290011898(459347), 9290011898(459339), 9290011816(458828), 9290011898(459354), 9290011816(458844), 9290011816(458836)	

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613		1-15	
Leviton	SureSlide	6615P	1-8		
Leviton	SureSlide	6631			
Leviton	SureSlide	6633		1-15	
Leviton	SureSlide	6672	1-15		
Leviton	SureSlide	6674	1-15		
Leviton	Trimatron	6602	9-15	1-8	
Leviton	Trimatron	6681		1-15	
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-15	
Leviton	IllumaTech	IPM10		2-15	1
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120		2-15	1
Philips	Sunrise	SR150LED120	1-15		
WattStopper	Micro Decorator	DCD267-W		1-15	
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153P v2 ²			X
Lutron	Diva	DVCL-153P v2.1 ²	1-15		
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P		1-15	
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-8		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²		1-15	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120		1-15	
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²		1-15*	
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²		1-15*	
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²		1-15	
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-11	
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)		1-15	

Sensors				
Lutron	Maestro	MSCL-OP153MH	11-15	1-10
Lutron	Maestro	MS-OPS2H	1-15	
Leviton	Decora	IPS02	1-15	
Leviton	Decora	IPS15	1-15	

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	1-15*
Lutron	Panel Module	HW/LP-RPM-4U-120	1-15*

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 10/13/2015



Philips LED Lamps
14W A21 Bulb (75W Equivalent)
with warm glow effect



Applicable Philips Part Numbers	
9290011839(459065), 9290011839(459073), 9290011839(459081), 9290011839(459099)	

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613	1-11		
Leviton	SureSlide	6615P		1-5	
Leviton	SureSlide	6631			
Leviton	SureSlide	6633	1-11		
Leviton	SureSlide	6672		1-11	
Leviton	SureSlide	6674	1-11		
Leviton	Trimatron	6602		1-11	
Leviton	Trimatron	6681	1-11		
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-11	
Leviton	IllumaTech	IPM10	1-11		
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120	1-11		
Philips	Sunrise	SR150LED120	1-11		
WattStopper	Micro Decorator	DCD267-W	1-11		
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153P v2 ²			X
Lutron	Diva	DVCL-153P v2.1 ²	1-11		
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-11		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P	1-5		
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²		1-11	
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120	1-11		
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-11*		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²	1-11*		
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²	1-11		
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-11	
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)		1-11	

Sensors				
Lutron	Maestro	MSCL-OP153MH	11*	1-10
Lutron	Maestro	MS-OPS2H	1-11*	
Leviton	Decora	IPS02	1-11*	
Leviton	Decora	IPS15	1-11*	

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	1-23
Lutron	Panel Module	HW/LP-RPM-4U-120	1-23

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 1/25/2016



Philips LED Lamps
18W A21 Bulb (100W Equivalent)
with warm glow effect



Applicable Philips Part Numbers	
9290011741(459107), 9290011741(459115), 9290011741(459123), 9290011741(459131)	

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Cooper	REACT	RI061-VW-K2				
Leviton	Decora	6161				
Leviton	SureSlide	6613	1-8			
Leviton	SureSlide	6615P		1-8		
Leviton	SureSlide	6631				
Leviton	SureSlide	6633	1-8			
Leviton	SureSlide	6672			1-8	
Leviton	SureSlide	6674				1-8
Leviton	Trimatron	6602				1-8
Leviton	Trimatron	6681	1-8			
Leviton	Trimatron	6683				
Leviton	Trimatron	6684				
Leviton	IllumaTech	IPE04-1LZ				
Leviton	IllumaTech	IPI06			1-8	
Leviton	IllumaTech	IPM10			1-8	
Leviton	Monet	MNE04-ILW				
Leviton	Monet	MNI06-1				
Philips	Sunrise	SR400RPC120				
Philips	Sunrise	SR1000VA120			1-8	
Philips	Sunrise	SR150LED120			1-8	
WattStopper	Micro Decorator	DCD267-W			1-8	
WattStopper	Architectural	ADMLV-703-W				
WattStopper	Architectural	AD-1103-W				
WattStopper	Paddle	PDMLV-703-W				
WattStopper	Paddle	PD-703-W				
WattStopper	Slide	SDMLV-603-W				
WattStopper	Slide	SD-603-W				
Lutron	Skylark	CTCL-153P				
Lutron	Diva	DVCL-153P v2 ²				X
Lutron	Diva	DVCL-153P v2.1 ²		1-8		
Lutron	Diva	DVPDC-203				
Lutron	Diva	DV-600P	1-8			
Lutron	Diva	DV-603PG				
Lutron	DIVA	DVELV-300P	1-8			
Lutron	Diva	DVWCL-153PDH				
Lutron	Glyder	GL-600P				

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer	Brand	Model	Part #	Use With Up to # of Bulbs		
				Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²			1-8	
Lutron	Maestro	MAELV-600				
Lutron	Maestro	MALV-600				
Lutron	Maestro	MRF2-600M				
Lutron	Maestro	MRF2-6ND-120			1-8	
Lutron	Grafik Eye	NGRX-PB				
Lutron	Nova	NLV600 ²				
Lutron	Nova	NLV1000 ²			1-8*	
Lutron	Nova	NT-600-W				
Lutron	Nova	NT-1500-WH				
Lutron	Nova	NT-2000-WH				
Lutron	Fluo	NTF-10				
Lutron	Nova	NTELV-300				
Lutron	Grafik Eye	QSGR-3P ²				1-8*
Lutron	Qoto	Q-600P				
Lutron	RADIO RA	RRD-6NA ²			1-8	
Lutron	Skylark	S-600P				
Lutron	Skylark	SELV-300P				
Lutron	Skylark	SLV-600P			1-8	
Lutron	Skylark	SCL153P v2 ²				
Lutron	Toggler	TG-600P				
Lutron	Credenza	TT-300				
Lutron	Credenza	TTCL-100DH				
Lutron	Power Module	PHPM-WBX				
Lutron	Verti	VT600-B-AL				
Lutron	Verti	VTELV-600M-B				
Lutron	Verti	VTELV-600M-I				
Lutron	Caseta	PD-6WCL (SD11)			1-8	

Sensors			
Lutron	Maestro	MSCL-OP153MH	1-8*
Lutron	Maestro	MS-OPS2H	1-8*
Leviton	Decora	IPS02	1-8*
Leviton	Decora	IPS15	1-8*

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	1-22
Lutron	Panel Module	HW/LP-RPM-4U-120	1-22

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 1/25/2016



Philips LED Lamps

12W UL Wet PAR38 SO



Applicable Philips Part Numbers
 9290011834(460055), 9290011834(460105), 9290011834(460071),
 9290011835(460089), 9290011835(461046), 9290011835(460097)

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Cooper	REACT	RI061-VW-K2			
Leviton	Decora	6161			
Leviton	SureSlide	6613			X
Leviton	SureSlide	6615P		1-7	
Leviton	SureSlide	6631			
Leviton	SureSlide	6633			X
Leviton	SureSlide	6672		1-14	
Leviton	SureSlide	6674			
Leviton	Trimatron	6602		1-14	
Leviton	Trimatron	6681			X
Leviton	Trimatron	6683			
Leviton	Trimatron	6684			
Leviton	IllumaTech	IPE04-1LZ			
Leviton	IllumaTech	IPI06		1-14	
Leviton	IllumaTech	IPM10		1-15	
Leviton	Monet	MNE04-ILW			
Leviton	Monet	MNI06-1			
Philips	Sunrise	SR400RPC120			
Philips	Sunrise	SR1000VA120			
Philips	Sunrise	SR150LED120			X
WattStopper	Micro Decorator	DCD267-W			X
WattStopper	Architectural	ADMLV-703-W			
WattStopper	Architectural	AD-1103-W			
WattStopper	Paddle	PDMLV-703-W			
WattStopper	Paddle	PD-703-W			
WattStopper	Slide	SDMLV-603-W			
WattStopper	Slide	SD-603-W			
Lutron	Skylark	CTCL-153P			
Lutron	Diva	DVCL-153P v2 ²			
Lutron	Diva	DVCL-153P v2.1 ²			X
Lutron	Diva	DVPDC-203			
Lutron	Diva	DV-600P	1-14		
Lutron	Diva	DV-603PG			
Lutron	DIVA	DVELV-300P		1-7	
Lutron	Diva	DVWCL-153PDH			
Lutron	Glyder	GL-600P			

¹Audible noise may be observed with this dimmer, depending on the application

²This dimmer has low end trim adjustment that may be used for optimal performance

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
TBD	Lamp not yet tested with this dimmer, compatibility unknown.

Dimmer Brand	Model	Part #	Use With Up to # of Bulbs		
			Best	OK	NR
Lutron	Maestro	MACL-153M v2 ²			X
Lutron	Maestro	MAELV-600			
Lutron	Maestro	MALV-600			
Lutron	Maestro	MRF2-600M			
Lutron	Maestro	MRF2-6ND-120			X
Lutron	Grafik Eye	NGRX-PB			
Lutron	Nova	NLV600 ²			
Lutron	Nova	NLV1000 ²	1-15		
Lutron	Nova	NT-600-W			
Lutron	Nova	NT-1500-WH			
Lutron	Nova	NT-2000-WH			
Lutron	Fluo	NTF-10			
Lutron	Nova	NTELV-300			
Lutron	Grafik Eye	QSGR-3P ²			X
Lutron	Qoto	Q-600P			
Lutron	RADIO RA	RRD-6NA ²			X
Lutron	Skylark	S-600P			
Lutron	Skylark	SELV-300P			
Lutron	Skylark	SLV-600P		1-10	
Lutron	Skylark	SCL153P v2 ²			
Lutron	Toggle	TG-600P			
Lutron	Credenza	TT-300			
Lutron	Credenza	TTCL-100DH			
Lutron	Power Module	PHPM-WBX			
Lutron	Verti	VT600-B-AL			
Lutron	Verti	VTELV-600M-B			
Lutron	Verti	VTELV-600M-I			
Lutron	Caseta	PD-6WCL (SD11)			X

Sensors			
Lutron	Maestro	MSCL-OP153MH	X
Lutron	Maestro	MS-OPS2H	1-15
Leviton	Decora	IPS02	1-15
Leviton	Decora	IPS15	1-15

Panel Modules			
Lutron	Panel Module	GP (Harrier) Card	1-15
Lutron	Panel Module	HW/LP-RPM-4U-120	1-15

Note: Lamp load is limited to 25% of dimmer's incandescent rating unless other value approved or lower value recommended by dimmer manufacturer.

*Dimmer tested only to the quantity of lamps indicated. May work similarly with additional lamps.

© 2014 Philips Lighting Company, A Division of Philips Electronics North America Corporation.
 All rights reserved. Updated 1/25/2016

