

**PHILIPS**

LED

Recessed downlight



---

## Beautiful light in an attractive fixture

Easily convert your standard 4" or 5/6" recessed cans into a high-quality, energy-efficient LED flood light. This Energy Star certified recessed retrofit downlight features a medium based socket adapter for easy installation. The Philips LED downlight has a white trim that provides a clean look and a bright white light, making it ideal for general lighting. This elegant, dimmable LED retrofit downlight is suitable for both wet and dry locations and is an ideal choice to upgrade the aesthetics of offices, conference rooms, reception and, lobby areas.

# Philips LED Recessed downlight

## Easy to experience

- Broad beam and soft light creates a beautiful atmosphere in any location
- UL Wet design suitable for both indoor and outdoor applications
- Installs in seconds - Medium based socket adapter makes installation quick and easy

## Superior Performance

- ENERGY STAR® Qualified
- 65W Energy Star equivalent 5"/6" performance<sup>1</sup>
- 50W Energy Star equivalent 4" performance<sup>1</sup>
- UL Listed
- Dimmable to 10%



## Ordering, Electrical and Technical Data (Subject to change without notice)

Product No.	Description	Model No.	Watts <sup>3</sup> (W)	Volts	Base	CRI	Color Temp. (K)	Dim	Lumens	LED Lifetime <sup>2</sup>	Energy Star Equiv. Watts <sup>1</sup> (W)
<b>LED Recessed downlight</b>											
80000-3	HATTON US 4 Soft white recessed LED	59221/XX/YY	8.5	120	E26	90	2700	Y	520	50000	50
80002-9	HATTON US 4 day light recessed LED white	59220/XX/YY	8.5	120	E26	83	5000	Y	680	50000	50
80003-7	HATTON US 5/6 soft white recessed LED	59222/XX/YY	10.0	120	E26	90	2700	Y	610	50000	65
80006-0	HATTON US Recessed 5/6 inch 5000K e26 us	59223/XX/YY	10.0	120	E26	83	5000	Y	800	50000	65

## Shipping Data (Subject to change without notice)

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Volume (cu. Ft.)	Pallet Qty	SKUs per layer	Layers High	SKU Dimensions (L x W x H) (In.)	Case Dimensions (L x W x H) (In.)	Pallet Dimensions (L x W x H) (In.)
<b>LED Recessed downlight</b>											
80000-3	800000	800005	4	3.03	0.743	240	40	6	5 x 6.7 x 6.9	21.6 x 7.6 x 7.9	48 x 40 x 52.2
80002-9	800024	800029	4	3.03	0.743	240	40	6	5 x 6.7 x 6.9	21.6 x 7.6 x 7.9	48 x 40 x 52.2
80003-7	800031	800142	4	3.03	1.064	180	36	5	5 x 8.2 x 8.3	21.6 x 9.1 x 9.4	48 x 40 x 52
80006-0	800062	800067	4	3.03	1.064	180	36	5	5 x 8.2 x 8.3	21.6 x 9.1 x 9.4	48 x 40 x 52

1. All Philips LED Lamp equivalencies for light output are based upon the ENERGY STAR® guidelines as detailed in the ENERGY STAR Lamps V1.1 September 2014 specification.

2. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50,L70).

■ This lamp is ENERGY STAR® Certified.

## Notes

These lamps comply with Part 15 of the FCC Rules. Operation is subject to the following two conditions:  
 (1) this device may not cause harmful interference, and  
 (2) this device must accept any interference received, including interference that may cause undesired operation. This Class B digital apparatus complies with Canadian ICES-003.



© 2016 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting North America Corporation  
 200 Franklin Square Drive, Somerset, NJ 08873  
 Tel. 855-486-2216

Philips Lighting Canada Ltd.  
 281 Hillmount Rd, Markham, ON, Canada L6C 2S3  
 Tel. 800-668-9008