



Philips Energy Saver  
Universal Compact  
Fluorescent Lamps

*Ideal for use in table and  
floor lamps, outdoor post  
lights, wall sconces, surface  
mount, reading lamps,  
recessed and hanging fixtures*

EnergySaver



## Energy saving universal lamps

**Philips Energy Saver Universal Compact Fluorescent Lamps**  
provide energy savings and reduced operating costs.

### **Energy savings**

- 25W saves up to \$123 in energy costs as compared to a 100W incandescent lamp\*

### **Long life**

- Lasts up to 15,000 hours\*\*

### **Energy saving replacement for incandescent bulbs**

- Provides warm, white light
- Can be used in enclosed fixtures

# PHILIPS

\*, \*\* See back page for footnotes

# Philips EnergySaver Universal Compact Fluorescent Lamps

## Ordering, Electrical and Technical Data (Subject to change without notice)

Product Number	Ordering Code	Nom. Watts	Volts	Lamps per SKU	Lamp Type	Lamp Base	Rated Avg. Life (Hrs.) <sup>1</sup>	Approx. Lumens <sup>2</sup>	CRI	Color Temp	MOL (In.)	Mercury Max
I4691-0	SLS Universal 14W	14	120	1	Universal	Medium	12,000	860	82	2700	5	2.6
I3077-3	SLS Universal 20W	20	120	1	Universal	Medium	15,000	1200	82	2700	5 5/8	2.6
I3574-9	SLS Universal 25W	25	120	1	Universal	Medium	15,000	1750	82	2700	6 1/5	2.6

## Shipping Data

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. ft.)	Pallet Qty.	SKUs Per Layer	Layers High	SKU Dimensions (W x D x H) (In.)	Case Dimensions (W x D x H) (In.)	Pallet Dimensions (W x D x H) (In.)
I4691-0	I4691-7	I4691-2	6	2.5	0.119	2,016	336	6	2.2 x 2.2 x 5.3	4.8 x 7.1 x 6.0	38.5 x 42.4 x 42.0
I3077-3	I3077-0	I3077-5	6	2	0.137	2,016	336	6	2.2 x 2.2 x 6.0	5.0 x 7.0 x 6.8	38.5 x 49.4 x 40.5
I3574-9	I3574-4	I3574-9	6	2	0.144	2,016	336	6	2.2 x 2.2 x 6.5	4.8 x 7.1 x 7.3	38.5 x 49.4 x 43.5

1) Rated average life is the length of operation (in hours) at which point an average of 50% of the lamps will still be operational and 50% will not.

2) Approximate lumen output at 40% of lamp rated average

■ ENERGY STAR® Qualified.

Footnotes from front:

\* At \$0.11 kWh, this 25-Watt Energy Saver bulb rated at 1750 lumens uses \$41.25 of electricity over its 15000 hour life. This is a \$123.75 savings when compared to the \$165 required to run a 100-watt incandescent bulb rated at 1600 lumens over the same period. Actual savings will vary depending on cost per kWh in your area.

\*\* Based on 3 hours average usage per day/7 days per week.

### WARNINGS AND CAUTIONS:

Do not use with dimmers. Some electronic timer and photosensor switches contain dimming circuitry, so before using such a switch, check with its manufacturer to ensure compatibility with electronic CFL bulbs. Do not use with emergency exit fixtures or lights. Outdoor use requires weather-protected fixture. Do not use where directly exposed to water. Before replacing, turn off power and let lamp cool to avoid electrical shock or burn. This device complies with Part 18 of the FCC Rules. Not for use in totally enclosed recessed fixtures. Reliable operating temperature range -4°F/-20°C to 140°F/60°C.

**Note:** This product may cause interference with radios, televisions, telephones, or remote controls. If interference occurs, move this product away from device or plug into another outlet.



© 2012 Philips Lighting Company, a division of  
Philips Electronics North America Company.  
All rights reserved.  
Printed in USA 10/12  
P-3754-E  
www.philips.com

Philips Lighting Company  
200 Franklin Square Drive  
Somerset, NJ 08873  
1-800-555-0050

Philips Lighting  
281 Hillmount Road  
Markham, Ontario  
Canada L6C 2S3  
1-800-555-0050  
A Division of Philips Electronics Ltd.