



Philips Energy Saver Soft
White Plus Compact
Fluorescent Lamps

*Ideal for use in table and
floor lamps, wall sconces,
open ceiling fixtures and
ceiling fans*

ENERGY SAVER



Energy saver soft white lamps

Philips Energy Saver Soft White Plus Compact Fluorescent Lamps provide inviting energy saving light and reduced operating costs.

Energy savings

- 20W saves up to \$48 in energy costs as compared to an 75W incandescent lamp*

Long life

- Lasts 8,000 hours**

Energy saving replacement for incandescent bulbs

- Provides warm, white light
- Fits into incandescent fixtures
- Shape and size similar to an incandescent A19

*, ** See back page for footnotes

PHILIPS

Philips Energy Saver Soft White Plus Compact Fluorescent Lamps

Ordering, Electrical and Technical Data (Subject to change without notice)

Product Number	Ordering Code	Nom. Watts	Volts	Lamps per SKU	Lamp Type	Lamp Base	Rated Avg. Life (Hrs.) ¹	Approx. Lumens ²	CRI	Color Temp	MOL (In.)	Mercury Max
41747-7	EL/A FAN 5W	5	120	1	A-Shape	Medium	8000	215	82	2700	3 4/5	3.0
41736-0	EL/A SWP 9W	9	120	1	A-Shape	Medium	8000	450	82	2700	4 2/7	2.0
41737-8	EL/A SWP 14W	14	120	1	A-Shape	Medium	8000	800	82	2700	4 2/5	2.0
20080-8	EL/A SWP 20W	20	120	1	A-Shape	Medium	8000	1100	82	2700	5 3/5	2.0

Shipping Data

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. ft.)	Pallet Qty.	SKUs Per Layer	Layers High	SKU Dimensions (W x D x H) (In.)	Case Dimensions (W x D x H) (In.)	Pallet Dimensions (W x D x H) (In.)
41747-7	41747-5	41747-0	6	0.67	0.13	2,256	282	8	2.3 x 2.3 x 4.8	5.2 x 7.6 x 5.4	38.5 x 48.6 x 43.6
41736-0	41736-9	41736-4	6	1.54	0.18	1,080	180	6	2.3 x 2.3 x 4.7	6.5 x 8.9 x 5.4	39.4 x 47.2 x 38.5
41737-8	41737-6	41737-1	6	0.86	0.18	1,554	222	7	2.6 x 2.6 x 5.4	5.9 x 8.5 x 6.1	40.0 x 46.9 x 43.0
20080-8	20080-0	20080-5	6	2.32	0.26	840	168	5	3.1 x 3.1 x 5.9	6.7 x 9.8 x 6.9	39.4 x 47.2 x 40.4

1) Rated average life is the length of operation (in hours) at which point an average of 50% of the lamps will still be operational and 50% will not.

2) Approximate lumen output at 40% of lamp rated average

■ ENERGY STAR® Qualified.

Footnotes from front:

*At \$ 0.11 kWh, this 20-Watt Energy Saver bulb rated at 1100 lumens uses \$17.60 of electricity over its 8000 hour life. This is a \$48.40 savings when compared to the \$66 required to run a 75-watt incandescent bulb rated at 1100 lumens over the same period. Actual savings will vary depending on cost per kWh in your area.

** Based on 3 hours average usage per day/7 days per week.

WARNINGS AND CAUTIONS:

Do not use with dimmers. Some electronic timer and photosensor switches contain dimming circuitry, so before using such a switch, check with its manufacturer to ensure compatibility with electronic CFL bulbs. Do not use with emergency exit fixtures or lights. Outdoor use requires weather-protected fixture. Do not use where directly exposed to water. Before replacing, turn off power and let lamp cool to avoid electrical shock or burn. This device complies with Part 18 of the FCC Rules. Not for use in totally enclosed recessed fixtures. Reliable operating temperature range -4°F/-20°C to 140°F/60°C.

Note: This product may cause interference with radios, televisions, telephones, or remote controls. If interference occurs, move this product away from device or plug into another outlet.



© 2012 Philips Lighting Company, a division of Philips Electronics North America Company.

All rights reserved.
Printed in USA 10/12

P-5777-C

www.philips.com

Philips Lighting Company
200 Franklin Square Drive
Somerset, NJ 08873

1-800-555-0050

A Division of Philips Electronics North America Corporation

Philips Lighting
281 Hillmount Road
Markham, Ontario
Canada L6C 2S3
1-800-555-0050

A Division of Philips Electronics Ltd.