

**PHILIPS**

Compact Fluorescent

Energy Saver GU24



---

# Energy savings and reduced operating costs.

## Energy saving

- 23W saves up to \$84 in energy costs as compared to a 100W incandescent lamp\*

## Long life

- Long life\*\*

## Energy saving replacement for incandescent bulbs

- Features a twist and lock connection with 2 pins for quick and easy replacement
- Available in warm white and cool white
- Easy retrofit for most GU24 fixtures or luminaires

See back page for footnotes.



# Philips Energy Saver GU24 Twister Compact Fluorescent Lamp

## Ordering, Electrical and Technical Data (Subject to change without notice)

Product No.	Ordering Code	Nom. Watts	Volts	Lamps per SKU	Lamp Type	Lamp Base	Rated Avg. Life (Hrs.) <sup>2</sup>	Approx. Lumens <sup>3</sup>	CRI	Color temp. (K)	MOL (in.)	Mercury Max
41138-9 <sup>1</sup>	EL/mdT 13W GU24 4100K	13	120	1	Twister	GU24	10,000	900	82	4100	3.6	2
41177-7 <sup>1</sup>	EL/mdT 18W GU24	18	120	1	Twister	GU24	10,000	1250	82	2700	4	2
41725-3 <sup>1</sup>	EL/mdT 23W GU24	23	120	1	Twister	GU24	10,000	1600	82	2700	4	2
41139-7 <sup>1</sup>	EL/mdT 23W GU24 4100K	23	120	1	Twister	GU24	10,000	1600	82	4100	4	2
45419-9	EL/mdTQS 13W GU24	13	120	1	Twister	GU24	10,000	900	82	2700	4	2
45416-5	EL/mdTQS 13W GU24 4100K	13	120	1	Twister	GU24	10,000	900	82	4100	4	2
45420-7	EL/mdTQS 18W GU24	18	120	1	Twister	GU24	10,000	1250	82	2700	4	2
45417-3	EL/mdTQS 18W GU24 4100K	18	120	1	Twister	GU24	10,000	1250	82	4100	4	2
45421-5	EL/mdTQS 23W GU24	23	120	1	Twister	GU24	10,000	1600	82	2700	4	2
45418-1	EL/mdTQS 23W GU24 4100K	23	120	1	Twister	GU24	10,000	1600	82	4100	4	2

## Shipping Data (Subject to change without notice)

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. ft.)	Pallet Qty.	SKU per Layer	Layers High	SKU Dimensions (W x D x H) (in.)	Case Dimensions (W x D x H) (in.)	Pallet Dimensions (W x D x H) (in.)
41138-9	41138-1	41138-6	6	1.27	0.09	2,226	318	7	2.2 x 2.2 x 4.3	4.8 x 6.9 x 4.8	39.4 x 47.2 x 39.1
41177-7	41177-0	41177-5	6	1.46	0.135	1,638	234	6	2.6 x 2.6 x 4.5	5.6 x 8.3 x 5.0	47.2 x 39.4 x 41.0
41725-3	41725-3	41725-8	6	1.46	1.679	1,404	234	6	2.6 x 2.6 x 4.9	5.6 x 8.3 x 5.5	47.2 x 39.4 x 39.5
41139-7	41139-8	41139-3	6	1.46	1.679	1,404	234	6	2.6 x 2.6 x 4.9	5.6 x 8.3 x 5.5	47.2 x 39.4 x 39.5
45419-9	45419-7	45419-2	6	1.27	0.09	2,226	318	7	2.2 x 2.2 x 4.3	4.8 x 6.9 x 4.8	39.4 x 47.2 x 39.1
45416-5	45416-6	45416-1	6	1.27	0.09	2,226	318	7	2.2 x 2.2 x 4.3	4.8 x 6.9 x 4.8	39.4 x 47.2 x 39.1
45420-7	45420-3	45420-8	6	1.46	0.135	1,638	234	6	2.6 x 2.6 x 4.5	5.6 x 8.3 x 5.0	47.2 x 39.4 x 41.0
45417-3	45417-3	45417-8	6	1.46	0.135	1,638	234	6	2.6 x 2.6 x 4.5	5.6 x 8.3 x 5.0	47.2 x 39.4 x 41.0
45421-5	45421-0	45421-5	6	1.46	1.679	1,404	234	6	2.6 x 2.6 x 4.9	5.6 x 8.3 x 5.5	47.2 x 39.4 x 39.5
45418-1	45418-0	45418-5	6	1.46	1.679	1,404	234	6	2.6 x 2.6 x 4.9	5.6 x 8.3 x 5.5	47.2 x 39.4 x 39.5

### WARNINGS AND CAUTIONS:

Do not use with dimmers. Some electronic timer and photosensor switches contain dimming circuitry, so before using such a switch, check with its manufacturer to ensure compatibility with electronic CFL bulbs. Do not use with emergency exit fixtures or lights. Outdoor use requires weather-protected fixture. Do not use where directly exposed to water. Before replacing, turn off power and let lamp cool to avoid electrical shock or burn. This device complies with Part 18 of the FCC Rules. Not for use in totally enclosed recessed fixtures. Reliable operating temperature range -4°F/-20°C to 140°F/60°C.

**Note:** This product may cause interference with radios, televisions, telephones, or remote controls. If interference occurs, move this product away from device or plug into another outlet.

1. Transitioning to the new QS (Quasi full Spiral).
2. Rated average life is the length of operation (in hours) at which point an average of 50% of the lamps will still be operational and 50% will not.
3. Approximate lumen output at 40% of lamp rated average

■ ENERGY STAR® Qualified.

Footnotes from front:

\* At \$ 0.11 kWh, this 23-Watt Energy Saver bulb rated at 1600 lumens uses \$25.30 of electricity over its 10,000 hour life. This is a \$84.70 savings when compared to the \$110 required to run a 100-watt incandescent bulb rated at 1600 lumens over the same period. Actual savings will vary depending on cost per kWh in your area.

\*\* Based on 3 hours average usage per day/7 days per week.

© 2015 Koninklijke Philips N.V. All rights reserved.  
Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting North America Corporation  
200 Franklin Square Drive, Somerset, NJ 08873  
Tel. 855-486-2216

Imported by: Philips Lighting,  
A division of Philips Electronics Ltd.  
281 Hillmount Rd, Markham, ON, Canada L6C 2S3  
Tel. 800-668-9008