# PHILIPS ADVANCE

### **LED** Driver

### Xitanium

180W 0.1-1.25A 0-10V Dimming with SimpleSet XH180C125V200BSF1








Philips Advance Xitanium outdoor LED drivers with SimpleSet technology are designed to give OEMs ultimate flexibility. With wide operating windows and simple programming, the drivers make it easy for luminaire manufacturers to design luminaires of different sizes and lumen levels for outdoor applications.

### **Specifications**


Input Voltage (Vac)	Output Power (W)	Output Voltage (V)	Output Current (A)	Efficiency@ Max Load and 75°C Case	Max Case Temp. (°C)	Input Current (A)	Max. Input Power (W)	THD @ Max Load (%)	Power Factor @ Max Load	Surge Protection (Combi- Wave, KV)	Envir. Protection Rating
347	347	70-210 0.1 -	0.1 - 1.25	92.3	Life - 85°C	0.56	200 <109	-100/	<10% >0.95	6	UL damp & dry
480	100	70-210	0.1 - 1.25	93.2	UL - 90°C	0.4	200	<10%			and Type HL

### **Enclosure**

	In. (mm)
Case Length (L2)	8.31 (211.0)
Case Width (W)	2.31 (58.0)
Case Height (H)	1.48 (37.6)
Mounting Length (M)	8.91 (226.2)
Overall Length (L1)	9.45 (240.0)
Center of SimpleSet Antenna (L3)	3.75 (95.3)



### **Wiring Diagram**



Dimming	Dimming Range (with specified dimmers)	Minimum Output Current (A)	
0-10V Analog Class 1 and 2 Wiring	10% ~ 100%	0.07	

#### **Features**

- · 50,000+ hour lifetime<sup>1</sup>
- Programmable output current through SimpleSet
- · Large operating window
- 6kV combi-wave surge rating to comply with ANSI C82.77-5 CAT C low

#### **Benefits**

- · Enables long life luminaire designs
- · Fast and simple way of programming
- Enables fixture designs with wide variety of loads and adjustable current options
- No external surge protection required to pass C82.77-5 CAT C low

#### **Application**

- · Area
- · Roadway
- · Parking garages
- Floodlights
- · HIgh-bay

### **Electrical Specifications**

All the specifications are typical and at 25°C Tcase unless specified otherwise.

#### **Product Data**

Order Information					
Full Product Code	XH180C125V200BSF1M (Mid-Pack, 10pcs/Box)				
Line Frequency	50/60Hz				
Min. Mains Voltage Operational	312 Vac				
Max. Mains Voltage Operational	528 Vac				
Output Information					
Maximum Open Circuit Voltage	290Vdc				
Output Current Ripple (ripple = peak to average / average)	15% max @ max lout				
Output Current Tolerance (at maximum output current)	<5%				
Protections	Short Circuit, Open Circuit Protection for LED + and LED – and Temperature Foldback				
Features					
0-10V Dimming	150μA (±3%) source current from driver. See dim curve for detail.				
AOC (Adjustable Output Current)	0.1A-1.25A via SimpleSet (Factory Default at 1.05A)				
Additional SimpleSet Configurable Features	Adjustable Min Dim level, Adjustable Lumen Output, Adjustable Lumen Output Min, OEM Write Protection				
<b>Environment &amp; Approbation</b>					
Operating Ambient Temp. Range	-40°C to +55°C				
Max Case Temperature (Tcase)	90°C				
Agency Approbations	UL 8750, CSA 250.13, UL Listed, ETL Class P				
Electromagnetic Compliance	FCC Title 47 Part 15 Class A				
Audible Noise	<24dB Class A				
Weight	2.1 Lbs / 0.95 kgs				

Philips Advance Xitanium LED Drivers are manufactured to engineering standards correlating to a designed and average life expectancy of 50,000 hours of operation at maximum rated case temperature. Minimum 90% survivals based on MTTF modeling.

### **Electrical Specifications**

All the specifications are typical and at 25°C Tcase unless specified otherwise.


### **0-10V Dimming Curve**

Dimming source current from the driver: 150µA (@ 0<Vdim<8V)

Minimum dim level: 10% of lout setting as default Maximum output voltage on the dimming wires: 12V

### **Approved Dimmer List**


Manufacturer	Manufacturer Part Number		
Lutron	Visit www.lutron.com/ advance for a list of dimmers (Mark VII) that will work with this driver		
Leviton	IllumaTech IP7 series		
Philips	Sunrise - SR1200ZTUNV		



### **Electrical Specifications**

All the specifications are typical and at 25°C Tcase unless specified otherwise.

### **Driver Output Window**




### **Notes**

- 1. Factory default output current is 1.05A.
- 2. To get a 100% to 10% dimming range, the output current setting through AOC should be  $\geq$  700mA.
- 3. Factory default minimum dimming level is 10%. This can be adjusted between 10% and 100% using Philips MultiOne.

### **Electrical Specifications**

All the specifications are typical and at 25°C Tcase unless specified otherwise.


### **Output Current Vs. Driver Case Temperature**



### Note

There is ±5°C tolerance on the driver case temperature.


### **Driver Lifetime Vs. Driver Case Temperature**




#### **Performance Characteristics**

Based on measurements on a typical sample at  $75^{\circ}$ C case. The accuracy of the measurements is within the tolerance of the measurement instruments.

### Efficiency Vs. Output Voltage at 347Vac




### Efficiency Vs. Output Voltage at 480Vac




#### **Performance Characteristics**

Based on measurements on a typical sample at  $75^{\circ}$ C case. The accuracy of the measurements is within the tolerance of the measurement instruments.


### **Power Factor Vs. Output Power**



### **Total Harmonic Distortion (THD) Vs. Output Power**



### **Inrush Current Info**



Vin	Ipeak	T (@ 10% of Ipeak)	
347 Vrms	59.3A	177µS	
480 Vrms	77.6A	175µS	

Inrush current is measured at peak of the corresponding line voltage. Source impedance per NEMA 410.

### **Lightning Surge Info**

ANSI Surge Type	Differential Mode (L-N)	Common Mode (L-G, N-G, L&N-G)	
1.2/50μs Combination Wave (w/t 2Ω)	6kV	6kV	

### **Isolation**

Isolation	Input	Output	0-10V	Enclosure
Input	NA	2xU+1kV	2.5kV	2xU+1kV
Output	2xU+1kV	NA	2.5kV	2xU+1kV
0-10V	2.5kV	2.5kV	NA	2xU+1kV
Enclosure	2xU+1kV	2xU+1kV	2xU+1kV	NA

U = Max input voltage

© 2016 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication. philips.com/leddrivers



Philips Lighting North America Corporation 10275 W. Higgins Road, Rosemont IL 60018 Tel: 800-322-2086 Fax: 888-423-1882 Customer/Technical Service: 800-372-3331 OEM Support: 866-915-5886

Philips Lighting Canada Ltd. 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008