

Indoor/Outdoor Luminaire Smart Service Guide File "Trimmed" - Rev: February 1, 2017

Additional Sorting / Filtering Fields

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
19096001484	912400478146	DCL20LED4K-8		ServiceSmart	Designer Canopy LED, 2639 Lumens, 4700K Color Temp, 120-277V, Bronze	C		X				66	Outdoor	Garage & Canopy	Garage & Canopy	Designer Canopy LED	
19096001682	912401050226	LPF4SG		ServiceSmart	LPF4 Stone Guard Accessory	C		X				68	Outdoor	Floodlights	Floodlights	LitePro LED Floodlight Large LPF4	
19096001644	912401050222	LPF4WG		ServiceSmart	LPF4 Wire Guard Accessory	C		X				68	Outdoor	Floodlights	Floodlights	LitePro LED Floodlight Large LPF4	
19096001569	912401050216	STKLPF4S-8		ServiceSmart	LPF4, 4000K, 9191 Lumens, Flood, Slip Fitter, 120-277V, Textured Dark Bronze, (equal to LPF4-C-4K-FL-5-8-82)	C		X		X		68	Outdoor	Floodlights	Floodlights	LitePro LED Floodlight Large LPF4	
19096001576	912401050217	STKLPF4T-8		ServiceSmart	LPF4, 4000K, 9191 Lumens, Flood, Trunion, 120-277V, Textured Dark Bronze, (equal to LPF4-C-4K-FL-7-8-82)	C		X		X		68	Outdoor	Floodlights	Floodlights	LitePro LED Floodlight Large LPF4	
19096001675	912401050225	LPF3SG		ServiceSmart	LPF3 Stone Guard Accessory	C		X				68	Outdoor	Floodlights	Floodlights	LitePro LED Floodlight Medium LPF3	
19096001637	912401050221	LPF3WG		ServiceSmart	LPF3 Wire Guard Accessory	C		X				68	Outdoor	Floodlights	Floodlights	LitePro LED Floodlight Medium LPF3	
19096001590	912401050215	STKLPF3S-8		ServiceSmart	LPF3, 4000K, 7012 Lumens, Flood, Slip Fitter, 120-277V, Textured Dark Bronze, (equal to LPF3-C-4K-FL-5-8-82)	C		X		X		68	Outdoor	Floodlights	Floodlights	LitePro LED Floodlight Medium LPF3	
19096001651	912401050223	LPF1SG		ServiceSmart	LPF1 Stone Guard Accessory	C		X				68	Outdoor	Floodlights	Floodlights	LitePro LED Floodlight Mini LPF1	
19096001613	912401050219	LPF1WG		ServiceSmart	LPF1 Wire Guard Accessory	C		X				68	Outdoor	Floodlights	Floodlights	LitePro LED Floodlight Mini LPF1	
19096001552	912401050211	STKLPF1K-8		ServiceSmart	LPF1, 4000K, 1772 Lumens, Flood, Knuckle Mount, 120-277V, Textured Dark Bronze, (equal to LPF1-E-4K-FL-K-8-82)	C		X		X		68	Outdoor	Floodlights	Floodlights	LitePro LED Floodlight Mini LPF1	
19096001668	912401050224	LPF2SG		ServiceSmart	LPF2 Stone Guard Accessory	C		X				68	Outdoor	Floodlights	Floodlights	LitePro LED Floodlight Small LPF2	
19096001820	912401050220	LPF2WG		ServiceSmart	LPF2 Wire Guard Accessory	C		X				68	Outdoor	Floodlights	Floodlights	LitePro LED Floodlight Small LPF2	
19096001583	912401050214	STKLPF2K-8		ServiceSmart	LPF2, 4000K, 3460 Lumens, Flood, Knuckle Mount, 120-277V, Textured Dark Bronze, (equal to LPF2-E-4K-FL-E-8-82)	C		X		X		68	Outdoor	Floodlights	Floodlights	LitePro LED Floodlight Small LPF2	
19096001132	912400480748	GP2A150PMAL-6	Demoted to B	SpecSmart	GP2 Small Floodlight 150W PMA Dual Voltage, w/Lamp, Bronze		50	X				69	Outdoor	Floodlights	Floodlights	GP Flood Series HID	
19096001149	912400480774	GP51000MAL-8	Demoted to B	SpecSmart	GP5 X-Large Floodlight 1000W MH Multi-Tap, w/Lamp & Tension Slip Fitter, Bronze		50	X				69	Outdoor	Floodlights	Floodlights	GP Flood Series HID	
19096001156	912400480781	GP51000MAL-8	Demoted to B	SpecSmart	GP5 X-Large Floodlight 1000W MH Multi-Tap, w/Lamp & Trunion Mount, Bronze		50	X				69	Outdoor	Floodlights	Floodlights	GP Flood Series HID	
19096001118	912400478358	FP1250PMAL-8		ServiceSmart	FloodPak Large 250W PSMH MT w/Lamp, Bronze	C,NL		X				70	Outdoor	Flood/Wall Mount	Flood/Wall Mount	FloodPak Large (FPL)	
19096001095	912400478374	FP400PMAL-8		ServiceSmart	FloodPak Large 400W PSMH MT w/Lamp, Bronze	C		X				70	Outdoor	Flood/Wall Mount	Flood/Wall Mount	FloodPak Large (FPL)	
19096001040	912400478410	FPM150PMAL-8		ServiceSmart	FloodPak Medium 150W PSMH MT w/Lamp, Bronze	C		X				70	Outdoor	Flood/Wall Mount	Flood/Wall Mount	FloodPak Medium (FPM)	
19096001514	912400475154	WP251PMAL-8		ServiceSmart	WP WallPison 250W PSMH MT, Bronze	C		X				72	Outdoor	Wall Mount	Wall Mount - Wall Packs	WP Wall Pack Large	
19096001163	912400477231	WP251PMAL-8	Demoted to B	SpecSmart	WP WallPison, 250W PSMH, MT w/Lamp, Bronze		50	X				72	Outdoor	Wall Mount	Wall Mount - Wall Packs	WP Wall Pack Large	
19096001477	912400475158	WP400PMAL-8		ServiceSmart	WP WallPison, 400W PSMH, MT, Bronze	C		X				72	Outdoor	Wall Mount	Wall Mount - Wall Packs	WP Wall Pack Large	
19096001507	912400461767	WP552		ServiceSmart	WP Replacement glass, gasket, hardware, door lens kit							72	Outdoor	Wall Mount	Wall Mount - Wall Packs	WP Wall Pack Large	
19096011308	912400511023	LPW16-78DGY		ServiceSmart	LPW16, 16 LED, 40W, 3374 Lumens, 700mA, 4000K, 120-277V, Dark Gray	C		X		X		73	Outdoor	Wall Mount	Wall Mount - Sconces	LitePro 16 LED Wall Sconce	
190960011216	912400511033	LPW16-518ZPCB		ServiceSmart	LPW16, 16 LED, 30W, 2698 Lumens, 530mA, 4000K, 120V, Bronze, w/button photocell	C		X		X		73	Outdoor	Wall Mount	Wall Mount - Sconces	LitePro 16 LED Wall Sconce	
19096011223	912400511032	LPW16-588Z		ServiceSmart	LPW16, 16 LED, 30W, 2698 Lumens, 530mA, 4000K, 120-277V, Bronze	C		X		X		73	Outdoor	Wall Mount	Wall Mount - Sconces	LitePro 16 LED Wall Sconce	
190960011230	912400511025	LPW16-718ZPCB		ServiceSmart	LPW16, 16 LED, 40W, 3374 Lumens, 700mA, 4000K, 120-277V, Bronze, w/built-in button photocell	C		X		X		73	Outdoor	Wall Mount	Wall Mount - Sconces	LitePro 16 LED Wall Sconce	
19096011247	912400511024	LPW16-788Z		ServiceSmart	LPW16, 16 LED, 40W, 3374 Lumens, 700mA, 4000K, 120-277V, Bronze	C		X		X		73	Outdoor	Wall Mount	Wall Mount - Sconces	LitePro 16 LED Wall Sconce	
190960011315	912400511035	LPW32-78WH		ServiceSmart	LPW32, 32 LED, 71W, 6913 Lumens, 700mA, 4000K, 120-277V, White	C		X		X		73	Outdoor	Wall Mount	Wall Mount - Sconces	LitePro 32 LED Wall Sconce	
190960011244	912400511037	LPW32-718ZPCB		ServiceSmart	LPW32, 32 LED, 71W, 6913 Lumens, 700mA, 4000K, 120-277V, Bronze, w/button photocell	C		X		X		73	Outdoor	Wall Mount	Wall Mount - Sconces	LitePro 32 LED Wall Sconce	
190960011261	912400511036	LPW32-788Z		ServiceSmart	LPW32, 32 LED, 71W, 6913 Lumens, 700mA, 4000K, 120-277V, Bronze	C		X		X		73	Outdoor	Wall Mount	Wall Mount - Sconces	LitePro 32 LED Wall Sconce	
190960011278	912400511034	LPW32-78DGY		ServiceSmart	LPW32, 32 LED, 71W, 6913 Lumens, 700mA, 4000K, 120-277V, Dark Gray	C		X		X		73	Outdoor	Wall Mount	Wall Mount - Sconces	LitePro 32 LED Wall Sconce	
190960011285	912400511038	LPW32-7D18ZMR		ServiceSmart	LPW32, 32 LED, 71W, 6913 Lumens, 700mA, 4000K, 120/277V, Bronze, with Motion Sensor	C		X		X	X	73	Outdoor	Wall Mount	Wall Mount - Sconces	LitePro 32 LED Wall Sconce	
190960011292	912400511043	LPWCVRPLT-8Z		ServiceSmart	LPW Universal wall cover mounting plate, Bronze	C		X				73	Outdoor	Wall Mount	Wall Mount - Sconces	LitePro 32 LED Wall Sconce	
190960011179	912400511021	LPW7-18ZPCB		ServiceSmart	LPW7, 14W, 1154 lumens, 350mA, 4000K, 120V, Bronze, with button photocell	C		X		X		73	Outdoor	Wall Mount	Wall Mount - Sconces	LitePro 7 LED Wall Sconce	
19096001186	912400511020	LPW7-88Z		ServiceSmart	LPW7, 14W, 1154 lumens, 350mA, 4000K, 120-277V, Bronze	C		X		X		73	Outdoor	Wall Mount	Wall Mount - Sconces	LitePro 7 LED Wall Sconce	
190960011193	912400511018	LPW7-8DGY		ServiceSmart	LPW7, 14W, 1154 lumens, 350mA, 4000K, 120-277V, Dark Gray	C		X		X		73	Outdoor	Wall Mount	Wall Mount - Sconces	LitePro 7 LED Wall Sconce	
19096001538	912401050010	LEDW1EDSK120PC8Z		ServiceSmart	LED Wall Light, 5000K, 12W, 829 Lumens, 120V, Built-in Photocell, Bronze	C		X				74	Outdoor	Wall Mount	Wall Mount - General Purpose	LED Wall Light (LWL)	
19096001521	912400480904	DTDA150NXL-1		ServiceSmart	Dark To Dawn, 150W, 150W, HPS, 120w w/Lamp	C		X				76	Outdoor	Site & Area		Dark To Dawn (DTD)	
19096001606	912401050002	DTDARMGY35		ServiceSmart	DTD LED Arm, 1.5" dia steel, light gray	C		X				76	Outdoor	Site & Area		Dark To Dawn LED (DTD)	
19096001545	912401050001	DTDLED1C3X120CY3P		ServiceSmart	DTD LED, 3356 Lumens, 5000K, 39W 120V, light gray, NEMA Twist Lock Photocell	C		X		X		76	Outdoor	Site & Area		Dark To Dawn LED (DTD)	
190960014910	912400228789	RS-ECF-PTF2-UNV-88P		SpecSmart	Pole Top Fitter, Universal Mount (single, double, triple, quad), Bronze Paint		50					76	Outdoor	Site & Area		Eciform	
190960014927	912400228788	RS-ECF-5-4		SpecSmart	Eciform Internal House Side Shield, QTY 4		50					76	Outdoor	Site & Area		Eciform	
190960019915	912400200630	RS-ECF-3-105LA-321A-NW-UNV-88P		SpecSmart	Eciform Area, Type 3, 105W, 11,249 Lumens, 32 LED, 4000K, 120-277V, Bronze		50			X		76	Outdoor	Site & Area		Eciform LED Area	
190960019922	912400200633	RS-ECF-3-160LA-481A-NW-UNV-88P		SpecSmart	Eciform Area, Type 3, 160W, 15,565 Lumens, 48 LED, 4000K, 120-277V, Bronze		50			X		76	Outdoor	Site & Area		Eciform LED Area	
190960019939	912400200636	RS-ECF-3-215LA-641A-NW-UNV-88P		SpecSmart	Eciform Area, Type 3, 215W, 20,252 Lumens, 64 LED, 4000K, 120-277V, Bronze		50			X		76	Outdoor	Site & Area		Eciform LED Area	
190960019946	912400200631	RS-ECF-4-105LA-321A-NW-UNV-88P		SpecSmart	Eciform Area, Type 4, 105W, 10,828 Lumens, 32 LED, 4000K, 120-277V, Bronze		50			X		76	Outdoor	Site & Area		Eciform LED Area	
190960019953	912400200634	RS-ECF-4-160LA-481A-NW-UNV-88P		SpecSmart	Eciform Area, Type 4, 160W, 14,955 Lumens, 48 LED, 4000K, 120-277V, Bronze		50			X		76	Outdoor	Site & Area		Eciform LED Area	
190960019960	912400200637	RS-ECF-4-215LA-641A-NW-UNV-88P		SpecSmart	Eciform Area, Type 4, 215W, 19,991 Lumens, 64 LED, 4000K, 120-277V, Bronze		50			X		76	Outdoor	Site & Area		Eciform LED Area	
190960019977	912400200632	RS-ECF-5-105LA-321A-NW-UNV-88P		SpecSmart	Eciform Area, Type 5, 105W, 10,494 Lumens, 32 LED, 4000K, 120-277V, Bronze		50			X		76	Outdoor	Site & Area		Eciform LED Area	
190960019984	912400200635	RS-ECF-5-160LA-481A-NW-UNV-88P		SpecSmart	Eciform Area, Type 5, 160W, 14,465 Lumens, 48 LED, 4000K, 120-277V, Bronze		50			X		76	Outdoor	Site & Area		Eciform LED Area	
190960019991	912400200638	RS-ECF-5-215LA-641A-NW-UNV-88P		SpecSmart	Eciform Area, Type 5, 215W, 19,880 Lumens, 64 LED, 4000K, 120-277V, Bronze		50			X		76	Outdoor	Site & Area		Eciform LED Area	

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
190096014903	912400213901	RS-ECF-RAM-88P		SpecSmart	EcoForm Retrofit Arm Kit, Round/Square Pole 4", Bronze		50					76	Outdoor	Site & Area			EcoForm LED Area
190096019861	912400215786	4.4356E-11		ServiceSmart	Anchor Bolt, 3/4" x 18" X 3.75", (1 Each with double nuts/double washers; order 4 per pole)	C						77	Outdoor	Site & Area			Anchor Bolts
190096019878	912400214158	4.4356E-11		ServiceSmart	Anchor Bolts, 5/8" X 18" X 3.62", (1 Each with double nuts/double washers; order 4 per pole)	C						77	Outdoor	Site & Area			Anchor Bolts
190096019885	912400215784	1-36-45		ServiceSmart	Anchor Bolt, 1" x 16" X 4.5", (1 Each with double nuts/double washers; order 4 per pole)	C						77	Outdoor	Site & Area			Anchor Bolts
190096015892	912400791465	AVA-3/J-250PSMHQUAD-88P		SpecSmart	AVA Shoebox, Type 3, 250W PSMH, MT, Bronze		50					77	Outdoor	Site & Area			Avolume (AVA)
190096019908	912400725111	AVA-3/J-400PSMHQUAD-88P		SpecSmart	AVA Shoebox, Type 3, 400W PSMH, MT, Bronze		50					77	Outdoor	Site & Area			Avolume (AVA)
190096010464	912400478927	MCL3400PMA-8		ServiceSmart	MCL Shoebox 400W PSMH MT Type 3, Bronze	C		X				77	Outdoor	Site & Area			MCL
190096011125	912400478932	MCL4400PMA-8		ServiceSmart	MCL Shoebox 400W PSMH MT Type 4, Bronze	C		X				77	Outdoor	Site & Area			MCL
190096011286	912400463824	VGC200		ServiceSmart	Roughlyte Series 4-3/8" Globe Diameter Glass Clear	C						79	Outdoor	Special Purpose	Special Purpose - Vaportite		Roughlyte Adapters/Accessories/Replacement Globes
190096014139	912400463830	VGR100		ServiceSmart	Roughlyte Series 3-1/2" Globe Diameter Glass Ruby (60W max)	C						79	Outdoor	Special Purpose	Special Purpose - Vaportite		Roughlyte Adapters/Accessories/Replacement Globes
190096011309	912400464183	VPRC10		ServiceSmart	Roughlyte Series 4-3/8" Globe Diameter Lxan, Clear Prismatic (75W Max.)	C						79	Outdoor	Special Purpose	Special Purpose - Vaportite		Roughlyte Adapters/Accessories/Replacement Globes
190096012125	912400461742	VPRCS		ServiceSmart	Roughlyte Series 3-1/2" Globe Diameter Lxan, Clear Prismatic (60W Max.)	C						79	Outdoor	Special Purpose	Special Purpose - Vaportite		Roughlyte Adapters/Accessories/Replacement Globes
190096011354	912400473177	VCLL10GCL/4	Demoted to B	SpecSmart	Roughlyte Ceiling Mount 100W Glass Globe Cast Guard w/ 3/4" Conduit Taps		50					79	Outdoor	Special Purpose	Special Purpose - Vaportite		Roughlyte Luminaires
190096014143	912400472521	VCLL1GCLN		ServiceSmart	Roughlyte Ceiling Mount 100W Glass Globe Cast Guard	C		X				79	Outdoor	Special Purpose	Special Purpose - Vaportite		Roughlyte Luminaires
190096011323	912400468220	VCLL1X		ServiceSmart	Roughlyte Ceiling Mount 100W Glass Globe	C		X				79	Outdoor	Special Purpose	Special Purpose - Vaportite		Roughlyte Luminaires
190096011170	912400470184	VCLX2GCL		ServiceSmart	Roughlyte Ceiling Mount 200W Glass Globe Cast Guard	C		X				79	Outdoor	Special Purpose	Special Purpose - Vaportite		Roughlyte Luminaires
190096011378	912400481846	VCLX2HFLB-8		ServiceSmart	Roughlyte Ceiling Mount 20W CF Glass Globe Cast Guard w/Lamp, 120V	C		X				79	Outdoor	Special Purpose	Special Purpose - Vaportite		Roughlyte Luminaires
190096012131	912400461738	VX1GCL		ServiceSmart	Roughlyte Surface/Ceiling Mount 100W Glass Globe Cast Guard	C		X				79	Outdoor	Special Purpose	Special Purpose - Vaportite		Roughlyte Luminaires
190096011248	912400461739	VX2GCL	Demoted to B	SpecSmart	Roughlyte Surface/Ceiling Mount 200W Glass Globe Cast Guard		50					79	Outdoor	Special Purpose	Special Purpose - Vaportite		Roughlyte Luminaires
190096012193	912400463832	VY11GCL		ServiceSmart	Roughlyte Pendant Mount 100W Glass Globe Cast Guard	C		X				79	Outdoor	Special Purpose	Special Purpose - Vaportite		Roughlyte Luminaires
190096011262	912400461747	VW1GCL		ServiceSmart	Roughlyte Wall Mount 100W Glass Globe Cast Guard	C		X				79	Outdoor	Special Purpose	Special Purpose - Vaportite		Roughlyte Luminaires
190096011130	912400468248	VWXL10A		ServiceSmart	Roughlyte Wall Mount 75W Lxan Globe	C						79	Outdoor	Special Purpose	Special Purpose - Vaportite		Roughlyte Luminaires
190096011460	912400472528	VWXL11GCLN		ServiceSmart	Roughlyte Wall Mount 100W Glass Globe Cast Guard	C		X				79	Outdoor	Special Purpose	Special Purpose - Vaportite		Roughlyte Luminaires
190096011347	912400470195	VWXL21GCL		ServiceSmart	Roughlyte Wall Mount 200W Glass Globe Cast Guard	C		X				79	Outdoor	Special Purpose	Special Purpose - Vaportite		Roughlyte Luminaires
190096011392	912400481870	VWXL32HFLB-8		ServiceSmart	Roughlyte Wall Mount 32W CF Glass Globe Cast Guard, 120V w/Lamp	C		X				79	Outdoor	Special Purpose	Special Purpose - Vaportite		Roughlyte Luminaires
19009601408	912400481871	VWXL42HFLB-8		ServiceSmart	Roughlyte Wall Mount 42W CF Glass Globe Cast Guard, 120V w/Lamp	C		X				79	Outdoor	Special Purpose	Special Purpose - Vaportite		Roughlyte Luminaires
783352016775	912400114156	B1-ALED7NPWS	Demoted to B	SpecSmart	120V, LED, Warm, 7 Watts, Narrow Flood, Small Aluminum Bullet w/ Shroud, Black		50					81	Outdoor	Landscape			Accent LED - Line Voltage
783352018007	912400115620	B3-HLED13NFW	Demoted to B	SpecSmart	120V, LED, Warm, 13 Watts, Narrow Flood, Medium Aluminum Bullet w/ Shroud, Bronze		50					81	Outdoor	Landscape			Accent LED - Line Voltage
783352016904	912400115706	B4-HLED18NFW	Demoted to B	SpecSmart	120V, LED, Warm, 18 Watts, Narrow Flood, Large Bullet / Short Shroud, Bronze		50					81	Outdoor	Landscape			Accent LED - Line Voltage
783352017703	912400118941	BTS016-ALED7FLW	Demoted to B	SpecSmart	120V, LED, Warm, 7 Watts, Flood, Micro Bullet, Black		50					81	Outdoor	Landscape			Accent LED - Line Voltage
783352016836	912400114155	B1-ALED7NPWL	Demoted to B	SpecSmart	120V, LED, Warm, 7 Watts, Narrow Flood, Small Aluminum Bullet w/ Shroud, Black		50					81	Outdoor	Landscape			Accent LED - Line Voltage
783352017079	912400118722	BLS016-AS7LED7FLW		ServiceSmart	12V, LED, Warm, 7 Watts, Flood, Micro Bullet W/Stake, Black	C		X				81	Outdoor	Landscape			Accent LED - Low Voltage
783352016997	912400118723	BLS016-AS7LED7NFW		ServiceSmart	12V, LED, Warm, 7 Watts, Narrow Flood, Micro Bullet W/Stake, Black	C		X				81	Outdoor	Landscape			Accent LED - Low Voltage
783352017093	912400118763	BLS016-HS7LED7FLW		ServiceSmart	12V, LED, Warm, 7 Watts, Flood, Micro Bullet W/Stake, Bronze	C		X				81	Outdoor	Landscape			Accent LED - Low Voltage
783352017017	912400118765	BLS016-HS7LED7NFW		ServiceSmart	12V, LED, Warm, 7 Watts, Narrow Flood, Micro Bullet W/Stake, Bronze	C		X				81	Outdoor	Landscape			Accent LED - Low Voltage
783352020307	912401335008	BL711-AS7LED2W		ServiceSmart	12V, LED, Warm 2W T3, Black	C						81	Outdoor	Landscape			Accent LED - Low Voltage
783352020314	912401335009	BL711-HS7LED2W		ServiceSmart	12V, LED, Warm 2W T3, Bronze	C						81	Outdoor	Landscape			Accent LED - Low Voltage
783352020826	912401150003	BL9DC-AS7		ServiceSmart	12V, LED, Cool, Small Architectural Accent LED, FlexScope, Black	C						81	Outdoor	Landscape			Accent LED - Low Voltage
783352020833	912401150004	BL9DC-HS7		ServiceSmart	12V, LED, Cool, Small Architectural Accent LED, FlexScope, Bronze	C						81	Outdoor	Landscape			Accent LED - Low Voltage
783352020802	912401150001	BL9DW-AS7		ServiceSmart	12V, LED, Warm, Small Architectural Accent LED, FlexScope, Black	C		X				81	Outdoor	Landscape			Accent LED - Low Voltage
783352020819	912401150002	BL9DW-HS7		ServiceSmart	12V, LED, Warm, Small Architectural Accent LED, FlexScope, Bronze	C		X				81	Outdoor	Landscape			Accent LED - Low Voltage
783352002341	912400104309	1020-H		ServiceSmart	120V, 100W, PAR 38, Large Classic, Bronze	C		X				82	Outdoor	Landscape			Accent - Line Voltage
783352033485	912400114154	B1-A		ServiceSmart	120V, 100W, PAR/R20, Small Aluminum Bullet, Black	C		X				82	Outdoor	Landscape			Accent - Line Voltage
783352033515	912400114159	B1-H		ServiceSmart	120V, 100W, PAR/R20, Small Aluminum Bullet, Bronze	C		X				82	Outdoor	Landscape			Accent - Line Voltage
783352033591	912400115618	B3-H		ServiceSmart	120V, 100W, PAR/R30, Medium Aluminum Bullet w/ Shroud, Bronze	C		X				82	Outdoor	Landscape			Accent - Line Voltage
78335203614	912400115695	B4-A	Demoted to B	SpecSmart	120V, 300W, R40, Large Bullet, Black		50	X				82	Outdoor	Landscape			Accent - Line Voltage
78335203645	912400115703	B4-H		ServiceSmart	120V, 300W, R40, Large Bullet, Bronze	C		X				82	Outdoor	Landscape			Accent - Line Voltage
78335204994	912400118939	BTS016-A		ServiceSmart	120V, 50W, MR16, Micro Bullet W/ Integral Transformer, Black	C						82	Outdoor	Landscape			Accent - Line Voltage
78335205014	912400118943	BTS016-H		ServiceSmart	120V, 50W, MR16, Micro Bullet W/ Integral Transformer, Black	C						82	Outdoor	Landscape			Accent - Line Voltage
78335205052	912400118964	BU1-A		ServiceSmart	120V, 50W, PAR/R20, Small Uitem Composite Bullet, Black	C		X				82	Outdoor	Landscape			Accent - Line Voltage
78335205069	912400118966	BU1-G		ServiceSmart	120V, 50W, PAR/R20, Small Uitem Composite Bullet, Verde	C		X				82	Outdoor	Landscape			Accent - Line Voltage
78335205076	912400118967	BU1-H		ServiceSmart	120V, 50W, PAR/R20, Small Uitem Composite Bullet, Black	C		X				82	Outdoor	Landscape			Accent - Line Voltage
78335205083	912400118972	BU3-A		ServiceSmart	120V, 75W PAR30, Medium Uitem Composite Bullet, Black	C		X				82	Outdoor	Landscape			Accent - Line Voltage
78335205090	912400118974	BU3-G		ServiceSmart	120V, 75W PAR30, Medium Uitem Composite Bullet, Verde	C		X				82	Outdoor	Landscape			Accent - Line Voltage

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
783352005106	912400118978	BU3-H		ServiceSmart	120V, 75W PAR30, Medium Uitem Composite Bullet, Bronze	C		X				82	Outdoor	Landscape		Accent - Line Voltage	
783352005113	912400118982	BU4-A		ServiceSmart	Large Uitem Composite Bullet, Black	C		X				82	Outdoor	Landscape		Accent - Line Voltage	
783352005120	912400118983	BU4-G		ServiceSmart	Large Uitem Composite Bullet, Verde	C		X				82	Outdoor	Landscape		Accent - Line Voltage	
783352005137	912400118984	BU4-H		ServiceSmart	Large Uitem Composite Bullet, Bronze	C		X				82	Outdoor	Landscape		Accent - Line Voltage	
783352002488	912400105334	J1LC		ServiceSmart	Long Shroud w/Convex Lens (R1), Bronze	C						83	Outdoor	Landscape		Accent - Line Voltage Accessories	
783352002518	912400105338	1HSD		ServiceSmart	Short Shroud (R1), Bronze	C						83	Outdoor	Landscape		Accent - Line Voltage Accessories	
783352002617	912400105346	1UASO		ServiceSmart	Small Uitem Shroud, Black	C						83	Outdoor	Landscape		Accent - Line Voltage Accessories	
783352002679	912400105353	1UHL0		ServiceSmart	Small Uitem Shroud, Bronze	C						83	Outdoor	Landscape		Accent - Line Voltage Accessories	
783352002693	912400105355	1UHSO		ServiceSmart	Small Uitem Shroud, Bronze	C						83	Outdoor	Landscape		Accent - Line Voltage Accessories	
783352002914	912400112684	4HLD		ServiceSmart	Long Shroud (B4), Bronze	C						83	Outdoor	Landscape		Accent - Line Voltage Accessories	
783352002945	912400112687	4HSD		ServiceSmart	Short Shroud (B4), Bronze	C						83	Outdoor	Landscape		Accent - Line Voltage Accessories	
783352002969	912400112693	4UASO		ServiceSmart	Large Uitem Shroud, Black	C						83	Outdoor	Landscape		Accent - Line Voltage Accessories	
783352003003	912400112697	4UGSO		ServiceSmart	Large Uitem Shroud, Verde	C						83	Outdoor	Landscape		Accent - Line Voltage Accessories	
783352003027	912400112704	4UHSD		ServiceSmart	Large Uitem Shroud, Bronze	C						83	Outdoor	Landscape		Accent - Line Voltage Accessories	
783352002016	912400118678	BU1-HLS7		ServiceSmart	12V, 75W, MR16, Small Bullet w/ Long Shroud & Stake, Bronze	C						84	Outdoor	Landscape		Accent - Low Voltage	
783352004154	912400118714	BU5016-AS7		ServiceSmart	12V, 50W, MR16, Micro Bullet w/Stake, Black	C						84	Outdoor	Landscape		Accent - Low Voltage	
783352002068	912400118716	BU5016-AS7BAB		ServiceSmart	12V, 20W, MR16, Micro Bullet w/Stake & Lamp, Black	C		X				84	Outdoor	Landscape		Accent - Low Voltage	
783352004260	912400118753	BU5016-HS7		ServiceSmart	12V, 50W, MR16, Micro Bullet w/Stake, Bronze	C						84	Outdoor	Landscape		Accent - Low Voltage	
783352002150	912400118755	BU5016-HS7BAB		ServiceSmart	12V, 20W, MR16, Micro Bullet w/Stake & Lamp, Bronze	C		X				84	Outdoor	Landscape		Accent - Low Voltage	
783352004352	912400118783	BU16-AS7		ServiceSmart	12V, 50W, MR16, Micro Bullet w/Stake, Black	C						84	Outdoor	Landscape		Accent - Low Voltage	
783352004376	912400118784	BU16-AS7BAB		ServiceSmart	12V, 20W, MR16, Micro Bullet w/Stake & Lamp, Black	C		X				84	Outdoor	Landscape		Accent - Low Voltage	
783352004468	912400118794	BU16-HS7		ServiceSmart	12V, 50W MR16, Micro Bullet w/Stake, Bronze	C						84	Outdoor	Landscape		Accent - Low Voltage	
783352004482	912400118796	BU16-HS7BAB		ServiceSmart	12V, 20W, MR16, Micro Bullet w/Stake & Lamp, Bronze	C		X				84	Outdoor	Landscape		Accent - Low Voltage	
783352002074	912400118802	BU11-AS7		ServiceSmart	12V, 35W MR11, Micro Bullet w/Stake, Black	C		X				84	Outdoor	Landscape		Accent - Low Voltage	
783352002071	912400118808	BU11-HS7		ServiceSmart	12V, 35W MR11, Micro Bullet w/Stake, Bronze	C		X				84	Outdoor	Landscape		Accent - Low Voltage	
7833520020970	912400119008	BU16-AS7		ServiceSmart	12V, 35W MR16, Micro Uitem Composite Bullet w/Stake, Black	C						84	Outdoor	Landscape		Accent - Low Voltage	
7833520020987	912400119015	BU16-GS7		ServiceSmart	12V, 35W MR16, Micro Uitem Composite Bullet w/Stake, Verde	C						84	Outdoor	Landscape		Accent - Low Voltage	
7833520020109	912400119023	BU16-HS7		ServiceSmart	12V, 35W MR16, Micro Uitem Composite Bullet w/Stake, Bronze	C						84	Outdoor	Landscape		Accent - Low Voltage	
783352001917	912400121604	CUL16S7		ServiceSmart	12V, 20W, MR16, MR16 Bullet w/ Stake, Copper	C						84	Outdoor	Landscape		Accent - Low Voltage	
783352002266	912400104302	I010-H		ServiceSmart	120V, 100W, A19, Beacons, Bronze	C		X				84	Outdoor	Landscape		Beacon - Line Voltage	
783352002280	912400104304	I012-H		ServiceSmart	120V, 100W, A19, Composite Beacon, Bronze	C		X				84	Outdoor	Landscape		Beacon - Line Voltage	
783352006233	912400121908	DWCL3-A		ServiceSmart	12V, 20W, T3, Composite Mini Beacon, Black	C						85	Outdoor	Landscape		Beacon - Low Voltage	
783352006240	912400121909	DWCL2-A		ServiceSmart	12V, 20W, T3, Composite Semi Recused Beacon, Black	C						85	Outdoor	Landscape		Beacon - Low Voltage	
783352014825	912400121673	DB14-H		ServiceSmart	120V, 100W INC, Round Top Bollard, 14", Bronze	C						85	Outdoor	Landscape		Bollard - Line Voltage	
783352020772	912400121701	DB30-A		ServiceSmart	120V, 100W INC, 100W INC Round Top Bollard, 30", Black	C		X				85	Outdoor	Landscape		Bollard - Line Voltage	
783352014832	912400121702	DB30-H		ServiceSmart	120V, 100W INC, 100W INC Round Top Bollard, 30", Bronze	C		X				85	Outdoor	Landscape		Bollard - Line Voltage	
19096019700	912400121711	DB30AA012LE		ServiceSmart	120V, LED, Warm, 11W, Clear Symmetric, Round Top Bollard, 30", Black	C		X				85	Outdoor	Landscape		Bollard LED - Line Voltage	
19096019717	912400121724	DB30HA012LE		ServiceSmart	120V, LED, Warm, 11W, Clear Symmetric, Round Top Bollard, 30", Bronze	C		X				85	Outdoor	Landscape		Bollard LED - Line Voltage	
4667732376	912401335011	DAL1-ALED2W		ServiceSmart	12V, LED, Deck Light, Aluminum, Warm 2W T3, Black	C		X				New	Outdoor	Landscape		Deck Light LED - Low Voltage	
46677323790	912401335014	DAL1-HLED2W		ServiceSmart	12V, LED, Deck Light, Aluminum, Warm 2W T3, Bronze	C		X				New	Outdoor	Landscape		Deck Light LED - Low Voltage	
19096019714	912401335015	DAL1-SLEED2W		ServiceSmart	12V, LED, Deck Light, Warm 2W T3, Stainless Steel	C						New	Outdoor	Landscape		Deck Light LED - Low Voltage	
19096019731	912401335017	DAL1-HLED2W		ServiceSmart	12V, LED, Deck Light, Uitem, Warm 2W T3, Bronze	C						New	Outdoor	Landscape		Deck Light LED - Low Voltage	
19096019748	912401335018	DAL1-NEED2W		ServiceSmart	12V, LED, Deck Light, Brass, Warm 2W T3, Bronze	C						New	Outdoor	Landscape		Deck Light LED - Low Voltage	
19096019755	912401335012	DAL1-BLED2W		ServiceSmart	12V, LED, Deck Light, Aluminum, Warm 2W T3, White	C						New	Outdoor	Landscape		Deck Light LED - Low Voltage	
19096019762	912401335013	DAL1-GLED2W		ServiceSmart	12V, LED, Deck Light, Aluminum, Warm 2W T3, Verde	C						New	Outdoor	Landscape		Deck Light LED - Low Voltage	
19096019779	912401335018	DAL1-GLED2W		ServiceSmart	12V, LED, Deck Light, Uitem, Warm 2W T3, Verde	C						New	Outdoor	Landscape		Deck Light LED - Low Voltage	
783352005731	912400121606	CUL20		SpecSmart	12V, 10W Xenon T3, Bell Shape Deck Light, Copper		50					86	Outdoor	Landscape		Deck Light - Low Voltage	
783352007322	912400123376	L16-AC		ServiceSmart	12V, 10W Xenon T3, Copper Line Light, 6", Copper			X				86	Outdoor	Landscape		Deck Light - Low Voltage	
783352005625	912400121627	CP3		ServiceSmart	Concrete Pour Kit (3)	C						87	Outdoor	Landscape		Inground/ Ingrade - Line Voltage Accessories	
783352005632	912400121303	CP4		ServiceSmart	Concrete Pour Kit (4)	C						87	Outdoor	Landscape		Inground/ Ingrade - Line Voltage Accessories	
783352000408	912400121332	CP5		ServiceSmart	Concrete Pour Kit, 1/2, 1/2 & 1/2	C						87	Outdoor	Landscape		Inground/ Ingrade - Line Voltage Accessories	
19096019786	912400444971	CP15		SpecSmart	Concrete Pour Kit (1.5)		50					87	Outdoor	Landscape		Inground/ Ingrade - Line Voltage Accessories	
19096019793	912400121572	CP25		SpecSmart	Stainless Steel Concrete Pour Kit (2.5), Stainless Steel		50					87	Outdoor	Landscape		Inground/ Ingrade - Line Voltage Accessories	
19096019809	912400121574	CP35		SpecSmart	Stainless Steel Concrete Pour Kit (3.5)		50					87	Outdoor	Landscape		Inground/ Ingrade - Line Voltage Accessories	

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
78352006691	912400122818	I2G-H		ServiceSmart	120V, 100W R30, Small Inground w/Bronze Rock Guard, Bronze	C		X				87	Outdoor	Landscape		Inground/Ingrade - Line Voltage	
78352006714	912400122850	I3G-H		ServiceSmart	120V, 100W Par/R20, Inground with Composite Rock Guard, Bronze	C		X				87	Outdoor	Landscape		Inground/Ingrade - Line Voltage	
78352021106	912400122934	I4G-H		ServiceSmart	120V, 150W PAR 38, Large Inground/Medium Base Socket/Stainless Steel Trim Ring, Bronze	C		X				87	Outdoor	Landscape		Inground/Ingrade - Line Voltage	
78352007223	912400123106	IT2IG-H	Demoted to B	SpecSmart	120V / 12V, 75W MR16, Small Inground w/Composite Rock Guard, Bronze		50					87	Outdoor	Landscape		Inground/Ingrade - Line Voltage	
78352021595	912401100006	IL90C-A		ServiceSmart	12V, LED, Cool, Zoomable Optics, FlexScape, Black	C		X				87	Outdoor	Landscape		Inground/Ingrade LED - Low Voltage	
78352021588	912401100005	IL90W-A		ServiceSmart	12V, LED, Warm, Zoomable Optics, FlexScape, Black	C		X				87	Outdoor	Landscape		Inground/Ingrade LED - Low Voltage	
78352006707	912400122973	I2-H		ServiceSmart	120V, 100W R30, Small Inground with Bronze Trim Ring, Bronze	C		X				88	Outdoor	Landscape		Inground/Ingrade - Low Voltage	
78352000125	912400123060	IL116G-H		ServiceSmart	12V, 75W MR16, Inground w/Guard, Bronze	C						88	Outdoor	Landscape		Inground/Ingrade - Low Voltage	
78352000132	912400123051	IL116-H		ServiceSmart	12V, 75W MR16, Inground, Bronze	C		X				88	Outdoor	Landscape		Inground/Ingrade - Low Voltage	
78352000149	912400123068	IL336-A		ServiceSmart	12V, 50W PAR 36, Well Light, Black	C						88	Outdoor	Landscape		Inground/Ingrade - Low Voltage	
78352000156	912400123071	IL336-AL		ServiceSmart	12V, 20W PAR 36, Well Light w/Lamp, Black	C		X				88	Outdoor	Landscape		Inground/Ingrade - Low Voltage	
78352007254	912400123116	IL516-H		ServiceSmart	12V, 35W MR16, Uttern Micro Inground, MR16, Bronze	C						88	Outdoor	Landscape		Inground/Ingrade - Low Voltage	
78352000392	912400121226	CP2		ServiceSmart	Concrete Pour Kit (2)	C						88	Outdoor	Landscape		Inground/Ingrade - Low Voltage Accessories	
78352003683	912400118661	B#1		SpecSmart	Cast Iron Box (1/2" NPT)		50					89	Outdoor	Landscape		Landscape Accessories, General	
78352003690	912400118662	B#2		ServiceSmart	Cast Iron Box (3/4" NPT)	C						89	Outdoor	Landscape		Landscape Accessories, General	
78352003573	912400118663	B#3		ServiceSmart	Cast Iron Box w/four 1/2" NPT+ two 1/2" NPT	C						89	Outdoor	Landscape		Landscape Accessories, General	
78352003706	912400118664	B#4		ServiceSmart	Cast Iron Box w/two 1/2" NPT+ two 1/2" NPT	C						89	Outdoor	Landscape		Landscape Accessories, General	
78352002037	912400123922	LVC3		ServiceSmart	Connectors (Box of 12)	C						89	Outdoor	Landscape		Landscape Accessories, General	
78352007360	912400123923	LVC4		ServiceSmart	Low Voltage "T" Connector	C						89	Outdoor	Landscape		Landscape Accessories, General	
78352002757	912400124331	MC1A		ServiceSmart	LV Mounting Canopy (Box of 6), Black	C		X				89	Outdoor	Landscape		Landscape Accessories, General	
78352007490	912400124334	MC1A		ServiceSmart	LV Mounting Canopy (Box of 6), Bronze	C		X				89	Outdoor	Landscape		Landscape Accessories, General	
78352003118	912400125333	PC3		ServiceSmart	Plug-In Photo Cell, Direct Mount	C		X				89	Outdoor	Landscape		Landscape Accessories, General	
78352012128	912400127007	S358	Demoted to B	SpecSmart	Perma-Post 3.5" O.D. (Box of 9), White		50	X				89	Outdoor	Landscape		Landscape Accessories, General	
78352012203	912400127018	S3A		ServiceSmart	Perma-Post 3" O.D. (Box of 12), Black	C		X				89	Outdoor	Landscape		Landscape Accessories, General	
78352012227	912400127020	S3G		ServiceSmart	Perma-Post 3" O.D. (Box of 12), Verde	C						89	Outdoor	Landscape		Landscape Accessories, General	
78352012234	912400127023	S3H		ServiceSmart	Perma-Post 3" O.D. (Box of 12), Bronze	C		X				89	Outdoor	Landscape		Landscape Accessories, General	
78352012241	912400127022	S3N		ServiceSmart	Perma-Post 3" O.D. Natural Bronze	C						89	Outdoor	Landscape		Landscape Accessories, General	
78352001825	912400127422	S7		ServiceSmart	Low Voltage Mounting Stake (Box of 12)	C		X				89	Outdoor	Landscape		Landscape Accessories, General	
78352012340	912400127540	S8		ServiceSmart	15" Low Voltage Mounting Stake (Box of 12)	C		X				89	Outdoor	Landscape		Landscape Accessories, General	
78352001665	912400128401	T5		ServiceSmart	Plug In Timer, Analog	C		X				89	Outdoor	Landscape		Landscape Accessories, General	
78352013644	912400128609	TM1A	Demoted to B	SpecSmart	N/Tree Mount Adapter, Black		50					89	Outdoor	Landscape		Landscape Accessories, General	
78352013668	912400128612	TM1H		ServiceSmart	Tree Mount Adapter, Bronze	C		X				89	Outdoor	Landscape		Landscape Accessories, General	
78352001726	912400128616	TM2H		ServiceSmart	Tree Mount Junction Box, Bronze	C		X				89	Outdoor	Landscape		Landscape Accessories, General	
78352001733	912400128621	TM2H		ServiceSmart	Composite Tree Mount Junction Box, Bronze	C		X				89	Outdoor	Landscape		Landscape Accessories, General	
78352013729	912400128622	TM510		ServiceSmart	Nylon Tree Strap, 10 Foot	C						89	Outdoor	Landscape		Landscape Accessories, General	
78352014566	912400129265	WAMM1-G		ServiceSmart	120V, 75W T3, Mini Arch Flood w/Shroud, Bronze	C						90	Outdoor	Landscape		Mini Flood/Wall Washer - Line Voltage	
78352021403	912400129302	WAMM14F-HS720T3		ServiceSmart	12V, 20W T3, Mini Arch Flood w/Shroud, with Lamp, Bronze	C		X				90	Outdoor	Landscape		Mini Flood/Wall Washer - Low Voltage	
78352014658	912400129289	WAMM14-HS7		SpecSmart	12V, 50W T4, Mini Arch Flood w/Shroud, Bronze		50					90	Outdoor	Landscape		Mini Flood/Wall Washer - Low Voltage	
19009619816	912400129281	WAMM1DWF-H		SpecSmart	120V, LED, Warm, Mini Arch Flood w/Frosted Shroud, Bronze		50					90	Outdoor	Landscape		Mini Flood/Wall Washer LED - Line Voltage	
19009619823	912400129334	WAMM1DWF-HS7		SpecSmart	12V, LED, Warm, Mini Arch Flood w/Frosted Shroud, Bronze		50	X				90	Outdoor	Landscape		Mini Flood/Wall Washer LED - Low Voltage	
78352003603	912400124189	MUS-G		ServiceSmart	120V, 100W A19, Med Mushroom, Verde	C						91	Outdoor	Landscape		Path Light - Line Voltage	
78352007919	912400124950	MUS-H		ServiceSmart	120V, 100W A19, Med Mushroom, Bronze	C						91	Outdoor	Landscape		Path Light - Line Voltage	
78352008589	912400125127	F3-G		ServiceSmart	120V, 75W A19, Small Horizontal Path Light, Verde	C						91	Outdoor	Landscape		Path Light - Line Voltage	
78352008909	912400125533	R3-G		ServiceSmart	120V, 100W A19, Large Indirect, Verde	C						91	Outdoor	Landscape		Path Light - Line Voltage	
78352001597	912400124587	MUS-A		ServiceSmart	120V, 100W A19, Med Mushroom, Black	C						91	Outdoor	Landscape		Path Light - Line Voltage	
78352020451	912401335023	CP121-AS7LEDQW		ServiceSmart	12V, LED, Warm 2W T3, Black	C		X				91	Outdoor	Landscape		Path Light LED - Low Voltage	
78352020444	912401335022	CP121-HS7LEDQW		ServiceSmart	12V, LED, Warm 2W T3, Bronze	C		X				91	Outdoor	Landscape		Path Light LED - Low Voltage	
78352020468	912401335024	MUL6-AS7LEDQW		ServiceSmart	12V, LED, Warm 2W T3, Black	C		X				91	Outdoor	Landscape		Path Light LED - Low Voltage	
78352020482	912401335026	MUL4-AS7LEDQW		ServiceSmart	12V, LED, Warm 2W T3, Bronze	C		X				91	Outdoor	Landscape		Path Light LED - Low Voltage	
78352020505	912401335028	RL4-AS7LEDQW		ServiceSmart	12V, LED, Warm 2W T3, Black	C		X				91	Outdoor	Landscape		Path Light LED - Low Voltage	
78352020512	912401335029	RL4-HS7LEDQW		ServiceSmart	12V, LED, Warm 2W T3, Bronze	C		X				91	Outdoor	Landscape		Path Light LED - Low Voltage	
4667723806	912401335031	RL8-AS7LEDQW		ServiceSmart	12V, LED, Warm 2W T3, Black	C		X				91	Outdoor	Landscape		Path Light LED - Low Voltage	
78352019653	912400121561	CP12-AS7		ServiceSmart	12V, 20W T3, Contemporary Path Light, Flat Roof w/Stake, Black	C						92	Outdoor	Landscape		Path Light - Low Voltage	
78352019660	912400121564	CP12-HS7		ServiceSmart	12V, 20W T3, Contemporary Path Light, Flat Roof w/Stake, Bronze	C						92	Outdoor	Landscape		Path Light - Low Voltage	

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
783352019677	912400121567	CP1.21-457		ServiceSmart	12V, 20W T3, Contemporary Path light, Rounded Roof w/Stake, Black	C		X				92	Outdoor	Landscape		Path Light - Low Voltage	
783352019684	912400442159	CP1.21-H57		ServiceSmart	12V, 20W T3, Contemporary Path light, Rounded Roof w/Stake, Bronze	C		X				92	Outdoor	Landscape		Path Light - Low Voltage	
783352005748	912400121611	CUL257	Demoted to B	ServiceSmart	12V, 20W T3, Small Path light w/Stake, Copper		50	X				92	Outdoor	Landscape		Path Light - Low Voltage	
783352005830	912400121621	CUL657		ServiceSmart	12V, 20W T3, Path light w/ Stake, Copper	C		X				92	Outdoor	Landscape		Path Light - Low Voltage	
783352001955	912400121629	CUL757		ServiceSmart	12V, 20W T3, Medium Path light w/ Straight Stem w/ Stake, Copper	C		X				92	Outdoor	Landscape		Path Light - Low Voltage	
783352005892	912400121635	CUL957		ServiceSmart	12V, 20W T3, Large Path light with Stake, Copper	C		X				92	Outdoor	Landscape		Path Light - Low Voltage	
783352019691	912400122613	IGAL3-AC57		ServiceSmart	12V, 10W Xenon T3, Garden Art Line Light Contemporary Path light, Copper	C		X				92	Outdoor	Landscape		Path Light - Low Voltage	
783352008046	912400124995	MUL4-AS7		ServiceSmart	12V, 20W T3, 5m Mushroom w/ lamp, Black	C		X				92	Outdoor	Landscape		Path Light - Low Voltage	
783352008077	912400124999	MUL4-GS7		ServiceSmart	12V, 20W T3, 5m Mushroom w/ lamp, Verde	C		X				92	Outdoor	Landscape		Path Light - Low Voltage	
783352020202	912400124604	MUL4-H57		ServiceSmart	12V, 20W T3, 5m Mushroom w/ lamp, Bronze	C		X				92	Outdoor	Landscape		Path Light - Low Voltage	
783352001948	912400126004	R14-AS7		ServiceSmart	12V, 20W T3, Large Horizon, Black	C		X				92	Outdoor	Landscape		Path Light - Low Voltage	
783352009043	912400126008	R14-H57		ServiceSmart	12V, 20W T3, Large Horizon, Bronze	C		X				92	Outdoor	Landscape		Path Light - Low Voltage	
783352019288	912400140051	R19-AS7		ServiceSmart	12V, 20W T3, Horizon Path Light With Stake, Black	C		X				92	Outdoor	Landscape		Path Light - Low Voltage	
783352019295	912400126053	R19-H57		ServiceSmart	12V, 20W T3, Horizon Path Light With Stake, Bronze	C		X				92	Outdoor	Landscape		Path Light - Low Voltage	
783352014139	912400126858	TUL1-G57		ServiceSmart	12V, 20W T3, 5M Tulip Path light, w/Lamp and Stake, Verde	C		X				92	Outdoor	Landscape		Path Light - Low Voltage	
190096019830	912400122615	GA3-SS7		ServiceSmart	12V, 10W Xenon T3, Garden Art Line Light Contemporary Path light, Stainless Steel	C		X				New	Outdoor	Landscape		Path Light - Low Voltage	
783352012074	912400126875	S24G		ServiceSmart	24" Stem, Verde	C						93	Outdoor	Landscape		Path Light Accessories	
190096019847	912400752745	7.81369E+11		ServiceSmart	941C-HSG/HWR ASSY	C						93	Outdoor	Landscape		Step Light - Line Voltage	
783352021540	912400773820	7.81369E+11		ServiceSmart	942C-HSG/HWR ASSY	C						93	Outdoor	Landscape		Step Light - Line Voltage	
783352010766	912400126253	RSC2AK5E	Demoted to B	SpecSmart	120V, 40W T10 (K5E), 40W T10 (K5E) Louvered Brick light, Black		50	X				93	Outdoor	Landscape		Step Light - Line Voltage	
783352010940	912400126284	RSC2HKF13E	Demoted to B	SpecSmart	120V, 13W PLCL3 (K5F13E), 13W PLCL3 (K5F13E) Louvered Brick light, Bronze		50	X				93	Outdoor	Landscape		Step Light - Line Voltage	
783352010995	912400126294	RSC2HK5E		ServiceSmart	120V, 40W T10 (K5E), 40W T10 (K5E) Louvered Brick light, Bronze	C		X				93	Outdoor	Landscape		Step Light - Line Voltage	
783352021304	912400126236	RSC2AK5HE	Demoted to B	SpecSmart	120V, LED, 3Watt, Louvered Brick light, Black		50					93	Outdoor	Landscape		Step Light LED - Line Voltage	
783352001979	912400124528	M4KM		ServiceSmart	Mounting kit for in Masonry,	C						94	Outdoor	Landscape		Step Light LED - Accessories	
783352010094	912400126188	R52-AHO	Demoted to B	SpecSmart	HSG Only for R5B2/R5C2/R5F2, Black, Black		50	X				94	Outdoor	Landscape		Step Light LED - Accessories	
783352010117	912400126190	R52-HHO		ServiceSmart	HSG Only for R5B2/R5C2/R5F2, Bronze, Bronze	C						94	Outdoor	Landscape		Step Light LED - Accessories	
783352013224	912400128421	TBC303-15		ServiceSmart	Inground Transformer 300W quad tap w/ breakers	C		X				94	Outdoor	Landscape		Transformers/Power Supply	
783352013248	912400128423	TBC603-15		ServiceSmart	Inground Transformer 600W quad tap w/ breakers	C		X				94	Outdoor	Landscape		Transformers/Power Supply	
783352015037	912400128425	TC152-12		ServiceSmart	150VA/150W Transformer, Grey	C		X				94	Outdoor	Landscape		Transformers/Power Supply	
783352015044	912400128427	TC152-12TP		ServiceSmart	150VA/150W Transformer w/Timer & Photo Cell, Grey	C		X				94	Outdoor	Landscape		Transformers/Power Supply	
783352015051	912400128428	TC154-15		ServiceSmart	300VA MULTITAP TFMR, 5M Painted, Hinged Door, Grey	C		X				94	Outdoor	Landscape		Transformers/Power Supply	
783352015068	912400128431	TC154-15		ServiceSmart	600VA MULTITAP TFMR, 5M Painted, Hinged Door, Grey	C		X				94	Outdoor	Landscape		Transformers/Power Supply	
783352015006	912400128444	TSS95-15		ServiceSmart	300VA MULTITAP TFMR, 5M Stainless, Hinged Door, Stainless Steel	C		X				94	Outdoor	Landscape		Transformers/Power Supply	
783352015013	912400128447	TSS654-15		ServiceSmart	600VA MULTITAP TFMR, 5M Stainless, Hinged Door, Stainless Steel	C		X				94	Outdoor	Landscape		Transformers/Power Supply	
662057949970	912400537462	B9DW-H	New Addition	ServiceSmart	120V, LED, Warm, Large Architectural Accent LED, FlexScape, Bronze	C		X				New	Outdoor	Landscape		FlexScape LED - Accent - Line Voltage	
662057949987	912400537463	B9DC-H	New Addition	ServiceSmart	120V, LED, Cool, Large Architectural Accent LED, FlexScape, Black	C		X				New	Outdoor	Landscape		FlexScape LED - Accent - Line Voltage	
662057949994	912400537464	B9DW-A	New Addition	ServiceSmart	120V, LED, Warm, Large Architectural Accent LED, FlexScape, Black	C		X				New	Outdoor	Landscape		FlexScape LED - Accent - Line Voltage	
662057950006	912400537465	B9DC-A	New Addition	ServiceSmart	120V, LED, Cool, Large Architectural Accent LED, FlexScape, Black	C		X				New	Outdoor	Landscape		FlexScape LED - Accent - Line Voltage	
783352014337	912400128719	UWULS16-H		ServiceSmart	12V, 50W, MR16, Micro Underwater, Bronze	C						95	Outdoor	Landscape		Underwater - Low Voltage	
190096019854	912401290010	ZoneScape1-A		ServiceSmart	Low Voltage App Based Control System	C		X				New	Outdoor	Landscape			