

Indoor/Outdoor Luminaire Smart Service Guide File "Trimmed" - Rev: February 1, 2017

Additional Sorting / Filtering Fields

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
66205789261	912400526316	LLAV11AHAL		ServiceSmart	Alcyon LED VERT 600/1000 ACC HOLDER AL	N						New	IPS	Accent/Track Lighting		Alcyon LED Vertical	Accessories
662057949734	912401052795	LLAV2030WH		ServiceSmart	Alcyon LED Vert. 2000lm 80 CR 3000K WH	N			X			New	IPS	Accent/Track Lighting		Alcyon LED Vertical	Track head
190096019663	912401051469	LLAV3030WH		ServiceSmart	Alcyon LED Vert. 3000lm 80 CR 3000K WH	N			X			New	IPS	Accent/Track Lighting		Alcyon LED Vertical	Track head
662057542034	912400526405	LLAV1130WH		ServiceSmart	Alcyon LED Vertical Cylinder 3000K 1200L White	N						8	IPS	Accent/Track Lighting		Alcyon LED Vertical	
66205789609	912400520464	LLAV12RF		ServiceSmart	Alcyon LED Vertical 600/1000 Cylinder Reflector Narrow Spot	N			X			9	IPS	Accent/Track Lighting		Alcyon LED Vertical	
662057896816	912400520529	LLAV11RNF		ServiceSmart	Alcyon LED Vertical 600/1000 Cylinder Reflector Spot	C.N			X			9	IPS	Accent/Track Lighting		Alcyon LED Vertical	
662057896793	912400520530	LLAV11RNS		ServiceSmart	Alcyon LED Vertical 600/1000 Cylinder Reflector Narrow Flood	C.N						9	IPS	Accent/Track Lighting		Alcyon LED Vertical	
662057897110	912400520465	LLAV11RS		ServiceSmart	Alcyon LED Vertical 600/1000 Cylinder Reflector Flood	N			X			9	IPS	Accent/Track Lighting		Alcyon LED Vertical	
662057896786	912400520532	LLAV12RNS		ServiceSmart	Alcyon LED Vertical 2000 Cylinder Reflector Spot	N.L			X			9	IPS	Accent/Track Lighting		Alcyon LED Vertical	
662057542041	912400526404	LLAV1130BK		SpecSmart	Alcyon LED Vertical Cylinder 3000K 1000L Black		100					8	IPS	Accent/Track Lighting		Alcyon LED Vertical	
662057896779	912400520466	LLAV12RF		ServiceSmart	Alcyon LED Vertical 2000 Cylinder Reflector Flood	N			X			9	IPS	Accent/Track Lighting		Alcyon LED Vertical	
662057896762	912400520531	LLAV12RNF		ServiceSmart	Alcyon LED Vertical 2000 Cylinder Reflector Narrow Flood	N			X			9	IPS	Accent/Track Lighting		Alcyon LED Vertical	
662057896755	912400520467	LLAV12RS		ServiceSmart	Alcyon LED Vertical 2000 Cylinder Reflector Narrow Spot	N			X			9	IPS	Accent/Track Lighting		Alcyon LED Vertical	
662057949741	912401052796	LLAV2030BK	New Addition	SpecSmart	Alcyon LED Vert. 2000lm 80 CR 3000K BK		100		X			New	IPS	Accent/Track Lighting		Alcyon LED Vertical	Track head
662057949826	912401052805	LLAV20930WHCW	New Addition	SpecSmart	Alcyon LED Vert. 2000lm 90 CR 3000K WH CW		100		X			New	IPS	Accent/Track Lighting		Alcyon LED Vertical	Track head
190096019502	912401053470	LLAV3030BK	New Addition	SpecSmart	Alcyon LED Vert. 3000lm 90 CR 3000K BK		100		X			New	IPS	Accent/Track Lighting		Alcyon LED Vertical	Track head
662057935331	912400531212	LT08RNF830BK		ServiceSmart	FLATBACK CYLINDER LED TRACK 800LM 25DEG	N			X			8	IPS	Accent/Track Lighting		CarePro LED Mini-Cylinder LED	
662057935348	912400531211	LT08RNF830WH		ServiceSmart	FLATBACK CYLINDER LED TRACK 800LM 25DEG	C.N			X			8	IPS	Accent/Track Lighting		CarePro LED Mini-Cylinder LED	
662057935355	912400531214	LT08RWF830BK		ServiceSmart	FLATBACK CYLINDER LED TRACK 800LM 40DEG	N			X			8	IPS	Accent/Track Lighting		CarePro LED Mini-Cylinder LED	
662057935324	912400531213	LT08RWF830WH		ServiceSmart	FLATBACK CYLINDER LED TRACK 800LM 40DEG	C.N			X			8	IPS	Accent/Track Lighting		CarePro LED Mini-Cylinder LED	
662057913438	912400527070	LLAVRM1H12120		SpecSmart	Recessed Alcyon LED FIX 120V 1Head 600/1000Lm		100		X			9	IPS	Accent/Track Lighting		Alcyon LED Recessed	Frames
662057913452	912400527072	LLAVRM1H2120		SpecSmart	Recessed Alcyon LED FIX 120V 2Head 600/1000Lm		100		X			9	IPS	Accent/Track Lighting		Alcyon LED Recessed	Frames
662057913476	912400527073	LLAVRM1H2277		SpecSmart	Recessed Alcyon LED FIX 27V 2Head 600/1000Lm		100		X			9	IPS	Accent/Track Lighting		Alcyon LED Recessed	Frames
662057913490	912400527074	LLAVRM1H3120		SpecSmart	Recessed Alcyon LED FIX 120V 3Head 600/1000Lm		100		X			9	IPS	Accent/Track Lighting		Alcyon LED Recessed	Frames
662057913506	912400527075	LLAVRM1H3277		SpecSmart	Recessed Alcyon LED FIX 27V 3Head 600/1000Lm		100		X			9	IPS	Accent/Track Lighting		Alcyon LED Recessed	Frames
662057913537	912400527077	LLAVRM1H4277		SpecSmart	Recessed Alcyon LED FIX 27V 4Head 600/1000Lm		100		X			9	IPS	Accent/Track Lighting		Alcyon LED Recessed	Frames
662057913568	912400527080	LLAVRM1H2120		SpecSmart	Recessed Alcyon LED FIX 120V 2Head 2000Lm		100		X			9	IPS	Accent/Track Lighting		Alcyon LED Recessed	Frames
662057913582	912400527082	LLAVRM1H3120		SpecSmart	Recessed Alcyon LED FIX 120V 3Head 2000Lm		100		X			9	IPS	Accent/Track Lighting		Alcyon LED Recessed	Frames
662057913605	912400527084	LLAVRM1H4120		SpecSmart	Recessed Alcyon LED FIX 120V 4Head 2000Lm		100		X			9	IPS	Accent/Track Lighting		Alcyon LED Recessed	Frames
662057912943	912400527025	LLAVRMWH1130H2		SpecSmart	Recessed Alcyon LED White 3000K 2Head 1000Lm w/Trim		100		X			9	IPS	Accent/Track Lighting		Alcyon LED Recessed	Trims-Light Engines
662057912967	912400527027	LLAVRMWH1130H3		SpecSmart	Recessed Alcyon LED White 3000K 3Head 1000Lm w/Trim		100		X			9	IPS	Accent/Track Lighting		Alcyon LED Recessed	Trims-Light Engines
662057898247	912400525203	LLAV11AHWH		ServiceSmart	Alcyon LED Vertical Accent 600/1000 Cylinder Acc. Holder White	N						9	IPS	Accent/Track Lighting		Alcyon LED Vertical Accessories	Accessories
662057898582	912400526277	LLAV11FR		ServiceSmart	Alcyon LED Frosted Etched Film 3" 600/1000lm	N						9	IPS	Accent/Track Lighting		Alcyon LED Vertical Accessories	Accessories
662057898520	912400526271	LLAV11LS		ServiceSmart	Alcyon LED Linear Spread Film 3" 600/1000lm	N						9	IPS	Accent/Track Lighting		Alcyon LED Vertical Accessories	Accessories
662057898568	912400526275	LLAV11SF		ServiceSmart	Alcyon LED Soft Focus Film 3" 600/1000lm	N						9	IPS	Accent/Track Lighting		Alcyon LED Vertical Accessories	Accessories
662057898544	912400526273	LLAV11SY		ServiceSmart	Alcyon LED System Spread Film 3" 600/1000lm	N						9	IPS	Accent/Track Lighting		Alcyon LED Vertical Accessories	Accessories
662057579951	912400492429	LFZ1V8K		ServiceSmart	LIGHT FLOOD LED VERTICAL BLADE DOUBER BK	N						New	IPS	Accent/Track Lighting		LightFlood	Accessories
662057784946	912400492430	LFZ2VAL		ServiceSmart	TRK HD FLD 2LM VISOR W/ROCK REFLECTOR AL	N						New	IPS	Accent/Track Lighting		LightFlood	Accessories
662057578831	912400492423	LFZ3SAL		SpecSmart	TRACK LED FLOOD 2000LM 3000K HD AL		100		X			New	IPS	Accent/Track Lighting		LightFlood	Track head
662057784939	912400492432	LFZ2VWH	New Addition	ServiceSmart	TRK HD FLD 2LM VISOR W/ROCK REFLECTOR WH	N						New	IPS	Accent/Track Lighting		LightFlood	Accessories
784197008628	912400462560	8122WH		SpecSmart	MINI MID CYL. 70W, T6 G12 WH NO REFLECTOR		100					New	IPS	Accent/Track Lighting		Mini HD	Track head
662057497938	912400474076	LLAV0030WH		ServiceSmart	Vertical LED Micro Cylinder 3000K White	N						10	IPS	Accent/Track Lighting		Mini LED Micro	
999999141170	912400468443	23SNT6WH		ServiceSmart	SpotLED SMDOT FOR 1000/2000 Lm WH	N.L						New	IPS	Accent/Track Lighting		Spot LED	Accessories
662057654935	912400471841	LLAB1AHBK		ServiceSmart	Spot LED LARGE SPOT ACC HOLDER, BLACK	N						New	IPS	Accent/Track Lighting		Spot LED	Accessories
999999141194	912400468439	23SN30BK		ServiceSmart	SpotLED SMDOT FOR 600 Lm BK	N						New	IPS	Accent/Track Lighting		Spot LED	Accessories
662057887173	912400520528	LLAB5AHWH		ServiceSmart	SpotLED SMALL ACCESSORY HOLDER, WHITE	N						New	IPS	Accent/Track Lighting		Spot LED	Accessories
662057955810	912401053051	LLAB030RPHVA		SpecSmart	SpotLED 1000lm 3000K Flood WH VA		100		X			New	IPS	Accent/Track Lighting		Spot LED	Track head
662057955759	912401053045	LLAB030RNF8KVA		ServiceSmart	SpotLED 1000lm 3000K NF BK VA	N			X			New	IPS	Accent/Track Lighting		Spot LED	Track head
662057955728	912401053042	LLAB030RNFPHVA		ServiceSmart	SpotLED 1000lm 3000K NF WH VA	N			X			New	IPS	Accent/Track Lighting		Spot LED	Track head
662057955650	912401053033	LLAB030RPHVA		SpecSmart	SpotLED 1000lm 3000K Spot WH VA		100		X			New	IPS	Accent/Track Lighting		Spot LED	Track head
662057947037	912401052651	LLAB130RFBKVA		SpecSmart	SpotLED 2000lm 3000K Flood BK VA		100		X			New	IPS	Accent/Track Lighting		Spot LED	Track head
662057946993	912401052648	LLAB130RPHVA		ServiceSmart	SpotLED 2000lm 3000K Flood WH VA	N			X			New	IPS	Accent/Track Lighting		Spot LED	Track head
662057946900	912401052639	LLAB130RNFPHVA		ServiceSmart	SpotLED 2000lm 3000K NF WH VA	N			X			New	IPS	Accent/Track Lighting		Spot LED	Track head

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
662057958279	912401053206	LIAB330RNFVHVA		ServiceSmart	SpotLED 3000lm 2000K NF WH VA	C.N.I.			X			New	IPS	Accent/Track Lighting		Spot LED	Track head
662057958187	912401053196	LIAB330R5WHVA		ServiceSmart	SpotLED 3000lm 3000K Spot WH VA	N			X			New	IPS	Accent/Track Lighting		Spot LED	Track head
662057655033	912400479788	LIAB330RNF8K		SpecSmart	Spot LED Small Narrow Flood 3000K Black		100		X			10	IPS	Accent/Track Lighting		Spot LED	
662057962153	912400608442	23JNT6BK		ServiceSmart	SpotLED Snoop for 1000/2000 Lm Black	N						10	IPS	Accent/Track Lighting		Spot LED	
662057657080	912400473842	LIAB1AHVWH		ServiceSmart	Spot LED Large Spot ACC Holder, White	N						10	IPS	Accent/Track Lighting		Spot LED	
662057955841	9124010531054	LIAB030RFBKVA	New Addition	SpecSmart	SpotLED 1000lm 3000K Flood BK VA		100		X			New	IPS	Accent/Track Lighting		Spot LED	Track head
662057946825	912401052630	LIAB130R5WHVA	New Addition	SpecSmart	SpotLED 2000lm 3000K Spot WH VA		100		X			New	IPS	Accent/Track Lighting		Spot LED	Track head
662057958378	912401053209	LIAB330RNF8KVA	New Addition	SpecSmart	SpotLED 3000lm 3000K NF BK VA		100		X			New	IPS	Accent/Track Lighting		Spot LED	Track head
662057958217	912401053199	LIAB330R5BKVA	New Addition	SpecSmart	SpotLED 3000lm 3000K Spot BK VA		100		X			New	IPS	Accent/Track Lighting		Spot LED	Track head
662057756677	912400471841	LIABR17MK		ServiceSmart	RECESSED SPOTLED MUD-IN KIT, 17" LENGTH	N						New	IPS	Accent/Track Lighting		Spot LED RM	Accessories
662057772028	912400470466	LIABR17VWH		ServiceSmart	RECESSED SPOTLED TRIM SECTION, 17" LENGT	N			X			New	IPS	Accent/Track Lighting		Spot LED RM	Track head
784197483654	912400640058	2256AL		ServiceSmart	ALCYON MR16 ENCLOSED STEP SPOT	N						New	IPS	Accent/Track Lighting		Alcyon	Track head
784197483944	912400640038	22DR2BK		ServiceSmart	ALCYON PAR20 RING	N						New	IPS	Accent/Track Lighting		Alcyon	Track head
784197483975	912400640041	22DR3BK		ServiceSmart	ALCYON PAR30 RING	N						New	IPS	Accent/Track Lighting		Alcyon	Track head
784197483968	912400640042	22DR3WH		ServiceSmart	ALCYON PAR30 RING	N						New	IPS	Accent/Track Lighting		Alcyon	Track head
784197484002	912400640047	22DR8BK		ServiceSmart	ALCYON PAR38 RING	N						New	IPS	Accent/Track Lighting		Alcyon	Track head
784197483999	912400640048	22DR8WH		ServiceSmart	ALCYON PAR38 RING	N						New	IPS	Accent/Track Lighting		Alcyon	Track head
784197522483	912400640050	2256BK		ServiceSmart	ALCYON MR16 SHOOT BLACK ALUMINUM	N						New	IPS	Accent/Track Lighting		Alcyon	Track head
784197483890	912400640055	2253AL		ServiceSmart	ALCYON PAR30 ENCLOSED STEP SPOT	N.L						New	IPS	Accent/Track Lighting		Alcyon	Track head
784197525248	912400640062	2253BK		ServiceSmart	ALCYON PAR38 ENCLOSED STEP SPOT	N						New	IPS	Accent/Track Lighting		Alcyon	Track head
784197483906	912400640063	2253WH		ServiceSmart	ALCYON PAR38 ENCLOSED STEP SPOT	N						New	IPS	Accent/Track Lighting		Alcyon	Track head
784197483692	912400640023	22G0VWH		ServiceSmart	Alcyon MR16 Glass Cylinder White	N						11	IPS	Accent/Track Lighting		Alcyon	
784197483753	912400640026	22G0RWH		ServiceSmart	Alcyon MR16 Glass Ring White	N						11	IPS	Accent/Track Lighting		Alcyon	
784197483685	912400640027	22M0CAL		ServiceSmart	Alcyon MR16 Mini Cylinder Aluminum	N						11	IPS	Accent/Track Lighting		Alcyon	
784197483678	912400640028	22M0GBK		ServiceSmart	Alcyon MR16 Mini Cylinder Black	N						11	IPS	Accent/Track Lighting		Alcyon	
784197483661	912400640029	22M0VWH		ServiceSmart	Alcyon MR16 Mini Cylinder White	N		X				11	IPS	Accent/Track Lighting		Alcyon	
784197483784	912400640036	22M0VWH		ServiceSmart	Alcyon MR16 Mini Round Wall Washer White	N						11	IPS	Accent/Track Lighting		Alcyon	
784197483739	912400640044	220r6BK		ServiceSmart	Alcyon MR16 Open Ring Black	N						11	IPS	Accent/Track Lighting		Alcyon	
784197483722	912400640045	220r6WH		ServiceSmart	Alcyon MR16 Open Ring White	N		X				11	IPS	Accent/Track Lighting		Alcyon	
784197483845	912400640054	22532WH		ServiceSmart	Alcyon PAR20 Enclosed Step Spot White	N.L						11	IPS	Accent/Track Lighting		Alcyon	
784197483883	912400640056	22533BK		ServiceSmart	Alcyon PAR30 Enclosed Step Spot Black	N						11	IPS	Accent/Track Lighting		Alcyon	
784197483876	912400640057	22533WH		ServiceSmart	Alcyon PAR30 Enclosed Step Spot White	N						11	IPS	Accent/Track Lighting		Alcyon	
784197483647	912400640059	2256BK		ServiceSmart	Alcyon MR16 Enclosed Step Spot Black	N						11	IPS	Accent/Track Lighting		Alcyon	
784197483630	912400640060	2256VWH		ServiceSmart	Alcyon MR16 Enclosed Step Spot White	N		X				11	IPS	Accent/Track Lighting		Alcyon	
784197483852	912400640053	22532BK	New Addition	ServiceSmart	ALCYON PAR20 ENCLOSED STEP SPOT	N						New	IPS	Accent/Track Lighting		Alcyon	Track head
784197483869	912400640052	22532AL	New Addition	ServiceSmart	ALCYON PAR20 ENCLOSED STEP SPOT	N						New	IPS	Accent/Track Lighting		Alcyon	Track head
662057287768	912400471825	LIAD1AHBK		ServiceSmart	ALCYON LED SMALL CYLINDER ACC HOLDER BLACK	N						New	IPS	Accent/Track Lighting		Alcyon LED Horizontal II	Accessories
662057287751	912400471826	LIAD1AHVWH		ServiceSmart	ALCYON LED SMALL CYLINDER ACC HOLDER WHI	N						New	IPS	Accent/Track Lighting		Alcyon LED Horizontal II	Accessories
662057287706	912400471828	LIAD19VWH		ServiceSmart	ALCYON LED SMALL CYLINDER SNOOT WHITE	N						New	IPS	Accent/Track Lighting		Alcyon LED Horizontal II	Accessories
662057287737	912400471839	LIAD19NBK		ServiceSmart	ALCYON LED MEDIUM CYLINDER SNOOT BLACK	N						New	IPS	Accent/Track Lighting		Alcyon LED Horizontal II	Accessories
662057287720	912400471840	LIAD19VWH		ServiceSmart	ALCYON LED MEDIUM CYLINDER SNOOT WHITE	N						New	IPS	Accent/Track Lighting		Alcyon LED Horizontal II	Accessories
662057986371	912401050187	L1RF		ServiceSmart	Alcyon Reflector Flood	N						New	IPS	Accent/Track Lighting		Alcyon LED Horizontal II	Reflector
662057986364	912401050186	L1RFN		ServiceSmart	Alcyon Reflector Narrow Flood	N						New	IPS	Accent/Track Lighting		Alcyon LED Horizontal II	Reflector
662057986357	912401050185	L1RS		ServiceSmart	Alcyon Reflector Spot	N						New	IPS	Accent/Track Lighting		Alcyon LED Horizontal II	Reflector
662057983576	912401050170	LIAD11830WTE		ServiceSmart	Alcyon Hor 1100lm 3000K 30K WH ELV/Trac	N			X			New	IPS	Accent/Track Lighting		Alcyon LED Horizontal II	Track head
662057983714	912401050182	LIAD11930WTECW		SpecSmart	Alcyon Hor 1100lm 3000K 30K WH ELV/TV CW	N	100		X			New	IPS	Accent/Track Lighting		Alcyon LED Horizontal II	Track head
662057287812	912400492415	LIADCA11	New Addition	ServiceSmart	ALCYON LED MEDIUM CYLINDER HEX CELL LOUV	N						New	IPS	Accent/Track Lighting		Alcyon LED Horizontal II	Accessories
784197902117	912400602728	9021BK		ServiceSmart	Mini Universal 250W Max Matte Black	C.N		X				11	IPS	Accent/Track Lighting		Mini Universal	
784197902100	912400602730	9021WH		ServiceSmart	Mini Universal 250W Max Matte White	C.N		X				11	IPS	Accent/Track Lighting		Mini Universal	
784197207335	912400602728	9021AL	New Addition	ServiceSmart	MINI UNIVERSAL 250W MAX SATIN ALUM	N						New	IPS	Accent/Track Lighting		Mini Universal	Track head
784197272197	912400604222	7515		ServiceSmart	4" RECESSED HOUSING	N						New	IPS	Accent/Track Lighting		Rings	Track head
784197762827	912400603655	6284		SpecSmart	120V Halogen Spot PAR30 Ring Matte White		100					11	IPS	Accent/Track Lighting		Rings	
784197762841	912400603667	6284		SpecSmart	PAR Ring, PAR38 250W Max. White		100					11	IPS	Accent/Track Lighting		Rings	
784197627805	912400602361	6278WH	Promoted to A	ServiceSmart	120V Halogen Spot PAR20 Ring Matte White	N						11	IPS	Accent/Track Lighting		Rings	

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
662057905907	912400528334	9030NBK		ServiceSmart	Lytspan Gimbal Ring PAR30 BK	N						11	IPS	Accent/Track Lighting		Rings	
662057905914	912400528335	9030NWH		ServiceSmart	Lytspan Gimbal Ring PAR30 WH	N						11	IPS	Accent/Track Lighting		Rings	
662057905938	912400528336	9038NBK		ServiceSmart	Lytspan Gimbal Ring PAR38 BK	C,N						11	IPS	Accent/Track Lighting		Rings	
662057905945	912400528337	9038NWH		ServiceSmart	Lytspan Gimbal Ring PAR38 WH	N						11	IPS	Accent/Track Lighting		Rings	
784197826993	912400466884	8410EBK		ServiceSmart	TRACK POWER JACK WITH ELECTRONIC	N						New	IPS	Accent/Track Lighting		SoftTech	Accessories
784197826997	912400466902	86758BK		ServiceSmart	SOFT-TECH MR16 BI-PIN RING FOCAL JACK	N						New	IPS	Accent/Track Lighting		SoftTech	Accessories
784197842000	912400462652	8420WH		ServiceSmart	Soft-Edge Spot5 PAR20 Matte White	N						11	IPS	Accent/Track Lighting		SoftTech	Frames
784197627225	912400462358	6272BK		ServiceSmart	SOFT EDGE SPOT AR70 MAT BLK	N						New	IPS	Accent/Track Lighting		SoftTech	Track head
784197627522	912400465153	62758BK		ServiceSmart	SOFT EDGE RING MR16 BIPIN MAT BLK	N						New	IPS	Accent/Track Lighting		SoftTech	Track head
784197841607	912400462649	8416WH		ServiceSmart	SOFT-EDGE SPOTS PAR16 MAT WHT	N						New	IPS	Accent/Track Lighting		SoftTech	Track head
784197843021	912400462654	8430BK		ServiceSmart	SOFT-EDGE SPOTS PAR30 MAT BLK	N						New	IPS	Accent/Track Lighting		SoftTech	Track head
784197843007	912400462655	8430WH		ServiceSmart	SOFT-EDGE SPOTS PAR30 MAT WHT	N						New	IPS	Accent/Track Lighting		SoftTech	Track head
784197627218	912400462359	6272WH		ServiceSmart	SOFT EDGE SPOT AR70 MAT WHT	N						New	IPS	Accent/Track Lighting		SoftTech	Track head
784197832025	912400462635	8320BK		ServiceSmart	SOFT-EDGE RING PAR20 MAT BLK	N						New	IPS	Accent/Track Lighting		SoftTech	Track head
784197833022	912400462638	8330BK		ServiceSmart	SOFT-EDGE RING PAR30 MAT BLK	N						New	IPS	Accent/Track Lighting		SoftTech	Track head
784197833008	912400462639	8330WH		ServiceSmart	SOFT-EDGE RING PAR30 MAT WHT	N						New	IPS	Accent/Track Lighting		SoftTech	Track head
784197526813	912400465156	62768BK		ServiceSmart	Soft Tech Spot MR 16 Bi-Pin Matte Black	N						11	IPS	Accent/Track Lighting		SoftTech	
784197526806	912400465157	62768WH		ServiceSmart	Soft Tech Spot MR 16 Bi-Pin Matte White	N		X				11	IPS	Accent/Track Lighting		SoftTech	
784197842024	912400462653	8420BK		ServiceSmart	Soft-Edge Spot5 PAR20 Matte Black	N		X				11	IPS	Accent/Track Lighting		SoftTech	
784197627515	912400465154	62758WH	New Addition	ServiceSmart	SOFT EDGE RING MR16 BIPIN MAT WHT	N						New	IPS	Accent/Track Lighting		SoftTech	Track head
784197833800	912400462642	8338WH	New Addition	ServiceSmart	SOFT-EDGE RING PAR38 MAT WHT	N						New	IPS	Accent/Track Lighting		SoftTech	Track head
784197823706	912400462610	8257WH		ServiceSmart	PAR20 WIRE Ring LyteSpot/White	N						12	IPS	Accent/Track Lighting		Lasso	
784197251093	912400460928	9175NWH		ServiceSmart	MINIFORMS MR16 SHALLOW RING-WHITE	N						New	IPS	Accent/Track Lighting		Miniforms	Accessories
784197817142	912400460922	91738BK		ServiceSmart	Low Volt MR16 Bi-Pin Cylinder Matte Black	N						12	IPS	Accent/Track Lighting		Miniforms	
784197917128	912400460923	91738WH		ServiceSmart	Low Volt MR16 Bi-Pin Cylinder Matte White	N						12	IPS	Accent/Track Lighting		Miniforms	
784197251086	912400460927	91758BK	New Addition	ServiceSmart	MINIFORMS MR16 SHALLOW RING-BLACK	N						New	IPS	Accent/Track Lighting		Miniforms	Accessories
784197823610	912400462592	8236WH		ServiceSmart	PAR30 CYLINDER SHADE ONLY/WHT	N						New	IPS	Accent/Track Lighting		ParTech	Accessories
784197823702	912400462594	8237WH		ServiceSmart	PAR30 BEZEL SHADE ONLY/WHT	N						New	IPS	Accent/Track Lighting		ParTech	Accessories
784197823900	912400462601	8239WH		ServiceSmart	PAR-TECH PAR30 MESH SHADE MATTE WHT	N						New	IPS	Accent/Track Lighting		ParTech	Accessories
784197823719	912400462593	8237BK		ServiceSmart	PAR30 BEZEL SHADE ONLY/BLK	N						New	IPS	Accent/Track Lighting		ParTech	Accessories
784197821500	912400462574	8215WH		ServiceSmart	PAR16 CONE SHADE ONLY/WHT	N						New	IPS	Accent/Track Lighting		ParTech	Track head
784197822514	912400462578	8225BK		ServiceSmart	PAR20 CONE SHADE ONLY/BLK	N						New	IPS	Accent/Track Lighting		ParTech	Track head
784197822507	912400462580	8225WH		ServiceSmart	PAR20 CONE SHADE ONLY/WHT	N						New	IPS	Accent/Track Lighting		ParTech	Track head
784197822804	912400462582	8228WH		ServiceSmart	PAR-TECH PAR20 RING SHADE MATTE WHT	N						New	IPS	Accent/Track Lighting		ParTech	Track head
784197822903	912400462588	8229WH		ServiceSmart	PAR-TECH PAR20 MESH SHADE MATTE WHT	N						New	IPS	Accent/Track Lighting		ParTech	Track head
784197820114	912400462569	8201BK		ServiceSmart	Low Profile Universal LyteSpot/Black	N		X				12	IPS	Accent/Track Lighting		ParTech	
784197820107	912400462570	8201WH		ServiceSmart	Low Profile Universal LyteSpot/White	N		X				12	IPS	Accent/Track Lighting		ParTech	
784197820213	912400462571	8202BK		ServiceSmart	Hinged Universal LyteSpot/Black	N						12	IPS	Accent/Track Lighting		ParTech	
784197820206	912400462572	8202WH		ServiceSmart	Hinged Universal LyteSpot/White	N						12	IPS	Accent/Track Lighting		ParTech	
784197823511	912400462589	8235BK		ServiceSmart	PAR30 Cone Shade only/Black	N						12	IPS	Accent/Track Lighting		ParTech	
784197823504	912400462590	8235WH		ServiceSmart	PAR30 Cone Shade only/White	N						12	IPS	Accent/Track Lighting		ParTech	
784197823627	912400462591	8236BK		ServiceSmart	PAR30 Cylinder Shade only/Black	N						12	IPS	Accent/Track Lighting		ParTech	
784197822606	912400462583	8226WH	New Addition	ServiceSmart	PAR20 CYLINDER SHADE ONLY/WHT	N						New	IPS	Accent/Track Lighting		ParTech	Track head
784197822705	912400462584	8227WH	New Addition	ServiceSmart	PAR20 BEZEL SHADE ONLY/WHT	N						New	IPS	Accent/Track Lighting		ParTech	Track head
784197825713	912400462609	8257BK	New Addition	ServiceSmart	PAR20 WIRE RING LYTESPOT/BLK	N						New	IPS	Accent/Track Lighting		ParTech	Accessories
784197953003	912400462882	9530BK		ServiceSmart	R-30 ROUND BACK CYLINDER MAT BLK	N						New	IPS	Accent/Track Lighting		Roundback Cylinder	Track head
784197963002	912400462886	9630BK		ServiceSmart	R-30 STEP CYLINDER MAT BLK	N						New	IPS	Accent/Track Lighting		Roundback Cylinder	Track head
784197912031	912400462751	9120WH		SpecSmart	R20 ROUND BACK CYLINDER MATTE WHITE		100					12	IPS	Accent/Track Lighting		Roundback Cylinder	
784197953034	912400462883	9530WH		ServiceSmart	R30 ROUND BACK CYLINDER MATTE WHITE	N						12	IPS	Accent/Track Lighting		Roundback Cylinder	
784197963033	912400462887	9630WH		ServiceSmart	R30 STEP CYLINDER MATTE WHITE	N						12	IPS	Accent/Track Lighting		Step Cylinder	
784197116170	912400461198	AF2AS	Promoted to A	ServiceSmart	Spread Lens Asymmetrical 5X5 DEG Beam Spread	N						13	IPS	Accent/Track Lighting		Accessories	Accessories
784197477998	912400461199	AF2FR		SpecSmart	Frosted Softening Lens, 2" Diameter		100					13	IPS	Accent/Track Lighting		Accessories	Accessories
784197282424	912400461205	AF2SF		ServiceSmart	White Diffusion Lens, 2" Diameter	N						13	IPS	Accent/Track Lighting		Accessories	Accessories
784197116163	912400461206	AF2SY	Promoted to A	ServiceSmart	Spread Lens Symmetrical 55 DEG Beam	N						13	IPS	Accent/Track Lighting		Accessories	Accessories

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category	
784197115975	912400461216	4F4AS		SpecSmart	Spread Lens for Adu 6"X8" HXMG S455 DEG		100						13	IPS	Accent/Track Lighting		Accessories	Accessories
784197162696	912400462985	AL2HC		ServiceSmart	2.5" Hex Cell Louver	N							13	IPS	Accent/Track Lighting		Accessories	Accessories
784197116118	912400461234	AL2HC		ServiceSmart	2" Hex Cell Louver	N							13	IPS	Accent/Track Lighting		Accessories	Accessories
784197162931	912400461235	AL3HC		ServiceSmart	3 3/4" Hex Cell Louver	N							13	IPS	Accent/Track Lighting		Accessories	Accessories
784197162641	912400462973	AF2SAS		ServiceSmart	2.5" SPREAD LENS ADYMETRICAL 5.55 DEG	N							New	IPS	Accent/Track Lighting		Accessories	Accessories
784197594183	912400465046	600N8K		ServiceSmart	2"IND Basic Track Black	N		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594190	912400465047	600NWH		ServiceSmart	2"IND Basic Track White	N		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594205	912400465049	600I8K		ServiceSmart	4"IND Basic Track Black	N		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594213	912400465050	600I8WH		ServiceSmart	4"IND Basic Track White	C,NL		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197539801	912400465051	6002NAL		SpecSmart	8" IND Basic Metallic Aluminum		100						13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594220	912400465052	6002NBK		ServiceSmart	8"IND Basic Track Black	N		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594237	912400465053	6002NWH		ServiceSmart	8"IND Basic Track White	C,NL		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594244	912400465055	6003NBK		SpecSmart	8"Join Basic Track MT Black		100						13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594251	912400465056	6003NWH		ServiceSmart	8"Join Basic Track White	N		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197539771	912400465057	6004NAL		SpecSmart	4" IND Basic Track w/o Live End Aluminum		100						13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594268	912400465058	6004NBK		ServiceSmart	4"IND Basic Track w/o Live End Black	N		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594275	912400465059	6004NWH		ServiceSmart	4"IND Basic Track w/o Live End White	N		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197539733	912400465063	6008NAL		SpecSmart	8" IND Basic Track w/o Live End Aluminum		100						13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594282	912400465064	6008NBK		ServiceSmart	8"IND Basic Track w/o Live End Black	C,NL		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594299	912400465065	6008NWH		ServiceSmart	8"IND Basic Track w/o Live End White	C,NL		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594541	912400465070	6048NBK		ServiceSmart	Basic PWR Extension Connector Black	C,NL		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594558	912400465071	6048NWH		SpecSmart	Basic PWR Extension Connector White		100						13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197539737	912400465072	6048NAL		SpecSmart	Basic Live End Aluminum		100						13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594589	912400465073	6048NBK		ServiceSmart	Basic Live End Black	N		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594596	912400465074	6048NWH		ServiceSmart	Basic Live End White	C,NL		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197539474	912400465075	6049NAL		SpecSmart	Basic Mini Coupler Aluminum		100						13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594565	912400465076	6049NBK		ServiceSmart	Basic Mini Coupler Black	N		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594572	912400465077	6049NWH		ServiceSmart	Basic Mini Coupler White	C,NL		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594466	912400465079	6050NBK		SpecSmart	Basic "L" Connector Black		100						13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594473	912400465080	6050NWH		ServiceSmart	Basic "L" Connector White	N		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594480	912400465082	6051NBK		ServiceSmart	Basic "T" Connector Black	N		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594497	912400465083	6051NWH		ServiceSmart	Basic "T" Connector White	N		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594503	912400465085	6052NBK		SpecSmart	Basic "X" Connector Black		100	X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594329	912400465093	6054NBK		SpecSmart	Basic In-Line Connector Black		100						13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594330	912400465092	6054NWH		ServiceSmart	Basic In-Line Connector White	N		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197606015	912400462273	6060BK		ServiceSmart	End Feed Canopy Black	N		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197606008	912400462274	6060WH		ServiceSmart	End Feed Canopy White	N		X					13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197606107	912400462276	6061WH		ServiceSmart	Floating Canopy White	N							13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197606312	912400462275	6063BK		SpecSmart	Floating Power Feed Black		100						13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197606305	912400462280	6063WH		SpecSmart	Floating Power Feed White		100						13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197607401	912400462284	6074WH		SpecSmart	Lytespot Extension Wand 18" White		100						13	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197564537	912400465032	56451BK		SpecSmart	FLUSH MTG CLIP FOR LYTESPAN TRK/MAT BLK		100						New	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197564520	912400465033	56451WH		SpecSmart	FLUSH MTG CLIP FOR LYTESPAN TRK/MAT WHT		100						New	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197606114	912400462275	6061BK		ServiceSmart	FLOATING CANOPY BK /REPLS 6071	N							New	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197594749	912400465093	6065NAL		ServiceSmart	END FED CANOPY ALUMINUM	N							New	IPS	Accent/Track Lighting		Basic Track & Accessories	Accessories
784197519124	912400465093	8476NWH		ServiceSmart	2 X 54W T5 HO FLOOD 4' MATTE WHITE	N							New	IPS	Accent/Track Lighting		PowerWash	Track head
784197302658	912400462870	8477WH		ServiceSmart	1 X 54W T5 HO FLOOD 4' MATTE WHITE	N							New	IPS	Accent/Track Lighting		PowerWash	Track head
784197302498	912400462819	9276WH		ServiceSmart	2 X 24W T5 HO Flood 2' Matte White	N							13	IPS	Accent/Track Lighting		PowerWash	
784197556075	912400491429	F861		ServiceSmart	TANGENT SURFACE FEED CANOPY	N							New	IPS	Accent/Track Lighting		Tangent	Accessories
784197555795	912400461435	FX35S		ServiceSmart	TANGENT SOFT COBE 120V GU/6Z 10	N							New	IPS	Accent/Track Lighting		Tangent	Track head
784197555818	912400491420	FX04		ServiceSmart	Tangent Track 4' Clear Anodize	N							13	IPS	Accent/Track Lighting		Tangent	
784197555856	912400491421	FX08		ServiceSmart	Tangent Track 8' Clear Anodize	N							13	IPS	Accent/Track Lighting		Tangent	
784197555696	912400461431	FX16C		ServiceSmart	Tangent Mini Cylinder 12V MR16	N							13	IPS	Accent/Track Lighting		Tangent	
784197556013	912400491423	FX25		ServiceSmart	Tangent Surface Mount Anchors (5 Pack)	N							13	IPS	Accent/Track Lighting		Tangent	

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
784197566020	912400491424	FX48	New Addition	ServiceSmart	TANGENT POWER FEED ANCHOR	N						New	IPS	Accent/Track Lighting		Tangent	Accessories
784197910129	912400462746	9102WH		SpecSmart	Radius 2' Plain Track Matte White		100					14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197910181	912400462747	9104BK		SpecSmart	Radius 4' Plain Track Matte Black		100					14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197910167	912400462749	9104WH		SpecSmart	Radius 4' Plain Track Matte White		100					14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197910228	912400462750	9106BK		ServiceSmart	Radius 6' Plain Track Matte Black	N						14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197910204	912400462752	9106WH		SpecSmart	Radius 6' Plain Track Matte White		100					14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197910266	912400462753	9108BK		SpecSmart	Radius 8' Plain Track Matte Black		100					14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197910242	912400462755	9108WH	Demoted to B	SpecSmart	Radius 8' Plain Track Matte White		100					14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197000523	912400462758	9147BK		ServiceSmart	Radius Surface Feed Connector/TR Matte Black	N						14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197910303	912400462760	9148BK		ServiceSmart	Radius Live End Feed Matte Black	N						14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197910280	912400462761	9148WH		ServiceSmart	Radius Live End Feed Matte White	N						14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197910341	912400462762	9149BK		ServiceSmart	Radius Mini Coupler Matte Black	N						14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197910327	912400462763	9149WH		ServiceSmart	Radius Mini Coupler Matte White	N						14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197910389	912400462764	9150BK		ServiceSmart	Radius Flush Non-Feed Connector COMB L or NL	N						14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197910365	912400462765	9150WH		ServiceSmart	Radius Flush Non-Feed Connector COMB L or NL	N						14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197170294	912400462767	9151WH		ServiceSmart	Radius Feed "T" Connector Matte White	N						14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197136864	912400462770	9155BK		ServiceSmart	Radius Feed Connector COMB L or In-Line Matte Black	N						14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197136857	912400462771	9155WH		ServiceSmart	Radius Feed Connector COMB L or In-Line Matte White	N						14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197910501	912400462772	9160BK		ServiceSmart	Radius Live End Canopy Matte Black	N						14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197910408	912400462773	9160WH		ServiceSmart	Radius Live End Canopy Matte White	N						14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197910563	912400462777	9163WH		SpecSmart	Radius Saddle Canopy Matte White		100					14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197369446	912400462801	9189WH		ServiceSmart	Radius T-Bar Clip, Flat, (Set of 5)	N						14	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197910440	912400462775	9162WH		ServiceSmart	RADIUS DLOG. FLUR. CONNCTR MAT WHIT	N						New	IPS	Accent/Track Lighting		Radius Track & Accessories	Accessories
784197572860	912400465098	9101NBK		SpecSmart	4' IND Advent Track Black		100					15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197572877	912400465099	9101NWH		SpecSmart	4' IND Advent Track White		100					15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197572891	912400465102	9102NBK		SpecSmart	8' IND Advent Track Black		100					15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197572907	912400465103	9102NWH		ServiceSmart	8' IND Advent Track White	N						15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197572921	912400465105	9103NBK		SpecSmart	8' Join Advent Track Black		100					15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197572938	912400465106	9103NWH		ServiceSmart	8' Join Advent Track White	N						15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197572952	912400465108	9104NBK		SpecSmart	4' 2-Circuit Track w/o Live End Black		100					15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197572969	912400465109	9104NWH		SpecSmart	4' 2-Circuit Track w/o Live End White		100					15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197572983	912400465111	9108NBK		SpecSmart	8' 2-Circuit Track w/o Live End Black		100					15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197572990	912400465112	9108NWH		ServiceSmart	8' 2-Circuit Track w/o Live End White	N						15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197573195	912400465120	9146NBK		SpecSmart	Conduit Continuation Kit/2 CRC/Black		100					15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197573201	912400465121	9146NWH		SpecSmart	Conduit Continuation Kit/2 CRC/White		100					15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197573621	912400465123	9148NBK		SpecSmart	Advent Live End Black		100					15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197573256	912400465124	9148NWH		ServiceSmart	Advent Live End White	N						15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197573225	912400465126	9149NBK		SpecSmart	Advent Mini Coupler Black		100					15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197573232	912400465127	9149NWH		SpecSmart	Advent Mini Coupler White		100					15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197573089	912400465130	9150NBK		SpecSmart	Advent "L" Connector Black		100					15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197573096	912400465131	9150NWH		SpecSmart	Advent "L" Connector White		100					15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197573126	912400465134	9151NWH	Demoted to B	SpecSmart	Advent "T" Connector White		100					15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197573171	912400465140	9153NWH		SpecSmart	Advent Variable Angle Connector White		100					15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197573058	912400465142	9154NBK		SpecSmart	Advent In-Line Connector Black		100					15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197573055	912400465143	9154NWH		SpecSmart	Advent In-Line Connector White		100					15	IPS	Accent/Track Lighting		Advent Track & Accessories	Accessories
784197469931	912400462996	9099BK		SpecSmart	POWERTrip, Basic, Live End Canopy, Black		100					15	IPS	Accent/Track Lighting		PowerTrip	Accessories
784197469914	912400462997	9099WH		SpecSmart	POWERTrip, Basic, Live End Canopy, White		100					15	IPS	Accent/Track Lighting		PowerTrip	Accessories
784197469894	912400462942	9099BK		SpecSmart	POWERTrip, RADIUS, LIVE END CANOPY, BLACK		100					15	IPS	Accent/Track Lighting		PowerTrip	Accessories
784197469887	912400462743	9099WH		ServiceSmart	POWERTrip, RADIUS, LIVE END CANOPY, WHITE	N						15	IPS	Accent/Track Lighting		PowerTrip	Accessories
784197531362	912400492648	PLD120BK		SpecSmart	PowerTrip New Design, Plug-In Breaker		100					15	IPS	Accent/Track Lighting		PowerTrip	Accessories
784197531379	912400492649	PLD120WH		SpecSmart	PowerTrip New Design, Plug-In Breaker		100					15	IPS	Accent/Track Lighting		PowerTrip	Accessories
784197531522	912400492654	PLD360BK		SpecSmart	PowerTrip New Design, Plug-In Breaker		100					15	IPS	Accent/Track Lighting		PowerTrip	Accessories
784197531577	912400492658	PLD600BK		SpecSmart	PowerTrip New Design, Plug-In Breaker		100					15	IPS	Accent/Track Lighting		PowerTrip	Accessories
784197531584	912400492659	PLD600WH		SpecSmart	PowerTrip New Design, Plug-In Breaker		100					15	IPS	Accent/Track Lighting		PowerTrip	Accessories

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
78419751638	912400492664	FL0900K		ServiceSmart	POWERTRIP NEW DESIGN, PLUG-IN BREAKER,		100					15	IPS	Accent/Track Lighting		PowerTrip	Accessories
78419751645	912400492665	FL0900WH		ServiceSmart	POWERTRIP NEW DESIGN, PLUG-IN BREAKER,		100					15	IPS	Accent/Track Lighting		PowerTrip	Accessories
784197608507	912400460360	G085		ServiceSmart	White Lytegan Convenience OUTLET	N						16	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197020064	912400460361	G087		ServiceSmart	REG Panel MTG Clips for Track LG (RClg/Box)		100					16	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197608903	912400460363	G089		ServiceSmart	9/16x11/16 Grid CLING Clip Kit (RClg/Box)	CAL						16	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197272227	912400460423	7516	Promoted to A	ServiceSmart	8" Recessed Housing for Basic and Advent Track	N		X				16	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197272258	912400460424	7517	Promoted to A	ServiceSmart	Splice Box/End Housing	N						16	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197274269	912400460433	7584		ServiceSmart	Track/18 Stem Kit/White		100					16	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197274320	912400460432	7586	Demoted to B	ServiceSmart	Stem Mounting Kit/48"L		100					16	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197274627	912400460434	7596		ServiceSmart	Track/Surface RACEWAY Adapter		100					16	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197002305	912400460435	7599		ServiceSmart	Track/3 D Pendant Adapter/White		100					16	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197277116	912400460448	7681		ServiceSmart	48" Stem Black		100					16	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197635749	912400461064	S6657		ServiceSmart	CLP Grid Ceiling Black		100					16	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197515546	912400462333	G170WH		ServiceSmart	Rectangular Monopoint, Matte White	N						16	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197619015	912400462344	G190BK		ServiceSmart	Monopoint Black	N						16	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197619022	912400462345	G190WH		ServiceSmart	Monopoint White	N		X				16	IPS	Accent/Track Lighting		Track Accessories	Accessories
78419758905	912400462422	7589BK	Demoted to B	ServiceSmart	Track Attachment Fitting Black		100					16	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197295516	912400461053	S6417		ServiceSmart	TRACK PART/STEM HANGER ASSEMBLY		100					New	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197296957	912400461060	S6491		ServiceSmart	BLCK COVER FOR DEAD-END		100					New	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197594770	912400461545	G150NAL		ServiceSmart	BASIC MONPOINT ALUMINUM	L						New	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197012113	912400460446	7662		ServiceSmart	ACCESS HOLDER FOR MR16	L						New	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197858209	912400460476	8582		ServiceSmart	PAR30 ACCESS HOLDER FOR CONE/CYLINDER	N						New	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197858308	912400460477	8583		ServiceSmart	PAR30 ACCESS HOLDER FOR CONE/CYLINDER	N						New	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197859503	912400460482	8595		ServiceSmart	PAR38 ACCESS HOLDER FOR BEZEL	N						New	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197910785	912400460489	9189		ServiceSmart	RADIUS T-BAR CLIP (PLAT/SET OF 9)	N						New	IPS	Accent/Track Lighting		Track Accessories	Accessories
784197515553	912400462332	G170BK	New Addition	ServiceSmart	RECTANGULAR MONPOINT, MATTE BLACK	N						New	IPS	Accent/Track Lighting		Track Accessories	Accessories
662057888788	912401050022	S45827K7		ServiceSmart	SLIM 4" SQUARE 600 LM 27K 80CHI 120V WHT TRIAC WET	N		X				18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057888795	912401050023	S45827K7AL		ServiceSmart	SLIM 4" SQUARE 600 LM 27K 80CHI 120V AL TRIAC WET		100		X			18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057888801	912401050024	S45830K7		ServiceSmart	SLIM 4" SQUARE 600 LM 30K 80CHI 120V WHT TRIAC WET	N		X	X			18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057888818	912401050025	S45830K7AL		ServiceSmart	SLIM 4" SQUARE 600 LM 30K 80CHI 120V AL TRIAC WET		100		X			18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057888825	912401050026	S45927K7		ServiceSmart	SLIM 4" SQUARE 600 LM 27K 90CHI 120V WHT TRIAC WET	N		X	X			18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057888832	912401050027	S45927K7AL		ServiceSmart	SLIM 4" SQUARE 600 LM 27K 90CHI 120V AL TRIAC WET		100		X	X		18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057888672	912401050011	S5R827K7		ServiceSmart	SLIM 5" ROUND 600 LM 27K 80CHI 120V WHT TRIAC WET	N		X	X			18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057888689	912401050012	S5R827K7AL		ServiceSmart	SLIM 5" ROUND 600 LM 27K 80CHI 120V AL TRIAC WET		100		X			18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057888696	912401050013	S5R830K7AL		ServiceSmart	SLIM 5" ROUND 600 LM 30K 80CHI 120V AL TRIAC WET		100		X			18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057936055	912400509398	S5R830K7		ServiceSmart	SLIM 5" ROUND 600 LM 30K 80CHI 120V WHT TRIAC WET	N		X	X			18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057988702	912401050014	S5R927K7		ServiceSmart	SLIM 5" ROUND 600 LM 27K 90CHI 120V WHT TRIAC WET	CAL		X	X			18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057988719	912401050015	S5R927K7AL		ServiceSmart	SLIM 5" ROUND 600 LM 27K 90CHI 120V AL TRIAC WET		100		X	X		18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057988849	912401050028	S60827K10		ServiceSmart	SLIM 6" SQUARE 900 LM 27K 80CHI 120V WHT TRIAC WET	N		X				18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057988856	912401050029	S60827K10AL		ServiceSmart	SLIM 6" SQUARE 900 LM 27K 80CHI 120V AL TRIAC WET		100		X			18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057988863	912401050030	S60830K10		ServiceSmart	SLIM 6" SQUARE 900 LM 30K 80CHI 120V WHT TRIAC WET	N		X	X			18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057988870	912401050031	S60830K10AL		ServiceSmart	SLIM 6" SQUARE 900 LM 30K 80CHI 120V AL TRIAC WET		100		X			18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057988887	912401050032	S60927K10		ServiceSmart	SLIM 6" SQUARE 900 LM 27K 90CHI 120V WHT TRIAC WET	N		X	X			18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057988894	912401050033	S60927K10AL		ServiceSmart	SLIM 6" SQUARE 900 LM 27K 90CHI 120V AL TRIAC WET		100		X	X		18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057988726	912401050016	S7R827K10		ServiceSmart	SLIM 7" ROUND 900 LM 27K 80CHI 120V WHT TRIAC WET	N		X	X			18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057988733	912401050017	S7R827K10AL		ServiceSmart	SLIM 7" ROUND 900 LM 27K 80CHI 120V AL TRIAC WET		100		X			18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057988740	912401050018	S7R830K10		ServiceSmart	SLIM 7" ROUND 900 LM 30K 80CHI 120V WHT TRIAC WET	N		X	X			18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057988757	912401050019	S7R830K10AL		ServiceSmart	SLIM 7" ROUND 900 LM 30K 80CHI 120V AL TRIAC WET		100		X			18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057988764	912401050020	S7R927K10		ServiceSmart	SLIM 7" ROUND 900 LM 27K 90CHI 120V WHT TRIAC WET	N		X	X			18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057988771	912401050021	S7R927K10AL		ServiceSmart	SLIM 7" ROUND 900 LM 27K 90CHI 120V AL TRIAC WET		100		X	X		18	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057952574	912401052989	S5R830K7WZ10U		ServiceSmart	SLIM 5" ROUND 650 LM 30-80 120-277V WHT 0-10V WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057952604	912401052992	S5R833K7WZ10U		ServiceSmart	SLIM 5" ROUND 650 LM 35-80 120-277V WHT 0-10V WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057952871	912401053020	S7R830K10WZ10U		ServiceSmart	SLIM 7" ROUND 900 LM 30-80 120-277V WHT 0-10V WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	
662057952901	912401053023	S7R833K10WZ10U		ServiceSmart	SLIM 7" ROUND 900 LM 35-80 120-277V WHT 0-10V WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight	

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category	
662057952864	912401053015	578827K108K210U	New Addition	SpecSmart	SLIM 7" ROUND 900 LM 27-80 120-277V BLK 0-10V WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057952888	912401053021	578830K10AL210U	New Addition	SpecSmart	SLIM 7" ROUND 900 LM 30-80 120-277V AL 0-10V WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057952895	912401053022	578830K108K210U	New Addition	SpecSmart	SLIM 7" ROUND 900 LM 30-80 120-277V BLK 0-10V WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057952918	912401053024	578835K10AL210U	New Addition	SpecSmart	SLIM 7" ROUND 900 LM 35-80 120-277V AL 0-10V WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057952925	912401053025	578835K108K210U	New Addition	SpecSmart	SLIM 7" ROUND 900 LM 35-80 120-277V BLK 0-10V WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057952949	912401053027	578840K10AL210U	New Addition	SpecSmart	SLIM 7" ROUND 900 LM 40-80 120-277V AL 0-10V WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057952956	912401053028	578840K108K210U	New Addition	SpecSmart	SLIM 7" ROUND 900 LM 40-80 120-277V BLK 0-10V WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057952963	912401053029	578927K10W210U	New Addition	SpecSmart	SLIM 7" ROUND 900 LM 27-90 120-277V WHT 0-10V WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057952970	912401053030	578927K10AL210U	New Addition	SpecSmart	SLIM 7" ROUND 900 LM 27-90 120-277V AL 0-10V WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057952987	912401053031	578927K108K210U	New Addition	SpecSmart	SLIM 7" ROUND 900 LM 27-90 120-277V BLK 0-10V WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057943129	912400510700	545827K78K	New Addition	SpecSmart	SLIM 4" SQUARE 600 LM 27K 80CH 120V BLK TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057943150	912400510701	545830K78K	New Addition	SpecSmart	SLIM 4" SQUARE 600 LM 30K 80CH 120V BLK TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057985459	912400510705	545835K7AL	New Addition	SpecSmart	SLIM 4" SQUARE 600 LM 35K 80CH 120V AL TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057943167	912400510702	545835K78K	New Addition	SpecSmart	SLIM 4" SQUARE 600 LM 35K 80CH 120V BLK TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057985473	912400510703	545840K7AL	New Addition	SpecSmart	SLIM 4" SQUARE 600 LM 40K 80CH 120V AL TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057943181	912400510704	545840K78K	New Addition	SpecSmart	SLIM 4" SQUARE 600 LM 40K 80CH 120V BLK TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057943527	912400510709	545927K78K	New Addition	SpecSmart	SLIM 5" SQUARE 600 LM 27K 90CH 120V BLK TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057943198	912400510704	545927K78K	New Addition	SpecSmart	SLIM 5" SQUARE 600 LM 27K 90CH 120V BLK TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057985497	912400510705	545935K7AL	New Addition	SpecSmart	SLIM 5" ROUND 600 LM 35K 80CH 120V AL TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057943411	912400510706	545935K78K	New Addition	SpecSmart	SLIM 5" ROUND 600 LM 35K 80CH 120V BLK TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057985527	912400510706	545940K7AL	New Addition	SpecSmart	SLIM 5" ROUND 600 LM 40K 80CH 120V AL TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057943428	912400510707	545940K78K	New Addition	SpecSmart	SLIM 5" ROUND 600 LM 40K 80CH 120V BLK TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057943435	912400510708	545927K108K	New Addition	SpecSmart	SLIM 6" SQUARE 900 LM 27K 80CH 120V BLK TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057985541	912400510708	545935K10AL	New Addition	SpecSmart	SLIM 6" SQUARE 900 LM 35K 80CH 120V AL TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057943459	912400510708	545935K108K	New Addition	SpecSmart	SLIM 6" SQUARE 900 LM 35K 80CH 120V BLK TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057985565	912400510705	545940K10AL	New Addition	SpecSmart	SLIM 6" SQUARE 900 LM 40K 80CH 120V AL TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057943466	912400510708	545940K108K	New Addition	SpecSmart	SLIM 6" SQUARE 900 LM 40K 80CH 120V BLK TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057943541	912400510709	545927K108K	New Addition	SpecSmart	SLIM 6" SQUARE 900 LM 27K 90CH 120V BLK TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057943473	912400510708	578827K108K	New Addition	SpecSmart	SLIM 7" ROUND 900 LM 27K 80CH 120V BLK TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057943480	912400510708	578835K108K	New Addition	SpecSmart	SLIM 7" ROUND 900 LM 35K 80CH 120V BLK TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057943558	912400510706	578927K108K	New Addition	SpecSmart	SLIM 7" ROUND 900 LM 27K 90CH 120V BLK TRIAC WET		100		X			New	IPS	Downlighting - Core Downlighting		SlimSurface LED Surface Mount Downlight		
662057961788	912401053568	1050LSQ09E1VA		SpecSmart	XCEED 5" IC 900LM FK SQ ELV 120V SCREW		100		X			New	IPS	Downlighting - Core Downlighting		5" Xceed LED Square	Frames	
662057961804	912401053570	1050LSQ09Z10UVA		SpecSmart	XCEED 5" IC 900LM FK SQ UNV 0-10V SCREW		100		X			New	IPS	Downlighting - Core Downlighting		5" Xceed LED Square	Frames	
662057961811	912400514740	1050LSQ09Z2VA		SpecSmart	XCEED LED 5" SQUARE LIGHT ENGINE 900LM 2700K		100		X			New	IPS	Downlighting - Core Downlighting		5" Xceed LED Square	Light Engine	
662057961828	912400514741	1050LSQ0935VA		SpecSmart	XCEED LED 5" SQUARE LIGHT ENGINE 900LM 3500K		100		X			New	IPS	Downlighting - Core Downlighting		5" Xceed LED Square	Light Engine	
662057483610	912400472726	1050LSQ0LCCW		SpecSmart	XCEED LED 5" SQUARE DOWNLIGHT CLEAR DIFFUSE		100		X			19	IPS	Downlighting - Core Downlighting		5" Xceed LED Square	Trims	
662057939094	912401052610	CP4RN		ServiceSmart	4" LED NEW CONSTRUCTION FRAME								New	IPS	Downlighting - Core Downlighting		Corepro Downlight LED	Frames
662057939100	912401052611	CP4RR		ServiceSmart	4" LED NEW REMODELER HOUSING	C, NL							New	IPS	Downlighting - Core Downlighting		Corepro Downlight LED	Frames
662057939117	912401052612	CP5RN		ServiceSmart	5" LED NEW CONSTRUCTION FRAME	N							New	IPS	Downlighting - Core Downlighting		Corepro Downlight LED	Frames
662057939124	912401052613	CP5RR		ServiceSmart	5" LED NEW REMODELER HOUSING	C, NL							New	IPS	Downlighting - Core Downlighting		Corepro Downlight LED	Frames
662057939131	912401052614	CP6RN		ServiceSmart	6" LED NEW CONSTRUCTION FRAME	C, NL							New	IPS	Downlighting - Core Downlighting		Corepro Downlight LED	Frames
662057939148	912401052615	CP6RR		ServiceSmart	6" LED NEW REMODELER HOUSING	C, NL							New	IPS	Downlighting - Core Downlighting		Corepro Downlight LED	Frames
662057939001	912401052601	CP4RB07930W		ServiceSmart	4" COREPRO LED 750 LM 30K 90CH 120V WHT	C, NL		X	X		X	19	IPS	Downlighting - Core Downlighting		Corepro Downlight LED	Trims	
662057939025	912401052603	CP4RB07840W		ServiceSmart	4" COREPRO LED 850 LM 40K 80CH 120V WHT	C, NL		X	X		X	19	IPS	Downlighting - Core Downlighting		Corepro Downlight LED	Trims	
662057939032	912401052604	CP5RB08930W		ServiceSmart	5" COREPRO LED 900 LM 30K 90CH 120V WHT	N		X	X		X	19	IPS	Downlighting - Core Downlighting		Corepro Downlight LED	Trims	
662057939056	912401052606	CP5RB08840W		ServiceSmart	5" COREPRO LED 1000 LM 40K 80CH 120V WHT	C, NL		X	X		X	19	IPS	Downlighting - Core Downlighting		Corepro Downlight LED	Trims	
662057939063	912401052607	CP6RB10930W		ServiceSmart	6" COREPRO LED 1000 LM 30K 90CH 120V WHT	N		X	X		X	19	IPS	Downlighting - Core Downlighting		Corepro Downlight LED	Trims	
662057939070	912401052608	CP6RB10840W		ServiceSmart	6" COREPRO LED 1200 LM 30K 80CH 120V WHT	C, NL		X	X		X	19	IPS	Downlighting - Core Downlighting		Corepro Downlight LED	Trims	
662057939018	912401052602	CP4RB07830W		ServiceSmart	4" COREPRO LED 800 LM 30K 80CH 120V WHT	C, NL		X	X		X	19	IPS	Downlighting - Core Downlighting		Corepro Downlight LED	Trims	
662057939049	912401052605	CP5RB08830W		ServiceSmart	5" COREPRO LED 950 LM 30K 80CH 120V WHT	C, NL		X	X		X	19	IPS	Downlighting - Core Downlighting		Corepro Downlight LED	Trims	
662057939087	912401052609	CP6RB10830W		ServiceSmart	6" COREPRO LED 1250 LM 40K 80CH 120V WHT	C, NL		X	X		X	19	IPS	Downlighting - Core Downlighting		Corepro Downlight LED	Trims	
662057939254	912401052611	CP6RB07830W		ServiceSmart	6" COREPRO LED 855 LM 30K 80CH 120V WHT	N		X	X		X	19	IPS	Downlighting - Core Downlighting		Corepro Downlight LED	Trims	
662057543970	912400481935	1001LED15N350L		SpecSmart	5" UNIFRAME LED NEW CONSTRUCTION NON-IC FRAME DIMMING 1500LM 3500K 120V		100		X			20	IPS	Downlighting - Core Downlighting		5" Uniframe LED	Frames	
662057961835	912401053572	1001LED09N27210U		SpecSmart	5" UNIFRAME LED NC UNV 0-10V 900LM 27K		100		X			New	IPS	Downlighting - Core Downlighting		5" Uniframe LED	Frames	

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
662057961859	912401053574	1001LED09N35210U		SpecSmart	5" UNFRAME LED NC UNV 0-10V 900LM 35K		100		X			New	IPS	Downlighting - Core Downlighting		5" Unframe LED	Frames
662057544083	912400481971	1101LED15N2701		SpecSmart	6 3/4" UNFRAME LED NEW CONSTRUCTION NON-IC FRAME DIMMING 1500LM 2700K 120V		100		X			20	IPS	Downlighting - Core Downlighting		6 3/4" Unframe LED	Frames
662057544120	912400481973	1101LED15N3501		SpecSmart	6 3/4" UNFRAME LED NEW CONSTRUCTION NON-IC FRAME DIMMING 1500LM 3500K 120V		100		X			20	IPS	Downlighting - Core Downlighting		6 3/4" Unframe LED	Frames
662057544144	912400481974	1101LED15N3502		SpecSmart	6 3/4" UNFRAME LED NEW CONSTRUCTION NON-IC FRAME DIMMING 1500LM 3500K 277V		100		X			20	IPS	Downlighting - Core Downlighting		6 3/4" Unframe LED	Frames
662057961910	912401053180	1101LED09N35210U		SpecSmart	5" UNFRAME LED NC UNV 0-10V 900LM 35K		100		X			New	IPS	Downlighting - Core Downlighting		5" Unframe LED	Frames
662057961897	912401053378	1101LED09N27210U	New Addition	SpecSmart	6" UNFRAME LED NC UNV 0-10V 900LM 27K		100		X			New	IPS	Downlighting - Core Downlighting		6 3/4" Unframe LED	Frames
784197200022	912400466198A	2000AC		ServiceSmart	3 3/4" INC LYTECASTER IC AIRSEAL FRAME	N		X				22	IPS	Downlighting - Core Downlighting		3 3/4" LyteCaster Incandescent	Frames
784197200015	912400462002	2000C		ServiceSmart	3 3/4" INC LYTECASTER IC FRAME	N		X				22	IPS	Downlighting - Core Downlighting		3 3/4" LyteCaster Incandescent	Frames
784197200060	912400462004	2000P1		SpecSmart	3 3/4" INC LYTECASTER NON-IC FRAME WITH BOX FOR ADJUSTABLE ACCENT		100					22	IPS	Downlighting - Core Downlighting		3 3/4" LyteCaster Incandescent	Frames
784197146638	912400462016	2002P1		ServiceSmart	3 3/4" INC LYTECASTER NON-IC FRAME	N		X				22	IPS	Downlighting - Core Downlighting		3 3/4" LyteCaster Incandescent	Frames
784197174590	912400491713	2003R		ServiceSmart	3 3/4" INC LYTECASTER REMODELER RING NON-IC	N		X				22	IPS	Downlighting - Core Downlighting		3 3/4" LyteCaster Incandescent	Frames
784197146559	912400460286	2005		ServiceSmart	3 3/4" BAFFLE BLACK	N						22	IPS	Downlighting - Core Downlighting		3 3/4" LyteCaster Incandescent	Trims
784197146597	912400460290	2011		ServiceSmart	3 3/4" PINHOLE WHITE	C,N						22	IPS	Downlighting - Core Downlighting		3 3/4" LyteCaster Incandescent	Trims
784197146627	912400460292	2013		ServiceSmart	3 3/4" CONE SPECULAR CLEAR	N		X				22	IPS	Downlighting - Core Downlighting		3 3/4" LyteCaster Incandescent	Trims
784197051020	912400460302	2090		ServiceSmart	3 3/4" FLAT GLASS SHOWER LIGHT CLEAR PLASTIC FLANGE	N						22	IPS	Downlighting - Core Downlighting		3 3/4" LyteCaster Incandescent	Trims
784197200107	912400460208	2005WH		ServiceSmart	3 3/4" BAFFLE WHITE	N		X				22	IPS	Downlighting - Core Downlighting		3 3/4" LyteCaster Incandescent	Trims
784197359690	912400462032	2013CD		ServiceSmart	3 3/4" CONE CLEAR DIFFUSE	C,N						22	IPS	Downlighting - Core Downlighting		3 3/4" LyteCaster Incandescent	Trims
784197201302	912400462035	2013WH		ServiceSmart	3 3/4" CONE WHITE	N		X				22	IPS	Downlighting - Core Downlighting		3 3/4" LyteCaster Incandescent	Trims
784197200206	912400460204	20027WH		ServiceSmart	3 3/4" RECESSED ADJUSTABLE WHITE STEP BAFFLE	N						22	IPS	Downlighting - Core Downlighting		3 3/4" LyteCaster Incandescent	Trims
662057206080	912400462056	2076WH		ServiceSmart	3-3/4" BAFFLE DOWNLIGHT WHITE	N		X				22	IPS	Downlighting - Core Downlighting		3 3/4" LyteCaster Incandescent	Trims
784197545642	912400468282	1001F13U		SpecSmart	5" UNFRAME NON-IC CFL 13W 120-277V		100					22	IPS	Downlighting - Core Downlighting		5" Unframe CFL	Frames
784197545198	912400468284	1001F26U		SpecSmart	5" UNFRAME NON-IC CFL 26W 120-277V		100					22	IPS	Downlighting - Core Downlighting		5" Unframe CFL	Frames
784197546465	912400461794	1001CL		ServiceSmart	5" PERFORMANCE CFL VERTICAL OPEN CL	N						22	IPS	Downlighting - Core Downlighting		5" Unframe CFL	Trims
784197546557	912400463893	1001HCL		SpecSmart	5" PERFORMANCE CFL HORIZONTAL OPEN CL		100					22	IPS	Downlighting - Core Downlighting		5" Unframe CFL	Trims
784197545499	912400472610	1101F2642U		ServiceSmart	6 3/4" UNFRAME NON-IC CFL 26-42W 120-277V	N		X				22	IPS	Downlighting - Core Downlighting		6 3/4" Unframe CFL	Frames
784197546052	912400461864	1101CL		ServiceSmart	6 3/4" PERFORMANCE CFL VERTICAL OPEN SPECULAR CLEAR	N		X				22	IPS	Downlighting - Core Downlighting		6 3/4" Unframe CFL	Trims
784197546144	912400463921	1101HCL	Demoted to B	SpecSmart	6 3/4" PERFORMANCE CFL HORIZONTAL OPEN CL		100	X				22	IPS	Downlighting - Core Downlighting		6 3/4" Unframe CFL	Trims
662057997889	912401052149	L3AHB		SpecSmart	3.75" ACCESSORY HOLDER BLACK		100					23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Accessories
662057997872	912401052148	L3AHW		SpecSmart	3.75" ACCESSORY HOLDER WHITE		100					23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Accessories
662057997882	912401052151	L3LS		SpecSmart	3.75" LINEAR SPREAD FILM		100					23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Accessories
662057999456	912401052146	L3N210U		SpecSmart	3.75" NEW CONSTRUCT. NON-IC 120V/277 0-10V DIM SCR		100		X			23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Accessories
662057998220	912401052154	L3RPF		SpecSmart	LYTECASTER 3.75" REPLACEMENT OPTIC FLOOD		100					23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Accessories
662057998213	912401052153	L3RPNF		SpecSmart	LYTECASTER 3.75" REPLACEMENT OPTIC NARROW FLOOD		100					23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Accessories
662057998206	912401052152	L3RPS		SpecSmart	LYTECASTER 3.75" REPLACEMENT OPTIC SPOT		100					23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Accessories
662057997575	912401052150	L3SD		SpecSmart	3.75" 5 DEGREE DIFFUSION FILM		100					23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Accessories
662057999326	912401052144	L3AE1		ServiceSmart	3.75" NEW CONSTRUCTION AIRSEAL IC 120V ELV DIM SCR	N		X	X		X	23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Frames
662057999333	912401052145	L3ANE1		ServiceSmart	3.75" NEW CONSTRUCT. AIRSEAL IC 120V ELV DIM NAIL	N			X		X	23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Frames
662057999319	912401052147	L3CE1		ServiceSmart	3.75" REMODELER NON-IC 120V ELV DIM	C,N,L		X	X			23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Frames
662057997995	912401052131	L308B27F		SpecSmart	3.75" LIGHT ENGINE 2700K 80CRI FLOOD		100		X			23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Light Engine
662057997988	912401052129	L308B27NF		ServiceSmart	3.75" LIGHT ENGINE 2700K 80CRI NARROW FLOOD	N			X			23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Light Engine
662057998053	912401052136	L308B30F		SpecSmart	3.75" LIGHT ENGINE 3000K 80CRI FLOOD		100		X			23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Light Engine
662057998015	912401052135	L308B30NF		ServiceSmart	3.75" LIGHT ENGINE 3000K 80CRI NARROW FLOOD	N		X	X			23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Light Engine
662057998138	912401052142	L308B35F		ServiceSmart	3.75" LIGHT ENGINE 3500K 80CRI FLOOD	N		X	X			23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Light Engine
662057998121	912401052141	L308B35NF		ServiceSmart	3.75" LIGHT ENGINE 3500K 80CRI NARROW FLOOD	N		X	X			23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Light Engine
662057998152	912401052132	L308B27F		SpecSmart	3.75" LIGHT ENGINE 2700K 90CRI FLOOD		100				X	23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Light Engine
662057998183	912401052130	L308B27NF		ServiceSmart	3.75" LIGHT ENGINE 2700K 90CRI NARROW FLOOD	N					X	23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Light Engine
662057998008	912401052137	L308B30S		SpecSmart	3.75" LIGHT ENGINE 3000K 80CRI SPOT		100		X			New	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Light Engine
662057997643	912401050201	L3RABW		ServiceSmart	3.75" ADJUSTABLE ACCENT WHITE BAFFLE WHITE FLANGE	N		X	X		X	23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
662057997667	912401050206	L3RAD		ServiceSmart	3.75" DOWNLIGHT SHOWER LIGHT FLAT GLASS ALUMINUM	N		X			X	23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
662057997865	912401052126	L3RAPA		ServiceSmart	3.75" ADJUSTABLE GIMBAL ALUMINUM	N						23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
662057997858	912401052125	L3RAPW		ServiceSmart	3.75" ADJUSTABLE GIMBAL BLACK	N		X				23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
662057997674	912401050205	L3RAW		ServiceSmart	3.75" DOWNLIGHT SHOWER LIGHT FLAT GLASS WHITE	N			X		X	23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
662057997605	912401050202	L3RBW		ServiceSmart	3.75" ADJUSTABLE ACCENT CHROME CONE WHITE FLANGE	N		X	X		X	23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
662057997629	912401052128	L3RDD		ServiceSmart	3.75" ADJUSTABLE ACCENT PINHOLE BAFFLE ALUMINUM	N			X		X	23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
66205997636	912401052127	L3RDW		ServiceSmart	3.75" ADJUSTABLE ACCENT PINHOLE BAFFLE WHITE	N			X		X	23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
66205997841	912401052124	L3RGA		ServiceSmart	3.75" ADJUSTABLE GIMBAL WHITE	C,N,L			X		X	23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
66205997834	912401052123	L3RGR		ServiceSmart	3.75" SQUARE SHOWER LIGHT ALUMINUM FACE PLATE	C,N			X		X	23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
66205997827	912401052122	L3RGR		ServiceSmart	3.75" SQUARE SHOWER LIGHT WHITE FACE PLATE	N		X	X		X	23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
66205997704	912401052118	L3RLWC		ServiceSmart	3.75" SQ. ADJUSTABLE DIFFUSE CONE WHITE FACE PLATE	N		X				23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
66205997711	912401052021	L3RLWD		ServiceSmart	3.75" SQ. DOWNLIGHT DIFFUSE CONE ALUM. FACE PLATE	N						23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
66205997728	912401052020	L3RLWW		ServiceSmart	3.75" SQ. DOWNLIGHT DIFFUSE CONE WHITE FACE PLATE	C,N,L						23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
66205997698	912401052119	L3RSA		ServiceSmart	3.75" SQ. ADJUSTABLE DIFFUSE CONE ALUM. FACE PLATE	N						23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
66205997681	912401052196	L3RSW		ServiceSmart	3.75" DOWNLIGHT WHITE BAFFLE WHITE FLANGE	N		X				23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
66205997766	912401052198	L3SAD		ServiceSmart	3.75" DOWNLIGHT DIFFUSED CONE WHITE FLANGE	N		X	X		X	23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
66205997773	912401052199	L3SADA		ServiceSmart	3.75" DOWNLIGHT WHITE CONE WHITE FLANGE	N		X	X		X	23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
66205997735	912401052121	L3SDO		ServiceSmart	3.75" SQ. DOWNLIGHT WHITE CONE WHITE FACE PLATE	N		X	X		X	23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
66205997742	912401052008	L3SDDA		ServiceSmart	3.75" WALL WASHER DIFFUSED CONE WHITE FLANGE	N		X	X		X	23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
66205997759	912401052197	L3SDW		ServiceSmart	3.75" DOWNLIGHT CHROME CONE WHITE FLANGE	N			X		X	23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
66205997797	912401052029	L3SLWA		ServiceSmart	3.75" WALL WASHER WHITE CONE WHITE FLANGE	N			X		X	23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
66205997780	912401052027	L3SLWW		ServiceSmart	3.75" WALL WASHER CHROME CONE WHITE FLANGE	N		X				23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
66205997810	912401052121	L3SSA		ServiceSmart	3.75" SQUARE WALL WASHER ALUMINUM FACE PLATE	N						23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
66205997803	912401052120	L3SSW		ServiceSmart	3.75" SQUARE WALL WASHER WHITE FACE PLATE	N		X				23	IPS	Downlighting - Core Downlighting		3" LyteCaster LED Accent	Trims
784197100056	912400468271	1000ACM		SpecSmart	5" INC LYTECASTER IC AIRSEAL FRAME		100					24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent	Frames
784197119959	912400461789	1000IC		ServiceSmart	5" INC LYTECASTER IC FRAME	N		X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent	Frames
784197120078	912400461788	10002P1		ServiceSmart	5" INC LYTECASTER NON-IC FRAME	N		X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent	Frames
784197124576	912400491667	1003R		ServiceSmart	5" INC LYTECASTER REMODELER RING NON-IC	C,N,L		X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent	Frames
784197120219	912400460172	1078	Demoted to B	SpecSmart	5" DROPPED OPALEX SHOWER LIGHT		100	X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent	Trims
784197120233	912400460173	1082	Demoted to B	SpecSmart	5" BASIC WHITE EYEBALL		100	X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent	Trims
784197501006	912400460177	1090		ServiceSmart	5" FLAT GLASS LENS SHOWER LIGHT CLEAR PLASTIC FLANGE	N		X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent	Trims
784197100506	912400461808	1005WH		ServiceSmart	5" STEP BAFFLE WHITE	N		X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent	Trims
784197359706	912400461817	1013CD		ServiceSmart	5" CONE CLEAR DIFFUSE	C,N,L		X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent	Trims
784197101305	912400461820	1013WH		ServiceSmart	5" CONE WHITE	C,N,L		X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent	Trims
784197107604	912400461847	1076WH		ServiceSmart	5" BASIC WHITE BAFFLE	N		X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent	Trims
784197031712	912400461850	1081WH		SpecSmart	5" OPEN WETLOCATION FOR LYTECEN PARK30 WHITE		100					24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent	Trims
784197017156	912400461856	1084WH		SpecSmart	5" OPEN WETLOCATION FOR LYTECEN PARK30 WHITE		100	X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent	Trims
784197205881	912400460058	C71		ServiceSmart	5" OPEN REFLECTOR TRIM WHITE	L		X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent	Trims
784197205874	912400461297	C76WH		ServiceSmart	5" SPUN WHITE BAFFLE REFLECTOR TRIM	N,L		X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent	Trims
784197120450	912400460159	1013		ServiceSmart	5" CONE SPECULAR CLEAR	N		X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent	Trims
784197120696	912400460170	1071		ServiceSmart	5" OPEN REFLECTOR WHITE	C,N,L		X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent	Trims
784197120702	912400460171	1076	Demoted to B	SpecSmart	5" BASIC BLACK BAFFLE		100	X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent	Trims
784197159290	912400461802	1004IC		ServiceSmart	5" INC LYTECEN NEW CONSTRUCTION IC & NON-IC HOUSING SCREW	N		X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent & CFL Frames	Frames
784197198596	912400461899	1004CN		ServiceSmart	5" INC LYTECEN NEW CONSTRUCTION IC & NON-IC HOUSING NAIL	N		X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent & CFL Frames	Frames
784197291839	912400461802	1004CNQ		ServiceSmart	5" INC LYTECEN NEW CONSTRUCTION IC & NON-IC HOUSING NAIL QUICK CONNECT	C,N,L		X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent & CFL Frames	Frames
784197159320	912400461897	1004CR		ServiceSmart	5" INC LYTECEN REMODELER IC & NON-IC HOUSING SCREW	C,N,L		X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent & CFL Frames	Frames
784197219826	912400461901	1004CX		ServiceSmart	5" LYTECEN ICX NEW CONSTRUCTION IC HOUSING SCREW	N		X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent & CFL Frames	Frames
784197239008	912400461805	1004CN	Demoted to B	SpecSmart	5" LYTECEN ICX NEW CONSTRUCTION IC HOUSING NAIL		100					24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent & CFL Frames	Frames
784197198503	912400461902	1005IC		ServiceSmart	5" INC LYTECEN NEW CONSTRUCTION IC & NON-IC SHALLOW HOUSING SCREW	N		X				24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent & CFL Frames	Frames
784197198534	912400461809	1005SCR	Demoted to B	SpecSmart	5" INC LYTECEN REMODELER IC & NON-IC SHALLOW HOUSING SCREW		100					24	IPS	Downlighting - Core Downlighting		5" LyteCaster Incandescent & CFL Frames	Frames
662057941639	912401052568	L4RAE1VA		ServiceSmart	LCA LED 4" 650LM ROUND IC FIX SCREW 120V	N		X	X			25	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Frames
662057941653	912401052569	L4RAE1VA		ServiceSmart	LCA LED 4" 650LM ROUND IC FIX NAIL 120V	C,N,L		X	X			25	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Frames
662057941769	912401052570	L4RAN210VA		ServiceSmart	LCA LED 4" 650LM ROUND IC FIX NAIL 0-10V U	C,N,L		X	X			25	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Frames
662057941646	912401052571	L4RAZ10DUVA		ServiceSmart	LCA LED 4" 650LM ROUND IC FIX SCREW 0-10V U	N		X	X			25	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Frames
662057998718	912401052558	L4R06827VA		SpecSmart	LCA LED 4" MODULE 80 CRI 27K 650LM		100		X			25	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Light Engine
662057998725	912401052559	L4R06830VA		ServiceSmart	LCA LED 4" MODULE 80 CRI 30K 650LM	N		X	X			25	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Light Engine
662057998749	912401052560	L4R06835VA		SpecSmart	LCA LED 4" MODULE 80 CRI 35K 650LM		100		X			25	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Light Engine
662057941035	912401052562	L4R06927VA		SpecSmart	LCA LED 4" MODULE 90 CRI 27K 650LM		100		X		X	25	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Light Engine
662057941042	912401052563	L4R068279VA		SpecSmart	LCA LED 4" ROUND ADJ WHITE 650LM 827		100		X			25	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Trims
662057941059	912401052564	L4R068309VA		SpecSmart	LCA LED 4" ROUND ADJ WHITE 650LM 830		100	X	X			25	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Trims

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
662057941066	912401052565	LARAD6835VA		SpecSmart	LCA LED 4" ROUND ADJ WHITE 650LM 835		100		X			25	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Trims
662057941080	912401052567	LARAD6927VA		SpecSmart	LCA LED 4" ROUND ADJ WHITE 550LM 927		100		X			25	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Trims
662057993690	912401050056	LARBW		ServiceSmart	LCA LED 4" ROUND WHITE BAFFLE	N		X	X			25	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Trims
662057993706	912401050057	LARDD		SpecSmart	LCA LED 4" ROUND CLEAR DIFFUSE CONE		100		X			25	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Trims
662057993713	912401050058	LARDW		SpecSmart	LCA LED 4" ROUND WHITE CONE AND FLANGE		100		X			25	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Trims
662057999388	912401052561	LAR06840VA	New Addition	SpecSmart	LCA LED 4" MODULE 80 CRU 40K 650LM		100					New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Light Engine
662057941073	912401052566	LARAD6840VA		SpecSmart	LCA LED 4" ROUND ADJ WHITE 650LM 840		100					New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Trims
662057950877	912401052849	LAR10827VA	New Addition	ServiceSmart	LCA LED 4" MODULE 80 CRU 27K 1000LM	N						New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Light Engine
190096019519	912401052850	LAR10830VA	New Addition	ServiceSmart	LCA LED 4" MODULE 80 CRU 30K 1000LM	N						New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Light Engine
662057950891	912401052851	LAR10835VA	New Addition	SpecSmart	LCA LED 4" MODULE 80 CRU 35K 1000LM		100					New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Light Engine
662057950907	912401052852	LAR10840VA	New Addition	SpecSmart	LCA LED 4" MODULE 80 CRU 40K 1000LM		100					New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Light Engine
662057950914	912401052853	LAR10927VA	New Addition	SpecSmart	LCA LED 4" MODULE 90 CRU 27K 1000LM		100					New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Light Engine
190096019526	912401052854	LAR10A11VA	New Addition	ServiceSmart	LCA LED 4" 1000LM ROUND IC FIK SCREW 120V	N						New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Frames
662057952079	912401052855	LAR10A11VA	New Addition	ServiceSmart	LCA LED 4" 1000LM ROUND IC FIK NAIL 120V	N						New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Frames
662057952062	912401052856	LAR10A210UVA	New Addition	ServiceSmart	LCA LED 4" 1000LM ROUND IC FIK NAIL 0-10V U	N						New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Frames
190096019533	912401052857	LAR10A210UVA	New Addition	ServiceSmart	LCA LED 4" 1000LM ROUND IC FIK SCREW 0-10V U	N						New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Frames
662057951904	912401052876	LARA10827VA	New Addition	SpecSmart	LCA LED 4" ROUND ADJ WHITE 1000LM 827		100					New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Trims
662057951911	912401052877	LARA10830VA	New Addition	SpecSmart	LCA LED 4" ROUND ADJ WHITE 1000LM 830		100					New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Trims
662057951928	912401052878	LARA10835VA	New Addition	SpecSmart	LCA LED 4" ROUND ADJ WHITE 1000LM 835		100					New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Trims
662057951935	912401052879	LARA10840VA	New Addition	SpecSmart	LCA LED 4" ROUND ADJ WHITE 1000LM 840		100					New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Trims
662057951942	912401052880	LARA10927VA	New Addition	SpecSmart	LCA LED 4" ROUND ADJ WHITE 1000LM 927		100					New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Trims
190096019540	912401053523	LAR06R11VA	New Addition	ServiceSmart	LCA LED 4" ROUND IC REMODELER 650LM 81V 120V	N						New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Frames
190096019557	912401053523	LAR06R210UVA	New Addition	ServiceSmart	LCA LED 4" ROUND IC REMODELER 650LM 0-10 U	N						New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Frames
190096019601	912401053524	LAR10R11VA	New Addition	ServiceSmart	LCA LED 4" ROUND IC REMODELER 1000LM 81V 120V	N						New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Frames
190096019618	912401053525	LAR10R210UVA	New Addition	ServiceSmart	LCA LED 4" ROUND IC REMODELER 1000LM 0-10V U	N						New	IPS	Downlighting - Core Downlighting		4" LyteCaster LED Round	Frames
662057941684	912401052582	LSRAE1VA		ServiceSmart	LCA LED 5" 1000LM ROUND IC FIK SCREW 120V	C		X	X			25	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Frames
662057993928	912401050069	LSRAEWG1		ServiceSmart	LCA LED 5" 700LM WG ROUND IC FIK SCREW	C,NL		X	X			25	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Frames
662057941707	912401052583	LSRANE1VA		ServiceSmart	LCA LED 5" 1000LM ROUND IC FIK NAIL 120V	C,NL			X			25	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Frames
662057993935	912401050071	LSRANEWG1		ServiceSmart	LCA LED 5" 700LM WG ROUND IC FIK NAIL	C,NL			X			25	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Frames
662057941714	912401052584	LSRANZ10UVA		ServiceSmart	LCA LED 5" 1000LM ROUND IC FIK NAIL 0-10V U	N			X			25	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Frames
662057941691	912401052585	LSRAZ10UVA		ServiceSmart	LCA LED 5" 1000LM ROUND IC FIK SCREW 0-10V U	N			X			25	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Frames
662057993829	912401050059	LSR078WG		ServiceSmart	LCA LED 5" MODULE 80 CRU 27K 700LM WG	N		X	X			25	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Light Engine
662057941097	912401052572	LSR10827VA		SpecSmart	LCA LED 5" MODULE 80 CRU 27K 1000LM		100		X			25	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Light Engine
662057941103	912401052573	LSR10830VA		ServiceSmart	LCA LED 5" MODULE 80 CRU 30K 1000LM	N		X	X			25	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Light Engine
662057941110	912401052574	LSR10835VA		ServiceSmart	LCA LED 5" MODULE 80 CRU 35K 1000LM	C,NL			X			25	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Light Engine
662057941134	912401052576	LSR10927VA		SpecSmart	LCA LED 5" MODULE 90 CRU 27K 1000LM		100		X		X	25	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Light Engine
662057941127	912401052575	LSR10840VA		SpecSmart	LCA LED 5" MODULE 80 CRU 40K 1000LM		100					New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Light Engine
662057941141	912401052577	LSRA10827VA		SpecSmart	LCA LED 5" ROUND ADJ WHITE 1000LM 827		100		X			25	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Trims
662057941158	912401052578	LSRA10830VA		SpecSmart	LCA LED 5" ROUND ADJ WHITE 1000LM 830		100	X	X			25	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Trims
662057941165	912401052579	LSRA10835VA		SpecSmart	LCA LED 5" ROUND ADJ WHITE 1000LM 835		100		X			25	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Trims
662057941189	912401052581	LSRA10927VA		SpecSmart	LCA LED 5" ROUND ADJ WHITE 1000LM 927		100		X			25	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Trims
662057993836	912401050072	LSRBW		ServiceSmart	LCA LED 5" ROUND WHITE BAFFLE	N		X	X			25	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Trims
662057993843	912401050073	LSRDD		SpecSmart	LCA LED 5" ROUND CLEAR DIFFUSE CONE		100		X			25	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Trims
662057993850	912401050074	LSRDW		SpecSmart	LCA LED 5" ROUND WHITE CONE AND FLANGE		100		X			25	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Trims
662057941172	912401052580	LSRA10840VA	New Addition	SpecSmart	LCA LED 5" ROUND ADJ WHITE 1000LM 840		100					New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Trims
662057950921	912401052858	LSR15827VA	New Addition	SpecSmart	LCA LED 5" MODULE 80 CRU 27K 1500LM		100					New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Light Engine
662057950938	912401052859	LSR15830VA	New Addition	ServiceSmart	LCA LED 5" MODULE 80 CRU 30K 1500LM	N						New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Light Engine
662057950945	912401052860	LSR15835VA	New Addition	ServiceSmart	LCA LED 5" MODULE 80 CRU 35K 1500LM	N						New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Light Engine
662057950952	912401052861	LSR15840VA	New Addition	SpecSmart	LCA LED 5" MODULE 80 CRU 40K 1500LM		100					New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Light Engine
662057950969	912401052862	LSR15927VA	New Addition	SpecSmart	LCA LED 5" MODULE 90 CRU 27K 1500LM		100					New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Light Engine
662057952093	912401052863	LSR15A11VA	New Addition	ServiceSmart	LCA LED 5" 1500LM ROUND IC FIK SCREW 120V	N						New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Frames
662057952116	912401052864	LSR15ANE1VA	New Addition	ServiceSmart	LCA LED 5" 1500LM ROUND IC FIK NAIL 120V	N						New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Frames
662057952109	912401052865	LSR15ANZ10UVA	New Addition	ServiceSmart	LCA LED 5" 1500LM ROUND IC FIK NAIL 0-10V U	N						New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Frames
662057952123	912401052866	LSR15AZ10UVA	New Addition	ServiceSmart	LCA LED 5" 1500LM ROUND IC FIK SCREW 0-10V U	N						New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Frames

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
662057951959	912401052881	LSRA15827WVA	New Addition	SpecSmart	LCA LED 5" ROUND ADJ WHITE 1500lm 827		100					New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Trims
662057951966	912401052882	LSRA15830WVA	New Addition	SpecSmart	LCA LED 5" ROUND ADJ WHITE 1500lm 830		100					New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Trims
662057951973	912401052883	LSRA15835WVA	New Addition	SpecSmart	LCA LED 5" ROUND ADJ WHITE 1500lm 835		100					New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Trims
662057951973	912401052884	LSRA15840WVA	New Addition	SpecSmart	LCA LED 5" ROUND ADJ WHITE 1500lm 840		100					New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Trims
662057951997	912401052885	LSRA15927WVA	New Addition	SpecSmart	LCA LED 5" ROUND ADJ WHITE 1500lm 927		100					New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Trims
190096019564	912401053326	LSR10RE1VA	New Addition	ServiceSmart	LCA LED 5" ROUND IC REMODELER 1000LM ELV 120V	N						New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Frames
190096019571	912401053327	LSR10R210UVA	New Addition	ServiceSmart	LCA LED 5" ROUND IC REMODELER 1000LM 0-10V U	N						New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Frames
190096019625	912401053328	LSR15RE1VA	New Addition	ServiceSmart	LCA LED 5" ROUND IC REMODELER 1500LM ELV 120V	N						New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Frames
190096019632	912401053329	LSR15R210UVA	New Addition	ServiceSmart	LCA LED 5" ROUND IC REMODELER 1500LM 0-10V U	N						New	IPS	Downlighting - Core Downlighting		5" LyteCaster LED Round	Frames
784197110239	912400461862	1100C		ServiceSmart	6 3/4" INC LYTECASTER IC FRAME	N		X				26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Frames
784197110222	912400461868	1102P1		ServiceSmart	6 3/4" INC LYTECASTER NON-IC FRAME	N		X				26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Frames
784197174583	912400491677	1103R		ServiceSmart	6 3/4" INC LYTECASTER REMODELER RING NON-IC	C,NL		X				26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Frames
784197121154	912400460183	1105		SpecSmart	6 3/4" STEP BAFFLE BLACK		100					26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
784197123352	912400460187	1113		ServiceSmart	6 3/4" CONE SPECULAR CLEAR	N		X				26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
784197123789	912400460194	1126		SpecSmart	6 3/4" REGRESSED FRESNEL LENS WHITE SPLAY		100					26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
784197124175	912400460208	1146	Demoted to B	SpecSmart	6 3/4" A LAMP OPEN REFLECTOR SPECULAR CLEAR		100					26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
784197117108	912400460219	1171		ServiceSmart	6 3/4" OPEN REFLECTOR WHITE	N		X				26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
784197035500	912400460220	1176		ServiceSmart	6 3/4" BASIC BAFFLE BLACK	N		X				26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
784197118204	912400460223	1182	Demoted to B	SpecSmart	6 3/4" BASIC WHITE EYEBALL		100					26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
784197503013	912400460224	1190		SpecSmart	6 3/4" FLAT GLASS LENS SHOWER LIGHT CLEAR PLASTIC FLANGE		100					26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
784197110703	912400461879	1105WH		ServiceSmart	6 3/4" STEP BAFFLE WHITE	N		X				26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
78419739713	912400461884	1113CD		ServiceSmart	6 3/4" CONE CLEAR DIFFUSE	N						26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
784197011130	912400461888	1113WH		SpecSmart	6 3/4" CONE WHITE		100					26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
784197243609	912400461892	1117WH		ServiceSmart	6 3/4" BASIC WHITE BAFFLE REFLECTOR	N		X				26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
784197113520	912400461913	1131WH		ServiceSmart	6 3/4" SLOPE CEILING 10-30 DEGREES BAFFLE WHITE	N		X				26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
784197113522	912400461918	1133WH		ServiceSmart	6 3/4" SLOPE CEILING 30-45 DEGREES BAFFLE WHITE	N						26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
784197017231	912400461935	1154WH		ServiceSmart	6 3/4" COMPLETE SLOPE CEILING 14-45 DEGREES WHITE BAFFLE	N						26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
784197030517	912400461941	1170WH		ServiceSmart	6 3/4" BASIC BAFFLE WHITE	N		X				26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
784197194758	912400461942	1177LX		ServiceSmart	5" AND 6 3/4" FLUSH OPALX SHOWER LIGHT WHITE PLASTIC FLANGE	C,NL		X				26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
784197117719	912400461944	1177SH	Demoted to B	SpecSmart	6 3/4" FLUSH OPALX SHOWER LIGHT WHITE PLASTIC FLANGE		100					26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
784197117818	912400461946	1178SH	Demoted to B	SpecSmart	6 3/4" DROP OPALX SHOWER LIGHT WHITE PLASTIC FLANGE		100					26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
784197290580	912400461246	B17WH		ServiceSmart	6 3/4" BAFFLE BR30 SHALLOW PLENUM WHITE	N		X				26	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent	Trims
662057994062	912401052596	LSRAE1VA		ServiceSmart	LCA LED 6" 1500LM ROUND IC FIK SCREW 120V	N		X	X			26	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Frames
662057994079	912401052597	LSRANE1VA		ServiceSmart	LCA LED 6" 1500LM ROUND IC FIK NAIL 120V	C,NL		X	X			26	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Frames
662057999715	912401052598	LSRANZ10UVA		ServiceSmart	LCA LED 6" 1500LM ROUND IC FIK NAIL 0-10V U	N		X				26	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Frames
662057999708	912401052599	LSRAZ10UVA		ServiceSmart	LCA LED 6" 1500LM ROUND IC FIK SCREW 0-10V U	N		X				26	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Frames
662057941196	912401052586	LSR15827VA		SpecSmart	LCA LED 6" MODULE 80 CRI 27K 1500LM		100		X			26	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Light Engine
662057941202	912401052587	LSR15830VA		ServiceSmart	LCA LED 6" MODULE 80 CRI 30K 1500LM	N		X	X			26	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Light Engine
662057941233	912401052590	LSR15927VA		SpecSmart	LCA LED 6" MODULE 90 CRI 27K 1500LM		100		X	X		26	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Light Engine
662057941219	912401052588	LSR15835VA		SpecSmart	LCA LED 6" MODULE 80 CRI 35K 1500LM		100		X			26	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Light Engine
662057941226	912401052589	LSR15840VA		SpecSmart	LCA LED 6" MODULE 80 CRI 40K 1500LM		100					New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Light Engine
662057941288	912401052595	LSRA15927WVA		SpecSmart	LCA LED 6" ROUND ADJ WHITE 1500lm 927		100		X			26	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Trims
662057941240	912401052591	LSRA15827WVA		SpecSmart	LCA LED 6" ROUND ADJ WHITE 1500lm 827		100		X			26	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Trims
662057941257	912401052592	LSRA15830WVA		SpecSmart	LCA LED 6" ROUND ADJ WHITE 1500lm 830		100	X	X			26	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Trims
662057953980	912401050085	LSR8W		ServiceSmart	LCA LED 6" ROUND WHITE BAFFLE	N		X	X			26	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Trims
662057953997	912401050086	LSR8D		SpecSmart	LCA LED 6" ROUND CLEAR DIFFUSE CONE		100		X			26	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Trims
662057994000	912401050087	LSR8W		SpecSmart	LCA LED 6" ROUND WHITE CONE		100		X			26	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Trims
662057941264	912401052593	LSRA15835WVA		SpecSmart	LCA LED 6" ROUND ADJ WHITE 1500lm 835		100		X			26	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Trims
662057941271	912401052594	LSRA15840WVA	New Addition	SpecSmart	LCA LED 6" ROUND ADJ WHITE 1500lm 840		100					New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Trims
662057950976	912401052867	LSR20827VA	New Addition	SpecSmart	LCA LED 6" MODULE 80 CRI 27K 2000LM		100					New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Light Engine
662057950983	912401052868	LSR20830VA	New Addition	ServiceSmart	LCA LED 6" MODULE 80 CRI 30K 2000LM	N						New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Light Engine
662057950990	912401052869	LSR20835VA	New Addition	ServiceSmart	LCA LED 6" MODULE 80 CRI 35K 2000LM	N						New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Light Engine
662057951003	912401052870	LSR20840VA	New Addition	SpecSmart	LCA LED 6" MODULE 80 CRI 40K 2000LM		100					New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Light Engine
662057951010	912401052871	LSR20927VA	New Addition	SpecSmart	LCA LED 6" MODULE 90 CRI 27K 2000LM		100					New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Light Engine

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
662057952130	912401052872	L6R20A11VA	New Addition	ServiceSmart	LCA LED 6" 2000LM ROUND IC FK SCREW 120V	N						New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Frames
662057952154	912401052873	L6R20ANE1VA	New Addition	ServiceSmart	LCA LED 6" 2000LM ROUND IC FK NAIL 120V	N						New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Frames
662057952147	912401052874	L6R20ANZ10UVA	New Addition	ServiceSmart	LCA LED 6" 2000LM ROUND IC FK NAIL 0-10V U	N						New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Frames
662057952161	912401052875	L6R20AZ10UVA	New Addition	ServiceSmart	LCA LED 6" 2000LM ROUND IC FK SCREW 0-10V U	N						New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Frames
662057952000	912401052886	L6RA20B27WVA	New Addition	SpecSmart	LCA LED 6" ROUND ADJ WHITE 2000lm 827		100					New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Trims
662057952017	912401052887	L6RA20B30WVA	New Addition	SpecSmart	LCA LED 6" ROUND ADJ WHITE 2000lm 830		100					New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Trims
662057952024	912401052888	L6RA20B35WVA	New Addition	SpecSmart	LCA LED 6" ROUND ADJ WHITE 2000lm 835		100					New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Trims
662057952031	912401052889	L6RA20B40WVA	New Addition	SpecSmart	LCA LED 6" ROUND ADJ WHITE 2000lm 840		100					New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Trims
662057952048	912401052890	L6RA20B27WVA	New Addition	SpecSmart	LCA LED 6" ROUND ADJ WHITE 2000lm 927		100					New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Trims
190096019588	912401053330	L6R15RE1VA	New Addition	ServiceSmart	LCA LED 6" ROUND IC REMODELER 1500LM ELV 120V	N						New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Frames
190096019595	912401053331	L6R15R210UVA	New Addition	ServiceSmart	LCA LED 6" ROUND IC REMODELER 1500LM 0-10V U	N						New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Frames
190096019649	912401053332	L6R20RE1VA	New Addition	ServiceSmart	LCA LED 6" ROUND IC REMODELER 2000LM ELV 120V	N						New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Frames
190096019656	912401053333	L6R20R210UVA	New Addition	ServiceSmart	LCA LED 6" ROUND IC REMODELER 2000LM 0-10V U	N						New	IPS	Downlighting - Core Downlighting		6" LyteCaster LED Round	Frames
784197006013	912400468411	2000ACV		ServiceSmart	3 1/4" MR16 IC AIRSEAL FRAME MAGNETIC TRANSFO 120V	N						27	IPS	Downlighting - Core Downlighting		3 1/4" LyteCaster MR16	Frames
784197146672	912400462003	2000LV		ServiceSmart	3 1/4" MR16 NON-IC FRAME MAGNETIC TRANSFO 120V	N		X				27	IPS	Downlighting - Core Downlighting		3 1/4" LyteCaster MR16	Frames
784197007456	912400468414	2000VE1		SpecSmart	3 1/4" MR16 NON-IC FRAME ELECTRONIC TRANSFO 120V		100					27	IPS	Downlighting - Core Downlighting		3 1/4" LyteCaster MR16	Frames
784197200053	912400463986	2000VVR		ServiceSmart	3 1/4" MR16 NON-IC REMODELER MAGNETIC TRANSFO 120V	N		X				27	IPS	Downlighting - Core Downlighting		3 1/4" LyteCaster MR16	Frames
784197239541	912400463997	2004ICV		ServiceSmart	3 3/4" LYTENING MR16 IC AIRSEAL HOUSING MAGNETIC TRANSFO 120V SCREW	C,N		X				27	IPS	Downlighting - Core Downlighting		3 3/4" LyteCaster MR16	Frames
784197238995	912400464826	2004ICVN		ServiceSmart	3 3/4" LYTENING MR16 IC AIRSEAL HOUSING MAGNETIC TRANSFO 120V NAIL	N		X				27	IPS	Downlighting - Core Downlighting		3 3/4" LyteCaster MR16	Frames
784197146556	912400460267	2006		SpecSmart	3 3/4" ADJUSTABLE SLOT MR16 WHITE		100					27	IPS	Downlighting - Core Downlighting		3 3/4" LyteCaster MR16	Trims
784197386962	912400462041	2025WH		ServiceSmart	3 3/4" MINI SWIVEL ADJUSTABLE MR16 WHITE	N		X				27	IPS	Downlighting - Core Downlighting		3 3/4" LyteCaster MR16	Trims
662057517995	912400461872	1104IC		ServiceSmart	6 3/4" INC LYTENING NEW CONSTRUCTION IC & NON-IC HOUSING SCREW	N		X				27	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent Frame	Frames
784197198589	912400463935	1104ICN		ServiceSmart	6 3/4" INC LYTENING NEW CONSTRUCTION IC & NON-IC HOUSING NAIL	C,N,L		X				27	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent Frame	Frames
784197291815	912400463975	1104ICNL		ServiceSmart	6 3/4" INC LYTENING NEW CONSTRUCTION IC & NON-IC HOUSING NAIL QUICK CONNECT	C,N,L		X				27	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent Frame	Frames
784197159337	912400463937	1104ICR		ServiceSmart	6 3/4" INC LYTENING REMODELER IC & NON-IC HOUSING SCREW	C,N		X				27	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent Frame	Frames
784197219819	912400463939	1104ICV		ServiceSmart	6 3/4" INC LYTENING ICX NEW CONSTRUCTION IC HOUSING SCREW	C,N		X				27	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent Frame	Frames
784197239015	912400463877	1104ICN		ServiceSmart	6 3/4" INC LYTENING ICX NEW CONSTRUCTION IC HOUSING NAIL	C,N		X				27	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent Frame	Frames
784197198497	912400463940	11045IC	Demoted to B	SpecSmart	6 3/4" INC LYTENING NEW CONSTRUCTION IC & NON-IC SHALLOW HOUSING SCREW		100					27	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent Frame	Frames
784197198541	912400463881	11045ICR		SpecSmart	6 3/4" INC LYTENING REMODELER IC & NON-IC SHALLOW HOUSING SCREW		100					27	IPS	Downlighting - Core Downlighting		6 3/4" LyteCaster Incandescent Frame	Frames
662057037196	912400468473	302MRSPX		ServiceSmart	LYTEPOINTS 3 3/4" REMODELER NON-IC MR16 MAGNETIC SILENT PACK	N		X				28	IPS	Downlighting - Core Downlighting		3 3/4" Lytepoints MR16	Frames
62456308128	912400475355	302MRAC3PX		ServiceSmart	LYTEPOINTS 3 3/4" IC-AIRSEAL HOUSING MR16 MAGNETIC SILENT PACK	C,N,L		X				28	IPS	Downlighting - Core Downlighting		3 3/4" Lytepoints MR16	Frames
784197433226	912400461486	302MREX		ServiceSmart	LYTEPOINTS 3 3/4" NON-IC FRAME MR16 120V ELECTRONIC	N		X				28	IPS	Downlighting - Core Downlighting		3 3/4" Lytepoints MR16	Frames
662057037233	912400475360	302MRIC7SPX	Demoted to B	SpecSmart	LYTEPOINTS 3 3/4" IC-AIRSEAL FRAME MR16 MAGNETIC SILENT PACK 7" BOX		100	X				28	IPS	Downlighting - Core Downlighting		3 3/4" Lytepoints MR16	Frames
662057037226	912400475361	302MRIC5SPX	Demoted to B	SpecSmart	LYTEPOINTS 3 3/4" IC-AIRSEAL FRAME MR16 MAGNETIC SILENT PACK 9" BOX		100	X				28	IPS	Downlighting - Core Downlighting		3 3/4" Lytepoints MR16	Frames
662057037141	912400468493	302MRSPX		ServiceSmart	LYTEPOINTS 3 3/4" NON-IC FRAME MR16 MAGNETIC SILENT PACK	N		X				28	IPS	Downlighting - Core Downlighting		3 3/4" Lytepoints MR16	Frames
784197316341	912400462096	303MRE		ServiceSmart	LYTEPOINTS 3 3/4" NON-IC SHALLOW REMODELER ELECTRONIC	C,N,L		X				28	IPS	Downlighting - Core Downlighting		3 3/4" Lytepoints MR16	Frames
784197436018	912400464946	3401MREX		ServiceSmart	LYTEPOINT 3 3/4" ADJUSTABLE	C,N,L		X				28	IPS	Downlighting - Core Downlighting		3 3/4" Lytepoints MR16	Frames
624563083418	912400462098	304CLX	Demoted to B	SpecSmart	LYTEPOINT 3 3/4" ADJUSTABLE CONE SPECULAR CLEAR		100	X				28	IPS	Downlighting - Core Downlighting		3 3/4" Lytepoints MR16	Trims
624563083319	912400464190	305WWX		ServiceSmart	LYTEPOINT 3 3/4" ADJUSTABLE Baffle WHITE	N		X				28	IPS	Downlighting - Core Downlighting		3 3/4" Lytepoints MR16	Trims
624563083494	912400462103	308WWX		SpecSmart	LYTEPOINT 3 3/4" ADJUSTABLE PINHOLE WHITE		100					28	IPS	Downlighting - Core Downlighting		3 3/4" Lytepoints MR16	Trims
784197439707	912400462111	313STX		ServiceSmart	LYTEPOINT 3 3/4" ADJUSTABLE GIMBAL BRUSHED STEEL	N,L						28	IPS	Downlighting - Core Downlighting		3 3/4" Lytepoints MR16	Trims
784197439714	912400462112	313WXX		ServiceSmart	LYTEPOINT 3 3/4" ADJUSTABLE GIMBAL WHITE	N,L		X				28	IPS	Downlighting - Core Downlighting		3 3/4" Lytepoints MR16	Trims
662057036908	912400462123	348WXX		ServiceSmart	LYTEPOINT 3 3/4" OPEN ADJUSTABLE	N,L		X				28	IPS	Downlighting - Core Downlighting		3 3/4" Lytepoints MR16	Trims
784197436070	912400462145	374CHX		ServiceSmart	LYTEPOINT 3 3/4" BASIC CONE DOWNLIGHT	N						28	IPS	Downlighting - Core Downlighting		3 3/4" Lytepoints MR16	Trims
784197436094	912400462147	375WXX		ServiceSmart	LYTEPOINT 3 3/4" ADJUSTABLE	N,L		X				28	IPS	Downlighting - Core Downlighting		3 3/4" Lytepoints MR16	Trims
784197436322	912400462152	378STX		ServiceSmart	LYTEPOINT 3 3/4" ADJUSTABLE	N		X				28	IPS	Downlighting - Core Downlighting		3 3/4" Lytepoints MR16	Trims
784197436339	912400462153	378WXX		ServiceSmart	LYTEPOINT 3 3/4" ADJUSTABLE	N,L		X				28	IPS	Downlighting - Core Downlighting		3 3/4" Lytepoints MR16	Trims
784197145125	912400460249	1955		SpecSmart	LYTECASTER RETAINING CLIP		100					28	IPS	Downlighting - Core Downlighting		LyteCaster Accessories	Accessories
784197145112	912400460250	1956		ServiceSmart	LYTECASTER SET OF 4 MOUNTING BAR CLIPS	N		X				28	IPS	Downlighting - Core Downlighting		LyteCaster Accessories	Accessories
784197367237	912400461497	LA556		SpecSmart	LYTECASTER AIRSEAL GASKET		100					28	IPS	Downlighting - Core Downlighting		LyteCaster Accessories	Accessories
783288154447	912400341080	PA		ServiceSmart	4" C PLUS NEW CONSTRUCTION NON-IC HOUSING	N		X				29	IPS	Downlighting - Core Downlighting		4" C Plus	Frames
783288154454	912400341081	PAABC		ServiceSmart	4" C PLUS NEW CONSTRUCTION IC-AIRSEAL HOUSING	C,N,L		X				29	IPS	Downlighting - Core Downlighting		4" C Plus	Frames
783288154461	912400341082	PAR		ServiceSmart	4" C PLUS NON-IC REMODELER HOUSING	C,N,L		X				29	IPS	Downlighting - Core Downlighting		4" C Plus	Frames
783288154485	912400341084	PABW		ServiceSmart	C PLUS 4" WHITE Baffle DOWNLIGHT	C,N,L		X				29	IPS	Downlighting - Core Downlighting		4" C Plus	Trims

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
78328154577	912400341093	PAGW		ServiceSmart	C PLUS 4" ADJUSTABLE GIMBAL WHITE	C		X				29	IPS	Downlighting - Core Downlighting		4" C Plus	Trims
78328154515	91240034087	PARC		ServiceSmart	4" C PLUS CLEAR CONE DOWNLIGHT	L		X				29	IPS	Downlighting - Core Downlighting		4" C Plus	Trims
78328131233	912400340776	CR18MBQP		ServiceSmart	6" C PLUS IC/AIRSEAL, INC REMODELER HOUSING	N		X				29	IPS	Downlighting - Core Downlighting		6" C Plus	Frames
78328182891	912400341655	PR26ASCNB1		ServiceSmart	6" C PLUS NEW CONSTRUCTION IC AIRSEAL 26W CFL VERTICAL	N		X				29	IPS	Downlighting - Core Downlighting		6" C Plus	Frames
78328169021	912400341293	PR75ASCNB		ServiceSmart	6" C PLUS NEW CONSTRUCTION IC AIRSEAL HOUSING	L		X				29	IPS	Downlighting - Core Downlighting		6" C Plus	Frames
78328188886	912400341792	QL6NBQP		ServiceSmart	6" C PLUS NEW CONSTRUCTION AIRSEAL / IC QUICKLIGHTS HOUSING	C,NL		X				29	IPS	Downlighting - Core Downlighting		6" C Plus	Frames
78328121166	912400340666	R18P		ServiceSmart	6" EYEBALL BR30 WHITE	C,NL		X				29	IPS	Downlighting - Core Downlighting		6" C Plus	Trims
78328121388	912400340678	R830W		ServiceSmart	6" PAR38,PAR30,BR30 GROOVED BAFFLE WHITE	L		X				29	IPS	Downlighting - Core Downlighting		6" C Plus	Trims
78328121395	912400340679	R840W		ServiceSmart	6" PAR38, BR40 GROOVED BAFFLE WHITE	CL		X				29	IPS	Downlighting - Core Downlighting		6" C Plus	Trims
78328190988	912400341977	RBA1DOCLR		ServiceSmart	C PLUS 6" CLEAR REFLECTOR FOR INC & CFL	CL		X				29	IPS	Downlighting - Core Downlighting		6" C Plus	Trims
78328137020	912400340829	RBC30WM		ServiceSmart	6" PAR38,PAR30,BR30 CONE GROOVED BAFFLE WHITE	N,L		X				29	IPS	Downlighting - Core Downlighting		6" C Plus	Trims
783238039904	912400340226	RC30C		ServiceSmart	6" CLEAR CONE FOR INC OR CFL WHITE FLANGE	L		X				29	IPS	Downlighting - Core Downlighting		6" C Plus	Trims
78328154386	912400341079	RF30W		ServiceSmart	6" PAR30 WHITE LARGE FLANGE TRIM	L		X				29	IPS	Downlighting - Core Downlighting		6" C Plus	Trims
783238039966	912400340230	RS30W		ServiceSmart	6" PAR30 WHITE SPAY TRIM	N,L		X				29	IPS	Downlighting - Core Downlighting		6" C Plus	Trims
78328017551	912400340101	SHR12C		ServiceSmart	6" A19 ALBALITE REGRESSED LENS PLASTIC WHITE FLANGE	C,NL		X				29	IPS	Downlighting - Core Downlighting		6" C Plus	Trims
78328015267	912400340092	SHR18C		ServiceSmart	6" A19 DROP OPAL SHOWER LIGHT VERTICAL PLASTIC WHITE FLANGE	C,NL		X				29	IPS	Downlighting - Core Downlighting		6" C Plus	Trims
78328161476	912400341222	SHR6CW		ServiceSmart	6" REGRESSED SHOWER LIGHT CFL VERTICAL WHITE	L		X				29	IPS	Downlighting - Core Downlighting		6" C Plus	Trims
662057979144	912401050103	PARD10N210VVB		ServiceSmart	4" LyteProfile FIK Nonic 1000 210 VB	C,NL		X				30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Frames
662057979182	912401050111	PARD10N210VVBEM		SpecSmart	4" LyteProfile FIK Nonic 1000 EM 210 VB		100					30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Frames
662057979151	912401050105	PARD15N210VVB		ServiceSmart	4" LyteProfile FIK Nonic 1500 210 VB	C,NL		X				30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Frames
662057979199	912401050112	PARD15N210VVBEM		SpecSmart	4" LyteProfile FIK Nonic 1500 EM 210 VB		100					30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Frames
662057979168	912401050123	PARD20N210VVB		ServiceSmart	4" LyteProfile FIK Nonic 2000 120 210 VB	N		X				30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Frames
662057979205	912401050125	PARD20N210VVBEM		SpecSmart	4" LyteProfile FIK Nonic 2000 120 210 VB		100					30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Frames
662057979175	912401050124	PARD20N210VVB		ServiceSmart	4" LyteProfile FIK Nonic 2000 277 210 VB	C,N		X				30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Frames
662057979212	912401050126	PARD20N210VVBEM		SpecSmart	4" LyteProfile FIK Nonic 2000 277 210 VB		100					30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Frames
662057980355	912401050120	PARD830VB		ServiceSmart	4" LyteProfile Light Engine 80CR 30K VB	C,NL		X				30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Light Engine
662057980362	912401050121	PARD835VB		ServiceSmart	4" LyteProfile Light Engine 80CR1 35K VB	C,NL		X				30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Light Engine
662057980386	912401050092	PARDCC		ServiceSmart	4" LyteProfile Comfort Clear Reflector	C,NL		X				30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Trims
662057980454	912401050099	PARLWCC		ServiceSmart	4" LyteProfile Comfort Clear Lens WW	N		X				30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Trims
662057981307	912401050143	PARD10N210VVB		SpecSmart	4" LyteProfile FIK Nonic 1000m 210 VB		100	X				30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Frames
662057981406	912401050145	PARD10N210VVBEM		SpecSmart	4" LyteProfile FIK Nonic 1000 EM 210 VB		100					30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Frames
662057981314	912401050142	PARD15N210VVB		ServiceSmart	4" LyteProfile FIK Nonic 1500m 210 VB	C,NL		X				30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Frames
662057981413	912401050146	PARD15N210VVBEM		SpecSmart	4" LyteProfile FIK Nonic 1500 EM 210 VB		100					30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Frames
662057981321	912401050143	PARD20N210VVB		ServiceSmart	4" LyteProfile FIK Nonic 2000m 210 VB	N		X				30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Frames
662057981420	912401050147	PARD20N210VVBEM		SpecSmart	4" LyteProfile FIK Nonic 2000 EM 210 VB		100					30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Frames
662057981338	912401050091	PARD25N210VVB		ServiceSmart	4" LyteProfile FIK Nonic 2500 120 210 VB	C,N		X				30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Frames
662057981437	912401050148	PARD25N210VVBEM		SpecSmart	4" LyteProfile FIK Nonic 2500 120 210 VB		100					30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Frames
662057981345	912401050144	PARD25N210VVB		ServiceSmart	4" LyteProfile FIK Nonic 2500 277 210 VB	N		X				30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Frames
662057981444	912401050149	PARD25N210VVBEM		SpecSmart	4" LyteProfile FIK Nonic 2500 277 210 VB		100					30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Frames
662057981277	912401050138	PARD830VB		ServiceSmart	4" LyteProfile Light Engine 80CR1 30K VB	C,NL		X				30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Light Engine
662057981284	912401050139	PARD835VB		ServiceSmart	4" LyteProfile Light Engine 80CR1 35K VB	C,NL		X				30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Light Engine
662057994796	912400532706	PARDCC		ServiceSmart	4" LyteProfile Comfort Clear Reflector	C,NL		X				30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Trims
662057994864	912400532713	PARLWCC		ServiceSmart	4" LyteProfile Comfort Clear WW	C,NL		X				30	IPS	Downlighting - Performance Downlighting		4" LyteProfile Downlight	Trims
662057569970	912400463688	CAZMR		SpecSmart	Calculate Accessory 1.75" Flush Mount Ring		100					31	IPS	Downlighting - Statement Downlighting		1 3/4" Calculate LED	Accessories
662057525492	912400492075	GAX2PMR		SpecSmart	Calculate Accessory 1.75" Square Flush Mount		100					31	IPS	Downlighting - Statement Downlighting		1 3/4" Calculate LED	Accessories
662057545156	912400482073	CL04DL30KX25R1		SpecSmart	1.75" FIK Remodeler, 3000K, 25 Degree 120V, CZL or CZx2L, rfd		100					31	IPS	Downlighting - Statement Downlighting		1 3/4" Calculate LED	Frames
662057741819	912400499193	CL04DL30KX25R1Z10V		SpecSmart	1.75" FIK Remodeler, 3000K, 25 Degree 120-277V, 0-10V dimming		100					31	IPS	Downlighting - Statement Downlighting		1 3/4" Calculate LED	Frames
662057634463	912400461267	CZLIC		SpecSmart	Calculate 2.0" Aperture New Construction		100					31	IPS	Downlighting - Statement Downlighting		1 3/4" Calculate LED	Frames
662057547476	912400470994	CLDLCCP		SpecSmart	Calculate 1.75" LED REF, Downlight Reflector		100					31	IPS	Downlighting - Statement Downlighting		1 3/4" Calculate LED	Trims
784197492410	912400471048	CSMRDCCDW		SpecSmart	CALCULATE 3"TRIM CCD W/WHITE FLANGE		100					31	IPS	Downlighting - Statement Downlighting		3" Calculate LED	Trims
784197492113	912400463032	CLVE1		ServiceSmart	Calculate 3" Frame Non IC, Low Voltage Electronic Transformer - 120V	N						31	IPS	Downlighting - Statement Downlighting		3" Calculate Low Voltage MR16	Frames
784197492212	912400471039	CSMRACCDW	Demoted to B	SpecSmart	Calculate 3" Trim Kit Adjustable Accent CCD w/White Flange		100					31	IPS	Downlighting - Statement Downlighting		3" Calculate Low Voltage MR16	Trims
784197272227	912400468697	8011CCLW		ServiceSmart	4" 18W Triple Tube Vertical Downlight Reflector Comfort Clear White Flange	N						32	IPS	Downlighting - Statement Downlighting		4" Calculate CFL	Trims
784197529222	912400471086	CAALVE1	Demoted to B	SpecSmart	Calculate 4" Frame IC,AirSeal Low Voltage, Electronic Transformer - 120V		100					32	IPS	Downlighting - Statement Downlighting		4" Calculate Low Voltage MR16	Frames

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
784197529284	912400463047	CALVMU		ServiceSmart	Calculate 4" Frame, Non-IC, Low Voltage	C,NL						32	IPS	Downlighting - Statement Downlighting		4" Calculate Low Voltage MR16	Frames
784197242862	912400471110	CAMRACCDW	Demoted to B	SpecSmart	Calculate 4" Trim Kit Adjustable Accent CCD w/White Flange		100					32	IPS	Downlighting - Statement Downlighting		4" Calculate Low Voltage MR16	Trims
784197240226	912400468661	S132BUM		SpecSmart	6" FK 1-LT 26/32W Triple Tube Electronic Remodeler		100					32	IPS	Downlighting - Statement Downlighting		6" Calculate CFL	Frames
662057601007	912400474682	S6132B2MX		SpecSmart	6" FK 1-26/32W TTT 277V w/Advance Mark 10		100					32	IPS	Downlighting - Statement Downlighting		6" Calculate CFL	Frames
662057131264	912400479305	S6132BULECD		SpecSmart	6" FK 1-26/32W TTT Lutron Eco-System		100					32	IPS	Downlighting - Statement Downlighting		6" Calculate CFL	Frames
662057107738	912400474683	S6132BUM7		SpecSmart	6" FK 1-26/32W TTT 120/277V MARK VII Dimming		100					32	IPS	Downlighting - Statement Downlighting		6" Calculate CFL	Frames
784197418588	912400468072	S6132BU		ServiceSmart	6" FK 1-32W Triple Tube for Vertical and Horizontal Lamp	N						32	IPS	Downlighting - Statement Downlighting		6" Calculate CFL	Frames
784197447083	912400472325	S6132BUEM		ServiceSmart	6" FK Steel 1-26/32W TTT 120/277V w/Emergency	C,NL						32	IPS	Downlighting - Statement Downlighting		6" Calculate CFL	Frames
662057601045	912400476899	S6132BUEM4E		SpecSmart	6" FK 1-26/32W TTT 120/277V EM w/ Integral EM Test		100					32	IPS	Downlighting - Statement Downlighting		6" Calculate CFL	Frames
662057011554	912400472328	S6132BULC		SpecSmart	6" FK Aperture, (1) 26/32W Triple Tube - Chicago Plenum		100					32	IPS	Downlighting - Statement Downlighting		6" Calculate CFL	Frames
784197510633	912400492778	S6132BUS		SpecSmart	6" FK Aperture, (1) 26/32W Triple Tube		100					32	IPS	Downlighting - Statement Downlighting		6" Calculate CFL	Frames
784197226527	912400468705	8021CCLW		ServiceSmart	6" 26/32W Triple Tube Vertical Reflector Comfort Clear White Flange	N						32	IPS	Downlighting - Statement Downlighting		6" Calculate CFL	Trims
784197226657	912400472808	8021WWCCCLW		SpecSmart	6" 26/32W Triple Tube Single Open Wall Wash Reflector		100					32	IPS	Downlighting - Statement Downlighting		6" Calculate CFL	Trims
784197226695	912400468727	8021CCLW		ServiceSmart	6" Horiz.Tri-Tube Downlight Reflector Comfort Clear White Flange	C,NL						32	IPS	Downlighting - Statement Downlighting		6" Calculate CFL	Trims
784197631334	912400468082	S7132BU		SpecSmart	7" FK 1-32W TTT Electronic 4-PIN UVN Steel FIK		100					32	IPS	Downlighting - Statement Downlighting		7" Calculate CFL	Frames
784197527112	912400468083	S7142BU		ServiceSmart	7" FK 1-26/32/42W Triple Tube ELECT Frame in Kit for Vertical & Horizontal Lamp	C,NL						32	IPS	Downlighting - Statement Downlighting		7" Calculate CFL	Frames
784197527136	912400473460	S7142BUEM	Demoted to B	SpecSmart	7" FK Steel 1-42W TTT 120/277V Emergency		100					32	IPS	Downlighting - Statement Downlighting		7" Calculate CFL	Frames
784197227555	912400468714	8022CCLW		SpecSmart	7" 32/42W Triple Tube Downlight Vertical Reflector Comfort Clear White Flange		100					32	IPS	Downlighting - Statement Downlighting		7" Calculate CFL	Trims
662057914206	912400517615	CALISA5K8FL		SpecSmart	Calculate White LED 4" Accent Light Engine - 1500lm/3500K, 80CRI, Flood		100					33	IPS	Downlighting - Statement Downlighting		4" Calculate White LED Accent	Frames
662057914411	912400527632	CALISNU210V		SpecSmart	Calculate White LED 4" Accent Frame in Kit, New Construction, 210V 120-277V		100					33	IPS	Downlighting - Statement Downlighting		4" Calculate White LED Accent	Frames
784197307950	912400491548	CALV1RM		SpecSmart	EVOLUTION 4" NON-IC 120V REMODEL FIK		100					New	IPS	Downlighting - Statement Downlighting		4" Calculate White LED Accent	Frames
662057914046	912400527999	CALACCLW		SpecSmart	Calculate White LED 4" Accent Reflector, CCL Finish, White Flange		100					33	IPS	Downlighting - Statement Downlighting		4" Calculate White LED Accent	Trims
662057862033	912400514414	CAL10NUV8210V		SpecSmart	Calculate 4" 1000 Lumen LED New Construction - 120-277V		100					33	IPS	Downlighting - Statement Downlighting		4" Calculate White LED Round	Frames
662057862118	912400514418	CAL15N2V8210V		SpecSmart	Calculate 4" 1500 Lumen LED New Construction - 277V		100					33	IPS	Downlighting - Statement Downlighting		4" Calculate White LED Round	Frames
662057855196	912400515146	CAL10DL30KCCCLW8		SpecSmart	Calculate 4" 1000 /1500 Lumen 3000K LED Downlight Trim Comfort Clear White Flange		100					33	IPS	Downlighting - Statement Downlighting		4" Calculate White LED Round	Trims
784197527198	912400468092	S8242HU		SpecSmart	8" FK 2-28/32/42W TriPE Tube ELEC 4PIN		100					33	IPS	Downlighting - Statement Downlighting		8" Calculate CFL	Frames
784197527082	912400472355	S8242HUEM		SpecSmart	8" FK Steel 2-28/32/42W TTT 120/277V with Emergency		100					33	IPS	Downlighting - Statement Downlighting		8" Calculate CFL	Frames
784197226978	912400468748	S838CCLW		SpecSmart	8" Horiz.T8U Tube Downlight Reflector CCD with White Flange		100					33	IPS	Downlighting - Statement Downlighting		8" Calculate CFL	Trims
190096030293	912400538354	CARRFT	New Addition - New Product	ServiceSmart	Calculate Accessory 4" Flush trim	N		X				New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
784197211387	912401128268	CARN	New Addition - New Product	ServiceSmart	Calculate 4" Non-IC	C,NL		X	X			New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
784197211431	912401128269	CARNEM	New Addition - New Product	ServiceSmart	Calculate 4" Non-IC Emergency	N		X	X			New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
784197211448	912400540185	CARNLC	New Addition - New Product	ServiceSmart	Calculate 4" Non-IC Chicago Plenum	N		X	X			New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
662057974842	912400538818	CAL10B35M210U	New Addition - New Product	ServiceSmart	Calculate 4" 1000lm 80 35K Med 0-10V Univ	N		X	X			New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
662057975351	912400538868	CAL15B35M210U	New Addition - New Product	ServiceSmart	Calculate 4" 1500lm 80 35K Med 0-10V Univ	N		X	X			New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
662057972008	912400539321	CARDLCC	New Addition - New Product	ServiceSmart	Calculate 4" DL CC finish W8 Ring	N		X	X			New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
662057965000	912400539338	CARRWCC	New Addition - New Product	ServiceSmart	Calculate 4" Wall Wash CC finish W8 Ring	N		X				New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
784197211394	912400540160	CARN3	New Addition - New Product	SpecSmart	Calculate 4" Non-IC 347V		100					New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
784197211455	912400540163	CARR	New Addition - New Product	SpecSmart	Calculate 4" Non-IC RM		100					New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
784197211462	912400540164	CARR3	New Addition - New Product	SpecSmart	Calculate 4" Non-IC RM 347V		100					New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
784197240578	912400540173	CARA	New Addition - New Product	SpecSmart	Calculate 4" Alnsa/IC		100					New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
662057974439	912400538776	CAL05830N210U	New Addition - New Product	SpecSmart	Calculate 4" 500lm 80 30K Nar 0-10V Univ		100					New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
662057974446	912400538772	CAL05835N210U	New Addition - New Product	SpecSmart	Calculate 4" 500lm 80 35K Nar 0-10V Univ		100					New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
662057974453	912400538778	CAL05840N210U	New Addition - New Product	SpecSmart	Calculate 4" 500lm 80 40K Nar 0-10V Univ		100					New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
662057974477	912400538780	CAL05830M210U	New Addition - New Product	SpecSmart	Calculate 4" 500lm 80 30K Med 0-10V Univ		100					New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
662057974484	912400538781	CAL05835M210U	New Addition - New Product	SpecSmart	Calculate 4" 500lm 80 35K Med 0-10V Univ		100					New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
662057974491	912400538782	CAL05840M210U	New Addition - New Product	SpecSmart	Calculate 4" 500lm 80 40K Med 0-10V Univ		100					New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
662057974514	912400538784	CAL05830W210U	New Addition - New Product	SpecSmart	Calculate 4" 500lm 80 30K Wide 0-10V Univ		100					New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
662057974521	912400538785	CAL05835W210U	New Addition - New Product	SpecSmart	Calculate 4" 500lm 80 35K Wide 0-10V Univ		100					New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
662057974538	912400538786	CAL05840W210U	New Addition - New Product	SpecSmart	Calculate 4" 500lm 80 40K Wide 0-10V Univ		100					New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
662057974798	912400538813	CAL10B30N210U	New Addition - New Product	SpecSmart	Calculate 4" 1000lm 80 30K Nar 0-10V Univ		100					New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
662057974804	912400538814	CAL10B35N210U	New Addition - New Product	SpecSmart	Calculate 4" 1000lm 80 35K Nar 0-10V Univ		100					New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
662057974811	912400538815	CAL10B40N210U	New Addition - New Product	SpecSmart	Calculate 4" 1000lm 80 40K Nar 0-10V Univ		100					New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
662057974835	912400538817	CAL10B30M210U	New Addition - New Product	SpecSmart	Calculate 4" 1000lm 80 30K Med 0-10V Univ		100					New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	
662057974859	912400538819	CAL10B40M210U	New Addition - New Product	SpecSmart	Calculate 4" 1000lm 80 40K Med 0-10V Univ		100					New	IPS	Downlighting - Statement Downlighting		Calculate 4" LED Round Gen3	

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliance	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
784197359874	912400468632	4M132HU		SpecSmart	LG		100					33	IPS	Downlighting - Statement Downlighting		Calculate CFL Matrix	Frames
784197363093	912400474573	4M132HUEME		SpecSmart	4 1/2" Square FK - 26, 32W Triple Integral EM with internal test switch		100					33	IPS	Downlighting - Statement Downlighting		Calculate CFL Matrix	Frames
784197363531	912400469794	4MCCUW	Promoted to A	ServiceSmart	4 1/2" x 4 1/2" Open Trim - CC/White	N						33	IPS	Downlighting - Statement Downlighting		Calculate CFL Matrix	Trims
66205782347	912400514424	CEL15NUVR210V		ServiceSmart	Calculate 6" 1500 Lumen LED New Construction 120-277V	C,N,L						34	IPS	Downlighting - Statement Downlighting		6" Calculate White LED Round	Frames
66205782385	912400514426	CEL20N1VR210V		ServiceSmart	Calculate 6" 2000 Lumen LED New Construction 120V	C,N,L						34	IPS	Downlighting - Statement Downlighting		6" Calculate White LED Round	Frames
66205782422	912400514428	CEL20N2VR210V		SpecSmart	Calculate 6" 2000 Lumen LED New Construction 277V		100					34	IPS	Downlighting - Statement Downlighting		6" Calculate White LED Round	Frames
190096030316	912400538336	CAGRPT	New Addition - New Product	ServiceSmart	Calculate Accessory 6" Flush trim	N		X				New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
784197211530	912401282271	CBRN	New Addition - New Product	ServiceSmart	Calculate 6" Non-IC	C,N,L		X	X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
784197211554	912401282272	CBRNEM	New Addition - New Product	ServiceSmart	Calculate 6" Non-IC Emergency	N		X	X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
784197211622	912400540183	CBRNLC	New Addition - New Product	ServiceSmart	Calculate 6" Non-IC Chicago Plenum	N		X	X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057978109	912400539109	CEL15S3M210U	New Addition - New Product	ServiceSmart	Calculate 6" 1500lm 80 35K Med 0-10V Univ	N		X	X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057979625	912400539157	CEL20S3M210U	New Addition - New Product	ServiceSmart	Calculate 6" 2000lm 80 35K Med 0-10V Univ	N		X	X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057972862	912400539441	CBRLCC	New Addition - New Product	ServiceSmart	Calculate 6" DL CC finish WH flng	N		X	X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057964342	912400539456	CBRWCC	New Addition - New Product	ServiceSmart	Calculate 6" Wall Wash CC finish WH flng	N		X				New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
784197211547	912400540172	CBRN3	New Addition - New Product	SpecSmart	Calculate 6" Non-IC 347V		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
784197211639	912400540175	CBRR	New Addition - New Product	SpecSmart	Calculate 6" Non-IC RM		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
784197211646	912400540176	CBRR3	New Addition - New Product	SpecSmart	Calculate 6" Non-IC RM 347V		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
784197246608	912400540173	CBRA	New Addition - New Product	SpecSmart	Calculate 6" Airstair/IC		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057977577	912400539055	CEL10S30N210U	New Addition - New Product	SpecSmart	Calculate 6" 1000lm 80 30K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057977584	912400539056	CEL10S35N210U	New Addition - New Product	SpecSmart	Calculate 6" 1000lm 80 35K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057977591	912400539057	CEL10S40N210U	New Addition - New Product	SpecSmart	Calculate 6" 1000lm 80 40K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057977614	912400539059	CEL10S30M210U	New Addition - New Product	SpecSmart	Calculate 6" 1000lm 80 30K Med 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057977621	912400539060	CEL10S35M210U	New Addition - New Product	SpecSmart	Calculate 6" 1000lm 80 35K Med 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057977638	912400539061	CEL10S40M210U	New Addition - New Product	SpecSmart	Calculate 6" 1000lm 80 40K Med 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057977652	912400539063	CEL10S30W210U	New Addition - New Product	SpecSmart	Calculate 6" 1000lm 80 30K Wide 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057977669	912400539064	CEL10S35W210U	New Addition - New Product	SpecSmart	Calculate 6" 1000lm 80 35K Wide 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057977676	912400539065	CEL10S40W210U	New Addition - New Product	SpecSmart	Calculate 6" 1000lm 80 40K Wide 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057978055	912400539104	CEL15S30N210U	New Addition - New Product	SpecSmart	Calculate 6" 1500lm 80 30K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057978062	912400539105	CEL15S35N210U	New Addition - New Product	SpecSmart	Calculate 6" 1500lm 80 35K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057978079	912400539106	CEL15S40N210U	New Addition - New Product	SpecSmart	Calculate 6" 1500lm 80 40K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057978093	912400539108	CEL15S30M210U	New Addition - New Product	SpecSmart	Calculate 6" 1500lm 80 30K Med 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057978116	912400539110	CEL15S40M210U	New Addition - New Product	SpecSmart	Calculate 6" 1500lm 80 40K Med 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057978130	912400539112	CEL15S30W210U	New Addition - New Product	SpecSmart	Calculate 6" 1500lm 80 30K Wide 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057978147	912400539113	CEL15S35W210U	New Addition - New Product	SpecSmart	Calculate 6" 1500lm 80 35K Wide 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057978154	912400539114	CEL15S40W210U	New Addition - New Product	SpecSmart	Calculate 6" 1500lm 80 40K Wide 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057979083	912400539152	CEL20S30N210U	New Addition - New Product	SpecSmart	Calculate 6" 2000lm 80 30K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057979090	912400539153	CEL20S35N210U	New Addition - New Product	SpecSmart	Calculate 6" 2000lm 80 35K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057979106	912400539154	CEL20S40N210U	New Addition - New Product	SpecSmart	Calculate 6" 2000lm 80 40K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057979133	912400539156	CEL20S30M210U	New Addition - New Product	SpecSmart	Calculate 6" 2000lm 80 30K Med 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057979132	912400539158	CEL20S40M210U	New Addition - New Product	SpecSmart	Calculate 6" 2000lm 80 40K Med 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057979922	912400539160	CEL20S30W210U	New Addition - New Product	SpecSmart	Calculate 6" 2000lm 80 30K Wide 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057979939	912400539161	CEL20S35W210U	New Addition - New Product	SpecSmart	Calculate 6" 2000lm 80 35K Wide 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057979977	912400539162	CEL20S40W210U	New Addition - New Product	SpecSmart	Calculate 6" 2000lm 80 40K Wide 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057981857	912400539188	CEL25S30N210U	New Addition - New Product	SpecSmart	Calculate 6" 2500lm 80 30K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057981864	912400539189	CEL25S35N210U	New Addition - New Product	SpecSmart	Calculate 6" 2500lm 80 35K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057981871	912400539190	CEL25S40N210U	New Addition - New Product	SpecSmart	Calculate 6" 2500lm 80 40K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057982038	912400539192	CEL25S30M210U	New Addition - New Product	SpecSmart	Calculate 6" 2500lm 80 30K Med 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057982151	912400539193	CEL25S35M210U	New Addition - New Product	SpecSmart	Calculate 6" 2500lm 80 35K Med 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057982168	912400539194	CEL25S40M210U	New Addition - New Product	SpecSmart	Calculate 6" 2500lm 80 40K Med 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057982182	912400539196	CEL25S30W210U	New Addition - New Product	SpecSmart	Calculate 6" 2500lm 80 30K Wide 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057982205	912400539197	CEL25S35W210U	New Addition - New Product	SpecSmart	Calculate 6" 2500lm 80 35K Wide 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057982212	912400539198	CEL25S40W210U	New Addition - New Product	SpecSmart	Calculate 6" 2500lm 80 40K Wide 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057982394	912400539225	CEL35S30N210U	New Addition - New Product	SpecSmart	Calculate 6" 3500lm 80 30K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	
662057983417	912400539226	CEL35S35N210U	New Addition - New Product	SpecSmart	Calculate 6" 3500lm 80 35K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculate 6" LED Round Gen3	

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
662057883424	912400539227	CEL35840NZ10U	New Addition - New Product	SpecSmart	Calculte 6" 3500lm 80 40K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
662057883448	912400539229	CEL35830MZ10U	New Addition - New Product	SpecSmart	Calculte 6" 3500lm 80 30K Med D-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
662057883455	912400539230	CEL35835MZ10U	New Addition - New Product	SpecSmart	Calculte 6" 3500lm 80 35K Med D-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
662057883509	912400539231	CEL35840MZ10U	New Addition - New Product	SpecSmart	Calculte 6" 3500lm 80 40K Med D-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
662057883752	912400539233	CEL35830WZ10U	New Addition - New Product	SpecSmart	Calculte 6" 3500lm 80 30K Wide D-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
662057883769	912400539234	CEL35835WZ10U	New Addition - New Product	SpecSmart	Calculte 6" 3500lm 80 35K Wide D-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
662057883790	912400539235	CEL35840WZ10U	New Addition - New Product	SpecSmart	Calculte 6" 3500lm 80 40K Wide D-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
66205795861	912400539273	CEL48830NZ10U	New Addition - New Product	SpecSmart	Calculte 6" 4800lm 80 30K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
66205795878	912400539274	CEL48835NZ10U	New Addition - New Product	SpecSmart	Calculte 6" 4800lm 80 35K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
66205795892	912400539275	CEL48840NZ10U	New Addition - New Product	SpecSmart	Calculte 6" 4800lm 80 40K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
66205799999	912400539277	CEL48830MZ10U	New Addition - New Product	SpecSmart	Calculte 6" 4800lm 80 30K Med D-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
19096020027	912400539278	CEL48835MZ10U	New Addition - New Product	SpecSmart	Calculte 6" 4800lm 80 35K Med D-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
19096021727	912400539279	CEL48840MZ10U	New Addition - New Product	SpecSmart	Calculte 6" 4800lm 80 40K Med D-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
19096021741	912400539281	CEL48830WZ10U	New Addition - New Product	SpecSmart	Calculte 6" 4800lm 80 30K Wide D-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
19096021758	912400539282	CEL48835WZ10U	New Addition - New Product	SpecSmart	Calculte 6" 4800lm 80 35K Wide D-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
19096021772	912400539283	CEL48840WZ10U	New Addition - New Product	SpecSmart	Calculte 6" 4800lm 80 40K Wide D-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
19096021925	912400539293	CEL60830NZ10U	New Addition - New Product	SpecSmart	Calculte 6" 6000lm 80 30K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
19096021932	912400539296	CEL60835NZ10U	New Addition - New Product	SpecSmart	Calculte 6" 6000lm 80 35K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
19096021949	912400539299	CEL60840NZ10U	New Addition - New Product	SpecSmart	Calculte 6" 6000lm 80 40K Nar 0-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
19096021963	912400539302	CEL60830MZ10U	New Addition - New Product	SpecSmart	Calculte 6" 6000lm 80 30K Med D-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
19096021970	912400539303	CEL60835MZ10U	New Addition - New Product	SpecSmart	Calculte 6" 6000lm 80 35K Med D-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
19096021987	912400539304	CEL60840MZ10U	New Addition - New Product	SpecSmart	Calculte 6" 6000lm 80 40K Med D-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
19096022007	912400539306	CEL60830WZ10U	New Addition - New Product	SpecSmart	Calculte 6" 6000lm 80 30K Wide D-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
19096022014	912400539307	CEL60835WZ10U	New Addition - New Product	SpecSmart	Calculte 6" 6000lm 80 35K Wide D-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
19096022021	912400539308	CEL60840WZ10U	New Addition - New Product	SpecSmart	Calculte 6" 6000lm 80 40K Wide D-10V Univ		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
662057972879	912400539442	GRDLCL	New Addition - New Product	SpecSmart	Calculte 6" DL CL finish WH flng		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
662057972886	912400539443	GRDLCD	New Addition - New Product	SpecSmart	Calculte 6" DL CD finish WH flng		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
19096022434	912400539445	GRDLWH	New Addition - New Product	SpecSmart	Calculte 6" DL WH finish WH flng		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
662057972923	912400539447	GRDLCCP	New Addition - New Product	SpecSmart	Calculte 6" DL CC finish Pol flng		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
662057972930	912400539448	GRDLCLP	New Addition - New Product	SpecSmart	Calculte 6" DL CL finish Pol flng		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
662057972947	912400539449	GRDLCDP	New Addition - New Product	SpecSmart	Calculte 6" DL CD finish Pol flng		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
662057972978	912400539452	GRDLCCF	New Addition - New Product	SpecSmart	Calculte 6" DL CC finish Flngless		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
662057972985	912400539453	GRDLCLF	New Addition - New Product	SpecSmart	Calculte 6" DL CL finish Flngless		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
662057972992	912400539454	GRDLCDF	New Addition - New Product	SpecSmart	Calculte 6" DL CD finish Flngless		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
19096022438	912400539456	GRDLWHF	New Addition - New Product	SpecSmart	Calculte 6" DL WH finish Flngless		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
66205796366	912400539460	GRWWWD	New Addition - New Product	SpecSmart	Calculte 6" Wall Wash CD finish WH flng		100					New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
19096022465	912400539462	GRWWWH	New Addition - New Product	SpecSmart	Calculte 6" Wall Wash WH finish WH flng		100					New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
19096022489	912400539473	GRWWWHF	New Addition - New Product	SpecSmart	Calculte 6" Wall Wash WH finish Flngless		100					New	IPS	Downlighting - Statement Downlighting		Calculte 6" LED Round Gen3	
19096030330	912400538538	CA7RPT	New Addition - New Product	ServiceSmart	Calculte Accessory 7" Flush trim	N		X				New	IPS	Downlighting - Statement Downlighting		Calculte 7" LED Round Gen3	
784197211714	912401282275	CFRN	New Addition - New Product	ServiceSmart	Calculte 7" Non-IC	N		X	X			New	IPS	Downlighting - Statement Downlighting		Calculte 7" LED Round Gen3	
784197211738	912401282276	CFRNEM	New Addition - New Product	ServiceSmart	Calculte 7" Non-IC Emergency	N		X	X			New	IPS	Downlighting - Statement Downlighting		Calculte 7" LED Round Gen3	
784197211721	912400540184	CFRNS	New Addition - New Product	SpecSmart	Calculte 7" Non-IC 347V		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 7" LED Round Gen3	
784197211745	912400540179	CFRNIC	New Addition - New Product	SpecSmart	Calculte 7" Non-IC Chicago Plenum		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 7" LED Round Gen3	
662057970745	912400539750	CFRDLNMCC	New Addition - New Product	SpecSmart	Calculte 7" DL NM CC finish WH flng	N			X			New	IPS	Downlighting - Statement Downlighting		Calculte 7" LED Round Gen3	
662057970752	912400539751	CFRDLNML	New Addition - New Product	SpecSmart	Calculte 7" DL NM CL finish WH flng		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 7" LED Round Gen3	
662057970769	912400539752	CFRDLNMC	New Addition - New Product	SpecSmart	Calculte 7" DL NM CD finish WH flng		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 7" LED Round Gen3	
19096022755	912400539754	CFRDLNMWH	New Addition - New Product	SpecSmart	Calculte 7" DL NM WH finish WH flng		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 7" LED Round Gen3	
662057970806	912400539756	CFRDLNMCPP	New Addition - New Product	SpecSmart	Calculte 7" DL NM CC finish Pol flng		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 7" LED Round Gen3	
662057970820	912400539758	CFRDLNMCDF	New Addition - New Product	SpecSmart	Calculte 7" DL NM CD finish Pol flng		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 7" LED Round Gen3	
19096022779	912400539765	CFRDLNMWHF	New Addition - New Product	SpecSmart	Calculte 7" DL NM WH finish Flngless		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 7" LED Round Gen3	
662057970912	912400539767	CFRDLWCC	New Addition - New Product	SpecSmart	Calculte 7" DL Wide CC finish WH flng	N			X			New	IPS	Downlighting - Statement Downlighting		Calculte 7" LED Round Gen3	
662057970929	912400539768	CFRDLWCL	New Addition - New Product	SpecSmart	Calculte 7" DL Wide CL finish WH flng		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 7" LED Round Gen3	
662057970936	912400539769	CFRDLWCD	New Addition - New Product	SpecSmart	Calculte 7" DL Wide CD finish WH flng		100		X			New	IPS	Downlighting - Statement Downlighting		Calculte 7" LED Round Gen3	
66205782460	912400514862	CEX615NUNVBZ10V		SpecSmart	Calculte 6x6 1500 Lumen LED New Construction 120-277V		100					35	IPS	Downlighting - Statement Downlighting		6" x 6" Calculte White LED Square	Frames

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
784197145002	912400460246	1950		ServiceSmart	Mounting Bars 18" Set of (2) (Order in Multiples of 12)	N						36	IPS	Downlighting - Statement Downlighting		Calculte Accessories	Accessories
784197145033	912400460247	1951		ServiceSmart	Mounting Bars 27" Set of (2) (Order in Multiples of 12)	N						36	IPS	Downlighting - Statement Downlighting		Calculte Accessories	Accessories
784197289041	912400460455	7994		SpecSmart	Set of 2 Telescoping Mounting Bars Calculte		100					36	IPS	Downlighting - Statement Downlighting		Calculte Accessories	Accessories
784197116064	912400461237	AL4HC		ServiceSmart	Hex Louver for Adjustable 6" and 7" Housing, Hex Cell	N						36	IPS	Downlighting - Statement Downlighting		Calculte Accessories	Accessories
784197228177	912400463053	CATCA2		SpecSmart	4" Evolution Thick Ceiling Adapter Ring		100					36	IPS	Downlighting - Statement Downlighting		Calculte Accessories	Accessories
784197493448	912400463073	CA3FMR		SpecSmart	Plaster Ring Accessory for 3" Evolution		100					36	IPS	Downlighting - Statement Downlighting		Calculte Accessories	Accessories
662057009223	912400463074	CA4FMR		SpecSmart	Plaster Ring Accessory for 4" LED Downlight		100					36	IPS	Downlighting - Statement Downlighting		Calculte Accessories	Accessories
862057503035	912400471415	CLAEM1520		SpecSmart	Calculte LED Field Wire EM-Pack 1500/2000 Lumen		100					36	IPS	Downlighting - Statement Downlighting		Calculte Accessories	Accessories