

Indoor/Outdoor Luminaire Smart Service Guide File "Trimmed" - Rev: February 1, 2017

Additional Sorting / Filtering Fields

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
784197061593	912401272954	ZFVG30L840-2-D-UNV-DM		ServiceSmart	2x2, 3000lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver	C.N.L.		X		X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197028770	912401272141	ZFVG3BL835-2-D-UNV-DM		ServiceSmart	2x2, 3800lm, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver	C.N.L.				X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197028732	912401272133	ZFVG3BL835-2-D-UNV-DM-EMLED		ServiceSmart	2x2, 3800lm, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver, Emergency	C.N.L.				X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197028947	912401273072	ZFVG3BL835-4-D-UNV-DM		SpecSmart	2x4, 3800lm, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver		50			X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197028848	912401273082	ZFVG3BL835-4-D-UNV-DM-EMLED		SpecSmart	2x4, 3800lm, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver, Emergency		50			X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049133	912401272139	ZFVG3BL840-2-D-UNV-DM		ServiceSmart	2x2, 3800lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver	C.N.L.		X		X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049188	912401272131	ZFVG3BL840-2-D-UNV-DM-EMLED		ServiceSmart	2x2, 3800lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver, Emergency	C.N.L.				X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049287	912401273077	ZFVG3BL840-4-D-UNV-DM		SpecSmart	2x4, 3800lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver		50			X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049348	912401273087	ZFVG3BL840-4-D-UNV-DM-EMLED		SpecSmart	2x4, 3800lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver, Emergency		50			X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049201	912401273068	ZFVG3BLH835-4-D-UNV-DM		SpecSmart	2x4, 3800lm Hi-Efficacy, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver		50			X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049294	912401273078	ZFVG3BLH835-4-D-UNV-DM-EMLED		SpecSmart	2x4, 3800lm Hi-Efficacy, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver, Emergency		50			X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049249	912401273073	ZFVG3BLH840-4-D-UNV-DM		SpecSmart	2x4, 3800lm Hi-Efficacy, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver		50			X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049300	912401273083	ZFVG3BLH840-4-D-UNV-DM-EMLED		SpecSmart	2x4, 3800lm Hi-Efficacy, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver, Emergency		50			X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197061302	912401272623	ZFVG3BL840-4-D-UNV-DM		ServiceSmart	2x4, 4300lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver	C.N.L.		X		X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197028787	912401272136	ZFVG4SL835-2-D-UNV-DM		ServiceSmart	2x2, 4500lm, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver	C.N.L.				X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197028749	912401272143	ZFVG4SL835-2-D-UNV-DM-EMLED		ServiceSmart	2x2, 4500lm, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver, Emergency	C.N.L.				X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049140	912401272140	ZFVG4SL840-2-D-UNV-DM		ServiceSmart	2x2, 4500lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver	C				X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197028961	912401272125	ZFVG4BL835-4-D-UNV-DM		ServiceSmart	2x4, 4800lm, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver	C.N.L.				X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197028862	912401272130	ZFVG4BL835-4-D-UNV-DM-EMLED		ServiceSmart	2x4, 4800lm, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver, Emergency	C.N.L.				X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049102	912401272128	ZFVG4BL840-4-D-UNV-DM		ServiceSmart	2x4, 4800lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver	C				X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049355	912401272136	ZFVG4BL840-4-D-UNV-DM-EMLED		ServiceSmart	2x4, 4800lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver, Emergency	C.N.L.				X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049256	912401273074	ZFVG4BLH840-4-D-UNV-DM		SpecSmart	2x4, 4800lm Hi-Efficacy, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver		50			X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197028978	912401272126	ZFVG5AL835-4-D-UNV-DM		ServiceSmart	2x4, 5400lm, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver	C.N.L.				X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049119	912401272129	ZFVG5AL840-4-D-UNV-DM		ServiceSmart	2x4, 5400lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver	C.N.L.		X		X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049362	912401272135	ZFVG5AL840-4-D-UNV-DM-EMLED		ServiceSmart	2x4, 5400lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver, Emergency	C.N.L.				X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049263	912401273075	ZFVG5ALH840-4-D-UNV-DM		SpecSmart	2x4, 5400lm Hi-Efficacy, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver		50			X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049324	912401273085	ZFVG5ALH840-4-D-UNV-DM-EMLED		SpecSmart	2x4, 5400lm Hi-Efficacy, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver, Emergency		50			X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197028985	912401272127	ZFVG7AL835-4-D-UNV-DM		ServiceSmart	2x4, 7400lm, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver	C.N.L.				X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049126	912401272142	ZFVG7AL840-4-D-UNV-DM		ServiceSmart	2x4, 7400lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver	C.N.L.				X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049379	912401272134	ZFVG7AL840-4-D-UNV-DM-EMLED		ServiceSmart	2x4, 7400lm, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver, Emergency	C.N.L.				X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049322	912401273073	ZFVG7ALH835-4-D-UNV-DM		SpecSmart	2x4, 7400lm Hi-Efficacy, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver		50			X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197049270	912401273076	ZFVG7ALH840-4-D-UNV-DM		SpecSmart	2x4, 7400lm Hi-Efficacy, 4000K, Opal Lens, Universal Electronic 0-10V Dimming Driver		50			X		38	IGA	Recessed	Softlights (Direct/Indirect)	EvoGrid LED	
784197028763	912401273519	ZFVG30L835-2-D-UNV-DM		ServiceSmart	2x2, 3000lm, 3500K, Opal Lens, Universal Electronic 0-10V Dimming Driver	N						New	IGA	Recessed	Softlights (Direct LED)	EvoGrid LED	
784197242336	912401282070	ZFVG3BL835-2-D-UNV-DM	New Addition - New Product	ServiceSmart	2x2, 3800lm, 3500K, 0-10v, UNV	C.N.L.						New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	
784197242329	912401282071	ZFVG4SL835-2-D-UNV-DM	New Addition - New Product	ServiceSmart	2x2, 4500lm, 3500K, 0-10v, UNV	C.N.L.						New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	
784197242312	912401282072	ZFVG4SL835-4-D-UNV-DM	New Addition - New Product	ServiceSmart	2x4, 4300lm, 3500K, 0-10v, UNV	C.N.L.				X		New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	
784197242305	912401282073	ZFVG4BL835-4-D-UNV-DM	New Addition - New Product	ServiceSmart	2x4, 4800lm, 3500K, 0-10v, UNV	C.N.L.				X		New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	
784197242299	912401282074	ZFVG5AL835-4-D-UNV-DM	New Addition - New Product	ServiceSmart	2x4, 5400lm, 3500K, 0-10v, UNV	C.N.L.				X		New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	
784197242275	912401282076	ZFVG3BL840-2-D-UNV-DM	New Addition - New Product	ServiceSmart	2x2, 3800lm, 4000K, 0-10v, UNV	C.N.L.				X		New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	
784197242251	912401282078	ZFVG4SL840-2-D-UNV-DM	New Addition - New Product	ServiceSmart	2x2, 4500lm, 4000K, 0-10v, UNV	C.N.L.				X		New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	
784197242444	912401282079	ZFVG4SL840-4-D-UNV-DM	New Addition - New Product	ServiceSmart	2x4, 4300lm, 4000K, 0-10v, UNV	C.N.L.				X		New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	
784197242220	912401282081	ZFVG4BL840-4-D-UNV-DM	New Addition - New Product	ServiceSmart	2x4, 4800lm, 4000K, 0-10v, UNV	C.N.L.				X		New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	
784197242213	912401282082	ZFVG5AL840-4-D-UNV-DM	New Addition - New Product	ServiceSmart	2x4, 5400lm, 4000K, 0-10v, UNV	C.N.L.				X		New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	
784197203634	912401281459	ZFVG418835-4-D-UNV-DM	New Addition - New Product	ServiceSmart	Base - 1x4, 4100lm, 3500K, 0-10v, UNV	C.N.L.		X				New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	
784197203641	912401281466	ZFVG388835-2-D-UNV-DM	New Addition - New Product	ServiceSmart	Base - 2x2, 3800lm, 3500K, 0-10v, UNV	C.N.L.		X		X		New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	
784197203658	912401281469	ZFVG428835-4-D-UNV-DM	New Addition - New Product	ServiceSmart	Base - 2x4, 4200lm, 3500K, 0-10v, UNV	C.N.L.		X		X		New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	
784197242282	912401282075	ZFVG418840-4-D-UNV-DM	New Addition - New Product	ServiceSmart	Base - 1x4, 4100lm, 4000K, 0-10v, UNV	C.N.L.		X		X		New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	
784197242268	912401282077	ZFVG388840-2-D-UNV-DM	New Addition - New Product	ServiceSmart	Base - 2x2, 3800lm, 4000K, 0-10v, UNV	C.N.L.		X		X		New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	
784197242237	912401282080	ZFVG428840-4-D-UNV-DM	New Addition - New Product	ServiceSmart	Base - 2x4, 4200lm, 4000K, 0-10v, UNV	C.N.L.		X		X		New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	
784197242176	912401282086	ZFVG3BL835-4-D-UNV-DM	New Addition - New Product	SpecSmart	1x4, 3800lm, 3500K, 0-10v, UNV	C.N.L.				X		New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	
784197242169	912401282087	ZFVG4SL835-4-D-UNV-DM	New Addition - New Product	SpecSmart	1x4, 4500lm, 3500K, 0-10v, UNV	C.N.L.				X		New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	
784197242152	912401282088	ZFVG7AL835-4-D-UNV-DM	New Addition - New Product	SpecSmart	1x4, 7400lm, 3500K, 0-10v, UNV	C.N.L.						New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	
784197242145	912401282089	ZFVG3BL840-4-D-UNV-DM	New Addition - New Product	SpecSmart	1x4, 3800lm, 4000K, 0-10v, UNV	C.N.L.				X		New	IGA	Recessed	Softlights (Direct LED)	FluoGrid Recessed LED	

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSGG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
784197242138	912401282090	1FGG451840-4-D-UNV-DIM	New Addition - New Product	SpecSmart	1x4, 4500lm, 4000K, 0-10v, UNV	C.N.L				X		New	IGA	Recessed	Soflights (Direct LED)	FluxGrid Recessed LED	
784197242121	912401282091	2FGG74L840-4-D-UNV-DIM	New Addition - New Product	SpecSmart	2x4, 7400lm, 4000K, 0-10v, UNV	C.N.L				X		New	IGA	Recessed	Soflights (Direct LED)	FluxGrid Recessed LED	
784197242206	912401282083	1FGG418830-4-D-UNV-DIM	New Addition - New Product	SpecSmart	Base - 1x4, 4100lm, 3000K, 0-10v, UNV	C.N.L				X		New	IGA	Recessed	Soflights (Direct LED)	FluxGrid Recessed LED	
784197242190	912401282084	2FGG388830-2-D-UNV-DIM	New Addition - New Product	SpecSmart	Base - 2x2, 3800lm, 3000K, 0-10v, UNV	C.N.L				X		New	IGA	Recessed	Soflights (Direct LED)	FluxGrid Recessed LED	
784197242183	912401282085	2FGG428830-4-D-UNV-DIM	New Addition - New Product	SpecSmart	Base - 2x4, 4200lm, 3000K, 0-10v, UNV	C.N.L				X		New	IGA	Recessed	Soflights (Direct LED)	FluxGrid Recessed LED	
784197242114	912401282092	1FGG418850-4-D-UNV-DIM	New Addition - New Product	SpecSmart	Base - 1x4, 4100lm, 5000K, 0-10v, UNV	C.N.L				X		New	IGA	Recessed	Soflights (Direct LED)	FluxGrid Recessed LED	
784197242107	912401282093	2FGG388850-2-D-UNV-DIM	New Addition - New Product	SpecSmart	Base - 2x2, 3800lm, 5000K, 0-10v, UNV	C.N.L				X		New	IGA	Recessed	Soflights (Direct LED)	FluxGrid Recessed LED	
784197242091	912401282094	2FGG428850-4-D-UNV-DIM	New Addition - New Product	SpecSmart	Base - 2x4, 4200lm, 5000K, 0-10v, UNV	C.N.L				X		New	IGA	Recessed	Soflights (Direct LED)	FluxGrid Recessed LED	
781370169817	912400393540	1DLG27L835-4-D-UNV-DIM		SpecSmart	1x4, 2700lm, 3500K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
781370181307	912401044236	2DLG27L840-2-D-UNV-DIM		SpecSmart	2x2, 2700lm, 4000K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
782343815472	912400393284	2DLG34L835-2-D-UNV-DIM	Demoted to B	SpecSmart	2x2, 3400lm, 3500K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
782343751732	912400355077	2DLG34L840-2-D-UNV-DIM		SpecSmart	2x2, 3400lm, 4000K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
782343882276	912400364135	2DLG38L835-2-D-UNV-DIM		SpecSmart	2x2, 3800lm, 3500K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
781370596163	912401263982	2DLG38L835-2-D-UNV-DIM-SW2C2	Demoted to B	SpecSmart	2x2, 3800lm, 3500K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver, SpaceWise		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
782343781098	912400393515	2DLG38L840-2-D-UNV-DIM		SpecSmart	2x2, 3800lm, 4000K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
781370596774	912401263978	2DLG38L840-2-D-UNV-DIM-SW2C2	Demoted to B	SpecSmart	2x2, 3800lm, 4000K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver, SpaceWise		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
782343815458	912400393283	2DLG43L835-4-D-UNV-DIM		SpecSmart	2x4, 4300lm, 3500K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
781370596194	912401263981	2DLG43L835-4-D-UNV-DIM-SW2C2	Demoted to B	SpecSmart	2x4, 4300lm, 3500K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver, SpaceWise		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
782343814730	912400393224	2DLG43L840-4-D-UNV-DIM		SpecSmart	2x4, 4300lm, 4000K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
781370596323	912401263964	2DLG43L840-4-D-UNV-DIM-SW2C2	Demoted to B	SpecSmart	2x4, 4300lm, 4000K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver, SpaceWise		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
782343873267	912400393564	2DLG44L835-2-D-UNV-DIM		SpecSmart	2x2, 4400lm, 3500K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
782343743591	912400393498	2DLG44L840-2-D-UNV-DIM		SpecSmart	2x2, 4400lm, 4000K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
782343841167	912400361222	2DLG49L835-4-D-UNV-DIM	Demoted to B	SpecSmart	2x4, 4900lm, 3500K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
782343786635	912400393278	2DLG49L840-4-D-UNV-DIM		SpecSmart	2x4, 4900lm, 4000K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
782343947043	912400367873	2DLG58L835-4-D-UNV-DIM		SpecSmart	2x4, 5800lm, 3500K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
782343496763	912400389882	2DLG58L840-4-D-UNV-DIM		SpecSmart	2x4, 5800lm, 4000K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
782343820230	912400359615	2DLG73L835-4-D-UNV-DIM		SpecSmart	2x4, 7300lm, 3500K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
782343786628	912400357277	2DLG73L840-4-D-UNV-DIM		SpecSmart	2x4, 7300lm, 4000K, Opal Diffuser, Universal Electronic 0-10V Dimming Driver		50			X		39	IGA	Recessed	Soflights (Direct/Indirect)	DualLED Recessed	
784197028305	912401270365	1CAG30L835-4-CS-UNV-DIM		SpecSmart	1x4, 3000lm, 3500K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197028299	912401270362	1CAG30L840-4-CS-UNV-DIM		SpecSmart	1x4, 3000lm, 4000K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197028350	912401270368	2CAG30L835-2-CS-UNV-DIM		SpecSmart	2x2, 3000lm, 3500K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197069650	912400399676	2CAG30L835-2-CS-UNV-DIM-CHIC		SpecSmart	2x2, 3000lm, 3500K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver, Chicago Plenum		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197024789	912401270147	2CAG30L835-2-CS-UNV-DIM-EMLED		SpecSmart	2x2, 3000lm, 3500K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver, Emergency		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197028343	912401270367	2CAG30L840-2-CS-UNV-DIM		SpecSmart	2x2, 3000lm, 4000K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197062033	912401271624	2CAG30L840-2-CS-UNV-DIM-EMLED		SpecSmart	2x2, 3000lm, 4000K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver, Emergency		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197028374	912401270370	2CAG34L835-2-CS-UNV-DIM		SpecSmart	2x2, 3400lm, 3500K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197059842	912400399704	2CAG34L835-2-CS-UNV-DIM-CHIC		SpecSmart	2x2, 3400lm, 3500K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver, Chicago Plenum		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197028367	912401270369	2CAG34L840-2-CS-UNV-DIM		SpecSmart	2x2, 3400lm, 4000K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197059882	912400399708	2CAG36L835-4-CS-UNV-DIM-CHIC		SpecSmart	2x4, 3600lm, 3500K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver, Chicago Plenum		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197028398	912401270372	2CAG38L835-2-CS-UNV-DIM		SpecSmart	2x2, 3800lm, 3500K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver, Emergency, Chicago Plenum		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197062040	912401271626	2CAG38L835-2-CS-UNV-DIM-EMLED		SpecSmart	2x2, 3800lm, 3500K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver, Emergency		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197028381	912401270373	2CAG38L840-2-CS-UNV-DIM		SpecSmart	2x2, 3800lm, 4000K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197042196	912401271316	2CAG38L840-2-CS-UNV-DIM-EMLED		SpecSmart	2x2, 3800lm, 4000K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver, Emergency		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197028435	912401270376	2CAG42L835-4-CS-UNV-DIM		SpecSmart	2x4, 4200lm, 3500K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197028449	912401270441	2CAG42L835-4-CS-UNV-DIM-EMLED		SpecSmart	2x4, 4200lm, 3500K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver, Emergency		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197028428	912401270375	2CAG42L840-4-CS-UNV-DIM		SpecSmart	2x4, 4200lm, 4000K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
78137058526	912401270293	2CAG42L840-4-CS-UNV-DIM-EMLED		SpecSmart	2x4, 4200lm, 4000K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver, Emergency		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197028459	912401270378	2CAG55L835-4-CS-UNV-DIM		SpecSmart	2x4, 5500lm, 3500K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197059767	912400399720	2CAG55L835-4-CS-UNV-DIM-CHIC		SpecSmart	2x4, 5500lm, 3500K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver, Chicago Plenum		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197024765	912401270145	2CAG55L835-4-CS-UNV-DIM-EMLED		SpecSmart	2x4, 5500lm, 3500K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver, Emergency		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197028442	912401270377	2CAG55L840-4-CS-UNV-DIM		SpecSmart	2x4, 5500lm, 4000K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
784197026808	912401270294	2CAG55L840-4-CS-UNV-DIM-EMLED		SpecSmart	2x4, 5500lm, 4000K, Diffuse Lens, Universal Electronic 0-10V Dimming Driver, Emergency		50			X		40	IGA	Recessed	Soflights (Direct/Indirect)	ClearAppeal LED	
781370669096	912401263845	HL32GLR33L35UXZT		ServiceSmart	2x2, 3300lm, 3500K, Acrylic Linear Prismatic Lens, 0-10V Dimming	N.L				X		41	IGA	Recessed	Soflights (Direct/Indirect)	HP90 LED Recessed	
781370113674	912400398847	HL32GLR41L35UXZT		ServiceSmart	2x4, 4100lm, 3500K, Acrylic Linear Prismatic Lens, 0-10V Dimming	N.L				X		41	IGA	Recessed	Soflights (Direct/Indirect)	HP90 LED Recessed	

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
781370281830	912401267024	HL522GLR3L35UXZT-EMLED		SpecSmart	2x2, 3300lm, 3500K, Acrylic Linear Prismatic Lens, with Emergency Module		50					41	IGA	Recessed	Softlights (Direct/Indirect)	HP90 LED Recessed	
78137025508	912401267464	HL524GLR4L135UXZT-EMLED		SpecSmart	2x4, 4300lm, 3500K, Acrylic Linear Prismatic Lens, with Emergency Module		50					41	IGA	Recessed	Softlights (Direct/Indirect)	HP90 LED Recessed	
734340958003	912400317177	ZAVG217-PMW-UNV-1/2-EB		SpecSmart	2x2, 2 Lamp, 17W TB, Perf Diffuser w/ White Overlay, Universal Electronic Ballast		50					42	IGA	Recessed	Softlights (Direct/Indirect)	Arisoa Recessed	
782343294994	912400348978	ZAVG232-PMW-UNV-1/2-EB10		SpecSmart	2x4, 2 Lamp, 32W TB, Perf Diffuser w/ White Overlay, Universal Electronic Ballast		50					42	IGA	Recessed	Softlights (Direct/Indirect)	Arisoa Recessed	
78137003709	912400309429	ZAVG317-PMW-UNV-1/3-EB		SpecSmart	2x2, 3 Lamp, 17W TB, Perf Diffuser w/ White Overlay, Universal Electronic Ballast		50					42	IGA	Recessed	Softlights (Direct/Indirect)	Arisoa Recessed	
734340840599	912400346653	ZAVG332-PMW-UNV-1/3-EB	Demoted to B	SpecSmart	2x4, 3 Lamp, 32W TB, Perf Diffuser w/ White Overlay, Universal Electronic Ballast		50					42	IGA	Recessed	Softlights (Direct/Indirect)	Arisoa Recessed	
782343932681	912401025247	CH2GPF228UNV-1/2-EB		ServiceSmart	2x4, 2 Lamp, 28W T5, Perf Diffuser w/ White Overlay, Air Return Option, Universal Electronic Ballast	C						42	IGA	Recessed	Softlights (Direct/Indirect)	Coffaire Recessed	
782343917688	912401025237	CH2GPF222UNV-1/2-EB		ServiceSmart	2x4, 2 Lamp, 32W TB, Perf Diffuser w/ White Overlay, Air Return Option, Universal Electronic Ballast	C						42	IGA	Recessed	Softlights (Direct/Indirect)	Coffaire Recessed	
782343917657	912401025235	CH2GPF332UNV-1/3-EB		ServiceSmart	2x4, 3 Lamp, 32W TB, Perf Diffuser w/ White Overlay, Air Return Option, Universal Electronic Ballast	L						42	IGA	Recessed	Softlights (Direct/Indirect)	Coffaire Recessed	
782343969809	912400384727	CS2GPF217UNV-1/2-EB		ServiceSmart	2x2, 2 Lamp, 17W TB, Perf Diffuser w/ White Overlay, Universal Electronic Ballast	N						42	IGA	Recessed	Softlights (Direct/Indirect)	Coffaire Recessed	
782343917831	912401025240	CS2GPF228UNV-1/2-EB		ServiceSmart	2x4, 2 Lamp, 28W T5, Perf Diffuser w/ White Overlay, Universal Electronic Ballast	C						42	IGA	Recessed	Softlights (Direct/Indirect)	Coffaire Recessed	
782343969823	912400384729	CS2GPF232UNV-1/2-EB		ServiceSmart	2x4, 2 Lamp, 32W TB, Perf Diffuser w/ White Overlay, Universal Electronic Ballast	C		X				42	IGA	Recessed	Softlights (Direct/Indirect)	Coffaire Recessed	
782343969847	912400384731	CS2GPF2FUNV-1/2-EB		ServiceSmart	2x2, 2 Lamp, 40W TTS, Perf Diffuser w/ White Overlay, Universal Electronic Ballast	C		X				42	IGA	Recessed	Softlights (Direct/Indirect)	Coffaire Recessed	
782343916919	912400393909	CS2GPF332UNV-1/3-EB		ServiceSmart	2x4, 3 Lamp, 32W TB, Perf Diffuser w/ White Overlay, Universal Electronic Ballast	C,N		X				42	IGA	Recessed	Softlights (Direct/Indirect)	Coffaire Recessed	
782343333396	912400180018	TVG300L85-2-F5-02F-UNV-DIM		ServiceSmart	2x2, 3000lm, 3500K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver	N				X		43	IGA	Recessed	Troffer	TSG LED Recessed	
782343332696	912401080014	TVG300L80-2-F5-02F-UNV-DIM		ServiceSmart	2x2, 3000lm, 4000K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver	N				X		43	IGA	Recessed	Troffer	TSG LED Recessed	
782343331156	912401080007	TVG321L85-4-F5-02F-UNV-DIM		SpecSmart	2x4, 3200lm, 3500K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver	N	50			X		43	IGA	Recessed	Troffer	TSG LED Recessed	
782343332719	912401260245	TVG38L80-2-F5-02F-UNV-DIM		ServiceSmart	2x2, 3800lm, 4000K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver	C,N,L				X		43	IGA	Recessed	Troffer	TSG LED Recessed	
782343332221	912401080010	TVG48L85-4-F5-02F-UNV-DIM		ServiceSmart	2x4, 4800lm, 3500K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver	C,N,L				X		43	IGA	Recessed	Troffer	TSG LED Recessed	
782343330432	912401080004	TVG48L80-4-F5-02F-UNV-DIM		ServiceSmart	2x4, 4800lm, 4000K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver	C,N,L				X		43	IGA	Recessed	Troffer	TSG LED Recessed	
782343332573	912401080011	TVG54L85-4-F5-02F-UNV-DIM		SpecSmart	2x4, 5400lm, 3500K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver	N	50			X		43	IGA	Recessed	Troffer	TSG LED Recessed	
782343330524	912401260999	TVG54L80-4-F5-02F-UNV-DIM		ServiceSmart	2x4, 5400lm, 4000K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver	C,N,L				X		43	IGA	Recessed	Troffer	TSG LED Recessed	
782343333402	912401080019	TVG38L85-2-F5-02F-UNV-DIM		SpecSmart	2x2, 3800lm, 3500K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver	N	50			X		43	IGA	Recessed	Troffer	TSG LED Recessed	
782343332030	912401080009	TVG43L85-4-F5-02F-UNV-DIM		SpecSmart	2x4, 4300lm, 3500K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver	N	50			X		43	IGA	Recessed	Troffer	TSG LED Recessed	
19096019694	912401080001	TVG32L80-4-F5-02F-UNV-DIM		ServiceSmart	2x4, 3200lm, 4000K, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Driver	C, N, L				X		43	IGA	Recessed	Troffer	TSG LED Recessed	
781370953631	912401275853	1T68232-01-UNV-1/2-EB		ServiceSmart	1x4, 2 Lamp, 32W TB, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	N						New	IGA	Recessed	Troffer	TSG Recessed	
781370989132	912400373181	TVG82176-01-UNV-1/2-EB		SpecSmart	2x2, 2 Lamp, 17W TB, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast		50					43	IGA	Recessed	Troffer	TSG Recessed	
781370943776	912400392909	TVG823168-01-UNV-1/2-EB		ServiceSmart	2x2, 2 Lamp, 31W UB TB, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	C,N,L						43	IGA	Recessed	Troffer	TSG Recessed	
734340981889	912400347273	TVG8232-01-UNV-1/2-EB		ServiceSmart	2x4, 2 Lamp, 32W TB, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	C,N,L				X		43	IGA	Recessed	Troffer	TSG Recessed	
734340992626	912400347245	TVG8332-01-UNV-1/21-EB		ServiceSmart	2x4, 3 Lamp, 32W TB, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	C				X		43	IGA	Recessed	Troffer	TSG Recessed	
734340976033	912400347246	TVG8332-01-UNV-1/3-EB		ServiceSmart	2x4, 3 Lamp, 32W TB, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	C,N,L				X		43	IGA	Recessed	Troffer	TSG Recessed	
734340976095	912400347248	TVG8432-01-UNV-1/4-EB		ServiceSmart	2x4, 4 Lamp, 32W TB, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	C,N				X		43	IGA	Recessed	Troffer	TSG Recessed	
734340976018	912400347250	TVG8432-01-UNV-1/4-EB-F1-LPT741		ServiceSmart	2x4, 4 Lamp, 32W TB, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast	N				X		43	IGA	Recessed	Troffer	TSG Recessed	
734340981919	912400347276	TVG8432-01-UNV-1/4-EB-LPT741		ServiceSmart	2x4, 4 Lamp, 32W TB, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast, w/ 741 Lamps	L				X		43	IGA	Recessed	Troffer	TSG Recessed	
782343040713	912400347563	T68F501D		ServiceSmart	2x4 Pattern 12 Prismatic Acrylic Lens Replacement Door Frame Assembly	N						43	IGA	Recessed	Troffer	TSG Recessed	
782343297872	912401025108	T68F501DL-5PK		ServiceSmart	2x4 Pattern 12 Prismatic Acrylic Lens Replacement, 5 Pack	N						43	IGA	Recessed	Troffer	TSG Recessed	
734340030617	912400342330	23MR221UB-F501-UNV-1/2-EB		SpecSmart	2x2, 2 Lamp, 31W UB TB, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast		50					44	IGA	Recessed	Troffer	Surface Modular	
734340030631	912400342332	23MR332-F501-UNV-1/3-EB		SpecSmart	2x4, 3 Lamp, 32W TB, Flat Steel Door Frame, Pattern 12 Prismatic Acrylic Lens, Universal Electronic Ballast		50					44	IGA	Recessed	Troffer	Surface Modular	
734340941807	912400347101	21P3G323168-33AL-UNV-1/2-EB-ASC		ServiceSmart	2x2, 2 Lamp, 31W UB TB, 9 Cell Semi-Specular Louver, Universal Electronic Ballast, Removable Air Slot Covers	C			X			45	IGA	Recessed	Parabolic	LP3 Parabolic Recessed	
734340608151	912400345006	21P3G332-36AL-UNV-1/3-EB-ASC		ServiceSmart	2x4, 3 Lamp, 32W TB, 18 Cell Semi-Specular Louver, Universal Electronic Ballast, Removable Air Slot Covers	C,N			X			45	IGA	Recessed	Parabolic	LP3 Parabolic Recessed	
734340079876	912400342634	21P3G323168-33AL-UNV-1/2-EB		ServiceSmart	2x2, 2 Lamp, 31W UB TB, 9 Cell Semi-Specular Louver, Universal Electronic Ballast	C,N			X			45	IGA	Recessed	Parabolic	LP3 Parabolic Recessed	
734340609196	912401020505	21P3G332-36AL-UNV-1/3-EB101		SpecSmart	2x4, 2 Lamp, 32W TB, 18 Cell Semi-Specular Louver, Universal Electronic Ballast		50					45	IGA	Recessed	Parabolic	LP3 Parabolic Recessed	
734340728095	912400346106	21P3G332-36AL-UNV-1/3-EB		ServiceSmart	2x4, 3 Lamp, 32W TB, 18 Cell Semi-Specular Louver, Universal Electronic Ballast	C,N,L			X			45	IGA	Recessed	Parabolic	LP3 Parabolic Recessed	
781370200665	912400369764	21P3G332-36AL-UNV-1/3-EB101-LPT741		SpecSmart	2x4, 3 Lamp, 32W TB, 18 Cell Semi-Specular Louver, Universal Electronic Ballast, w/ 741 Lamps							45	IGA	Recessed	Parabolic	LP3 Parabolic Recessed	
734340458824	912400344643	1P336ALD	Demoted to B	SpecSmart	2x4 18 Cell Semi-Specular Louver Replacement		50					45	IGA	Recessed	Parabolic	LP3 Parabolic Recessed	
734340775488	912400346341	FMA14		ServiceSmart	1x4 Flange Mounting Frame Assembly For Recessed Fixtures	C,N,L						45	IGA	Recessed	Troffer	Recessed Accessories	
734340775471	912400346340	FMA22		ServiceSmart	2x2 Flange Mounting Frame Assembly For Recessed Fixtures	C,N,L						45	IGA	Recessed	Troffer	Recessed Accessories	
734340775464	912400346339	FMA24		ServiceSmart	2x4 Flange Mounting Frame Assembly For Recessed Fixtures	C,N,L						45	IGA	Recessed	Troffer	Recessed Accessories	
782343403648	912400393874	OW1448-CS	Demoted to B	SpecSmart	Replacement Lens For OWV Wraparound		50					47	IGA	Linear	Wraparound	DW Wrap	
782343403662	912400393804	OW1848-CS		ServiceSmart	Replacement Lens For OWV Wraparound	N						47	IGA	Linear	Wraparound	DW Wrap	
734340949810	912401025078	OWN217-UNV-1/2-EB		ServiceSmart	2, 2 Lamp, 17W TB, Narrow Housing, Universal Electronic Ballast	N						47	IGA	Linear	Wraparound	DW Wrap	
734340608281	912400345515	OWN232-UNV-1/2-EB		ServiceSmart	4, 2 Lamp, 32W TB, Narrow Housing, Universal Electronic Ballast	N			X			47	IGA	Linear	Wraparound	DW Wrap	
734340608298	912400345516	OWW432-UNV-1/4-EB		ServiceSmart	4, 4 Lamp, 32W TB, Wide Housing, Universal Electronic Ballast	C,N,L				X		47	IGA	Linear	Wraparound	DW Wrap	
734340608911	912400345518	TOWN232-UNV-1/4-EB		ServiceSmart	8, 2 Lamp Tandem, 32W TB, Narrow Housing, Universal Electronic Ballast	C,N,L						47	IGA	Linear	Wraparound	DW Wrap	

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
781370097219	912401261070	OWL640L835-UNV-GIM		ServiceSmart	4', 4000lm, 3500K, Universal Electronic 0-10v Driver	L		X		X		47	IGA	Linear	Wraparound	OWL LED Wrap	
781370049003	912401261072	OWL640L840-UNV-GIM		ServiceSmart	4', 4000lm, 4000K, Universal Electronic 0-10v Driver	L		X		X		47	IGA	Linear	Wraparound	OWL LED Wrap	
781370049010	912401261075	OWL450L840-UNV-GIM		SpecSmart	4', 5000lm, 4000K, Universal Electronic 0-10v Driver		50			X		47	IGA	Linear	Wraparound	OWL LED Wrap	
781370049027	912401261077	OWL470L840-UNV-GIM		SpecSmart	4', 7000lm, 4000K, Universal Electronic 0-10v Driver		50			X		47	IGA	Linear	Wraparound	OWL LED Wrap	
781370169015	912401261079	OWL850L840-UNV-GIM		SpecSmart	8', 10000lm, 4000K, Universal Electronic 0-10v Driver		50			X		47	IGA	Linear	Wraparound	OWL LED Wrap	
734340054677	912400345771	SL113-120-EB-LP		ServiceSmart	21-1/4", 1 Lamp, 13W T5, 120V Electronic Ballast, w/ Lamp	C.NL						48	IGA	Linear	Undercabinet	CJ/SL Valuline Undercabinet	
734340054745	912400345772	SL18-120-EB-LP		ServiceSmart	12-1/4", 1 Lamp, 8W T5, 120V Electronic Ballast, w/ Lamp	C.NL						48	IGA	Linear	Undercabinet	CJ/SL Valuline Undercabinet	
734340055520	912400345784	SL213-120-EB-LP		ServiceSmart	42-1/2", 2 Lamp, 13W T5, 120V Electronic Ballast, w/ Lamps	C.NL						48	IGA	Linear	Undercabinet	CJ/SL Valuline Undercabinet	
734340054943	912400345777	SL281-120-EB-LP		ServiceSmart	33-1/2", 2 Lamp, 8W T5, 13W T5, 120V Electronic Ballast, w/ Lamps	C.NL						48	IGA	Linear	Undercabinet	CJ/SL Valuline Undercabinet	
734340054752	912400345773	SL28-120-EB-LP		ServiceSmart	24-1/2", 2 Lamp, 8W T5, 120V Electronic Ballast, w/ Lamps	C.NL						48	IGA	Linear	Undercabinet	CJ/SL Valuline Undercabinet	
190096019670	912400514963	LINC31001120WHG		SpecSmart	LINC3100 Wiring Module, 120V, White		50					48	IGA	Linear	Undercabinet	LINC3 100 LED Undercabinet	
190096019687	912400514964	LINC31001277WHG		SpecSmart	LINC3100 Wiring Module, 277V, White		50					48	IGA	Linear	Undercabinet	LINC3 100 LED Undercabinet	
782343978641	912400396115	LF4E2830ULAG		ServiceSmart	4', 4000lm, 3000K, 100% Frost Lens, Universal Electronic Driver, Non-dimming	C.NL		X		X		49	IGA	Linear	Strip	FluxStream EZ LED Strip	
782343978634	912400396118	LF4E2840ULAG		ServiceSmart	4', 4000lm, 4000K, 100% Frost Lens, Universal Electronic Driver, Non-dimming	C.NL		X		X		49	IGA	Linear	Strip	FluxStream EZ LED Strip	
734340078171	912400346346	N117-UNV-1/1-EB		ServiceSmart	Small Cross Section Strip, 2", 1 Lamp, 17W T8, Universal Electronic Ballast	C.NL						49	IGA	Linear	Strip	N Narrow Strip	
7343400776188	912400346347	N125-UNV-1/1-EB		ServiceSmart	Small Cross Section Strip, 3", 1 Lamp, 23W T8, Universal Electronic Ballast	C.NL						49	IGA	Linear	Strip	N Narrow Strip	
734340078195	912400346348	N132-UNV-1/1-EB		ServiceSmart	Small Cross Section Strip, 4", 1 Lamp, 32W T8, Universal Electronic Ballast	C.NL		X				49	IGA	Linear	Strip	N Narrow Strip	
7343400752571	912401025060	TH132-UNV-1/2-EB		ServiceSmart	Small Cross Section Strip, 8", 1 Lamp Tandem, 32W T8, Universal Electronic Ballast	C.NL						49	IGA	Linear	Strip	N Narrow Strip	
782343950036	912401025250	10324		SpecSmart	Belmont 1 1x4 Diffuser		50					50	IGA	Linear	Strip	Belmont Surface Fluorescent	
782343950043	912400393946	10325		SpecSmart	Belmont Cloud 1x4 Diffuser		50					50	IGA	Linear	Strip	Belmont Surface Fluorescent	
782343950050	912400393947	10326		SpecSmart	Belmont B 1x4 Diffuser		50					50	IGA	Linear	Strip	Belmont Surface Fluorescent	
782343950081	912400393948	10327		SpecSmart	Belmont Cloud 2x4 Diffuser		50					50	IGA	Linear	Strip	Belmont Surface Fluorescent	
782343941904	912400393943	BE1W232UNWH	Demoted to B	SpecSmart	Belmont 1x4 Chassis, 2 Lamp, 32W T8, 120-277V, White		50					50	IGA	Linear	Strip	Belmont Surface Fluorescent	
782343941928	912400394015	BE2W432UNWH4	Demoted to B	SpecSmart	Belmont 2x4 Chassis, 4 Lamp, 32W T8, 120-277V, White		50					50	IGA	Linear	Strip	Belmont Surface Fluorescent	
782343941935	912400394091	BESF3X4	Demoted to B	SpecSmart	Belmont 1x4 Spill Frame Diffuser, White		50					50	IGA	Linear	Strip	Belmont Surface Fluorescent	
782343941959	912400393945	BESF2X4	Demoted to B	SpecSmart	Belmont 2x4 Spill Frame Diffuser, White		50					50	IGA	Linear	Strip	Belmont Surface Fluorescent	
782343298060	912400349018	CEH-600-C		ServiceSmart	42" Top Swivel Canopy bottom swivel to meet California standards	L						50	IGA	Linear	Strip	Strip & Industrial Accessories	
782343298059	912400348992	CG-4		ServiceSmart	Wire Guard, Use w/ 4" T Strip, TH Strip	L						50	IGA	Linear	Strip	Strip & Industrial Accessories	
782343296103	912400348995	CG-4		ServiceSmart	Wire Guard, Use w/ 4" N Strip	C.NL						50	IGA	Linear	Strip	Strip & Industrial Accessories	
782343300244	912400349033	CS-24		ServiceSmart	Straight Stem, 3/8" Trade Size, 24" Length	C.NL						50	IGA	Linear	Strip	Strip & Industrial Accessories	
782343297803	912400349015	CS-400		ServiceSmart	Rigid Canopy, Use w/ 3/8" Straight Stem	C						50	IGA	Linear	Strip	Strip & Industrial Accessories	
782343300480	912400349033	CS-48		ServiceSmart	Straight Stem, 3/8" Trade Size, 48" Length	C.NL						50	IGA	Linear	Strip	Strip & Industrial Accessories	
782343297902	912400349016	CS-500		ServiceSmart	42 Deg Top Swivel Canopy, Use w/ 3/8" Straight Stem	C						50	IGA	Linear	Strip	Strip & Industrial Accessories	
782343299708	912400349026	FL-123		ServiceSmart	5' Chain & "S" Hooks, Use w/ Strips or Industrials	C						50	IGA	Linear	Strip	Strip & Industrial Accessories	
782343368785	912400396116	SH4528UNV-1/1-EB		ServiceSmart	T5 Strip, 4", 1 Lamp, 28W T5, Universal Electronic Ballast	N						50	IGA	Linear	Strip	SV Narrow Strip T5	
782343980309	912400395059	SH4528UNV-1/2-EB		ServiceSmart	T5 Strip, 4", 2 Lamp, 28W T5, Universal Electronic Ballast	C						50	IGA	Linear	Strip	SV Narrow Strip T5	
734340026272	912400346616	T132-UNV-1/1-EB		ServiceSmart	Standard Strip, 4", 1 Lamp, 32W T8, Universal Electronic Ballast	N						50	IGA	Linear	Strip	T Standard Strip	
734340078201	912400346349	T217-UNV-1/2-EB		ServiceSmart	Standard Strip, 2", 2 Lamp, 17W T8, Universal Electronic Ballast	N						50	IGA	Linear	Strip	T Standard Strip	
734340068128	912400345519	T232-UNV-1/2-EB		ServiceSmart	Standard Strip, 4", 2 Lamp, 32W T8, Universal Electronic Ballast	C.NL		X				50	IGA	Linear	Strip	T Standard Strip	
734340068688	912401025056	T259-UNV-1/2-EB		ServiceSmart	Standard Strip, 8", 2 Lamp, 59W T8, Universal Electronic Ballast	C.NL		X				50	IGA	Linear	Strip	T Standard Strip	
734340068142	912400345521	T7232-UNV-1/4-EB		ServiceSmart	Standard Strip, 8", 2 Lamp Tandem, 32W T8, Universal Electronic Ballast	C.NL		X				50	IGA	Linear	Strip	T Standard Strip	
782343957462	912400398341	16178E		ServiceSmart	Bottom Glass Enclosure, Use w/ A16 and A17 Aluminium High Bay Reflectors	L						52	IGA	Industrial	Industrial	HBO/HBE High Bay	
734340172102	912400343121	JAR6		ServiceSmart	Bottom Glass Enclosure, Use w/ A24 Aluminium High Bay Reflector	C						52	IGA	Industrial	Industrial	HBO/HBE High Bay	
782343174609	912400348161	A16		ServiceSmart	16" Aluminium High Bay Reflector, Use w/ HBO High Bay, 450W Max	C						52	IGA	Industrial	Industrial	HBO/HBE High Bay	
782343174647	912400348165	A24		ServiceSmart	24" Aluminium High Bay Reflector, Use w/ HBO High Bay	C						52	IGA	Industrial	Industrial	HBO/HBE High Bay	
782343356012	912400349370	AR22		ServiceSmart	22" Acrylic High Bay Reflector, Use w/ HBO High Bay, 450W Max	C						52	IGA	Industrial	Industrial	HBO/HBE High Bay	
734340130984	912400349448	HBO100MMT-OR		SpecSmart	Die Cast High Bay Housing, 1000W MH, Multi-Tap Ballast		50					52	IGA	Industrial	Industrial	HBO/HBE High Bay	
734340394634	912400344291	HBO230PMT-PSC-OR		SpecSmart	Die Cast High Bay Housing, 250W Pulse Start MH, Multi-Tap Ballast		50					52	IGA	Industrial	Industrial	HBO/HBE High Bay	
734340394122	912400344287	HBO120PMT-PSC-OR		SpecSmart	Die Cast High Bay Housing, 820W Pulse Start MH, Multi-Tap Ballast		50					52	IGA	Industrial	Industrial	HBO/HBE High Bay	
734340703603	912400345992	HBO400PMT-PSC-OR		ServiceSmart	Die Cast High Bay Housing, 400W Pulse Start MH, Multi-Tap Ballast	C		X				52	IGA	Industrial	Industrial	HBO/HBE High Bay	
734340157468	912400349061	HMR	Demoted to B	SpecSmart	Male Hook 3/4" NPT For HD High Bay/Low Bay		50					52	IGA	Industrial	Industrial	High Bay/Low Bay Accessories	
782343601105	912400351760	HP12-3		SpecSmart	Male Hook 3/4" NPT, 3' Usable Cord, Twist Lock Plug 120V AC 15 Amp, Nema LS 15P		50					52	IGA	Industrial	Industrial	High Bay/Low Bay Accessories	
782343601204	912400351763	HP27-3		SpecSmart	Male Hook 3/4" NPT, 3' Usable Cord, Twist Lock Plug 277V AC 15 Amp, Nema L7 15P		50					52	IGA	Industrial	Industrial	High Bay/Low Bay Accessories	
734340586084	912400393731	MD360		ServiceSmart	Motion Detector, 120/277V, Use w/ FBX, FBD High Bays	C.NL						52	IGA	Industrial	Industrial	High Bay/Low Bay Accessories	

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
782343184752	912400348230	BRA/CRA		ServiceSmart	Specification Grade 28" Low Bay Optical Assembly, Use w/ LBN Low Bay	C,N,L						52	IGA	Industrial	Industrial	LBD/LBN Low Bay	
782343589526	912401025134	LBN400PMT-PSC-OR		ServiceSmart	Specification Grade Low Bay Housing, 400W Pulse Start MH, Multi-Tap Ballast	C						52	IGA	Industrial	Industrial	LBD/LBN Low Bay	
782343241295	912400348993	1F232-PP-UNV-1/2-EB		ServiceSmart	10% Uplight, 4', 2 Lamp, 32W T8, Painted Reflector, Universal Electronic Ballast	C						53	IGA	Industrial	Industrial Linear	IF Specification Industrial	
782343296202	912400348997	FL-173		ServiceSmart	Wire Guard, Use w/ 1F Industrial, 2F Industrial, 1FD Industrial	C						53	IGA	Industrial	Industrial Linear	IF Specification Industrial	
782343295128	912400348948	1FD232-PP-UNV-1/2-EB		SpecSmart	10% Uplight, 4', 2 Lamp, 32W T8, Painted Reflector, Universal Electronic Ballast		50					53	IGA	Industrial	Industrial Linear	1FD General Purpose Industrial	
782343142394	912401261309	FBX CHAIN KIT		ServiceSmart	54" Chain/Hanger Kit, Use with FBX High Bay	C,N,L		X				53	IGA	Industrial	Industrial Linear	FBX LED High Bay	
781370009946	912400389505	FBX16L40-UNV		ServiceSmart	LED High Bay, 16,000 LM, 4000K, Universal Electronic Driver	C,N,L		X		X		53	IGA	Industrial	Industrial Linear	FBX LED High Bay	
782343686874	912400389502	FBX24L40-UNV		ServiceSmart	LED High Bay, 24,000 LM, 4000K, Universal Electronic Driver	C,N,L		X		X		53	IGA	Industrial	Industrial Linear	FBX LED High Bay	
781370375775	912401261677	FBX-GRIP10		ServiceSmart	10' cable hanger kit, use with FBX High Bay	C,N,L		X				53	IGA	Industrial	Industrial Linear	FBX LED High Bay	
781370375768	912401261727	FBX-GRIPS		ServiceSmart	5' Cable/Hanger Kit, Use with FBX High Bay	C,N,L		X				53	IGA	Industrial	Industrial Linear	FBX LED High Bay	
782343142790	912401261311	FBX-PENHGR		ServiceSmart	Pendant Hanger, Use with FBX High Bay	C,N,L						53	IGA	Industrial	Industrial Linear	FBX LED High Bay	
781370299927	912401261322	FBX12L40-UNV		ServiceSmart	12000 lumen FBX High Bay, 4000K, Universal Electronic, 0-10V Dimming Driver	C,N,L		X		X		53	IGA	Industrial	Industrial Linear	FBX LED High Bay	
781370754419	912401264353	FBX16L50-UNV		ServiceSmart	16000 lumen FBX High Bay, 5000K, Universal Electronic, 0-10V Dimming Driver	C,N,L				X		53	IGA	Industrial	Industrial Linear	FBX LED High Bay	
781370644616	912401261725	FBX24L50-UNV		ServiceSmart	24000 lumen FBX High Bay, 5000K, Universal Electronic, 0-10V Dimming Driver	C,N,L				X		53	IGA	Industrial	Industrial Linear	FBX LED High Bay	
782343143872	912401262554	WG-FBX-2W		ServiceSmart	WireGuard FBX 16K, 20K, 24K lumen versions	C,N,L						New	IGA	Industrial	Industrial Linear	FBX LED High Bay	
782343143551	912401262184	WG-FBX-4		ServiceSmart	WireGuard FBX 36K, 45K lumen versions	C,N,L						New	IGA	Industrial	Industrial Linear	FBX LED High Bay	
782343143889	912401262067	WG-FBX-2W		ServiceSmart	WireGuard FBX 8K, 12K lumen versions	C,N,L						New	IGA	Industrial	Industrial Linear	FBX LED High Bay	
781370299668	912401261321	FBX20L40-UNV		ServiceSmart	20000 lumen FBX High Bay, 4000K, Universal Electronic, 0-10V Dimming Driver	C,N,L				X		New	IGA	Industrial	Industrial Linear	FBX LED High Bay	
78197228071	912401280918	FBX-SLCA-2W	New Addition	ServiceSmart	FBX field installed lens	C						New	IGA	Industrial	Industrial Linear	FBX LED High Bay	
78197222493	912401280921	FBX-SLCR-2W	New Addition	ServiceSmart	FBX field installed lens	C						New	IGA	Industrial	Industrial Linear	FBX LED High Bay	
78197228033	912401280915	FBX-SLFA-2W	New Addition	ServiceSmart	FBX field installed lens	C						New	IGA	Industrial	Industrial Linear	FBX LED High Bay	
78197222861	912401280924	FBX-SLFB-2W	New Addition	ServiceSmart	FBX field installed lens	C						New	IGA	Industrial	Industrial Linear	FBX LED High Bay	
782343184103	912400348218	FKR-126		ServiceSmart	Chain Hanger Set, (2) 5' Chains & "Y" Hooks, Use w/ IA Industrial, IS Industrial, T Strips	C						53	IGA	Industrial	Industrial Linear	IA/IS All Purpose Industrial	
782343259009	912400348780	FKR-173		ServiceSmart	Wire Guard, Use w/ IA Industrial, IS Industrial	C,N,L						53	IGA	Industrial	Industrial Linear	IA/IS All Purpose Industrial	
734340608229	912400345009	A232-UNV-1/2-EB		ServiceSmart	Uplight Reflector, 4', 2 Lamp, 32W T8, Universal Electronic Ballast	C,N,L						53	IGA	Industrial	Industrial Linear	IA/IS All Purpose Industrial	
734340608243	912400345511	IS232-UNV-1/2-EB		ServiceSmart	Solid Top Reflector, 4', 2 Lamp, 32W T8, Universal Electronic Ballast	N		X				53	IGA	Industrial	Industrial Linear	IA/IS All Purpose Industrial	
734340608236	912400345510	1IA232-UNV-1/4-EB		ServiceSmart	Uplight Reflector, 8', 2 Lamp Tandem, 32W T8, Universal Electronic Ballast	C,N,L						53	IGA	Industrial	Industrial Linear	IA/IS All Purpose Industrial	
734340608250	912400345512	1IS232-UNV-1/4-EB		ServiceSmart	Solid Top Reflector, 8', 2 Lamp Tandem, 32W T8, Universal Electronic Ballast	N		X				53	IGA	Industrial	Industrial Linear	IA/IS All Purpose Industrial	
734340130249	912400342905	ODL32-120		ServiceSmart	Led Dock Light, 15 Watts, 32" Arm, Toggle Switch, 6' Cord And Plug, 120 V	C						53	IGA	Industrial	Industrial	LED Dock Light	
782343199558	912400348231	FBX454HD-UNV-1/4-EB-2LS		ServiceSmart	4 Lamp, 54W TSHO, Universal Electronic Ballast, Two Level Switching Option	C,N,L		X				54	IGA	Industrial	Industrial Linear	FBX Fluorescent High Bay	
782343829615	912401025191	FBX-4E-1W		ServiceSmart	Door Frame and Clear Lens Assembly, Use w/ 4 Lamp FBD High Bay	C,N,L						54	IGA	Industrial	Industrial Linear	FBX Fluorescent High Bay	
782343393406	912401025118	FBX612-UNV-1/42-EB		ServiceSmart	6 Lamp, 32W T8, Universal Electronic Ballast, Two Level Switching Option	C		X				54	IGA	Industrial	Industrial Linear	FBX Fluorescent High Bay	
782343366097	912400349427	FBX612-UNV-1/42-EBH		ServiceSmart	6 Lamp, 32W T8, Universal Electronic High Ballast Factor Ballast, Two Level Switching Option	C,N,L						54	IGA	Industrial	Industrial Linear	FBX Fluorescent High Bay	
782343264003	912400348812	FBX654HD-UNV-1/42-EB		ServiceSmart	6 Lamp, 54W TSHO, Universal Electronic Ballast, Two Level Switching Option	C,N		X				54	IGA	Industrial	Industrial Linear	FBX Fluorescent High Bay	
782343829653	912401025192	FBX-6E-1W		ServiceSmart	Door Frame and Clear Lens Assembly, Use w/ 6 Lamp FBD High Bay	C,N,L						54	IGA	Industrial	Industrial Linear	FBX Fluorescent High Bay	
781370531225	912400370644	FBF/FBE-CHAIN KIT		ServiceSmart	54" Chain/Hanger Kit, Use w/ FBD High High Bays	C		X				54	IGA	Industrial	Industrial Linear	FBX Fluorescent High Bay	
781370588838	912400385687	FBF/FBE-GRIP10	Promoted to A	ServiceSmart	10' Gripple Hanger Kit, Use w/ FBD High Bays	C						54	IGA	Industrial	Industrial Linear	FBX Fluorescent High Bay	
781370899813	912400372888	FBF/FBE-GRIPS		ServiceSmart	5' Gripple Hanger Kit, Use w/ FBD High Bays	C						54	IGA	Industrial	Industrial Linear	FBX Fluorescent High Bay	
782343829592	912401025189	WG-FBD4		ServiceSmart	Wire Guard, Use w/ 4 Lamp FBD High Bay	C						54	IGA	Industrial	Industrial Linear	FBX Fluorescent High Bay	
782343829608	912401025190	WG-FBD6		ServiceSmart	Wire Guard, Use w/ 6 Lamp FBD	N						54	IGA	Industrial	Industrial Linear	FBX Fluorescent High Bay	
734340608267	912400345513	DWA232-UNV-1/2-EB		ServiceSmart	Wet Location Industrial, High Impact Acrylic Lens, Plastic Latches, 4', 2 Lamp, 32W T8, Universal Electronic Ballast	C,N,L		X				54	IGA	Industrial	Industrial Linear	Vaporume	
734340374599	912400344165	TBK		ServiceSmart	Top Bracket Kit For V2/DW Industrial	C,N,L						54	IGA	Industrial	Industrial Linear	Vaporume	
734340608274	912400345514	DWA232-UNV-1/4-EB		ServiceSmart	Wet Location Industrial, High Impact Acrylic Lens, Plastic Latches, 8', 2 Lamp Tandem, 32W T8, Universal Electronic Ballast	C,N,L						54	IGA	Industrial	Industrial Linear	Vaporume	
734340374667	912400344170	V2/DW-BA8L-CS		ServiceSmart	4" Replacement Acrylic Lens For DWA2 Industrial	C,N						54	IGA	Industrial	Industrial Linear	Vaporume	
734340374704	912400344172	V2/DW-BA8L		ServiceSmart	4" Replacement Acrylic Lens For DWA2 Industrial	C,N,L						54	IGA	Industrial	Industrial Linear	Vaporume	
781370485887	912400370467	WBK		ServiceSmart	Wall Bracket for V2/DW Vaporume	C						54	IGA	Industrial	Industrial Linear	Vaporume	
782343494479	912400381547	DWA232L840-2-UNV		ServiceSmart	Wet Location Industrial, High Impact Acrylic Lens, Plastic Latches, 2', 2700lm, 4000K, Universal Electronic Driver	N		X		X		54	IGA	Industrial Linear	Industrial Linear	Vaporume LED	
782343500699	912400381927	DWA232L840-4-UNV		ServiceSmart	Wet Location Industrial, High Impact Acrylic Lens, Plastic Latches, 4', 5100lm, 4000K, Universal Electronic Driver	N		X		X		54	IGA	Industrial Linear	Industrial Linear	Vaporume LED	
781370455446	912400393988	DWA270L840-4-UNV		ServiceSmart	Wet Location Industrial, High Impact Acrylic Lens, Plastic Latches, 4', 7000lm, 4000K, Universal Electronic Driver	C,N,L				X		54	IGA	Industrial Linear	Industrial Linear	Vaporume LED	
734340234114	912400343438	4AR1LR		ServiceSmart	Surface Mount, AC Only, Single Face, Red Letters, Clear Background, Satin Aluminum Housing	L						56	IGA	Exit/Emergency	Exit Signs	44R Line Edge-Lit	
734340234121	912400343439	4AR1LR		ServiceSmart	Surface Mount, AC Only, Double Face, Red Letters, Mirror Background, Satin Aluminum Housing	L						56	IGA	Exit/Emergency	Exit Signs	44R Line Edge-Lit	
734340234497	912400343451	4AR1L1R		ServiceSmart	Universal Mount, AC Only, Single Face, Red Letters, Clear Background, Satin Aluminum Housing	L		X				56	IGA	Exit/Emergency	Exit Signs	44R Line Edge-Lit	
734340234534	912400343455	4AR1L1WR		ServiceSmart	Universal Mount, AC Only, Single Face, Red Letters, Clear Background, White Housing	L						56	IGA	Exit/Emergency	Exit Signs	44R Line Edge-Lit	
734340234503	912400343456	4AR1L2R		ServiceSmart	Universal Mount, AC Only, Double Face, Red Letters, Mirror Background, Satin Aluminum Housing	L		X				56	IGA	Exit/Emergency	Exit Signs	44R Line Edge-Lit	

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
734340234558	912400343460	44RLU2WR		ServiceSmart	Universal Mount, AC Only, Double Face, Red Letters, Mirror Background, White Housing	L						56	IGA	Exit/Emergency	Exit Signs	44R Line Edge-Lit	
734340453713	912400344611	EH44RLLR		ServiceSmart	Surface Mount, Emergency Operation Nicad Battery, Single Face, Red Letters, Clear Background, Satin Aluminum Housing	L						56	IGA	Exit/Emergency	Exit Signs	44R Line Edge-Lit	
734340234404	912400343449	EH44RLDU2G		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Single Face, Green Letters, Clear Background, Satin Aluminum Housing	L		X				56	IGA	Exit/Emergency	Exit Signs	44R Line Edge-Lit	
734340234367	912400343447	EH44RLDU1R		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Single Face, Red Letters, Clear Background, Satin Aluminum Housing	C,NL		X				56	IGA	Exit/Emergency	Exit Signs	44R Line Edge-Lit	
723243029397	912400347485	EH44RLDU1RM		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Single Face, Red Letters, Mirror Background, Satin Aluminum Housing	C,NL						56	IGA	Exit/Emergency	Exit Signs	44R Line Edge-Lit	
734340234466	912400343451	EH44RLDU2WG		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Single Face, Green Letters, Clear Background, White Housing	L						56	IGA	Exit/Emergency	Exit Signs	44R Line Edge-Lit	
734340234442	912400343451	EH44RLDU1WR		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Single Face, Red Letters, Clear Background, White Housing	L						56	IGA	Exit/Emergency	Exit Signs	44R Line Edge-Lit	
734340234411	912400343450	EH44RLDU2G		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Double Face, Green Letters, Mirror Background, Satin Aluminum Housing	L		X				56	IGA	Exit/Emergency	Exit Signs	44R Line Edge-Lit	
734340234374	912400343448	EH44RLDU2R		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Double Face, Red Letters, Mirror Background, Satin Aluminum Housing	L		X				56	IGA	Exit/Emergency	Exit Signs	44R Line Edge-Lit	
734340234475	912400343454	EH44RLDU2WG		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Double Face, Green Letters, Mirror Background, Satin Aluminum Housing	L						56	IGA	Exit/Emergency	Exit Signs	44R Line Edge-Lit	
734340234459	912400343452	EH44RLDU2WR		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Double Face, Red Letters, Mirror Background, White Housing	L						56	IGA	Exit/Emergency	Exit Signs	44R Line Edge-Lit	
781370514928	912401025366	BB45VL		ServiceSmart	Back Box Rough In Section, AC Only	L						56	IGA	Exit/Emergency	Exit Signs	45V Line Edge-Lit	
781370518127	912400319061	BB8R45VXL		ServiceSmart	Back Box Rough In Section, Emergency Operation Nicad Battery	C,NL						56	IGA	Exit/Emergency	Exit Signs	45V Line Edge-Lit	
782343842546	912401025209	SSL3G		ServiceSmart	Universal Mount, AC Only, Single/Double Face, Green Letters, Black Housing w/ Satin Aluminum Housing	L						57	IGA	Exit/Emergency	Exit Signs	55 Line Die Cast Contemporary	
781370104085	912401025273	SSL3R		ServiceSmart	Universal Mount, AC Only, Single/Double Face, Red Letters, Black Housing w/ Satin Aluminum Housing	L		X				57	IGA	Exit/Emergency	Exit Signs	55 Line Die Cast Contemporary	
781370104092	912401025274	SSL3WG		ServiceSmart	Universal Mount, AC Only, Single/Double Face, Green Letters, White Housing	L						57	IGA	Exit/Emergency	Exit Signs	55 Line Die Cast Contemporary	
782343390580	912400349641	SSL3WR		ServiceSmart	Universal Mount, AC Only, Single/Double Face, Red Letters, White Housing	L		X				57	IGA	Exit/Emergency	Exit Signs	55 Line Die Cast Contemporary	
781370104054	912401025271	FR5L3G		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Single/Double Face, Green Letters, Black Housing w/ Satin Aluminum Face	N,L						57	IGA	Exit/Emergency	Exit Signs	55 Line Die Cast Contemporary	
781370104047	912401025270	FR5L3R		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Single/Double Face, Red Letters, Black Housing w/ Satin Aluminum Face	L		X				57	IGA	Exit/Emergency	Exit Signs	55 Line Die Cast Contemporary	
781370104078	912401025272	FR5L3WG		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Single/Double Face, Green Letters, White Housing	L						57	IGA	Exit/Emergency	Exit Signs	55 Line Die Cast Contemporary	
781370621698	912400371075	FR5L3WR		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Single/Double Face, Red Letters, White Housing	L		X				57	IGA	Exit/Emergency	Exit Signs	55 Line Die Cast Contemporary	
781370410100	912401025228	FR5L3DG		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Single/Double Face, Green Letters, Black Housing w/ Satin Aluminum Face	L						57	IGA	Exit/Emergency	Exit Signs	55 Line Die Cast Contemporary	
781370410094	912401025228	FR5L3DR		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Single/Double Face, Red Letters, Black Housing w/ Satin Aluminum Face	C,L						57	IGA	Exit/Emergency	Exit Signs	55 Line Die Cast Contemporary	
781370410117	912400391551	FR5L3DWR		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Single/Double Face, Red Letters, White Housing	C,L						57	IGA	Exit/Emergency	Exit Signs	55 Line Die Cast Contemporary	
781370954116	912401025428	GOML43WR		ServiceSmart	Universal Mount, AC Only, Single Face w/Extra Facoplats, Red Letters, White Housing, White Face Plate	L						57	IGA	Exit/Emergency	Exit Signs	60 Line Wet Location	
781370921286	912400372810	FR6MMLD398		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Single Face w/Extra Facoplats, Red Letters, Black Housing, Black Face Plate	C						57	IGA	Exit/Emergency	Exit Signs	60 Line Wet Location	
781370921309	912400372812	FR6MMLD39W		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Single Face w/Extra Facoplats, Red Letters, White Housing, White Face Plate	C						57	IGA	Exit/Emergency	Exit Signs	60 Line Wet Location	
734340011326	912400342221	CKL3RW		ServiceSmart	Universal Mount, AC Only, Red Letters, White Thermoplastic Housing	C						57	IGA	Exit/Emergency	Exit Signs	Compac Exit	
734340753301	912400346211	CKL3GW		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Green Letters, White Thermoplastic Housing	C						57	IGA	Exit/Emergency	Exit Signs	Compac Exit	
734340753264	912400346207	CKL3RW		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Red Letters, White Thermoplastic Housing	C,NL						57	IGA	Exit/Emergency	Exit Signs	Compac Exit	
734340754018	912400346244	CCAL3GW		ServiceSmart	Semi Recessed Lamp Heads, 6V 6W MR16 Lamps, Universal Mount Double Face, Green Letters, White Thermoplastic Housing	L						58	IGA	Exit/Emergency	Emergency Commercial	Compac CCAK Combo Unit	
734340753156	912400346216	CCAL3RW		ServiceSmart	Semi Recessed Lamp Heads, 6V 6W MR16 Lamps, Universal Mount Double Face, Red Letters, White Thermoplastic Housing	L						58	IGA	Exit/Emergency	Emergency Commercial	Compac CCAK Combo Unit	
734340753170	912400346218	CCTL3RW		ServiceSmart	Semi Recessed Lamp Heads, 6V 5.4W Tungsten Lamps, Universal Mount Double Face, Red Letters, White Thermoplastic Housing	C						58	IGA	Exit/Emergency	Emergency Commercial	Compac CCTX Combo Unit	
784197038342	912401289498	VLLU		ServiceSmart	Value + Economy Grade 3.6V LED Emergency white and (2) 1 watt LED lamps	N						New	IGA	Exit/Emergency		Value+	
784197043234	912401289499	VLLUR		ServiceSmart	Value + Economy Grade 3.6V LED Emergency white and (2) 1 watt LED lamps and remote head capability	C,NL						New	IGA	Exit/Emergency		Value+	
784197043858	912401289502	VLLUZ		ServiceSmart	Value + Economy Grade 3.6V LED Emergency white and (2) 2 watt LED lamps	C,NL						New	IGA	Exit/Emergency		Value+	
784197043896	912401289506	VLLCG		ServiceSmart	Value + Economy Grade Emergency Combo unit 3.6V and (2) 1 watt LED lamps. No remote capability, Green letters.	C,NL						New	IGA	Exit/Emergency		Value+	
784197043902	912401289507	VLLCG2R		ServiceSmart	Value + Economy Grade Emergency Combo unit 3.6V and (2) 1 watt LED lamps and remote capability, Green letters.	C,NL						New	IGA	Exit/Emergency		Value+	
784197043957	912401289512	VLL2RGG		ServiceSmart	Value + Remote Head 3.6V, 6V, 9.6V, or 12V with (2) 1 watt LED lamp	C,NL						New	IGA	Exit/Emergency		Value+	
784197043885	912401289501	VLLCR2R	New Addition	ServiceSmart	Value + Economy Grade Emergency Combo unit 3.6V and (2) 1 watt LED lamps. No remote capability, Red letters.	L						New	IGA	Exit/Emergency		Value+	
784197043872	912401289504	VLLCR	New Addition	ServiceSmart	Value + Economy Grade Emergency Combo unit 3.6V and (2) 1 watt LED lamps and remote capability, Red letters.	L						New	IGA	Exit/Emergency		Value+	
784197043926	912401289509	VLL3R	New Addition	ServiceSmart	Value + Remote Head 3.6V (1) 1 watt LED lamp	L						New	IGA	Exit/Emergency		Value+	
784197043933	912401289510	VLL2R	New Addition	ServiceSmart	Value + Remote Head 3.6V (2) 1 watt LED lamps	L						New	IGA	Exit/Emergency		Value+	
782343263020	912400348806	VESWG		ServiceSmart	Universal Mount, AC Only, Green Letters, White Thermoplastic Housing	C,NL		X				58	IGA	Exit/Emergency	Exit Signs	Value+ Exit	
782343263044	912400348808	VESWEM		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Green Letters, White Thermoplastic Housing	C,NL						58	IGA	Exit/Emergency	Exit Signs	Value+ Exit	
782343263006	912400348805	VERW		ServiceSmart	Universal Mount, AC Only, Red Letters, White Thermoplastic Housing	C,N		X				58	IGA	Exit/Emergency	Exit Signs	Value+ Exit	
782343263037	912400348807	VVERWEM		ServiceSmart	Universal Mount, Emergency Operation Nicad Battery, Red Letters, White Thermoplastic Housing	C,NL		X				58	IGA	Exit/Emergency	Exit Signs	Value+ Exit	
734340753226	912400346203	CAX6		ServiceSmart	Semi Recessed Lamp Heads, White Thermoplastic Housing, Lead Acid Battery, 6V 6W MR16 Lamps	N						59	IGA	Exit/Emergency	Emergency Commercial	Compac CAX Unit	
734340753240	912400346205	CAX6H		ServiceSmart	Semi Recessed Lamp Heads, White Thermoplastic Housing, Lead Acid Battery, 6V 8W MR16 Lamps	N						59	IGA	Exit/Emergency	Emergency Commercial	Compac CAX Unit	
781370380120	912401025318	CAX6L24W12		ServiceSmart	Semi Recessed Lamp Heads, White Thermoplastic Housing, Lead Acid Battery, 6V 12W MR16 Lamps	C						59	IGA	Exit/Emergency	Emergency Commercial	Compac CAX Unit	
781370797957	912400372040	CFX6		ServiceSmart	Fixed Lens, White Thermoplastic Housing, Lead Acid Battery, 6V 5W MR11 Lamps	C						59	IGA	Exit/Emergency	Emergency Commercial	Compac CFX Unit	
781370797971	912400372042	CTX6		ServiceSmart	White Thermoplastic Housing, Lead Acid Battery, 6V 5.4W Tungsten Lamps	C						59	IGA	Exit/Emergency	Emergency Commercial	Compac CTX Unit	
781370799818	912400372046	CTX618		ServiceSmart	White Thermoplastic Housing, Lead Acid Battery, 6V 9W Tungsten Lamps	N						59	IGA	Exit/Emergency	Emergency Commercial	Compac CTX Unit	
734340611410	912400345534	CTN6L12WC5WA		ServiceSmart	White Thermoplastic Housing, Lead Acid Battery, 6V 5.4W Tungsten Lamps	C						59	IGA	Exit/Emergency	Emergency Commercial	Compac CTX Unit	

UPC	12NC	Part Number	Update	ServiceSmart / SpecSmart	Product Description	Stocked In	Up To Quantities	Distributor Stock Item	Energy Star	DLC Qualified	Title 24 Compliant	LSSG Page #	Category	Product Section	Product Sub Section	Product Family	Product Category
734340611458	912400345537	CTK6L18WCSWC		ServiceSmart	White Thermoplastic Housing, Lead Acid Battery, 6V 9W Tungsten Lamps	C						59	IGA	Exit/Emergency	Emergency Commercial	Compact CTX Unit	
734340611540	912400345541	CTK6L24WCSWF		ServiceSmart	White Thermoplastic Housing, Lead Acid Battery, 6V 12W Halogen Lamps	C						59	IGA	Exit/Emergency	Emergency Commercial	Compact CTX Unit	
734340592573	912400345442	CCRHP		ServiceSmart	Weatherproof Remote Metal Chrome Lamp Head, 6V 6W Halogen Lamp	N		X				61	IGA	Exit/Emergency	Emergency Architectural	Emergency Remote Fixtures & Accessories	
782343833162	912400340561	SMR10WG		ServiceSmart	Symmetry Remote Dual Lamp, 6V 5.4W Tungsten	C						61	IGA	Exit/Emergency	Emergency Architectural	Emergency Remote Fixtures & Accessories	
734340115352	912400342802	WG4		SpecSmart	Wire Guard		50					61	IGA	Exit/Emergency	Emergency Architectural	Emergency Remote Fixtures & Accessories	
734340085648	912400342659	WGS		SpecSmart	Wire Guard		50					61	IGA	Exit/Emergency	Emergency Architectural	Emergency Remote Fixtures & Accessories	
734340107807	912401025012	MSLL		ServiceSmart	White LED, White Universal Louver Faceplates (Vertical and Horizontal), 120VAC	L						61	IGA	Exit/Emergency	Emergency Architectural	MSL Mini Step Lite	
782343573235	912400351489	PLACMBZ		ServiceSmart	Wall Light, Die Cast Aluminum Bronze Housing, AC 120/277V w/ Integral Nicad Battery Backup, 6V 8-3W LEDs	L						61	IGA	Exit/Emergency	Emergency Architectural	Patron LED Wall Light	
78234352431	912401025123	PLEMBZ		ServiceSmart	Wall Light, Die Cast Aluminum Bronze Housing, Nicad Battery, 6V 8-3W LEDs	L						61	IGA	Exit/Emergency	Emergency Architectural	Patron LED Wall Light	
781370379858	912401025308	PONBZ		ServiceSmart	Die Cast Aluminum Bronze Housing, Nicad Battery, 6V 6W, Halogen Lamp	C,L		X				61	IGA	Exit/Emergency	Emergency Architectural	Patron Wall Light	
734340643596	912400345722	DEB-1W		ServiceSmart	Emergency Ballast, 350-450lm, One Lamp Operation, Fluorescent	L		X				62	IGA	Exit/Emergency	Emergency Ballasts	DEB Series - Emergency Ballast	
734340524021	912400345623	DEB-5W		ServiceSmart	Emergency Ballast, 1100-1400lm, One or Two Lamp Operation, Fluorescent	C,NL		X				62	IGA	Exit/Emergency	Emergency Ballasts	DEB Series - Emergency Ballast	
734340602395	912401025045	DEB-7LP		ServiceSmart	Emergency Ballast, 390-700lm, One Lamp Operation, Low Profile, Fluorescent	C,NL						62	IGA	Exit/Emergency	Emergency Ballasts	DEB Series - Emergency Ballast	
782343823422	912400359847	DEB-7W		ServiceSmart	Emergency Ballast, 600-700lm, One or Two Lamp Operation, Fluorescent	C		X				62	IGA	Exit/Emergency	Emergency Ballasts	DEB Series - Emergency Ballast	
781370584191	912400370841	MTD		ServiceSmart	Auxiliary Power Transfer Device (Internal Luminaire Mounted)	C						62	IGA	Exit/Emergency	Emergency Ballasts	MTD Series - Transfer Device	
781370988821	912401025422	MTD20-277		SpecSmart	Auxiliary Power Transfer Device 277V (Wall or Ceiling Mounted)		50					62	IGA	Exit/Emergency	Emergency Ballasts	MTD Series - Transfer Device	
782343568231	912400351435	4ARLU18NYC		SpecSmart	NYC Universal Edge Lit LED Exit, Universal Mount, AC Only, Single Face, 8" Red Letters, Clear Background, Satin Aluminum Housing		50					62	IGA	Exit/Emergency	New York City Products	New York City Approved	
782343568248	912400351436	4ARLU28NYC		SpecSmart	NYC Universal Edge Lit LED Exit, Universal Mount, AC Only, Double Face, Red Letters, Mirror Background, Satin Aluminum Housing		50					62	IGA	Exit/Emergency	New York City Products	New York City Approved	
782343568262	912400351438	ER44RLDU28NYC		ServiceSmart	NYC Universal Edge Lit LED Exit, Universal Mount, Emergency Operation Nicad Battery, Double Face, 8" Red Letters, Mirror Background, Satin Aluminum Housing	N						62	IGA	Exit/Emergency	New York City Products	New York City Approved	