

PHILIPS

Ballast compatibility guide

LED InstantFit T8

with EasySmart technology



T8 EasySmart Instant-Start Ballasts⁷

14W 2100lm
(4ft.)

46645-8,
46646-6,
46647-4,
46648-2

Manufacturer	Ballast Model	System Certified/ Certified ²
Philips - Advance	ICN-2P32-N	System Certified
Philips - Advance	ICN-3P32-N	System Certified
Philips - Advance	IOPA-2P32-N	System Certified
Philips - Advance	IOPA-4P32-N	System Certified
Philips - Advance	IOPA-2P32-LW-N	System Certified
Philips - Advance	IOPA-3P32-LW-N	System Certified
Philips - Advance	IOPA-1P32-HL-N	System Certified
Philips - Advance	IOPA-2P32-HL-SC	System Certified
Philips - Advance	IOPA-4P32-HL-90C-G	System Certified
Philips - Advance	IOP-2P32-N	System Certified
Philips - Advance	IOP-2P32-LW-N	System Certified
Philips - Advance	IOP-4P32-LW-N	System Certified
Philips - Advance	IOP-2P32-HL-N	System Certified
Philips - Advance	IOP-3P32-HL-N	System Certified
Philips - Advance	GOPA-3P32-LW-SC	System Certified
Philips - Advance	GOPA-4P32-LW-SC	System Certified
Philips - Advance	REB-2P32-SC	System Certified

Manufacturer	Ballast Model	System Certified/ Certified ²
Universal Lighting Technologies	B232IUNVHP-N	Certified
Universal Lighting Technologies	B332IUNVHP-A	Certified
Universal Lighting Technologies	B432IUNVHP-A	Certified
Universal Lighting Technologies	B132IUNVHE-A	Certified
Universal Lighting Technologies	B432IUNVHE-A	Certified
Universal Lighting Technologies	B132IUNVEL-A	Certified
Universal Lighting Technologies	B432IUNVEL-A	Certified
Universal Lighting Technologies	B332IUNVHEH-A	Certified
General Electric	GE-232-MV-N	Certified
General Electric	GE-332-MV-N	Certified
General Electric	GE-232-MV-N-DIY	Certified
General Electric	GE-332-MV-N-DIY	Certified
General Electric	GE-432-MV-N-DIY	Certified
General Electric	GE232MAX347-N	Certified
General Electric	GE432MAX347-N	Certified
General Electric	GE232-120RES-DIY	Certified
General Electric	GE432-120RES-DIY	Certified

Manufacturer	Ballast Model	System Certified/ Certified ²
Osram - Sylvania	QTP 1X32T8/UNV ISN-SC	Certified
Osram - Sylvania	QTP 2X32T8/UNV ISN-SC	Certified
Osram - Sylvania	QTP 4X32T8/UNV ISN-SC	Certified
Osram - Sylvania	QHE 2X32T8/UNV ISN-SC	Certified
Osram - Sylvania	QHE 3x32T8/UNV ISN-SC	Certified
Osram - Sylvania	QHE 4X32T8/UNV ISN-SC	Certified
Osram - Sylvania	QHE 1x32T8/UNV ISL-SC	Certified
Osram - Sylvania	QHE 2X32T8/UNV ISL-SC	Certified
Osram - Sylvania	QHE 3x32T8/UNV ISL-SC	Certified
Osram - Sylvania	QHE 4X32T8/UNV ISL-SC	Certified
Osram - Sylvania	QHE 1x32T8/UNV ISH-SC	Certified
Osram - Sylvania	QHE 3x32T8/UNV ISH-SC	Certified
Osram - Sylvania	QHE 4x32T8/UNV ISH	Certified
Osram - Sylvania	QHE 2X32T8/UNV ISH HT SC	Certified
Osram - Sylvania	QHE 1x32T8/UNV ISL-SC-1	Certified

1. System performance (Philips InstantFit LED T8 lamps with EasySmart technology and ballast) has been evaluated by the lamp and ballast manufacturer.
 2. System performance (Philips InstantFit LED T8 lamps with EasySmart technology and ballast) has been evaluated by the lamp manufacturer only.
- * Please contact Philips for questions about third party ballasts that are not on this list. Information in this document is subject to change without prior notice



© 2017 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

PLt-17031CR 03/17



Philips Lighting North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Imported by: Philips Lighting,
A division of Philips Electronics Ltd.
281 Hillmount Rd, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008