



Value beyond illumination

Philips Ledalite FloatPlane Suspended with **Power over ethernet (PoE) technology**, allows the lighting system to be merged with the IT system. In addition to providing high quality and energy efficient LED lighting, connected lighting with PoE can inform owners of maintenance requests, occupancy trends, temperature control, and more creating

Features

- Power and data over the same Ethernet cable. No need to run line voltage wiring to the luminaires.
- Each luminaire gets a unique IP address and is directly connected to a building's IT network via a PoE switch.
- Ease of IT integration: Each luminaire can be identified, managed and controlled from various IT platforms.
- Occupancy and daylight sensors embedded in luminaires.
- PoE Emergency driver available.
- Sizes 4ft, 8ft
- 3000K, 3500K & 4000K
- Lumen output up to 6000lm/4ft
- Efficacy up to 129 lm/W
- Wide upper hemisphere distribution for uniform ceilings
- 5 Year warranty