

PHILIPS

Ballast
compatibility guide

TrueForce lamps



Applicable part numbers for all TrueForce high lumen lamps
(for high bay lighting applications):

46560-9
46562-5
46565-8
46567-4



RoHS
COMPLIANT



TrueForce lamps

Manufacturer	ANSI Type	Lamp Wattage	Ballast Model	System Certified/ Certified ²
Philips Lighting	M135 / M155	400	71A6092-AEE	System Certified
Philips Lighting	M59	400	71A6091-A	System Certified
Philips Lighting	M59	400	71A6051-A	System Certified
General Electric	M59	400	GEM400ML5AA4-5	Certified
Osram Sylvania	M135 / M155	400	M400/MULTI-PS-KIT	Certified
Universal Lighting Technologies	M59	400	M400MLTAC4M	Certified
Holophane (Div. of Acuity Brands)	M59	400	RKB40LMHMT	Certified
Cooper Lighting	M59	400	MHKT-400-CWA-MT	Certified
Cooper Lighting	M59	400	MPKT-400-CWA-MT	Certified
Robertson	M155	400	CMH0400H04912	Certified
Souhegan Lighting Products	M155	400	S400M-4/PS	Certified

1. System Performance (Philips TrueForce LED lamp and ballast) has been evaluated by both the lamp and ballast manufacturer.
2. System Performance (Philips TrueForce LED lamp and ballast) has been evaluated by the lamp manufacturer only.

© 2017 Philips Lighting Holding B.V. All rights reserved.
Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
281 Hillmount Rd, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008