

**PHILIPS
LIGHTOLIER**

Track lighting

OmniSpot LED

Recessed multiples
600lm & 1000lm



One frame, one fixture, **multiple advantages**

Philips Lightolier OmniSpot LED recessed multiples are designed for easy specifying and quick installation. Even last minute changes in the lighting layout won't have to be a waste of your time, because... time is money.

Benefits

- Utilizes the same LED technology, reflectors and accessories as the OmniSpot LED track heads which provides performance consistency and design continuity within a space.
- Field changeable optics allow for quick modifications when distribution needs to be adjusted for a given area within an application.
- Employs quick-connect technology design that enables future proof values with our plug-and-play receptacle for easy installation.



OmniSpot LED recessed multiples

OmniSpot LED recessed multiples are a three-part system designed to meet performance and aesthetic attributes of today's accent lighting needs. Utilizing the same LED technology and optics as the track heads, OmniSpot LED RM provides performance consistency and design continuity within a space. It also provides a high center providing a high center beam candlepower – all while being neatly hidden in a ceiling for a clean streamlined look.

Features

- Lumens: 600 & 1000
- Watts: 12W
- Efficacy: 98lm/W
- CCT: 2700K, 3000K, 3500K, and 4000K
- CRI: 80, 90
- Field Changeable Optics
- Dimming: 0-10V
- Voltage: 120V-277V
- Lifetime: 50,000 hrs
- Warranty: 5 years
- Accessories: Snoot, Hex Cell, Diffusion Films

Frame

example: LCRM10H2

Series	Styles	Lumens	Heads
LC	RM	10	
LC OmniSpot LED cylinder	RM Recessed Multiple	10 600lm and 1000lm	H1 1 head H2 2 head H3 3 head H4 4 head

Reflector

example: LLMRNS

Series	Beam spreads (ordered separately)
LLM	
LLM Reflector for 600 / 1000lm	RNS 11° Narrow Spot RS 18° Spot RNF 24° Narrow Flood RF 36° Flood

Fixture

example: LC10930H2BKZ10U

Series	Styles	Lumens	CRI/CCT	Heads	Finishes	Flanges	Dimming/Volts
LC	RM						Z10U
LC OmniSpot LED cylinder	RM Recessed Multiple	06 600lm 10 1000lm	827 80CRI/2700K 830 80CRI/3000K 835 80CRI/3500K 840 80CRI/4000K 927 90CRI/2700K 930 90CRI/3000K 930CW 90CRI/3000K with Crisp White	H1 1 head H2 2 head H3 3 head H4 4 head	BK Matte Black WH Matte White	- Flange (leave blank) F Flangeless	Z10U 0-10V 1% 120/277V

Accessories¹

example: LC10SNBK

Series	Finishes/Types
LC10AH Accessory holder ²	WH Matte White
LC10SN Snoot	BK Matte Black
7472 Hex cell	- Matte Black ³
LC10 Diffusion film	SY Symmetrical Spread SF Soft Focus LS Linear Spread FR Frosted Etched

Mud-in Kit

LCRM10H1MK	600/1000lm for 1 head configs
LCRM10H2MK	600/1000lm for 2 head configs
LCRM10H3MK	600/1000lm for 3 head configs
LCRM10H4MK	600/1000lm for 4 head configs



Visit philips.com/warranties for more information on the standard 5-year limited warranty.

1. Aperture ring on the fixture can hold a maximum of 1 film and 1 snoot.
2. Accessory holder can hold a maximum of 1 hex cell, 1 film, and 1 snoot.
3. Hex cell needs to be ordered with an Accessory holder.

© 2018 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting, North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
281 Hillmount Rd, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008