

Light to go



Things just got easier.
Introducing our new line up
of lighting essentials –
quick to order, easy on your
wallet and simple to use.

Make your next lighting
choice a brand you can trust.
Make it Philips Lighting.

philips.com/Lighttogo



© 2018 Philips Lighting Holding B.V. All rights reserved.
Philips reserves the right to make changes in specifications and/or to discontinue any product
at any time without notice or obligation and will not be liable for any consequences resulting
from the use of this publication.

PLI-1710ILL 04/18 philips.com/Lighttogo

Philips Lighting,
North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
281 Hillmount Rd,
Markham, ON, Canada L6C 2S3
Tel. 800-668-9008

PHILIPS



Downlighting

- Flat downlight
- Mini downlight
- Mini gimbal
- Surface mount
- Retrofit downlight



Light to go

**Easy order.
Budget friendly.
Job ready.**



**Easy order.
Budget friendly.
Job ready.**

Philips Light to go downlights




Philips knows contractors look for dependability and ease of installation when choosing a downlight – and these lights were designed with that in mind. They are also versatile and suitable to be used in wet locations. Adding light where you need it has never been easier.

You've found
your **go to**
downlights,

Philips
Light to go
downlights



Flat downlight - round



- **Detachable electric box with remodel NEC clip.**
- Quick and easy installation without frame or reflector.
- Available in 4" & 6" sizes.
- LED technology featuring long lifetimes for reduced maintenance.
- 1" depth, low profile for non-intrusive install.
- IC-rated for direct contact with insulation.
- Through wiring capability.
- Lifetime >50,000 hours (L70).
- Mercury free and Wet location rated.
- Listings: ENERGY STAR®, Title 24 rated, UL 1598 wet location rated (in covered ceilings).
- Backed by the Philips 5-year warranty

Flat downlight - square



- **Detachable electric box with remodel NEC clip.**
- 1" depth, low profile for non-intrusive install.
- Available in 4" & 6" sizes.
- Quick and easy installation without frame or reflector.
- LED technology featuring long lifetimes for reduced maintenance.
- IC-rated for direct contact with insulation.
- Through wiring capability.
- Lifetime >50,000 hours (L70).
- Mercury free and Wet location rated.
- Listings: ENERGY STAR®, Title 24 rated, UL 1598 wet location rated (in covered ceilings).
- Backed by the Philips 5-year warranty

Surface mount



- One piece plastic flange. White matte finish.
- Available in 5" & 7" sizes.
- Diffused lens for smooth, comfortable light pattern.
- Power supply – Integral class 2 driver (see Electrical section for specifications).
- Utilizes edge lit LED technology.
- Lifetime L70 at 50,000 hours and backed by the Philips 5-year warranty
- Compliance: Non-conductive fixture for shower light application.
- Support Wire: Support wire attached to the fixture to hook on the mounting bracket to hold the fixture.

Easy order. Budget friendly. Job ready.



Philips Catalog Code	Size	Lumens	Color Temp	Dimming	Replaces
FDL4R07930TE1W	4"	700	3000K	ELV/TRIAC	50W PAR20
FDL6R09930TE1W	6"	900	3000K	ELV/TRIAC	65W PAR30

Accessories (order separately)
 FDLRN - Round new construction plate
 FDL06C - 6ft extension cable
 FDL20C - 20ft extension cable

Philips Catalog Code	Size	Lumens	Color Temp	Dimming	Replaces
FDL4S07930TE1W	4"	700	3000K	ELV/TRIAC	50W PAR20
FDL6S09930TE1W	6"	900	3000K	ELV/TRIAC	65W PAR30

Accessories (order separately)
 FDLSN - Square new construction plate
 FDL06C - 6ft extension cable
 FDL20C - 20ft extension cable

Philips Catalog Code	Size	Lumens	Color Temp	Dimming	Replaces
PSD5R079301W	5"	600	3000K	ELV/TRIAC	65W PAR30
PSD7R099301W	7"	1000	3000K	ELV/TRIAC	75W PAR38

Please refer to the specification sheets for additional information and technical data, philips.com/Lighttogo

Mini downlight



- **Detachable electric box with remodel NEC clip.**
- Quick and easy installation without frame or reflector.
- 550 Lumen output from the mini 1-1/4" aperture.
- LED technology featuring long lifetimes for reduced maintenance.
- 1" depth, low profile for non-intrusive install.
- IC-rated for direct contact with insulation.
- Lifetime >50,000 hours (L70).
- TRIAC dimming down to 10%.
- Listings: ENERGY STAR®, Title 24 (JA8-2016), ETL listed, damp location rated & AirSeal/IC.
- Backed by the Philips 5-year warranty

Mini gimbal



- **Detachable electric box with remodel NEC clip.**
- Quick and easy installation without frame or reflector.
- 550 Lumen output from the mini 1-1/2" aperture.
- LED technology featuring long lifetimes for reduced maintenance.
- 1" depth, low profile for non-intrusive install.
- IC-rated for direct contact with insulation.
- Lifetime >50,000 hours (L70).
- TRIAC dimming down to 10%.
- Listings: ENERGY STAR®, Title 24 (JA8-2016), ETL listed, damp location rated & AirSeal/IC.
- Backed by the Philips 5-year warranty.

Retrofit downlight



- Utilizes existing frames to make replacing old downlighting and upgrading to LED, a truly easy task.
- Available in 4" & 5/6" sizes.
- Flexible springs allow for installation without tools.
- Contemporary and simple design with baffle trim.
- Uniform LED light with glare-reduction filter, means a more comfortable space
- Long lifetime will reduce your future maintenance (L70 at 42,000 hours).
- Backed by the Philips 5-year warranty

Philips Catalog Code	Size	Lumens	Color Temp	Beam Spread	Replaces
PMD3R069301FW	3"	550	3000K	Flood	50W MR16

Accessories (order separately)
 PMDRN - Round new construction plate
 PMD06C - 6ft extension cable
 PMD20C - 20ft extension cable

Philips Catalog Code	Size	Lumens	Color Temp	Beam Spread	Replaces
PMG3R06930NFIW	3"	550	3000K	Narrow Flood	50W MR16

Accessories (order separately)
 PMDRN - Round new construction plate
 PMD06C - 6ft extension cable
 PMD20C - 20ft extension cable

Philips Catalog Code	Size	Lumens	Color Temp	Dimming	Replaces
PRD4R089301W	4"	900	3000K	ELV/TRIAC	50W PAR20
PRD5R129301W	5/6"	1400	3000K	ELV/TRIAC	65W PAR30

Please refer to the specification sheets for additional information and technical data, philips.com/Lighttogo