

# Light to go



Things just got easier.  
Introducing our new line up  
of lighting essentials –  
quick to order, easy on your  
wallet and simple to use.

Make your next lighting  
choice a brand you can trust.

**Make it Philips Lighting.**

[philips.com/Lighttogo](http://philips.com/Lighttogo)



© 2018 Philips Lighting Holding BV. All rights reserved.  
Philips reserves the right to make changes in specifications and/or to discontinue any product  
at any time without notice or obligation and will not be liable for any consequences resulting  
from the use of this publication.

PLI-17100LL 01/18 [philips.com/Lighttogo](http://philips.com/Lighttogo)

Philips Lighting,  
North America Corporation  
200 Franklin Square Drive,  
Somerset, NJ 08873  
Tel. 855-486-2216

Philips Lighting Canada Ltd.  
281 Hillmount Rd.  
Markham, ON, Canada L6C 2S3  
Tel. 800-668-9008

**PHILIPS**

Indoor

Recessed, Linear,  
High Bay & Exit/  
Emergency



## Light to go

**Easy order.  
Budget friendly.  
Job ready.**





**Easy order.  
Budget friendly.  
Job ready.**



## Flat panel



- High quality fixture will pay off in the long run.
- Help bolster wellbeing and productivity without worrying about flicker and other undesired effects.
- Immerse users in comfortable, welcoming spaces that are free of glare

- with color that remains consistent throughout the space and over time.
- Protect both the integrity of electrical equipment and overall building efficiency from the effects of total harmonic distortion.

## Recessed troffer



- Discretely designed to blend seamlessly into your space.
- Access to LED boards and drivers from below the ceiling increases maintenance convenience.

- Diffused ribbed lens creates soft, even illumination.
- Choose from 3500 or 4000K color temperatures.

## Linear

### Linear strip

### Linear wraparound

### Linear industrial



- Rugged and reliable, the Philips LED Linear family includes strip, industrial and wraparound luminaires.
- Simple installation.
- Efficacy up to 131 lumens per watt.

- Before, during and after installation, you can trust them to help you quickly complete projects without hassles or troubleshooting, while delivering consistent comfort and long-term energy savings.

Easy order. Budget friendly. Job ready.



Philips Catalog Code	Size	Lumens	Color Temp	Dimming	Replaces
P2FXP38B835-2-DS-UNV-DIM	2x2'	3800	3500K	0-10V	2xF17T8
P2FXP38B840-2-DS-UNV-DIM			4000K		2xF17T8
P2FXP42B835-4-DS-UNV-DIM	2x4'	4200	3500K	0-10V	2xF32T8
P2FXP42B840-4-DS-UNV-DIM			4000K		2xF32T8

Philips Catalog Code	Size	Lumens	Color Temp	Dim.	Replaces
P2FGG38B835-2-D-UNV-DIM	2'x2'	3800	3500K	0-10V	2xF17T8
P2FGG38B840-2-D-UNV-DIM			4000K		2xF17T8
P2FGG42B835-4-D-UNV-DIM	2'x4'	4200	3500K	0-10V	2xF32T8
P2FGG42B840-4-D-UNV-DIM			4000K		2xF32T8

Philips Catalog Code	Size	Lum.	Color Temp	Dim.	Replaces
PFSSEZ440L830-UNV (Strip)	4'	4000	3000K	N/A	2xF32T8
PFSSEZ440L840-UNV (Strip)			4000K		2xF32T8
PFSWEZ440L830-UNV (Wraparound)	4'	4000	3000K	N/A	2xF32T8
PFSWEZ440L840-UNV (Wraparound)			4000K		2xF32T8
PFSI455L840-UNV-DIM (Industrial)	4'	5500	4000	0-10V	3xF32T8
PFSI8110L840-UNV-DIM (Industrial)	8'	11000	4000	0-10V	6xF32T8

## Exit & Emergency



- A complete family of dependable products to make buying, ordering & installation for large projects easier.
- Exit signs run off a long-life, 6 volt maintenance-free battery.
- All 3 versions can mount on wall or ceiling.
- Emergency unit and Exit combo can be used for indoor or covered outdoor spaces.
- Units and combos also contain a manual test switch with LED light indicator and supply emergency illumination for at least 90 minutes.

## High bay



- Versatile fixture ideal for a variety of spaces including warehouses, big box retail and school gymnasiums.
- 16,000 & 24,000 lumen versions available.
- Simple installation.
- Dimming is standard.
- Both versions are serious energy savers with outputs up to 138 lumens per watt.
- DLC listed.

## Philips Light to go luminaires

Philips knows contractors look for dependability and ease of installation when choosing their lighting – and these LED luminaires were designed with that in mind. Strong and long lasting with solid performance, adding light where you need it is quick and easier than ever.

You've found your go to lights,

Philips Light to go

Philips Catalog Code	Letter Color	Finish	Operation	
PVERWEM (Exit Sign)	Red	White	Emergency (Nicad Battery)	
PVEGWEM (Exit Sign)	Green	White	Emergency (Nicad Battery)	
Philips Catalog Code	Voltage	Finish	# LED Lamps	Remote
PVLLCR2R (Red Letter Exit Combo)	3.6V	White	2 - 1W	2-1W or 1-2W Head
PVLLCG2R (Green Letter Exit Combo)	3.6V	White	2 - 1W	2-1W or 1-2W Head
PVLLU (Emergency Unit)	3.6V	White	2 - 1W	None
PVLL1R (Remote Lamp Head)	3.6V	White	1 - 1W	Indoor
PVLL2R (Remote Lamp Head)	3.6V	White	2 - 1W	Indoor
PVLL1RGO (Remote Lamp Head)	3.6, 6, 9.6 or 12V	Gray	1 - 1W	Outdoor
PVLL2RGO (Remote Lamp Head)	3.6, 6, 9.6 or 12V	Gray	2 - 1W	Outdoor

Philips Catalog Code	Size	Lumens	Color Temp	Dim.	Replaces
PFBX16LL40-UNV	2' x 2'	16,000	4000K	0-10V	6x F32T8 or 400W HID
PFBX16LL50-UNV			5000K		
PFBX24LL40-UNV	2' x 2'	24,000	4000K	0-10V	8x F32T8 or 400W HID
PFBX24LL50-UNV			5000K		
PFBX CHAIN KIT, PFBX-GRIP10, PFBX-GRIP5, PFBX-PENHGR	High bay mounting accessories (54" chains, 10' cable, 5' cable, pendant hanger)				

