



PHILIPS
LEDALITE

Linear

EyeLine
suspended & wall



Make **the room** the view...

EyeLine helps make your space a destination.

Stylishly sophisticated, boldly dramatic... **Philips Ledalite EyeLine** is sure to make a statement in any architectural space. Horizontally ultra-thin linear light panels make **EyeLine** appear weightless, and so utterly organic that it becomes a natural design element of the built environment. Providing gentle, glare free illumination, **EyeLine** will startle you with its robust performance, while allowing you to maximize row spacing in large open plan areas, and keep energy densities to a minimum.


Make your room the view with **EyeLine**.

EyeLine suspended & wall

4ft modules • 3000, 3500, 4000K

Features

- **Applications:** Office, higher education, retail
- **Types:** Suspended & wall mount, direct/indirect
- **Lengths:** 4ft standalone modules & continuous row
- **Color temperatures:** 3000k, 3500K, 4000K (80 and 90 CRI)
- **Lumen packages:** 3400lm (25W), 4800lm (36W), 6800lm (54W)
- **Controls:** SpaceWise DT
- **Efficacy:** Up to 133 LPW



EyeLine suspended & wall

Family	Ceiling Type	Mount Type	Source	CRI/Color Temp ¹	Lumens ¹	Optics	Distribution ¹	Run Length	Voltage ³
EL EyeLine	G T-Grid C Chicago T-Grid D Drywall S Open Structure	S Suspended	L LED	840 80CRI, 4000K	68 6800 lm/4ft	Q Symmetric MesoOptics Lens	N 65% Up / 35% Dn G 20% Up / 80% Dn J 100% Dn	04 4ft XX Total run length	D 120/277V Dual 3 347V
		W Wall		835 80CRI, 3500K 830 80CRI, 3000K 935 90CRI, 3500K	48 4800 lm/4ft 34 3400 lm/4ft 24 2400 lm/4ft				
Driver	Circuit	EM Option ^{2,3,4}	Sensors	Fixture Color ⁵	Power Cord Color	Cable Drop Length	Ceiling Mount		
E Philips Advance 0-10v (1% dim)	R 1 Circuit, Remote Driver	N No Option E EM Wiring Ready B EM Batt. Pack	NN No Integral Sensor SZ SpaceWise DT Sensor	W White B Black R Racing Red G Graphite Grey C Custom	W White B Black	04 4ft 08 8ft 12 12ft 20 20ft	R1 Drywall R3 Surface/Structure/Hard Ceiling R5 T-Grid 24" Span Mount R6-1* On-Grid 15/16" non-tegular R6-2* On-Grid 9/16" non-tegular R6-3* On-Grid 9/16" 5/16" tegular		
S Philips Advance SR (5% dim)									

¹ Nominal values within a range. Consult photometry data for color temp, lumens & distribution of chosen configuration.

² Not all wiring types are available with all configurations. Consult Philips Ledalite for a complete list of available

³ 347V not available with EM Batt. Packs, Philips Advance SR drivers, or SpaceWise DT sensors

⁴ EM Batt. Pack not available with Drywall Ceiling

⁵ All fixture colors, other than White result in a reduced fixture efficacy between 5-20%

© 2018 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.
philips.com/EyeLine



Philips Lighting North America Corporation
 200 Franklin Square Drive, Somerset, NJ 08873
 Tel. 855-486-2216

Philips Lighting Canada Ltd.
 281 Hillmount Rd, Markham, ON, Canada L6C 2S3
 Tel. 800-668-9008