

**PHILIPS**

LED

MainsFit  
(UL Type-B) lamps



**easy** install ✓  
**energy savings** ✓  
**peace of mind** ✓

Philips MainsFit (UL Type B) T8 LED lamps use a double-ended design which significantly simplifies installation, saving time and costs. This product can replace either T8 or T12 lamps in fixtures containing shunted or non-shunted G13 (medium bi-pin) lamp holders.

- **Proven over 40% energy savings<sup>1</sup>** over fluorescent systems
- **Lifetime delivered** — average life rating of 50,000 hours<sup>2</sup> means satisfied customers
- **Improved profit** and more time growing business instead of doing rework
- **UL Classified** and double-ended design for safety
- **Ballast Bypass** – UL Type-B
- **Light quality and performance predictability**— consistent light output and no flicker means satisfied happy customers and no wasted time redoing a job.
- **Proven product history** and a company with a long history of innovation and reliability in the lighting industry.
- **Wide beam** light distribution – 240° beam angle and 350° illumination angle.
- **Installation simplicity** – can be used with both shunted and non-shunted sockets
- **DLC Certified** – all MainsFit lamps are DLC certified

# Philips MainsFit LED lamps

## Ordering, electrical and technical data (Subject to change without notice)

Product Number	Model Number	DLC Product ID	Ordering Code	Volts	Base	CRI	Color Temp. (K)	Pkg Qty	LED Lifetime <sup>3</sup>	MOL (in.)	Beam Angle
<b>MainsFit LED T8 High Efficiency - 4ft</b>											
53267-1	9290018768	PHOGPIG6	12T8/PRO/48-830/BB17/G 10/1 FB	120-277	G13	82	3000	10	50,000	48	240°
53268-9	9290018769	PS838QCF	12T8/PRO/48-835/BB17/G 10/1 FB	120-277	G13	82	3500	10	50,000	48	240°
53269-7	9290018770	PLRV3PP4	12T8/PRO/48-840/BB18/G 10/1 FB	120-277	G13	82	4000	10	50,000	48	240°
53270-5	9290018771	PYPHBOOB	12T8/PRO/48-850/BB18/G 10/1 FB	120-277	G13	82	5000	10	50,000	48	240°
<b>MainsFit LED T8 - 4ft</b>											
47731-5	9290018454	P3V56EPW	14T8PRO/48-830/BB17/G 10/1 FB	120-277	G13	82	3000	10	50,000	48	240°
47732-3	9290018455	PN3X1615	14T8PRO/48-835/BB17/G 10/1 FB	120-277	G13	82	3500	10	50,000	48	240°
47733-1	9290018456	PTLPG7HI	14T8PRO/48-840/BB18/G 10/1 FB	120-277	G13	82	4000	10	50,000	48	240°
47734-9	9290018457	PDSO3H88	14T8PRO/48-850/BB18/G 10/1 FB	120-277	G13	82	5000	10	50,000	48	240°
<b>MainsFit LED T8 High Output - 4ft</b>											
47174-8	9290013631A	P3STDHPR	16.5T8PRO/48-830/BB20/G	120-277	G13	82	3000	10	50,000	48	240°
47175-5	9290013632A	PY5XD54C	16.5T8PRO/48-835/BB20/G	120-277	G13	82	3500	10	50,000	48	240°
47176-3	9290013633A	PKVUC6JH	16.5T8PRO/48-840/BB21/G	120-277	G13	82	4000	10	50,000	48	240°
47177-1	9290013634A	PFKMF7AO	16.5T8PRO/48-850/BB21/G	120-277	G13	82	5000	10	50,000	48	240°

## Technical data (Subject to change without notice)

MainsFit LED T8 High Efficiency - 4ft				
Product Number	Bare Lamp Watts (W)	Initial Lumens <sup>4</sup>	Beam Angle	Dimmable <sup>5</sup>
53267-1	12	1700	240°	N
53268-9	12	1700	240°	N
53269-7	12	1800	240°	N
53270-5	12	1800	240°	N
<b>MainsFit LED T8 - 4ft</b>				
47731-5	14	1700	240°	N
47732-3	14	1700	240°	N
47733-1	14	1800	240°	N
47734-9	14	1800	240°	N

MainsFit LED T8 High Output - 4ft				
Product Number	Bare Lamp Watts (W)	Initial Lumens <sup>4</sup>	Beam Angle	Dimmable <sup>5</sup>
47174-8	17	2000	240°	N
47175-5	17	2000	240°	N
47176-3	17	2100	240°	N
47177-1	17	2100	240°	N

For more information on Philips' limited warranty please visit [www.philips.com/warranties](http://www.philips.com/warranties)

## Shipping data (Subject to change without notice)

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. ft.)	Pallet Qty	Lamps/ SKU	SKUs per Layer	Layers High	SKU Dimensions (L x W x H) (in.)	Case Dimensions (L x W x H) (in.)	Pallet Dimensions (L x W x H) (in.)
<b>MainsFit LED T8 High Efficiency - 4ft</b>												
53267-1	53267-3	53267-8	10	6.65	0.79	550	1	50	10	11 x 11 x 47.8	49.5 x 7.1 x 3.9	51.2 x 40 x 47
53268-9	53268-0	53268-5	10	6.65	0.79	550	1	50	10	11 x 11 x 47.8	49.5 x 7.1 x 3.9	51.2 x 40 x 47
53269-7	53269-7	53269-2	10	6.65	0.79	550	1	50	10	11 x 11 x 47.8	49.5 x 7.1 x 3.9	51.2 x 40 x 47
53270-5	53270-3	53270-8	10	6.65	0.79	550	1	50	10	11 x 11 x 47.8	49.5 x 7.1 x 3.9	51.2 x 40 x 47
<b>MainsFit LED T8 - 4ft</b>												
47731-5	47731-8	47731-3	10	6.65	0.42	550	1	50	11	11 x 11 x 47.6	49.5 x 7.1 x 3.9	50.0 x 35.9 x 42.6
47732-3	47732-5	47732-0	10	6.65	0.42	550	1	50	11	11 x 11 x 47.6	49.5 x 7.1 x 3.9	50.0 x 35.9 x 42.6
47733-1	47733-2	47733-7	10	6.65	0.42	550	1	50	11	11 x 11 x 47.6	49.5 x 7.1 x 3.9	50.0 x 35.9 x 42.6
47734-9	47734-9	47734-4	10	6.65	0.42	550	1	50	11	11 x 11 x 47.6	49.5 x 7.1 x 3.9	50.0 x 35.9 x 42.6
<b>MainsFit LED T8 High Output - 4ft</b>												
47174-8	47174-3	47174-8	10	6.20	0.42	550	1	50	11	11 x 11 x 47.6	50 x 35.9 x 3.9	50.0 x 35.9 x 42.6
47175-5	47175-0	47175-5	10	6.20	0.42	550	1	50	11	11 x 11 x 47.6	50 x 35.9 x 3.9	50.0 x 35.9 x 42.6
47176-3	47176-7	47176-6	10	6.20	0.42	550	1	50	11	11 x 11 x 47.6	50 x 35.9 x 3.9	50.0 x 35.9 x 42.6
47177-1	47177-4	47177-9	10	6.20	0.42	550	1	50	11	11 x 11 x 47.6	50 x 35.9 x 3.9	50.0 x 35.9 x 42.6

- Savings based on comparison to F32T8 electronic instant start systems
- Tested to B50 L70 requirement
- LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70)
- Photometric testing consistent with IES LM-79
- Product is not dimmable



© 2018 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting North America Corporation  
200 Franklin Square Drive, Somerset, NJ 08873  
Tel. 855-486-2216

Philips Lighting Canada Ltd.  
281 Hillmount Rd, Markham, ON, Canada L6C 2S3  
Tel. 800-668-9008