

PHILIPS

LED

CorePro Dimmable
MR16 Lamps



Affordable, high-quality lamps, **perfect for accent lighting**

The CorePro LED MR16 lamps are an affordable and ideal solution for spot and general retrofit lighting applications in the hospitality and retail industries.

These lamps have a new look and feel with a single optics lens, while providing a crisp and uniform beam.











Easy to experience

- Suitable for use in enclosed fixtures¹
- 25,000-hr life²
- “Perfect fit” mechanical design fits most MR16 fixtures

1. See Technical Application Guide for complete details. All lamps include an over temperature protection (OTP) feature that systematically reduces the lamp power and consequently its internal temperature should it be subjected to abnormally high ambient temperature conditions.

CorePro dimmable MR16 lamps

Ordering, electrical and technical data (subject to change without notice)

Product Number	12NC	Description	Watts	Beam Angle	Lumens	Volts	CRI	LED Lifetime	CCT	MC/CP ¹	Dim	Release date	
MR16 50W replacement lamps													
D 	533117	929001880704	7.3MR16/LED/827/F25/DIM 12V 10/1FB	7.3	25	515	12V	80	25,000	2700	CP	Yes	Nov 2018
D 	533125	929001880804	7.3MR16/LED/830/F25/DIM 12V 10/1FB	7.3	25	515	12V	80	25,000	3000	CP	Yes	Nov 2018
D 	533141	929001881004	7.3MR16/LED/827/F35/DIM 12V 10/1FB	7.3	35	515	12V	80	25,000	2700	CP	Yes	Nov 2018
D 	533158	929001881104	7.3MR16/LED/830/F35/DIM 12V 10/1FB	7.3	35	515	12V	80	25,000	3000	CP	Yes	Nov 2018
MR16 75W replacement lamps													
D 	533513	929001881304	8.5MR16/LED/827/F25/DIM 12V 10/1FB	8.5	25	600	12V	80	25,000	2700	CP	Yes	Nov 2018
D 	533174	929001881404	8.5MR16/LED/830/F25/DIM 12V 10/1FB	8.5	25	620	12V	80	25,000	3000	CP	Yes	Nov 2018
D 	533521	929001881504	8.5MR16/LED/840/F25/DIM 12V 10/1FB	8.5	25	660	12V	80	25,000	4000	CP	Yes	Nov 2018
D 	533182	929001881604	8.5MR16/LED/827/F35/DIM 12V 10/1FB	8.5	35	600	12V	80	25,000	2700	CP	Yes	Nov 2018
D 	533190	929001881704	8.5MR16/LED/830/F35/DIM 12V 10/1FB	8.5	35	620	12V	80	25,000	3000	CP	Yes	Nov 2018
D 	533331	929001881804	8.5MR16/LED/840/F35/DIM 12V 10/1FB	8.5	35	660	12V	80	25,000	4000	CP	Yes	Nov 2018

1. MC/CP = MasterClass or CorePro product.

 Energy Star qualified.

D Damp location.



© 2019 Signify Holding. All rights reserved.
Signify reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Signify North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Signify Canada Ltd.
281 Hillmount Rd, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008