



**PHILIPS**

LED lamps

CorePro

**Affordable solutions**  
with **energy savings**  
for everyday applications

Philips **CorePro** product families

# Affordable LED lamps with **uncompromising quality**

## Philips **CorePro** product families

The CorePro line of LED lamps is designed to help you identify the right product within your budget. We deliver true value and retrofit solutions for every application. Now offering a wider portfolio of CorePro LED lamps, we can help you illuminate a space with the reliability of Philips quality.

**Philips CorePro – Flexibility, reliability and affordability at your fingertips.**



## Philips CorePro

For every job requiring efficiency, value and uncompromising quality, these LED lamps are perfect for basic lighting needs across a wide range of applications. The CorePro line of LEDs meet industry efficiency standards and minimize maintenance costs for quick payback.

### CorePro can provide the following:

- Up to 80% energy savings<sup>†</sup>
- More choices with our expanded portfolio
- Lifetime of 15,000+ hours<sup>\*</sup>
- Color rendering index (CRI) 80+

For more information about the Philips LED lamps portfolio, please visit our website at [www.usa.lighting.philips.com/products/ledlamps](http://www.usa.lighting.philips.com/products/ledlamps) or download our digital catalog [here](#).

# Contents



4

## LED tubes

- InstantFit **4**
- MainsFit **6**
- InstantFit PLED **7**



11

## LED spots

- PAR **11**
- MR16 **15**



17

## LED bulbs

- A-Shape **17**
- Reflectors **19**



20

## LED candle & deco

- Filament **20**
- Vintage **21**
- Decorative **22**

# CorePro linear LED

CorePro LED tubes offer a more affordable solution with a 50,000-hour lifetime<sup>1</sup> and a 5-year limited warranty. The glass housing fits many applications. CorePro LED tubes offer a simple retrofit replacement and low energy consumption with instant savings. They are perfect for standard applications that demand a quality, cost effective solution.

## CorePro InstantFit T8

Ordering, electrical and technical data (Subject to change without notice)



G13



Product Number	Model Number	Ordering Code	Volts	Bare Lamp Watts	Base	CRI	Color Temp.	Life	Lumens	DLC ID	Case Qty
CorePro InstantFit T8 4 FT			V	W			K	Hrs.	lm		
53046-9	9290018660	12T8/PRO/48-830/IF17/G10/1FB	120-277, 347	12	G13	82	3000	50,000	1700	PRRGSCTH	10
53047-7	9290018661	12T8/PRO/48-835/IF17/G10/1FB	120-277, 347	12	G13	82	3500	50,000	1700	P9ZCH9LL	10
53048-5	9290018662	12T8/PRO/48-840/IF18/G10/1FB	120-277, 347	12	G13	82	4000	50,000	1800	PIAVUPWL	10
53049-3	9290018663	12T8/PRO/48-850/IF18/G10/1FB	120-277, 347	12	G13	82	5000	50,000	1800	PSDP6ZG1	10
47009-6	9290013430A	14T8/PRO/48-830/IF20/G10/1FB	100-277, 347	14	G13	82	3000	50,000	2000	PTDUF2EB	10
47010-4	9290013431A	14T8/PRO/48-835/IF20/G10/1FB	100-277, 347	14	G13	82	3500	50,000	2000	PV2NCRIM	10
47011-2	9290013432A	14T8/PRO/48-840/IF21/G10/1FB	100-277, 347	14	G13	82	4000	50,000	2100	PUQ8ZEAH	10
47012-0	9290013433A	14T8/PRO/48-850/IF21/G10/1FB	100-277, 347	14	G13	82	5000	50,000	2100	P8HU6SVS	10
45656-6	9290013435	17T8 LED/48-4000 IF G 10/1	100-277, 347	17	G13	80	4000	36,000	2100	Not DLC	10
45657-4	9290013436	17T8 LED/48-5000 IF G 10/1	100-277, 347	17	G13	80	5000	36,000	2100	Not DLC	10

Shipping data (Subject to change without notice)

Product Number	SKU UPC	Case UPC	Case Qty	Case Weight	Case Cube	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions	Case Dimensions	Pallet Dimensions
CorePro InstantFit T8 4 FT				lbs	cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
53046-9	46677530464	50046677530469	10	6.68	0.72	650	50	13	1.1 x 1.1 x 47.8	49.1 x 7 x 3.6	51.2 x 40 x 47
53047-7	46677530471	50046677530476	10	6.68	0.72	650	50	13	1.1 x 1.1 x 47.8	49.1 x 7 x 3.6	51.2 x 40 x 47
53048-5	46677530488	50046677530483	10	6.68	0.72	650	50	13	1.1 x 1.1 x 47.8	49.1 x 7 x 3.6	51.2 x 40 x 47
53049-3	46677530495	50046677530490	10	6.68	0.72	650	50	13	1.1 x 1.1 x 47.8	49.1 x 7 x 3.6	51.2 x 40 x 47
47009-6	46677452407	50046677470093	10	6.68	0.72	650	50	13	1.1 x 1.1 x 47.8	49.1 x 7 x 3.6	51.2 x 40 x 47
47010-4	46677452759	50046677470109	10	6.68	0.72	650	50	13	1.1 x 1.1 x 47.8	49.1 x 7 x 3.6	51.2 x 40 x 47
47011-2	46677453251	50046677470116	10	6.68	0.72	650	50	13	1.1 x 1.1 x 47.8	49.1 x 7 x 3.6	51.2 x 40 x 47
47012-0	46677452483	50046677470123	10	6.68	0.72	650	50	13	1.1 x 1.1 x 47.8	49.1 x 7 x 3.6	51.2 x 40 x 47
45656-6	46677452285	50046677470079	10	6.64	0.79	550	50	11	1.1 x 1.1 x 47.8	49.5 x 7.1 x 3.9	50.6 x 39.4 x 48.3
45657-4	46677452414	50046677470086	10	6.64	0.79	550	50	11	1.1 x 1.1 x 47.8	49.5 x 7.1 x 3.9	50.6 x 39.4 x 48.3

## CorePro InstantFit T5

Ordering, electrical and technical data (Subject to change without notice)



G5



Product Number	Model Number	Ordering Code	Volts	Color Temp.	Base	CRI	Color Temp.	Life*	Lumens	DLC ID	Case Qty
<b>CorePro InstantFit T5 2FT</b>			<b>V</b>	<b>W</b>			<b>K</b>	<b>Hrs.</b>	<b>lm</b>		
47641-6	9290018231	8T5HE/24-830/IF10/G/DIM 10/1	40-60	8	G5	82	3000	50,000	1000	No DLC Category	10
47642-4	9290018232	8T5HE/24-835/IF10/G/DIM 10/1	40-60	8	G5	82	3500	50,000	1000	No DLC Category	10
47643-2	9290018233	8T5HE/24-840/IF10/G/DIM 10/1	40-60	8	G5	82	4000	50,000	1050	No DLC Category	10
47644-0	9290018234	8T5HE/24-850/IF10/G/DIM 10/1	40-60	8	G5	82	5000	50,000	1050	No DLC Category	10
<b>CorePro InstantFit T5 3FT</b>			<b>V</b>	<b>W</b>			<b>K</b>	<b>Hrs.</b>	<b>lm</b>		
47645-7	9290018235	11T5HE/36-830/IF14/G/DIM 10/1	50-80	11	G5	82	3000	50,000	1400	No DLC Category	10
47646-5	9290018236	11T5HE/36-835/IF14/G/DIM 10/1	50-80	11	G5	82	3500	50,000	1400	No DLC Category	10
47647-3	9290018237	11T5HE/36-840/IF15/G/DIM 10/1	50-80	11	G5	82	4000	50,000	1500	No DLC Category	10
47648-1	9290018238	11T5HE/36-850/IF15/G/DIM 10/1	50-80	11	G5	82	5000	50,000	1500	No DLC Category	10
<b>CorePro InstantFit T5 4FT</b>			<b>V</b>	<b>W</b>			<b>K</b>	<b>Hrs.</b>	<b>lm</b>		
47649-9	9290018239	14T5HE/48-830/IF20/G/DIM 10/1	70-105	14	G5	82	3000	50,000	2000	P10H91X1	10
47650-7	9290018240	14T5HE/48-835/IF20/G/DIM 10/1	70-105	14	G5	82	3500	50,000	2000	PX50DKZF	10
47651-5	9290018241	14T5HE/48-840/IF21/G/DIM 10/1	70-105	14	G5	82	4000	50,000	2100	P2RN9SKT	10
47652-3	9290018242	14T5HE/48-850/IF21/G/DIM 10/1	70-105	14	G5	82	5000	50,000	2100	PLAEVGFO	10

Shipping data (Subject to change without notice)

Product Number	SKU UPC	Case UPC	Case Qty	Case Weight	Case Cube	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions	Case Dimensions	Pallet Dimensions
<b>CorePro InstantFit T5 2FT</b>				<b>lbs</b>	<b>cu. Ft.</b>				<b>L x W x H (in.)</b>	<b>L x W x H (in.)</b>	<b>L x W x H (in.)</b>
47641-6	46677476410	50046677476415	10	3.11	0.33	1560	120	13	0.8 x 0.8 x 22.2	24.4 x 6.5 x 3.6	49.6 x 39.8 x 52.7
47642-4	46677476427	50046677476422	10	3.11	0.33	1560	120	13	0.8 x 0.8 x 22.2	24.4 x 6.5 x 3.6	49.6 x 39.8 x 52.7
47643-2	46677476434	50046677476439	10	3.11	0.33	1560	120	13	0.8 x 0.8 x 22.2	24.4 x 6.5 x 3.6	49.6 x 39.8 x 52.7
47644-0	46677476441	50046677476446	10	3.11	0.33	1560	120	13	0.8 x 0.8 x 22.2	24.4 x 6.5 x 3.6	49.6 x 39.8 x 52.7
<b>CorePro InstantFit T5 3FT</b>				<b>lbs</b>	<b>cu. Ft.</b>				<b>L x W x H (in.)</b>	<b>L x W x H (in.)</b>	<b>L x W x H (in.)</b>
47645-7	46677476458	50046677476453	10	4.27	0.51	910	70	13	0.8 x 0.8 x 34	36.3 x 6.5 x 3.7	47.2 x 39.4 x 53.7
47646-5	46677476465	50046677476460	10	4.27	0.51	910	70	13	0.8 x 0.8 x 34	36.3 x 6.5 x 3.7	47.2 x 39.4 x 53.7
47647-3	46677476472	50046677476477	10	4.27	0.51	910	70	13	0.8 x 0.8 x 34	36.3 x 6.5 x 3.7	47.2 x 39.4 x 53.7
47648-1	46677476489	50046677476484	10	4.27	0.51	910	70	13	0.8 x 0.8 x 34	36.3 x 6.5 x 3.7	47.2 x 39.4 x 53.7
<b>CorePro InstantFit T5 4FT</b>				<b>lbs</b>	<b>cu. Ft.</b>				<b>L x W x H (in.)</b>	<b>L x W x H (in.)</b>	<b>L x W x H (in.)</b>
47649-9	46677476496	50046677476491	10	5.01	0.67	780	60	13	45.8 x 0.8 x 0.8	48.1 x 6.5 x 3.7	48.9 x 40 x 48
47650-7	46677476502	50046677476507	10	5.01	0.67	780	60	13	45.8 x 0.8 x 0.8	48.1 x 6.5 x 3.7	48.9 x 40 x 48
47651-5	46677476519	50046677476514	10	5.01	0.67	780	60	13	45.8 x 0.8 x 0.8	48.1 x 6.5 x 3.7	48.9 x 40 x 48
47652-3	46677476526	50046677476521	10	5.01	0.67	780	60	13	45.8 x 0.8 x 0.8	48.1 x 6.5 x 3.7	48.9 x 40 x 48

Footnotes on page 23.

# MainsFit linear LED

Philips MainsFit (UL Type-B) T8 LED lamps use a double-ended design which significantly simplifies installation, saving time and costs. This ballast bypass product replaces either T8 or T12 lamps in fixtures containing shunted or non-shunted G13 (medium bi-pin) lamp holders for over 40% energy savings.

## CorePro MainsFit T8

40% energy savings when compared to what? We need that info or need to remove that comparison statement per Rob Farley.

Ordering, electrical and technical data (Subject to change without notice)



Product Number	Model Number	Ordering Code	Volts	Bare Lamp Watts	Base	CRI	Color Temp.	Life	Lumens	DLC ID	Case Qty
CorePro MainsFit T8 4 FT			V	W			K	Hrs.	lm		
53267-1	9290018768	12T8/PRO/48-830/BB17/G 10/1 FB	120-277	12	G13	80	3000	50,000	1700	PH0GP1G6	10
53268-9	9290018769	12T8/PRO/48-835/BB17/G 10/1 FB	120-277	12	G13	80	3500	50,000	1700	PS838QCF	10
53269-7	9290018770	12T8/PRO/48-840/BB18/G 10/1 FB	120-277	12	G13	80	4000	50,000	1800	PRLV3PP4	10
53270-5	9290018771	12T8/PRO/48-850/BB18/G 10/1 FB	120-277	12	G13	80	5000	50,000	1800	PYPHBOOB	10
47731-5	9290018454	14T8PRO/48-830/BB17/G 10/1 FB	120-277	14	G13	80	3000	50,000	1700	P3V56EPW	10
47732-3	9290018455	14T8PRO/48-835/BB17/G 10/1 FB	120-277	14	G13	80	3500	50,000	1700	PN3X1615	10
47733-1	9290018456	14T8PRO/48-840/BB18/G 10/1 FB	120-277	14	G13	80	4000	50,000	1800	PTLPG7HI	10
47734-9	9290018457	14T8PRO/48-850/BB18/G 10/1 FB	120-277	14	G13	80	5000	50,000	1800	PDSO3H88	10
47174-8	9290013631A	16.5T8PRO/48-830/BB20/G 10/1 FB	120-277	16.5	G13	80	3000	50,000	2000	PHYVFGFP	10
47175-5	9290013632A	16.5T8PRO/48-835/BB20/G 10/1 FB	120-277	16.5	G13	80	3500	50,000	2000	PQQVXTJP	10
47176-3	9290013633A	16.5T8PRO/48-840/BB21/G 10/1 FB	120-277	16.5	G13	80	4000	50,000	2100	P566AJFG	10
47177-1	9290013634A	16.5T8PRO/48-850/BB21/G 10/1 FB	120-277	16.5	G13	80	5000	50,000	2100	P67Y1JEP	10

Shipping data (Subject to change without notice)

Product Number	SKU UPC	Case UPC	Case Qty	Case Weight	Case Cube	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions	Case Dimensions	Pallet Dimensions
CorePro MainsFit T8 4 FT				lbs	cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
53267-1	46677532673	50046677532678	10	6.68	0.72	650	50	13	1.1 x 1.1 x 47.8	49.1 x 7 x 3.6	51.2 x 40 x 47
53268-9	46677532680	50046677532685	10	6.68	0.72	650	50	13	1.1 x 1.1 x 47.8	49.1 x 7 x 3.6	51.2 x 40 x 47
53269-7	46677532697	50046677532692	10	6.68	0.72	650	50	13	1.1 x 1.1 x 47.8	49.1 x 7 x 3.6	51.2 x 40 x 47
53270-5	46677532703	50046677532708	10	6.68	0.72	650	50	13	1.1 x 1.1 x 47.8	49.1 x 7 x 3.6	51.2 x 40 x 47
47731-5	46677477318	50046677477313	10	6.65	0.79	550	50	11	1.1 x 1.1 x 47.6	49.5 x 7.1 x 3.9	50 x 35.9 x 42.6
47732-3	46677477325	50046677477320	10	6.65	0.79	550	50	11	1.1 x 1.1 x 47.6	49.5 x 7.1 x 3.9	50 x 35.9 x 42.6
47733-1	46677477332	50046677477337	10	6.65	0.79	550	50	11	1.1 x 1.1 x 47.6	49.5 x 7.1 x 3.9	50 x 35.9 x 42.6
47734-9	46677477349	50046677477344	10	6.65	0.79	550	50	11	1.1 x 1.1 x 47.6	49.5 x 7.1 x 3.9	50 x 35.9 x 42.6
47174-8	46677471743	50046677471748	10	6.65	0.79	550	50	11	1.1 x 1.1 x 47.6	49.5 x 7.1 x 3.9	50 x 35.9 x 42.6
47175-5	46677471750	50046677471755	10	6.65	0.79	550	50	11	1.1 x 1.1 x 47.6	49.5 x 7.1 x 3.9	50 x 35.9 x 42.6
47176-3	46677471767	50046677471762	10	6.65	0.79	550	50	11	1.1 x 1.1 x 47.6	49.5 x 7.1 x 3.9	50 x 35.9 x 42.6
47177-1	46677471774	50046677471779	10	6.65	0.79	550	50	11	1.1 x 1.1 x 47.6	49.5 x 7.1 x 3.9	50 x 35.9 x 42.6

# CorePro PLED

Downlighting in general areas represents a major lighting cost for many buildings. CorePro LED pinned-based lamps are retrofit LED lamps that deliver incredible energy savings over a 50,000 hour lifetime\* and requires less maintenance and servicing. You can easily upgrade your existing fixtures and lower your downlighting costs with energy efficient LED lamps.

- Made of shatter-resistant plastic instead of glass
- Instant on
- No flickering or stroboscopic effects<sup>1</sup>
- Simple lamp-for-lamp replacement
- Energy savings of up to 60%<sup>2</sup>
- No mercury allowing for non-hazardous waste disposal
- Long LED lifetime: 50,000-hour rated life<sup>3</sup>
- Minimal color shift and stable flux output throughout lifetime
- No harmful UV radiation

## CorePro 4-pin PL-C/T

Ordering, electrical and technical data (Subject to change without notice)



Product Number	Model Number	Ordering Code	Pkg Qty	Volts	Color Temp.	Base	CRI	Color Temp.	Life*	Lumens	DLC ID
CorePro 4-pin PL-C/T				V	W			K	Hrs.	lm	
45836-4	9290013880	8.5PL-C/T LED/26H-2700 IF 4P1PK10/1	1	100-277, 347	8.5	GX24Q	82	2700	50,000	900	P227UKPG
45837-2	9290013881	8.5PL-C/T LED/26H-3000 IF 4P1PK10/1	1	100-277, 347	8.5	GX24Q	82	3000	50,000	900	PYHS75V7
45838-0	9290013882	8.5PL-C/T LED/26H-3500 IF 4P1PK10/1	1	100-277, 347	8.5	GX24Q	82	3500	50,000	900	P1956NU5
45839-8	9290013883	8.5PL-C/T LED/26H-4000 IF 4P1PK10/1	1	100-277, 347	8.5	GX24Q	82	4000	50,000	950	PUK7J4AA
45840-6	9290013884	10.5PL-C/T LED/26V-2700 IF 4P1PK10/1	1	100-277, 347	10.5	GX24Q	82	2700	50,000	1200	PW2GPMX6
45841-4	9290013885	10.5PL-C/T LED/26V-3000 IF 4P1PK10/1	1	100-277, 347	10.5	GX24Q	82	3000	50,000	1200	PGPTBMF9
45842-2	9290013886	10.5PL-C/T LED/26V-3500 IF 4P1PK10/1	1	100-277, 347	10.5	GX24Q	82	3500	50,000	1200	PZ1KKRNR
45843-0	9290013887	10.5PL-C/T LED/26V-4000 IF 4P1PK10/1	1	100-277, 347	10.5	GX24Q	82	4000	50,000	1300	PV2HQGWZ
47606-9	9290018197	12PLC/T LED/32H/827/IF/4P/DIM 1PK10/1	1	100-277, 347	12	G24/GX24	82	2700	50,000	1300	PIADVYIP
47607-7	9290018198	12PLC/T LED/32H/830/IF/4P/DIM 1PK10/1	1	100-277, 347	12	G24/GX24	82	3000	50,000	1350	PO8NB9Q1
47608-5	9290018199	12PLC/T LED/32H/835/IF/4P/DIM 1PK10/1	1	100-277, 347	12	G24/GX24	82	3500	50,000	1400	PZHf15J0
47609-3	9290018200	12PLC/T LED/32H/840/IF/4P/DIM 1PK10/1	1	100-277, 347	12	G24/GX24	82	4000	50,000	1450	PT5IC4ON
47610-1	9290018201	12PLC/T LED/32V/827/IF/4P/DIM 1PK10/1	1	100-277, 347	12	G24/GX24	82	2700	50,000	1350	PUS3MZTV
47611-9	9290018202	12PLC/T LED/32V/830/IF/4P/DIM 1PK10/1	1	100-277, 347	12	G24/GX24	82	3000	50,000	1400	PEIZQ8AS
47612-7	9290018203	12PLC/T LED/32V/835/IF/4P/DIM 1PK10/1	1	100-277, 347	12	G24/GX24	82	3500	50,000	1450	PJG8ADHK
47613-5	9290018204	12PLC/T LED/32V/840/IF/4P/DIM 1PK10/1	1	100-277, 347	12	G24/GX24	82	4000	50,000	1500	PFKH6AQA

## Shipping data (Subject to change without notice)

Product Number	SKU UPC	Case UPC	Case Qty	Case Weight	Case Cube	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions	Case Dimensions	Pallet Dimensions
CorePro 4-pin PL-C/T				lbs	cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
45836-4	46677458362	50046677472554	10	2.25	0.11	4140	690	6	1.3 x 1.3 x 6.4	8 x 3.4 x 7.2	48.6 x 40.6 x 49.2
45837-2	46677458379	50046677472769	10	2.25	0.11	4140	690	6	1.3 x 1.3 x 6.4	8 x 3.4 x 7.2	48.6 x 40.6 x 49.2
45838-0	46677458386	50046677472776	10	2.25	0.11	4140	690	6	1.3 x 1.3 x 6.4	8 x 3.4 x 7.2	48.6 x 40.6 x 49.2
45839-8	46677458393	50046677472783	10	2.25	0.11	4140	690	6	1.3 x 1.3 x 6.4	8 x 3.4 x 7.2	48.6 x 40.6 x 49.2
45840-6	46677458409	50046677472790	10	2.53	0.16	2960	370	8	2 x 2 x 4.9	11 x 4.5 x 5.7	48 x 40.8 x 51.5
45841-4	46677458416	50046677472806	10	2.53	0.16	2960	370	8	2 x 2 x 4.9	11 x 4.5 x 5.7	48 x 40.8 x 51.5
45842-2	46677458423	50046677472813	10	2.53	0.16	2960	370	8	2 x 2 x 4.9	11 x 4.5 x 5.7	48 x 40.8 x 51.5
45843-0	46677458430	50046677472820	10	2.53	0.16	2960	370	8	2 x 2 x 4.9	11 x 4.5 x 5.7	48 x 40.8 x 51.5
47606-9	46677476069	50046677476064	10	2.27	0.11	4140	690	6	1.3 x 1.3 x 6.4	8 x 3.4 x 7.2	47.2 x 39.4 x 49.2
47607-7	46677476076	50046677476071	10	2.27	0.11	4140	690	6	1.3 x 1.3 x 6.4	8 x 3.4 x 7.2	47.2 x 39.4 x 49.2
47608-5	46677476083	50046677476088	10	2.27	0.11	4140	690	6	1.3 x 1.3 x 6.4	8 x 3.4 x 7.2	47.2 x 39.4 x 49.2
47609-3	46677476090	50046677476095	10	2.27	0.11	4140	690	6	1.3 x 1.3 x 6.4	8 x 3.4 x 7.2	47.2 x 39.4 x 49.2
47610-1	46677476106	50046677476101	10	2.27	0.11	4140	690	6	2 x 2 x 4.9	8 x 3.4 x 7.2	47.2 x 39.4 x 49.2
47611-9	46677476113	50046677476118	10	2.27	0.11	4140	690	6	2 x 2 x 4.9	8 x 3.4 x 7.2	47.2 x 39.4 x 49.2
47612-7	46677476120	50046677476125	10	2.27	0.11	4140	690	6	2 x 2 x 4.9	8 x 3.4 x 7.2	47.2 x 39.4 x 49.2
47613-5	46677476137	50046677476132	10	2.27	0.11	4140	690	6	2 x 2 x 4.9	8 x 3.4 x 7.2	47.2 x 39.4 x 49.2

## CorePro 2-pin PL-S

Ordering, electrical and technical data (Subject to change without notice)



Product Number	Model Number	Ordering Code	Pkg Qty	Volts	Bare Lamp Watts	Base	CRI	Color Temp.	Life*	Lumens	DLC ID
CorePro 2-pin PL-S				V	W			K	Hrs.	lm	
52951-1	9290018628	5PL-S/LED/13H/827/IF5/P/2P 20/1	1	120-277	5	GX23	82	2700	50,000	580	No DLC Category
52956-0	9290018629	5PL-S/LED/13H/830/IF5/P/2P 20/1	1	120-277	5	GX23	82	3000	50,000	580	No DLC Category
52957-8	9290018630	5PL-S/LED/13H/835/IF5/P/2P 20/1	1	120-277	5	GX23	82	3500	50,000	580	No DLC Category
52958-6	9290018631	5PL-S/LED/13H/840/IF5/P/2P 20/1	1	120-277	5	GX23	82	4000	50,000	580	No DLC Category

## Shipping data (Subject to change without notice)

Product Number	SKU UPC	Case UPC	Case Qty	Case Weight	Case Cube	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions	Case Dimensions	Pallet Dimensions
CorePro 2-pin PL-S				lbs	cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
52951-1	46677529512	50046677529517	20	2.25	0.12	7920	1320	6	0.9 x 1.3 x 6.6	5.7 x 4.9 x 7.2	47.2 x 39.4 x 49.2
52956-0	46677529567	50046677529562	20	2.25	0.12	7920	1320	6	0.9 x 1.3 x 6.6	5.7 x 4.9 x 7.2	47.2 x 39.4 x 49.2
52957-8	46677529574	50046677529579	20	2.25	0.12	7920	1320	6	0.9 x 1.3 x 6.6	5.7 x 4.9 x 7.2	47.2 x 39.4 x 49.2
52958-6	46677529581	50046677529586	20	2.25	0.12	7920	1320	6	0.9 x 1.3 x 6.6	5.7 x 4.9 x 7.2	47.2 x 39.4 x 49.2



# CorePro PLED

## CorePro 2-pin PL-C

Ordering, electrical and technical data (Subject to change without notice)



Product Number	Model Number	Ordering Code	Pkg Qty	Volts	Bare Lamp Watts	Base	CRI	Color Temp.	Life	Lumens	DLC ID
CorePro 2-pin PL-C				V	W			K	Hrs.	lm	
53230-9	9290018845	5PL-C/LED/13H/827/IF5/P/2P 20/1	1	120-277	5	G24D	82	2700	50,000	550	No DLC Category
53231-7	9290018846	5PL-C/LED/13H/830/IF5/P/2P 20/1	1	120-277	5	G24D	82	3000	50,000	550	No DLC Category
53233-3	9290018847	5PL-C/LED/13H/835/IF5/P/2P 20/1	1	120-277	5	G24D	82	3500	50,000	580	No DLC Category
53234-1	9290018848	5PL-C/LED/13H/840/IF5/P/2P 20/1	1	120-277	5	G24D	82	4000	50,000	580	No DLC Category
53235-8	9290018849	5PL-C/LED/13V/827/IF5/P/2P 20/1	1	120-277	5	G24D	82	2700	50,000	550	No DLC Category
53236-6	9290018850	5PL-C/LED/13V/830/IF5/P/2P 20/1	1	120-277	5	G24D	82	3000	50,000	550	No DLC Category
53237-4	9290018851	5PL-C/LED/13V/835/IF5/P/2P 20/1	1	120-277	5	G24D	82	3500	50,000	580	No DLC Category
53238-2	9290018852	5PL-C/LED/13V/840/IF5/P/2P 20/1	1	120-277	5	G24D	82	4000	50,000	580	No DLC Category

Shipping data (Subject to change without notice)

Product Number	SKU UPC	Case UPC	Case Qty	Case Weight	Case Cube	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions	Case Dimensions	Pallet Dimensions
CorePro 2-pin PL-C				lbs	cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
53230-9	46677532307	50046677532302	20	3.18	0.195	4760	680	7	1.3 x 1.3 x 6.4	8.2 x 6.6 x 6.2	48.0 x 40.6 x 49.2
53231-7	46677532314	50046677532319	20	3.18	0.195	4760	680	7	1.3 x 1.3 x 6.4	8.2 x 6.6 x 6.2	48.0 x 40.6 x 49.2
53233-3	46677532338	50046677532333	20	3.18	0.195	4760	680	7	1.3 x 1.3 x 6.4	8.2 x 6.6 x 6.2	48.0 x 40.6 x 49.2
53234-1	46677532345	50046677532340	20	3.18	0.195	4760	680	7	1.3 x 1.3 x 6.4	8.2 x 6.6 x 6.2	48.0 x 40.6 x 49.2
53235-8	46677532352	50046677532357	20	2.97	0.285	3600	400	9	10.2 x 8.2 x 5.4	11.2 x 8.2 x 5.4	48.0 x 39.8 x 54.0
53236-6	46677532369	50046677532364	20	2.97	0.285	3600	400	9	10.2 x 8.2 x 5.4	11.2 x 8.2 x 5.4	48.0 x 39.8 x 54.0
53237-4	46677532376	50046677532371	20	2.97	0.285	3600	400	9	10.2 x 8.2 x 5.4	11.2 x 8.2 x 5.4	48.0 x 39.8 x 54.0
53238-2	46677532383	50046677532388	20	2.97	0.285	3600	400	9	10.2 x 8.2 x 5.4	11.2 x 8.2 x 5.4	48.0 x 39.8 x 54.0

Footnotes on page 23.

## CorePro 4-pin PL-C

Ordering, electrical and technical data (Subject to change without notice)



Product Number	Model Number	Ordering Code	Pkg Qty	Volts	Bare Lamp Watts	Base	CRI	Color Temp.	Life	Lumens	DLC ID
CorePro 4-pin PL-C				V	W			K	Hrs.	lm	
53239-0	9290018853	5.5PL-C/LED/13H/827/IF5/P/4P 20/1	1	120-277	5.5	G24Q	82	2700	50,000	550	No DLC Category
53240-8	9290018854	5.5PL-C/LED/13H/830/IF5/P/4P 20/1	1	120-277	5.5	G24Q	82	3000	50,000	550	No DLC Category
53241-6	9290018855	5.5PL-C/LED/13H/835/IF5/P/4P 20/1	1	120-277	5.5	G24Q	82	3500	50,000	580	No DLC Category
53242-4	9290018856	5.5PL-C/LED/13H/840/IF5/P/4P 20/1	1	120-277	5.5	G24Q	82	4000	50,000	580	No DLC Category
53243-2	9290018857	5.5PL-C/LED/13V/827/IF5/P/4P 20/1	1	120-277	5.5	G24Q	82	2700	50,000	550	No DLC Category
53244-0	9290018858	5.5PL-C/LED/13V/830/IF5/P/4P 20/1	1	120-277	5.5	G24Q	82	3000	50,000	550	No DLC Category
53245-7	9290018859	5.5PL-C/LED/13V/835/IF5/P/4P 20/1	1	120-277	5.5	G24Q	82	3500	50,000	580	No DLC Category
53246-5	9290018860	5.5PL-C/LED/13V/840/IF5/P/4P 20/1	1	120-277	5.5	G24Q	82	4000	50,000	580	No DLC Category

Shipping data (Subject to change without notice)

Product Number	SKU UPC	Case UPC	Case Qty	Case Weight	Case Cube	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions	Case Dimensions	Pallet Dimensions
CorePro 4-pin PL-C				lbs	cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
53239-0	46677532390	50046677532395	20	3.18	0.195	4760	680	7	1.3 x 1.3 x 6.4	8.2 x 6.6 x 6.2	48.0 x 40.6 x 49.2
53240-8	46677532406	50046677532401	20	3.18	0.195	4760	680	7	1.3 x 1.3 x 6.4	8.2 x 6.6 x 6.2	48.0 x 40.6 x 49.2
53241-6	46677532413	50046677532418	20	3.18	0.195	4760	680	7	1.3 x 1.3 x 6.4	8.2 x 6.6 x 6.2	48.0 x 40.6 x 49.2
53242-4	46677532420	50046677532425	20	3.18	0.195	4760	680	7	1.3 x 1.3 x 6.4	8.2 x 6.6 x 6.2	48.0 x 40.6 x 49.2
53243-2	46677532437	50046677532432	20	2.97	0.285	3600	400	9	10.2 x 8.2 x 5.4	11.2 x 8.2 x 5.4	48.0 x 39.8 x 54.0
53244-0	46677532444	50046677532449	20	2.97	0.285	3600	400	9	10.2 x 8.2 x 5.4	11.2 x 8.2 x 5.4	48.0 x 39.8 x 54.0
53245-7	46677532451	50046677532456	20	2.97	0.285	3600	400	9	10.2 x 8.2 x 5.4	11.2 x 8.2 x 5.4	48.0 x 39.8 x 54.0
53246-5	46677532468	50046677532463	20	2.97	0.285	3600	400	9	10.2 x 8.2 x 5.4	11.2 x 8.2 x 5.4	48.0 x 39.8 x 54.0

# CorePro LED spots

CorePro LED spots are a perfect fit for spot lighting and deliver halogen-like light. The PARs feature a glass housing and a beautifully crafted lens, matching the look and feel of a halogen lamp, while providing all of the LED benefits. Those who experience the light will be delighted by the uniform beam, natural color and absence of flicker or stroboscopic effects<sup>1</sup> throughout the full dimming range.

## CorePro LED PAR

Everything you value in LED PARs with a classic glass design for a familiar look.

Thanks to a single optic beam, the latest LED spots provide a clean beam that's free from shadows with beam angles from 15 and 40 degrees to suit every general lighting application.

- 25,000 hours\*
- Emit virtually no UV/IR light in the beam
- CRI 80
- 3-year limited warranty
- Contains no mercury

### CorePro glass PAR (1 of 2)

Ordering, electrical and technical data (Subject to change without notice)



E26



Product Number	Model Number	Ordering Code	Volts	Watts	Base	CRI	Life	MBCP	Beam Angle	Pkg Qty	Lumens	Life	Energy Cost	Color Temp
CorePro Glass PAR20			V	W			Hrs.				lm	Yrs.		K
47111-0	9290013165	7PAR20/LED/F25/830/E26/GL/DIM 120V 6/1	120	7	E26	80	25,000	1500	25°	10	500	22.8	\$0.84	3000
47114-4	9290013169	7PAR20/LED/F40/830/E26/GL/DIM 120V 6/1	120	7	E26	80	25,000	1000	40°	10	500	22.8	\$0.84	3000
47112-8	9290013167	7PAR20/LED/F25/840/E26/GL/DIM 120V 6/1	120	7	E26	80	25,000	1500	25°	10	500	22.8	\$0.84	4000
47115-1	9290013170	7PAR20/LED/F40/840/E26/GL/DIM 120V 6/1	120	7	E26	80	25,000	1000	40°	10	500	22.8	\$0.84	4000
47110-2	9290013172	7PAR20/LED/827-822/F25/GL/DIM 1PK 6/1	120	7	E26	80	25,000	1500	25°	10	500	22.8	\$0.84	2200-2700
47113-6	9290013173	7PAR20/LED/827-822/F40/GL/DIM 1PK 6/1	120	7	E26	80	25,000	800	40°	10	500	22.8	\$0.84	2200-2700
CorePro Glass PAR30S			V	W			Hrs.				lm	Yrs.		K
52976-8	9290013204	10PAR30S/LED/827/F25/DIM/ULW/120V 6/1FB	120	10	E26	80	25,000	3300	25°	1	800	22.8	\$1.20	2700
52977-6	9290013205	10PAR30S/LED/830/F25/DIM/ULW/120V 6/1FB	120	10	E26	80	25,000	3300	25°	1	850	22.8	\$1.20	3000
52978-4	9290013207	10PAR30S/LED/840/F25/DIM/ULW/120V 6/1FB	120	10	E26	80	25,000	3300	25°	1	850	22.8	\$1.20	4000
52979-2	9290013209	10PAR30S/LED/827/F40/DIM/ULW/120V 6/1FB	120	10	E26	80	25,000	1600	40°	1	800	22.8	\$1.20	2700
52980-0	9290013210	10PAR30S/LED/830/F40/DIM/ULW/120V 6/1FB	120	10	E26	80	25,000	1600	40°	1	850	22.8	\$1.20	3000
52981-8	9290013212	10PAR30S/LED/840/F40/DIM/ULW/120V 6/1FB	120	10	E26	80	25,000	1600	40°	1	850	22.8	\$1.20	4000
CorePro Glass PAR30L			V	W			Hrs.				lm	Yrs.		K
52970-1	9290013215	10PAR30L/LED/827/F25/DIM/ULW/120V 6/1FB	120	10	E26	80	25,000	3300	25°	1	800	22.8	\$1.20	2700
52971-9	9290013216	10PAR30L/LED/830/F25/DIM/ULW/120V 6/1FB	120	10	E26	80	25,000	3300	25°	1	850	22.8	\$1.20	3000
52972-7	9290013218	10PAR30L/LED/840/F25/DIM/ULW/120V 6/1FB	120	10	E26	80	25,000	3300	25°	1	850	22.8	\$1.20	4000
52973-5	9290013220	10PAR30L/LED/827/F40/DIM/ULW/120V 6/1FB	120	10	E26	80	25,000	1600	40°	1	800	22.8	\$1.20	2700
52974-3	9290013221	10PAR30L/LED/830/F40/DIM/ULW/120V 6/1FB	120	10	E26	80	25,000	1600	40°	1	850	22.8	\$1.20	3000
52975-0	9290013223	10PAR30L/LED/840/F40/DIM/ULW/120V 6/1FB	120	10	E26	80	25,000	1600	40°	1	850	22.8	\$1.20	4000

Footnotes on page 23.

## Shipping data (Subject to change without notice)

Product Number	SKU UPC	Case UPC	Case Qty	Case Weight	Case Cube	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions	Case Dimensions	Pallet Dimensions
<b>CorePro Glass PAR20</b>				lbs	cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
47111-0	46677471118	50046677471113	6	2.41	0.12	2244	204	11	2.8 x 2.8 x 3.5	8.6 x 5.8 x 4.2	47.2 x 39.4 x 52
47114-4	46677471149	50046677471144	6	2.41	0.12	2244	204	11	2.8 x 2.8 x 3.5	8.6 x 5.8 x 4.2	47.2 x 39.4 x 52
47112-8	46677471125	50046677471120	6	2.41	0.12	2244	204	11	2.8 x 2.8 x 3.5	8.6 x 5.8 x 4.2	47.2 x 39.4 x 52
47115-1	46677471156	50046677471151	6	2.41	0.12	2244	204	11	2.8 x 2.8 x 3.5	8.6 x 5.8 x 4.2	47.2 x 39.4 x 52
47110-2	46677471101	50046677471106	6	2.41	0.12	2244	204	11	2.8 x 2.8 x 3.5	8.6 x 5.8 x 4.2	47.2 x 39.4 x 52
47113-6	46677471132	50046677471137	6	2.41	0.12	2244	204	11	2.8 x 2.8 x 3.5	8.6 x 5.8 x 4.2	47.2 x 39.4 x 52
<b>CorePro Glass PAR30S</b>				lbs	cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
52976-8	46677529765	50046677529760	6	4.03	0.26	1056	96	11	4.1 x 4.1 x 3.6	12.5 x 8.4 x 4.3	47.2 x 39.4 x 52.6
52977-6	46677529772	50046677529777	6	4.03	0.26	1056	96	11	4.1 x 4.1 x 3.6	12.5 x 8.4 x 4.3	47.2 x 39.4 x 52.6
52978-4	46677529789	50046677529784	6	4.03	0.26	1056	96	11	4.1 x 4.1 x 3.6	12.5 x 8.4 x 4.3	47.2 x 39.4 x 52.6
52979-2	46677529796	50046677529791	6	4.03	0.26	1056	96	11	4.1 x 4.1 x 3.6	12.5 x 8.4 x 4.3	47.2 x 39.4 x 52.6
52980-0	46677529802	50046677529807	6	4.03	0.26	1056	96	11	4.1 x 4.1 x 3.6	12.5 x 8.4 x 4.3	47.2 x 39.4 x 52.6
52981-8	46677529819	50046677529814	6	4.03	0.26	1056	96	11	4.1 x 4.1 x 3.6	12.5 x 8.4 x 4.3	47.2 x 39.4 x 52.6
<b>CorePro Glass PAR30L</b>				lbs	cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
52970-1	46677529703	50046677529708	6	4.92	0.34	768	96	8	4.1 x 4.1 x 4.9	12.5 x 8.4 x 5.6	47.2 x 39.4 x 50.2
52971-9	46677529710	50046677529715	6	4.92	0.34	768	96	8	4.1 x 4.1 x 4.9	12.5 x 8.4 x 5.6	47.2 x 39.4 x 50.2
52972-7	46677529727	50046677529722	6	4.92	0.34	768	96	8	4.1 x 4.1 x 4.9	12.5 x 8.4 x 5.6	47.2 x 39.4 x 50.2
52973-5	46677529734	50046677529739	6	4.92	0.34	768	96	8	4.1 x 4.1 x 4.9	12.5 x 8.4 x 5.6	47.2 x 39.4 x 50.2
52974-3	46677529741	50046677529746	6	4.92	0.34	768	96	8	4.1 x 4.1 x 4.9	12.5 x 8.4 x 5.6	47.2 x 39.4 x 50.2
52975-0	46677529758	50046677529753	6	4.92	0.34	768	96	8	4.1 x 4.1 x 4.9	12.5 x 8.4 x 5.6	47.2 x 39.4 x 50.2

## CorePro Glass PAR CA Pre-build (1 of 2)

## Ordering, electrical and technical data (Subject to change without notice)



E26

Product Number	Model Number	Ordering Code	Volts	Watts	Base	CRI	Life	MBCP	Beam Angle	Pkg Qty	Lumens	Life*	Energy Cost	Color Temp
<b>CorePro Glass PAR30S CA Pre-build</b>			V	W			Hrs.				lm	Yrs.		K
53130-0	9290012949	12PAR30S/AMB/F25/830/DIM ULW CA 6/1	120	12	E26	80	25,000	3300	25°	1	850	22.8	\$1.45	3000
53131-9	9290012952	12PAR30S/AMB/F40/830/DIM ULW CA 6/1	120	12	E26	80	25,000	1500	40°	1	850	22.8	\$1.45	2700
<b>CorePro Glass PAR30L CA Pre-build</b>			V	W			Hrs.				lm	Yrs.		K
53128-5	9290012941	12PAR30L/AMB/F25/830/DIM ULW CA 6/1	120	12	E26	80	25,000	3300	25°	1	800	22.8	\$1.45	3000
53129-3	9290012945	12PAR30L/AMB/F40/830/DIM ULW CA 6/1	120	12	E26	80	25,000	1500	40°	1	850	22.8	\$1.45	3000

## Shipping data (Subject to change without notice)

Product Number	SKU UPC	Case UPC	Case Qty	Case Weight	Case Cube	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions	Case Dimensions	Pallet Dimensions
<b>CorePro Glass PAR30S CA Pre-build</b>				lbs	cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
53130-0	46677534424	50046677531305	6	4.03	0.26	1056	96	11	4.1 x 4.1 x 3.6	12.5 x 8.4 x 4.3	47.2 x 39.4 x 52.6
53131-9	46677534431	50046677531312	6	4.03	0.26	1056	96	11	4.1 x 4.1 x 3.6	12.5 x 8.4 x 4.3	47.2 x 39.4 x 52.6
<b>CorePro Glass PAR30L CA Pre-build</b>				lbs	cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
53128-5	46677534400	50046677531282	6	4.92	0.34	768	96	8	4.1 x 4.1 x 4.9	12.5 x 8.4 x 5.6	47.2 x 39.4 x 50.2
53129-3	46677534417	50046677531299	6	4.92	0.34	768	96	8	4.1 x 4.1 x 4.9	12.5 x 8.4 x 5.6	47.2 x 39.4 x 50.2

# CorePro LED PAR

## CorePro glass PAR (2 of 2)

Ordering, electrical and technical data (Subject to change without notice)



Product Number	Model Number	Ordering Code	Volts	Watts	Base	CRI	Life	MBCP	Beam Angle	Pkg Qty	Lumens	Life*	Energy Cost	Color Temp
CorePro Glass PAR38			V	W			Hrs.				lm	Yrs.		K
52950-3	9290013183	14PAR38/LED/827/F25/DIM/ULW/120V 6/1FB	120	14	E26	80	25,000	5700	25°	1	1150	22.8	\$1.69	2700
52952-9	9290013184	14PAR38/LED/830/F25/DIM/ULW/120V FB 6/1	120	14	E26	80	25,000	6000	25°	1	1200	22.8	\$1.69	3000
47467-6	9290013185	14PAR38/LED/835/F25/GL/DIM FB 1PK 6/1	120	14	E26	80	25,000	5700	25°	1	1200	22.8	\$1.69	3500
52953-7	9290013186	14PAR38/LED/840/F25/DIM/ULW/120V 6/1FB	120	14	E26	80	25,000	6000	25°	1	1200	22.8	\$1.69	4000
52954-5	9290013187	14PAR38/LED/850/F25/DIM/ULW/120V 6/1FB	120	14	E26	80	25,000	6000	25°	1	1200	22.8	\$1.69	5000
52955-2	9290013188	14PAR38/LED/827/F40/DIM/ULW/120V 6/1FB	120	14	E26	80	25,000	2450	40°	1	1150	22.8	\$1.69	2700
52959-4	9290013189	14PAR38/LED/830/F40/DIM/ULW/120V 6/1FB	120	14	E26	80	25,000	2500	40°	1	1200	22.8	\$1.69	3000
47468-4	9290013190	14PAR38/LED/835/F40/GL/DIM FB 1PK 6/1	120	14	E26	80	25,000	2370	40°	1	1200	22.8	\$1.69	3500
52960-2	9290013191	14PAR38/LED/840/F40/DIM/ULW/120V 6/1FB	120	14	E26	80	25,000	2500	40°	1	1200	22.8	\$1.69	4000
52961-0	9290013192	14PAR38/LED/850/F40/DIM/ULW/120V 6/1FB	120	14	E26	80	25,000	2500	40°	1	1200	22.8	\$1.69	5000
52962-8	9290013194	12PAR38/LED/827/F25/DIM/ULW/120V 6/1FB	120	12	E26	80	25,000	4100	25°	1	850	22.8	\$1.45	2700
52963-6	9290013195	12PAR38/LED/830/F25/DIM/ULW/120V 6/1FB	120	12	E26	80	25,000	4100	25°	1	900	22.8	\$1.45	3000
47469-2	9290013196	12PAR38/LED/835/F25/GL/DIM FB 1PK 6/1	120	12	E26	80	25,000	4000	25°	1	900	22.8	\$1.45	3500
52964-4	9290013197	12PAR38/LED/840/F25/DIM/ULW/120V 6/1FB	120	12	E26	80	25,000	4100	25°	1	900	22.8	\$1.45	4000
52965-1	9290013198	12PAR38/LED/850/F25/DIM/ULW/120V 6/1FB	120	12	E26	80	25,000	4100	25°	1	900	22.8	\$1.45	5000
52966-9	9290013199	12PAR38/LED/827/F40/DIM/ULW/120V 6/1FB	120	12	E26	80	25,000	1800	40°	1	850	22.8	\$1.45	2700
52967-7	9290013200	12PAR38/LED/830/F40/DIM/ULW/120V 6/1FB	120	12	E26	80	25,000	1900	40°	1	900	22.8	\$1.45	3000
47470-0	9290013201	12PAR38/LED/835/F40/GL/DIM FB 1PK 6/1	120	12	E26	80	25,000	1640	40°	1	900	22.8	\$1.45	3500
52968-5	9290013202	12PAR38/LED/840/F40/DIM/ULW/120V 6/1FB	120	12	E26	80	25,000	1900	40°	1	900	22.8	\$1.45	4000
52969-3	9290013203	12PAR38/LED/850/F40/DIM/ULW/120V 6/1FB	120	12	E26	80	25,000	1900	40°	1	900	22.8	\$1.45	5000

## CorePro Glass PAR CA Pre-build (2 of 2)

Ordering, electrical and technical data (Subject to change without notice)



Product Number	Model Number	Ordering Code	Volts	Watts	Base	CRI	Life	MBCP	Beam Angle	Pkg Qty	Lumens	Life*	Energy Cost	Color Temp
CorePro Glass PAR30S CA Pre-build			V	W			Hrs.				lm	Yrs.		K
53125-0	9290012912	16PAR38/AMB/F25/827/DIM ULW CA 6/1	120	16	E26	80	25,000	6000	25°	1	1200	22.8	\$1.93	2700
53120-0	9290012913	16PAR38/AMB/F25/830/DIM ULW CA 6/1	120	16	E26	80	25,000	6000	25°	1	1200	22.8	\$1.93	3000
53127-7	9290012914	16PAR38/AMB/F25/840/DIM ULW CA	120	16	E26	80	25,000	6000	25°	1	1200	22.8	\$1.93	4000
53124-4	9290012916	16PAR38/AMB/F40/827/DIM ULW CA 6/1	120	16	E26	80	25,000	2500	40°	1	1200	22.8	\$1.93	2700
53122-8	9290012917	16PAR38/AMB/F40/830/DIM ULW CA 6/1	120	16	E26	80	25,000	2500	40°	1	1200	22.8	\$1.93	3000
53126-9	9290012920	13.5PAR38/AMB/F25/827/DIM ULW CA 6/1	120	13.5	E26	80	25,000	4100	25°	1	950	22.8	\$1.63	2700
53121-0	9290012921	13.5PAR38/AMB/F25/830/DIM ULW CA 6/1	120	13.5	E26	80	25,000	4100	25°	1	950	22.8	\$1.63	3000
53429-7	9290012924	13.5PAR38/AMB/F40/827/DIM ULW CA 6/1	120	13.5	E26	80	25,000	1700	40°	1	950	22.8	\$1.63	2700
53123-6	9290012925	13.5PAR38/AMB/F40/830/DIM ULW CA 6/1	120	13.5	E26	80	25,000	1700	40°	1	950	22.8	\$1.63	3000

Footnotes on page 23.

## Shipping data (Subject to change without notice)

Product Number	SKU UPC	Case UPC	Case Qty	Case Weight	Case Cube	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions	Case Dimensions	Pallet Dimensions
CorePro Glass PAR38				lbs	cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
52950-3	46677529505	50046677529500	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
52952-9	46677529529	50046677529524	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
47467-6	46677474676	50046677474671	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
52953-7	46677529536	50046677529531	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
52954-5	46677529543	50046677529548	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
52955-2	46677529550	50046677529555	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
52959-4	46677529598	50046677529593	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
47468-4	46677474683	50046677474688	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
52960-2	46677529604	50046677529609	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
52961-0	46677529611	50046677529616	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
52962-8	46677529628	50046677529623	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
52963-6	46677529635	50046677529630	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
47469-2	46677474690	50046677474695	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
52964-4	46677529642	50046677529647	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
52965-1	46677529659	50046677529654	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
52966-9	46677529666	50046677529661	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
52967-7	46677529673	50046677529678	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
47470-0	46677474706	50046677474701	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
52968-5	46677529680	50046677529685	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
52969-3	46677529697	50046677529692	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54


## Shipping data (Subject to change without notice)

Product Number	SKU UPC	Case UPC	Case Qty	Case Weight	Case Cube	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions	Case Dimensions	Pallet Dimensions
CorePro Glass PAR30S CA Pre-build				lbs	cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
53125-0	46677531041	50046677531251	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
53120-0	46677531058	50046677531206	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
53127-7	46677479923	50046677531275	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
53124-4	46677479817	50046677531244	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
53122-8	46677534356	50046677531220	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
53126-9	46677534363	50046677531268	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
53121-0	46677534370	50046677531213	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
53429-7	46677534387	50046677534290	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54
53123-6	46677534394	50046677531237	6	6.51	0.72	384	48	8	4.9 x 4.9 x 5.4	17.2 x 12.1 x 6	47.2 x 39.4 x 54

# CorePro LED MR16 & GU10

## CorePro MR16 & GU10

Ordering, electrical and technical data (Subject to change without notice)



Product Number	Model Number	Ordering Code	Volts	Watts	Base	CRI	Color Temp.	Life	Lumens	MBCP	Beam Angle	Pkg Qty
<b>CorePro AirFlux MRX16 8.5W</b>			<b>V</b>	<b>W</b>			<b>K</b>	<b>Hrs.</b>	<b>lm</b>			
45750-7	9290011498A	8.5MRX16/LED/F25 2700 DIM AF 10/1	12	8.5	GU5.3	80	2700	40,000	635	3100	25°	10
45753-1	9290011501A	8.5MRX16/LED/F35 2700 DIM AF 10/1	12	8.5	GU5.3	80	2700	40,000	635	1650	35°	10
45751-5	9290011499A	8.5MRX16/LED/F25 3000 DIM AF 10/1	12	8.5	GU5.3	80	3000	40,000	660	3250	25°	10
53166-5	9290011502A	8.5MRX16/F35 3000 DIM AF 10/1 CA	12	8.5	GU5.3	80	3000	25,000	660	1700	35°	10
45754-9	9290011502A	8.5MRX16/LED/F35 3000 DIM AF 10/1	12	8.5	GU5.3	80	3000	40,000	660	1700	35°	10
45752-3	9290011500A	8.5MRX16/LED/F25 4000 DIM AF 10/1	12	8.5	GU5.3	80	4000	40,000	710	3350	25°	10
53167-3	9290011503A	8.5MRX16/F35 4000 DIM AF 10/1 CA	12	8.5	GU5.3	80	4000	40,000	710	1750	35°	10
45755-6	9290011503A	8.5MRX16/LED/F35 4000 DIM AF 10/1	12	8.5	GU5.3	80	4000	40,000	710	1750	35°	10
<b>CorePro AirFlux2 MR16 7W</b>			<b>V</b>	<b>W</b>			<b>K</b>	<b>Hrs.</b>	<b>lm</b>			
46152-5	9290011525	7MR16/LED/S15/827/DIM AF2 10/1	12	7	GU5.3	80	2700	40,000	500	3500	15°	10
53181-4	9290011528A	7MR16/LED/F25/827/DIM AF2 10/1 CA	12	7	GU5.3	80	2700	25,000	500	2400	25°	10
46155-8	9290011528	7MR16/LED/F25/827/DIM AF2 10/1	12	7	GU5.3	80	2700	40,000	500	2400	25°	10
46158-2	9290011531	7MR16/LED/F35/827/DIM AF2 10/1	12	7	GU5.3	80	2700	40,000	500	1320	35°	10
53186-3	9290011531	7MR16/LED/F35/827/DIM AF2 10/1 CA	12	7	GU5.3	80	2700	25,000	500	1320	35°	10
46153-3	9290011526	7MR16/LED/S15/830/DIM AF2 10/1	12	7	GU5.3	80	3000	40,000	500	3600	15°	10
46156-6	9290011529	7MR16/LED/F25/830/DIM AF2 10/1	12	7	GU5.3	80	3000	40,000	500	2500	25°	10
53185-5	9290011529A	7MR16/LED/F25/830/DIM AF2 10/1 CA	12	7	GU5.3	80	3000	25,000	500	2500	25°	10
46159-0	9290011532	7MR16/LED/F35/830/DIM AF2 10/1	12	7	GU5.3	80	3000	40,000	500	1350	35°	10
53187-1	9290011532A	7MR16/LED/F35/830/DIM AF2 10/1 CA	12	7	GU5.3	80	3000	25,000	500	1350	35°	10
46154-1	9290011527	7MR16/LED/S15/840/DIM AF2 10/1	12	7	GU5.3	80	4000	40,000	530	3800	15°	10
46157-4	9290011530	7MR16/LED/F25/840/DIM AF2 10/1	12	7	GU5.3	80	4000	40,000	530	2600	25°	10
46160-8	9290011533	7MR16/LED/F35/840/DIM AF2 10/1	12	7	GU5.3	80	4000	40,000	530	1400	35°	10
<b>CorePro Entry MR16 6.4W</b>			<b>V</b>	<b>W</b>			<b>K</b>	<b>Hrs.</b>	<b>lm</b>			
47033-6	9290011518	6.4MR16/F25/3000 DIM 12V 10/1	12	6.4	GU5.3	90	3000	40,000	430	1300	25°	10
47034-4	9290011522	6.4MR16/F35/3000 DIM 12V 10/1	12	6.4	GU5.3	90	3000	40,000	430	1300	35°	10
<b>CorePro Single Optic MR16 7.3W</b>			<b>V</b>	<b>W</b>			<b>K</b>	<b>Hrs.</b>	<b>lm</b>			
53311-7	9290018807	7.3MR16/LED/827/F25/DIM 12V 10/1FB	12	7.3	GU5.3	82	2700	25,000	515	2400	25°	10
53314-1	9290018810	7.3MR16/LED/827/F35/DIM 12V 10/1FB	12	7.3	GU5.3	82	2700	25,000	515	1350	35°	10
53312-5	9290018808	7.3MR16/LED/830/F25/DIM 12V 10/1FB	12	7.3	GU5.3	82	3000	25,000	515	2500	25°	10
53315-8	9290018811	7.3MR16/LED/830/F35/DIM 12V 10/1FB	12	7.3	GU5.3	82	3000	25,000	515	1350	35°	10
<b>CorePro Single Optic MR16 8.5W</b>			<b>V</b>	<b>W</b>			<b>K</b>	<b>Hrs.</b>	<b>lm</b>			
53351-3	9290018813	8.5MR16/LED/827/F25/DIM 12V 10/1FB	12	8.5	GU5.3	80	2700	25,000	621	2900	25°	10
53318-2	9290018816	8.5MR16/LED/827/F35/DIM 12V 10/1FB	12	8.5	GU5.3	80	2700	25,000	621	1500	35°	10
53317-4	9290018814	8.5MR16/LED/830/F25/DIM 12V 10/1FB	12	8.5	GU5.3	80	3000	25,000	621	2900	25°	10
53319-0	9290018817	8.5MR16/LED/830/F35/DIM 12V 10/1FB	12	8.5	GU5.3	80	3000	25,000	621	1500	35°	10
53352-1	9290018815	8.5MR16/LED/840/F25/DIM 12V 10/1FB	12	8.5	GU5.3	80	4000	25,000	621	2900	25°	10
53333-1	9290018818	8.5MR16/LED/840/F35/DIM 12V 10/1FB	12	8.5	GU5.3	80	4000	25,000	621	1500	35°	10
<b>CorePro Glass GU10</b>			<b>V</b>	<b>W</b>			<b>K</b>	<b>Hrs.</b>	<b>lm</b>			
47156-5	9290013582	4.5GU10/LED/822-27/F35/CLA/GL/DIM 10/1	120	4.5	GU10	80	2200-2700	25,000	380	700	35°	10
46814-0	9290013006	4.5GU10/LED/F35/830/DIM 10/1	120	4.5	GU10	80	3000	25,000	400	750	35°	10
45765-5	9290011565	5GU10/LED/827-22/F35/DIM 120V 10/1	120	5	GU10	80	2700-2200	25,000	400	700	35°	10

## Shipping data (Subject to change without notice)

Product Number	SKU UPC	Case UPC	Case Qty	Case Weight	Case Cube	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions	Case Dimensions	Pallet Dimensions
				lbs	cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
<b>CorePro AirFlux MRX16 8.5W</b>											
45750-7	46677457501	50046677457506	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
45753-1	46677457532	50046677457537	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
45751-5	46677457518	50046677457513	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
53166-5	46677473815	50046677531664	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
45754-9	46677457549	50046677457544	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
45752-3	46677457525	50046677457520	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
53167-3	46677530990	50046677531671	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
45755-6	46677457556	50046677457551	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
<b>CorePro AirFlux2 MR16 7W</b>											
				lbs	cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
46152-5	46677461522	50046677461527	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
53181-4	46677531003	50046677531817	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
46155-8	46677461553	50046677461558	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
46158-2	46677461584	50046677461589	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
53186-3	46677531027	50046677531862	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
46153-3	46677461539	50046677461534	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
46156-6	46677461560	50046677461565	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
53185-5	46677531010	50046677531855	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
46159-0	46677461591	50046677461596	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
53187-1	46677531034	50046677531879	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
46154-1	46677461546	50046677461541	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
46157-4	46677461577	50046677461572	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
46160-8	46677461607	50046677461602	10	1.34	0.06	6110	470	13	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 42.6
<b>CorePro Entry MR16 6.4W</b>											
				lbs	cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
47033-6	46677470333	50046677470338	10	1.34	0.06	8160	510	16	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 51.5
47034-4	46677470340	50046677470345	10	1.34	0.06	8160	510	16	1.8 x 1.8 x 2.2	9.3 x 4 x 2.8	47.2 x 39.4 x 51.5
<b>CorePro Single Optic MR16 7.3W</b>											
				lbs	cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
53311-7	46677533113	50046677533118	10	1.65	0.06	8160	510	1	1.8 x 1.8 x 2.0	9.3 x 4 x 2.8	47.2 x 39.4 x 51.1
53314-1	46677533144	50046677533149	10	1.65	0.06	8160	510	1	1.8 x 1.8 x 2.0	9.3 x 4 x 2.8	47.2 x 39.4 x 51.1
53312-5	46677533120	50046677533125	10	1.65	0.06	8160	510	1	1.8 x 1.8 x 2.0	9.3 x 4 x 2.8	47.2 x 39.4 x 51.1
53315-8	46677533151	50046677533156	10	1.65	0.06	8160	510	1	1.8 x 1.8 x 2.0	9.3 x 4 x 2.8	47.2 x 39.4 x 51.1
<b>CorePro Single Optic MR16 8.5W</b>											
				lbs	cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
53351-3	46677533519	50046677533514	10	1.65	0.06	8160	510	1	1.8 x 1.8 x 2.0	9.3 x 4 x 2.8	47.2 x 39.4 x 51.1
53318-2	46677533182	50046677533187	10	1.65	0.06	8160	510	1	1.8 x 1.8 x 2.0	9.3 x 4 x 2.8	47.2 x 39.4 x 51.1
53317-4	46677533175	50046677533170	10	1.65	0.06	8160	510	1	1.8 x 1.8 x 2.0	9.3 x 4 x 2.8	47.2 x 39.4 x 51.1
53319-0	46677533199	50046677533194	10	1.65	0.06	8160	510	1	1.8 x 1.8 x 2.0	9.3 x 4 x 2.8	47.2 x 39.4 x 51.1
53352-1	46677533526	50046677533521	10	1.65	0.06	8160	510	1	1.8 x 1.8 x 2.0	9.3 x 4 x 2.8	47.2 x 39.4 x 51.1
53333-1	46677533335	50046677533330	10	1.65	0.06	8160	510	1	1.8 x 1.8 x 2.0	9.3 x 4 x 2.8	47.2 x 39.4 x 51.1
<b>CorePro Glass GU10</b>											
				lbs	cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
47156-5	46677471569	50046677471564	10	1.52	0.08	5700	380	15	2 x 2 x 2.4	10.5 x 4.4 x 3	47.2 x 39.4 x 51.6
46814-0	46677468149	50046677468144	10	1.52	0.08	5700	380	15	2 x 2 x 2.4	10.5 x 4.4 x 3	48 x 40 x 51.6
45765-5	46677457655	50046677457650	10	1.52	0.08	4560	380	12	2 x 2 x 2.4	10.5 x 4.4 x 3	47.2 x 39.5 x 42.3



# CorePro A-shape LED bulbs

The affordable LED bulb solution.

CorePro LED bulbs are compatible with existing fixtures are designed for retrofit replacement of incandescent bulbs. They deliver energy savings and minimize maintenance cost. The CorePro LED bulbs are perfect for basic lighting needs. It provides the dependable performance you expect from LED at an affordable price.

## CorePro A-shape

Ordering, electrical and technical data (Subject to change without notice)



Product Number	Model Number	Ordering Code	Wattage	Watt Equiv	Volts	Lamp Type	Base	CRI	Life'	Finish	Lumens	LED Lifetime	Energy Cost	Color Temp.
			W		V				Hrs.		lm	Yrs.		K
<b>CorePro A19</b>														
47072-4	9290013153	4.5A19/LED/850/E26/FR/GL/ND FB 1PK 6/1	4.5	40	120	A19	E26	80	15,000	Frosted	450	13.7	\$0.54	5000
46071-7	9290012037	5A19/LED/850/ND 120V 6/1	5	40	120	A19	E26	80	10,950	Frosted	450	10.0	\$0.60	5000
46063-4	9290012036	5.5A19/LED/827/ND 120V 6/1	5.5	40	120	A19	E26	80	10,950	Frosted	450	10.0	\$0.66	2700
47073-2	9290013154	7A19/LED/827/E26/FR/GL/ND FB 1PK 6/1	7	60	120	A19	E26	80	15,000	Frosted	800	13.7	\$0.84	2700
47074-0	9290013155	7A19/LED/850/E26/FR/GL/ND/FB 1PK 6/1	7	60	120	A19	E26	80	15,000	Frosted	800	13.7	\$0.84	5000
53201-0	9290012615	8A19/LED/827/ND D2D 120V 6/1 CA	8	60	120	A19	E26	80	25,000	Frosted	800	22.8	\$0.96	2700
46232-5	9290012126	8.5A19/LED/827/CL/ND 120V 10/1	9	60	120	A19	E26	80	10,950	Clear	800	10.0	\$1.08	2700
46301-8	9290012194	9.5A19/LED/850 ND 120V 6/1	9.5	60	120	A19	E26	80	10,950	Frosted	1000	10.0	\$1.14	5000
46298-5	9290012193	10.5A19/LED/827 ND 120V 6/1	10.5	60	120	A19	E26	80	10,950	Frosted	1000	10.0	\$1.26	2700
45568-3	9290011349	14.5A19/LED/827 ND 120V 6/1	14.5	100	120	A19	E26	80	10,950	Frosted	1500	10.0	\$1.75	2700
<b>CorePro A30</b>														
47928-7	9290018547	20A30/LED/865/P/E26/ND 4/1FB	20	160 GLS 40 CFL	120	A30	E26	80	25,000	Frosted	2300	22.8	\$2.41	6500
<b>CorePro A35</b>														
47929-5	9290018548	24A35/LED/865/P/E26E39/ND 4/1FB	24	200 GLS 50 CFL	120	A35	E26	80	25,000	Frosted	3000	22.8	\$2.89	6500
<b>CorePro A40</b>														
47930-3	9290018549	42A40/LED/865/P/E26E39/ND 4/1FB	42	300 GLS 85 CFL	120	A40	E26	80	25,000	Frosted	5000	22.8	\$5.06	6500

## Shipping data (Subject to change without notice)

Product Number	SKU UPC	Case UPC	Case Qty	Case Weight	Case Cube	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions	Case Dimensions	Pallet Dimensions
<b>CorePro A19</b>					cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
47072-4	46677470722	50046677470727	6	0.92	0.15	1872	234	8	2.6 x 2.6 x 4.7	8.3 x 5.6 x 5.4	47.2 x 39.4 x 49
46071-7	46677460716	50046677460711	6	1.14	0.12	1764	252	7	2.4 x 2.4 x 4.4	7.8 x 5.4 x 5.1	47.2 x 39.4 x 41.5
46063-4	46677460631	50046677460636	6	1.14	0.12	1764	252	7	2.4 x 2.4 x 4.4	7.8 x 5.4 x 5.1	47.2 x 39.4 x 41.5
47073-2	46677470739	50046677470734	6	0.92	0.15	1872	234	8	2.6 x 2.6 x 4.7	8.3 x 5.6 x 5.4	47.2 x 39.4 x 49
47074-0	46677470746	50046677470741	6	0.92	0.15	1872	234	8	2.6 x 2.6 x 4.7	8.3 x 5.6 x 5.4	47.2 x 39.4 x 49
53201-0	46677530501	50046677532012	6	1.14	0.12	2376	264	9	2.4 x 2.4 x 4.4	7.8 x 5.4 x 5.1	47.2 x 39.4 x 52.2
46232-5	46677462321	50046677462326	10	2.47	0.21	1820	260	7	2.4 x 2.4 x 4.7	12.8 x 5.3 x 5.4	47.2 x 39.4 x 37.8
46301-8	46677463014	50046677463019	6	1.14	0.12	1764	252	7	2.4 x 2.4 x 4.4	7.8 x 5.4 x 5.1	47.2 x 39.4 x 41.5
46298-5	46677462987	50046677462982	6	1.14	0.12	1764	252	7	2.4 x 2.4 x 4.4	7.8 x 5.4 x 5.1	47.2 x 39.4 x 41.5
45568-3	46677455682	50046677455687	6	1.14	0.12	2376	264	9	2.4 x 2.4 x 4.4	7.8 x 5.4 x 5.1	48.6 x 40 x 46.5
<b>CorePro A30</b>					cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
47928-7	46677479282	50046677479287	4	3.09	0.43	320	80	4	4.1 x 4.1 x 9.1	8.6 x 8.6 x 10	47.2 x 39.4 x 46.1
<b>CorePro A35</b>					cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
47929-5	46677479299	50046677479294	4	3.5	0.58	256	64	4	4.6 x 4.6 x 9.8	9.7 x 9.7 x 10.6	47.2 x 39.4 x 48.3
<b>CorePro A40</b>					cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
47930-3	46677479305	50046677479300	4	7.71	0.98	144	48	3	5.3 x 5.3 x 12.1	11.3 x 11.3 x 13.2	47.2 x 39.4 x 45.8

# CorePro LED reflectors

An affordable choice for recessed and general lighting applications.

- 15,000 hour lifetime

## CorePro LED reflectors

Ordering, electrical and technical data (Subject to change without notice)



Product Number	Model Number	Ordering Code	Wattage	Watt Equiv	Bulb	Volts	Base	CRI	Life	Lumens	LED Lifetime	Energy Cost	Color Temp.
CorePro BR30			W			V			Hrs.	lm	Yrs.		K
47384-3	929001391666	11BR30/827/DIM	11	65	BR30	120	E26	80	15,000	650	13.7	\$1.32	2700

Shipping data (Subject to change without notice)

Product Number	SKU UPC	Case UPC	Case Qty	Case Weight	Case Cube	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions	Case Dimensions	Pallet Dimensions
CorePro BR30					cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
47384-3	46677473846	50056677473841	6	0.32	0.29	960	120	8	3.6 x 3.6 x 5.2	11.2 x 7.6 x 5.8	47.2 x 39.4 x 52.8

# CorePro LED filament

## CorePro LED filament

Ordering, electrical and technical data (Subject to change without notice)



E12

E26



Product Number	Model Number	Ordering Code	Wattage	Volts	Base	CRI	Life'	Lumens	LED Lifetime	Energy Cost	Color Temp.
CorePro Filament B11			W	V			Hrs.	lm	Yrs.		K
47075-7	9290013148	2.5B11/LED/827/E12/CL-A/DIM 1PK 6/1	2.5	120	E12	80	15,000	300	13.7	\$0.26	2700
47076-5	9290013149	4B11/LED/827/E12/CL-A/DIM 1PK 6/1	4	120	E12	80	15,000	450	13.7	\$0.41	5000
47078-1	9290013151	4B11/LED/827/E26/CL-A/DIM 1PK 6/1	4	120	E26	80	15,000	800	13.7	\$0.41	2700
CorePro Filament BA11			W	V			Hrs.	lm	Yrs.		K
47077-3	9290013150	4BA11/LED/827/E12/CL-A/DIM 1PK 6/1	4	120	E12	80	15,000	800	13.7	\$0.41	5000

Shipping data (Subject to change without notice)

Product Number	SKU UPC	Case UPC	Case Qty	Case Weight	Case Cube	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions	Case Dimensions	Pallet Dimensions
CorePro Filament B11					cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
47075-7	46677470753	50046677470758	6	0.44	0.05	5724	636	9	1.6 x 1.6 x 4.3	5 x 3.5 x 5	47.2 x 39.4 x 51.2
47076-5	46677470760	50046677470765	6	0.92	0.15	1872	234	8	2.6 x 2.6 x 4.7	8.3 x 5.6 x 5.4	47.2 x 39.4 x 49
47078-1	46677470784	50046677470789	6	0.92	0.15	1872	234	8	2.6 x 2.6 x 4.7	8.3 x 5.6 x 5.4	47.2 x 39.4 x 49
CorePro Filament BA11					cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
47077-3	46677470777	50046677470772	6	0.92	0.15	1872	234	8	2.6 x 2.6 x 4.7	8.3 x 5.6 x 5.4	47.2 x 39.4 x 49

# CorePro LED vintage

## CorePro LED vintage

Ordering, electrical and technical data (Subject to change without notice)



Product Number	Model Number	Ordering Code	Wattage	Volts	Base	CRI	Life	Lumens	LED Lifetime	Energy Cost	Color Temp.
CorePro Vintage A15			W	V			Hrs.	lm	Yrs.		K
4 6111-1	9290012096	2A15/LED/822/FCL/ND 120V 6/1	2	120	E12	80	15,000	300	13.7	\$0.20	2200
CorePro Vintage A19			W	V			Hrs.	lm	Yrs.		K
46166-5	9290012101	4.5A19b/LEDFilament/820/CL-A/DIM 120V	4.5	120	E26	80	15,000	220	13.7	\$0.46	2200
CorePro Vintage BA11			W	V			Hrs.	lm	Yrs.		K
46652-4	9290012687	4.5BA11/LEDFilament/820/CL-A/DIM 120V	4.5	120	E26	80	15,000	350	13.7	\$0.46	2200
CorePro Vintage G16.5			W	V			Hrs.	lm	Yrs.		K
47582-2	9290013355	4.5G16.5/VIN/822/E12/GL_CL/DIM FB IPK6/1	4.5	120	E26	80	15,000	400	13.7	\$0.46	2200
CorePro Vintage ST19			W	V			Hrs.	lm	Yrs.		K
46167-3	9290012102	5.5ST19/LEDFilament/820/CL-A/DIM 120V	5.5	120	E12	80	15,000	350	13.7	\$0.56	2000

Shipping data (Subject to change without notice)

Product Number	SKU UPC	Case UPC	Case Qty	Case Weight	Case Cube	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions	Case Dimensions	Pallet Dimensions
CorePro Vintage A15					cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
4 6111-1	4 66774 61119	50046677461114	6	0.51	0.08	3840	384	10	2 x 2 x 3.9	6.5 x 4.5 x 4.5	47.2 x 39.4 x 51
CorePro Vintage A19					cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
46166-5	4 66774 61669	50046677461664	10	0.89	0.16	1680	210	8	2 x 2 x 3.8	11.7 x 5.7 x 4.2	47.2 x 39.4 x 42.9
CorePro Vintage BA11					cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
46652-4	4 66774 66527	50046677466522	12	1.93	0.28	1512	216	7	2.6 x 2.6 x 4.7	10.9 x 8.3 x 5.4	47.2 x 39.4 x 43.5
CorePro Vintage G16.5					cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
47582-2	4 66774 70685	50046677475821	6	1.43	0.2	1020	204	5	2.6 x 2.6 x 4.7	8.8 x 6 x 6.7	47.2 x 39.4 x 39
CorePro Vintage ST19					cu. Ft.				L x W x H (in.)	L x W x H (in.)	L x W x H (in.)
46167-3	4 66774 61676	50046677461671	6	0.67	0.07	3840	480	8	1.8 x 1.8 x 5	5.8 x 4 x 5.5	47.2 x 39.4 x 50.4

# CorePro LED decorative

The CorePro LED luster is designed for retrofit replacement of incandescent lamps.

- Non-Dimmable
- Huge energy savings

## CorePro LED decorative

Ordering, electrical and technical data (Subject to change without notice)



Product Number	Model Number	Ordering Code	Wattage	Watt Equiv	Volts	Base	CRI	Lumens	LED Lifetime	Energy Cost	Color Temp.	Life	Finish	Dimming
<b>CorePro Clear Classic B11</b>			<b>W</b>		<b>V</b>			<b>lm</b>	<b>Yrs.</b>		<b>K</b>	<b>Hrs.</b>		
46187-1	9290012137	4.5B11/LED/827/E12/CL/DIM 1PK 10/1	4.5	40	120	E12	80	300	13.7	\$0.54	2700	15,000	Clear	Y
46193-9	9290012138	4.5B11/LED/827/E26/CL/DIM 1PK 10/1	4.5	40	120	E26	80	300	13.7	\$0.54	2700	15,000	Clear	Y
<b>CorePro G25</b>			<b>W</b>		<b>V</b>			<b>lm</b>	<b>Yrs.</b>		<b>K</b>	<b>Hrs.</b>		
46587-2	9290012693	4G25/LED/850/ND 120V 1PK 6/1	4	40	120	E26	80	350	13.7	\$0.48	5000	15,000	Clear	N
46586-4	9290012674	4.5G25/LED/827/ND 120V 1PK 6/1	4.5	40	120	E26	80	350	13.7	\$0.54	2700	15,000	Clear	N
46589-8	9290012694	5G25/LED/850/ND 120V 1PK 6/1	5	60	120	E26	80	500	13.7	\$0.60	5000	15,000	Clear	N
46588-0	9290012675	6.5G25/LED/827/ND 120V 1PK 6/1	6.5	60	120	E26	80	500	13.7	\$0.78	2700	15,000	Clear	N

Shipping data (Subject to change without notice)

Product Number	SKU UPC	Case UPC	Case Qty	Case Weight	Case Cube	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions	Case Dimensions	Pallet Dimensions
					<b>cu. Ft.</b>				<b>L x W x H (in.)</b>	<b>L x W x H (in.)</b>	<b>L x W x H (in.)</b>
46187-1	46677461874	50046677461879	10	1.24	0.07	6570	730	9	1.4 x 1.4 x 4.4	7.6 x 3.3 x 5	47.2 x 39.4 x 51.7
46193-9	46677461935	50046677461930	10	1.24	0.07	6570	730	9	1.4 x 1.4 x 4.4	7.6 x 3.3 x 5	47.2 x 39.4 x 51.7
					<b>cu. Ft.</b>				<b>L x W x H (in.)</b>	<b>L x W x H (in.)</b>	<b>L x W x H (in.)</b>
46587-2	46677465872	50046677465877	6	1.81	0.18	1380	138	10	3.3 x 3.3 x 3.8	10.3 x 6.9 x 4.4	47.2 x 39.4 x 50.6
46586-4	46677465865	50046677465860	6	1.81	0.18	1380	138	10	3.3 x 3.3 x 3.8	10.3 x 6.9 x 4.4	47.2 x 39.4 x 50.6
46589-8	46677465896	50046677465891	6	1.81	0.18	1380	138	10	3.3 x 3.3 x 3.8	10.3 x 6.9 x 4.4	47.2 x 39.4 x 50.6
46588-0	46677465889	50046677465884	6	1.81	0.18	1380	138	10	3.3 x 3.3 x 3.8	10.3 x 6.9 x 4.4	47.2 x 39.4 x 50.6



*Footnotes:*

† Energy savings is calculated based on Philips LED 13W PAR38 when compared to a 100W Halogen PAR38. Energy savings may vary depending on LED lamp type.

\* LED Lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output. (B50, L70).

1  $P_{st}^{LM} < 1.0$  measured according to IEC 61547-1 and IEC 61000-4-15.

2 Savings based on comparison to F32T8 electronic instant start systems.

3 Based on the next leading competitor and their number of compatible ballasts.



© 2018 Signify Holding. All rights reserved. Signify reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

PLT-18109BR 10/18 [www.philips.com/lighting](http://www.philips.com/lighting)

Philips Lighting  
North America Corporation  
200 Franklin Square Drive  
Somerset, NJ 08873  
Tel. 855-486-2216

Philips Lighting Canada Ltd.  
281 Hillmount Rd,  
Markham, ON,  
Canada L6C 2S3  
Tel. 800-668-9008