

Model Number	VESA Mount Pattern	Bolt Size	Stand Screw Size x Qty
19PFL3504D/F7	100 x 100	M4 x 12mm	M4 x 12mm
19PFL3505D/F7	100 x 100	M4 x 12mm	(M4 x 12mm) x 4
19PFL4505D/F7	100 x 100	M4 x 12mm	(M4 x 10mm) x 2
22PFL3504D/F7	100 x 100	M4 x 12mm	M4 x 12mm
22PFL3505D/F7	100 x 100	M4 x 12mm	(M4 x 12mm) x 4
22PFL4505D/F7	100 x 100	M4 x 12mm	(M4 x 10mm) x 2
22PFL4507/F7	100 x 100	M4 x 12mm	(M4 x 14mm) x 2
22PFL4907/F7	100 x 100	M4 x 12mm	(M4 x 14mm) x 2
26PFL4507/F7	200 x 100	M4 x 12mm	(M4 x 14mm) x 3
26PFL4907/F7	200 x 100	M4 x 12mm	(M4 x 14mm) x 3
32PFL3504D/F7	200 x 200	M4 x 16mm	M4 x 20mm
32PFL3505D/F7	200 x 200	M4 x 16mm	(M4 x 20mm) x 3
32PFL3506/F7	200 x 200	M4 x 12mm	(M4 x 14mm) x 3
32PFL3514D/F7	200 x 200	M4 x 16mm	M4 x 20mm
32PFL3515D/F7	200 x 200	M4 x 16mm	(M4 x 20mm) x 3
32PFL4505D/F7	200 x 100	M4 x 16mm	(M4 x 10mm) x 4
32PFL4507/F7	200 x 100	M4 x 12mm	(M4 x 14mm) x 3
32PFL4907/F7	200 x 100	M4 x 12mm	(M4 x 14mm) x 3
32PFL6704D/F7	200 x 300	M6 x 10mm	
40PFL3505D/F7	400 x 200	M8 x 16mm	(M5 x 20mm) x 4
40PFL3705D/F7	400 x 200	M8 x 16mm	(M5 x 20mm) x 4
40PFL3706/F7	400 x 200	M8 x 40mm	(M5 x 20mm) x 4
40PFL3907/F7	400 x 200	M8 x 40mm	(M5 x 20mm) x 4
40PFL4706/F7	400 x 400	M6 x 25mm	(M4 x 14mm) x 4
40PFL4707/F7	400 x 300	M6 x 40mm	(M5 x 20mm) x 4
40PFL4907/F7	400 x 300	M6 x 40mm	(M5 x 20mm) x 4
40PFL5505D/F7	400 x 200	M8 x 16mm	(M5 x 20mm) x 4
40PFL5705D/F7	400 x 200	M8 x 16mm	(M5 x 20mm) x 4
40PFL5706/F7	400 x 200	M8 x 40mm	(M5 x 20mm) x 4
40PFL7505D/F7	400 x 400	M8 x 40mm w/ Spacer	(M4 x 10mm) x 4
40PFL7705D/F7	400 x 400	M8 x 40mm w/ Spacer	(M4 x 10mm) x 4
42PFL3704D/F7	200 x 200	M8 x 16mm	M5 x 20mm
42PFL5704D/F7	400 x 400	M8 x 16mm	

Model Number	VESA Mount Pattern	Bolt Size	Stand Screw Size x Qty
42PFL6704D/F7	400 x 400	M8 x 16mm	
42PFL7704D/F7	400 x 400	M8 x 16mm	
46PFL3505D/F7	400 x 400	M8 x 40mm w/ Spacer	(M5 x 20mm) x 4
46PFL3705D/F7	400 x 400	M8 x 16mm	(M5 x 20mm) x 4
46PFL3706/F7	400 x 400	M8 x 40mm	(M5 x 20mm) x 4
46PFL3907/F7	400 x 400	M8 x 40mm	(M5 x 20mm) x 4
46PFL4706/F7	400 x 400	M6 x 25mm	(M4 x 16mm) x 6
46PFL5505D/F7	400 x 400	M8 x 16mm	(M5 x 20mm) x 4
46PFL5705D/F7	400 x 400	M8 x 16mm	(M5 x 20mm) x 4
46PFL5706/F7	400 x 400	M8 x 40mm	(M5 x 20mm) x 4
46PFL7505D/F7	400 x 400	M8 x 40mm w/ Spacer	(M4 x 10mm) x 4
46PFL7705D/F7	400 x 400	M8 x 40mm w/ Spacer	(M4 x 10mm) x 4
47PFL3704D/F7	400 x 400	M8 x 16mm	M4 x 14mm
47PFL5704D/F7	400 x 400	M8 x 16mm	
47PFL6704D/F7	400 x 400	M8 x 16mm	
47PFL7704D/F7	400 x 400	M8 x 16mm	
50PFL3707/F7	400 x 400	M6 x 25mm	(M4 x 10mm) x 8
50PFL3807/F7	400 x 400	M6 x 26mm	(M4 x 10mm) x 8
52PFL3704D/F7	400 x 400	M8 x 16mm	
52PFL5704D/F7	400 x 400	M8 x 16mm	
52PFL7704D/F7	400 x 400	M8 x 16mm	
55PFL3907/F7	400 x 400	M8 x 40mm	(M5 x 20mm) x 4
55PFL4706/F7	400 x 400	M6 x 25mm	(M4 x 16mm) x 6
55PFL5505D/F7	400 x 400	M8 x 16mm	(M5 x 20mm) x 4
55PFL5705D/F7	400 x 400	M8 x 16mm	(M5 x 20mm) x 4
55PFL5706/F7	400 x 400	M8 x 40mm	(M5 x 20mm) x 4
55PFL7505D/F7	400 x 400	M8 x 40mm w/ Spacer	(M4 x 10mm) x 4
42PFL5907/F7	400 x 300	M6 x 18mm w/ Spacer	(M6 x 18mm) x 4
46PFL5907/F7	400 x 300	M6 x 18mm w/ Spacer	(M6 x 18mm) x 4
50PFL5907/F7	400 x 300	M6 x 18mm w/ Spacer	(M6 x 18mm) x 4
55PFL5907/F7	400 x 300	M6 x 18mm w/ Spacer	(M6 x 18mm) x 4
55PFL7705D/F7	400 x 400	M8 x 40mm w/ Spacer	(M4 x 10mm) x 4