

Find the right professional LED work light for the job

HDL10	Penlight Professional	PEN20	Penlight Premium	New RCH55	RCH6	RCH10	RCH19	RCH21S	New RCH25	RCH31UV	CBL10	CBH51	New PJH10	PJH20	MDLS CRI
Boost light 100 lm <10 h	Boost light 130 lm <11 h	Boost light 200 lm <2 h	Boost light 145 lm <6 h	Boost light 300 lm <1.5 h	Boost light 130 lm 2 h	Boost light 150 lm <5 h	Boost light 250 lm 4 h	Boost light 300 lm 3.5 h	Boost light 500 lm <3.5 h	Boost light 350 lm 3.5 h	Boost light 330 lm	Boost light 1200 lm 3 h	Boost light 1000 lm <3 h	Boost light 2300 lm 2 h	Boost light 1500 lm 1 h
Eco light 50 lm <10 h		Eco light 100 lm <4.5 h	Eco light	Dimmed light 30 lm <12 h	Eco light 70 lm 4 h		Eco light 120 lm 7 h	Eco light 120 lm 6 h	Dimmed light 50 lm <10 h	Eco light 150 lm <8 h		Eco light 500 lm 5.5 h	Dimmed light 100 lm <12 h	Eco light 1200 lm 4 h	Eco light 750 lm 2.5 h
Light angle/flexibility 50°	Light angle/flexibility 40°	Light angle/flexibility 80°	Light angle/flexibility 80°	Light angle/flexibility 120° 180°	Light angle/flexibility 90° 90°	Light angle/flexibility 120°	Light angle/flexibility 90° 180°	Light angle/flexibility 90° 90°	Light angle/flexibility 120° 180°	Light angle/flexibility 90° 90°	Light angle/flexibility 120°	Light angle/flexibility 120° 360°	Light angle/flexibility 90° 180°	Light angle/flexibility 90° 180°	Light angle/flexibility 360° 90°
Features 20 lm spot light	Features FindMe	Features FindMe	Features 120 lm FindMe	Features Dimming 120 lm	Features Headband FindMe		Features FindMe	Features Dimming 300 lm	Features UV light FindMe				Features Dimming	Features CRI 92 Matte filter	Features CRI 92 Matte filter
Fixture Headband	Fixture Clip	Fixture Clip Magnet	Fixture 80° clip Magnet	Fixture 360° hook Magnet	Fixture Clip Magnet	Fixture 360° hook Magnet	Fixture 360° hook Magnet	Fixture 360° hook Magnet	Fixture 360° hook Magnet	Fixture 360° hook Magnet	Fixture 360° hook	Fixture 1.1 - 1.8 m holder	Fixture Magnet		Fixture Clamp Magnet
Robustness IPX4	Robustness IP54	Robustness IP54 IK07	Robustness IP54 IK07	Robustness IP68 IK09	Robustness IP54 IK07	Robustness IP54 IK07	Robustness IP20 IK07	Robustness IP65 IK08	Robustness IP68 IK09	Robustness IP54 IK07	Robustness IP54 IK07	Robustness IP54 IK07	Robustness IP68 IK09	Robustness IP67 IK09	Robustness IP54 IK07
Grease resistance Garage proof	Grease resistance Garage proof	Grease resistance Garage proof	Grease resistance Garage proof	Grease resistance Garage proof	Grease resistance Garage proof	Grease resistance Garage proof	Grease resistance Garage proof	Grease resistance Garage proof	Grease resistance Garage proof	Grease resistance Garage proof	Grease resistance Garage proof	Grease resistance Garage proof	Grease resistance Garage proof	Grease resistance Garage proof	Grease resistance Garage proof
Power supply 3x AAA	Power supply 3x AAA	Power supply 2 h	Power supply 2 h	Power supply 2.5 h	Power supply 1 h	Power supply 4 h	Power supply 3 h	Power supply 2 h	Power supply 3.5 h	Power supply 2.5 h	Power supply 100-240 V 5 m	Power supply 100-240 V 5 m	Power supply 2 h	Power supply 100-240 V 5 m	Power supply 1.1 h 3.2 h
Order entry LPL29B1 GOC 39360631	Order entry LPL19B1 GOC 38819031	Order entry LPL42X1 GOC 39631731	Order entry LPL28RECHX1 GOC 39220394	Order entry LPL62X1 GOC 05163931	Order entry LPL38X1 GOC 39607231	Order entry LPL20X1 GOC 39060531	Order entry LPL46X1 GOC 39823631	Order entry LPL47X1 GOC 39841031	Order entry LPL63X1 GOC 05165331	Order entry LPL34UVX1 GOC 39419131	Order entry LPL35X1 GOC 39421431	Order entry LPL45X1 GOC 39732131	Order entry LPL64X1 GOC 05167731	Order entry LPL39X1 GOC 39609631	Order entry LPL403MODX1 GOC 39627066