

**PHILIPS**

Automotive lighting

# Safety you can see

Catalog 2019-2020

Countries outside of European Union





# Safety you can see!

Our advanced light engine technology has been on the forefront of automotive lighting for more than 100 years. As a **leading supplier** of lamps and lighting products to the automotive industry and aftermarket, we combine technical innovations with a genuine concern for **safety** and driving comfort. Our automotive lighting is today the choice of many consumers and major automobile manufacturers. Our mission is to introduce **innovative products** that constantly improve road safety and increase workshop productivity.

Our products are designed to perform efficiently and durably for continuous **customer satisfaction**. Many garages and workshops already appreciate our new range of professional LED work lights for their outstanding light output and robustness.

High-quality lighting really does make a difference.

**That's safety you can see!**



## Original equipment quality

We are committed to producing **best-in-class products** and services in the Original Equipment Manufacturer (OEM) market and automotive aftermarket. Our products are manufactured from **high-quality materials** and tested

to the highest specifications to maximize **safety** and driving **comfort** of our customers.

- We are the **choice** of major car manufacturers

- Our lighting equips **one in two cars** in Europe and one in three in the world
- Manufacturing processes that **exceed** current industry **specifications**

## Philips anti-UV-quartz glass for optimal lighting performance

**All Philips quartz-glass lamps also offer a UV shield to protect your modern plastic optics from harmful UV rays.**

- **More powerful light**

Quartz glass high resistance allows for increased pressure inside the lamp and thus generates more powerful light.

- **Better resistance**

Philips quartz glass lamps (filament at 2 800°C and glass up to 800°C) are capable of withstanding severe thermal shocks.

- **Optimal protection against ultraviolet rays**

All Philips quartz-glass lamps also offer a UV shield to protect your modern plastic optics from harmful UV rays.



# Table of content

## Introduction

2

Safety you can see

## Halogen

6

### 12V Car lighting

Vision	10
VisionPlus	10
X-tremeVision G-force	11
LongLife EcoVision	11
WhiteVision	12
WhiteVision ultra	12
CrystalVision	13
DiamondVision	13
RacingVision	15
Which lamp for which function?	16



### 24V Bus and truck lighting

MasterDuty	47
MasterLife	48
MasterDuty BlueVision	48
Which lamp for which function?	49



36

### Two-wheeler lighting

Vision moto	39
CityVision moto	39
X-tremeVision moto	40
CrystalVision ultra moto	40
Which lamp for which function?	41



## Kits

56

### for cars and trucks

12V spare kits	58
24V spare kits	60
Headlight restoration kit	61





## Xenon

# 62


### for cars and truck

Xenon Vision	65
Xenon X-tremeVision gen2	66
Xenon LongerLife	67
Xenon WhiteVision gen2	68
Our pro-active solution against Xenon lamp piracy	69

## Annexes

# 90

Lighting technology explained	90
Specimen packaging	92
Understanding Philips ordering codes	93
Bases technical illustrations	94
Product index	95



## LED retrofit

# 74

### for cars and trucks

Which LED lighting for which function?	78
Ultinon LED	80
X-tremeUltinon LED	80
CANbus LED adapter	81



# Halogen





# 12V car lighting



# Which car lamp do you need?




## Experience more light

Up to **30%** more vision\*



**Vision**  
★★★★★





Available in H1, H3, H4, H7, HB3, HB4, H11

Up to **60%** more vision\*



**VisionPlus**  
★★★★★





Available in H1, H4, H7

Up to **130%** brighter light\*



**X-tremeVision**  
★★★★★





Available in H1, H4, H7

New

Up to **130%** brighter light\*



**X-tremeVision G-force**  
★★★★★





Available in H1, H4, H7, H11, HB4\*\*\*

## Light that lasts

Lifetime up to **1500 hours\*\***



**LongLife EcoVision**  
★★★★★



Available in H1, H3, H4, H7, H11, H18, H19

Images for illustration purposes only.

\* Compared to the minimum legal standard

\*\* Lifetime differs per type, indication for H7 only

\*\*\* 10 G applies to H4 and H7

\*\*\*\* Non-ECE homologated, for o-road only



# Enjoy your passion

**Intense white**  
xenon effect



**WhiteVision**  
★★★★★



Beam performance



Light color



Lifetime\*\*



Available in H1, H3, H4, H7, H8, H11, HB3, HB4

Up to **150%**  
brighter light\*



**RacingVision**  
★★★★★



Beam performance



Light color



Lifetime\*\*



Available in H4, H7

**Bright white**  
white light




**CrystalVision\*\*\*\***  
★★★★★



Beam performance



Light color



Lifetime\*\*



Available in H1, H3, H4, H7, H11, HB3, HB4

**Ultimate**  
white light



**DiamondVision\*\*\*\***  
★★★★★



Beam performance



Light color



Lifetime\*\*



Available in H1, H3, H4, H7, HB3, HB4

# Vision

Up to **30%**  
more vision\*

- **Competitive price-performance ratio**
- **High-quality and ultra-resistant car lamp**

Philips Vision headlamps ensure excellent light-beam performance at a very **competitive price**.

\*Compared to the minimum legal standard



Standard

Vision

Available in C1 and B1 packaging



Available in



# VisionPlus

Up to **60%**  
more vision\*

- **Greater driving comfort with enhanced visibility**
- **High-quality and ultra-resistant car lamp**

Philips VisionPlus headlamps allow drivers to see farther for greater **safety** and **comfort**.

\*Compared to the minimum legal standard



Standard

VisionPlus

Available in S2 and B1 packaging



Available in





# X-tremeVision G-force

Up to **130%**  
brighter light\*

- Durable headlights with up to 10G vibration resistance\*\*
- White light for higher contrast and more visibility
- Best-in-class lifetime

Philips X-tremeVision G-force car bulbs are among the **brightest** you can buy with up to 10 G vibration resistance. **See further, react faster** and **drive safer**.

\*Compared to the minimum legal standard  
\*\*10 G applies to H4 and H7



Standard

X-tremeVision G-force

Available in S2 and B1 packaging



Available in



# LongLife EcoVision

Longer Lifetime,  
less replacement

- Lasts significantly longer\*
- High-quality and ultra-resistant car lamp

Tired of **changing** your headlamps all the time? With **longer lifetime**, Philips LongLife EcoVision is the choice for drivers seeking to **minimize maintenance** on their vehicles.


\*Lifetime differs per type, indication for H7 only.



Available in



Available in S2, C1 and B1 packaging



# WhiteVision

## Intense white xenon effect

- **Maximum visibility, premium look**
- **Maximum white light for greater contrast**
- **100% road legal**

Philips WhiteVision lamps add an intense white xenon look to your car headlights for a **premium driving experience** at night.



Standard

WhiteVision

Available in S2 and B1 packaging



Available in



# WhiteVision ultra

## Sharp white look

- **Superior white stylish look with up to 4 200 Kelvin**
- **100% road-legal performance**
- **Driving comfort with up to 60% more vision\***

Philips WhiteVision ultra, featuring the latest coating formula, delivers a stunning white light of up to 4 200 Kelvin. These are the whitest road-legal halogen lights in our portfolio and the perfect choice if you're looking for a cool, stylish look.

\*Compared to the minimum legal standard



Available in S2 and B1 packaging



Available in



# CrystalVision

## Bright white light

- Up to 4300K
- Bluish effect in the headlight
- Non-ECE homologated, for off-road only

Offering a bright white light, close to **daylight**, Philips CrystalVision produces more light than a standard headlamp and is ideal for all-purpose driving.



Standard

CrystalVision

Available in S2 and B1 packaging



Available in



# DiamondVision

## Ultimate white light

- Up to 5000K
- Blue-coated glass
- Non-ECE homologated, for off-road only

Philips DiamondVision produces a dazzling **white light** at up to **5000K**, offering more light output than standard headlamps. Its **styling effect** is ideal for city driving.



Standard

DiamondVision

Available in S2 and B1 packaging



Available in









# RacingVision

## Up to 150%\* brighter light

- For a sportive drive and an increased performance
- See further, react faster
- Optimized for winter light conditions

When driving on poorly lit country roads, you rely on the performance of your headlights. Faced with an unexpected danger, reaction time is everything. Even split seconds can make a crucial difference to your safety. The superior beam performance of the Philips RacingVision headlamp helps you identify dangerous situations faster and stay in perfect control of your vehicle – whatever road conditions you're facing.

\*Compared to the minimum legal standard



Standard



RacingVision

Available in S2 and B1 packaging



Available in



H4



H7



# Which lamp for which **function**?



**X-tremeVision  
G-force**  
New



## Low beam – high beam



## Front indicators



## Daytime Running Lights



## Interior lights



## Dashboard lights

## Front parking lights



## Side indicators

## Front fog lights







Vision

VisionPlus

X-tremeVision

LongLife  
EcoVision

WhiteVision

RacingVision

CrystalVision


DiamondVision

[philips.com/mylamps](http://philips.com/mylamps)



**Trunk lights**

**Rear indicators**



**3<sup>rd</sup> stop light**

**Reversing light**




**Glove compartment lights**



**Rear parking lights**



**Rear fog lights**



**Stop lights**

**License plate lights**

\*Combines stop and rear parking light function

12V car lighting

Halogen

## H1 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258PRB1	12	55	P14,5s	47516930	8 711500 475169	-	8711500475176	ECE	10
12258PRC1	12	55	P14,5s	47518360	8 711500 475183	8727900363791	8711500475190	ECE	100

## H1 VisionPlus



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258VPS2	12	55	P14,5s	36322728	8 727900 363227	-	8727900363210	ECE	5
12258VPB1	12	55	P14,5s	36320330	8 727900 363203	-	8727900363197	ECE	10

## H1 X-tremeVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258XV+E2	12	55	P14,5s	35635928	8 727900 356359	-	8727900356366	ECE	5
12258XV+B1	12	55	P14,5s	37164230	8 727900 371642	-	8727900371659	ECE	10

## H1 X-tremeVision G-force



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258XVGS2	12	55	P14,5s	35520828	8 727900 355208	-	8727900355215	ECE	5
12258XVGB1	12	55	P14,5s	35522230	8 727900 355222	-	8727900355239	ECE	10

## H1 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258LLECOS2	12	55	P14,5s	36255828	8 727900 362558	-	8727900362565	ECE	5
12258LLECOB1	12	55	P14,5s	36196430	8 727900 361964	-	8727900361971	ECE	10
12258LLECO1	12	55	P14,5s	36187230	8 727900 361872	-	8727900370683	ECE	10

## H1 WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258WHVSM	12	55	P14,5s	78884928	8 711500 788849	-	8711500788856	ECE	5
12258WHVB1	12	55	P14,5s	37156730	8 727900 371567	-	8727900371574	ECE	10

## H1 Rally (for off-road only)



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12454RAB1	12	100	P14,5s	40722130	8 711500 407221	-	8711500407238	-	10
12454RAC1	12	100	P14,5s	69639730	8 711500 696397	-	8727900366396	-	10

## H1 CrystalVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258CVSM	12	55	P14,5s	48971528	8 711500 489715	-	8711500489722	-	5
12258CVB1	12	55	P14,5s	82687930	8 711500 826879	-	8711500826893	-	10

## H1 DiamondVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12258DVS2	12	55	P14,5s	69742428	8 711500 697424	-	8711500697431	-	5
12258DVB1	12	55	P14,5s	82690930	8 711500 826909	-	8711500826916	-	10

## H2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12311C1	12	55	X511	47752130	8 711500 477521	-	8727900370782	ECE	10

## H3 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12336PRB1	12	55	PK22s	69561130	8 711500 695611	-	8711500695628	ECE	10
12336PRC1	12	55	PK22s	69534560	8 711500 695345	8711500775696	8711500695352	ECE	100

## H3 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12336LLECO1	12	55	PK22s	77704130	8 711500 777041	-	8711500779366	ECE	10

## H3 WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12336WHVB1	12	55	PK22s	77951930	8 711500 779519	-	8711500779526	ECE	10

## H3 Rally (for off-road only)



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12455RAC1	12	100	PK22s	47898630	8 711500 478986	-	8711500779373	-	10

## H3 CrystalVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12336CVB1	12	55	PK22s	77496530	8 711500 774965	-	8711500774996	-	10

## H3 DiamondVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12336DVS2	12	55	PK22s	69745528	8 711500 697455	-	8711500697462	-	5
12336DVB1	12	55	PK22s	77494130	8 711500 774941	-	8711500774972	-	10

## H4 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342PRB1	12	60/55	P43t-38	47480330	8 711500 474803	-	8711500474810	ECE	10
12342PRC1	12	60/55	P43t-38	49099560	8 711500 490995	8711500827807	8711500490988	ECE	100
12342PRC2	12	60/55	P43t-38	78028760	8 711500 780287	8711500780294	8711500780300	ECE	100



## H4 VisionPlus



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342VPS2	12	60/55	P43t-38	39925728	8 727900 399257	-	8727900350937	ECE	5
12342VPB1	12	60/55	P43t-38	39934930	8 727900 399349	-	8727900399332	ECE	10
12342VPC2	12	60/55	P43t-38	37435360	8 727900 374353	8727900374360	8727900374377	ECE	100

## H4 X-tremeVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342XV+E2	12	60/55	P43t-38	35637328	8 727900 356373	-	8727900356380	ECE	5
12342XV+B1	12	60/55	P43t-38	22107030	8 711500 221070	-	8711500221087	ECE	10

## H4 X-tremeVision G-force



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342XVGS2	12	60/55	P43t-38	35525328	8 727900 355253	-	8727900355284	ECE	5
12342XVGB1	12	60/55	P43t-38	35529130	8 727900 355291	-	8727900355390	ECE	10

## H4 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342LLECOS2	12	60/55	P43t-38	36257228	8 727900 362572	-	8727900362589	ECE	5
12342LLECOB1	12	60/55	P43t-38	36198830	8 727900 361988	-	8727900361995	ECE	10
12342LLECO1	12	60/55	P43t-38	36189630	8 727900 361896	-	8727900370836	ECE	10

## H4 ColorVision Yellow



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342CVPYS2	12	60/55	P43t-38	36789828	8 727900 367898	-	8727900367904	ECE	5

## H4 ColorVision Blue



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342CVPBS2	12	60/55	P43t-38	36793528	8 727900 367935	-	8727900367942	ECE	5

## H4 WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342WHVSM	12	60/55	P43t-38	78886328	8 711500 788863	-	8711500788870	ECE	5
12342WHVB1	12	60/55	P43t-38	22103230	8 711500 221032	-	8711500221049	ECE	10

## H4 WhiteVision ultra



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342WUUSM	12	60/55	P43t-38	00022430	8 727900 354904	-	8727900 54911	ECE	5
12342WUUB1	12	60/55	P43t-38	00020028	8 727900 354898	-	8727900354881	ECE	10

## H4 RacingVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342RVS2	12	60/55	P43t-38	00020028	8 719018 000200	-	8719018000217	ECE	5
12342RVB1	12	60/55	P43t-38	00022430	8 719018 000224	-	8719018000231	ECE	10

## H4 Rally (for off-road only)



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12569RAB1	12	100/90	P43t-38	40728330	8 711500 407283	-	8711500407290	-	10
12569RAC1	12	100/90	P43t-38	40177930	8 711500 401779	-	8711500779441	-	10
12754C1	12	100/90	P43t-38	77438530	8 711500 774385	-	8711500779380	-	10

## H4 CrystalVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342CVSM	12	60/55	P43t-38	48981428	8 711500 489814	-	8711500489821	-	5
12342CVB1	12	60/55	P43t-38	53287630	8 727900 532876	-	8727900532883	-	10

## H4 DiamondVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342DVS2	12	60/55	P43t-38	69573428	8 711500 695734	-	8711500697448	-	5
12342DVB1	12	60/55	P43t-38	53289030	8 727900 532890	-	8727900532906	-	10

## H7 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972PRB1	12	55	PX26d	40607130	8 711500 406071	-	8711500406088	ECE	10
12972PRC1	12	55	PX26d	400593760	8 711500 405937	8711500827838	8711500405944	ECE	100
12972PRC2	12	55	PX26d	37432260	8 727900 374322	8727900374339	8727900374346	ECE	100

## H7 VisionPlus



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972VPS2	12	55	PX26d	39938728	8 727900 399387	-	8727900399370	ECE	5
12972VPB1	12	55	PX26d	39936330	8 727900 399363	-	8727900399356	ECE	10
12972VPC2	12	55	PX26d	37426160	8 727900 374261	8727900374278	8727900374285	ECE	100

## H7 X-tremeVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972XV+E2	12	55	PX26d	35639728	8 727900 356397	-	8727900356403	ECE	5
12972XV+B1	12	55	PX26d	37168030	8 727900 371680	-	8727900371697	ECE	10

## H7 X-tremeVision G-force



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972XVGS2	12	55	PX26d	35541328	8 727900 355413	-	8727900355789	ECE	5
12972XVGB1	12	55	PX26d	35579630	8 727900 355796	-	8727900355802	ECE	10

## H7 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972LLECOS2	12	55	PX26d	36259628	8 727900 362596	-	8727900362602	ECE	5
12972LLECOB1	12	55	PX26d	36200830	8 727900 362008	-	8727900362015	ECE	10
12972LLECO1	12	55	PX26d	36192630	8 727900 361926	-	8727900371024	ECE	10

## H7 ColorVision Yellow



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972CVPYS2	12	55	PX26d	36802428	8 727900 368024	-	8727900368031	ECE	5

## H7 ColorVision Blue



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972CVPBS2	12	55	PX26d	36810928	8 727900 368109	-	8727900368130	ECE	5

## H7 WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972WHVSM	12	55	PX26d	78888728	8 711500 788887	-	8711500788894	ECE	5
12972WHVB1	12	55	PX26d	37160430	8 727900 371604	-	8727900371611	ECE	10

## H7 WhiteVision ultra



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972WVUSM	12	55	PX26d	35495928	8 727900 354959	-	8727900 54942	ECE	5
12972WVUB1	12	55	PX26d	35493530	8 727900 354935	-	8727900354928	ECE	10

## H7 RacingVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972RVS2	12	55	PX26d	00024828	8 719018 000248	-	8719018000255	ECE	5
12972RVB1	12	55	PX26d	00026230	8 719018 000262	-	8719018000279	ECE	10

## H7 Rally (for off-road only)



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12035RAB1	12	80	PX26d	40732030	8 711500 407320	-	8711500407337	-	10
12035RAC1	12	80	PX26d	47208330	8 711500 472083	-	8727900371109	-	10

## H7 CrystalVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972CVSM	12	55	PX26d	48983828	8 711500 489838	-	8711500489845	-	5
12972CVB1	12	55	PX26d	53291330	8 727900 532913	-	8727900532920	-	10



## H7 DiamondVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972DVS2	12	55	PX26d	69747928	8 711500 697479	-	8711500697486	-	5
12972DVB1	12	55	PX26d	53293730	8 727900 532937	-	8727900532944	-	10

## H8 WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12360WHVB1	12	35	PGJ19-1	37471130	8 727900 374711	-	8727900374728	ECE	10

## H8



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12360B1	12	35	PGJ19-1	82416530	8 711500 824165	-	8727900362909	ECE	10
12360C1	12	35	PGJ19-1	47582430	8 711500 475824	-	8727900371017	ECE	10

## H9



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12361B1	12	65	PGJ19-5	36308130	8 727900 363081	-	8727900363098	ECE	10
12361C1	12	65	PGJ19-5	47584830	8 711500 475848	-	8727900371000	ECE	10

## H10



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9145C1	12	45	PY20d	52974530	8 711559 529745	-	8727900370737	ECE	10

## H11 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12362PRB1	12	55	PGJ19-2	36428630	8 727900 364286	-	8727900364293	ECE	10
12362PRC1	12	55	PGJ19-2	36430930	8 727900 364309	-	8727900370751	ECE	10

## H11 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12362LLECOB1	12	55	PGJ19-2	36310430	8 727900 363104	-	8727900363111	ECE	10
12362LLECOB1	12	55	PGJ19-2	36194030	8 727900 361940	-	8727900370744	ECE	10

## H11 WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12362WHVB1	12	55	PGJ19-2	37469830	8 727900 374698	-	8727900374704	ECE	10

## H11 X-tremeVision G-force



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12362XVGB1	12	55	PGJ19-2	00119130	8 719018 001191	-	8719018001207	ECE	10

## H11 CrystalVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12362CVSM	12	55	PGJ19-2	52646128	8 711559 526461	-	8711559526843	-	5
12362CVB1	12	55	PGJ19-2	82685530	8 711500 826855	-	8711500826862	-	10

## H13



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9008C1	12	60/55	P26,4t	87798730	8 711500 877987	-	8727900370768	ECE	10

## H15



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12580B1	12	55/15	PGJ23t-1	02001730	8 719018 020017	-	8719018020031	ECE	10
12580C1	12	55/15	PGJ23t-1	02000030	8 719018 020000	-	8719018020024	ECE	10

## H16



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12366C1	12	19	PGJ19-3	36856730	8 727900 368567	-	8727900370775	ECE	10

## H18 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12643LLC1	12	65	PY26d-1	35603830	8 727900 356038	-	8727900356045	ECE	10

## H19 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12644LLC1	12	60/65	PU43t-3	35605230	8 727900 356052	-	8727900356069	ECE	10

## HB1 9004



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9004C1	12	65/45	P29t	47074430	8 711500 470744	-	8727900370997	-	10

## HB3 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9005PRB1	12	60	P20d	24724730	8 711500 247247	-	8711500247254	ECE	10
9005PRC1	12	60	P20d	24689930	8 711500 246899	-	8727900370980	ECE	10

## HB3 WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9005WHVB1	12	60	P20d	37475930	8 727900 374759	-	8727900374766	ECE	10

## HB3 CrystalVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9005CVB1	12	60	P20d	53299930	8 727900 532999	-	8727900533002	-	10

## HB3 DiamondVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9005DVB1	12	65	P20d	53295130	8 727900 532951	-	8727900532968	-	10

## HB4 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9006PRB1	12	51	P22d	24726130	8 711500 247261	-	8711500247278	ECE	10
9006PRC1	12	51	P22d	24687530	8 711500 246875	-	8727900370973	ECE	10

## HB4 WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9006WHVB1	12	51	P22d	37473530	8 727900 374735	-	8727900374742	ECE	10

## HB4 X-tremeVision G-force



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9006XVGB1	12	51	P22d	00123830	8 719018 001214	-	8719018001245	ECE	10

## HB4 CrystalVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9006CVSM	12	60	P22d	52620128	8 711559 526201	-	8711559526454	-	5
9006CVB1	12	60	P22d	53301930	8 727900 533019	-	8727900533026	-	10

## HB4 DiamondVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9006DVS2	12	55	P22d	53248728	8 727900 532487	-	8727900532494	-	5
9006DVB1	12	55	P22d	53297530	8 727900 532975	-	8727900532982	-	10

## HB5 9007



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9007C1	12	65/55	PX29t	24550230	8 711500 245502	-	8727900370966	-	10

## HIR2 LongLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
9012LLC1	12	55	PX22d	35125530	8 727900 351255	-	8727900370935	ECE	10

## H27W/1



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12059C1	12	27	PG13	52854030	8 711559 528540	-	8727900370799	ECE	10

## H27W/2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12060C1	12	27	PGJ13	52857130	8 711559 528571	-	8727900370805	ECE	10

## R2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12620B1	12	45/40	P45t-41	5543930	8 711500 055439	-	8711559525327	ECE	10
12620C1	12	45/40	P45t-41	40085730	8 711500 400857	-	8711500779359	ECE	10

## R2 Rally (for off-road only)



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12596(H5)C1	12	60/55	P45t-41	51226630	8 711559 512266	-	8727900370843	-	10

## R2 Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12475B1	12	45/40	P45t-41	24716230	8 711500 247162	-	8711500247179	ECE	10
12475C1	12	45/40	P45t-41	40466430	8 711500 404664	-	8727900371130	ECE	10

## 12V signaling and interior lighting (for 12V LED retrofit lighting, please refer to page 74)

### P21W VisionPlus



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12498VPB2	12	21	BA15s	36318030	8 727900 363180	-	8727900363173	ECE	10

### P21W LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12498LLECOB2	12	21	BA15s	38210530	8 727900 382105	-	8727900382112	ECE	10
12498LLECOCP	12	21	BA15s	38198628	8 727900 381986	8727900381993	8727900391695	ECE	5x10

### P21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12498B2	12	21	BA15s	5549130	8 711500 055491	-	8711559520131	ECE	10
12498CP	12	21	BA15s	49078073	8 711500 490780	8711500490797	8711500490803	ECE	200

### P21/4W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12594B2	12	21/4	BAZ15d	40485530	8 711500 404855	-	8711500471017	ECE	10
12594CP	12	21/4	BAZ15d	48433828	8 711500 484338	8711500484345	8727900391565	ECE	5x10

### P21/5W VisionPlus



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12499VPB2	12	21/5	BAY15d	36316630	8 727900 363166	-	8727900363159	ECE	10

### P21/5W LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12499LLECOB2	12	21/5	BAY15d	38212930	8 727900 382129	-	8727900382136	ECE	10
12499LLECOCP	12	21/5	BAY15d	38201328	8 727900 382013	8727900382020	8727900391053	ECE	5x10



## P21/5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12499B2	12	21/5	BAY15d	5545330	8 711500 055453	-	8711559520148	ECE	10
12499CP	12	21/5	BAY15d	48159773	8 711500 481597	8711500481603	8711500481610	ECE	200

## PR21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12088CP	12	21	BAW15s	48531128	8 711500 485311	8711500485328	8727900391589	ECE	5x10

## PR21/5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12495CP	12	21/5	BAW15d	48873228	8 711500 488732	8711500488749	8727900391572	ECE	5x10

## PY21W SilverVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12496SVB2	12	21	BAU15s	31117730	8 711500 311177	-	8711500311191	ECE	10

## PY21W LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12496LLECOCP	12	21	BAU15s	38218128	8 727900 382181	8727900382198	8727900391084	ECE	5x10

## PY21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12496NAB2	12	21	BAU15s	52372930	8 711559 523729	-	8711559523743	ECE	10
12496NACP	12	21	BAU15s	52534173	8 711559 525341	8711559525358	8711559525365	ECE	200

## Stop P22



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12401CP	12	15	BA15s	87821228	8 711500 878212	8711500878229	8711500790538	-	5x10

## Stop P25



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12445CP	12	18	BA15s	48440628	8 711500 484406	8711500484413	8727900391602	-	5x10

## R5W LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12821LLECOB2	12	5	BA15s	38208230	8 727900 382082	-	8727900382099	ECE	10
12821LLECOCP	12	5	BA15s	38195528	8 727900 381955	8727900381962	8727900390940	ECE	5x10

## R5W BA15s



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12821B2	12	5	BA15s	5546030	8 711500 055460	-	8711500417701	ECE	10
12821CP	12	5	BA15s	48269373	8 711500 482693	8711500482709	8711500482716	ECE	200

## R5W BA15d



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12822CP	12	5	BA15d	45407228	8 711500 454072	8711500454959	8711500790521	ECE	5x10

## R10W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12814B2	12	10	BA15s	5547730	8 711500 055477	-	8711500417718	ECE	10
12814CP	12	10	BA15s	48341673	8 711500 483416	8711500483423	8711500483430	ECE	200

## RY10W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12093NACP	12	10	BAU15s	48362128	8 711500 483621	8711500483638	8727900391619	ECE	5x10

## BA7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12829CP	12	2	BA7s	52123728	8 711559 521237	8711500401236	8727900390933	-	5x10

## T2W - T3W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12913CP	12	2	BA9s	21997828	8 711500 219978	8711500219985	8711500220820	-	5x10
12910CP	12	3	BA9s	21949728	8 711500 219497	8711500219503	8711500220837	-	5x10

## T4W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12929B2	12	4	BA9s	5550730	8 711500 055507	-	8711559520094	ECE	10
12929CP	12	4	BA9s	21979473	8 711500 219794	8711500219800	8711500219817	ECE	200

## Miniature halogen signaling USA

### H5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12023CP	12	5	BA9s	51270928	8 711559 512709	8711559512464	8727900371222	-	5x10

### H6W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12036B2	12	6	BAX9s	24720930	8 711500 247209	-	8711500247216	ECE	10
12036CP	12	6	BAX9s	87603428	8 711500 876034	8711500876041	8727900370676	ECE	5x10

## H6W WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12036WHVB2	12	6	BAX9s	37467430	8 711500 245670	-	8727900374681	ECE	10
12036BVCP	12	6	BAX9s	87609628	8 711500 876096	8711500876102	8727900370720	ECE	5x10

## H10W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12024CP	12	10	BA9s	52941728	8 711559 529417	8711559529424	8727900371192	-	5x10

## H20W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12025CP	12	20	BA9s	87600328	8 711500 876003	8711500876010	8727900371154	-	5x10

## H21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12356CP	12	21	BAY9s	87989928	8 711500 879899	8711500879905	8727900371116	ECE	5x10

## HY21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12146CP	12	21	BAW9s	35244328	8 727900 352443	8727900352450	8727900370867	ECE	5x10

## Wedge base

### W1,2W - W2,3W - W2W - WBT5



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12521CP	12	1	W2x4,6d	48321828	8 711500 483218	8711500483225	8727900391671	-	5x10
12516B2	12	1.2	W2x4,6d	5554530	8 711500 055545	-	8711500417763	-	10
12516CP	12	1.2	W2x4,6d	48153573	8 711500 481535	8711500481542	8711500481559	-	200
12505CP	12	2	W2x4,6d	48327028	8 711500 483270	8711500483287	8727900391657	-	5x10
12061CP	12	2.3	W2x4,6d	48330028	8 711500 483300	8711500483317	8727900391640	ECE	5x10

### W2,2W - W3W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12960CP	12	2.2	W2,1x9,5d	48150428	8 711500 481504	8711500481511	8727900391633	-	5x10
12256B2	12	3	W2,1x9,5d	52410830	8 711559 524108	-	8711559524122	ECE	10
12256CP	12	3	W2,1x9,5d	48144328	8 711500 481443	8711500481450	8727900391664	ECE	5x10



## W5W LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12961LLECOB2	12	5	W2,1x9,5d	38204430	8 727900 382044	-	8727900382051	ECE	10
12961LLECOCP	12	5	W2,1x9,5d	38189428	8 727900 381894	8727900381900	8727900390872	ECE	5x10

## W5W WhiteVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12961NBVB2	12	5	W2,1x9,5d	39204330	8 727900 392043	-	8727900392050	ECE	10

## W5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12961B2	12	5	W2,1x9,5d	40421330	8 711500 404213	-	8711559520070	ECE	10
12961CP	12	5	W2,1x9,5d	49090273	8 711500 490902	8711500490919	8711500490926	ECE	200

## WY5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12396NAB2	12	5	W2,1x9,5d	40058130	8 711500 400581	-	8711500400598	ECE	10
12396NACP	12	5	W2,1x9,5d	53002428	8 711559 530024	8711559530031	8727900390889	ECE	5x10

## WBT10 VisionPlus



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12040VPB2	12	6	W2,1x9,5d	52416030	8 711559 524160	-	8711559524184	-	10

## W16W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12067B2	12	16	W2,1x9,5d	40587630	8 711500 405876	-	8711559521053	ECE	10
12067CP	12	16	W2,1x9,5d	48272328	8 711500 482723	8711500482730	8727900391626	ECE	5x10

## W21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12065B2	12	21	W3x16d	70146330	8 727900 701463	-	8727900701470	ECE	10
12065CP	12	21	W3x16d	47135228	8 711500 471352	8711500471369	8727900391107	ECE	5x10

## W21/5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12066B2	12	21/5	W3x16q	69739130	8 727900 697391	-	8727900697407	ECE	10
12066CP	12	21/5	W3x16q	47138328	8 711500 471383	8711500471390	8727900391091	ECE	5x10

## WY21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12071B2	12	21	WX3x16d	69741430	8 727900 697414	-	8727900697421	ECE	10
12071CP	12	21	WX3x16d	52539628	8 711559 525396	8711559525402	8727900391688	ECE	5x10

## Festoon

### Festoon T6,2x27



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12818CP	12	3	SV6	48461128	8 711500 484611	8711500484628	8727900695632	-	5x10

### Festoon T6,2x35



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12848CP	12	3	SV6	48467328	8 711500 484673	8711500484680	8727900391558	-	5x10

### C5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12844B2	12	5	SV8,5	5551430	8 711500 055514	-	8711500417749	ECE	10
12844CP	12	5	SV8,5	48156673	8 711500 481566	8711500481573	8711500481580	ECE	200

### Festoon T10,5x30 LongLife EcoVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12860LLECOCP	12	10	SV8,5	38192428	8 727900 381924	8727900381931	8727900391114	-	5x10

### Festoon T10,5x38



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12854CP	12	10	SV8,5	48248828	8 711500 482488	8711500482495	8727900391510	-	5x10

### Festoon T10,5x43



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12864CP	12	5	SV8,5	48205128	8 711500 482051	8711500482075	8727900391527	-	5x10
12866B2	12	10	SV8,5	5552130	8 711500 055521	-	8711500417756	-	10
12866CP	12	10	SV8,5	48242628	8 711500 482426	8711500482433	8727900391534	-	5x10

### Festoon T15x43



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12850CP	12	15	SV8,5	48285328	8 711500 482853	8711500482860	8727900391541	-	5x10

## Bax

### Bax tool box 12V



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55502GKKM	12	-	-	69717928	8 727900 697179	-	8727900697230	-	5

### Bax 8,3s/1,35 black



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12597B2	12	1.2	B8,3s/1,35	53018530	8 711559 530185	-	8711559530192	-	10
12597CP	12	1.2	B8,3s/1,35	48365228	8 711500 483652	8711500483669	8727900390957	-	5x10

### Bax 8,3s/1,5 blue



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12602CP	12	2	B8,3s/1,5	48396628	8 711500 483966	8711500483973	8727900390995	-	5x10

### Bax 8,5d/2 black



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12598B2	12	1.2	B8,5d/2	40588330	8 711500 405883	-	8711500405890	-	10
12598CP	12	1.2	B8,5d/2	48387428	8 711500 483874	8711500483881	8727900390964	-	5x10

### Bax 8,5d/1,5 blue



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12603CP	12	1.2	B8,5d/1,5	48399728	8 711500 483997	8711500484000	8727900391015	-	5x10

### Bax 8,5d/2 green



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12600CP	12	2	B8,5d/2	48393528	8 711500 483935	8711500483942	8727900390971	-	5x10

### Bax 8,5d green



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12604CP	12	2	B8,5d	40508128	8 711500 405081	8711500404589	8727900391022	-	5x10

### Bax 8,5d beige



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12637CP	12	1.5	B8,5d	51487128	8 711559 514871	8711500400178	8727900371048	-	5x10

### Bax 10d black halogen



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12615CP	12	5	B10d	52807628	8 711559 528076	8711500243768	8727900370911	-	5x10

### Bax 10d brown halogen



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12614CP	12	3	B10d	52805228	8 711559 528052	8711559512723	8727900370928	-	5x10



## Bax 8,4d light blue



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12623CP	12	1.2	BX8,4d	51384328	8 711559 513843	8711500244154	8727900370904	-	5x10

## Bax 8,4d beige



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12627CP	12	1.5	BX8,4d	51414728	8 711559 514147	8711500247414	8727900370959	-	5x10
12629CP	12	1.8	BX8,4d	51488828	8 711559 514888	8711559512488	8727900371031	-	5x10

## Bax 8,4d black



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12625CP	12	1.2	BX8,4d	51409328	8 711559 514093	8711500244420	8727900371208	-	5x10

## Bax 8,4d light green



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12626CP	12	2	BX8,4d	51412328	8 711559 514123	8711500246066	8727900370942	-	5x10

## Bax 8,4d olive green



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12611CP	12	1.3	BX8,4d	77432328	8 711500 774323	8711500774330	8711500779397	-	5x10

## Bax 8,4d orange



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12624CP	12	1.1	BX8,4d	51411628	8 711559 514116	8711500245137	8727900370898	-	5x10

## Bax 8,5d white



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12638CP	12	1.12	BX8,5d	48846628	8 711500 488466	8711500488473	8727900391503	-	5x10

## HiPerVision

### P13W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12277C1	12	13	PG18,5d-1	69672130	8 727900 696721	-	8727900391008	ECE	10



### PCY16W HiPerClick



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12271AC1	12	16	PU20d/2	38965430	8 727900 389654	-	8727900391152	ECE	10



### PW16W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12177C1	12	16	WP3,3x14,5/8	39623230	8 727900 396232	-	8727900396249	ECE	10



### PS19W LongLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12085LLC1	12	19	PG20/1	70046630	8 727900 700466	-	8727900390926	ECE	10



### PS19W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12085C1	12	19	PG20/1	69653030	8 727900 696530	-	8727900390988	ECE	10



### PSY19W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12275NAC1	12	19	PG20/2	52735230	8 711559 527352	-	8727900390858	ECE	10



### HiPerVision LCP



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12197HTRC1	13.5	24	HPSL 2A	39621830	8 727900 396218	-	8727900396225	-	10



### PS24W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12086FFC1	12	24	PG20/3	70044230	8 727900 700442	-	8727900390919	ECE	10



### PSX24W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12276C1	12	24	PG20/7	69676930	8 727900 696769	-	8727900390902	ECE	10



### PSY24W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12188NAC1	12	24	PG20/4	69668430	8 727900 696684	-	8727900390834	ECE	10



## PSY24W SilverVision+



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12180SV+C1	12	24	PG20/4	70379530	8 727900 703795	-	8727900390841	ECE	10

## PW24W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12182HTRC1	12	24	WP3,3x14,5/3	39196130	8 727900 391961	-	8727900397369	ECE	10

## PWY24W SilverVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12174SVHTRC1	12	24	WP3,3x14,5/4	39200530	8 727900 392005	-	8727900397352	ECE	10

## PWY24W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12174NAHTRC1	12	24	WP3,3x14,5/4	39202930	8 727900 392029	-	8727900397345	ECE	10

## PY24W SilverVision+



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12274SV+C1	12	24	PGU20/4	69678330	8 727900 696783	-	8727900390780	ECE	10

## PY24W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12190NAC1	12	24	PGU20/4	69690530	8 727900 696905	-	8727900390803	ECE	10

## PSX26W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12278C1	12	26	PG18,5d/3	38874930	8 727900 388749	-	8727900390896	ECE	10

# Halogen





# Two-wheeler lighting



# Which **two-wheeler lamp** do you need?



## Experience more light

Up to **30%** more vision\*



**Vision moto**  
★★★★★




Beam performance



Light color  
Up to **3200 K**



Lifetime\*\*  
Up to **550 h**



Available in  
H4, H7, HS1

See and **be seen**



**10 G**  
Vibration resistant


**CityVision moto**  
★★★★★



Beam performance



Light color  
Up to **3200 K**



Lifetime\*\*  
Up to **400 h**



Available in  
H4, H7, HS1

Up to **130%** brighter light\*



**10 G**  
Vibration resistant


**X-tremeVision moto**  
★★★★★



Beam performance



Light color  
Up to **3500 K**



Lifetime\*\*  
Up to **450 h**



Available in  
H4, H7


## Enjoy your passion

**Bright white** light



**10 G**  
Vibration resistant

**CrystalVision ultra**  
★★★★★



Beam performance



Light color  
Up to **3700 K**



Lifetime\*\*  
Up to **400 h**



Available in  
H4, H7, HS1



Philips two-wheeler lighting is designed to resist extreme vibration – up to 10 G.

Images for illustration purposes only

\* Compared to the minimum legal requirement

\*\* Lifetime differs per type, indication for H7 only

# Vision moto

Up to **30%**  
more vision\*

- Better performance\*
- High-quality and ultra-resistant motorcycle lamp

Producing **up to 30% more vision\*** than a standard lamp, Philips Vision moto allows riders to see farther with improved light-beam performance at a very **competitive price**.

\*Compared to the minimum legal standard



Standard

Vision moto

Available in



H4

H7

HS1


# CityVision moto

See and be seen

- Distinctive orange effect
- Maximum safety
- Specifically designed for city use
- Up to 40% more vision\*

For maximum safety and visibility, Philips CityVision moto produces a distinctive, attention-grabbing **orange effect**. Motorcycle riders everywhere are looking for more safety, especially riders in heavy city traffic.

\*Compared to the minimum legal standard



Standard

CityVision moto

Available in



H4

H7

HS1



# X-tremeVision moto

Up to **130% more vision\***

- **Maximum brightness**
- **Unique gas filling for optimal lifetime and durability**
- **Significantly longer beam\***
- **Maximum comfort and safety**

Philips X-tremeVision moto offers up to **130% more vision\*** for riders who need to see farther for **ultimate performance** and **safety**.

\*Compared to the minimum legal standard



Standard



X-tremeVision moto

Available in



H4



H7

# CrystalVision ultra moto

**Bright white light**

- **White modern look**
- **Customization and style on the road**
- **High quality and ultra-resistant headlamp**

For riders seeking ultimate style, Philips CrystalVision ultra moto headlamps provide them with **bright white light**. Customize your style **with no compromise on visibility and comfort**.



Standard



CrystalVision ultra moto

Available in



H4



H7



HS1



# Which lamp for which function?



12258 12336 12342 12972 12361 12362 12636 9005 9006 12620 12728 12008

H1 H3 H4 H7 H9 H11 HS1 HB3 HB4 R2 S2 S3



Low beam - high beam



12961 12067 12065 12071 12396 12356

W5W W16W W21W WY21W WY5W H21W



12821 12814 12093 12498 12496 12499

R5W R10W RY10W P21W PY21W P21/5W



Front indicators



12256 12961 12066 12929 12821 12814 12498 12499

W3W W5W W21/5W T4W R5W R10W P21W P21/5W



Rear position light



12256 12961 12929 12821 12814 12036 12844

W3W W5W T4W R5W R10W H6W C5W



Licence plate light



Vision moto

CityVision moto



X-tremeVision moto

CrystalVision ultra moto

[philips.co.uk/c-m-li/motorcycle-lights](http://philips.co.uk/c-m-li/motorcycle-lights)



12929 12821 12814 12036

T4W R5W R10W H6W



12256 12961 12067 12913 12910

W3W W5W W16W T2W T3W



Front position light



12067 12066 12498 12088 12499 12495

W16W W21/5W P21W PR21W P21/5W PR21/5W



Stop light



12356 12961 12067 12065 12071

W5W W16W W21W WY21W H21W



12821 12814 12093 12498 12496

R5W R10W RY10W P21W PY21W



Rear indicators

Two-wheeler lighting

Halogen

## H4 Vision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342PRBW	12	60/55	P43t-38	49024730	8 711500 490247	-	8711500490254	ECE	10

## H4 CityVision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342CTVBW	12	60/55	P43t-38	39896030	8 727900 398960	-	8727900398977	ECE	10

## H4 X-tremeVision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342XV+BW	12	60/55	P43t-38	00056930	8 719018 000569	-	8719018000576	ECE	10

## H4 CrystalVision ultra moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12342CVUBW	12	60/55	P43t-38	22148330	8 711500 221483	-	8711500221490	ECE	10

## H7 Vision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972PRBW	12	55	PX26d	49026130	8 711500 490261	-	8711500490278	ECE	10

## H7 CityVision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972CTVBW	12	55	PX26d	39898430	8 727900 398984	-	8727900398991	ECE	10

## H7 X-tremeVision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972XV+BW	12	55	PX26d	37867230	8 727900 378672	-	8727900378689	ECE	10

## H7 CrystalVision ultra moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12972CVUBW	12	55	PX26d	22118630	8 711500 221186	-	8711500221193	ECE	10

## HS1 Vision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12636BW	12	35/35	PX43t	53035330	8 727900 530353	-	8727900530360	ECE	10
12636C1	12	35/35	PX43t	51250130	8 711559 512501	-	8727900370881	ECE	10

## HS1 CityVision moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12636CTVBW	12	35/35	PX43t	39894630	8 727900 398946	-	8727900398953	ECE	10

## HS1 CristalVision ultra moto



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12636BVBW	12	35/35	PX43t	78195630	8 711500 781956	-	8711500781963	ECE	10

## S2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12728BW	12	35/35	BA20d	77385230	8 711500 773852	-	8711500773869	ECE	10
12728C1	12	35/35	BA20d	77359330	8 711500 773593	-	8711500779342	ECE	10

## S3



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12008BW	12	15	P26s	77381430	8 711500 773814	-	8711500773845	ECE	10
12008C1	12	15	P26s	77394430	8 711500 773944	-	8711500779335	ECE	10

## Signaling lamps

### W3W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12256B2	12	3	W2,1x9,5d	52410830	8 711559 524108	-	8711559524122	ECE	10
12256CP	12	3	W2,1x9,5d	48144328	8 711500 481443	8711500481450	8727900391664	ECE	5x10

### P21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12498B2	12	21	BA15s	05549130	8 711500 055491	-	8711559520131	ECE	10
12498CP	12	21	BA15s	49078073	8 711500 490780	8711500490797	8711500490803	ECE	200

### P21/5W ExtraDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12499EDBW	12	21/5	BAY15d	87900430	8 711500 879004	-	8711500879035	ECE	10

# Halogen





# 24V Bus and truck lighting



# Which 24V lamp do you need?



## Safety and durability

Built to **last**



**MasterDuty**



Light color  
Up to **3200 K**




Lifetime\*  
Up to **550 h**



Available in  
H1, H3, H4, H7, H11

**Best-in-class**  
lifetime



**MasterLife**



Light color  
Up to **3200 K**



Lifetime\*  
Up to **1200 h**



Available in  
H1, H3, H4, H7, H11

## Safety and style


**Maximum**  
**xenon**  
effect



**MasterDuty**  
**BlueVision**



Light color  
Up to **3500 K**



Lifetime\*  
Up to **500 h**



Available in  
H3, H4, H7




Heavy duty  
vibration  
resistant

Images for illustration purposes only  
\* Lifetime differs per type, indication for H7 only

# Safety and durability

## Philips 24V headlighting advantage

Combining **vibration resistance** with **high quality**, Philips truck headlamps last longer than standard lamps.



## MasterDuty

### Built to last

- Lasts up to 550 hours\*
- Maximum vibration resistance
- Up to 130% more vision\*\*
- Reinforced mount and base guards against shocks
- Extra robust double-coil filament

The Philips MasterDuty headlamps are designed for **maximum vibration resistance** and excellent **lifetime**. MasterDuty is the **right choice** for drivers seeking **toughness** that **lasts**.

\*Lifetime differs per type, indication for H7 only

\*\*Compared to the minimum legal standard, applies to H1, H4, H7 and H11.



Available in B1 and C1 packaging



Available in



# MasterLife

## Best-in-class lifetime


- Lasts up to 1200 hours\*
- Up to 100% more vision\*\*
- Maximum vibration resistance\*
- Extra-robust double-coil filament

Philips MasterLife lasts up to **1200 hours\*** while withstanding extreme **stress** and **vibration**. With a **minimum failure rate** our lamps keep your fleet productive and on the move by minimizing time-consuming interruptions.

**MasterLife is the smartest choice for large fleet owners!**

\*Lifetime differs per type, indication for H7 only.

\*\*Compared to the minimum legal standard, applies to H1, H4, H7 and H11.



Available in C1 packaging



Available in



# MasterDuty BlueVision

## Maximum xenon effect

- Maximum vibration resistance\*
- High-performance quartz glass with xenon-effect coating
- Distinctive blue cap, looks sharp even when turned off

For drivers seeking **ultimate style** and **performance**, Philips MasterDuty BlueVision produces a **blue xenon effect**. It combines the **durability** and **vibration resistance** of Philips MasterDuty with an additional blue xenon effect for maximum style.

\*Compared to average H4 or H7 24V lamps on the market



Standard

MasterDuty BlueVision

Available in S2 and B1 packaging



Available in






# Which lamp for which function?




philips.com/automotive




## Low beam – high beam

## Front fog lights



## Interior lights

## Dashboard lights



## Front indicators

## Front position lights



## Side indicators

## Rear position lights



## Running lights

## Rear indicators





## License plate lights

## Stop lights

## Reversing light

## Rear fog lights



24V bus and truck lighting

Halogen

## H1 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13258MDB1	24	70	P14,5s	82585830	8 711500 825858	-	8711500825865	ECE	10
13258MDC1	24	70	P14,5s	82577360	8 711500 825773	8711500828507	8711500825780	ECE	100

## H1 MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13258MLC1	24	70	P14,5s	82569830	8 711500 825698	-	8727900370812	ECE	10

## H2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13311C1	24	70	X511	47751430	8 711500 477514	-	8727900371079	ECE	10

## H3 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13336MDB1	24	70	PK22s	77459030	8 711500 774590	-	8711500774613	ECE	10
13336MDC1	24	70	PK22s	77460660	8 711500 774606	8711500775313	8711500774637	ECE	100

## H3 MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13336MLC1	24	70	PK22s	77462030	8 711500 774620	-	8711500779403	ECE	10

## H3 MasterDuty BlueVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13336MDBVS2	24	70	PK22s	77486628	8 711500 774866	-	8711500774897	ECE	5
13336MDBVB1	24	70	PK22s	77488030	8 711500 774880	-	8711500774910	ECE	10

## H4 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13342MDB1	24	75/70	P43t-38	82587230	8 711500 825872	-	8711500825889	ECE	10
13342MDC1	24	75/70	P43t-38	82579760	8 711500 825797	8711500828002	8711500825803	ECE	100

## H4 MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13342MLC1	24	75/70	P43t-38	82571130	8 711500 825711	-	8727900371086	ECE	10

## H4 MasterDuty BlueVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13342MDBVS2	24	75/70	P43t-38	53275328	8 727900 532753	-	8727900532760	ECE	5
13342MDBVB1	24	75/70	P43t-38	53281430	8 727900 532814	-	8727900532821	ECE	10

## H7 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13972MDB1	24	70	PX26d	82589630	8 711500 825896	-	8711500825902	ECE	10
13972MDC1	24	70	PX26d	82581060	8 711500 825810	8711500828514	8711500825827	ECE	100

## H7 MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13972MLC1	24	70	PX26d	82573530	8 711500 825735	-	8727900371147	ECE	10

## H7 MasterDuty BlueVision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13972MDBVS2	24	70	PX26d	53277728	8 727900 532777	-	8727900532784	ECE	5
13972MDBVB1	24	70	PX26d	53279130	8 727900 532791	-	8727900532807	ECE	10

## H11 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
24362MDC1	24	70	PGJ19-2	82583430	8 711500 825834	-	8727900371055	ECE	10

## H11 MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
24362MLC1	24	70	PGJ19-2	82575930	8 711500 825759	-	8727900371062	ECE	10

## R2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13620C1	24	55/50	P45t-41	40087130	8 711500 400871	-	8711500779458	ECE	10

## 24V signaling and interior lighting (for 24V LED retrofit lighting, please refer to page 74)

### P21W MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13498MDCP	24	21	BA15s	69949473	8 727900 699494	8727900699500	8727900699517	ECE	200

### P21W MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13498MLCP	24	21	BA15s	69961628	8 727900 699616	8727900699623	8727900391145	ECE	5x10

### P21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13498B2	24	21	BA15s	40455830	8 711500 404558	-	8711500405449	ECE	10
13498CP	24	21	BA15s	48415473	8 711500 484154	8711500484161	8711500484178	ECE	200

## P21/5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13499B2	24	21/5	BAY15d	40456530	8 711500 404565	-	8711500405371	ECE	10
13499CP	24	21/5	BAY15d	48424673	8 711500 484246	8711500484253	8711500484260	ECE	200

## PY21W MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13496MLCP	24	21	BAU15s	69964728	8 727900 699647	8727900699654	8727900391138	ECE	5x10

## Stop P22



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13401CP	24	15	BA15s	87826728	8 711500 878267	8711500878274	8711500790507	-	5x10
13402CP	24	15	BA15d	87836628	8 711500 878366	8711500878373	8711500790514	-	5x10

## Stop P25



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13445CP	24	18	BA15s	48443728	8 711500 484437	8711500484444	8727900390810	-	5x10

## R5W MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13821MDCP	24	5	BA15s	69955528	8 727900 699555	8727900699562	8727900390766	ECE	5x10

## R5W MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13821MLCP	24	5	BA15s	69970828	8 727900 699708	8727900699715	8727900390773	ECE	5x10

## R5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13821B2	24	5	BA15s	40453430	8 711500 404534	-	8711500405425	ECE	10
13821CP	24	5	BA15s	48338673	8 711500 483386	8711500483393	8711500483409	ECE	200
13822CP	24	5	BA15d	40904128	8 711500 409041	8711500878021	8711500790491	ECE	5x10

## R10W MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13814MDCP	24	10	BA15s	69952428	8 727900 699524	8727900699531	8727900391121	ECE	5x10

## R10W MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13814MLCP	24	10	BA15s	69967828	8 727900 699678	8727900699685	8727900390742	ECE	5x10



## R10W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13814B2	24	10	BA15s	40452730	8 711500 404527	-	8711559526409	ECE	10
13814CP	24	10	BA15s	48344773	8 711500 483447	8711500483454	8711500483461	ECE	200

## BA7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13829CP	24	3	BA7s	52133628	8 711559 521336	8711500401274	8727900390759	-	5x10

## T4W MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13929MDCP	24	4	BA9s	69958628	8 727900 699586	8727900699593	8727900391039	ECE	5x10

## T4W MasterLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13929MLCP	24	4	BA9s	69976028	8 727900 699760	8727900699777	8727900391046	ECE	5x10

## T2W - T3W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13913CP	24	2	BA9s	22003528	8 711500 220035	8711500220042	8711500220844	-	5x10
13910CP	24	3	BA9s	21955828	8 711500 219558	8711500219565	8711500220851	-	5x10

## T4W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13929B2	24	4	BA9s	40454130	8 711500 404541	-	8711500405432	ECE	10
13929CP	24	4	BA9s	21985573	8 711500 219855	8711500219862	8711500219879	ECE	200

## Miniature halogen signaling USA

### H21W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
24356CP	24	21	BAY9s	87615728	8 711500 876157	8711500876164	8727900371161	ECE	5x10

## Wedge base

### W2,5W - W3W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13960CP	24	2.5	W2,1x9,5d	48147428	8 711500 481474	8711500481481	8727900391275	-	5x10
13256CP	24	3	W2,1x9,5d	48141228	8 711500 481412	8711500481429	8727900391169	ECE	5x10

### W5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13961B2	24	5	W2,1x9,5d	52420730	8 711559 524207	-	8711559524214	ECE	10
13961CP	24	5	W2,1x9,5d	48138273	8 711500 481382	8711500481399	8711559530376	ECE	200

### WBT5



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13521CP	24	1	W2x4,6d	48324928	8 711500 483249	8711500483256	8727900391176	-	5x10
13516CP	24	1.2	W2x4,6d	48306573	8 711500 483065	8711500483072	8711500483089	-	200
13974CP	24	2	W2x4,6d	48318828	8 711500 483188	8711500483195	8727900391183	-	5x10

## Festoon

### Festoon T6,2x27



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13818CP	24	3	SV6	48464228	8 711500 484642	8711500484659	8727900391251	-	5x10

### Festoon T6,2x35



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13848CP	24	3	SV6	48470328	8 711500 484703	8711500484710	8727900391268	-	5x10

### Festoon T10,5x38 10W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13854CP	24	10	SV8,5	48251828	8 711500 482518	8711500482525	8727900391206	-	5x10

### C5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13844B2	24	5	SV8,5	40463330	8 711500 404633	-	8711500405388	ECE	10
13844CP	24	5	SV8,5	48197973	8 711500 481979	8711500481986	8711500481993	ECE	200

### Festoon T10,5x43 5W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13864CP	24	5	SV8,5	48233428	8 711500 482334	8711500482341	8727900391213	-	5x10

## Festoon T10,5x43 10W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13866CP	24	10	SV8,5	48245728	8 711500 482457	8711500482464	8727900391220	-	5x10

## Festoon T15x43 15W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13850CP	24	15	SV8,5	48288428	8 711500 482884	8711500482891	8727900391244	-	5x10

## Festoon T15x43 18W



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13807CP	24	18	SV8,5	48294528	8 711500 482945	8711500482952	8727900391237	-	5x10

## Bax

### Bax 8,3s/1,35 grey



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13597CP	24	1.2	B8,3s/1,35	48384328	8 711500 483843	8711500483850	8727900390797	-	5x10

### Bax 8,5d/2 grey



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
13598CP	24	1.2	B8,5d/2	48390428	8 711500 483904	8711500483911	8727900390827	-	5x10

### Bax 8,5d brown



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
24032CP	24	1.2	B8,5d	48852728	8 711500 488527	8711500488534	8727900391077	-	5x10

### Bax 8,5d/2 yellow



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
24029CP	24	1.2	B8,5d/2	48402428	8 711500 484024	8711500484031	8727900391190	-	5x10

# Kits







# Spare and headlight restoration **kits** for cars and trucks

For increased **safety**, it is **recommended** by most European countries that all vehicles be equipped with a **homologated spare kit**. It will not only keep drivers in **compliance** with the law, but will also keep them **safer** as they will always be prepared to **replace** a burned-out lamp.

Our **Headlight restoration kit** renovates car, truck and two-wheeler lenses to like-new condition. It's our **cost-effective alternative** to complete headlight replacement.

[www.philips.com/automotive](http://www.philips.com/automotive)



## 12V spare kits

### Easy Kit H1



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55472EKMM	12	-	-	69551928	8 727900 695519	-	8727900695533	ECE	5

#### Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A
Quantity	1	-	-	-	1	1	1	1	1

### Easy Kit H4



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55473EKMM	12	-	-	69555728	8 727900 695557	-	8727900695571	ECE	5

#### Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A
Quantity	-	1	-	-	1	1	1	1	1

### Easy Kit H7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55474EKMM	12	-	-	69558828	8 727900 695588	-	8727900695601	ECE	5

#### Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A
Quantity	-	-	1	-	1	1	1	1	1

### Easy Kit H1/H7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55475EKMM	12	-	-	69562528	8 727900 695625	-	8727900695656	ECE	5

#### Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A
Quantity	1	-	1	-	1	1	1	1	1





## Essential Box H1



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55717EBKM	12	-	-	70032928	8 727900 700329	-	8727900700336	ECE	5

### Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A	Fuse 15A	Fuse 20A
Quantity	1	-	-	-	1	1	1	1	1	1	1

## Essential Box H4



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55718EBKM	12	-	-	70034328	8 727900 700343	-	8727900700350	ECE	5

### Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A	Fuse 15A	Fuse 20A
Quantity	-	1	-	-	1	1	1	1	1	1	1

## Essential Box H7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55719EBKM	12	-	-	70036728	8 727900 700367	-	8727900700374	ECE	5

### Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A	Fuse 15A	Fuse 20A
Quantity	-	-	1	-	1	1	1	1	1	1	1

## Essential Box H1/H7



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55720EBKM	12	-	-	70038128	8 727900 700381	-	8727900700398	ECE	5

### Content

Lamp type	H1	H4	H7	R2	P21W	P21/5W	PY21W	W5W	Fuse 10A	Fuse 15A	Fuse 20A
Quantity	1	-	1	-	1	1	1	1	1	1	1

## 24V spare kits

### MiniKit H4 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55554SKMDKM	24	-	-	69586130	8 727900 695861	-	8727900695885	ECE	10

#### Content

Lamp type	H4	H7	P21W	R5W	R10W	C5W	T4W	Fuse15A	Fuse 20A	Fuse 30A
Quantity	1	-	1	1	1	1	1	1	1	1

### MiniKit H7 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55555SKMDKM	24	-	-	69590830	8 727900 695908	-	8727900695939	ECE	10

#### Content

Lamp type	H4	H7	P21W	R5W	R10W	C5W	T4W	Fuse15A	Fuse 20A	Fuse 30A
Quantity	-	1	1	1	1	1	1	1	1	1

### MaxiKit H4 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55559LKMDKM	24	-	-	69684494	8 727900 696844	-	8727900696851	ECE	4

#### Content

Lamp type	H4	P21W	P21/5W	PY21W	R5W	R10W	C5W	W5W	T4W	Fuse 10A	Fuse 15A	Fuse 20A	Fuse 30A
Quantity	2	2	2	1	3	2	2	1	1	2	2	2	2

### MaxiKit H7 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55560LKMDKM	24	-	-	69686894	8 727900 696868	-	8727900696875	ECE	4

#### Content

Lamp type	H7	P21W	P21/5W	PY21W	R5W	R10W	C5W	W5W	T4W	Fuse 10A	Fuse 15A	Fuse 20A	Fuse 30A
Quantity	2	2	2	1	3	2	2	1	1	2	2	2	2

### MaxiKit H1/H7 MasterDuty



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
55561LKMDKM	24	-	-	69688294	8 727900 696882	-	8727900696899	ECE	4

#### Content

Lamp type	H1	H7	P21W	P21/5W	PY21W	R5W	R10W	C5W	W5W	T4W	Fuse 10A	Fuse 15A	Fuse 20A	Fuse 30A
Quantity	1	1	2	2	1	3	2	2	1	1	2	2	2	2



# Headlight restoration kit



## Safety

## Restores headlight lenses to like-new condition!

- Less glare and up to 100% brighter lenses
- Provides safer night-time driving
- Removes haze and yellowing from harmful UV-rays and dirt
- Professional results without power tools in 30 minutes
- High-quality and economical
- 2-year UV-protection guaranteed

Removes the fading and yellowing of headlight lenses and restores them to their original state of **transparency** for **greater safety**. Headlight lenses fade and oxidize from constant exposure to the elements and become scratched due to impacts.



Before

After



### Headlight restoration kit



Ordering number	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
HRK00XM	39976931	8 727900 399769	-	8727900399776	-	6

# Xenon



# Car and truck

lighting





# Which xenon lamp do you need?



## Experience more light

Ideal for replacement

**Xenon Vision**

Standard

Xenon Vision

Beam performance

Light color

Up to **4300 K**

Standard: 4150 K

Available in D1S, D1R, D2S, D2R, D3S, D3R, D4S, D4R, D5S

Up to **150% more vision\***

**Xenon X-tremeVision gen2**

Standard

Xenon X-tremeVision gen2

Beam performance

Light color

Up to **4800 K**

Standard: 4150 K

Available in D1S, D2S, D2R, D3S, D4S

## Light that lasts

Peace of mind **4 + 3** years warranty

**Xenon LongerLife\*\***

4 years warranty +3

Beam performance

Lifetime

Up to **7 years**

Available in D1S, D2S, D2R

## Enjoy your passion

Homogeneous **white** LED effect

**Xenon WhiteVision gen2**

Standard

Xenon WhiteVision gen2

Beam performance

Light color

Up to **5000 K**

Standard: 4150 K

Available in D1S, D2S, D2R, D3S

Images for illustration purposes only

\* Compared to the minimum legal standard (except for D2R that provides up to 20% more vision)

\*\* Not available in all countries, please contact your sales representative





# Experience more light

## Xenon Vision

### Ideal for replacement

- **Single-lamp replacement technology: new lamp matches color temperature of the unchanged one**
- Ideal economical solution for **a single-lamp replacement**
- **Homologated 4300K**

Philips Xenon Vision allows drivers to replace a single burned-out lamp while **matching** the **color** of the unchanged one.



Standard



Xenon Vision

Available in C1 and S1 packaging



Available in



# Experience more light



## Xenon X-tremeVision gen2

### Our brightest xenon lamp

- Optimal light performance
- Up to 150% more vision\*
- Maximum safety and visibility
- Designed for demanding drivers

Philips Xenon X-tremeVision gen2 is the latest development in **Xenon technology**. It offers the **most powerful** beam with light emission pushed to the limit. This means outstanding light performance with a unique light setting for **optimal driving comfort**.

[www.philips.com/xenongen2](http://www.philips.com/xenongen2)

\*Compared to the minimum legal standard (except for D2R that provides up to 20% more vision).



Standard



Xenon X-tremeVision gen2

Available in C1 and S1 packaging



Available in





# Light that lasts

**4** years warranty **+3**

## Xenon LongerLife

### Peace of mind with the longest guarantee

Equip your car with Philips Xenon LongerLife lamps and you can drive up to 7 years without the worry of lamp failures. Philips Xenon LongerLife lamps automatically come with a **4-year warranty**. Register your purchase online and you can extend this warranty by an **extra 3 years**.

Available in C1 and S1 packaging



Available in



Car and truck lighting

### 3 years extra warranty for free in 3 simple steps

Register online at [www.philips.co.uk/xenonwarranty](http://www.philips.co.uk/xenonwarranty), within 30 days of purchase



**1** Connect to [www.philips.co.uk/xenonwarranty](http://www.philips.co.uk/xenonwarranty) to confirm you've purchased a genuine Philips product by verifying the security code located on the certificate of authenticity sticker.



**2** Fill in your personal information, indicate your point-of-purchase and provide the proof-of-purchase.



**3** Print and save your 7-year warranty certificate together with your proof-of-purchase.



You can now drive safely and worry-free for 7 years!



Enjoy your passion

## Xenon WhiteVision gen2

### Ultimate white LED effect

- Intense homogeneous bright white light
- Perfect match with LED lighting on your car
- Up to 5000 K white light on the road
- Up to 120% more vision\*
- 100% road legal

Philips Xenon WhiteVision gen2 lamps create an **intense white look** of your car and produce brighter, homogeneous white light on the road.

[www.philips.com/xenongen2](http://www.philips.com/xenongen2)

\*Compared to the minimum legal standard (except for D2R that provides up to 20% more vision).



Standard



Xenon WhiteVision gen2

Available in C1 and S1 packaging



Available in



D1S



D2S



D2R



D3S



# Our **pro-active solution** against xenon lamp **piracy**

## COA Certificate of authenticity

**Counterfeit** Philips xenon lamps are becoming increasingly available through online and offline distribution channels.

These counterfeit lamps are **poor imitations** of **inferior quality**.

Buying, selling or being in possession of counterfeit products is illegal.



To **protect** our customers and all consumers from counterfeit Philips lighting products, we've created a **pro-active solution** using unique, **state-of-the-art** technology.

Philips **Certificate of Authenticity (COA)** is available on **every xenon lamp package you order**.

Using the **Security code**, professionals can verify the **authenticity** of the Philips

product on a dedicated, fully secure internet platform. Professionals can either scan the QR code or go to **www.philips.com/original**.

We are committed to helping **protect** our customers from poor imitations of inferior quality that may damage your vehicle or result in personal injury.

**Always ensure that you are buying genuine Philips products.**

### Visual verification



### Online verification

**1** Connect to [www.philips.com/original](http://www.philips.com/original) follow the simple instructions:

**2** Type in the unique security code

**3** Type in the label ID number

Retype the code again to make sure it's been entered correctly. Additional rejection of code entry may indicate this product is counterfeit.



## D1S Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85415VIS1	85	35	PK32d-2	36489733	8 727900 364897	-	8727900364903	ECE	2
85415VIC1	85	35	PK32d-2	36473633	8 727900 364736	-	8727900364743	ECE	2

## D1S X-tremeVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85415XV2S1	85	35	PK32d-2	37697533	8 727900 376975	-	8727900376982	ECE	2
85415XV2C1	85	35	PK32d-2	37701933	8 727900 377019	-	8727900377026	ECE	2

## D1S LongerLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85415SYS1	85	35	PK32d-2	37246533	8 727900 372465	-	8727900372472	ECE	2
Ordering codes for Germany, Austria, Switzerland, Netherlands, Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom									
85415SYC1	85	35	PK32d-2	37516933	8 727900 375169	-	8727900375176	ECE	2
Ordering codes for Germany, Austria, Switzerland, Netherlands									
85415SYC1	85	35	PK32d-2	37250233	8 727900 372502	-	8727900372519	ECE	2
Ordering codes for Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom									
85415SYC1	85	35	PK32d-2	37522033	8 727900 375220	-	8727900375237	ECE	2
Ordering codes for Central Europe (Poland, Romania, Czech Republic) and other East European countries									

## D1S WhiteVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85415WHV2S1	85	35	PK32d-2	36072133	8 727900 360721	-	8727900377248	ECE	2
85415WHV2C1	85	35	PK32d-2	37725533	8 727900 377255	-	8727900377262	ECE	2

## D1R Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85409VIC1	85	35	PK32d-3	36475033	8 727900 364750	-	8727900364767	ECE	2

## D2S Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85122VIS1	85	35	P32d-2	36491033	8 727900 364910	-	8727900364927	ECE	2
85122VIC1	85	35	P32d-2	36477433	8 727900 364774	-	8727900364781	ECE	2

## D2S X-tremeVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85122XV2S1	85	35	P32d-2	37703333	8 727900 377033	-	8727900377040	ECE	2
85122XV2C1	85	35	P32d-2	37707133	8 727900 377071	-	8727900377088	ECE	2

Philips Xenon LongerLife lighting is not available in all countries. For more information, please contact your Philips representative.

## D2S LongerLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85122SYS1	85	35	P32d-2	37254033	8 727900 372540	-	8727900372557	ECE	2
Ordering codes for Germany, Austria, Switzerland, Netherlands, Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom									
85122SYC1	85	35	P32d-2	37518333	8 727900 375183	-	8727900375190	ECE	2
Ordering codes for Germany, Austria, Switzerland, Netherlands									
85122SYC1	85	35	P32d-2	37244133	8 727900 372441	-	8727900372458	ECE	2
Ordering codes for Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom									
85122SYC1	85	35	P32d-2	37524433	8 727900 375244	-	8727900375251	ECE	2
Ordering codes for Central Europe (Poland, Romania, Czech Republic) and other East European countries									

## D2S WhiteVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85122WHV2S1	85	35	P32d-2	37727933	8 727900 377279	-	8727900377286	ECE	2
85122WHV2C1	85	35	P32d-2	37729333	8 727900 377293	-	8727900377309	ECE	2

## D2R Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85126VIS1	85	35	P32d-3	36493433	8 727900 364934	-	8727900364941	ECE	2
85126VIC1	85	35	P32d-3	36479833	8 727900 364798	-	8727900364804	ECE	2

## D2R X-tremeVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85126XV2S1	85	35	P32d-3	37709533	8 727900 377095	-	8727900377101	ECE	2
85126XV2C1	85	35	P32d-3	37711833	8 727900 377118	-	8727900377125	ECE	2

## D2R LongerLife



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85126SYS1	85	35	P32d-3	37248933	8 727900 372489	-	8727900372496	ECE	2
Ordering codes for Germany, Austria, Switzerland, Netherlands, Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom									
85126SYC1	85	35	P32d-3	37520633	8 727900 375206	-	8727900375213	ECE	2
Ordering codes for Germany, Austria, Switzerland, Netherlands									
85126SYC1	85	35	P32d-3	37252633	8 727900 372526	-	8727900372533	ECE	2
Ordering codes for Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom									
85126SYC1	85	35	P32d-3	37526833	8 727900 375268	-	8727900375275	ECE	2
Ordering codes for Central Europe (Poland, Romania, Czech Republic) and other East European countries									

## D2R WhiteVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
85126WHV2S1	85	35	P32d-3	37731633	8 727900 377316	-	8727900377323	ECE	2
85126WHV2C1	85	35	P32d-3	37733033	8 727900 377330	-	8727900377347	ECE	2

Philips Xenon LongerLife lighting is not available in all countries. For more information, please contact your Philips representative.

## D3S Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42403VIS1	42	35	PK32d-5	36495833	8 727900 364958	-	8727900364965	ECE	2
42403VIC1	42	35	PK32d-5	36481133	8 727900 364811	-	8727900364828	ECE	2

## D3S X-tremeVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42403XV2S1	42	35	PK32d-5	37713233	8 727900 377132	-	8727900377149	ECE	2
42403XV2C1	42	35	PK32d-5	37717033	8 727900 377170	-	8727900377187	ECE	2

## D3S WhiteVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42403WHV2S1	42	35	PK32d-5	37735433	8 727900 377354	-	8727900377361	ECE	2
42403WHV2C1	42	35	PK32d-5	37737833	8 727900 377378	-	8727900377385	ECE	2

## D3R Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42306VIC1	42	35	PK32d-6	36483533	8 727900 364835	-	8727900364842	ECE	2

## D4S Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42402VIC1	42	35	P32d-5	36485933	8 727900 364859	-	8727900364866	ECE	2

## D4S X-tremeVision gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42402XV2S1	42	35	P32d-5	37719433	8 727900 377194	-	8727900377200	ECE	2
42402XV2C1	42	35	P32d-5	37721733	8 727900 377217	-	8727900377224	ECE	2

## D4R Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
42406VIC1	42	35	P32d-6	36487333	8 727900 364873	-	8727900364880	ECE	2

## D5S Vision



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12410C1	12	25	PK32d-7	36981633	8 727900 369816	-	8727900369823	ECE	2





# LED retrofit



# Car and truck

lighting





# Which **LED** lamp do you need?



## The next level of white light



**2** years **+1** extended warranty


### Ultinon LED



#### Beam performance



#### Light color



#### Lifetime



#### Available in

LED-HL [≈H4], [≈H7]  
LED-FOG [≈H8/H11/H16]

New

## Brighter. Whiter. Stronger.



LUXEON  
Altilon  
OEM LED\*

**2** years **+3** extended warranty


### X-tremeUltinon LED



#### Beam performance



#### Light color



#### Lifetime



#### Available in

LED-HL [≈H1], [≈H4], [≈H7], [≈HB3/4], [≈H11], [≈HIR2]  
LED-FOG [≈H8/H11/H16]

Images for illustration purposes only.

\* Applies to X-tremeUltinon LED-HL [≈H4], [≈H7] and LED-FOG [≈H8/H11/H16].

\*\* Compared to the minimum legal standard for halogen bulbs. Up to +200% for X-tremeUltinon LED-HL [≈HB3/4], [≈H1], [≈H11], and LED-HL [≈HIR2] types.



It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.

[philips.com/automotiveLED](http://philips.com/automotiveLED)






LED retrofit lighting for cars and trucks


LED



# Which LED for which function?



## X-tremeUltinon LED – Original automotive performance in LED



<td> <td> <td> </td></td></td>	<td> <td> </td></td>	<td> </td>	
<td> <td> <td> </td></td></td>	<td> <td> </td></td>	<td> </td>	

## Ultinon LED – The next level of white light



<td> <td> <td> <td> <td> <td> </td></td></td></td></td></td>	<td> <td> <td> <td> <td> </td></td></td></td></td>	<td> <td> <td> <td> </td></td></td></td>	<td> <td> <td> </td></td></td>	<td> <td> </td></td>	<td> </td>	
--	--	--	--------------------------------	----------------------	------------	--

## CANbus adapter for optimal control



CANbus LED-HL [≈H4]	CANbus LED-HL [≈H7]	CANbus 5W	CANbus LED-FOG [≈H8/H11/H16]	Smart CANbus 21W	CANbus 5W	CANbus 5W



It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.



Glove compartment lights	Rear position/parking lights	Rear indicators	Rear fog lights	Trunk lights	License plate lights	3rd stop light	Stop lights	Reversing light

### X-tremeUltinon LED – Original automotive performance in LED

 LED-T10 [≈W5W]	 LED-T10 [≈W5W]	 LED-AMBER [≈PY21W]	 LED-RED [≈P21W]	 LED-T10 [≈W5W]	 LED-T10 [≈W5W]	 LED-RED [≈P21W]	 LED-RED [≈P21W], [≈P21/5W]	 LED-WHITE [≈P21W]
 LED-Fest 30/38/43 mm	 LED-(T20)-RED [≈P21/5W], [≈W21/5W]	 LED-AMBER [≈WY21W]	 LED-T20-RED [≈W21W]	 LED-Fest 30/38/43 mm	 LED-Fest 30/38/43 mm	 LED-T20-RED [≈W21W]	 LED-T20-RED [≈W21W], [≈W21/5W]	 LED-T20-WHITE [≈W21W]

### Ultinon LED – The next level of white light

 LED-T10 [≈W5W]	 LED-RED [≈P21W]	 LED-AMBER [≈PY21W]	 LED-RED [≈P21W]	 LED-T10 [≈W5W]	 LED-T10 [≈W5W]	 LED-RED [≈P21W]	 LED-RED [≈P21W], [≈P21/5W]	 LED-WHITE [≈P21W]
 LED-Fest 30/38/43 mm	 LED-T20-RED [≈W21W]	 LED-AMBER [≈WY21W]	 LED-T20-RED [≈W21W]	 LED-Fest 30/38/43 mm	 LED-T20-RED [≈W21W]	 LED-T20-RED [≈W21W], [≈W21/5W]	 LED-T20-WHITE [≈W21W]	

### CANbus adapter for optimal control

 CANbus 5W	 CANbus 5W	 Smart CANbus 21W	 CANbus 21W	 CANbus 5W	 CANbus 5W	 CANbus 21W	 CANbus 21W	 CANbus 21W
---------------	---------------	----------------------	----------------	---------------	---------------	----------------	----------------	----------------

\*LED CANbus adapter 21W included in the pack

LED retrofit lighting for cars and trucks

LED

# Ultinon LED

## The next level of white light

- Get up to **+160%** brighter light\* for superior visibility
- Up to **6 200 K** color temperature for **pure white light**
- **Philips SafeBeam** technology for glare-free driving
- Up to **8-year lifetime**
- **Extended warranty** up to **3 years**.

\*Compared to the minimum legal standard for halogen bulbs



Standard halogen

Ultinon LED

Available in X2 packaging



Available in



LED-HL [=H4]



LED-HL [=H7]



LED-FOG [=H8/H11/H16]

# X-tremeUltinon LED

## Brighter. Whiter. Stronger.

- Up to **+200%** brighter light\* for superior visibility
- Up to **5 800 K** color temperature for **arctic white light**
- Unique Philips heat management technologies: **AirCool, AirFlux, Ceralight\*\***
- **Philips SafeBeam** technology for glare-free driving
- Up to **12-year lifetime**
- **Extended warranty** up to **5 years**.

\*Compared to the minimum legal standard for halogen bulbs  
 \*\*Ceralight: cooling system for LED-T10 using ceramic material for enhanced heat and vibration resistance



Standard halogen

X-tremeUltinon LED

Available in X2 packaging



Available in



LED-HL [=H1]



LED-HL [=H11]



LED-HL [=HB3/HB4]



LED-HL [=HIR2]



# X-tremeUltinon LED gen2

## Unique with automotive OEM LED

- **Exclusive** automotive LED technology thanks to Lumileds LUXEON Altilon LED chips
- Up to **250% brighter homogeneous** light\*
- Up to **5 800 K** color temperature for **cool white light**
- **Optimal spectrum** for best road sign visibility
- **IP65:** dust tight and water resistant
- Unique Philips heat management technologies
- **Philips SafeBeam** technology for glare-free driving
- Up to **12-year lifetime**
- **Extended warranty** up to **5 years**.

\*Compared to the minimum legal standard for halogen bulbs



Standard halogen



X-tremeUltinon LED gen2

Available in X2 packaging



Available in



LED-HL [H4]



LED-HL [H7]



LED-FOG [H8/H11/H16]


# CANbus LED adapter

## Better fit for LED retrofit bulbs

- **Prevent inaccurate dashboard warnings**
- **Easy installation**
- No flickering effect\*
- Fully functional high beam indicator\*\*

In the installation and operation of LED retrofit bulbs, users can run across challenges. Philips CANbus LED adapters ensure a better fit for their peace of mind.

\*Not applicable for H7  
\*\*For H4 only




Available in X2 packaging



Available in



LED-CANBUS for  
LED-HL [H4]  
LED-HL [H7]  
LED-HL [H8/H11/H18]



LED-CANBUS [5W]  
LED-CANBUS [21W]





## 12V LED retrofit headlighting

### LED-HL [≈H1] X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11258XUX2	12	25	P14.5s	06030331		-	8719018060310	-	6

### LED-HL [≈H4] X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11342XUWX2	12	22	P43t-38	06012931		-	8719018060136	-	6

### LED-HL [≈H4] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11342ULWX2	12	15	P43t-38	39859531		-	8727900398601	-	6

### LED-HL [≈H7] X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11972XUWX2	12	25	PX26d	06014331		-	8 719 018 060 150	-	6

### LED-HL [≈H7] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11972ULWX2	12	14	PX26d	39861831		-	8727900398625	-	6

### LED-HL [≈H11] X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11362XUX2	12	22	PGJ19-2	05202531		-	8719018052032	-	6

### LED-HL [≈HB3/HB4] X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11005XUWX2	12	25	P20d/P22d	39875531		-	8727900398762	-	6

### LED-FOG [≈H8/H11/H16] X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11366XUWX2	12	15.5	PGJ19-1/2/3	06016731		-	8 719 018 060 174	-	6

### LED-FOG [≈H8/H11/H16] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11366ULWX2	12	10	PGJ19-1/2/3	39863231		-	8727900398649	-	6

### LED-HL [≈HIR2] X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11012XUX2	12	25	PX22d	05200131		-	8719018052018	-	6









## 12V LED retrofit signaling and interior lighting

### LED-FEST 30 mm 4000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
129404000KX1	12	1	SV8,5-8	39714730	8 727900 397147	-	8727900397154	-	10

### LED-FEST 30 mm 6000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
129416000KX1	12	1	SV8,5-8	39716130	8 727900 387223	-	8727900387230	-	10

### LED-FEST 30 mm 6000 K Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11860ULWX1	12	0.6	SV8,5-8	05037330	8 719018 050373	-	8719018050380	-	10

### LED-FEST 38 mm 4000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
128584000KX1	12	1	SV8,5-8	39706230	8 727900 703412	-	8727900703405	-	10

### LED-FEST 38 mm 6000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
128596000KX1	12	1	SV8,5-8	39708630	8 727900 703399	-	8727900703382	-	10

### LED-FEST 38 mm 6000 K Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11854ULWX1	12	0.6	SV8,5-8	05039730	8 719018 050397	-	8719018050403	-	10

### LED-FEST 43 mm 4000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
129454000KX1	12	1	SV8,5-8	39710930	8 727900 397109	-	8727900397116	-	10

### LED-FEST 43 mm 6000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
129466000KX1	12	1	SV8,5-8	39712330	8 727900 383416	-	8727900383423	-	10

### LED-FEST 43 mm 6000 K Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11864ULWX1	12	0.6	SV8,5-8	05041030	8 719018 050410	-	8719018050427	-	10

## LED-T10 [≈W5W] 4000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
127994000KX2	12	0.9	W2,1x9,5d	39594530	8 727900 395945	-	8727900395952	-	10

## LED-T10 [≈W5W] 4000 K Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11961ULW4X2	12	0.6	W2,1x9,5d	5083030	8 719018 050830	-	8719018050847	-	10

## LED-T10 [≈W5W] 6000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
127996000KX2	12	0.9	W2,1x9,5d	39596930	8 727900 395969	-	8727900395976	-	10

## LED-T10 [≈W5W] 6000 K Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11961ULWX2	12	0.6	W2,1x9,5d	05031130	8 719018 050311	-	8719018050328	-	10

## LED-T10 [≈W5W] 8000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
127998000KX2	12	0.9	W2,1x9,5d	39598330	8 727900 395983	-	8727900395990	-	10

## 12V LED retrofit signaling lighting

### LED-RED [≈P21/5W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11499XURX2	12/24	0.3/2.2	BAY15d	05151630	8 719018 051516	-	8719018051523	-	10

### LED-RED [≈P21/5W] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11499ULRX2	12	2.7	BAY15d	05025030	8 719018 050250	-	8719018050267	-	10

### LED-RED [≈P21W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498XURX2	12/24	2.3	BA15s	05157830	8 719018 051578	-	8719018051585	-	10

### LED-RED [≈P21W] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498ULRX2	12	2.7	BA15s	05023630	8 719018 050236	-	8719018050243	-	10

## LED-WHITE [≈P21W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498XUWX2	12/24	2.7	BA15S	05145530	8 719018 051455	-	8719018051486	-	10

## LED-WHITE [≈P21W] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498ULWX2	12	1.95	BA15s	05035930	8 719018 050359	-	8719018050366	-	10

## LED-T20-WHITE [≈W21W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065XUWX2	12/24	1.7	W3x16d	05146230	8 719018 051462	-	8719018051479	-	10

## LED-T20-WHITE [≈W21W] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065ULWX2	12	1.95	W3x16d	05033530	8 719018 050335	-	8719018050342	-	10

## LED-T20-WHITE [≈W21/5W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11066XUWX2	12/24	0.3/1.8	w3x16q	05149330	8 719018 051493	-	8719018051509	-	10

## LED-T20-RED [≈W21W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065XURX2	12V/24V	2.1	W3x16d	05153030	8 719018 051530	-	8719018051547	-	10

## LED-T20-RED [≈W21W] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065ULRX2	12	2.7	W3x16d	05027430	8 719018 050274	-	8719018050281	-	10

## LED-T20-RED [≈W21/5W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11066XURX2	12/24	0.3/2.2	W3x16q	05155430	8 719018 051554	-	8719018051561	-	10

## LED-T20-RED [≈W21/5W] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11066ULRX2	12	2.7	W3x16q	05029830	8 719018 050298	-	8719018050304	-	10

## LED-T20-AMBER [≈WY21W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065XUAXM	12	1.8	W3x16d	05161530	8 719018 051615	-	8719018051622	-	10

## LED-T20-AMBER [≈WY21W] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065ULAX2	12	0.75	W3x16d	05075530	8 719018 050755	-	8719018050762	-	10

## LED-AMBER [≈PY21W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498XUAXM	12	1.8	BAU15s	05159230	8 719018 051592	-	8719018051608	-	10

## LED-AMBER [≈PY21W] Ultinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498ULAX2	12	0.75	BAU15s	05073130	8 719018 050731	-	8719018050748	-	10

## CANbus LED adapter

### LED-CANbus [≈5W]



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
12956X2	12	5	-	39722230	8 727900 397222	-	8727900397239	-	10

### LED-CANbus [≈21W]



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
18957X2	12	21	-	39587730	8 727900 395877	-	8727900395884	-	10

### LED-CANbus for LED-HL [≈H4]



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
18960C2	12	10	-	39809030	8 727900 398090	-	8727900398106	-	10

### LED-CANbus for LED-HL [≈H7]



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
18952C2	12	10	-	05064930	8 719018 050649	-	8719018050656	-	10

### LED-CANbus for LED-FOG [≈H8/H11/H16]



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
18954C2	12	10	-	05066330	8 719018 050663	-	8719018050670	-	10

## LED connector rings for LED-HL

### Type B



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11172BX2	-	-	-	05121930	8 719018 051219	-	8719018051226	-	20

### Type C



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11172CX2	-	-	-	05123330	8 719018 051233	-	8719018051240	-	20



## 24V LED retrofit interior and signaling lighting

### LED-FEST 38 mm 6000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
249446000KX1	24	1	SV8.5	39718530	8 727900 384185	-	8727900384192	-	10

### LED-FEST 43 mm 6000 K X-tremeUltinon



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
249466000KX1	24	1	SV8.5	39720830	8 727900 397208	-	8727900397215	-	10

### LED-WHITE [≈P21W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498XUWX2	12/24	2.7	BA15S	05145530	8 719018 051455	-	8719018051486	-	10

### LED-T20-WHITE [≈W21W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065XUWX2	12/24	1.7	W3x16d	05146230	8 719018 051462	-	8719018051479	-	10

### LED-T20-WHITE [≈W21/5W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11066XUWX2	12/24	0.3/1.8	W3x16q	05149330	8 719018 051493	-	8719018051509	-	10

### LED-RED [≈P21W] X-tremeUltinon gen2




Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11498XURX2	12/24	2.3	BA15s	05157830	8 719018 051578	-	8719018051585	-	10

### LED-RED [≈P21/5W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11499XURX2	12/24	0.3/2.2	BAY15d	05151630	8 719018 051516	-	8719018051523	-	10

### LED-T20-RED [≈W21W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11065XURX2	12V/24V	2.1	W3x16d	05153030	8 719018 051530	-	8719018051547	-	10

### LED-T20-RED [≈W21/5W] X-tremeUltinon gen2



Ordering number	V	W	Base	GOC	EAN1	EAN2	EAN3	ECE	Packing quantity
11066XURX2	12/24	0.3/2.2	W3x16q	05155430	8 719018 051554	-	8719018051561	-	10

# Lighting technology explained

[www.philips.com/automotive](http://www.philips.com/automotive)

## ■ AirCool technology

Smart cooling system that diverts heat away from the light's critical components (active cooling with a fan).

## ■ AirFlux technology

Optimal thermal management resulting in longer lifetime (passive cooling using heat sink).

## ■ Asymmetrical beam pattern

An offset beam pattern for low-beam applications. Provides a longer beam in the lane of traffic, which avoids blinding oncoming traffic.

## ■ Automotive Grade Quality

The Philips Automotive Grade Quality products are designed and developed following strict quality control processes (including applicable ISO norms), leading to consistently high production standards.

## ■ Ballast

The electronic driver that controls a xenon HID bulb.

## ■ Base

Bottom part of the bulb which ensures a proper mechanical and electrical connection with the lamp unit of the car. Its precision is important for a correct beam pattern.

## ■ Board voltage

Electrical voltage in the board net of the vehicle. In cars, the operational voltage at the bulb connector typically varies between 13 and 14 volts (V). The official test voltage for halogen headlight bulbs is 13.2V according to ECE R37. For trucks with a 24V board net the test voltage is 28V. The board voltage has a significant impact on filament bulb lifetime. In general, a 5% voltage increase reduces the lifetime by 50%.

## ■ Burner

Burner is the glass part of a halogen or xenon HID bulb in which the light emission is generated. It consists of hard or quartz glass and contains the filament and the two electrodes.

## ■ Candela (cd)

Unit of luminous intensity that measures the amount of luminous power emitted by a light source in a particular direction.

## ■ CeraLight

Cooling system using ceramic material for enhanced heat and vibration resistance.

## ■ Color temperature

Thermal measure for light color. Derived from the color emitted by a "black body" which is heated up to a certain temperature (see also Kelvin).

## ■ Cut-off zone

The line between the bright and dark zones of low beam light. Above the cut-off zone the amount of light is limited in order to avoid blinding oncoming traffic.

## ■ D(...)

Nomenclature for xenon HID bulbs where **D** stands for "discharge." Available technical types: **D1S, D1R, D2S, D2R, D3S, D3R, D4S, D4R** and **D5S**.

**D1** and **D2** First bulbs introduced in 1991

**D3** and **D4** Mercury-free bulbs that replace D1 and D2

For D1 and D3, the electronic high-voltage starter is already integrated in the bulb base. The **S** type is used with projector (lens) systems. Version **R** is used in open reflectors and features an additional coating on the outer tube (pinstripe) which blocks out some areas to avoid glare. The **D5S** is a 25-watt bulb with integrated starter and integrated ballast.

## ■ Discharge bulb

The correct, technical term of the so-called xenon bulb is **high-intensity discharge** bulb. The light is emitted by an electric arc which is produced between two electrodes. **See also** HID and xenon light.

## ■ DOT

The United States Department of Transportation which oversees federal highway, air, railroad, maritime and other transportation administration functions. It fulfills a role similar to the Economic Commission for Europe (ECE).

## ■ DRL

Daytime Running Lights.

## ■ ECE

Economic Commission for Europe. One of five regional commissions of the United Nations (UN) based in Geneva that contributes to enhancing the effectiveness of the UN through the regional implementation of outcomes of global UN Conferences and Summits. The ECE is responsible for harmonizing technical specifications for vehicles whose regulations are also mandatory in many countries outside Europe.

## ■ ECE R

This stands for the ECE Regulation.

Examples for vehicle lighting:

**R37** Filament lamps

**R99** Gas-discharge light sources

**R48** Installation of lighting and light-signaling devices

## ■ Electric arc

The connecting luminous discharge between the two electrodes of a xenon HID bulb. This is similar in principle to a bolt of lightning. The electric arc is created by the high-voltage starter and stabilized and controlled by the ballast.

## ■ Electrodes

Electrical conductors which are positioned opposite each other in the vessel of a xenon gas-discharge bulb. The electric arc, which emits light, is produced between the electrodes.

## ■ EMI conform

Automotive standards of electromagnetic interference.

## ■ E-mark

The ECE mark of approval. The digit following the "E" indicates in which country the approval has been granted. For example: E1 indicates Germany and E2 indicates France. An approval granted by one ECE member is valid for all member states and is typically adopted by national regulations. Single minor deviations are possible.

### ■ Festoon

A tube-shaped bulb with contacts at each end such as C5W, which is commonly used for interior and license plate lighting.

### ■ Filament

A coiled tungsten wire that emits light.

### ■ H(...)

Nomenclature for halogen bulbs. H = halogen.

The bulbs are numbered consecutively.

The most common types are:

**H1** First halogen bulb (single filament).

**H4** Double filament for both low beam and high beam application in one headlamp unit.

**H7** Most common halogen bulb in Europe for low beam, high beam, and fog lighting.

### ■ Halogen

A gas that is used to create the halogen cycle process in a light bulb. During operation the tungsten molecules evaporate from the tungsten. In the cycle process they combine with the halogen molecules and fall back to the wire. This extends the lifetime of a bulb and allows operation at a higher intensity. Halogen bulbs contain a high-pressure halogen filling. Non-halogen incandescent bulbs often use a vacuum.

### ■ HB(...)

ECE name of original North American bulb types which were approved for use in Europe as well. For example:

HB3 refers to 9005 and HB4 refers to 9006.

### ■ Hg

Symbol for mercury (Latin: hydrargyrum). Xenon bulb types D1 and D2 still contain approximately one third of the amount of mercury as a normal domestic energy-saving bulb. D3, D4 und D5 are completely mercury free.

### ■ HID

High Intensity Discharge. Correct technical name for a so-called xenon bulb.

**See also** gas-discharge bulb, xenon light, xenon system.

### ■ High-voltage starter

Creates high-voltage pulses of approximately 20 000 volts to ignite the electric arc in a xenon HID bulb.

### ■ HiPerVision

Very compact signaling-bulb range with high-precision filaments and a long lifetime. For use in signaling lights, fog lamps, rear and daytime running lights.

### ■ Illuminance (lux)

Contrary to luminous flux (lumen), which is a measure of the total amount of light emitted by a light source, illuminance describes the amount of luminous flux per unit area, such as on the road. This is measured with a lux meter.

### ■ IP65 certification

Dust ingress and splash water protection improving durability.

### ■ Kelvin (K)

A unit of measure of temperature based upon an absolute scale whereby zero (minus 273° C) represents the point where all thermal motion ceases. In lighting, however, this is a measure of color temperature. The higher the color temperature, the whiter and cooler the light appears.

### ■ LED

Light Emitting Diode.

### ■ Lifetime

Statistical data that indicate the failure rate of a percentage of bulbs operated at a specific voltage over a certain period of time. Common lifetime data indication:

**B3** Time when statistically 3% of the test samples have failed

**TC** Time when 63% of the test samples have failed.

### ■ Luminance

The intensity of light emitted from a surface per unit area in a given direction from, for example, the filament or the electric arc of a xenon HID bulb. An important indicator of the amount of light a headlamp unit provides on the road. The unit is candela/m<sup>2</sup> (cd/m<sup>2</sup>).

### ■ Lumen (lm)

Unit of luminous flux.

### ■ Luminous flux (lumen)

The total amount of light that is emitted by a light source in all directions.

### ■ Lux (lx)

Unit of illuminance. 1 Lux = 1 lm/m<sup>2</sup>.

**See also** Illuminance.

### ■ Lux meter

Illuminance measuring device.

### ■ LUXEON

Lumileds LED chips technology.

### ■ Pb

Symbol for lead (Latin: plumbum).

All Philips automotive bulbs are **lead-free**.

### ■ Quartz glass

Temperature and pressure resistant glass for halogen and xenon HID bulbs. The glass also has a special coating to block out harmful ultraviolet (UV) light.

### ■ SafeBeam technology

Technology that projects the light exactly where you need it on the road.

### ■ Tungsten

Filament and electrode material.

### ■ UV-block

Ultraviolet (UV) rays blocking glass absorbs the UV light created by the filament or the electric arc. UV block is mandatory for all ECE complying car bulbs because UV light can damage the plastic cover of the headlamp.

**See also** Quartz glass.

### ■ Wedge base

Bulb with a glass base, such as W5W. Mainly used for position lights, side indicators and interior lighting.

### ■ Xenon (Xe)

One of the noble gases. Commonly used to refer to HID bulbs.

### ■ Xenon light

Headlights with HID bulbs.

**See also** D(...), Discharge bulb, HID.

### ■ Xenon system

A complete xenon system consists of the HID bulb, the high-voltage starter and the electronic ballast which controls the electric arc.

# Specimen packaging

Discover the perfect anti-theft solution for your store.



VP VisionPlus



LLECO LongLife  
EcoVision



XV X-tremeVision



WHV WhiteVision



RV RacingVision



VI Xenon Vision



XV2 Xenon X-tremeVision gen2



WHV2 Xenon WhiteVision gen2



SY Xenon LongerLife

## Ordering information

Description	Ordering number	GOC	EAN1	EAN3
<b>12V halogen</b>				
H1 VP SF	56252SF	39991228	8727900399912	8727900399929
H4 VP SF	56293SF	39010028	8727900390100	8727900390117
H7 VP SF	56295SF	39012428	8727900390124	8727900390131
H1 VP BF	56279BF	26949730	8718696269497	8718696269503
H4 VP BF	56278BF	26947330	8718696269473	8718696269480
H7 VP BF	56277BF	26945930	8718696269459	8718696269466
H1 LLECO SF	56261SF	26909128	8718696269091	8718696269107
H4 LLECO SF	56292SF	39002528	8727900390025	8727900390032
H7 LLECO SF	56294SF	39004928	8727900390049	8727900390056
H1 LLECO BF	56273BF	26939830	8718696269398	8718696269404
H4 LLECO BF	56270BF	26933630	8718696269336	8718696269343
H7 LLECO BF	56268BF	26927530	8718696269275	8718696269282
H1 XV+ SF	56400SF	26957230	8718696269572	8718696269589
H4 XV+ SF	56399SF	26955830	8718696269558	8718696269565
H7 XV+ SF	56364SF	26953430	8718696269534	8718696269541
H1 XV+ BF	56406BF	26969530	8718696269695	8718696269701
H4 XV+ BF	56405BF	26967130	8718696269671	8718696269688
H7 XV+ BF	56404BF	26965730	8718696269657	8718696269664
H1 WHV SF	56403SF	26963328	8718696269633	8718696269640
H4 WHV SF	56402SF	26962628	8718696269626	8718696269619
H7 WHV SF	56401SF	26959628	8718696269596	8718696269602
H1 WHV BF	56409BF	26975630	8718696269756	8718696269763
H4 WHV BF	56408BF	26973230	8718696269732	8718696269749
H7 WHV BF	56407BF	26971830	8718696269718	8718696269725
H4 ColorVision Green SF	56262SF	26911428	8718696269114	8718696269121

Description	Ordering number	GOC	EAN1	EAN3
H4 RV SF	56648SF	27010330	8718696270103	8718696270110
H4 RV BF	56649BF	27012730	8718696270127	8718696270134
H7 RV SF	56650SF	27014130	8718696270141	8718696270158
H7 RV BF	56651BF	27016530	8718696270165	8718696270172
<b>Xenon</b>				
D1S Vision S1	85415VISF	36504733	8727900365047	8727900365054
D2S Vision S1	85122VISF	36507833	8727900365078	8727900365085
D2R Vision S1	85126VISF	36511533	8727900365115	8727900365122
D3S Vision S1	42403VISF	36515333	8727900365153	8727900365160
D1S XV2 SF	56643SF	39655333	8727900396553	8727900396560
D2S XV2 SF	56644SF	39657733	8727900396577	8727900396584
D2R XV2 SF	56645SF	39659133	8727900396591	8727900396607
D3S XV2 SF	56646SF	39661433	8727900396614	8727900396621
D4S XV2 SF	56647SF	39663833	8727900396638	8727900396645
D1S WHV2 SF	56640SF	39649233	8727900396492	8727900396508
D2S WHV2 SF	56641SF	39651533	8727900396515	8727900396522
D3S WHV2 SF	56642SF	39653933	8727900396539	8727900396546

Philips marketing tool images are non-contractual and may be modified.




# Understanding Philips ordering codes

All our automotive lighting products can be ordered using **Philips Order Entry**.

With Philips Order Entry you can identify the **lamp type**, the **product range** and the **packaging type**.

Example: **12972RVB1**, H7 RacingVision, single blister



## 3/ Packaging type



**Commercial pack**  
Material carton  
Contents **C1** 1 lamp  
Contents **CP** 10 lamps  
Packaging type **C1/CP**



**Single blister**  
Material carton/plastic  
Contents 1 lamp  
Packaging type **B1**



**Double blister**  
Material carton/plastic  
Contents 2 lamps  
Packaging type **B2**

## 1/ Lamp type

Every **lamp type** is designated by Philips with a unique number called lamp type.

- All 12V lamps start with 12 (for example: 12972 for H7 12V)
- All 24V lamps starting with 13 (for example: 13972 for H7 24V)

## 2/ Range type

Most lamp types are available in different product **ranges**. These are indicated by a **color code**, to indicate the availability of a lamp in a specific product range.

### Color code

	Vision Up to 30% more vision	Range type <b>PR</b>
	VisionPlus Up to 60% more vision	Range type <b>VP</b>
	X-tremeVision Up to 130% brighter light	Range type <b>XV+</b>
	X-tremeVision G-force Up to 130% brighter light	Range type <b>XVG</b>
	LongLife EcoVision Lifetime up to 1500 hours	Range type <b>LLECO</b>
	WhiteVision Intense white xenon effect	Range type <b>WHV</b> or <b>BVU</b>
	WhiteVision ultra Sharp white look	Range type <b>WVU</b>



**Special pack**  
Material plastic  
Contents **S2** 2 lamps  
Contents **SM** 4 lamps  
(2 headlamps,  
2 position lamps)  
Packaging type **S2/SM**


































































**Xenon single blister**  
Material carton/plastic  
Contents 1 lamp  
Packaging type **S1**



**LED X1/X2 blister**  
Material carton/plastic  
Contents **X1** 1 lamp  
Contents **X2** 2 lamps  
Packaging types **X1/X2**

	RacingVision Up to 150% brighter light	Range type <b>RV</b>
	CrystalVision Bright white light	Range type <b>CV</b>
	DiamondVision Ultimate white light	Range type <b>DV</b>
	Standard	Range type <b>STD</b>
	Ultinon LED The next level of white light	Range type <b>UL</b>
	X-tremeUltinon LED Brighter. Whiter. Stronger.	Range type <b>XU</b>

# Technical illustrations Bases

 <b>SV6</b> IEC 7004-5	 <b>SV8,5-8</b> IEC 7004-81	 <b>W2x4,6d</b> IEC 7004-94	 <b>W2,1x9,5d</b> IEC 7004-91	 <b>W3x16d</b> IEC 7004-105	 <b>W3x16q</b> IEC 7004-106	 <b>WX3x16d</b> IEC 7004-105
 <b>BAX 9s</b> IEC 7004-8	 <b>BAY 9s</b> IEC 7004-9	 <b>BA 7s</b>	 <b>BA 9s</b> IEC 7004-14	 <b>BA 15s</b> IEC 7004-11A	 <b>BA 15d</b> IEC 7004-11A	 <b>BAU 15s</b> IEC 7004-11A
 <b>BAY 15d</b> IEC 7004-11B	 <b>BAW 9s</b> IEC 7004-149-1	 <b>BAW 15d</b> IEC 7004-11E-1	 <b>BAW 15s</b> IEC 7004-11E11	 <b>BAZ 15d</b> IEC 7004-11C	 <b>BA20d</b> IEC 7004-12	 <b>P43t-38</b> IEC 7004-39
 <b>P45t-41</b> IEC 7004-95	 <b>P20d-PY20d</b> IEC 7004-31	 <b>P22d</b> IEC 7004-32	 <b>PX22d</b>	 <b>PG13</b> IEC 7004-107	 <b>PGJ13</b> IEC 7004-107	 <b>PGJ23t-1</b>
 <b>HPSL HTR</b>	 <b>PG18,5d</b> IEC 7004-147	 <b>PG20</b> IEC 7004-127	 <b>PGU20</b>	 <b>PU20d</b>	 <b>PGJ19-1/2</b> IEC 7004-110	 <b>PGJ19-3</b> IEC 7004-110
 <b>PGJ19-5</b> IEC 7004-110	 <b>PGJ23t-1</b>	 <b>P14,5s</b> IEC 7004-46	 <b>X511</b> IEC 7004-99	 <b>P26s</b>	 <b>PX26d,4t</b> IEC 7004-128-2	 <b>PX26d</b> IEC 7004-5
 <b>P29t-PX29t</b> IEC 7004-66	 <b>P32d</b> IEC 7004-111	 <b>P32d-2</b> IEC 7004-111	 <b>P32d-3</b> IEC 7004-111	 <b>P32d-5</b> IEC 7004-111	 <b>P32d-6</b> IEC 7004-111	 <b>PK32d-2</b> IEC 7004-111
 <b>PK32d-3/5/6</b> IEC 7004-111	 <b>PK32d-7</b> IEC 7004-111	 <b>PK22s</b> IEC 7004-47	 <b>PU43t-3</b> IEC 7004-171-2	 <b>PY26d-1</b> IEC 7004-5-7	 <b>W3x16d</b> IEC 7004-105-1	 <b>W3x16q</b> IEC 7004-106-1
 <b>W2,1x9,5d</b>	 <b>WP3,3x14,5/3</b>	 <b>Bax 8,3s</b>	 <b>Bax 8,4d</b>	 <b>Bax 8,5d/1</b>	 <b>Bax 8,5d/2</b>	 <b>Bax 10d</b>

# Product **index** by ordering number

## Halogen 12 V car lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12023CP	H5W	Standard	12	5	BA9s	51270928	8711559512709	8711559512464	8727900371222	28
12024CP	H10W	Standard	12	10	BA9s	52941728	8711559529417	8711559529424	8727900371192	29
12025CP	H20W	Standard	12	20	BA9s	87600328	8711500876003	8711500876010	8727900371154	29
12035RAB1	H7	Rally	12	80	PX26d	40732030	8711500407320	-	8711500407337	22
12035RAC1	H7	Rally	12	80	PX26d	47208330	8711500472083	-	8727900371109	22
12036B2	H6W	Standard	12	6	BAX9s	24720930	8711500247209	-	8711500247216	28
12036BVCP	H6W	WhiteVision	12	6	BAX9s	87609628	8711500876096	8711500876102	8727900370720	28
12036CP	H6W	Standard	12	6	BAX9s	87603428	8711500876034	8711500876041	8727900370676	28
12036WHVB2	H6W	WhiteVision	12	6	BAX9s	37467430	8711500245670	-	8727900374681	29
12040VPB2	WBT10	VisionPlus	12	6	W2,1x9,5d	52416030	8711559524160	-	8711559524184	30
12059C1	H27W/1	Standard	12	27	PG13	52854030	8711559528540	-	8727900370799	25
12060C1	H27W/2	Standard	12	27	PGJ13	52857130	8711559528571	-	8727900370805	25
12061CP	W2,3W	Standard	12	2,3	W2x4,6d	48330028	8711500483300	8711500483317	8727900391640	29
12065B2	W21W	Standard	12	21	W3x16d	70146330	8727900701463	-	8727900701470	30
12065CP	W21W	Standard	12	21	W3x16d	47135228	8711500471352	8711500471369	8727900391107	30
12066B2	W21/5W	Standard	12	21/5	W3x16q	69739130	8727900697391	-	8727900697407	30
12066CP	W21/5W	Standard	12	21/5	W3x16q	47138328	8711500471383	8711500471390	8727900391091	30
12067B2	W16W	Standard	12	16	W2,1x9,5d	40587630	8711500405876	-	8711559521053	30
12067CP	W16W	Standard	12	16	W2,1x9,5d	48272328	8711500482723	8711500482730	8727900391626	30
12071B2	WY21W	Standard	12	21	WX3x16d	69741430	8727900697414	-	8727900697421	30
12071CP	WY21W	Standard	12	21	WX3x16d	52539628	8711559525396	8711559525402	8727900391688	30
12085C1	PS19W	Standard	12	19	PG20/1	69653030	8727900696530	-	8727900390988	34
12085LLC1	PS19W	LongLife	12	19	PG20/1	70046630	8727900700466	-	8727900390926	34
12086FFC1	PS24W	Standard	12	24	PG20/3	70044230	8727900700442	-	8727900390919	34
12088CP	PR21W	Standard	12	21	BAW15s	48531128	8711500485311	8711500485328	8727900391589	27
12093NACP	RY10W	Standard	12	10	BAU15s	48362128	8711500483621	8711500483638	8727900391619	28
12146CP	HY21W	Standard	12	21	BAW9s	35244328	8727900352443	8727900352450	8727900370867	29
12174NAHTRC1	PWY24W	Standard	12	24	WP3,3x14,5/4	39202930	8727900392029	-	8727900397345	35
12174SVHTRC1	PWY24W	SilverVision+	12	24	WP3,3x14,5/4	39200530	8727900392005	-	8727900397352	35
12177C1	PW16W	Standard	12	16	WP3,3x14,5/8	39623230	8727900396232	-	8727900396249	34
12180SV+C1	PSY24W	SilverVision+	12	24	PG20/4	70379530	8727900703795	-	8727900390841	35
12182HTRC1	PW24W	Standard	12	24	WP3,3x14,5/3	39196130	8727900391961	-	8727900397369	35
12188NAC1	PSY24W	Standard	12	24	PG20/4	69668430	8727900696684	-	8727900390834	34
12190NAC1	PY24W	Standard	12	24	PGU20/4	69690530	8727900696905	-	8727900390803	35
12197HTRC1	HiPerVision LCP	Standard	13.5	24	HPSL 2A	39621830	8727900396218	-	8727900396225	34
12256B2	W3W	Standard	12	3	W2,1x9,5d	52410830	8711559524108	-	8711559524122	29
12256CP	W3W	Standard	12	3	W2,1x9,5d	48144328	8711500481443	8711500481450	8727900391664	29
12258CVB1	H1	CrystalVision	12	55	P14,5s	82687930	8711500826879	-	8711500826893	18
12258CVSM	H1	CrystalVision	12	55	P14,5s	48971528	8711500489715	-	8711500489722	18
12258DVB1	H1	DiamondVision	12	55	P14,5s	82690930	8711500826909	-	8711500826916	19
12258DVS2	H1	DiamondVision	12	55	P14,5s	69742428	8711500697424	-	8711500697431	19
12258LLECOB1	H1	LongLife EcoVision	12	55	P14,5s	36196430	8727900361964	-	8727900361971	18
12258LLECO1	H1	LongLife EcoVision	12	55	P14,5s	36187230	8727900361872	-	8727900370683	18
12258LLECOS2	H1	LongLife EcoVision	12	55	P14,5s	36255828	8727900362558	-	8727900362565	18
12258PRB1	H1	Vision	12	55	P14,5s	47516930	8711500475169	-	8711500475176	18
12258PRC1	H1	Vision	12	55	P14,5s	47518360	8711500475183	8727900363791	8711500475190	18
12258SPC1	H1	Spot	12	55	P14,5s	40460230	8711500404602	-	8727900370690	19
12258VPB1	H1	VisionPlus	12	55	P14,5s	36320330	8727900363203	-	8727900363197	18
12258VPS2	H1	VisionPlus	12	55	P14,5s	36322728	8727900363227	-	8727900363210	18
12258WHVB1	H1	WhiteVision	12	55	P14,5s	37156730	8727900371567	-	8727900371574	18
12258WHVSM	H1	WhiteVision	12	55	P14,5s	78884928	8711500788849	-	8711500788856	18
12258XVGS2	H1	X-tremeVision G-force	12	55	P14,5s	35520828	8727900355208	-	8727900355215	18
12258XVGB1	H1	X-tremeVision G-force	12	55	P14,5s	35522230	8727900355222	-	8727900355239	18
12258XV+B1	H1	X-tremeVision	12	55	P14,5s	37164230	8727900371642	-	8727900371659	18
12258XV+S2	H1	X-tremeVision	12	55	P14,5s	37166628	8727900371666	-	8727900371673	18
12271AC1	PCY16W	HiPerClick	12	16	PU20d/2	38965430	8727900389654	-	8727900391152	34
12274SV+C1	PY24	SilverVision+	12	24	PGU20/4	69678330	8727900696783	-	8727900390780	35
12275NAC1	PSY19W	Standard	12	19	PG20/2	52735230	8711559527352	-	8727900390858	34
12276C1	PSX24W	Standard	12	24	PG20/7	69676930	8727900696769	-	8727900390902	34
12277C1	P13W	Standard	12	13	PG18,5d-1	69672130	8727900696721	-	8727900391008	34
12278C1	PSX26W	Standard	12	26	PG18,5d/3	38874930	8727900388749	-	8727900390896	35
12311C1	H2	Standard	12	55	X511	47752130	8711500477521	-	8727900370782	19

## Halogen 12 V car lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12336CVB1	H3	CrystalVision	12	55	PK22s	77496530	8711500774965	-	8711500774996	19
12336DVB1	H3	DiamondVision	12	55	PK22s	77494130	8711500774941	-	8711500774972	19
12336DVS2	H3	DiamondVision	12	55	PK22s	69745528	8711500697455	-	8711500697462	19
12336LLECO1	H3	LongLife EcoVision	12	55	PK22s	77704130	8711500777041	-	8711500779366	19
12336PRB1	H3	Vision	12	55	PK22s	69561130	8711500695611	-	8711500695628	19
12336PRC1	H3	Vision	12	55	PK22s	69534560	8711500695345	8711500775696	8711500695352	19
12336WHVB1	H3	WhiteVision	12	55	PK22s	77951930	8711500779519	-	8711500779526	19
12342CVPBS2	H4	ColorVision Blue	12	60/55	P43t-38	36793528	8727900367935	-	8727900367942	20
12342CVPYS2	H4	ColorVision Yellow	12	60/55	P43t-38	36789828	8727900367898	-	8727900367904	20
12342CVSM	H4	CrystalVision	12	60/55	P43t-38	48981428	8711500489814	-	8711500489821	21
12342DVB1	H4	DiamondVision	12	60/55	P43t-38	53289030	8727900532890	-	8727900532906	21
12342DVS2	H4	DiamondVision	12	60/55	P43t-38	69573428	8711500695734	-	8711500697448	21
12342LLECOB1	H4	LongLife EcoVision	12	60/55	P43t-38	36198830	8727900361988	-	8727900361995	20
12342LLECO1	H4	LongLife EcoVision	12	60/55	P43t-38	36189630	8727900361896	-	8727900370836	20
12342LLECOS2	H4	LongLife EcoVision	12	60/55	P43t-38	36257228	8727900362572	-	8727900362589	20
12342PRB1	H4	Vision	12	60/55	P43t-38	47480330	8711500474803	-	8711500474810	19
12342PRC1	H4	Vision	12	60/55	P43t-38	49099560	8711500490995	8711500827807	8711500490988	19
12342PRC2	H4	Vision	12	60/55	P43t-38	78028760	8711500780287	8711500780294	8711500780300	19
12342RVB1	H4	RacingVision	12	60/55	P43t-38	00022430	8719018000224	-	8719018000231	21
12342RVS2	H4	RacingVision	12	60/55	P43t-38	00020028	8719018000200	-	8719018000217	21
12342VPB1	H4	VisionPlus	12	60/55	P43t-38	39934930	8727900399349	-	8727900399332	20
12342VPC2	H4	VisionPlus	12	60/55	P43t-38	37435360	8727900374353	8727900374360	8727900374377	20
12342VPS2	H4	VisionPlus	12	60/55	P43t-38	39925728	8727900399257	-	8727900350937	20
12342WHVB1	H4	WhiteVision	12	60/55	P43t-38	22103230	8711500221032	-	8711500221049	20
12342WHVSM	H4	WhiteVision	12	60/55	P43t-38	78886328	8711500788863	-	8711500788870	20
12342XVGS2	H4	X-tremeVision G-force	12	60/55	P43t-38	35525328	8727900355253	-	8727900355284	20
12342XVGB1	H4	X-tremeVision G-force	12	60/55	P43t-38	35529130	8727900355291	-	8727900355390	20
12342XV+B1	H4	X-tremeVision	12	60/55	P43t-38	22107030	8711500221070	-	8711500221087	20
12342XV+S2	H4	X-tremeVision	12	60/55	P43t-38	22109428	8711500221094	-	8711500221100	20
12356CP	H21W	Standard	12	21	BAY9s	87989928	8711500879899	8711500879905	8727900371116	29
12360B1	H8	Standard	12	35	PGJ19-1	82416530	8711500824165	-	8727900362909	23
12360C1	H8	Standard	12	35	PGJ19-1	47582430	8711500475824	-	8727900371017	23
12360WHVB1	H8	WhiteVision	12	35	PGJ19-1	37471130	8727900374711	-	8727900374728	23
12361B1	H9	Standard	12	65	PGJ19-5	36308130	8727900363081	-	8727900363098	23
12361C1	H9	Standard	12	65	PGJ19-5	47584830	8711500475848	-	8727900371000	23
12362XVGB1	H11	X-tremeVision G-force	12	55	PGJ19-2	00119130	8719018001191	-	8719018001207	23
12362CVB1	H11	CrystalVision	12	55	PGJ19-2	82685530	8711500826855	-	8711500826862	24
12362CVSM	H11	CrystalVision	12	55	PGJ19-2	52646128	8711559526461	-	8711559526843	24
12362LLECOB1	H11	LongLife EcoVision	12	55	PGJ19-2	36310430	8727900363104	-	8727900363111	22
12362LLECO1	H11	LongLife EcoVision	12	55	PGJ19-2	36194030	8727900361940	-	8727900370744	22
12362PRB1	H11	Vision	12	55	PGJ19-2	36428630	8727900364286	-	8727900364293	22
12362PRC1	H11	Vision	12	55	PGJ19-2	36430930	8727900364309	-	8727900370751	22
12362WHVB1	H11	WhiteVision	12	55	PGJ19-2	37469830	8727900374698	-	8727900374704	22
12366C1	H16	Standard	12	19	PGJ19-3	36856730	8727900368567	-	8727900370775	24
12396NAB2	WY5W	Standard	12	5	W2,1x9,5d	40058130	8711500400581	-	8711500400598	30
12396NACP	WY5W	Standard	12	5	W2,1x9,5d	53002428	8711559530024	8711559530031	8727900390889	30
12401CP	Stop P22	Standard	12	15	BA15s	87821228	8711500878212	8711500878229	8711500790538	27
12445CP	Stop P25	Standard	12	18	BA15s	48440628	8711500484406	8711500484413	8727900391602	27
12454RAB1	H1	Rally	12	100	P14,5s	40722130	8711500407221	-	8711500407238	18
12454RAC1	H1	Rally	12	100	P14,5s	69639730	8711500696397	-	8727900366396	18
12455RAC1	H3	Rally	12	100	PK22s	47898630	8711500478986	-	8711500779373	19
12475B1	R2	R2 Visio	12	45/40	P45t-41	24716230	8711500247162	-	8711500247179	26
12475C1	R2	R2 Visio	12	45/40	P45t-41	40466430	8711500404664	-	8727900371130	26
12495CP	PR21/5W	Standard	12	21/5	BAW15d	48873228	8711500488732	8711500488749	8727900391572	27
12496LLECOCP	PY21W	LongLife EcoVision	12	21	BAU15s	38218128	8727900382181	8727900382198	8727900391084	27
12496NAB2	PY21W	Standard	12	21	BAU15s	52372930	8711559523729	-	8711559523743	27
12496NACP	PY21W	Standard	12	21	BAU15s	52534173	8711559525341	8711559525358	8711559525365	27
12496SVB2	PY21W	SilverVision	12	21	BAU15s	31117730	8711500311773	-	8711500311191	27
12498B2	P21W	Standard	12	21	BA15s	5549130	8711500055491	-	8711559520131	26
12498CP	P21W	Standard	12	21	BA15s	49078073	8711500490780	8711500490797	8711500490803	26
12498LLECOB2	P21W	LongLife EcoVision	12	21	BA15s	38210530	8727900382105	-	8727900382112	26
12498LLECOCP	P21W	LongLife EcoVision	12	21	BA15s	38198628	8727900381986	8727900381993	8727900391695	26
12498VPB2	P21W	VisionPlus	12	21	BA15s	36318030	8727900363180	-	8727900363173	26
12499B2	P21/5W	Standard	12	21/5	BAY15d	5545330	8711500055453	-	8711559520148	27
12499CP	P21/5W	Standard	12	21/5	BAY15d	48159773	8711500481597	8711500481603	8711500481610	27



## Halogen 12 V car lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12499LLECOB2	P21/5W	LongLife Ecovision	12	21/5	BAY15d	38212930	8727900382129	-	8727900382136	26
12499LLECOCP	P21/5W	LongLife Ecovision	12	21/5	BAY15d	38201328	8727900382013	8727900382020	8727900391053	26
12499VPB2	P21/5W	VisionPlus	12	21/5	BAY15d	36316630	8727900363166	-	8727900363159	26
12505CP	W2W	Standard	12	2	W2x4,6d	48327028	8711500483270	8711500483287	8727900391657	29
12516B2	W1,2W	Standard	12	1.2	W2x4,6d	5554530	8711500055545	-	8711500417763	29
12516CP	W1,2W	Standard	12	1.2	W2x4,6d	48153573	8711500481535	8711500481542	8711500481559	29
12521CP	WBT5	Standard	12	1	W2x4,6d	48321828	8711500483218	8711500483225	8727900391671	29
12569RAB1	H4	Rally	12	100/90	P43t-38	40728330	8711500407283	-	8711500407290	21
12569RAC1	H4	Rally	12	100/90	P43t-38	40177930	8711500401779	-	8711500779441	21
12580C1	H15	Standard	12	55/15	PGJ23t-1	02000030	8719018020000	-	8719018020024	24
12580B1	H15	Standard	12	55/15	PGJ23t-1	02001730	8719018020017	-	8719018020031	24
12594B2	P21/4W	Standard	12	21/4	BAZ15d	40485530	8711500404855	-	8711500471017	26
12594CP	P21/4W	Standard	12	21/4	BAZ15d	48433828	8711500484338	8711500484345	8727900391565	26
12596(H5)C1	R2	Rally	12	65/55	P45t-41	51226630	8711559512266	-	8727900370843	26
12597B2	Bax 8,3s/1,35 black	Standard	12	1.2	B8,3s/1,35	53018530	8711559530185	-	8711559530192	32
12597CP	Bax 8,3s/1,35 black	Standard	12	1.2	B8,3s/1,35	48365228	8711500483652	8711500483669	8727900390957	32
12598B2	Bax 8,5d/2 black	Standard	12	1.2	B8,5d/2	40588330	8711500405883	-	8711500405890	32
12598CP	Bax 8,5d/2 black	Standard	12	1.2	B8,5d/2	48387428	8711500483874	8711500483881	8727900390964	32
12600CP	Bax 8,5d/2 green	Standard	12	2	B8,5d/2	48393528	8711500483935	8711500483942	8727900390971	32
12602CP	Bax 8,3s/1,5 blue	Standard	12	2	B8,3s/1,5	48396628	8711500483966	8711500483973	8727900390995	32
12603CP	Bax 8,5d/1,5 blue	Standard	12	1.2	B8,5d/1,5	48399728	8711500483997	8711500484000	8727900391015	32
12604CP	B8,5d green	Standard	12	2	B8,5d	40508128	8711500405081	8711500404589	8727900391022	32
12611CP	BX8,4d olive green	Standard	12	1.3	BX8,4d	77432328	8711500774323	8711500774330	8711500779397	33
12614CP	B10d brown halogen	Standard	12	3	B10d	52805228	8711559528052	8711559512723	8727900370928	32
12615CP	B10d black halogen	Standard	12	5	B10d	52807628	8711559528076	8711500243768	8727900370911	32
12620B1	R2	Standard	12	45/40	P45t-41	5543930	8711500055439	-	8711559525327	26
12620C1	R2	Standard	12	45/40	P45t-41	40085730	8711500400857	-	8711500779359	26
12620B1	BX8,4d light blue	Standard	12	1.2	BX8,4d	51384328	8711559513843	8711500244154	8727900370904	33
12624CP	BX8,4d orange	Standard	12	1.1	BX8,4d	51411628	8711559514116	8711500245137	8727900370898	33
12625CP	BX8,4d black	Standard	12	1.2	BX8,4d	51409328	8711559514093	8711500244420	8727900371208	33
12626CP	BX8,4d light green	Standard	12	2	BX8,4d	51412328	8711559514123	8711500246066	8727900370942	33
12627CP	BX8,4d beige	Standard	12	1.5	BX8,4d	51414728	8711559514147	8711500247414	8727900370959	33
12629CP	BX8,4d beige	Standard	12	1.8	BX8,4d	51488828	8711559514888	8711559512488	8727900371031	33
12637CP	B8,5d beige	Standard	12	1.5	B8,5d	51487128	8711559514871	8711500400178	8727900371048	32
12638CP	BX8,5d white	Standard	12	1.12	BX8,5d	48846628	8711500488466	8711500488473	8727900391503	33
12643LLC1	H18	LongLife EcoVision	12	65	PY26d-1	35603830	8727900356038	-	8727900356045	24
12644LLC1	H19	LongLife EcoVision	12	60/55	PU43t-3	35605230	8727900356052	-	8727900356069	24
12754C1	H4	Rally	12	100/90	P43t-38	77438530	8711500774385	-	8711500779380	21
12814B2	R10W	Standard	12	10	BA15s	5547730	8711500055477	-	8711500417718	28
12814CP	R10W	Standard	12	10	BA15s	48341673	8711500483416	8711500483423	8711500483430	28
12818CP	Festoon T6,2x27	Standard	12	3	SV6	48461128	8711500484611	8711500484628	8727900695632	31
12821B2	R5W BA15s	Standard	12	5	BA15s	5546030	8711500055460	-	8711500417701	27
12821CP	R5W BA15s	Standard	12	5	BA15s	48269373	8711500482693	8711500482709	8711500482716	27
12821LLECOB2	R5W	LongLife EcoVision	12	5	BA15s	38208230	8727900382082	-	8727900382099	27
12821LLECOCP	R5W	LongLife EcoVision	12	5	BA15s	38195528	8727900381955	8727900381962	8727900390940	27
12822CP	R5W BA15d	Standard	12	5	BA15d	45407228	8711500454072	8711500454959	8711500790521	28
12829CP	BA7	Standard	12	2	BA7s	52123728	8711559521237	8711500401236	8727900390933	28
12844B2	Festoon C5W	Standard	12	5	SV8,5	5551430	8711500055514	-	8711500417749	31
12844CP	Festoon C5W	Standard	12	5	SV8,5	48156673	8711500481566	8711500481573	8711500481580	31
12848CP	Festoon T6,2x27	Standard	12	3	SV6	48467328	8711500484673	8711500484680	8727900391558	31
12850CP	Festoon T15x43	Standard	12	15	SV8,5	48285328	8711500482853	8711500482860	8727900391541	31
12854CP	Festoon T10,5x38	Standard	12	10	SV8,5	48248828	8711500482488	8711500482495	8727900391510	31
12860LLECOCP	Festoon T10,5x30	LongLife EcoVision	12	10	SV8,5	38192428	8727900381924	8727900381931	8727900391114	31
12864CP	Festoon T10,5x43	Standard	12	5	SV8,5	48205128	8711500482051	8711500482075	8727900391527	31
12866B2	Festoon T10,5x43	Standard	12	10	SV8,5	5552130	8711500055521	-	8711500417756	31
12866CP	Festoon T10,5x43	Standard	12	10	SV8,5	48242628	8711500482426	8711500482433	8727900391534	31
12910CP	T3W	Standard	12	3	BA9s	21949728	8711500219497	8711500219503	8711500220837	28
12913CP	T2W	Standard	12	2	BA9s	21997828	8711500219978	8711500219985	8711500220820	28
12929B2	T4W	Standard	12	4	BA9s	5550730	8711500055507	-	8711559520094	28
12929CP	T4W	Standard	12	4	BA9s	21979473	8711500219794	8711500219800	8711500219817	28
12960CP	W2,2W	Standard	12	2.2	W2,1x9,5d	48150428	8711500481504	8711500481511	8727900391633	29
12961B2	W5W	Standard	12	5	W2,1x9,5d	40421330	8711500404213	-	8711559520070	30
12961BVB2	W5W	WhiteVision	12	5	W2,1x9,5d	31029330	8711500310293	-	8711559523774	30
12961CP	W5W	Standard	12	5	W2,1x9,5d	49090273	8711500490902	8711500490919	8711500490926	30
12961LLECOB2	W5W	LongLife EcoVision	12	5	W2,1x9,5d	38204430	8727900382044	-	8727900382051	30

## Halogen 12 V car lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12961LLECOCP	W5W	LongLife EcoVision	12	5	W2,1x9,5d	38189428	8727900381894	8727900381900	8727900390872	30
12961NBVB2	W5W	WhiteVision	12	5	W2,1x9,5d	39204330	8727900392043	-	8727900392050	30
12972CVB1	H7	CrystalVision	12	55	PX26d	53291330	8727900532913	-	8727900532920	21
12972CVPBS2	H7	ColorVision Blue	12	55	PX26d	36810928	8727900368109	-	8727900368130	22
12972CVPYS2	H7	ColorVision Yellow	12	55	PX26d	36802428	8727900368024	-	8727900368031	22
12972CVSM	H7	CrystalVision	12	55	PX26d	48983828	8711500489838	-	8711500489845	22
12972DVB1	H7	DiamondVision	12	55	PX26d	53293730	8727900532937	-	8727900532944	23
12972DVS2	H7	DiamondVision	12	55	PX26d	69747928	8711500697479	-	8711500697486	23
12972LLECOB1	H7	LongLife EcoVision	12	55	PX26d	36200830	8727900362008	-	8727900362015	22
12972LLECO1	H7	LongLife EcoVision	12	55	PX26d	36192630	8727900361926	-	8727900371024	22
12972LLECOS2	H7	LongLife EcoVision	12	55	PX26d	36259628	8727900362596	-	8727900362602	22
12972PRB1	H7	Vision	12	55	PX26d	40607130	8711500406071	-	8711500406088	21
12972PRC1	H7	Vision	12	55	PX26d	40593760	8711500405937	8711500827838	8711500405944	21
12972PRC2	H7	Vision	12	55	PX26d	37432260	8727900374322	8727900374339	8727900374346	21
12972RVB1	H7	RacingVision	12	55	PX26d	00026230	8719018000262	-	8719018000279	22
12972RVS2	H7	RacingVision	12	55	PX26d	00024828	8719018000248	-	8719018000255	22
12972VPB1	H7	VisionPlus	12	55	PX26d	39936330	8727900399363	-	8727900399356	21
12972VPC2	H7	VisionPlus	12	55	PX26d	37426160	8727900374261	8727900374278	8727900374285	21
12972VPS2	H7	VisionPlus	12	55	PX26d	39938728	8727900399387	-	8727900399370	21
12972WHVB1	H7	WhiteVision	12	55	PX26d	37160430	8727900371604	-	8727900371611	22
12972WHVSM	H7	WhiteVision	12	55	PX26d	78888728	8711500788887	-	8711500788894	22
12972WVUB1	H7	WhiteVision ultra	12	55	PX26d	35493530	8727900354935	-	8727900354928	22
12972WVUSM	H7	WhiteVision ultra	12	55	PX26d	35495928	8727900354959	-	8727900354942	22
12972XVGS2	H7	X-tremeVision G-force	12	55	PX26d	35541328	8727900355413	-	8727900355789	22
12972XVGB1	H7	X-tremeVision G-force	12	55	PX26d	35579630	8727900355796	-	8727900355802	22
12972XV+B1	H7	X-tremeVision	12	55	PX26d	37168030	8727900371680	-	8727900371697	21
12972XV+S2	H7	X-tremeVision	12	55	PX26d	37170328	8727900371703	-	8727900371710	21
55502GKKM	Bax Tool Box 12V	Standard	12	-	-	69717928	8727900697179	-	8727900697230	32
9004C1	HB1	Standard	12	65/45	P29t	47074430	8711500470744	-	8727900370997	24
9005CVB1	HB3	CrystalVision	12	60	P20d	53299930	8727900532999	-	8727900533002	24
9005DVB1	HB3	DiamondVision	12	65	P20d	53295130	8727900532951	-	8727900532968	25
9005PRB1	HB3	Vision	12	60	P20d	24724730	8711500247247	-	8711500247254	24
9005PRC1	HB3	Vision	12	60	P20d	24689930	8711500246899	-	8727900370980	24
9005WHVB1	HB3	WhiteVision	12	60	P20d	37475930	8727900374759	-	8727900374766	24
9006CVB1	HB4	CrystalVision	12	60	P22d	53301930	8727900533019	-	8727900533026	25
9006CVSM	HB4	CrystalVision	12	60	P22d	52620128	8711559526201	-	8711559526454	25
9006DVB1	HB4	DiamondVision	12	55	P22d	53297530	8727900532975	-	8727900532982	25
9006DVS2	HB4	DiamondVision	12	55	P22d	53248728	8727900532487	-	8727900532494	25
9006PRB1	HB4	Vision	12	51	P22d	24726130	8711500247261	-	8711500247278	25
9006PRC1	HB4	Vision	12	51	P22d	24687530	8711500246875	-	8727900370973	25
9006WHVB1	HB4	WhiteVision	12	51	P22d	37473530	8727900374735	-	8727900374742	25
9006XVGB1	HB4	X-tremeVision G-force	12	51	P22d	00123830	8719018001214	-	8719018001245	25
9007C1	HB5	Standard	12	65/55	PX29t	24550230	8711500245502	-	8727900370966	25
9008C1	H13	Standard	12	60/55	P26,4t	87798730	8711500877987	-	8727900370768	24
9012LLC1	HIR2	LongLife	12	55	PX22d	35125530	8727900351255	-	8727900370935	25
9145C1	H10	Standard	12	45	PY20d	52974530	8711559529745	-	8727900370737	23

## Halogen two-wheeler lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12008BW	S3	Standard	12	15	P26s	77381430	8711500773814	-	8711500773845	43
12008C1	S3	Standard	12	15	P26s	77394430	8711500773944	-	8711500779335	43
12256B2	W3W	Standard	12	3	W2,1x9,5d	52410830	8711559524108	-	8711559524122	43
12256CP	W3W	Standard	12	3	W2,1x9,5d	48144328	8711500481443	8711500481450	8727900391664	43
12342CTVBW	H4	CityVision moto	12	60/55	P43t-38	39896030	8727900398960	-	8727900398977	42
12342PRBW	H4	Vision moto	12	60/55	P43t-38	49024730	8711500490247	-	8711500490254	42
12498B2	P21W	Standard	12	21	BA15s	05549130	8711500055491	-	8711559520131	43
12498CP	P21W	Standard	12	21	BA15s	49078073	8711500490780	8711500490797	8711500490803	43
12499EDBW	P21/5W	ExtraDuty	12	21/5	BAY15d	87900430	8711500879004	-	8711500879035	43
12636BW	HS1	Vision moto	12	35/35	PX43t	53035330	8727900530353	-	8727900530360	42
12636C1	HS1	Vision moto	12	35/35	PX43t	51250130	8711559512501	-	8727900370881	42
12636CTVBW	HS1	CityVision moto	12	35/35	PX43t	39894630	8727900398946	-	8727900398953	43
12728BW	S2	Standard	12	35/35	BA20d	77385230	8711500773852	-	8711500773869	43
12728C1	S2	Standard	12	35/35	BA20d	77359330	8711500773593	-	8711500779342	43
12972CTVBW	H7	CityVision moto	12	55	PX26d	39898430	8727900398984	-	8727900398991	42
12972PRBW	H7	Vision moto	12	55	PX26d	49026130	8711500490261	-	8711500490278	42

## Halogen two-wheeler lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12342XV+BW	H4	X-tremeVision moto	12	60/55	P43t-38	00056930	8719018000569	-	8719018000576	42
12972XV+BW	H7	X-tremeVision moto	12	55	PX26d	37867230	8727900378672	-	8727900378689	42
12342CVUBW	H4	CrystalVision ultra moto	12	60/55	P43t-38	22148330	8711500221483	-	8711500221490	42
12972CVUBW	H7	CrystalVision ultra moto	12	55	PX26d	22118630	8711500221186	-	8711500221193	42
12636VBW	HS1	CrystalVision ultra moto	12	35/35	PX43t	78195630	8711500781956	-	8711500781963	43

## Halogen 24 V lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
13256CP	W3W	Standard	24	3	W2,1x9,5d	48141228	8711500481412	8711500481429	8727900391169	54
13258MDB1	H1	MasterDuty	24	70	P14,5s	82585830	8711500825858	-	8711500825865	50
13258MDC1	H1	MasterDuty	24	70	P14,5s	82577360	8711500825773	8711500828507	8711500825780	50
13258MLC1	H1	MasterLife	24	70	P14,5s	82569830	8711500825698	-	8727900370812	50
13311C1	H2	Standard	24	70	X511	47751430	8711500477514	-	8727900371079	50
13336MDB1	H3	MasterDuty	24	70	PK22s	77459030	8711500774590	-	8711500774613	50
13336MDBVB1	H3	MasterDuty BlueVision	24	70	PK22s	77488030	8711500774880	-	8711500774910	50
13336MDBVS2	H3	MasterDuty BlueVision	24	70	PK22s	77486628	8711500774866	-	8711500774897	50
13336MDC1	H3	MasterDuty	24	70	PK22s	77460660	8711500774606	8711500775313	8711500774637	50
13336MLC1	H3	MasterLife	24	70	PK22s	77462030	8711500774620	-	8711500779403	50
13342MDB1	H4	MasterDuty	24	75/70	P43t-38	82587230	8711500825872	-	8711500825889	50
13342MDBVB1	H4	MasterDuty BlueVision	24	75/70	P43t-38	53281430	8727900532814	-	8727900532821	50
13342MDBVS2	H4	MasterDuty BlueVision	24	75/70	P43t-38	53275328	8727900532753	-	8727900532760	50
13342MDC1	H4	MasterDuty	24	75/70	P43t-38	82579760	8711500825797	8711500828002	8711500825803	50
13342MLC1	H4	MasterLife	24	75/70	P43t-38	82571130	8711500825711	-	8727900371086	50
13401CP	Stop P22	Standard	24	15	BA15s	87826728	8711500878267	8711500878274	8711500790507	52
13402CP	Stop P22	Standard	24	15	BA15d	87836628	8711500878366	8711500878373	8711500790514	52
13445CP	Stop P25	Standard	24	18	BA15s	48443728	8711500484437	8711500484444	8727900390810	52
13496MLCP	PY21W	MasterLife	24	21	BAU15s	69964728	8727900699647	8727900699654	8727900391138	52
13498B2	P21W	Standard	24	21	BA15s	40458330	8711500404583	-	8711500405449	51
13498CP	P21W	Standard	24	21	BA15s	48415473	8711500484154	8711500484161	8711500484178	51
13498MDCP	P21W	MasterDuty	24	21	BA15s	69949473	8727900699494	8727900699500	8727900699517	51
13498MLCP	P21W	MasterLife	24	21	BA15s	69961628	8727900699616	8727900699623	8727900391145	51
13499B2	P21/5W	Standard	24	21/5	BAY15d	40456530	8711500404565	-	8711500405371	52
13499CP	P21/5W	Standard	24	21/5	BAY15d	48424673	8711500484246	8711500484253	8711500484260	52
13516CP	WBT5	Standard	24	1.2	W2x4,6d	48306573	8711500483065	8711500483072	8711500483089	54
13521CP	WBT5	Standard	24	1	W2x4,6d	48324928	8711500483249	8711500483256	8727900391176	54
13597CP	Bax 8,3s/1,35 grey	Standard	24	1.2	B8,3s/1,35	48384328	8711500483843	8711500483850	8727900390797	55
13598CP	Bax 8,5d/2 grey	Standard	24	1.2	B8,5d/2	48390428	8711500483904	8711500483911	8727900390827	55
13620C1	R2	Standard	24	55/50	P45t-41	40087130	8711500400871	-	8711500779458	51
13807CP	Festoon T15x43	Standard	24	18	SV8,5	48294528	8711500482945	8711500482952	8727900391237	55
13814B2	R10W	Standard	24	10	BA15s	40452730	8711500404527	-	8711559526409	53
13814CP	R10W	Standard	24	10	BA15s	48344773	8711500483447	8711500483454	8711500483461	53
13814MDCP	R10W	MasterDuty	24	10	BA15s	69952428	8727900699524	8727900699531	8727900391121	52
13814MLCP	R10W	MasterLife	24	10	BA15s	69967828	8727900699678	8727900699685	8727900390742	52
13818CP	Festoon T6,2x27	Standard	24	3	SV6	48464228	8711500484642	8711500484659	8727900391251	54
13821B2	R5W	Standard	24	5	BA15s	40453430	8711500404534	-	8711500405425	52
13821CP	R5W	Standard	24	5	BA15s	48338673	8711500483386	8711500483393	8711500483409	52
13821MDCP	R5W	MasterDuty	24	5	BA15s	69955528	8727900699555	8727900699562	8727900390766	52
13821MLCP	R5W	MasterLife	24	5	BA15s	69970828	8727900699708	8727900699715	8727900390773	52
13822CP	R5W	Standard	24	5	BA15d	40904128	8711500409041	8711500878021	8711500790491	52
13829CP	BA7	Standard	24	3	BA7s	52133628	8711559521336	8711500401274	8727900390759	53
13844B2	C5W	Standard	24	5	SV8,5	40463330	8711500404633	-	8711500405388	54
13844CP	C5W	Standard	24	5	SV8,5	48197973	8711500481979	8711500481986	8711500481993	54
13848CP	Festoon T6,2x35	Standard	24	3	SV6	48470328	8711500484703	8711500484710	8727900391268	54
13850CP	Festoon T15x43	Standard	24	15	SV8,5	48288428	8711500482884	8711500482891	8727900391244	55
13854CP	Festoon T10,5x38 10W	Standard	24	10	SV8,5	48251828	8711500482518	8711500482525	8727900391206	54
13864CP	Festoon T10,5x43 5W	Standard	24	5	SV8,5	48233428	8711500482334	8711500482341	8727900391213	54
13866CP	Festoon T10,5x43 10W	Standard	24	10	SV8,5	48245728	8711500482457	8711500482464	8727900391220	55
13910CP	T3W	Standard	24	3	BA9s	21955828	8711500219558	8711500219565	8711500220851	53
13913CP	T2W	Standard	24	2	BA9s	22003528	8711500220035	8711500220042	8711500220844	53
13929B2	T4W	Standard	24	4	BA9s	40454130	8711500404541	-	8711500405432	53
13929CP	T4W	Standard	24	4	BA9s	21985573	8711500219855	8711500219862	8711500219879	53
13929MDCP	T4W	MasterDuty	24	4	BA9s	69958628	8727900699586	8727900699593	8727900391039	53
13929MLCP	T4W	MasterLife	24	4	BA9s	69976028	8727900699760	8727900699777	8727900391046	53
13960CP	W2,5W	Standard	24	2.5	W2,1x9,5d	48147428	8711500481474	8711500481481	8727900391275	54
13961B2	W5W	Standard	24	5	W2,1x9,5d	52420730	8711559524207	-	8711559524214	54

## Halogen 24 V lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
13961CP	W5W	Standard	24	5	W2,1x9,5d	48138273	8711500481382	8711500481399	8711559530376	54
13972MDB1	H7	MasterDuty	24	70	PX26d	82589630	8711500825896	-	8711500825902	51
13972MDBVB1	H7	MasterDuty BlueVision	24	70	PX26d	53279130	8727900532791	-	8727900532807	51
13972MDBVS2	H7	MasterDuty BlueVision	24	70	PX26d	53277728	8727900532777	-	8727900532784	51
13972MDC1	H7	MasterDuty	24	70	PX26d	82581060	8711500825810	8711500828514	8711500825827	51
13972MLC1	H7	MasterLife	24	70	PX26d	82573530	8711500825735	-	8727900371147	51
13974CP	WBT5	Standard	24	2	W2x4,6d	48318828	8711500483188	8711500483195	8727900391183	54
24029CP	Bax 8,5d/2 yellow	Standard	24	1.2	B8,5d/2	48402428	8711500484024	8711500484031	8727900391190	55
24032CP	Bax 8,5d brown	Standard	24	1.2	B8,5d	48852728	8711500488527	8711500488534	8727900391077	55
24356CP	H21W	Standard	24	21	BAY9s	87615728	8711500876157	8711500876164	8727900371161	53
24362MDC1	H11	MasterDuty	24	70	PGJ19-2	82583430	8711500825834	-	8727900371055	51
24362MLC1	H11	MasterLife	24	70	PGJ19-2	82575930	8711500825759	-	8727900371062	51

## Kits

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
<b>12V Spare kits</b>										
55472EKKM	H1	Easy Kit	12	-	-	69551928	8727900695519	-	8727900695533	58
55473EKKM	H4	Easy Kit	12	-	-	69555728	8727900695557	-	8727900695571	58
55474EKKM	H7	Easy Kit	12	-	-	69558828	8727900695588	-	8727900695601	58
55475EKKM	H1/H7	Easy Kit	12	-	-	69562528	8727900695625	-	8727900695656	58
55717EBKM	H1	Essential Box	12	-	-	70032928	8727900700329	-	8727900700336	59
55718EBKM	H4	Essential Box	12	-	-	70034328	8727900700343	-	8727900700350	59
55719EBKM	H7	Essential Box	12	-	-	70036728	8727900700367	-	8727900700374	59
55720EBKM	H1/H7	Essential Box	12	-	-	70038128	8727900700381	-	8727900700398	59
<b>24V Spare kits</b>										
55554SKMDKM	MiniKit H4	MasterDuty	24	-	-	69586130	8727900695861	-	8727900695885	60
55555SKMDKM	MiniKit H7	MasterDuty	24	-	-	69590830	8727900695908	-	8727900695939	60
55559LKMDKM	MaxiKit H4	MasterDuty	24	-	-	69684494	8727900696844	-	8727900696851	60
55560LKMDKM	MaxiKit H7	MasterDuty	24	-	-	69686894	8727900696868	-	8727900696875	60
55561LKMDKM	MaxiKit H1/H7	MasterDuty	24	-	-	69688294	8727900696882	-	8727900696899	60
<b>Headlight restoration kit</b>										
HRK00XM	-	-	-	-	-	39976931	8727900399769	-	8727900399776	61



## Xenon lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12410C1	D5S	Vision	12	25	PK32d-7	36981633	8727900369816	-	8727900369823	72
42306VIC1	D3R	Vision	42	35	PK32d-6	36483533	8727900364835	-	8727900364842	72
42402VIC1	D4S	Vision	42	35	P32d-5	36485933	8727900364859	-	8727900364866	72
42402XV2C1	D4S	X-tremeVision gen2	42	35	P32d-5	37721733	8727900377217	-	8727900377224	72
42402XV2S1	D4S	X-tremeVision gen2	42	35	P32d-5	37719433	8727900377194	-	8727900377200	72
42403VIC1	D3S	Vision	42	35	PK32d-5	36481133	8727900364811	-	8727900364828	72
42403VIS1	D3S	Vision	42	35	PK32d-5	36495833	8727900364958	-	8727900364965	72
42403WHV2C1	D3S	WhiteVision gen2	42	35	PK32d-5	37737833	8727900377378	-	8727900377385	72
42403WHV2S1	D3S	WhiteVision gen2	42	35	PK32d-5	37735433	8727900377354	-	8727900377361	72
42403XV2C1	D3S	X-tremeVision gen2	42	35	PK32d-5	37717033	8727900377170	-	8727900377187	72
42403XV2S1	D3S	X-tremeVision gen2	42	35	PK32d-5	37713233	8727900377132	-	8727900377149	72
42406VIC1	D4R	Vision	42	35	P32d-6	36487333	8727900364873	-	8727900364880	72
85122SYC1	D2S	LongerLife	85	35	P32d-2	37518333	8727900375183	-	8727900375190	71
Ordering codes for Germany, Austria, Switzerland, Netherlands										
85122SYC1	D2S	LongerLife	85	35	P32d-2	37244133	8727900372441	-	8727900372458	71
Ordering codes for Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom										
85122SYC1	D2S	LongerLife	85	35	P32d-2	37524433	8727900375244	-	8727900375251	71
Ordering codes for Central Europe (Poland, Romania, Czech Republic) and other East European countries										
85122SYS1	D2S	LongerLife	85	35	P32d-2	37254033	8727900372540	-	8727900372557	71
Ordering codes for Germany, Austria, Switzerland, Netherlands, Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom										
85122VIC1	D2S	Vision	85	35	P32d-2	36477433	8727900364774	-	8727900364781	70
85122VIS1	D2S	Vision	85	35	P32d-2	36491033	8727900364910	-	8727900364927	70
85122WHV2C1	D2S	WhiteVision gen2	85	35	P32d-2	37729333	8727900377293	-	8727900377309	71
85122WHV2S1	D2S	WhiteVision gen2	85	35	P32d-2	37727933	8727900377279	-	8727900377286	71
85122XV2C1	D2S	X-tremeVision gen2	85	35	P32d-2	37707133	8727900377071	-	8727900377088	70
85122XV2S1	D2S	X-tremeVision gen2	85	35	P32d-2	37703333	8727900377033	-	8727900377040	70
85126SYC1	D2R	LongerLife	85	35	P32d-3	37520633	8727900375206	-	8727900375213	71
Ordering codes for Germany, Austria, Switzerland, Netherlands										
85126SYC1	D2R	LongerLife	85	35	P32d-3	37252633	8727900372526	-	8727900372533	71
Ordering codes for Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom										
85126SYC1	D2R	LongerLife	85	35	P32d-3	37526833	8727900375268	-	8727900375275	71
Ordering codes for Central Europe (Poland, Romania, Czech Republic) and other East European countries										
85126SYS1	D2R	LongerLife	85	35	P32d-3	37248933	8727900372489	-	8727900372496	71
Ordering codes for Germany, Austria, Switzerland, Netherlands										
85126VIC1	D2R	Vision	85	35	P32d-3	36479833	8727900364798	-	8727900364804	71
85126VIS1	D2R	Vision	85	35	P32d-3	36493433	8727900364934	-	8727900364941	71
85126WHV2C1	D2R	WhiteVision gen2	85	35	P32d-3	37733033	8727900377330	-	8727900377347	71
85126WHV2S1	D2R	WhiteVision gen2	85	35	P32d-3	37731633	8727900377316	-	8727900377323	71
85126XV2C1	D2R	X-tremeVision gen2	85	35	P32d-3	37711833	8727900377118	-	8727900377125	71
85126XV2S1	D2R	X-tremeVision gen2	85	35	P32d-3	37709533	8727900377095	-	8727900377101	71
85409VIC1	D1R	Vision	85	35	PK32d-3	36475033	8727900364750	-	8727900364767	70
85415SYC1	D1S	LongerLife	85	35	PK32d-2	37516933	8727900375169	-	8727900375176	70
Ordering codes for Germany, Austria, Switzerland, Netherlands										
85415SYC1	D1S	LongerLife	85	35	PK32d-2	37250233	8727900372502	-	8727900372519	70
Ordering codes for Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom										
85415SYC1	D1S	LongerLife	85	35	PK32d-2	37522033	8727900375220	-	8727900375237	70
Ordering codes for Central Europe (Poland, Romania, Czech Republic) and other East European countries										
85415SYS1	D1S	LongerLife	85	35	PK32d-2	37246533	8727900372465	-	8727900372472	70
Ordering codes for Germany, Austria, Switzerland, Netherlands, Scandinavia (Sweden, Norway, Finland, Denmark), United Kingdom										
85415VIC1	D1S	Vision	85	35	PK32d-2	36473633	8727900364736	-	8727900364743	70
85415VIS1	D1S	Vision	85	35	PK32d-2	36489733	8727900364897	-	8727900364903	70
85415WHV2C1	D1S	WhiteVision gen2	85	35	PK32d-2	37725533	8727900377255	-	8727900377262	70
85415WHV2S1	D1S	WhiteVision gen2	85	35	PK32d-2	36072133	8727900360721	-	8727900377248	70
85415XV2C1	D1S	X-tremeVision gen2	85	35	PK32d-2	37701933	8727900377019	-	8727900377026	70
85415XV2S1	D1S	X-tremeVision gen2	85	35	PK32d-2	37697533	8727900376975	-	8727900376982	70

## LED retrofit lighting

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
11005XUWX2	LED-HL [=HB3/HB4]	XU	12	25	P20d/P22d	39875531	8727900398755	-	8727900398762	83
11012XUX2	LED-HL [=HIR2]	XU	12	25	PX22d	05200131	8719018052001	-	8719018052018	83
11065ULAX2	LED-AMBER [=WY21W]	UL	12	0.75	W3Xx16d	05075530	8719018050755	-	8719018050762	88
11065ULRX2	LED-T20-RED [=W21W]	UL	12	2.7	W3x16d	05027430	8719018050274	-	8719018050281	87
11065ULWX2	LED-T20-WHITE [=W21W]	UL	12	1.95	W3x16d	05033530	8719018050335	-	8719018050342	87
11065XUAXM	LED-AMBER [=WY21W]	XU	12	1.8	W3x16d	05161530	8719018051615	-	8719018051622	88
11065XURX2	LED-RED [=W21W]	XU	12/24	2.1	W3x16d	05153030	8719018051530	-	8719018051547	86
11065XUWX2	LED-WHITE [=W21W]	XU	12/24	1.7	W3x16d	05146230	8719018051462	-	8719018051479	87
11066ULRX2	LED-T20-RED [=W21/5W]	UL	12	2.7	W3x16q	05029830	8719018050298	-	8719018050304	87
11066XURX2	LED-T20-RED [=W21/5W]	XU	12/24	0.3/2.2	W3x16q	05155430	8719018051554	-	8719018051561	87
11066XUWX2	LED-T20-WHITE [=W21/5W]	XU	12/24	0.3/1.8	W3x16q	05149330	8719018051493	-	8719018051509	87
11258XUX2	LED-HL [=H1]	XU	12	25	P14,5s	06030331	8719018060303	-	8719018060310	83
11342ULWX2	LED-HL [=H4]	UL	12	15	P43t-38	39859531	8727900398595	-	8727900398601	83
11342XUWX2	LED-HL [=H4]	XU	12	22	P43t-38	06012931	8719018060129	-	8719018060136	83
11362XUX2	LED-HL [=H11]	XU	12	22	PGJ19-2	05202531	8719018052025	-	8719018052032	83
11366ULWX2	LED-FOG [=H8/H11/H16]	UL	12	10	PGJ19-1/2/3	39863231	8727900398632	-	8727900398649	83
11366XUWX2	LED-HL [=H8/H11/H16]	XU	12	15.5	PGJ19-1/2/3	06016731	8719018060167	-	8719018060174	83
11498ULAX2	LED-AMBER [=PY21W]	UL	12	0.75	BAU15s	05073130	8719018050731	-	8719018050748	88
11498ULRX2	LED-RED [=P21W]	UL	12	2.7	BA15s	05023630	8719018050236	-	8719018050243	86
11498ULWX2	LED-WHITE [=P21W]	UL	12	1.95	BA15s	05035930	8719018050359	-	8719018050366	87
11498XUAXM	LED-AMBER [=PY21W]	XU	12	1.8	BAU15S	05159230	8719018051592	-	8719018051608	88
11498XURX2	LED-RED [=P21W]	XU	12/24	2.3	BA15s	05157830	8719018051578	-	8719018051585	86
11498XUWX2	LED-WHITE [=P21W]	XU	12/24	2.7	BA15s	05145530	8719018051455	-	8719018051486	87
11499ULRX2	LED-RED [=P21/5W]	UL	12	2.7	BAY15d	05025030	8719018050250	-	8719018050267	86
11499XURX2	LED-RED [=P21/5W]	XU	12/24	0.3/2.2	BAY15d	05151630	8719018051516	-	8719018051523	86
11854ULWX1	LED-FEST 38mm 6000K	UL	12	0.6	SV8,5-8	05039730	8719018050397	-	8719018050403	85
11860ULWX1	LED-FEST 30mm 6000K	UL	12	0.6	SV8,5-8	05037330	8719018050373	-	8719018050380	85
11864ULWX1	LED-FEST 43mm 6000K	UL	12	0.6	SV8,5-8	05041030	8719018050410	-	8719018050427	85
11961ULW4X2	LED-T10 [=W5W] 4 000 K	UL	12	0.6	W2,1x9,5d	05083030	8719018050830	-	8719018050847	86
11961ULWX2	LED-T10 [=W5W] 6000K	UL	12	0.6	W2,1x9,5d	05031130	8719018050311	-	8719018050328	86
11972ULWX2	LED-HL [=H7]	UL	12	14	PX26d	39861831	8727900398618	-	8727900398625	83
11972XUWX2	LED-HL [=H7]	XU	12	25	PX26d	06014331	8719018060143	-	8719018060150	83
127994000KX2	LED-T10 [=W5W] 4000K	XU	12	0.9	W2,1x9,5d	39594530	8727900395945	-	8727900395952	86
127996000KX2	LED-T10 [=W5W] 6000K	XU	12	0.9	W2,1x9,5d	39596930	8727900395969	-	8727900395976	86
127998000KX2	LED-T10 [=W5W] 8000K	XU	12	0.9	W2,1x9,5d	39598330	8727900395983	-	8727900395990	86
128584000KX1	LED-FEST 38mm 4000K	XU	12	1	SV8,5-8	39706230	8727900703412	-	8727900703405	85
128596000KX1	LED-FEST 38mm 6000K	XU	12	1	SV8,5-8	39708630	8727900703399	-	8727900703382	85
129404000KX1	LED-FEST 30mm 4000K	XU	12	1	SV8,5-8	39714730	8727900397147	-	8727900397154	85
129416000KX1	LED-FEST 30mm 6000K	XU	12	1	SV8,5-8	39716130	8727900387223	-	8727900387230	85
129454000KX1	LED-FEST 43mm 4000K	XU	12	1	SV8,5-8	39710930	8727900397109	-	8727900397116	85
129466000KX1	LED-FEST 43mm 6000K	XU	12	1	SV8,5-8	39712330	8727900383416	-	8727900383423	85
249446000KX1	LED-FEST 38mm 6000K	XU	24	1	SV8,5	39718530	8727900384185	-	8727900384192	89
249466000KX1	LED-FEST 43mm 6000K	XU	24	1	SV8,5	39720830	8727900397208	-	8727900397215	89

## LED retrofit CANbus adapter

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
12956X2	LED-CANBUS [=5W]	-	12	5		39722230	8727900397222		8727900397239	88
18952C2	LED-CANBUS for LED-HL [=H7]	-	12	10		05064930	8719018050649	-	8719018050656	88
18954C2	LED-CANBUS for LED-FOG [=H8/H11/H16]	-	12	10		05066330	8719018050663	-	8719018050670	88
18957X2	LED-CANBUS [=21W]	-	12	21		39587730	8727900395877		8727900395884	88
18960C2	LED-CANBUS for LED-HL [=H4]	-	12	10		39809030	8727900398090	-	8727900398106	88

## LED retrofit Connector ring

Ordering number	Type	Range	V	W	Base	GOC	EAN1	EAN2	EAN3	Page
11172BX2	Type B - LED connector ring for LED-HL [H7]	-	-	-	-	05121930	8719018051219		8719018051226	88
11172CX2	Type C - LED connector ring for LED-HL [H7]	-	-	-	-	05123330	8719018051233		8719018051240	88







2019 © Lumileds Holding B.V. All rights reserved.

The Philips trademark and the Philips shield emblem are registered trademarks of Koninklijke Philips N.V. Specifications are subject to change without notice.

[www.philips.com/automotive](http://www.philips.com/automotive)