

Which LED for which function?



Headlights	Front fog lights	Front position/parking lights	Front indicators	Dashboard lights	Interior lights	Glove compartment lights	Rear position/parking lights	Rear indicators	Rear fog lights	Trunk lights	License plate lights	3rd stop light	Stop lights	Reversing light



Ultinon Pro9000 HL

X-tremeUltinon LED



Ultinon Pro5000 HL

Ultinon LED



Ultinon Essential HL

Ultinon Pro3000 SL



LED adapters

--	--	--

LED adapters

--	--	--	--	--	--	--	--	--	--	--	--	--

*LED CANbus adapter 21W included in the pack