

# L'illuminazione a LED adatta a ogni funzione



Abbaglianti, anabbaglianti	Luci antinebbia anteriori	Luci di stazionamento	Indicatori di direzione anteriori	Luce cruscotto	Illuminazione interna	Luce vano portaoggetti	Luci di stazionamento posteriori	Indicatori di direzione posteriori	Luci antinebbia posteriori	Luce portabagaglio	Luce targa	3° luce stop	Luci stop	Luci di retromarcia



### Ultinon Pro9000 HL

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		

### X-tremeUltinon LED

SL-WHITE [≈W5W]	SL-AMBER [≈PY21W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	SL-RED [≈P21/5W]	SL-AMBER [≈PY21W]	SL-RED [≈P21W]	IL/SL-WHITE [≈W5W]	SL-WHITE [≈W5W]	SL-RED [≈P21W]	SL-RED [≈P21W], [≈P21/5W]	SL-RED [≈P21W]	SL-WHITE [≈P21W]
SL-WHITE [≈W21/5W]	SL-AMBER [≈WY21W]	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21/5W]	SL-AMBER [≈WY21W]	SL-RED [≈W21W]	SL-WHITE Fest 30/38/43 mm	SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21W]	SL-RED [≈W21W], [≈W21/5W]	SL-RED [≈W21W]	SL-WHITE [≈W21W]



### Ultinon Pro5000 HL

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		

### Ultinon LED

SL-WHITE [≈W5W]	SL-AMBER [≈PY21W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	SL-RED [≈P21/5W]	SL-AMBER [≈PY21W]	SL-RED [≈P21W]	IL/SL-WHITE [≈W5W]	SL-WHITE [≈W5W]	SL-RED [≈P21W]	SL-RED [≈P21W], [≈P21/5W]	SL-RED [≈P21W]	SL-WHITE [≈P21W]
SL-WHITE [≈W21/5W]	SL-AMBER [≈WY21W]	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21/5W]	SL-AMBER [≈WY21W]	SL-RED [≈W21W]	SL-WHITE Fest 30/38/43 mm	SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21W]	SL-RED [≈W21W], [≈W21/5W]	SL-RED [≈W21W]	SL-WHITE [≈W21W]



### Ultinon Essential HL

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		

### Ultinon Pro3000 SL

SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	SL-RED [≈P21/5W]	SL-RED [≈P21W]	IL/SL-WHITE [≈W5W]	SL-WHITE [≈W5W]	SL-RED [≈P21W]	SL-RED [≈P21W], [≈P21/5W]	SL-RED [≈P21W]	SL-WHITE [≈P21W]
SL-WHITE [≈W5W]	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21/5W]	SL-RED [≈W21W]	SL-WHITE Fest 30/38/43 mm	SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21W]	SL-RED [≈W21W], [≈W21/5W]	SL-RED [≈W21W]	SL-WHITE [≈W21W]



### Adattatori LED

CANbus adapter HL [≈H4], [≈H7]	Light Repair HL [≈H1], [≈H7]	CANbus adapter FL [≈H8/H11/H16]

### Adattatori LED

CANbus adapter SL [≈5W]	Smart CANbus SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	Smart CANbus SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]

\*Adattatore LED CANbus 21W incluso nella confezione