

Which car lamp do you need?



Enhanced brightness

<p>New</p> <p>Up to 200% more brightness*</p> <p>RacingVision GT200</p> <p>Beam up to +80 m***</p> <p>Beam performance* Up to +200% +80 m</p> <p>Light color** Up to 3500 K Standard: 3100 K</p> <p>Lifetime** Up to 250 h</p> <p>Available in H4, H7</p>	<p>New</p> <p>Up to 150% more brightness*</p> <p>X-tremeVision Pro150</p> <p>Beam up to +70 m***</p> <p>Beam performance* Up to +150% +70 m</p> <p>Light color** Up to 3400 K Standard: 3100 K</p> <p>Lifetime** Up to 450 h</p> <p>Available in H1, H4, H7, H11, HB3, HB4, HIR2</p>	<p>Up to 60% more vision*</p> <p>VisionPlus</p> <p>Beam performance* Up to +60%</p> <p>Light color** Up to 3250 K Standard: 3100 K</p> <p>Lifetime** Up to 500 h</p> <p>Available in H1, H4, H7</p>	<p>Up to 30% more vision*</p> <p>Vision</p> <p>Beam performance* Up to +30%</p> <p>Light color** Up to 3200 K Standard: 3100 K</p> <p>Lifetime** Up to 600 h</p> <p>Available in H1, H3, H4, H7, H11, HB3, HB4</p>
--	---	---	--

Unique style

New

Sharp white look

WhiteVision ultra

H4, H7 up to **4200 K**

Beam performance* **Up to +60%**

Light color** Up to **4200 K**
Standard: 3100 K

Lifetime** Up to **350 h**

Available in **H1, H3, H4, H7, H8, H11, HB3, HB4, HIR2, PSX24W**

Extended lifetime

Lifetime up to **1500 hours****

LongLife EcoVision

Beam performance

Light color** Up to **3100 K**
Standard: 3100 K

Lifetime** Up to **1500 h**

Available in **H1, H3, H4, H7, H11, H18, H19, HIR2**

Images for illustration purposes only. * Compared to the minimum legal standard. ** Lifetime and color temperature differ per type, indication for H7 only. *** Compared to derived minimum after ECE regulation, based on 1 Lux. Farthest distance from the car, applies to H4 and H7.