



LED-HL [≈H1]	LED-HL [≈H4]	LED-HL [≈H7]	LED-T10 [≈W5W]	LED-FOG [≈H8/H11/H16]	LED-AMBER [≈PY21W]	LED-T10 [≈W5W]	LED-T10 [≈W5W]
LED-HL [≈HB3/HB4]	LED-HL [≈H11]	LED-HL [≈H12]	LED-T20-WHITE [≈W21/5W]	LED-AMBER [≈WY21W]	LED-Fest 30/38/43 mm	LED-Fest 30/38/43 mm	LED-Fest 30/38/43 mm
5800K	5800K	5800K	6000K	5800K	CAN bus*	4000K	4000K
5800K	5800K	5800K	6000K	5800K	AMBER	4000K	4000K
5800K	5800K	5800K	6000K	5800K	AMBER	4000K	4000K

LED-HL [≈H4] LED-HL [≈H7]	LED-T10 [≈W5W]	LED-FOG [≈H8/H11/H16]	LED-AMBER [≈PY21W] LED-AMBER [≈WY21W]	LED-T10 [≈W5W] LED-Fest 30/38/43 mm	LED-T10 [≈W5W] LED-Fest 30/38/43 mm
---	---	--	--	---	---

CANbus LED-HL ≈H4	CANbus LED-HL ≈H7	CANbus 5W	CANbus LED-FOG ≈H8/H11/H16	Smart CANbus 21W	CANbus 5W	CANbus 5W



4000K 6000K LED-T10 [≈W5W]	6000K 8000K LED-T10 [≈W5W]	CAN bus⁺ LED-AMBER [≈PY21W]	RED LED-RED [≈P21W]	4000K 6000K LED-T10 [≈W5W]	6000K 8000K LED-T10 [≈W5W]	RED LED-RED [≈P21W]	RED LED-RED [≈P21W], [≈P21/5W]	WHITE LED-WHITE [≈P21W]
4000K 6000K LED-Fest 30/38/43 mm	RED LED-(T20)-RED [≈P21/5W], [≈W21/5W]	CAN bus⁺ LED-AMBER [≈WY21W]	RED LED-T20-RED [≈W21W]	4000K 6000K LED-Fest 30/38/43 mm	6000K LED-Fest 30/38/43 mm	RED LED-T20-RED [≈W21W]	RED LED-T20-RED [≈W21W], [≈W21/5W]	WHITE LED-T20-WHITE [≈W21W]

 LED-T10 [≈W5W]	 LED-RED [≈P21/5W]	 LED-AMBER [≈PY21W]	 LED-RED [≈P21W]	 LED-T10 [≈W5W]	 LED-T10 [≈W5W]	 LED-RED [≈P21W]	 LED-RED [≈P21W], [≈P21/5W]	 LED-WHITE [≈P21W]
 LED-Fest 30/38/43 mm	 LED-T20-RED [≈W21/5W]	 LED-AMBER [≈WY21W]	 LED-T20-RED [≈W21W]		 LED-Fest 30/38/43 mm	 LED-T20-RED [≈W21W]	 LED-T20-RED [≈W21W], [≈W21/5W]	 LED-T20-WHITE [≈W21W]

CANbus 5W	CANbus 5W	Smart CANbus 21W	CANbus 21W	CANbus 5W	CANbus 5W	CANbus 21W	CANbus 21W	CANbus 21W

 

PHILIPS