

# Which LED lamp do you need?



New

Original automotive performance in LED

Ultinon Pro9000

Lumileds TopContact OEM LED

2 years

+3 extended warranty



Beam performance



Light color


Up to 5800 K



Standard: 3100 K

Lifetime

Up to 5000 h



Available in

LED-HL [≈H1], [≈H3], [≈H4], [≈H7], [≈HB3/4], [≈H11], [≈HIR2]

LED-FL [≈H8/H11/H16]

New

The perfect blend of performance and durability

Ultinon Pro5000

Automotive grade LED

2 years

+1 extended warranty



Beam performance



Light color


Up to 5800 K



Standard: 3100 K

Lifetime

Up to 3000 h



Available in

LED-HL [≈H1], [≈H3], [≈H4], [≈H7], [≈HB3/4], [≈H11], [≈HIR2]


LED-FL [≈H8/H11/H16]

Transform your car lights

Ultinon Essential



Beam performance



Light color


Up to 6500 K



Standard: 3100 K

Lifetime

Up to 1500 h



Available in

LED-HL [≈H1], [≈H3], [≈H4], [≈H7], [≈HB3/4], [≈H11], [≈HIR2]

LED-FL [≈H8/H11/H16]

Images for illustration purposes only.

\* Applies to Ultinon Pro9000 HL [≈H4], [≈H7], [≈HB3/4], [≈H11], [≈HIR2] and FOG [≈H8/H11/H16].

\*\* Compared to the minimum legal standard for halogen bulbs. Up to +200% for Ultinon Pro9000 HL [≈H1] and [≈H3] types.



It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.