

Which car lamp do you need?



Enhanced brightness

<p>New</p> <p>Up to 200% more brightness¹</p> <p>RacingVision GT200</p> <p>Beam up to +80 m²</p>   <p>Light color⁴ Up to 3500 K Standard: 3100 K</p> <p>Lifetime⁴ Up to 250 h</p> <p>Available in H4, H7</p>	<p>Up to 130% more brightness¹</p> <p>X-tremeVision G-force</p> <p>10 G Vibration resistant</p>   <p>Light color⁴ Up to 3500 K Standard: 3100 K</p> <p>Lifetime⁴ Up to 450 h</p> <p>Available in H1, H4, H7, H11, HB3, HB4³</p>	<p>Up to 60% more vision¹</p> <p>VisionPlus</p>   <p>Light color⁴ Up to 3250 K Standard: 3100 K</p> <p>Lifetime⁴ Up to 500 h</p> <p>Available in H1, H4, H7</p>	<p>Up to 30% more vision¹</p> <p>Vision</p>   <p>Light color⁴ Up to 3200 K Standard: 3100 K</p> <p>Lifetime⁴ Up to 600 h</p> <p>Available in H1, H3, H4, H7, H11, HB3, HB4</p>
---	---	---	--



Unique style

<p>New</p> <p>Sharp white look</p> <p>WhiteVision ultra</p> <p>H4, H7 up to 4200 K</p>   <p>Light color⁴ Up to 4200 K Standard: 3100 K</p> <p>Lifetime⁴ Up to 350 h</p> <p>Available in H1, H3, H4, H7, H8, H11, HB3, HB4, HIR2, PSX24W</p>	<p>Ultimate white light</p> <p>DiamondVision⁵</p>   <p>Light color⁴ Up to 5000 K Standard: 3100 K</p> <p>Lifetime⁴ Up to 400 h</p> <p>Available in H1, H3, H4, H7, H11, HB3, HB4</p>	<p>Bright white light</p> <p>CrystalVision⁵</p>   <p>Light color⁴ Up to 4300 K Standard: 3100 K</p> <p>Lifetime⁴ Up to 400 h</p> <p>Available in H1, H3, H4, H7, H11, HB3, HB4</p>
--	--	--

Extended lifetime

Lifetime up to **1500 hours⁴**

LongLife EcoVision

Light color⁴
Up to **3100 K**
Standard: 3100 K

Lifetime⁴
Up to **1500 h**

Available in H1, H3, H4, H7, H11, H18, H19, HIR2

Images for illustration purposes only. ¹ Compared to the minimum legal standard. ² Compared to derived minimum after ECE regulation, based on 1 Lux. Farthest distance from the car, applies to H4 and H7. ³ 10 G applies to H4 and H7. ⁴ Lifetime and color temperature differ per type, indication for H7 only. ⁵ Non-ECE homologated, for off-road only.