




Which **xenon lamp** do you need?


Enhanced **brightness**

Up to **150% more vision***


Xenon X-tremeVision gen2



Beam performance*



Light color




Available in
D1S, D2S, D2R, D3S,
D4S, D5S

Ideal for **replacement**


Xenon Vision



Beam performance



Light color



Available in
D1S, D1R, D2S, D2R, D3S,
D3R, D4S, D4R, D5S, D8S


Unique **style**

Homogeneous white
LED effect


Xenon WhiteVision gen2



Beam performance*



Light color



Available in
D1S, D2S, D2R, D3S

Images for illustration purposes only.

* Compared to the minimum legal standard (except for D2R that provides up to 20% more vision, and D5S which supports up to 120% more vision).