

PHILIPS

Automotive

Find the right **professional**  
**LED work light** for the job



	New										New			
HDL10	HL22M	Penlight Professional	PEN20S	Penlight Premium	RCH5S	RCH10S	RCH21S	RCH25	RCH31UV	CBL10	CBH52	PJH10	PJH20	MDLS CRI
Boost light 100 lm <10 h	Boost light 300 lm <3 h	Boost light 130 lm <11 h	Boost light 200 lm <2 h	Boost light 145 lm <2.5 h	Boost light 300 lm <1.5 h	Boost light 200 lm <3 h	Boost light 300 lm 3.5 h	Boost light 500 lm <3.5 h	Boost light 350 lm 3.5 h	Boost light 330 lm	Boost light 1200 lm <3 h	Boost light 1000 lm <3 h	Boost light 2300 lm 2 h	Boost light 1500 lm 1 h
Eco light 50 lm <10 h	Eco light 150 / 50 lm <6 / <12 h		Eco light 100 lm <4 h	Eco light 60 lm <6 h	Dimmed light 30 lm <12 h	Eco light 100 lm <6 h	Eco light 120 lm 6 h	Dimmed light 50 lm <10 h	Eco light 150 lm <8 h		Eco light 900 / 500 lm <4 / <5 h	Dimmed light 100 lm <12 h	Eco light 1200 lm 4 h	Eco light 750 lm 2.5 h
Light angle/flexibility 50° 90°	Light angle/flexibility 110° 45°	Light angle/flexibility 40°	Light angle/flexibility 80°	Light angle/flexibility 80°	Light angle/flexibility 120° 180°	Light angle/flexibility 120°	Light angle/flexibility 90° 90°	Light angle/flexibility 120° 180°	Light angle/flexibility 90° 90°	Light angle/flexibility 120°	Light angle/flexibility 120° 360°	Light angle/flexibility 90° 180°	Light angle/flexibility 90° 180°	Light angle/flexibility 360° 120°
Fixture Headband	Fixture Headband	Features 20 lm spot light	Features 100 lm spot light	Features 120 lm spot light	Features Dimming 120 lm		Features FindMe	Features Dimming 300 lm	Features UV light FindMe		Features Sliding light module	Features Dimming	Features CRI 92 Matte filter	Features CRI 92 Matte filter
Robustness IPX4	Robustness IP67 IK07	Robustness IP54	Robustness IP54 IK07	Robustness IP54 IK07	Robustness IP68 IK09	Robustness IP54 IK07	Robustness IP65 IK08	Robustness IP68 IK09	Robustness IP54 IK07	Robustness IP54 IK07	Robustness IP54 IK07	Robustness IP68 IK09	Robustness IP67 IK09	Robustness IP54 IK07
Grease resistance	Grease resistance	Grease resistance	Grease resistance	Grease resistance	Grease resistance	Grease resistance	Grease resistance	Grease resistance	Grease resistance	Grease resistance	Grease resistance	Grease resistance	Grease resistance	Grease resistance
Garage proof	Garage proof	Garage proof	Garage proof	Garage proof	Garage proof	Garage proof	Garage proof	Garage proof	Garage proof	Garage proof	Garage proof	Garage proof	Garage proof	Garage proof
Power supply 3x AAA	Power supply <3 h	Power supply 3x AAA	Power supply <2 h	Power supply 2 h	Power supply <2.5 h	Power supply <3 h	Power supply <2 h	Power supply <3.5 h	Power supply 2.5 h	Power supply 100-240 V 5 m	Power supply 100-240 V 5 m	Power supply <4.5 h	Power supply 100-240 V 5 m	Power supply 1.1 h 3.2 h
	Charging features Micro USB		Charging features Micro USB 1500x	Charging features Micro USB	Charging features Docking station	Charging features Micro USB 1500x	Charging features Docking station	Charging features Docking station	Charging features Docking station		Charging features 3.2 h	Charging features Micro USB	Charging features 3.5 h Power bank	Charging features 1500x
Order entry LPL29B1 GOC 39360631	Order entry LPL74X1 GOC 00824431	Order entry LPL19B1 GOC 38819031	Order entry LPL67X1 GOC 05261231	Order entry LPL28RECHX1 GOC 39220394	Order entry LPL62X1 GOC 05163931	Order entry LPL66X1 GOC 05205631	Order entry LPL47X1 GOC 39841031	Order entry LPL63X1 GOC 05165331	Order entry LPL34UVX1 GOC 39419131	Order entry LPL35X1 GOC 39421431	Order entry LPL73X1 GOC 00521231	Order entry LPL64X1 GOC 05167731	Order entry LPL39X1 GOC 39609631	Order entry LPL403MODX1 GOC 39627066