

# Which **xenon** lamp do you need?



## Enhanced brightness




Up to **150%**  
more vision\*

**Xenon X-tremeVision gen2**



Standard




Xenon X-tremeVision gen2



### Beam performance\*



### Light color



Available in  
D1S, D2S, D2R, D3S,  
D4S, D5S

Ideal for  
**replacement**

**Xenon Vision**




Standard




Xenon Vision



### Beam performance



### Light color



Available in  
D1S, D1R, D2S, D2R, D3S,  
D3R, D4S, D4R, D5S, D8S

## Unique style



**Homogeneous white**  
LED effect

**Xenon WhiteVision gen2**




Standard




Xenon WhiteVision gen2



### Beam performance\*



### Light color




Available in  
D1S, D2S, D2R, D3S

## Extended lifetime




Peace of mind  
**4 + 3** years  
warranty

**Xenon LongerLife\*\***



**4** years warranty  
**+3**

### Beam performance



### Lifetime



Available in  
D1S, D2S, D2R

Images for illustration purposes only.

\* Compared to the minimum legal standard (except for D2R that provides up to 20% more vision, and D5S which supports up to 120% more vision).

\*\* Not available in all countries, please contact your sales representative.