



Ultinon Drive
LED Lightbars



Philips Ultinon Drive 5000L

Powerful brightness for a safer drive

September 2021

Projecting light for approximately 400 meters (up to 458, depending on model)*, the Ultinon Drive 5000L series of LED lightbars is road-legal for cars and trucks, rated ECE-R149 (with reference numbers ranging from 37.5 to 50). It ensures safety through brightness, is built to last, corrosion-free, and resistant to water and shocks. The UD5050L is equipped with the off-road boost function, unleashing its full power to 4000 Lumen and providing additional visibility in difficult terrain.



UD5050L



UD5001L



UD5002L



UD5003L



UD5004L

Bright, long beam for superior visibility

- Outstanding beam for approx. 400 meters*
- ECE R149 with reference numbers from 37.5 to 50**
- Homogenous beam with up to 6500 Kelvin crisp white light



Enhanced safety off-road with boost function for more power***

- The UD5050L unleashes its full 4000 Lumen off-road for 448 meters visibility



Ultra-durable gear

- Sturdy one-piece design with performance heatsink
- Unbreakable polycarbonate lens
- Corrosion-free stainless-steel brackets
- Water and dust ingress: IP69K & IP68
- Shock resistance: IK07



Powerful road-legal LED lightbars

- Approved for road use under ECE R149



* Beam length measured on 1 lux. See table for details.

** For effective lumen, wattage, ECE reference number, see table for details.

*** Applies to UD5050L with off-road boost mode.

PHILIPS

Ultinon Drive LED Lightbars



Philips Ultinon Drive 5000L

September 2021



Codes

| PHILIPS DESIGNATION | REFERENCE | 12NC | EAN1 | EAN3 | GOC | MOQ |
|---|-----------|----------------|---------------|---------------|----------|-----|
| Ultinon Drive 5001L 10" single-row LED Lightbar | UD5001LX1 | 9237.950.00101 | 8719018014849 | 8719018014856 | 01484994 | 4 |
| Ultinon Drive 5002L 20" single-row LED Lightbar | UD5002LX1 | 9237.950.00201 | 8719018014863 | 8719018014870 | 01486394 | 4 |
| Ultinon Drive 5003L 20" double-row LED Lightbar | UD5003LX1 | 9237.950.00301 | 8719018014887 | 8719018014894 | 01488794 | 4 |
| Ultinon Drive 5004L 30" single-row LED Lightbar | UD5004LX1 | 9237.950.00401 | 8719018014900 | 8719018014917 | 01490033 | 2 |
| Ultinon Drive 5050L 10" double-row boost LED Lightbar | UD5050LX1 | 9237.950.00501 | 8719018014931 | 8719018014924 | 01493194 | 4 |

Delivery information

| REFERENCE | 12NC | PACK | EAN1 | | | | | EAN3 | | | | | Pallet | | | | |
|-----------|----------------|------|------|------|------|-----|--------------|------|------|------|------|--------------|--------|-----|-----|-----|--------------|
| | | | QTY | L | B | H | Gross Weight | QTY | L | B | H | Gross Weight | QTY | L | B | H | Gross Weight |
| UD5001LX1 | 9237.950.00101 | X1 | 1 | 35.0 | 9.0 | 9.0 | 742 | 4 | 37.0 | 20.0 | 20.0 | 3.0 | 360 | 115 | 100 | 140 | 277 |
| UD5002LX1 | 9237.950.00201 | X1 | 1 | 61.0 | 9.0 | 9.0 | 1,195 | 4 | 63.0 | 20.0 | 20.0 | 4.8 | 168 | 120 | 100 | 140 | 210 |
| UD5003LX1 | 9237.950.00301 | X1 | 1 | 61.0 | 10,5 | 9.0 | 1,637 | 4 | 63.0 | 20.0 | 23.0 | 6.6 | 140 | 120 | 100 | 130 | 239 |
| UD5004LX1 | 9237.950.00401 | X1 | 1 | 86,5 | 9.0 | 9.0 | 1,620 | 2 | 88.0 | 20.0 | 11.0 | 3.3 | 132 | 110 | 100 | 140 | 225 |
| UD5050LX1 | 9237.950.00501 | X1 | 1 | 35.0 | 10.5 | 9.0 | 1,020 | 4 | 37.0 | 20.0 | 23.0 | 4.1 | 300 | 115 | 100 | 135 | 316 |