

Welche LED-Beleuchtung für welche Funktion?



Frontscheinwerfer	Nebelscheinwerfer	Parkleuchten vorne	Blinkerleuchten vorne	Armaturenbeleuchtung	Innenraumbeleuchtung	Blinkerleuchten seitlich	Handschuhfachbeleuchtung	Parkleuchten hinten	Blinkerleuchten hinten	Nebelschlussleuchten	Kofferraumbeleuchtung	Kennzeichenbeleuchtung	Drittes Bremslicht	Bremsleuchten	Rückfahrleuchten



Ultinon Pro9000 HL

HL [≈H1] 5800K	HL [≈H3] 5800K	HL [≈H4] 5800K	HL [≈H7] 5800K	FL [≈H8/H11/H16] 5800K
HL [≈HB3/HB4] 5800K	HL [≈H11] 5800K	HL [≈HIR2] 5800K		

Ultinon Pro6000 SL

SL-T10 [≈W5W] 4000K, 6000K, 8000K	SL-AMB [≈P21W] AMBER	SL-AMB [≈P21/5W] AMBER	SL-T10 [≈W5W] 4000K, 6000K	SL-T10 [≈W5W] 4000K, 6000K	SL-AMB [≈W5W] AMBER	SL-T10 [≈W5W] 4000K, 6000K	SL-RED [≈W5W] RED	SL-AMB [≈P21W] AMBER	SL-RED [≈P21W] RED	SL-T10 [≈W5W] 4000K, 6000K, 8000K	SL-T10 [≈W5W] 4000K, 6000K, 8000K	SL-RED [≈P21W] RED	SL-RED [≈P21W] RED	SL-WHITE [≈P21W] WHITE
SL-WHITE [≈R5/R10] WHITE	SL-AMB [≈W21W] AMBER	SL-AMB [≈W21/5W] AMBER	SL-FEST 30/38/43 mm 4000K, 6000K	SL-T10 [≈W5W] 4000K, 6000K, 8000K	SL-FEST 30/38/43 mm 4000K, 6000K	SL-RED [≈W21/5W] RED	SL-AMB [≈P21/5W] AMBER	SL-RED [≈W21W] RED	SL-FEST 30/38/43 mm 4000K, 6000K	SL-FEST 30/38/43 mm 4000K, 6000K	SL-RED [≈W21W] RED	SL-RED [≈P21/5W] RED	SL-RED [≈P21/5W] RED	SL-WHITE [≈W21W] WHITE
SL-WHITE [≈P21/5W] WHITE	SL-WHITE [≈P21/5W] WHITE		SL-WHITE [≈R5/R10] WHITE	SL-WHITE [≈R5/R10] WHITE	SL-WHITE [≈R5/R10] WHITE		SL-AMB [≈W21W] AMBER		SL-WHITE [≈R5/R10] WHITE	SL-WHITE [≈R5/R10] WHITE	SL-WHITE [≈R5/R10] WHITE	SL-RED [≈W21W] RED	SL-RED [≈W21W] RED	SL-T16 [≈W16W] WHITE
SL-WHITE [≈W21/5W] WHITE	SL-WHITE [≈W21/5W] WHITE						SL-AMB [≈W21/5W] AMBER					SL-RED [≈W21/5W] RED		



Ultinon Pro5000 HL

HL [≈H1] 5800K	HL [≈H3] 5800K	HL [≈H4] 5800K	HL [≈H7] 5800K	FL [≈H8/H11/H16] 5800K
HL [≈HB3/HB4] 5800K	HL [≈H11] 5800K	HL [≈HIR2] 5800K		

LED-Adapter

CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]
-------------------------	--------------------------	-------------------------	-------------------------	-------------------------	-------------------------	--------------------------	--------------------------	--------------------------	--------------------------	-------------------------	-------------------------	--------------------------	--------------------------	--------------------------



LED-Adapter

CANbus adapter HL [≈H4], [≈H7]	Light Repair HL [≈H1], [≈H7]	CANbus adapter FL [≈H8/H11/H16]
--------------------------------	------------------------------	---------------------------------