

# Jaké LED osvětlení pro jakou funkci?



Světlomety	Přední mlhová světla	Přední parkovací světla	Přední ukazatele směru	Osvětlení přístrojové desky	Osvětlení interiéru	Boční ukazatel směru	Osvětlení odkládací schránky	Zadní parkovací světla	Zadní ukazatel směru	Zadní mlhové světlo	Osvětlení kufru	Osvětlení RZ	Třetí brzdové světlo	Brzdová světla	Zadní světlo



### Ultinon Pro9000 HL

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		

### Ultinon Pro6000 SL

SL-T10 [≈W5W]	SL-AMB [≈P21W]	SL-AMB [≈P21/5W]	SL-T10 [≈W5W]	SL-T10 [≈W5W]	SL-AMB [≈W5W]	SL-T10 [≈W5W]	SL-RED [≈P21/5W]	SL-AMB [≈P21W]	SL-RED [≈P21W]	SL-T10 [≈W5W]	SL-T10 [≈W5W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-WHITE [≈P21W]
SL-WHITE [≈R5/R10]	SL-AMB [≈W21W]	SL-AMB [≈W21/5W]	SL-FEST 30/38/43 mm	SL-T10 [≈W5W]	SL-FEST 30/38/43 mm	SL-RED [≈W21/5W]	SL-AMB [≈P21/5W]	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-FEST 30/38/43 mm	SL-FEST 30/38/43 mm	SL-RED [≈W21W]	SL-RED [≈P21/5W]	SL-RED [≈P21/5W]	SL-WHITE [≈W21W]
SL-WHITE [≈P21/5W]	SL-WHITE [≈P21/5W]	SL-WHITE [≈P21/5W]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-AMB [≈W21W]	SL-AMB [≈W21W]	SL-AMB [≈W21W]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-T16 [≈W16W]
SL-WHITE [≈W21/5W]	SL-WHITE [≈W21/5W]	SL-WHITE [≈W21/5W]					SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]				SL-RED [≈W21/5W]	SL-RED [≈W21/5W]	SL-RED [≈W21/5W]



### Ultinon Pro5000 HL

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		

### Ultinon Pro3000 SL

SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	SL-RED [≈P21/5W]	SL-RED [≈P21/5W]	SL-RED [≈P21W]	IL/SL-WHITE [≈W5W]	SL-WHITE [≈W5W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-WHITE [≈P21W]
IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21/5W]	SL-RED [≈W21/5W]	SL-RED [≈W21W]	SL-WHITE Fest 30/38/43 mm	SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-WHITE [≈W21W]



### Ultinon Essential

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		



### LED adaptéry

CANbus adapter HL [≈H4], [≈H7]	Light Repair HL [≈H1], [≈H7]	CANbus adapter FL [≈H8/H11/H16]

### LED adaptéry

CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]