

Which LED for which function?



Headlights	Front fog lights	Front position/parking lights	Front indicators	Dashboard lights	Interior lights	Side indicators	Glove compartment lights	Rear position/parking lights	Rear indicators	Rear fog lights	Trunk lights	License plate lights	3 rd stop light	Stop lights	Reversing light



Ultinon Pro9000 HL

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		

Ultinon Pro5000 HL

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		

Ultinon Essential

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		

LED adapters

CANbus adapter HL [≈H4], [≈H7]	Light Repair HL [≈H1], [≈H7]	CANbus adapter FL [≈H8/H11/H16]

Ultinon Pro6000 SL

SL-T10 [≈W5W]	SL-AMB [≈P21W]	SL-AMB [≈P21/5W]	SL-T10 [≈W5W]	SL-T10 [≈W5W]	SL-AMB [≈W5W]	SL-T10 [≈W5W]	SL-RED [≈P21/5W]	SL-AMB [≈P21W]	SL-RED [≈P21W]	SL-T10 [≈W5W]	SL-T10 [≈W5W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-WHITE [≈P21W]
SL-WHITE [≈R5/R10]	SL-AMB [≈W21W]	SL-AMB [≈W21/5W]	SL-FEST 30/38/43 mm	SL-T10 [≈W5W]	SL-FEST 30/38/43 mm	SL-RED [≈W21/5W]	SL-AMB [≈P21/5W]	SL-RED [≈W21W]	SL-FEST 30/38/43 mm	SL-FEST 30/38/43 mm	SL-RED [≈W21W]	SL-RED [≈P21/5W]	SL-RED [≈P21/5W]	SL-WHITE [≈W21W]	
SL-WHITE [≈P21/5W]	SL-WHITE [≈P21/5W]	SL-WHITE [≈P21/5W]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-AMB [≈W21W]	SL-AMB [≈W21W]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-RED [≈W21W]	SL-T16 [≈W16W]	
SL-WHITE [≈W21/5W]	SL-WHITE [≈W21/5W]	SL-WHITE [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	

Ultinon Pro3000 SL

SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	SL-RED [≈P21/5W]	SL-RED [≈P21/5W]	SL-RED [≈P21W]	IL/SL-WHITE [≈W5W]	SL-WHITE [≈W5W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-WHITE [≈P21W]
IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21/5W]	SL-RED [≈W21/5W]	SL-RED [≈W21W]	IL/SL-WHITE Fest 30/38/43 mm	SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-RED [≈W21W]	
CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	

LED adapters

CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]