

# Opciones de iluminación mediante LED para cada uso?



Lámparas delanteras	Luces delanteras de niebla	Luces delanteras de posición	Luces intermitentes delanteras	Luces de salpicadero	Iluminación interior	Luces intermitentes laterales	Luz de guantera	Luces traseras de posición	Luces intermitentes traseras	Luces traseras de niebla	Luz del maletero	Lámpara de placa de matriculación	Tercera luz de frenado	Luces de frenado	Luces de marcha atrás



### Ultinon Pro9000 HL

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		

### Ultinon Pro6000 SL

SL-T10 [≈W5W]	SL-AMB [≈P21W]	SL-AMB [≈P21/5W]	SL-T10 [≈W5W]	SL-T10 [≈W5W]	SL-AMB [≈W5W]	SL-T10 [≈W5W]	SL-RED [≈P21/5W]	SL-AMB [≈P21W]	SL-RED [≈P21W]	SL-T10 [≈W5W]	SL-T10 [≈W5W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-WHITE [≈P21W]
SL-WHITE [≈R5/R10]	SL-AMB [≈W21W]	SL-AMB [≈W21/5W]	SL-FEST 30/38/43 mm	SL-T10 [≈W5W]	SL-FEST 30/38/43 mm	SL-RED [≈W21/5W]	SL-AMB [≈P21/5W]	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-FEST 30/38/43 mm	SL-FEST 30/38/43 mm	SL-RED [≈W21W]	SL-RED [≈P21/5W]	SL-RED [≈P21/5W]	SL-WHITE [≈W21W]
SL-WHITE [≈P21/5W]	SL-WHITE [≈P21/5W]	SL-WHITE [≈P21/5W]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-AMB [≈W21W]	SL-AMB [≈W21W]	SL-AMB [≈W21W]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-T16 [≈W16W]
SL-WHITE [≈W21/5W]	SL-WHITE [≈W21/5W]	SL-WHITE [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]



### Ultinon Pro5000 HL

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		

### Ultinon Pro3000 SL

SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	SL-RED [≈P21/5W]	SL-RED [≈P21/5W]	SL-RED [≈P21W]	IL/SL-WHITE [≈W5W]	SL-WHITE [≈W5W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-WHITE [≈P21W]
IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21/5W]	SL-RED [≈W21/5W]	SL-RED [≈W21W]	SL-WHITE Fest 30/38/43 mm	SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-WHITE [≈W21W]



### Ultinon Essential

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		



### Adaptadores LED

CANbus adapter HL [≈H4], [≈H7]	Light Repair HL [≈H1], [≈H7]	CANbus adapter FL [≈H8/H11/H16]

### Adaptadores LED

CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]