

Opções de iluminação LED para cada uso



Luz de estrada médios	Luzes antinevoeiro	Luz de posição dianteira	Indicadores dianteiros	Luz do painel	Luz interior	Piscas secundárias	Luz portalvas	Luz de posição traseira	Indicadores traseiros	Luzes antinevoeiro traseira	Luz porta bagagens	Luz da matrícula	Luz do travão traseiro	Luzes de stop	Luz marcha atrás



Ultinon Pro9000 HL

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		

Ultinon Pro6000 SL

SL-T10 [≈W5W]	SL-AMB [≈P21W]	SL-AMB [≈P21/5W]	SL-T10 [≈W5W]	SL-T10 [≈W5W]	SL-AMB [≈W5W]	SL-T10 [≈W5W]	SL-RED [≈P21/5W]	SL-AMB [≈P21W]	SL-RED [≈P21W]	SL-T10 [≈W5W]	SL-T10 [≈W5W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-WHITE [≈P21W]
SL-WHITE [≈R5/R10]	SL-AMB [≈W21W]	SL-AMB [≈W21/5W]	SL-FEST 30/38/43 mm	SL-T10 [≈W5W]	SL-FEST 30/38/43 mm	SL-RED [≈W21/5W]	SL-AMB [≈P21/5W]	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-FEST 30/38/43 mm	SL-FEST 30/38/43 mm	SL-RED [≈W21W]	SL-RED [≈P21/5W]	SL-RED [≈P21/5W]	SL-WHITE [≈W21W]
SL-WHITE [≈P21/5W]	SL-WHITE [≈P21/5W]		SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-AMB [≈W21W]	SL-AMB [≈W21W]	SL-AMB [≈W21W]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-WHITE [≈R5/R10]	SL-T16 [≈W16W]
SL-WHITE [≈W21/5W]	SL-WHITE [≈W21/5W]						SL-AMB [≈W21/5W]	SL-AMB [≈W21/5W]					SL-RED [≈W21/5W]	SL-RED [≈W21/5W]	



Ultinon Pro5000 HL

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		

Ultinon Pro3000 SL

SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	IL/SL-WHITE [≈W5W]	SL-RED [≈P21/5W]	SL-RED [≈P21/5W]	SL-RED [≈P21W]	IL/SL-WHITE [≈W5W]	SL-WHITE [≈W5W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-RED [≈P21W]	SL-WHITE [≈P21W]
	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21/5W]	SL-RED [≈W21/5W]	SL-RED [≈W21W]	SL-WHITE Fest 30/38/43 mm	SL-WHITE Fest 30/38/43 mm	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-RED [≈W21W]	SL-WHITE [≈W21W]



Ultinon Essential

HL [≈H1]	HL [≈H3]	HL [≈H4]	HL [≈H7]	FL [≈H8/H11/H16]
HL [≈HB3/HB4]	HL [≈H11]	HL [≈HIR2]		

Adaptadores LED

CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈5W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]	CANbus adapter SL [≈21W]



Adaptadores LED

CANbus adapter HL [≈H4], [≈H7]	Light Repair HL [≈H1], [≈H7]	CANbus adapter FL [≈H8/H11/H16]

*Adaptador LED CANbus 21W incluído no pacote.