

Таблица применимости светодиодных ламп



Фары	Передние противотуманные фары	Передние стояночные фары	Передние указатели поворота	Освещение панели управления	Внутреннее освещение	Боковые указатели поворота	Подсветка бардачка	Задние стояночные фары	Задние указатели поворота	Задний противотуманный фонарь	Подсветка багажника	Освещение номерного знака	Дополнительный стоп-сигнал	Стоп-сигнал	Фонарь заднего хода
Ultinon Pro9000 HL															
HL [=H1], HL [=H3], HL [=H4], HL [=H7], FL [=H8/H11/H16]	HL [=HB3/HB4], HL [=H11], HL [=HIR2]	SL-T10 [=W5W], SL-AMB [=P21W], SL-AMB [=P21/5W]	SL-T10 [=W5W], SL-AMB [=W5W]	SL-T10 [=W5W], SL-AMB [=W5W]	SL-FEST 30/38/43 mm, SL-T10 [=W5W]	SL-T10 [=W5W], SL-AMB [=P21/5W]	SL-T10 [=W5W], SL-RED [=P21/5W]	SL-AMB [=P21W], SL-RED [=P21W]	SL-T10 [=W5W], SL-T10 [=W5W]	SL-T10 [=W5W], SL-T10 [=W5W]	SL-RED [=P21W], SL-RED [=P21W]	SL-RED [=P21W], SL-RED [=P21W]	SL-RED [=P21W], SL-RED [=P21W]	SL-RED [=P21W], SL-RED [=P21W]	SL-WHITE [=P21W], SL-WHITE [=P21W]
Ultinon Pro5000 HL															
HL [=H1], HL [=H3], HL [=H4], HL [=H7], FL [=H8/H11/H16]	HL [=HB3/HB4], HL [=H11], HL [=HIR2]	SL-WHITE [=P21/5W], SL-WHITE [=P21/5W]	SL-WHITE [=R5/R10], SL-WHITE [=R5/R10]	SL-WHITE [=R5/R10], SL-WHITE [=R5/R10]	SL-WHITE [=R5/R10], SL-WHITE [=R5/R10]	SL-WHITE [=R5/R10], SL-WHITE [=R5/R10]	SL-WHITE [=R5/R10], SL-WHITE [=R5/R10]	SL-AMB [=P21W], SL-AMB [=P21W]	SL-AMB [=P21W], SL-AMB [=P21W]	SL-AMB [=P21W], SL-AMB [=P21W]	SL-AMB [=P21W], SL-AMB [=P21W]	SL-AMB [=P21W], SL-AMB [=P21W]	SL-AMB [=P21W], SL-AMB [=P21W]	SL-AMB [=P21W], SL-AMB [=P21W]	SL-AMB [=P21W], SL-AMB [=P21W]
Ultinon Essential															
HL [=H1], HL [=H3], HL [=H4], HL [=H7], FL [=H8/H11/H16]	HL [=HB3/HB4], HL [=H11], HL [=HIR2]	IL/SL-WHITE [=W5W], IL/SL-WHITE [=W5W]	IL/SL-WHITE [=W5W], IL/SL-WHITE [=W5W]	IL/SL-WHITE [=W5W], IL/SL-WHITE [=W5W]	IL/SL-WHITE Fest 30/38/43 mm, IL/SL-WHITE Fest 30/38/43 mm	IL/SL-WHITE [=W5W], IL/SL-WHITE [=W5W]	IL/SL-WHITE [=W5W], IL/SL-WHITE [=W5W]	IL/SL-WHITE [=W5W], IL/SL-WHITE [=W5W]	IL/SL-WHITE [=W5W], IL/SL-WHITE [=W5W]	IL/SL-WHITE [=W5W], IL/SL-WHITE [=W5W]	IL/SL-WHITE [=W5W], IL/SL-WHITE [=W5W]	IL/SL-WHITE [=W5W], IL/SL-WHITE [=W5W]	IL/SL-WHITE [=W5W], IL/SL-WHITE [=W5W]	IL/SL-WHITE [=W5W], IL/SL-WHITE [=W5W]	IL/SL-WHITE [=W5W], IL/SL-WHITE [=W5W]
Адаптеры для светодиодных ламп															
CANbus adapter HL [=H4], [=H7]	Light Repair HL [=H1], [=H7]	CANbus adapter FL [=H8/H11/H16]	CANbus adapter SL [=5W]	CANbus adapter SL [=21W]	CANbus adapter SL [=5W]	CANbus adapter SL [=5W]	CANbus adapter SL [=5W]	CANbus adapter SL [=5W]	CANbus adapter SL [=21W]	CANbus adapter SL [=21W]	CANbus adapter SL [=21W]	CANbus adapter SL [=21W]	CANbus adapter SL [=5W]	CANbus adapter SL [=5W]	CANbus adapter SL [=21W]

