

Which LED lamp do you need?



Original automotive performance in LED

Ultinon Pro9000

Lumileds TopContact OEM LED

2 years **+3** extended warranty

Beam performance: Up to **+250%****

Light color: Up to **5800 K**
Standard: 3100 K

Lifetime: Up to **5000 h**

Available in
LED-HL [~H1], [~H3], [~H4], [~H7], [~HB3/4], [~H11], [~HIR2]
LED-FL [~H8/H11/H16]

The perfect blend of performance and durability

Ultinon Pro5000

Automotive grade LED

2 years **+1** extended warranty

Beam performance: Up to **+160%****

Light color: Up to **5800 K**
Standard: 3100 K

Lifetime: Up to **3000 h**

Available in
LED-HL [~H1], [~H3], [~H4], [~H7], [~HB3/4], [~H11], [~HIR2]
LED-FL [~H8/H11/H16]

Transform your car lights

Ultinon Essential

Beam performance: **Extra performance**

Light color: Up to **6500 K**
Standard: 3100 K

Lifetime: Up to **1500 h**

Available in
LED-HL [~H1], [~H3], [~H4], [~H7], [~HB3/4], [~H11], [~HIR2]
LED-FL [~H8/H11/H16]

Images for illustration purposes only.

* Applies to Ultinon Pro9000 HL [~H4], [~H7], [~HB3/4], [~H11], [~HIR2] and FOG [~H8/H11/H16].
 ** Compared to the minimum legal standard for halogen bulbs. Up to +200% for Ultinon Pro9000 HL [~H1] and [~H3] types.

ECE R37 It is your own responsibility to ensure that the use of the LED retrofit lights complies with applicable local legal requirements.