























# Discover our Xperion 6000 LED work lights





### UV Pillar

Boost light	 <b>500 lm</b>	 Up to <b>4.5 h</b>
Eco light	 <b>250 lm</b>	 Up to <b>10 h</b>
Spotlight	 <b>180 lm</b>	 Up to <b>12 h</b>
Light angle/ flexibility	 <b>100°</b>	 <b>90° rotatable</b>
Special light features		 <b>95 CRI</b>
Fixture	 <b>360° rotatable hook</b>	 <b>2 magnets</b>
Grip/grease resistance	 <b>ABS*, Rubber</b>	 <b>Garage proof</b>
Robustness	 <b>IP65</b>	 <b>IK07</b>
Lithium battery power supply	 <b>&lt;4.5 h</b>	 <b>USB Type-C</b>
Additional accessories**	 <b>Find My Device</b>	 <b>Multi Dock Station</b>

### Pillar






Boost light	 <b>500 lm</b>	 Up to <b>4.5 h</b>
Eco light	 <b>250 lm</b>	 Up to <b>10 h</b>
Spotlight	 <b>180 lm</b>	 Up to <b>12 h</b>
Light angle/ flexibility	 <b>100°</b>	 <b>90° rotatable</b>
Special light features	<b>Foldable</b>	
Fixture	 <b>360° rotatable hook</b>	 <b>2 magnets</b>
Grip/grease resistance	 <b>ABS*, Rubber</b>	 <b>Garage proof</b>
Robustness	 <b>IP65</b>	 <b>IK07</b>
Lithium battery power supply	 <b>&lt;4.5 h</b>	 <b>USB Type-C</b>
Additional accessories**	 <b>Find My Device</b>	 <b>Multi Dock Station</b>



















### Pocket






Boost light	 <b>300 lm</b>	 Up to <b>3.5 h</b>
Eco light	 <b>150 lm</b>	 Up to <b>7 h</b>
Spotlight	 <b>100 lm</b>	 Up to <b>10 h</b>
Light angle/ flexibility	 <b>110°</b>	
Special light features	<b>25 cm flexible hose, rotatable in all directions</b>	
Fixture	 <b>360° rotatable hook</b>	 <b>1 magnet</b>
Grip/grease resistance	 <b>ABS*, Rubber</b>	 <b>Garage proof</b>
Robustness	 <b>IP65</b>	 <b>IK07</b>
Lithium battery power supply	 <b>&lt;3.5 h</b>	 <b>USB Type-C</b>
Additional accessories**	 <b>Multi Dock Station</b>	
















### Slim

Boost light	 <b>500 lm</b>	 Up to <b>4.5 h</b>
Eco light	 <b>250 lm</b>	 Up to <b>7 h</b>
Spotlight	 <b>150 lm</b>	 Up to <b>9 h</b>
Light angle/ flexibility	 <b>100°</b>	 <b>270° rotatable</b>
Special light features	<b>180° foldable</b>	
Fixture	 <b>360° rotatable hook</b>	 <b>2 magnets</b>
Grip/grease resistance	 <b>ABS*, Rubber</b>	 <b>Garage proof</b>
Robustness	 <b>IP54</b>	 <b>IK07</b>
Lithium battery power supply	 <b>&lt;4 h</b>	 <b>USB Type-C</b>
Additional accessories**	 <b>Find My Device</b>	 <b>Multi Dock Station</b>

### Line

Boost light	 <b>300 lm</b>	 Up to <b>4.5 h</b>
Eco light	 <b>150 lm</b>	 Up to <b>8 h</b>
Spotlight	 <b>120 lm</b>	 Up to <b>9 h</b>
Light angle/ flexibility	 <b>110°</b>	
Fixture	 <b>360° rotatable hook</b>	 <b>1 magnet</b>
Grip/grease resistance	 <b>ABS*</b>	 <b>Garage proof</b>
Robustness	 <b>IP65</b>	 <b>IK07</b>
Lithium battery power supply	 <b>&lt;3.5 h</b>	 <b>USB Type-C</b>

\*Acrylonitrile-butadiene-styrene copolymer

\*\*Accessories to buy separately, except for the Philips Xperion 6000 UV Pillar which already includes the Find My Device function